

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001712

Luminaire Tested: SA4XXDIP-B795D1035UB2750-4F0-XX-W2A-D_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001712
REPORT IS A COMBINATION OF REPORTS P996334 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B795D1035UB2750-4F0-XX-W2A-D_3000K
Description: Define 4 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7347.0 lumens
Efficiency: N/A
Efficacy: 114.1 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 64.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001712

CATALOG NUMBER: SA4XXDIP-B795D1035UB2750-4F0-XX-W2A-D_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1001712

CATALOG NUMBER: SA4XXDIP-B795D1035UB2750-4F0-XX-W2A-D_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	48	48	48
1	95	90	86	82	86	82	79	76	67	65	63	54	52	50	41	40	39
2	86	78	72	67	78	71	66	61	59	55	51	47	44	41	36	34	32
3	78	69	61	55	71	63	56	51	51	46	42	41	37	34	31	29	27
4	71	60	52	46	65	55	48	43	45	40	36	36	32	29	28	25	23
5	65	54	45	39	59	49	42	36	40	35	31	32	28	25	25	22	20
6	60	48	40	34	54	44	37	31	36	31	27	29	25	22	22	20	17
7	56	43	35	30	50	40	32	27	33	27	23	26	22	19	20	17	15
8	51	39	31	26	47	36	29	24	30	24	21	24	20	17	19	16	14
9	48	36	28	23	43	33	26	21	27	22	18	22	18	15	17	14	12
10	45	33	25	20	41	30	23	19	25	20	16	20	16	14	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7788	7788	7788
5°	7809	7585	7599
10°	7758	7435	7414
15°	7686	7268	7206
20°	7578	7086	7005
25°	7457	6886	6787
30°	7325	6687	6565
35°	7177	6485	6367
40°	7059	6289	6162
45°	6882	6107	5982
50°	6732	5899	5791
55°	6577	5698	5572
60°	6336	5450	5365
65°	6071	5181	5115
70°	5749	4874	4828
75°	5300	4533	4554
80°	4796	4186	4267
85°	4126	3836	4035

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6882 cd/sqm

TEST NUMBER: P1001712

CATALOG NUMBER: SA4XXDIP-B795D1035UB2750-4F0-XX-W2A-D_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.5	1.2
10°-20°	259.3	3.5
20°-30°	392.0	5.3
30°-40°	474.3	6.5
40°-50°	501.4	6.8
50°-60°	471.9	6.4
60°-70°	391.5	5.3
70°-80°	274.8	3.7
80°-90°	157.6	2.1
90°-100°	136.1	1.9
100°-110°	357.1	4.9
110°-120°	597.3	8.1
120°-130°	725.9	9.9
130°-140°	760.1	10.3
140°-150°	702.6	9.6
150°-160°	564.8	7.7
160°-170°	364.2	5.0
170°-180°	125.5	1.7
0°-30°	741.8	10.1
0°-40°	1216.0	16.6
0°-60°	2189.2	29.8
0°-90°	3013.2	41.0
90°-120°	1090.6	14.8
90°-150°	3279.2	44.6
90°-180°	4334.0	59.0
0°-180°	7347.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	955	955	955	955	955	
5°	956	953	945	954	953	91
15°	916	918	914	924	923	258
25°	838	845	848	860	861	386
35°	734	746	757	772	775	459
45°	612	632	652	670	676	473
55°	479	502	534	555	562	427
65°	332	366	402	429	437	329
75°	184	224	268	298	308	195
85°	57	102	150	182	192	59
90°	20	74	128	165	175	15
95°	68	70	115	150	160	78
105°	307	334	379	414	388	322
115°	562	574	608	633	641	553
125°	785	788	812	836	843	701
135°	970	970	981	1000	1008	748
145°	1118	1120	1120	1127	1133	699
155°	1224	1225	1222	1226	1223	565
165°	1292	1287	1287	1294	1286	365
175°	1321	1315	1316	1325	1313	126
180°	1321	1321	1321	1321	1321	

TEST NUMBER: P1001712

CATALOG NUMBER: SA4XXDIP-B795D1035UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	955.0	955.0	955.0	955.0	955.0
2.5°	959.3	956.1	947.5	955.0	953.9
5°	956.1	952.9	945.4	953.9	952.9
7.5°	949.7	947.5	941.1	950.7	949.7
10°	941.1	940.0	934.7	944.3	943.2
12.5°	929.3	929.3	926.1	934.7	934.7
15°	916.5	917.6	914.4	924.0	922.9
17.5°	899.4	902.6	901.5	911.2	910.1
20°	881.2	884.4	885.5	896.2	896.2
22.5°	860.9	865.2	867.3	878.0	880.1
25°	838.4	844.9	848.1	859.8	860.9
27.5°	813.8	823.5	827.7	838.4	839.5
30°	789.2	797.8	805.3	817.0	819.2
32.5°	762.5	773.2	781.8	795.7	797.8
35°	733.6	746.5	757.2	772.1	775.3
37.5°	704.8	719.7	732.6	747.5	750.7
40°	677.0	690.9	705.8	721.9	726.1
42.5°	644.9	660.9	679.1	697.3	700.5
45°	611.7	632.0	652.4	670.5	675.9
47.5°	580.7	601.0	624.5	642.7	649.1
50°	546.5	570.0	593.5	614.9	621.3
52.5°	512.3	535.8	563.6	585.0	591.4
55°	479.1	501.6	533.6	555.0	561.5
57.5°	441.7	469.5	500.5	526.2	531.5
60°	405.3	433.1	468.4	493.0	501.6
62.5°	370.0	401.0	436.3	460.9	469.5
65°	331.5	365.7	402.1	428.8	437.4
67.5°	295.2	331.5	370.0	396.8	405.3
70°	257.7	294.1	334.7	363.6	371.1
72.5°	221.4	258.8	302.6	330.5	339.0
75°	183.9	223.5	268.4	298.4	308.0
77.5°	148.7	190.4	237.4	267.4	278.1
80°	116.6	159.3	206.4	238.5	247.0
82.5°	84.5	129.4	176.5	209.6	219.2
85°	56.7	101.6	149.7	181.8	192.5
87.5°	35.3	79.1	126.2	157.2	166.8
90°	20.1	73.7	127.6	164.6	175.0
92.5°	30.8	66.3	120.3	156.1	164.7
95°	68.3	70.0	114.7	149.6	160.2
97.5°	116.6	169.3	109.4	142.2	152.8
100°	173.9	219.4	124.8	136.9	145.3
102.5°	239.1	274.4	326.9	132.4	141.0
105°	307.0	334.4	378.9	414.5	387.5
107.5°	371.3	392.4	436.8	468.5	480.0
110°	435.5	453.4	496.8	523.4	534.8

TEST NUMBER: P1001712

CATALOG NUMBER: SA4XXDIP-B795D1035UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	497.6	516.4	553.6	576.2	588.7
115°	561.8	574.3	607.6	633.1	640.6
117.5°	620.1	630.4	665.5	687.0	695.5
120°	678.3	685.5	715.5	738.9	745.4
122.5°	733.6	735.6	766.4	788.8	794.4
125°	785.0	787.8	812.5	835.9	843.3
127.5°	835.4	835.3	861.6	879.8	886.3
130°	882.7	882.6	902.6	922.9	929.3
132.5°	927.2	928.0	944.9	964.1	969.5
135°	970.5	969.5	981.0	1000.1	1008.5
137.5°	1010.0	1009.0	1018.2	1036.3	1040.6
140°	1048.6	1049.6	1052.5	1069.4	1075.8
142.5°	1082.2	1086.1	1086.0	1099.8	1104.0
145°	1117.7	1119.6	1119.6	1127.0	1133.3
147.5°	1145.4	1150.2	1149.3	1151.3	1156.5
150°	1176.1	1178.9	1177.9	1177.9	1178.9
152.5°	1200.6	1203.6	1201.6	1203.6	1202.6
155°	1224.4	1225.4	1222.4	1226.3	1223.4
157.5°	1245.1	1245.1	1241.2	1246.1	1241.2
160°	1262.9	1259.9	1258.9	1264.9	1258.9
162.5°	1278.7	1274.8	1273.8	1279.7	1272.8
165°	1291.6	1286.6	1286.6	1294.5	1285.6
167.5°	1302.4	1297.5	1296.5	1305.4	1295.5
170°	1311.3	1305.4	1306.4	1314.3	1304.4
172.5°	1317.3	1311.3	1312.3	1320.2	1309.3
175°	1321.2	1315.3	1316.3	1325.2	1313.3
177.5°	1324.2	1317.3	1319.2	1327.1	1315.3
180°	1321.2	1321.2	1321.2	1321.2	1321.2

(END OF REPORT)