

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001716

Luminaire Tested: SA4XXDIP-B795D1035UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001716
REPORT IS A COMBINATION OF REPORTS P996338 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B795D1035UB2750-4F0-XX-W2A-F_2700K
Description: Define 4 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7452.0 lumens
Efficiency: N/A
Efficacy: 115.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 64.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001716

CATALOG NUMBER: SA4XXDIP-B795D1035UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1001716

CATALOG NUMBER: SA4XXDIP-B795D1035UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52
1	97	92	89	85	89	85	82	79	71	68	66	58	56	55	46	45	44
2	88	81	75	69	81	74	69	64	62	58	55	51	48	46	40	39	37
3	80	71	64	58	73	65	59	54	55	50	46	45	42	39	36	33	31
4	73	63	55	49	67	58	51	46	49	43	39	40	36	33	32	29	27
5	67	56	48	42	62	52	44	39	43	38	34	36	32	29	29	26	24
6	62	50	42	36	57	46	39	34	39	34	29	32	28	25	26	23	21
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	24	21	18
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	17
9	50	37	30	25	45	35	28	23	30	24	21	25	21	18	20	17	15
10	46	34	27	22	42	32	25	21	27	22	19	23	19	16	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10789	10789	10789
5°	10798	10479	10492
10°	10706	10188	10117
15°	10553	9842	9694
20°	10357	9468	9255
25°	10136	9072	8784
30°	9870	8645	8267
35°	9595	8208	7766
40°	9307	7737	7234
45°	9005	7265	6737
50°	8673	6807	6186
55°	8310	6272	5639
60°	7938	5686	5069
65°	7514	5082	4427
70°	7025	4354	3738
75°	6294	3509	2994
80°	5363	2537	2106
85°	4162	1412	1134

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9005 cd/sqm

TEST NUMBER: P1001716

CATALOG NUMBER: SA4XXDIP-B795D1035UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.7	1.7
10°-20°	351.3	4.7
20°-30°	517.1	6.9
30°-40°	601.1	8.1
40°-50°	601.0	8.1
50°-60°	525.7	7.1
60°-70°	390.3	5.2
70°-80°	221.4	3.0
80°-90°	66.1	0.9
90°-100°	43.5	0.6
100°-110°	286.4	3.8
110°-120°	546.8	7.3
120°-130°	694.2	9.3
130°-140°	742.6	10.0
140°-150°	694.4	9.3
150°-160°	560.0	7.5
160°-170°	361.1	4.8
170°-180°	124.5	1.7
0°-30°	993.1	13.3
0°-40°	1594.2	21.4
0°-60°	2720.9	36.5
0°-90°	3398.7	45.6
90°-120°	876.6	11.8
90°-150°	3007.8	40.4
90°-180°	4053.0	54.4
0°-180°	7452.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1323	1323	1323	1323	1323	
5°	1322	1318	1306	1318	1316	125
15°	1258	1254	1238	1245	1242	355
25°	1140	1132	1117	1118	1114	524
35°	981	973	958	951	946	613
45°	800	793	776	764	761	617
55°	605	602	587	575	568	542
65°	410	405	394	384	378	406
75°	218	213	208	204	202	232
85°	57	57	55	55	54	62
90°	3	14	22	27	29	7
95°	54	21	22	27	28	66
105°	295	301	306	314	279	309
115°	551	554	553	554	554	542
125°	774	778	776	779	780	691
135°	960	959	963	965	967	740
145°	1107	1110	1110	1111	1113	692
155°	1214	1215	1212	1216	1213	560
165°	1280	1276	1276	1283	1275	362
175°	1310	1304	1305	1314	1302	125
180°	1310	1310	1310	1310	1310	

TEST NUMBER: P1001716

CATALOG NUMBER: SA4XXDIP-B795D1035UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1323.1	1323.1	1323.1	1323.1	1323.1
2.5°	1327.3	1324.2	1312.5	1323.1	1322.0
5°	1322.0	1317.8	1306.1	1317.8	1315.7
7.5°	1312.5	1308.3	1295.5	1305.1	1304.0
10°	1298.7	1294.5	1280.7	1289.2	1287.1
12.5°	1280.7	1276.5	1261.6	1271.2	1268.0
15°	1258.4	1254.2	1238.3	1244.6	1241.5
17.5°	1233.0	1227.7	1212.8	1217.1	1215.0
20°	1204.4	1199.1	1183.2	1186.3	1184.2
22.5°	1173.6	1166.2	1150.3	1156.7	1152.4
25°	1139.7	1132.3	1117.4	1118.5	1114.2
27.5°	1101.5	1094.1	1080.3	1078.2	1072.9
30°	1063.4	1054.9	1041.1	1036.9	1031.6
32.5°	1023.1	1015.7	1000.8	995.5	990.2
35°	980.7	973.2	958.4	951.0	945.7
37.5°	936.1	929.8	913.9	906.5	899.0
40°	892.7	884.2	868.3	857.7	852.4
42.5°	846.0	841.8	823.8	811.0	807.9
45°	800.4	793.0	776.1	764.4	761.2
47.5°	752.7	747.4	731.5	718.8	710.3
50°	704.0	699.7	684.9	670.0	663.7
52.5°	656.3	650.9	635.0	622.3	613.8
55°	605.4	602.2	587.3	574.6	568.3
57.5°	557.7	554.5	539.6	526.9	520.5
60°	507.8	502.5	488.7	479.2	473.9
62.5°	459.1	454.8	440.0	431.5	426.2
65°	410.3	405.0	394.4	383.8	378.5
67.5°	360.5	356.2	345.6	335.0	334.0
70°	314.9	307.5	299.0	290.5	287.3
72.5°	266.1	258.7	252.3	246.0	242.8
75°	218.4	213.1	207.8	203.6	202.5
77.5°	171.7	169.6	164.3	163.3	160.1
80°	130.4	127.2	125.1	123.0	121.9
82.5°	90.1	89.1	89.1	88.0	86.9
85°	57.2	57.2	55.1	55.1	54.1
87.5°	27.6	26.5	25.4	25.4	25.4
90°	2.9	13.7	21.6	27.4	29.4
92.5°	14.7	12.7	20.6	26.5	26.5
95°	53.9	20.6	21.6	27.4	28.4
97.5°	102.9	124.4	21.6	26.5	27.4
100°	160.7	178.3	43.1	26.5	27.4
102.5°	225.3	237.1	248.9	28.4	28.4
105°	294.9	300.8	305.7	314.5	279.2
107.5°	358.6	361.5	368.4	373.3	377.2
110°	423.2	426.2	432.1	434.0	437.0



TEST NUMBER: P1001716

CATALOG NUMBER: SA4XXDIP-B795D1035UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	485.9	491.8	493.8	492.8	496.7
115°	550.6	553.5	552.6	554.5	554.5
117.5°	608.4	612.3	615.3	614.3	614.3
120°	667.2	671.1	670.1	672.1	670.1
122.5°	722.1	724.0	726.0	727.0	725.0
125°	774.0	777.9	775.9	778.9	779.9
127.5°	824.0	824.9	829.8	828.9	827.9
130°	872.0	872.9	875.9	876.9	876.9
132.5°	916.0	918.0	921.9	922.9	921.9
135°	960.1	959.2	963.1	965.0	967.0
137.5°	999.3	999.3	1004.2	1006.2	1005.2
140°	1037.5	1039.5	1041.5	1044.4	1045.4
142.5°	1071.8	1075.7	1076.7	1078.7	1078.7
145°	1107.1	1110.0	1110.0	1111.0	1113.0
147.5°	1134.5	1140.4	1139.4	1140.4	1141.4
150°	1164.9	1168.8	1167.8	1167.8	1168.8
152.5°	1190.4	1193.3	1191.4	1193.3	1192.3
155°	1213.9	1214.9	1211.9	1215.8	1212.9
157.5°	1234.5	1234.5	1230.5	1235.4	1230.5
160°	1252.1	1249.2	1248.2	1254.1	1248.2
162.5°	1267.8	1263.9	1262.9	1268.8	1261.9
165°	1280.5	1275.6	1275.6	1283.4	1274.6
167.5°	1291.3	1286.4	1285.4	1294.2	1284.4
170°	1300.1	1294.2	1295.2	1303.0	1293.2
172.5°	1306.0	1300.1	1301.1	1308.9	1298.1
175°	1309.9	1304.0	1305.0	1313.8	1302.1
177.5°	1312.8	1306.0	1307.9	1315.8	1304.0
180°	1309.9	1309.9	1309.9	1309.9	1309.9

(END OF REPORT)