

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000126

Luminaire Tested: SA2XXRDIP-B865D330UB35-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000126
REPORT IS A COMBINATION OF REPORTS P988686 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B865D330UB35-4F0-XX-W2A-F4
Description: Define 2 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4305.5 lumens
Efficiency: N/A
Efficacy: 76.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 56.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000126

CATALOG NUMBER: SA2XXRDIP-B865D330UB35-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1000126

CATALOG NUMBER: SA2XXRDIP-B865D330UB35-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	106	106	106	106	94	94	94	84	84	84	74	74	74
1	103	99	95	92	97	94	90	87	84	81	79	75	73	71	67	66	64
2	94	87	81	76	89	83	77	73	74	70	67	67	64	61	60	57	55
3	87	77	70	64	82	73	67	62	66	61	57	60	56	52	54	50	48
4	80	69	61	55	75	66	59	53	59	54	49	54	49	45	48	45	42
5	73	62	54	48	69	59	52	46	54	48	43	49	44	40	44	40	37
6	68	56	48	42	64	53	46	41	49	43	38	44	39	35	40	36	33
7	63	51	43	37	60	49	41	36	44	38	34	40	35	32	37	33	29
8	59	46	39	33	56	44	37	32	41	35	30	37	32	29	34	30	27
9	55	43	35	30	52	41	34	29	38	32	28	34	29	26	32	27	24
10	51	39	32	27	49	38	31	27	35	29	25	32	27	24	29	25	22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	23168	23168	23168
5°	23205	22040	21878
10°	22975	20905	20215
15°	22660	19562	18318
20°	22242	18036	16337
25°	21815	16472	14523
30°	21240	14947	12542
35°	20676	13409	10840
40°	20106	11900	9088
45°	19440	10340	7560
50°	18751	8839	6156
55°	18034	7337	4886
60°	17202	5867	3698
65°	16243	4474	3006
70°	15084	3244	2390
75°	13633	2476	1826
80°	11529	1676	1226
85°	8052	768	593

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 19440 cd/sqm

TEST NUMBER: P1000126

CATALOG NUMBER: SA2XXRDIP-B865D330UB35-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	137.2	3.2
10°-20°	376.6	8.7
20°-30°	528.7	12.3
30°-40°	576.3	13.4
40°-50°	529.7	12.3
50°-60°	416.0	9.7
60°-70°	270.7	6.3
70°-80°	139.4	3.2
80°-90°	36.8	0.9
90°-100°	75.3	1.7
100°-110°	254.4	5.9
110°-120°	267.4	6.2
120°-130°	219.9	5.1
130°-140°	176.7	4.1
140°-150°	133.5	3.1
150°-160°	93.9	2.2
160°-170°	55.3	1.3
170°-180°	18.0	0.4
0°-30°	1042.4	24.2
0°-40°	1618.7	37.6
0°-60°	2564.3	59.6
0°-90°	3011.2	69.9
90°-120°	597.1	13.9
90°-150°	1127.2	26.2
90°-180°	1294.0	30.1
0°-180°	4305.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1464	1464	1464	1464	1464	
5°	1464	1457	1440	1452	1448	139
15°	1392	1378	1332	1307	1294	392
25°	1264	1221	1134	1080	1060	581
35°	1089	1021	905	821	792	681
45°	890	801	662	568	536	687
55°	677	574	430	351	326	605
65°	457	350	230	185	182	453
75°	244	151	106	97	95	258
85°	57	29	25	25	25	65
90°	0	5	12	12	12	4
95°	12	31	140	53	41	13
105°	44	66	264	473	402	46
115°	77	97	221	457	529	76
125°	107	127	213	370	430	95
135°	126	150	210	311	356	97
145°	144	165	209	260	284	90
155°	163	176	203	230	239	75
165°	178	183	195	206	210	50
175°	185	185	187	189	189	18
180°	186	186	186	186	186	

TEST NUMBER: P1000126

CATALOG NUMBER: SA2XXRDIP-B865D330UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1463.6	1463.6	1463.6	1463.6	1463.6
2.5°	1470.2	1463.6	1449.0	1462.2	1459.6
5°	1463.6	1456.9	1439.7	1451.6	1447.7
7.5°	1451.6	1443.7	1425.2	1430.4	1423.8
10°	1435.7	1426.5	1400.0	1396.0	1388.1
12.5°	1415.9	1404.0	1368.2	1360.3	1345.7
15°	1392.0	1377.5	1332.4	1307.3	1294.0
17.5°	1364.2	1343.0	1287.4	1258.3	1237.1
20°	1332.4	1305.9	1239.7	1206.6	1177.5
22.5°	1298.0	1267.5	1190.7	1145.7	1125.8
25°	1263.6	1221.2	1133.8	1079.5	1059.6
27.5°	1222.5	1177.5	1080.8	1018.5	988.1
30°	1178.8	1128.5	1022.5	955.0	919.2
32.5°	1136.4	1075.5	966.9	887.4	854.3
35°	1088.7	1021.2	904.6	821.2	792.0
37.5°	1042.4	969.5	846.3	755.0	721.8
40°	993.4	913.9	785.4	691.4	656.9
42.5°	943.0	858.3	724.5	626.5	593.4
45°	890.1	801.3	662.2	568.2	536.4
47.5°	839.7	745.7	602.6	508.6	479.5
50°	784.1	690.1	544.4	453.0	425.2
52.5°	729.8	630.5	488.7	401.3	376.2
55°	676.8	573.5	430.5	351.0	325.8
57.5°	622.5	516.6	378.8	304.6	283.4
60°	566.9	460.9	324.5	257.0	235.8
62.5°	512.6	406.6	278.1	214.6	204.0
65°	456.9	349.7	230.5	185.4	181.5
67.5°	404.0	296.7	185.4	162.9	158.9
70°	348.3	245.0	153.6	140.4	135.1
72.5°	295.4	197.3	128.5	117.9	115.2
75°	243.7	151.0	106.0	96.7	95.4
77.5°	192.1	107.3	83.4	78.1	75.5
80°	144.4	76.8	63.6	58.3	58.3
82.5°	100.7	51.7	43.7	41.1	41.1
85°	57.0	29.1	25.2	25.2	25.2
87.5°	21.2	10.6	10.6	9.3	9.3
90°	0.4	4.8	12.1	11.6	11.8
92.5°	5.4	17.0	55.0	25.4	21.8
95°	12.5	30.7	139.9	52.8	40.7
97.5°	18.6	40.5	228.1	106.0	68.2
100°	27.5	49.6	282.0	211.2	127.8
102.5°	35.7	57.8	283.8	357.0	249.2
105°	43.6	65.7	264.5	472.8	402.3
107.5°	52.1	73.5	246.7	514.8	505.5
110°	60.7	81.6	234.5	508.0	547.6



TEST NUMBER: P1000126

CATALOG NUMBER: SA2XXRDIP-B865D330UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	68.5	89.2	226.7	485.0	546.9
115°	76.8	96.9	221.3	456.8	529.4
117.5°	85.3	104.6	218.5	429.8	503.0
120°	93.2	112.1	216.0	405.8	477.7
122.5°	100.7	119.8	214.6	387.0	451.2
125°	107.1	126.7	212.8	370.0	429.5
127.5°	112.5	133.4	211.7	355.6	409.1
130°	117.1	139.2	211.0	341.0	392.3
132.5°	121.4	144.9	210.6	325.8	374.9
135°	125.7	149.9	210.3	311.0	355.9
137.5°	129.6	154.2	210.3	296.0	337.7
140°	134.2	158.2	209.9	282.8	318.8
142.5°	138.9	161.4	209.9	270.0	299.9
145°	143.5	165.0	209.2	259.7	284.2
147.5°	148.5	167.8	208.1	250.6	270.3
150°	153.5	170.6	207.1	242.8	258.1
152.5°	158.5	173.5	205.3	236.2	247.8
155°	163.1	176.2	203.1	229.8	238.8
157.5°	167.1	178.3	201.0	223.7	231.0
160°	171.0	180.4	198.8	217.6	223.5
162.5°	174.9	182.0	197.1	211.9	216.3
165°	177.8	183.1	194.6	206.4	209.6
167.5°	180.3	184.2	192.4	201.4	203.1
170°	182.8	184.8	190.6	196.8	197.4
172.5°	184.2	185.2	188.5	192.6	192.8
175°	185.3	185.4	187.1	189.4	188.9
177.5°	186.0	185.6	185.6	187.1	186.0
180°	185.6	185.6	185.6	185.6	185.6

(END OF REPORT)