

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001771

Luminaire Tested: SA4XXDIP-B795D1205UB2750-4F0-XX-W2A-D_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001771
REPORT IS A COMBINATION OF REPORTS P996393 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B795D1205UB2750-4F0-XX-W2A-D_2700K
Description: Define 4 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7994.0 lumens
Efficiency: N/A
Efficacy: 112.8 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 70.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001771

CATALOG NUMBER: SA4XXDIP-B795D1205UB2750-4F0-XX-W2A-D_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1001771

CATALOG NUMBER: SA4XXDIP-B795D1205UB2750-4F0-XX-W2A-D_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	76	76	76	60	60	60	45	45	45
1	94	90	86	82	85	81	78	75	66	63	61	51	50	48	38	37	36
2	85	78	71	66	77	71	65	61	57	53	50	45	42	40	33	31	30
3	78	68	61	55	70	62	55	50	50	45	41	39	36	33	29	27	25
4	71	60	52	46	64	55	48	42	44	39	35	35	31	28	26	23	21
5	65	53	45	39	58	48	41	36	39	34	30	31	27	24	23	20	18
6	60	48	39	34	54	43	36	31	35	30	26	28	24	21	21	18	16
7	55	43	35	29	50	39	32	27	32	27	23	25	21	18	19	16	14
8	51	39	31	26	46	35	29	24	29	24	20	23	19	16	17	15	13
9	47	35	28	23	43	32	26	21	27	21	18	21	17	15	16	13	11
10	44	32	25	20	40	29	23	19	24	19	16	19	16	13	15	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7721	7721	7721
5°	7742	7519	7533
10°	7692	7371	7350
15°	7619	7205	7144
20°	7513	7025	6944
25°	7393	6827	6729
30°	7263	6630	6508
35°	7116	6428	6313
40°	6997	6236	6110
45°	6824	6054	5931
50°	6674	5848	5741
55°	6520	5650	5523
60°	6281	5403	5319
65°	6020	5136	5071
70°	5700	4833	4786
75°	5256	4494	4514
80°	4754	4149	4230
85°	4090	3803	3999

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 6824 cd/sqm

TEST NUMBER: P1001771

CATALOG NUMBER: SA4XXDIP-B795D1205UB2750-4F0-XX-W2A-D_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.7	1.1
10°-20°	257.0	3.2
20°-30°	388.6	4.9
30°-40°	470.2	5.9
40°-50°	497.1	6.2
50°-60°	467.8	5.9
60°-70°	388.2	4.9
70°-80°	272.4	3.4
80°-90°	156.7	2.0
90°-100°	142.5	1.8
100°-110°	404.2	5.1
110°-120°	687.9	8.6
120°-130°	841.3	10.5
130°-140°	883.7	11.1
140°-150°	818.1	10.2
150°-160°	658.0	8.2
160°-170°	424.3	5.3
170°-180°	146.2	1.8
0°-30°	735.4	9.2
0°-40°	1205.6	15.1
0°-60°	2170.4	27.2
0°-90°	2987.8	37.4
90°-120°	1234.6	15.4
90°-150°	3777.7	47.3
90°-180°	5006.0	62.6
0°-180°	7994.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	947	947	947	947	947	
5°	948	945	937	946	945	90
15°	909	910	906	916	915	256
25°	831	838	841	852	854	383
35°	727	740	751	766	769	455
45°	606	627	647	665	670	469
55°	475	497	529	550	557	423
65°	329	363	399	425	434	326
75°	182	222	266	296	305	194
85°	56	101	148	180	191	59
90°	20	76	130	168	179	15
95°	77	73	118	153	164	89
105°	356	384	429	466	433	373
115°	653	666	699	725	732	644
125°	914	917	942	965	973	816
135°	1130	1129	1141	1160	1169	871
145°	1302	1304	1304	1312	1318	814
155°	1426	1428	1424	1429	1425	658
165°	1505	1499	1499	1508	1498	425
175°	1539	1532	1533	1544	1530	147
180°	1539	1539	1539	1539	1539	

TEST NUMBER: P1001771

CATALOG NUMBER: SA4XXDIP-B795D1205UB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	946.8	946.8	946.8	946.8	946.8
2.5°	951.0	947.9	939.4	946.8	945.7
5°	947.9	944.7	937.2	945.7	944.7
7.5°	941.5	939.4	933.0	942.6	941.5
10°	933.0	931.9	926.6	936.2	935.1
12.5°	921.3	921.3	918.2	926.6	926.6
15°	908.6	909.7	906.5	916.0	915.0
17.5°	891.7	894.8	893.8	903.3	902.3
20°	873.6	876.8	877.9	888.5	888.5
22.5°	853.5	857.7	859.9	870.5	872.6
25°	831.2	837.6	840.8	852.4	853.5
27.5°	806.8	816.4	820.6	831.2	832.3
30°	782.5	790.9	798.4	810.0	812.1
32.5°	755.9	766.6	775.0	788.8	790.9
35°	727.3	740.0	750.6	765.5	768.7
37.5°	698.7	713.5	726.3	741.1	744.3
40°	671.1	684.9	699.8	715.7	719.9
42.5°	639.3	655.2	673.3	691.3	694.5
45°	606.5	626.6	646.7	664.8	670.1
47.5°	575.7	595.9	619.2	637.2	643.6
50°	541.8	565.1	588.4	609.6	616.0
52.5°	507.9	531.2	558.7	579.9	586.3
55°	475.0	497.3	529.1	550.3	556.6
57.5°	437.9	465.4	496.2	521.6	526.9
60°	401.8	429.4	464.4	488.8	497.3
62.5°	366.8	397.6	432.6	457.0	465.4
65°	328.7	362.6	398.6	425.2	433.6
67.5°	292.6	328.7	366.8	393.3	401.8
70°	255.5	291.6	331.9	360.5	367.9
72.5°	219.5	256.6	300.0	327.6	336.1
75°	182.4	221.6	266.1	295.8	305.3
77.5°	147.4	188.7	235.4	265.1	275.7
80°	115.6	158.0	204.6	236.4	244.9
82.5°	83.8	128.3	174.9	207.8	217.3
85°	56.2	100.7	148.4	180.2	190.8
87.5°	35.0	78.5	125.1	155.9	165.4
90°	20.5	75.5	130.3	167.9	178.7
92.5°	33.2	68.0	122.8	159.4	167.9
95°	77.1	73.0	117.5	153.1	163.8
97.5°	133.6	189.7	112.2	145.6	156.2
100°	200.5	248.7	131.3	140.3	148.8
102.5°	276.5	313.6	367.7	136.2	144.7
105°	356.0	384.1	429.2	466.0	433.1
107.5°	430.9	452.4	497.6	529.8	541.8
110°	505.8	524.1	568.1	594.8	606.7

TEST NUMBER: P1001771

CATALOG NUMBER: SA4XXDIP-B795D1205UB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	578.4	598.0	635.3	657.6	670.6
115°	653.4	666.3	699.1	724.8	732.2
117.5°	721.3	732.2	767.5	788.6	797.1
120°	789.3	797.1	826.6	850.1	856.3
122.5°	853.8	856.1	887.0	909.3	914.5
125°	913.7	917.3	941.5	965.0	972.6
127.5°	972.4	972.5	999.5	1017.4	1023.7
130°	1027.8	1027.8	1048.3	1068.6	1074.9
132.5°	1079.6	1080.8	1098.1	1117.4	1122.5
135°	1130.3	1129.2	1141.2	1160.5	1169.2
137.5°	1176.4	1175.4	1185.3	1203.5	1207.7
140°	1221.3	1222.6	1225.9	1243.1	1249.6
142.5°	1260.5	1265.2	1265.2	1279.2	1283.4
145°	1302.0	1304.3	1304.3	1311.9	1318.4
147.5°	1334.2	1340.0	1338.9	1341.1	1346.5
150°	1369.9	1373.4	1372.3	1372.3	1373.4
152.5°	1398.7	1402.2	1399.9	1402.2	1401.1
155°	1426.4	1427.5	1424.1	1428.7	1425.2
157.5°	1450.6	1450.6	1445.9	1451.7	1445.9
160°	1471.3	1467.8	1466.7	1473.6	1466.7
162.5°	1489.7	1485.1	1483.9	1490.8	1482.8
165°	1504.7	1498.9	1498.9	1508.1	1497.8
167.5°	1517.3	1511.6	1510.4	1520.8	1509.3
170°	1527.7	1520.8	1521.9	1531.1	1519.6
172.5°	1534.6	1527.7	1528.8	1538.0	1525.4
175°	1539.2	1532.3	1533.4	1543.8	1530.0
177.5°	1542.7	1534.6	1536.9	1546.1	1532.3
180°	1539.2	1539.2	1539.2	1539.2	1539.2

(END OF REPORT)