

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000171

Luminaire Tested: SA2XXRDIP-B865D530UB40-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000171
REPORT IS A COMBINATION OF REPORTS P988731 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B865D530UB40-4F0-XX-W2A-F1
Description: Define 2 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4865.0 lumens
Efficiency: N/A
Efficacy: 78.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 62.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000171

CATALOG NUMBER: SA2XXRDIP-B865D530UB40-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1000171

CATALOG NUMBER: SA2XXRDIP-B865D530UB40-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67
1	101	97	93	90	94	91	87	85	80	77	75	69	67	66	60	58	57
2	92	85	79	74	86	80	75	70	70	66	63	62	59	56	53	51	49
3	85	75	68	63	79	71	65	60	63	58	54	55	51	48	48	45	43
4	78	67	59	54	73	63	56	51	56	51	46	49	45	42	43	40	37
5	72	60	52	46	67	57	50	44	51	45	40	45	40	37	39	36	33
6	66	54	46	41	62	51	44	39	46	40	36	41	36	32	36	32	29
7	61	49	41	36	58	47	40	35	42	36	32	37	32	29	33	29	26
8	57	45	37	32	54	43	36	31	38	33	28	34	29	26	30	27	24
9	53	41	34	29	50	39	32	28	35	30	26	32	27	24	28	24	22
10	50	38	31	26	47	36	30	25	33	27	23	29	25	22	26	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	22945	22945	22945
5°	22982	21828	21666
10°	22755	20703	20020
15°	22442	19374	18143
20°	22028	17863	16179
25°	21605	16312	14383
30°	21034	14804	12420
35°	20477	13280	10736
40°	19911	11786	9001
45°	19252	10242	7487
50°	18569	8753	6096
55°	17861	7265	4840
60°	17035	5811	3662
65°	16086	4429	2976
70°	14941	3214	2367
75°	13504	2450	1807
80°	11417	1660	1213
85°	7967	759	586

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 19252 cd/sqm

TEST NUMBER: P1000171

CATALOG NUMBER: SA2XXRDIP-B865D530UB40-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	135.8	2.8
10°-20°	372.9	7.7
20°-30°	523.6	10.8
30°-40°	570.7	11.7
40°-50°	524.5	10.8
50°-60°	412.0	8.5
60°-70°	268.1	5.5
70°-80°	138.0	2.8
80°-90°	37.2	0.8
90°-100°	41.6	0.9
100°-110°	132.4	2.7
110°-120°	226.5	4.7
120°-130°	297.9	6.1
130°-140°	334.4	6.9
140°-150°	327.9	6.7
150°-160°	275.1	5.7
160°-170°	182.4	3.8
170°-180°	63.8	1.3
0°-30°	1032.3	21.2
0°-40°	1603.1	33.0
0°-60°	2539.6	52.2
0°-90°	2982.9	61.3
90°-120°	400.5	8.2
90°-150°	1360.8	28.0
90°-180°	1882.0	38.7
0°-180°	4865.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1450	1450	1450	1450	1450	
5°	1450	1443	1426	1438	1434	137
15°	1379	1364	1320	1295	1282	388
25°	1251	1209	1123	1069	1049	576
35°	1078	1011	896	813	784	675
45°	882	794	656	563	531	681
55°	670	568	426	348	323	599
65°	452	346	228	184	180	449
75°	241	150	105	96	94	255
85°	56	29	25	25	25	65
90°	1	7	20	19	19	5
95°	30	35	36	36	35	33
105°	122	124	125	126	126	129
115°	227	231	230	229	227	225
125°	331	336	334	332	332	295
135°	428	434	435	435	433	331
145°	519	523	527	527	525	324
155°	594	595	597	600	598	273
165°	646	645	645	649	646	182
175°	672	670	669	673	670	64
180°	673	673	673	673	673	

TEST NUMBER: P1000171

CATALOG NUMBER: SA2XXRDIP-B865D530UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1449.5	1449.5	1449.5	1449.5	1449.5
2.5°	1456.0	1449.5	1435.0	1448.1	1445.5
5°	1449.5	1442.9	1425.8	1437.7	1433.7
7.5°	1437.7	1429.8	1411.4	1416.7	1410.1
10°	1421.9	1412.7	1386.5	1382.6	1374.7
12.5°	1402.2	1390.4	1355.0	1347.1	1332.7
15°	1378.6	1364.2	1319.6	1294.7	1281.6
17.5°	1351.1	1330.1	1275.0	1246.1	1225.2
20°	1319.6	1293.4	1227.8	1195.0	1166.1
22.5°	1285.5	1255.3	1179.2	1134.6	1115.0
25°	1251.4	1209.4	1122.8	1069.1	1049.4
27.5°	1210.7	1166.1	1070.4	1008.7	978.5
30°	1167.4	1117.6	1012.7	945.8	910.3
32.5°	1125.5	1065.1	957.6	878.9	846.1
35°	1078.2	1011.3	895.9	813.3	784.4
37.5°	1032.3	960.2	838.2	747.7	714.9
40°	983.8	905.1	777.9	684.7	650.6
42.5°	934.0	850.0	717.5	620.4	587.7
45°	881.5	793.6	655.9	562.7	531.2
47.5°	831.6	738.5	596.8	503.7	474.8
50°	776.5	683.4	539.1	448.6	421.1
52.5°	722.8	624.4	484.0	397.5	372.5
55°	670.3	568.0	426.3	347.6	322.7
57.5°	616.5	511.6	375.2	301.7	280.7
60°	561.4	456.5	321.4	254.5	233.5
62.5°	507.6	402.7	275.5	212.5	202.0
65°	452.5	346.3	228.2	183.6	179.7
67.5°	400.1	293.8	183.6	161.3	157.4
70°	345.0	242.7	152.2	139.0	133.8
72.5°	292.5	195.4	127.2	116.7	114.1
75°	241.4	149.5	104.9	95.8	94.4
77.5°	190.2	106.2	82.6	77.4	74.8
80°	143.0	76.1	63.0	57.7	57.7
82.5°	99.7	51.2	43.3	40.7	40.7
85°	56.4	28.9	24.9	24.9	24.9
87.5°	21.0	10.5	10.5	9.2	9.2
90°	0.6	7.4	19.9	18.7	19.3
92.5°	12.5	17.0	17.6	18.2	18.2
95°	29.5	35.2	36.4	36.4	35.2
97.5°	49.4	54.5	56.8	56.8	56.8
100°	72.1	76.7	78.4	78.4	77.8
102.5°	96.0	99.4	101.7	102.3	101.7
105°	122.1	123.8	125.0	126.1	126.1
107.5°	148.3	150.5	150.5	151.1	148.3
110°	173.3	176.7	176.7	176.7	175.0

TEST NUMBER: P1000171

CATALOG NUMBER: SA2XXRDIP-B865D530UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	200.5	203.9	203.4	201.7	200.5
115°	227.2	230.6	229.5	228.9	227.2
117.5°	253.9	258.5	255.6	253.9	252.2
120°	280.6	285.2	280.6	280.6	278.9
122.5°	305.1	310.7	307.9	306.2	305.1
125°	330.6	335.7	334.0	332.3	331.8
127.5°	355.6	361.9	359.6	357.3	355.6
130°	378.9	386.3	385.2	384.0	381.8
132.5°	405.0	410.7	411.3	408.5	406.7
135°	427.8	434.0	435.2	434.6	432.9
137.5°	452.8	457.9	459.0	458.4	456.2
140°	474.9	480.0	482.9	482.9	480.6
142.5°	497.6	502.8	504.5	505.0	502.8
145°	519.2	523.2	526.6	527.2	524.9
147.5°	538.5	543.7	545.9	547.1	544.8
150°	558.4	561.8	564.1	565.8	564.1
152.5°	576.0	579.4	582.3	584.6	582.3
155°	593.6	595.4	597.1	599.9	598.2
157.5°	609.0	610.1	611.3	615.2	612.4
160°	622.6	623.8	624.3	627.7	625.5
162.5°	635.1	635.1	635.7	639.7	636.8
165°	645.9	645.3	645.3	649.3	646.5
167.5°	655.6	653.9	653.9	657.8	655.0
170°	663.0	661.3	660.7	664.7	661.3
172.5°	668.1	666.4	665.8	669.8	666.4
175°	672.0	670.3	669.2	673.2	669.8
177.5°	674.3	672.6	671.5	674.9	671.5
180°	673.2	673.2	673.2	673.2	673.2

(END OF REPORT)