

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001776

Luminaire Tested: SA4XXDIP-B795D1205UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001776
REPORT IS A COMBINATION OF REPORTS P996398 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B795D1205UB2750-4F0-XX-W2A-F_2700K
Description: Define 4 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8162.0 lumens
Efficiency: N/A
Efficacy: 115.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 70.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001776

CATALOG NUMBER: SA4XXDIP-B795D1205UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1001776

CATALOG NUMBER: SA4XXDIP-B795D1205UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	48	48	48
1	96	92	88	84	87	84	80	77	69	67	64	55	54	52	43	42	41
2	87	80	74	69	79	73	68	64	60	57	53	49	46	44	38	36	34
3	80	70	63	57	72	64	58	53	53	49	45	43	40	37	33	31	29
4	73	62	54	48	66	57	50	45	47	42	38	38	35	32	30	27	25
5	67	55	47	41	61	51	44	38	42	37	33	34	30	27	27	24	22
6	61	50	42	36	56	46	38	33	38	33	29	31	27	24	24	21	19
7	57	45	37	31	52	41	34	29	34	29	25	28	24	21	22	19	17
8	53	40	33	28	48	37	31	26	31	26	22	26	22	19	20	17	15
9	49	37	30	25	45	34	27	23	29	24	20	24	20	17	19	16	14
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10789	10789	10789
5°	10798	10479	10492
10°	10706	10188	10117
15°	10553	9842	9694
20°	10357	9468	9255
25°	10136	9072	8784
30°	9870	8645	8267
35°	9595	8208	7766
40°	9307	7737	7234
45°	9005	7265	6737
50°	8673	6807	6186
55°	8310	6272	5639
60°	7938	5686	5069
65°	7514	5082	4427
70°	7025	4354	3738
75°	6294	3509	2994
80°	5363	2537	2106
85°	4162	1412	1134

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9005 cd/sqm

TEST NUMBER: P1001776

CATALOG NUMBER: SA4XXDIP-B795D1205UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.7	1.5
10°-20°	351.3	4.3
20°-30°	517.1	6.3
30°-40°	601.1	7.4
40°-50°	601.0	7.4
50°-60°	525.7	6.4
60°-70°	390.3	4.8
70°-80°	221.4	2.7
80°-90°	66.6	0.8
90°-100°	51.1	0.6
100°-110°	336.5	4.1
110°-120°	642.5	7.9
120°-130°	815.7	10.0
130°-140°	872.6	10.7
140°-150°	815.9	10.0
150°-160°	658.0	8.1
160°-170°	424.3	5.2
170°-180°	146.2	1.8
0°-30°	993.1	12.2
0°-40°	1594.2	19.5
0°-60°	2720.9	33.3
0°-90°	3399.2	41.6
90°-120°	1030.1	12.6
90°-150°	3534.3	43.3
90°-180°	4763.0	58.4
0°-180°	8162.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1323	1323	1323	1323	1323	
5°	1322	1318	1306	1318	1316	125
15°	1258	1254	1238	1245	1242	355
25°	1140	1132	1117	1118	1114	524
35°	981	973	958	951	946	613
45°	800	793	776	764	761	617
55°	605	602	587	575	568	542
65°	410	405	394	384	378	406
75°	218	213	208	204	202	232
85°	57	57	55	55	54	62
90°	4	16	25	32	34	7
95°	63	24	25	32	33	78
105°	346	353	359	370	328	363
115°	647	650	649	652	652	637
125°	910	914	912	915	916	812
135°	1128	1127	1132	1134	1136	869
145°	1301	1304	1304	1306	1308	813
155°	1426	1428	1424	1429	1425	658
165°	1505	1499	1499	1508	1498	425
175°	1539	1532	1533	1544	1530	147
180°	1539	1539	1539	1539	1539	

TEST NUMBER: P1001776

CATALOG NUMBER: SA4XXDIP-B795D1205UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1323.1	1323.1	1323.1	1323.1	1323.1
2.5°	1327.3	1324.2	1312.5	1323.1	1322.0
5°	1322.0	1317.8	1306.1	1317.8	1315.7
7.5°	1312.5	1308.3	1295.5	1305.1	1304.0
10°	1298.7	1294.5	1280.7	1289.2	1287.1
12.5°	1280.7	1276.5	1261.6	1271.2	1268.0
15°	1258.4	1254.2	1238.3	1244.6	1241.5
17.5°	1233.0	1227.7	1212.8	1217.1	1215.0
20°	1204.4	1199.1	1183.2	1186.3	1184.2
22.5°	1173.6	1166.2	1150.3	1156.7	1152.4
25°	1139.7	1132.3	1117.4	1118.5	1114.2
27.5°	1101.5	1094.1	1080.3	1078.2	1072.9
30°	1063.4	1054.9	1041.1	1036.9	1031.6
32.5°	1023.1	1015.7	1000.8	995.5	990.2
35°	980.7	973.2	958.4	951.0	945.7
37.5°	936.1	929.8	913.9	906.5	899.0
40°	892.7	884.2	868.3	857.7	852.4
42.5°	846.0	841.8	823.8	811.0	807.9
45°	800.4	793.0	776.1	764.4	761.2
47.5°	752.7	747.4	731.5	718.8	710.3
50°	704.0	699.7	684.9	670.0	663.7
52.5°	656.3	650.9	635.0	622.3	613.8
55°	605.4	602.2	587.3	574.6	568.3
57.5°	557.7	554.5	539.6	526.9	520.5
60°	507.8	502.5	488.7	479.2	473.9
62.5°	459.1	454.8	440.0	431.5	426.2
65°	410.3	405.0	394.4	383.8	378.5
67.5°	360.5	356.2	345.6	335.0	334.0
70°	314.9	307.5	299.0	290.5	287.3
72.5°	266.1	258.7	252.3	246.0	242.8
75°	218.4	213.1	207.8	203.6	202.5
77.5°	171.7	169.6	164.3	163.3	160.1
80°	130.4	127.2	125.1	123.0	121.9
82.5°	90.1	89.1	89.1	88.0	86.9
85°	57.2	57.2	55.1	55.1	54.1
87.5°	27.6	26.5	25.4	25.4	25.4
90°	3.5	16.1	25.3	32.2	34.5
92.5°	17.3	15.0	24.2	31.1	31.1
95°	63.3	24.2	25.3	32.2	33.4
97.5°	120.9	146.2	25.3	31.1	32.2
100°	188.8	209.5	50.7	31.1	32.2
102.5°	264.8	278.6	292.4	33.4	33.4
105°	346.5	353.4	359.2	369.5	328.1
107.5°	421.4	424.8	432.9	438.6	443.2
110°	497.3	500.8	507.7	510.0	513.4

TEST NUMBER: P1001776

CATALOG NUMBER: SA4XXDIP-B795D1205UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	571.0	577.9	580.2	579.1	583.7
115°	647.0	650.4	649.3	651.6	651.6
117.5°	714.9	719.5	723.0	721.8	721.8
120°	784.0	788.6	787.4	789.7	787.4
122.5°	848.5	850.8	853.1	854.2	851.9
125°	909.5	914.1	911.8	915.2	916.4
127.5°	968.2	969.3	975.1	973.9	972.8
130°	1024.6	1025.7	1029.2	1030.4	1030.4
132.5°	1076.4	1078.7	1083.3	1084.5	1083.3
135°	1128.2	1127.1	1131.7	1134.0	1136.3
137.5°	1174.3	1174.3	1180.0	1182.3	1181.2
140°	1219.2	1221.5	1223.8	1227.2	1228.4
142.5°	1259.4	1264.1	1265.2	1267.5	1267.5
145°	1300.9	1304.3	1304.3	1305.5	1307.8
147.5°	1333.1	1340.0	1338.9	1340.0	1341.2
150°	1368.8	1373.4	1372.3	1372.3	1373.4
152.5°	1398.7	1402.2	1399.9	1402.2	1401.1
155°	1426.4	1427.5	1424.1	1428.7	1425.2
157.5°	1450.6	1450.6	1445.9	1451.7	1445.9
160°	1471.3	1467.8	1466.7	1473.6	1466.7
162.5°	1489.7	1485.1	1483.9	1490.8	1482.8
165°	1504.7	1498.9	1498.9	1508.1	1497.8
167.5°	1517.3	1511.6	1510.4	1520.8	1509.3
170°	1527.7	1520.8	1521.9	1531.1	1519.6
172.5°	1534.6	1527.7	1528.8	1538.0	1525.4
175°	1539.2	1532.3	1533.4	1543.8	1530.0
177.5°	1542.7	1534.6	1536.9	1546.1	1532.3
180°	1539.2	1539.2	1539.2	1539.2	1539.2

(END OF REPORT)