

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001777

Luminaire Tested: SA4XXDIP-B795D1205UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001777
REPORT IS A COMBINATION OF REPORTS P996399 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B795D1205UB2750-4F0-XX-W2A-F_3000K
Description: Define 4 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8232.1 lumens
Efficiency: N/A
Efficacy: 116.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 70.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001777

CATALOG NUMBER: SA4XXDIP-B795D1205UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1001777

CATALOG NUMBER: SA4XXDIP-B795D1205UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	48	48	48
1	96	92	88	84	87	84	80	77	69	67	64	55	54	52	43	42	41
2	87	80	74	69	79	73	68	64	60	57	53	49	46	44	38	36	34
3	80	70	63	57	72	64	58	53	53	49	45	43	40	37	33	31	29
4	73	62	54	48	66	57	50	45	47	42	38	38	35	32	30	27	25
5	67	55	47	41	61	51	44	38	42	37	33	34	30	27	27	24	22
6	61	50	42	36	56	46	38	33	38	33	29	31	27	24	24	21	19
7	57	45	37	31	52	41	34	29	34	29	25	28	24	21	22	19	17
8	53	40	33	28	48	37	31	26	31	26	22	26	22	19	20	17	15
9	49	37	30	25	45	34	27	23	29	24	20	24	20	17	19	16	14
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10881	10881	10881
5°	10890	10568	10581
10°	10798	10275	10203
15°	10643	9926	9777
20°	10445	9549	9334
25°	10223	9150	8859
30°	9954	8719	8338
35°	9676	8278	7833
40°	9387	7803	7296
45°	9083	7327	6794
50°	8747	6865	6238
55°	8380	6326	5687
60°	8007	5735	5111
65°	7578	5126	4464
70°	7086	4390	3770
75°	6349	3540	3019
80°	5408	2559	2125
85°	4199	1425	1142

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9083 cd/sqm

TEST NUMBER: P1001777

CATALOG NUMBER: SA4XXDIP-B795D1205UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	125.8	1.5
10°-20°	354.3	4.3
20°-30°	521.5	6.3
30°-40°	606.2	7.4
40°-50°	606.2	7.4
50°-60°	530.2	6.4
60°-70°	393.6	4.8
70°-80°	223.3	2.7
80°-90°	67.2	0.8
90°-100°	51.5	0.6
100°-110°	339.4	4.1
110°-120°	648.0	7.9
120°-130°	822.7	10.0
130°-140°	880.1	10.7
140°-150°	823.0	10.0
150°-160°	663.6	8.1
160°-170°	428.0	5.2
170°-180°	147.5	1.8
0°-30°	1001.6	12.2
0°-40°	1607.8	19.5
0°-60°	2744.1	33.3
0°-90°	3428.2	41.6
90°-120°	1039.0	12.6
90°-150°	3564.7	43.3
90°-180°	4804.0	58.4
0°-180°	8232.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1334	1334	1334	1334	1334	
5°	1333	1329	1317	1329	1327	127
15°	1269	1265	1249	1255	1252	358
25°	1149	1142	1127	1128	1124	529
35°	989	982	967	959	954	618
45°	807	800	783	771	768	622
55°	610	607	592	580	573	547
65°	414	408	398	387	382	410
75°	220	215	210	205	204	234
85°	58	58	56	56	54	62
90°	4	16	26	32	35	7
95°	64	24	26	32	34	79
105°	350	356	362	373	331	366
115°	653	656	655	657	657	642
125°	917	922	920	923	924	819
135°	1138	1137	1141	1144	1146	877
145°	1312	1316	1316	1317	1319	820
155°	1439	1440	1436	1441	1438	663
165°	1518	1512	1512	1521	1511	429
175°	1552	1546	1547	1557	1543	148
180°	1552	1552	1552	1552	1552	

TEST NUMBER: P1001777

CATALOG NUMBER: SA4XXDIP-B795D1205UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1334.4	1334.4	1334.4	1334.4	1334.4
2.5°	1338.7	1335.5	1323.7	1334.4	1333.3
5°	1333.3	1329.1	1317.3	1329.1	1326.9
7.5°	1323.7	1319.4	1306.6	1316.2	1315.2
10°	1309.8	1305.5	1291.6	1300.2	1298.0
12.5°	1291.6	1287.4	1272.4	1282.0	1278.8
15°	1269.2	1264.9	1248.9	1255.3	1252.1
17.5°	1243.5	1238.2	1223.2	1227.5	1225.3
20°	1214.6	1209.3	1193.3	1196.5	1194.3
22.5°	1183.6	1176.2	1160.1	1166.5	1162.3
25°	1149.4	1141.9	1127.0	1128.0	1123.8
27.5°	1110.9	1103.4	1089.5	1087.4	1082.1
30°	1072.4	1063.9	1050.0	1045.7	1040.4
32.5°	1031.8	1024.3	1009.4	1004.0	998.7
35°	989.0	981.6	966.6	959.1	953.8
37.5°	944.1	937.7	921.7	914.2	906.7
40°	900.3	891.7	875.7	865.0	859.7
42.5°	853.2	849.0	830.8	818.0	814.8
45°	807.3	799.8	782.7	770.9	767.7
47.5°	759.2	753.8	737.8	724.9	716.4
50°	710.0	705.7	690.7	675.8	669.3
52.5°	661.9	656.5	640.5	627.6	619.1
55°	610.5	607.3	592.4	579.5	573.1
57.5°	562.4	559.2	544.2	531.4	525.0
60°	512.2	506.8	492.9	483.3	477.9
62.5°	463.0	458.7	443.7	435.2	429.8
65°	413.8	408.4	397.8	387.1	381.7
67.5°	363.5	359.3	348.6	337.9	336.8
70°	317.6	310.1	301.5	293.0	289.8
72.5°	268.4	260.9	254.5	248.1	244.9
75°	220.3	214.9	209.6	205.3	204.2
77.5°	173.2	171.1	165.7	164.7	161.5
80°	131.5	128.3	126.2	124.0	123.0
82.5°	90.9	89.8	89.8	88.7	87.7
85°	57.7	57.7	55.6	55.6	54.5
87.5°	27.8	26.7	25.7	25.7	25.7
90°	3.5	16.3	25.5	32.5	34.8
92.5°	17.4	15.1	24.4	31.4	31.4
95°	63.9	24.4	25.5	32.5	33.7
97.5°	121.9	147.5	25.5	31.4	32.5
100°	190.4	211.3	51.1	31.4	32.5
102.5°	267.1	281.0	294.9	33.7	33.7
105°	349.5	356.5	362.3	372.7	330.9
107.5°	425.0	428.5	436.6	442.4	447.0
110°	501.6	505.1	512.1	514.4	517.9

TEST NUMBER: P1001777

CATALOG NUMBER: SA4XXDIP-B795D1205UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	575.9	582.9	585.2	584.1	588.7
115°	652.6	656.0	654.9	657.2	657.2
117.5°	721.1	725.7	729.2	728.0	728.0
120°	790.7	795.4	794.2	796.5	794.2
122.5°	855.8	858.1	860.4	861.6	859.2
125°	917.3	921.9	919.6	923.1	924.3
127.5°	976.5	977.7	983.5	982.3	981.2
130°	1033.4	1034.6	1038.1	1039.2	1039.2
132.5°	1085.7	1088.0	1092.6	1093.8	1092.6
135°	1137.9	1136.8	1141.4	1143.7	1146.0
137.5°	1184.4	1184.4	1190.2	1192.5	1191.3
140°	1229.6	1232.0	1234.3	1237.8	1238.9
142.5°	1270.3	1274.9	1276.1	1278.4	1278.4
145°	1312.1	1315.6	1315.6	1316.7	1319.1
147.5°	1344.6	1351.6	1350.4	1351.6	1352.7
150°	1380.6	1385.2	1384.1	1384.1	1385.2
152.5°	1410.8	1414.3	1411.9	1414.3	1413.1
155°	1438.6	1439.8	1436.3	1441.0	1437.5
157.5°	1463.0	1463.0	1458.4	1464.2	1458.4
160°	1483.9	1480.4	1479.3	1486.3	1479.3
162.5°	1502.5	1497.9	1496.7	1503.7	1495.5
165°	1517.6	1511.8	1511.8	1521.1	1510.6
167.5°	1530.4	1524.6	1523.4	1533.9	1522.2
170°	1540.8	1533.9	1535.0	1544.3	1532.7
172.5°	1547.8	1540.8	1542.0	1551.3	1538.5
175°	1552.4	1545.5	1546.6	1557.1	1543.1
177.5°	1555.9	1547.8	1550.1	1559.4	1545.5
180°	1552.4	1552.4	1552.4	1552.4	1552.4

(END OF REPORT)