

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001778

Luminaire Tested: SA4XXDIP-B795D1205UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001778
REPORT IS A COMBINATION OF REPORTS P996400 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B795D1205UB2750-4F0-XX-W2A-F_3500K
Description: Define 4 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8268.0 lumens
Efficiency: N/A
Efficacy: 116.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 70.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001778

CATALOG NUMBER: SA4XXDIP-B795D1205UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1001778

CATALOG NUMBER: SA4XXDIP-B795D1205UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	48	48	48
1	96	92	88	84	87	84	80	77	69	67	64	55	54	52	43	42	41
2	87	80	74	69	79	73	68	64	60	57	53	49	46	44	38	36	34
3	80	70	63	57	72	64	58	53	53	49	45	43	40	37	33	31	29
4	73	62	54	48	66	57	50	45	47	42	38	38	35	32	30	27	25
5	67	55	47	41	61	51	44	38	42	37	33	34	30	27	27	24	22
6	61	50	42	36	56	46	38	33	38	33	29	31	27	24	24	21	19
7	57	45	37	31	52	41	34	29	34	29	25	28	24	21	22	19	17
8	53	40	33	28	48	37	31	26	31	26	22	26	22	19	20	17	15
9	49	37	30	25	45	34	27	23	29	24	20	24	20	17	19	16	14
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10929	10929	10929
5°	10938	10615	10627
10°	10845	10320	10247
15°	10690	9969	9820
20°	10491	9591	9376
25°	10268	9190	8898
30°	9998	8757	8374
35°	9719	8314	7867
40°	9427	7837	7328
45°	9122	7359	6824
50°	8785	6895	6266
55°	8417	6353	5711
60°	8041	5760	5134
65°	7611	5148	4484
70°	7117	4409	3786
75°	6374	3555	3032
80°	5433	2570	2133
85°	4221	1430	1149

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9122 cd/sqm

TEST NUMBER: P1001778

CATALOG NUMBER: SA4XXDIP-B795D1205UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.3	1.5
10°-20°	355.9	4.3
20°-30°	523.8	6.3
30°-40°	608.9	7.4
40°-50°	608.8	7.4
50°-60°	532.5	6.4
60°-70°	395.3	4.8
70°-80°	224.3	2.7
80°-90°	67.5	0.8
90°-100°	51.8	0.6
100°-110°	340.8	4.1
110°-120°	650.9	7.9
120°-130°	826.3	10.0
130°-140°	883.9	10.7
140°-150°	826.5	10.0
150°-160°	666.5	8.1
160°-170°	429.9	5.2
170°-180°	148.2	1.8
0°-30°	1006.0	12.2
0°-40°	1614.9	19.5
0°-60°	2756.1	33.3
0°-90°	3443.2	41.6
90°-120°	1043.5	12.6
90°-150°	3580.2	43.3
90°-180°	4825.0	58.4
0°-180°	8268.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1340	1340	1340	1340	1340	
5°	1339	1335	1323	1335	1333	127
15°	1275	1270	1254	1261	1258	359
25°	1154	1147	1132	1133	1129	531
35°	993	986	971	963	958	621
45°	811	803	786	774	771	625
55°	613	610	595	582	576	549
65°	416	410	400	389	383	411
75°	221	216	210	206	205	235
85°	58	58	56	56	55	62
90°	4	16	26	33	35	7
95°	64	24	26	33	34	79
105°	351	358	364	374	332	367
115°	655	659	658	660	660	645
125°	921	926	924	927	928	823
135°	1143	1142	1146	1149	1151	881
145°	1318	1321	1321	1322	1325	823
155°	1445	1446	1443	1447	1444	666
165°	1524	1518	1518	1528	1517	431
175°	1559	1552	1553	1564	1550	148
180°	1559	1559	1559	1559	1559	

TEST NUMBER: P1001778

CATALOG NUMBER: SA4XXDIP-B795D1205UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1340.2	1340.2	1340.2	1340.2	1340.2
2.5°	1344.5	1341.3	1329.5	1340.2	1339.2
5°	1339.2	1334.9	1323.1	1334.9	1332.7
7.5°	1329.5	1325.2	1312.3	1322.0	1320.9
10°	1315.5	1311.2	1297.3	1305.9	1303.7
12.5°	1297.3	1293.0	1278.0	1287.6	1284.4
15°	1274.7	1270.4	1254.3	1260.8	1257.6
17.5°	1249.0	1243.6	1228.6	1232.9	1230.7
20°	1220.0	1214.6	1198.5	1201.7	1199.6
22.5°	1188.8	1181.3	1165.2	1171.6	1167.3
25°	1154.5	1146.9	1131.9	1133.0	1128.7
27.5°	1115.8	1108.3	1094.3	1092.2	1086.8
30°	1077.1	1068.5	1054.6	1050.3	1044.9
32.5°	1036.3	1028.8	1013.8	1008.4	1003.0
35°	993.4	985.9	970.8	963.3	957.9
37.5°	948.3	941.8	925.7	918.2	910.7
40°	904.2	895.6	879.5	868.8	863.4
42.5°	857.0	852.7	834.4	821.5	818.3
45°	810.8	803.3	786.1	774.3	771.1
47.5°	762.5	757.1	741.0	728.1	719.5
50°	713.1	708.8	693.7	678.7	672.3
52.5°	664.8	659.4	643.3	630.4	621.8
55°	613.2	610.0	594.9	582.1	575.6
57.5°	564.9	561.7	546.6	533.7	527.3
60°	514.4	509.0	495.1	485.4	480.0
62.5°	465.0	460.7	445.7	437.1	431.7
65°	415.6	410.2	399.5	388.8	383.4
67.5°	365.1	360.8	350.1	339.4	338.3
70°	319.0	311.4	302.8	294.3	291.0
72.5°	269.6	262.0	255.6	249.1	245.9
75°	221.2	215.9	210.5	206.2	205.1
77.5°	174.0	171.8	166.5	165.4	162.2
80°	132.1	128.9	126.7	124.6	123.5
82.5°	91.3	90.2	90.2	89.1	88.1
85°	58.0	58.0	55.8	55.8	54.8
87.5°	27.9	26.8	25.8	25.8	25.8
90°	3.5	16.3	25.7	32.7	35.0
92.5°	17.5	15.2	24.5	31.5	31.5
95°	64.1	24.5	25.7	32.7	33.8
97.5°	122.5	148.1	25.7	31.5	32.7
100°	191.3	212.2	51.3	31.5	32.7
102.5°	268.2	282.2	296.2	33.8	33.8
105°	351.0	358.0	363.9	374.4	332.4
107.5°	426.8	430.3	438.5	444.3	449.0
110°	503.8	507.3	514.3	516.6	520.1

TEST NUMBER: P1001778

CATALOG NUMBER: SA4XXDIP-B795D1205UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	578.4	585.4	587.8	586.6	591.3
115°	655.4	658.9	657.7	660.1	660.1
117.5°	724.2	728.9	732.4	731.2	731.2
120°	794.2	798.9	797.7	800.0	797.7
122.5°	859.5	861.8	864.2	865.3	863.0
125°	921.3	926.0	923.6	927.1	928.3
127.5°	980.8	981.9	987.8	986.6	985.4
130°	1037.9	1039.1	1042.6	1043.8	1043.8
132.5°	1090.4	1092.7	1097.4	1098.6	1097.4
135°	1142.9	1141.7	1146.4	1148.7	1151.0
137.5°	1189.5	1189.5	1195.4	1197.7	1196.5
140°	1235.0	1237.3	1239.7	1243.2	1244.3
142.5°	1275.8	1280.5	1281.7	1284.0	1284.0
145°	1317.8	1321.3	1321.3	1322.5	1324.8
147.5°	1350.5	1357.5	1356.3	1357.5	1358.6
150°	1386.6	1391.3	1390.1	1390.1	1391.3
152.5°	1416.9	1420.4	1418.1	1420.4	1419.3
155°	1444.9	1446.1	1442.6	1447.3	1443.8
157.5°	1469.4	1469.4	1464.8	1470.6	1464.8
160°	1490.4	1486.9	1485.7	1492.7	1485.7
162.5°	1509.1	1504.4	1503.2	1510.2	1502.1
165°	1524.2	1518.4	1518.4	1527.7	1517.2
167.5°	1537.1	1531.2	1530.1	1540.6	1528.9
170°	1547.6	1540.6	1541.7	1551.1	1539.4
172.5°	1554.6	1547.6	1548.7	1558.1	1545.2
175°	1559.2	1552.2	1553.4	1563.9	1549.9
177.5°	1562.7	1554.6	1556.9	1566.2	1552.2
180°	1559.2	1559.2	1559.2	1559.2	1559.2

(END OF REPORT)