

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000242

Luminaire Tested: SA2XXRDIP-B865D925UB35-4F0-XX-W2A-A1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000242
REPORT IS A COMBINATION OF REPORTS P988802 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B865D925UB35-4F0-XX-W2A-A1
Description: Define 2 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6585.0 lumens
Efficiency: N/A
Efficacy: 87.5 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 75.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000242

CATALOG NUMBER: SA2XXRDIP-B865D925UB35-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P1000242

CATALOG NUMBER: SA2XXRDIP-B865D925UB35-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	56	56	50
1	99	95	91	88	91	87	84	82	74	72	70	62	61	59	51	50	49	49	49	44
2	90	83	78	73	83	77	72	68	66	62	59	55	53	51	46	44	42	42	42	38
3	83	74	67	62	77	69	63	58	59	55	51	50	47	44	41	39	37	37	37	33
4	76	66	59	53	70	62	55	50	53	48	44	45	41	38	38	35	33	33	33	29
5	71	60	52	46	65	56	49	44	48	43	39	41	37	34	34	31	29	29	29	26
6	65	54	46	41	60	50	43	38	44	38	34	37	33	30	31	29	26	26	26	23
7	61	49	41	36	56	46	39	34	40	35	31	34	30	27	29	26	24	24	24	21
8	56	45	37	32	52	42	35	31	37	31	28	32	28	25	27	24	22	22	22	19
9	53	41	34	29	49	39	32	28	34	29	25	29	25	22	25	22	20	20	20	18
10	49	38	31	26	46	36	29	25	31	26	23	27	23	20	23	20	18	18	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	30172	30172	30172	30172
5°	30242	32048	30348	25603
10°	29909	33873	30122	21143
15°	29261	33885	29757	15882
20°	28480	28009	29100	13103
25°	27533	17501	28129	11147
30°	26324	11206	27041	9597
35°	24854	8612	25659	8212
40°	23216	7238	24208	7183
45°	21467	6161	22362	6030
50°	19671	5235	20590	5216
55°	17682	4549	18636	4490
60°	15916	3469	16762	3428
65°	14270	2610	15116	2961
70°	12446	2086	13425	2413
75°	10522	1598	11485	1826
80°	8351	1087	8990	1198
85°	5806	560	6357	593

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 27600 cd/sqm

TEST NUMBER: P1000242

CATALOG NUMBER: SA2XXRDIP-B865D925UB35-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	180.8	2.7
10°-20°	504.7	7.7
20°-30°	649.5	9.9
30°-40°	616.2	9.4
40°-50°	528.1	8.0
50°-60°	402.2	6.1
60°-70°	253.6	3.9
70°-80°	126.5	1.9
80°-90°	35.9	0.5
90°-100°	72.7	1.1
100°-110°	231.3	3.5
110°-120°	395.7	6.0
120°-130°	520.4	7.9
130°-140°	584.1	8.9
140°-150°	572.8	8.7
150°-160°	480.5	7.3
160°-170°	318.7	4.8
170°-180°	111.4	1.7
0°-30°	1334.9	20.3
0°-40°	1951.1	29.6
0°-60°	2881.3	43.8
0°-90°	3297.3	50.1
90°-120°	699.7	10.6
90°-150°	2377.1	36.1
90°-180°	3288.0	49.9
0°-180°	6585.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1906	1906	1906	1906	1906	
5°	1907	2121	1914	1694	1907	181
15°	1798	2394	1828	1122	1798	506
25°	1595	1277	1629	813	1595	732
35°	1309	629	1351	600	1309	819
45°	983	437	1024	428	983	759
55°	664	303	699	299	664	598
65°	401	158	425	179	401	398
75°	188	84	205	95	188	204
85°	41	24	45	25	41	47
90°	1	34	1	34	1	6
95°	52	62	52	62	52	58
105°	213	220	213	220	213	225
115°	397	397	397	397	397	393
125°	578	580	578	580	578	516
135°	747	756	747	756	747	577
145°	907	917	907	917	907	567
155°	1037	1045	1037	1045	1037	477
165°	1128	1129	1128	1129	1128	318
175°	1174	1170	1174	1170	1174	112
180°	1176	1176	1176	1176	1176	

TEST NUMBER: P1000242

CATALOG NUMBER: SA2XXRDIP-B865D925UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1
2.5°	1918.0	1926.0	1930.0	1935.3	1947.2	1955.1	1967.0	1969.7	1968.4	1973.7	1959.1
5°	1907.4	1924.7	1940.6	1953.8	1975.0	1988.2	2002.8	2020.0	2024.0	2043.9	2032.0
7.5°	1892.9	1918.0	1940.6	1967.0	1998.8	2016.1	2038.6	2065.1	2077.0	2100.8	2107.5
10°	1869.0	1904.8	1943.2	1971.0	2014.7	2045.2	2066.4	2108.8	2136.6	2172.4	2167.1
12.5°	1830.6	1877.0	1928.6	1975.0	2032.0	2051.8	2091.6	2135.3	2171.0	2204.2	2233.3
15°	1797.5	1850.5	1907.4	1964.4	2029.3	2066.4	2106.1	2163.1	2201.5	2259.8	2285.0
17.5°	1752.5	1820.0	1887.6	1951.1	2028.0	2070.4	2119.4	2175.0	2232.0	2287.6	2307.5
20°	1706.1	1779.0	1851.8	1937.9	2025.3	2066.4	2116.7	2185.6	2241.2	2285.0	2285.0
22.5°	1650.5	1739.2	1822.7	1904.8	2000.2	2059.8	2111.4	2192.2	2232.0	2241.2	2205.5
25°	1594.8	1683.6	1775.0	1877.0	1985.6	2038.6	2096.9	2172.4	2185.6	2148.5	2055.8
27.5°	1528.6	1627.9	1731.3	1841.2	1955.1	2021.4	2074.3	2124.7	2099.5	2000.2	1855.8
30°	1461.0	1568.3	1684.9	1789.5	1927.3	1988.2	2033.3	2047.8	1968.4	1806.8	1620.0
32.5°	1390.8	1495.5	1618.7	1744.5	1883.6	1941.9	1971.0	1932.6	1786.9	1582.9	1355.1
35°	1308.7	1426.6	1555.1	1686.2	1824.0	1867.7	1884.9	1790.9	1604.1	1340.5	1114.0
37.5°	1234.5	1352.4	1490.2	1624.0	1757.8	1781.6	1764.4	1617.3	1380.2	1119.3	898.1
40°	1147.1	1272.9	1408.1	1557.7	1667.7	1674.3	1631.9	1441.2	1147.1	902.1	765.6
42.5°	1066.3	1193.5	1328.6	1480.9	1564.4	1541.8	1484.9	1234.5	957.7	777.5	667.6
45°	982.9	1103.4	1249.1	1384.2	1443.8	1390.8	1304.7	1038.5	804.0	668.9	584.2
47.5°	902.1	1014.7	1159.0	1288.8	1299.4	1239.8	1137.8	870.3	696.7	588.1	519.2
50°	822.6	935.2	1070.3	1177.6	1167.0	1084.9	969.6	756.4	605.3	519.2	462.3
52.5°	743.1	845.1	976.2	1061.0	1016.0	936.5	822.6	641.1	528.5	453.0	409.3
55°	663.6	759.0	871.6	941.8	870.3	778.9	698.1	549.7	458.3	397.4	364.3
57.5°	597.4	672.9	776.2	818.6	732.5	661.0	590.8	472.9	397.4	353.7	315.3
60°	524.5	593.4	678.2	703.4	614.6	556.3	496.7	400.0	340.4	302.0	276.8
62.5°	462.3	519.2	584.2	584.2	506.0	462.3	417.3	335.1	286.1	255.6	243.7
65°	401.4	442.4	488.8	483.5	417.3	378.8	343.1	276.8	239.8	218.6	206.6
67.5°	341.7	373.5	404.0	385.5	337.8	304.7	271.5	223.9	198.7	184.1	168.2
70°	287.4	312.6	328.5	311.3	263.6	235.8	211.9	180.1	160.3	141.7	132.5
72.5°	241.1	251.7	257.0	235.8	196.0	180.1	162.9	140.4	123.2	113.9	111.3
75°	188.1	197.4	193.4	177.5	144.4	132.5	119.2	103.3	99.3	94.0	91.4
77.5°	147.0	147.0	140.4	125.8	103.3	94.0	88.7	80.8	76.8	75.5	72.9
80°	104.6	103.3	99.3	83.5	70.2	64.9	64.9	59.6	58.3	55.6	55.6
82.5°	68.9	68.9	63.6	50.3	46.4	45.0	43.7	41.1	41.1	39.7	39.7
85°	41.1	38.4	31.8	27.8	26.5	26.5	25.2	23.8	25.2	23.8	23.8
87.5°	18.5	14.6	10.6	10.6	10.6	10.6	10.6	10.6	10.6	10.6	10.6
90°	1.0	3.6	6.3	8.9	11.6	12.9	15.3	20.2	25.0	29.9	34.7
92.5°	21.8	23.6	25.4	27.1	28.9	29.8	29.9	30.1	30.4	30.6	30.8
95°	51.6	53.8	56.0	58.2	60.4	61.5	61.7	62.2	62.6	63.1	63.5
97.5°	86.3	88.3	90.3	92.3	94.3	95.3	95.7	96.6	97.5	98.3	99.2
100°	126.0	127.8	129.6	131.3	133.1	134.0	134.3	135.0	135.6	136.3	136.9
102.5°	167.7	169.0	170.4	171.7	173.0	173.7	174.1	175.0	175.9	176.7	177.6
105°	213.4	214.0	214.7	215.3	216.0	216.3	216.5	217.0	217.4	217.9	218.3
107.5°	259.0	259.9	260.8	261.7	262.6	263.0	263.0	263.0	263.0	263.0	263.0
110°	302.7	304.0	305.3	306.6	307.9	308.6	308.6	308.6	308.6	308.6	308.6

TEST NUMBER: P1000242

CATALOG NUMBER: SA2XXRDIP-B865D925UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	350.3	351.6	352.9	354.2	355.5	356.2	356.1	355.9	355.7	355.5	355.3
115°	396.9	398.2	399.6	400.9	402.2	402.9	402.7	402.2	401.8	401.3	400.9
117.5°	443.6	445.4	447.1	448.9	450.6	451.5	451.0	449.9	448.8	447.7	446.6
120°	490.2	492.0	493.8	495.5	497.3	498.2	497.3	495.5	493.8	492.0	490.2
122.5°	532.9	535.1	537.3	539.5	541.7	542.8	542.2	541.1	540.0	538.9	537.8
125°	577.5	579.5	581.5	583.5	585.5	586.5	586.2	585.5	584.8	584.2	583.5
127.5°	621.2	623.6	626.0	628.5	630.9	632.1	631.7	630.8	629.9	629.1	628.2
130°	661.9	664.8	667.6	670.5	673.4	674.8	674.6	674.1	673.7	673.2	672.8
132.5°	707.5	709.7	711.9	714.2	716.4	717.5	717.6	717.8	718.1	718.3	718.5
135°	747.2	749.6	752.0	754.5	756.9	758.1	758.3	758.8	759.2	759.7	760.1
137.5°	790.9	792.9	794.9	796.8	798.8	799.8	800.0	800.5	800.9	801.4	801.8
140°	829.6	831.6	833.6	835.5	837.5	838.5	839.1	840.2	841.3	842.4	843.5
142.5°	869.3	871.3	873.3	875.2	877.2	878.2	878.5	879.2	879.9	880.5	881.2
145°	907.0	908.5	910.1	911.6	913.1	913.9	914.6	915.9	917.2	918.6	919.9
147.5°	940.7	942.7	944.7	946.7	948.7	949.7	950.1	951.0	951.9	952.7	953.6
150°	975.5	976.8	978.1	979.4	980.7	981.4	981.8	982.7	983.6	984.5	985.4
152.5°	1006.2	1007.5	1008.9	1010.2	1011.5	1012.2	1012.7	1013.8	1014.9	1016.0	1017.1
155°	1037.0	1037.7	1038.3	1039.0	1039.7	1040.0	1040.3	1041.0	1041.6	1042.3	1042.9
157.5°	1063.8	1064.2	1064.7	1065.1	1065.6	1065.8	1066.0	1066.5	1066.9	1067.4	1067.8
160°	1087.6	1088.0	1088.5	1088.9	1089.4	1089.6	1089.7	1089.9	1090.2	1090.4	1090.6
162.5°	1109.4	1109.4	1109.4	1109.4	1109.4	1109.4	1109.5	1109.7	1110.0	1110.2	1110.4
165°	1128.3	1128.1	1127.9	1127.6	1127.4	1127.3	1127.3	1127.3	1127.3	1127.3	1127.3
167.5°	1145.2	1144.5	1143.9	1143.2	1142.5	1142.2	1142.2	1142.2	1142.2	1142.2	1142.2
170°	1158.1	1157.4	1156.8	1156.1	1155.4	1155.1	1155.0	1154.8	1154.5	1154.3	1154.1
172.5°	1167.0	1166.3	1165.7	1165.0	1164.3	1164.0	1163.9	1163.7	1163.4	1163.2	1163.0
175°	1173.9	1173.3	1172.6	1172.0	1171.3	1171.0	1170.8	1170.3	1169.9	1169.4	1169.0
177.5°	1177.9	1177.2	1176.6	1175.9	1175.2	1174.9	1174.7	1174.2	1173.8	1173.3	1172.9
180°	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9

TEST NUMBER: P1000242

CATALOG NUMBER: SA2XXRDIP-B865D925UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1
2.5°	1973.7	1976.3	1980.3	1998.8	2001.5	2006.8	2004.1	2004.1	2005.5	2002.8	2004.1
5°	2058.4	2062.4	2082.3	2104.8	2110.1	2104.8	2111.4	2120.7	2120.7	2120.7	2118.1
7.5°	2137.9	2152.5	2175.0	2208.1	2214.7	2221.4	2233.3	2225.3	2228.0	2239.9	2235.9
10°	2214.7	2235.9	2261.1	2288.9	2303.5	2312.8	2318.1	2330.0	2357.8	2326.0	2337.9
12.5°	2287.6	2318.1	2344.6	2375.0	2385.6	2397.5	2401.5	2412.1	2412.1	2410.8	2420.1
15°	2335.3	2363.1	2386.9	2406.8	2409.5	2406.8	2404.2	2405.5	2409.5	2393.6	2402.8
17.5°	2345.9	2348.5	2356.5	2348.5	2349.9	2322.0	2306.1	2302.2	2265.1	2266.4	2296.9
20°	2294.2	2249.2	2237.3	2193.6	2167.1	2095.5	2092.9	2073.0	1994.9	2018.7	2013.4
22.5°	2152.5	2075.7	1973.7	1923.3	1898.2	1822.7	1764.4	1723.3	1695.5	1667.7	1655.8
25°	1965.7	1841.2	1696.8	1597.5	1582.9	1512.7	1405.4	1355.1	1295.5	1276.9	1308.7
27.5°	1724.6	1563.0	1400.1	1247.8	1220.0	1156.4	1102.1	1066.3	997.4	993.5	996.1
30°	1397.5	1234.5	1098.1	998.8	929.9	900.7	865.0	838.5	810.7	821.3	823.9
32.5°	1148.4	993.5	866.3	813.3	781.5	763.0	732.5	715.3	703.4	699.4	698.1
35°	912.7	809.3	752.4	700.7	682.2	668.9	646.4	638.5	627.9	629.2	629.2
37.5°	781.5	695.4	653.0	626.5	609.3	602.7	588.1	580.2	573.6	570.9	574.9
40°	674.2	614.6	588.1	564.3	549.7	547.1	539.1	529.8	521.9	523.2	527.2
42.5°	596.1	561.6	529.8	511.3	500.7	496.7	490.1	483.5	483.5	479.5	478.2
45°	533.8	506.0	479.5	462.3	455.7	450.4	442.4	441.1	435.8	437.1	438.4
47.5°	478.2	455.7	435.8	418.6	412.0	410.6	402.7	397.4	397.4	396.1	394.7
50°	427.8	405.3	388.1	378.8	369.6	366.9	365.6	364.3	361.6	361.6	362.9
52.5°	386.8	364.3	351.0	343.1	337.8	335.1	335.1	333.8	333.8	333.8	332.5
55°	341.7	323.2	312.6	310.0	307.3	306.0	304.7	302.0	300.7	303.3	300.7
57.5°	299.4	292.7	283.5	280.8	274.2	274.2	270.2	267.6	264.9	267.6	267.6
60°	266.2	257.0	251.7	243.7	238.4	233.1	226.5	225.2	222.5	221.2	219.9
62.5°	231.8	223.9	210.6	198.7	190.7	185.4	182.8	181.5	181.5	180.1	180.1
65°	193.4	174.8	168.2	164.3	162.9	161.6	159.0	157.6	159.0	157.6	159.0
67.5°	151.0	148.4	144.4	141.7	140.4	139.1	139.1	137.8	137.8	137.8	137.8
70°	131.1	124.5	123.2	120.5	120.5	119.2	119.2	119.2	119.2	117.9	120.5
72.5°	108.6	104.6	103.3	102.0	102.0	102.0	100.7	100.7	100.7	99.3	100.7
75°	88.7	87.4	84.8	84.8	83.5	84.8	83.5	83.5	82.1	83.5	83.5
77.5°	71.5	70.2	68.9	68.9	67.6	67.6	67.6	67.6	67.6	67.6	68.9
80°	54.3	53.0	51.7	53.0	51.7	53.0	51.7	51.7	53.0	51.7	51.7
82.5°	39.7	38.4	38.4	37.1	37.1	37.1	37.1	37.1	37.1	37.1	37.1
85°	23.8	22.5	22.5	23.8	22.5	23.8	22.5	22.5	22.5	23.8	23.8
87.5°	10.6	11.9	10.6	10.6	10.6	10.6	10.6	10.6	10.6	10.6	11.9
90°	34.3	33.8	33.4	32.9	32.7	32.8	33.0	33.3	33.5	33.7	33.5
92.5°	31.0	31.2	31.5	31.7	31.8	31.8	31.8	31.8	31.8	31.8	31.8
95°	63.5	63.5	63.5	63.5	63.5	63.3	62.8	62.4	61.9	61.5	61.9
97.5°	99.2	99.2	99.2	99.2	99.2	99.2	99.2	99.2	99.2	99.2	99.2
100°	136.9	136.9	136.9	136.9	136.9	136.8	136.6	136.4	136.2	136.0	136.2
102.5°	177.8	178.0	178.3	178.5	178.6	178.5	178.3	178.0	177.8	177.6	177.8
105°	218.7	219.2	219.6	220.1	220.3	220.3	220.3	220.3	220.3	220.3	220.3
107.5°	263.2	263.4	263.7	263.9	264.0	263.4	262.3	261.2	260.1	259.0	260.1
110°	308.6	308.6	308.6	308.6	308.6	308.3	307.6	306.9	306.3	305.6	306.3

TEST NUMBER: P1000242

CATALOG NUMBER: SA2XXRDIP-B865D925UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	354.6	354.0	353.3	352.6	352.3	352.1	351.6	351.2	350.7	350.3	350.7
115°	400.7	400.5	400.2	400.0	399.9	399.6	398.9	398.2	397.6	396.9	397.6
117.5°	445.9	445.3	444.6	443.9	443.6	443.3	442.6	441.9	441.3	440.6	441.3
120°	490.2	490.2	490.2	490.2	490.2	489.9	489.2	488.5	487.9	487.2	487.9
122.5°	537.2	536.5	535.9	535.2	534.9	534.7	534.2	533.8	533.3	532.9	533.3
125°	582.8	582.2	581.5	580.8	580.5	580.4	580.2	579.9	579.7	579.5	579.7
127.5°	627.3	626.4	625.5	624.6	624.2	623.9	623.2	622.5	621.9	621.2	621.9
130°	672.4	671.9	671.5	671.0	670.8	670.4	669.5	668.6	667.8	666.9	667.8
132.5°	717.4	716.3	715.2	714.1	713.5	713.2	712.5	711.8	711.2	710.5	711.2
135°	759.9	759.7	759.4	759.2	759.1	758.8	758.1	757.5	756.8	756.2	756.8
137.5°	801.6	801.4	801.1	800.9	800.8	800.4	799.5	798.6	797.7	796.8	797.7
140°	843.5	843.5	843.5	843.5	843.5	843.1	842.2	841.3	840.4	839.5	840.4
142.5°	881.4	881.6	881.9	882.1	882.2	881.8	880.9	880.0	879.1	878.2	879.1
145°	920.1	920.3	920.6	920.8	920.9	920.5	919.6	918.7	917.8	916.9	917.8
147.5°	954.0	954.5	954.9	955.4	955.6	955.2	954.3	953.4	952.6	951.7	952.6
150°	986.1	986.7	987.4	988.1	988.4	988.1	987.4	986.7	986.1	985.4	986.1
152.5°	1018.0	1018.9	1019.8	1020.7	1021.1	1020.7	1019.8	1018.9	1018.0	1017.1	1018.0
155°	1044.0	1045.1	1046.2	1047.3	1047.9	1047.6	1046.9	1046.2	1045.6	1044.9	1045.6
157.5°	1069.3	1070.9	1072.4	1073.9	1074.7	1074.1	1073.0	1071.9	1070.8	1069.7	1070.8
160°	1091.9	1093.2	1094.5	1095.8	1096.5	1096.1	1095.2	1094.3	1093.5	1092.6	1093.5
162.5°	1112.0	1113.5	1115.1	1116.6	1117.4	1116.8	1115.7	1114.6	1113.5	1112.4	1113.5
165°	1128.8	1130.4	1131.9	1133.4	1134.2	1133.7	1132.6	1131.5	1130.4	1129.3	1130.4
167.5°	1143.7	1145.3	1146.8	1148.3	1149.1	1148.6	1147.5	1146.4	1145.3	1144.2	1145.3
170°	1155.6	1157.2	1158.7	1160.2	1161.0	1160.3	1159.0	1157.7	1156.4	1155.1	1156.4
172.5°	1164.6	1166.1	1167.7	1169.2	1170.0	1169.3	1168.0	1166.7	1165.3	1164.0	1165.3
175°	1170.5	1172.1	1173.6	1175.1	1175.9	1175.2	1173.9	1172.6	1171.3	1170.0	1171.3
177.5°	1174.2	1175.6	1176.9	1178.2	1178.9	1178.2	1176.9	1175.6	1174.2	1172.9	1174.2
180°	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9

TEST NUMBER: P1000242

CATALOG NUMBER: SA2XXRDIP-B865D925UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1
2.5°	2009.4	2000.2	1997.5	2000.2	1997.5	1998.8	1989.6	1955.1	1964.4	1949.8	1957.8
5°	2123.3	2115.4	2098.2	2095.5	2092.9	2090.2	2077.0	2046.5	2034.6	2014.7	2013.4
7.5°	2232.0	2232.0	2218.7	2209.4	2197.5	2188.3	2171.0	2126.0	2107.5	2083.6	2070.4
10°	2339.3	2304.8	2319.4	2310.1	2281.0	2275.7	2243.9	2217.4	2181.6	2157.8	2136.6
12.5°	2416.1	2405.5	2392.2	2384.3	2376.3	2359.1	2337.9	2270.4	2251.8	2204.2	2180.3
15°	2413.4	2406.8	2410.8	2410.8	2408.1	2404.2	2386.9	2337.9	2306.1	2259.8	2218.7
17.5°	2283.6	2300.8	2318.1	2330.0	2356.5	2368.4	2384.3	2355.2	2335.3	2295.5	2251.8
20°	2057.1	2099.5	2149.8	2160.4	2184.3	2254.5	2286.3	2311.4	2319.4	2306.1	2270.4
22.5°	1741.9	1777.6	1899.5	1896.8	1931.3	2014.7	2107.5	2183.0	2242.6	2275.7	2262.4
25°	1364.3	1414.7	1479.6	1528.6	1641.2	1765.7	1880.9	2001.5	2104.8	2196.2	2218.7
27.5°	1031.9	1098.1	1149.8	1214.7	1271.6	1418.7	1567.0	1755.1	1875.6	2049.2	2139.2
30°	834.5	865.0	916.6	947.1	974.9	1087.5	1255.7	1441.2	1653.1	1853.1	2008.1
32.5°	712.6	733.8	772.2	785.5	814.6	890.1	996.1	1165.7	1384.2	1626.6	1830.6
35°	639.8	662.3	670.3	682.2	706.0	753.7	826.6	949.7	1147.1	1384.2	1627.9
37.5°	577.5	589.5	612.0	619.9	627.9	663.6	712.6	798.7	929.9	1124.6	1394.8
40°	533.8	540.4	552.4	559.0	564.3	589.5	633.2	691.4	788.1	936.5	1185.5
42.5°	487.5	495.4	503.4	511.3	517.9	537.8	564.3	619.9	684.8	797.4	977.6
45°	442.4	447.7	457.0	462.3	471.6	487.5	511.3	549.7	608.0	679.5	825.2
47.5°	401.4	408.0	412.0	418.6	425.2	442.4	464.9	490.1	537.8	608.0	714.0
50°	364.3	372.2	377.5	378.8	384.1	400.0	418.6	446.4	476.9	531.2	623.9
52.5°	337.8	339.1	343.1	348.4	347.0	356.3	373.5	394.7	426.5	470.2	537.8
55°	307.3	311.3	313.9	315.3	315.3	323.2	332.5	352.3	377.5	413.3	470.2
57.5°	268.9	272.9	280.8	283.5	287.4	291.4	295.4	308.6	329.8	364.3	410.6
60°	229.2	231.8	239.8	245.1	247.7	258.3	263.6	274.2	286.1	311.3	355.0
62.5°	184.1	186.8	190.7	196.0	201.3	217.2	230.5	241.1	250.4	267.6	303.3
65°	160.3	161.6	164.3	165.6	166.9	173.5	185.4	200.0	217.2	230.5	251.7
67.5°	139.1	140.4	141.7	144.4	145.7	147.0	152.3	156.3	173.5	192.1	208.0
70°	119.2	121.9	123.2	123.2	124.5	127.2	129.8	135.1	140.4	149.7	169.6
72.5°	100.7	102.0	104.6	104.6	104.6	107.3	109.9	112.6	115.2	120.5	128.5
75°	83.5	86.1	86.1	86.1	87.4	87.4	90.1	92.7	95.4	99.3	102.0
77.5°	68.9	68.9	68.9	68.9	70.2	70.2	71.5	74.2	75.5	76.8	79.5
80°	51.7	53.0	53.0	53.0	54.3	54.3	54.3	57.0	58.3	58.3	60.9
82.5°	38.4	38.4	38.4	39.7	38.4	39.7	39.7	41.1	39.7	41.1	42.4
85°	23.8	23.8	23.8	25.2	25.2	25.2	25.2	25.2	25.2	25.2	26.5
87.5°	11.9	11.9	11.9	11.9	11.9	11.9	11.9	11.9	13.2	11.9	11.9
90°	33.3	33.0	32.8	32.7	32.9	33.4	33.8	34.3	34.7	29.9	25.0
92.5°	31.8	31.8	31.8	31.8	31.7	31.5	31.2	31.0	30.8	30.6	30.4
95°	62.4	62.8	63.3	63.5	63.5	63.5	63.5	63.5	63.5	63.1	62.6
97.5°	99.2	99.2	99.2	99.2	99.2	99.2	99.2	99.2	99.2	98.3	97.5
100°	136.4	136.6	136.8	136.9	136.9	136.9	136.9	136.9	136.9	136.3	135.6
102.5°	178.0	178.3	178.5	178.6	178.5	178.3	178.0	177.8	177.6	176.7	175.9
105°	220.3	220.3	220.3	220.3	220.1	219.6	219.2	218.7	218.3	217.9	217.4
107.5°	261.2	262.3	263.4	264.0	263.9	263.7	263.4	263.2	263.0	263.0	263.0
110°	306.9	307.6	308.3	308.6	308.6	308.6	308.6	308.6	308.6	308.6	308.6

TEST NUMBER: P1000242

CATALOG NUMBER: SA2XXRDIP-B865D925UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	351.2	351.6	352.1	352.3	352.6	353.3	354.0	354.6	355.3	355.5	355.7
115°	398.2	398.9	399.6	399.9	400.0	400.2	400.5	400.7	400.9	401.3	401.8
117.5°	441.9	442.6	443.3	443.6	443.9	444.6	445.3	445.9	446.6	447.7	448.8
120°	488.5	489.2	489.9	490.2	490.2	490.2	490.2	490.2	490.2	492.0	493.8
122.5°	533.8	534.2	534.7	534.9	535.2	535.9	536.5	537.2	537.8	538.9	540.0
125°	579.9	580.2	580.4	580.5	580.8	581.5	582.2	582.8	583.5	584.2	584.8
127.5°	622.5	623.2	623.9	624.2	624.6	625.5	626.4	627.3	628.2	629.1	629.9
130°	668.6	669.5	670.4	670.8	671.0	671.5	671.9	672.4	672.8	673.2	673.7
132.5°	711.8	712.5	713.2	713.5	714.1	715.2	716.3	717.4	718.5	718.3	718.1
135°	757.5	758.1	758.8	759.1	759.2	759.4	759.7	759.9	760.1	759.7	759.2
137.5°	798.6	799.5	800.4	800.8	800.9	801.1	801.4	801.6	801.8	801.4	800.9
140°	841.3	842.2	843.1	843.5	843.5	843.5	843.5	843.5	843.5	842.4	841.3
142.5°	880.0	880.9	881.8	882.2	882.1	881.9	881.6	881.4	881.2	880.5	879.9
145°	918.7	919.6	920.5	920.9	920.8	920.6	920.3	920.1	919.9	918.6	917.2
147.5°	953.4	954.3	955.2	955.6	955.4	954.9	954.5	954.0	953.6	952.7	951.9
150°	986.7	987.4	988.1	988.4	988.1	987.4	986.7	986.1	985.4	984.5	983.6
152.5°	1018.9	1019.8	1020.7	1021.1	1020.7	1019.8	1018.9	1018.0	1017.1	1016.0	1014.9
155°	1046.2	1046.9	1047.6	1047.9	1047.3	1046.2	1045.1	1044.0	1042.9	1042.3	1041.6
157.5°	1071.9	1073.0	1074.1	1074.7	1073.9	1072.4	1070.9	1069.3	1067.8	1067.4	1066.9
160°	1094.3	1095.2	1096.1	1096.5	1095.8	1094.5	1093.2	1091.9	1090.6	1090.4	1090.2
162.5°	1114.6	1115.7	1116.8	1117.4	1116.6	1115.1	1113.5	1112.0	1110.4	1110.2	1110.0
165°	1131.5	1132.6	1133.7	1134.2	1133.4	1131.9	1130.4	1128.8	1127.3	1127.3	1127.3
167.5°	1146.4	1147.5	1148.6	1149.1	1148.3	1146.8	1145.3	1143.7	1142.2	1142.2	1142.2
170°	1157.7	1159.0	1160.3	1161.0	1160.2	1158.7	1157.2	1155.6	1154.1	1154.3	1154.5
172.5°	1166.7	1168.0	1169.3	1170.0	1169.2	1167.7	1166.1	1164.6	1163.0	1163.2	1163.4
175°	1172.6	1173.9	1175.2	1175.9	1175.1	1173.6	1172.1	1170.5	1169.0	1169.4	1169.9
177.5°	1175.6	1176.9	1178.2	1178.9	1178.2	1176.9	1175.6	1174.2	1172.9	1173.3	1173.8
180°	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9

TEST NUMBER: P1000242

CATALOG NUMBER: SA2XXRDIP-B865D925UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1
2.5°	1945.9	1939.2	1939.2	1935.3	1935.3	1914.1	1914.1	1920.7	1912.7	1903.5	1890.2
5°	1996.2	1981.6	1977.6	1972.3	1955.1	1928.6	1918.0	1914.1	1898.2	1878.3	1855.8
7.5°	2043.9	2020.0	2008.1	1996.2	1973.7	1936.6	1915.4	1900.8	1877.0	1846.5	1817.4
10°	2090.2	2059.8	2029.3	2014.7	1982.9	1936.6	1906.1	1882.3	1847.8	1806.8	1765.7
12.5°	2132.6	2069.0	2063.7	2034.6	1988.2	1935.3	1888.9	1854.5	1810.7	1763.1	1715.4
15°	2169.7	2104.8	2073.0	2046.5	1985.6	1919.4	1870.3	1828.0	1769.7	1715.4	1657.1
17.5°	2188.3	2118.1	2096.9	2053.1	1990.9	1904.8	1838.6	1786.9	1723.3	1658.4	1592.2
20°	2206.8	2124.7	2090.2	2059.8	1975.0	1877.0	1802.8	1743.2	1673.0	1596.2	1523.3
22.5°	2216.1	2124.7	2083.6	2041.2	1959.1	1846.5	1759.1	1688.9	1606.8	1528.6	1441.2
25°	2200.2	2116.7	2067.7	2024.0	1931.3	1809.4	1708.7	1629.3	1541.8	1453.1	1364.3
27.5°	2160.4	2098.2	2041.2	1996.2	1892.9	1761.7	1655.8	1565.7	1475.6	1376.3	1286.2
30°	2086.3	2058.4	2013.4	1963.1	1850.5	1719.3	1593.5	1500.8	1401.4	1302.1	1208.0
32.5°	1971.0	1994.9	1965.7	1922.0	1800.1	1661.1	1527.3	1433.2	1324.6	1217.3	1131.2
35°	1830.6	1915.4	1899.5	1869.0	1747.2	1598.8	1465.0	1351.1	1242.5	1133.9	1047.8
37.5°	1677.0	1805.4	1818.7	1800.1	1686.2	1535.2	1388.2	1276.9	1165.7	1055.7	968.3
40°	1466.3	1663.7	1706.1	1714.0	1622.6	1458.4	1304.7	1196.1	1086.2	978.9	872.9
42.5°	1272.9	1522.0	1575.0	1608.1	1541.8	1382.9	1227.9	1107.4	998.8	902.1	796.1
45°	1091.5	1351.1	1437.2	1479.6	1450.4	1296.8	1136.5	1023.9	924.6	835.8	733.8
47.5°	904.7	1165.7	1286.2	1353.8	1353.8	1209.4	1049.1	937.8	842.5	766.9	676.9
50°	780.2	997.4	1121.9	1210.7	1234.5	1120.6	969.6	861.0	770.9	688.8	619.9
52.5°	665.0	859.7	963.0	1055.7	1124.6	1025.2	880.9	782.8	694.1	617.3	563.0
55°	574.9	720.6	814.6	916.6	993.5	928.6	794.8	699.4	622.6	559.0	512.6
57.5°	488.8	615.9	692.8	782.8	865.0	816.0	708.7	626.5	559.0	503.4	462.3
60°	415.9	519.2	578.9	649.1	751.1	716.6	627.9	552.4	498.1	447.7	413.3
62.5°	353.7	435.8	486.1	536.5	629.2	613.3	544.4	486.1	439.8	397.4	368.2
65°	290.1	357.6	397.4	441.1	515.3	521.9	466.3	425.2	382.8	345.7	319.2
67.5°	234.5	287.4	323.2	360.3	419.9	438.4	400.0	365.6	329.8	299.4	275.5
70°	189.4	226.5	253.0	282.1	331.2	353.7	333.8	310.0	280.8	255.6	234.5
72.5°	149.7	173.5	189.4	211.9	251.7	274.2	272.9	251.7	230.5	213.3	196.0
75°	109.9	128.5	141.7	156.3	188.1	209.3	214.6	205.3	184.1	170.9	157.6
77.5°	83.5	94.0	100.7	111.3	133.8	152.3	160.3	157.6	143.1	132.5	123.2
80°	63.6	66.2	68.9	72.9	91.4	108.6	113.9	112.6	104.6	100.7	90.1
82.5°	45.0	46.4	47.7	49.0	55.6	70.2	75.5	78.2	71.5	67.6	58.3
85°	26.5	27.8	27.8	30.5	31.8	35.8	45.0	45.0	43.7	38.4	37.1
87.5°	13.2	13.2	11.9	11.9	13.2	14.6	17.2	19.9	17.2	15.9	14.6
90°	20.2	15.3	12.9	11.6	8.9	6.3	3.6	1.0	3.6	6.3	8.9
92.5°	30.1	29.9	29.8	28.9	27.1	25.4	23.6	21.8	23.6	25.4	27.1
95°	62.2	61.7	61.5	60.4	58.2	56.0	53.8	51.6	53.8	56.0	58.2
97.5°	96.6	95.7	95.3	94.3	92.3	90.3	88.3	86.3	88.3	90.3	92.3
100°	135.0	134.3	134.0	133.1	131.3	129.6	127.8	126.0	127.8	129.6	131.3
102.5°	175.0	174.1	173.7	173.0	171.7	170.4	169.0	167.7	169.0	170.4	171.7
105°	217.0	216.5	216.3	216.0	215.3	214.7	214.0	213.4	214.0	214.7	215.3
107.5°	263.0	263.0	263.0	262.6	261.7	260.8	259.9	259.0	259.9	260.8	261.7
110°	308.6	308.6	308.6	307.9	306.6	305.3	304.0	302.7	304.0	305.3	306.6

TEST NUMBER: P1000242

CATALOG NUMBER: SA2XXRDIP-B865D925UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	355.9	356.1	356.2	355.5	354.2	352.9	351.6	350.3	351.6	352.9	354.2
115°	402.2	402.7	402.9	402.2	400.9	399.6	398.2	396.9	398.2	399.6	400.9
117.5°	449.9	451.0	451.5	450.6	448.9	447.1	445.4	443.6	445.4	447.1	448.9
120°	495.5	497.3	498.2	497.3	495.5	493.8	492.0	490.2	492.0	493.8	495.5
122.5°	541.1	542.2	542.8	541.7	539.5	537.3	535.1	532.9	535.1	537.3	539.5
125°	585.5	586.2	586.5	585.5	583.5	581.5	579.5	577.5	579.5	581.5	583.5
127.5°	630.8	631.7	632.1	630.9	628.5	626.0	623.6	621.2	623.6	626.0	628.5
130°	674.1	674.6	674.8	673.4	670.5	667.6	664.8	661.9	664.8	667.6	670.5
132.5°	717.8	717.6	717.5	716.4	714.2	711.9	709.7	707.5	709.7	711.9	714.2
135°	758.8	758.3	758.1	756.9	754.5	752.0	749.6	747.2	749.6	752.0	754.5
137.5°	800.5	800.0	799.8	798.8	796.8	794.9	792.9	790.9	792.9	794.9	796.8
140°	840.2	839.1	838.5	837.5	835.5	833.6	831.6	829.6	831.6	833.6	835.5
142.5°	879.2	878.5	878.2	877.2	875.2	873.3	871.3	869.3	871.3	873.3	875.2
145°	915.9	914.6	913.9	913.1	911.6	910.1	908.5	907.0	908.5	910.1	911.6
147.5°	951.0	950.1	949.7	948.7	946.7	944.7	942.7	940.7	942.7	944.7	946.7
150°	982.7	981.8	981.4	980.7	979.4	978.1	976.8	975.5	976.8	978.1	979.4
152.5°	1013.8	1012.7	1012.2	1011.5	1010.2	1008.9	1007.5	1006.2	1007.5	1008.9	1010.2
155°	1041.0	1040.3	1040.0	1039.7	1039.0	1038.3	1037.7	1037.0	1037.7	1038.3	1039.0
157.5°	1066.5	1066.0	1065.8	1065.6	1065.1	1064.7	1064.2	1063.8	1064.2	1064.7	1065.1
160°	1089.9	1089.7	1089.6	1089.4	1088.9	1088.5	1088.0	1087.6	1088.0	1088.5	1088.9
162.5°	1109.7	1109.5	1109.4	1109.4	1109.4	1109.4	1109.4	1109.4	1109.4	1109.4	1109.4
165°	1127.3	1127.3	1127.3	1127.4	1127.6	1127.9	1128.1	1128.3	1128.1	1127.9	1127.6
167.5°	1142.2	1142.2	1142.2	1142.5	1143.2	1143.9	1144.5	1145.2	1144.5	1143.9	1143.2
170°	1154.8	1155.0	1155.1	1155.4	1156.1	1156.8	1157.4	1158.1	1157.4	1156.8	1156.1
172.5°	1163.7	1163.9	1164.0	1164.3	1165.0	1165.7	1166.3	1167.0	1166.3	1165.7	1165.0
175°	1170.3	1170.8	1171.0	1171.3	1172.0	1172.6	1173.3	1173.9	1173.3	1172.6	1172.0
177.5°	1174.2	1174.7	1174.9	1175.2	1175.9	1176.6	1177.2	1177.9	1177.2	1176.6	1175.9
180°	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9

TEST NUMBER: P1000242

CATALOG NUMBER: SA2XXRDIP-B865D925UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1
2.5°	1884.9	1886.2	1890.2	1878.3	1859.8	1851.8	1828.0	1824.0	1820.0	1820.0	1824.0
5°	1842.5	1837.2	1838.6	1816.0	1789.5	1773.7	1740.5	1745.8	1728.6	1718.0	1720.7
7.5°	1796.2	1781.6	1780.3	1751.1	1718.0	1688.9	1654.4	1646.5	1630.6	1612.0	1604.1
10°	1737.9	1727.3	1707.4	1674.3	1631.9	1608.1	1561.7	1533.9	1529.9	1502.1	1491.5
12.5°	1678.3	1659.7	1639.9	1593.5	1545.8	1507.4	1473.0	1442.5	1421.3	1397.5	1381.6
15°	1609.4	1586.9	1564.4	1515.4	1459.7	1421.3	1369.6	1324.6	1262.4	1213.3	1185.5
17.5°	1533.9	1508.7	1478.3	1424.0	1369.6	1316.7	1221.3	1168.3	1124.6	1095.5	1078.2
20°	1455.7	1427.9	1397.5	1343.2	1249.1	1156.4	1103.4	1062.3	1035.8	1006.7	985.5
22.5°	1373.6	1344.5	1311.4	1226.6	1127.2	1062.3	1021.3	982.9	944.4	928.6	918.0
25°	1296.8	1270.3	1227.9	1112.7	1034.5	974.9	928.6	903.4	883.5	862.3	842.5
27.5°	1217.3	1168.3	1108.7	1012.0	963.0	902.1	868.9	850.4	816.0	801.4	792.1
30°	1121.9	1067.6	1010.7	941.8	884.8	842.5	812.0	781.5	761.7	747.1	731.2
32.5°	1025.2	973.6	937.8	866.3	823.9	780.2	751.1	732.5	703.4	694.1	687.5
35°	941.8	898.1	866.3	808.0	768.3	728.5	707.3	679.5	661.0	643.8	633.2
37.5°	859.7	835.8	802.7	753.7	711.3	679.5	650.4	641.1	615.9	606.7	596.1
40°	802.7	766.9	739.1	696.7	661.0	626.5	608.0	586.8	569.6	555.0	551.0
42.5°	733.8	707.3	691.4	645.1	608.0	588.1	565.6	541.8	528.5	516.6	502.0
45°	682.2	658.3	635.8	598.7	565.6	540.4	520.6	504.7	482.2	476.9	454.3
47.5°	627.9	604.0	586.8	549.7	519.2	495.4	480.8	459.6	441.1	429.2	418.6
50°	573.6	553.7	537.8	506.0	479.5	454.3	434.5	413.3	405.3	385.5	378.8
52.5°	521.9	508.7	491.4	461.0	434.5	413.3	392.1	374.9	362.9	352.3	344.4
55°	478.2	457.0	449.0	415.9	393.4	370.9	352.3	341.7	327.2	320.6	313.9
57.5°	429.2	417.3	404.0	378.8	353.7	332.5	319.2	303.3	295.4	287.4	282.1
60°	386.8	369.6	359.0	337.8	315.3	295.4	283.5	271.5	260.9	254.3	243.7
62.5°	337.8	324.5	317.9	295.4	276.8	258.3	247.7	235.8	227.8	215.9	202.7
65°	295.4	284.8	276.8	258.3	241.1	223.9	213.3	198.7	188.1	181.5	180.1
67.5°	258.3	250.4	238.4	221.2	204.0	190.7	178.8	166.9	165.6	162.9	162.9
70°	217.2	209.3	202.7	184.1	169.6	155.0	152.3	148.4	144.4	143.1	140.4
72.5°	181.5	174.8	166.9	151.0	136.4	132.5	129.8	127.2	123.2	121.9	120.5
75°	147.0	137.8	132.5	117.9	113.9	111.3	108.6	104.6	102.0	100.7	98.0
77.5°	112.6	103.3	103.3	95.4	92.7	88.7	86.1	83.5	82.1	79.5	79.5
80°	79.5	79.5	76.8	72.9	68.9	67.6	63.6	62.3	60.9	62.3	59.6
82.5°	58.3	53.0	53.0	50.3	47.7	46.4	43.7	43.7	42.4	42.4	42.4
85°	33.1	33.1	31.8	29.1	27.8	27.8	26.5	26.5	25.2	25.2	23.8
87.5°	13.2	11.9	13.2	11.9	11.9	10.6	10.6	10.6	9.3	10.6	9.3
90°	11.6	12.9	15.3	20.2	25.0	29.9	34.7	34.3	33.8	33.4	32.9
92.5°	28.9	29.8	29.9	30.1	30.4	30.6	30.8	31.0	31.2	31.5	31.7
95°	60.4	61.5	61.7	62.2	62.6	63.1	63.5	63.5	63.5	63.5	63.5
97.5°	94.3	95.3	95.7	96.6	97.5	98.3	99.2	99.2	99.2	99.2	99.2
100°	133.1	134.0	134.3	135.0	135.6	136.3	136.9	136.9	136.9	136.9	136.9
102.5°	173.0	173.7	174.1	175.0	175.9	176.7	177.6	177.8	178.0	178.3	178.5
105°	216.0	216.3	216.5	217.0	217.4	217.9	218.3	218.7	219.2	219.6	220.1
107.5°	262.6	263.0	263.0	263.0	263.0	263.0	263.0	263.2	263.4	263.7	263.9
110°	307.9	308.6	308.6	308.6	308.6	308.6	308.6	308.6	308.6	308.6	308.6

TEST NUMBER: P1000242

CATALOG NUMBER: SA2XXRDIP-B865D925UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	355.5	356.2	356.1	355.9	355.7	355.5	355.3	354.6	354.0	353.3	352.6
115°	402.2	402.9	402.7	402.2	401.8	401.3	400.9	400.7	400.5	400.2	400.0
117.5°	450.6	451.5	451.0	449.9	448.8	447.7	446.6	445.9	445.3	444.6	443.9
120°	497.3	498.2	497.3	495.5	493.8	492.0	490.2	490.2	490.2	490.2	490.2
122.5°	541.7	542.8	542.2	541.1	540.0	538.9	537.8	537.2	536.5	535.9	535.2
125°	585.5	586.5	586.2	585.5	584.8	584.2	583.5	582.8	582.2	581.5	580.8
127.5°	630.9	632.1	631.7	630.8	629.9	629.1	628.2	627.3	626.4	625.5	624.6
130°	673.4	674.8	674.6	674.1	673.7	673.2	672.8	672.4	671.9	671.5	671.0
132.5°	716.4	717.5	717.6	717.8	718.1	718.3	718.5	717.4	716.3	715.2	714.1
135°	756.9	758.1	758.3	758.8	759.2	759.7	760.1	759.9	759.7	759.4	759.2
137.5°	798.8	799.8	800.0	800.5	800.9	801.4	801.8	801.6	801.4	801.1	800.9
140°	837.5	838.5	839.1	840.2	841.3	842.4	843.5	843.5	843.5	843.5	843.5
142.5°	877.2	878.2	878.5	879.2	879.9	880.5	881.2	881.4	881.6	881.9	882.1
145°	913.1	913.9	914.6	915.9	917.2	918.6	919.9	920.1	920.3	920.6	920.8
147.5°	948.7	949.7	950.1	951.0	951.9	952.7	953.6	954.0	954.5	954.9	955.4
150°	980.7	981.4	981.8	982.7	983.6	984.5	985.4	986.1	986.7	987.4	988.1
152.5°	1011.5	1012.2	1012.7	1013.8	1014.9	1016.0	1017.1	1018.0	1018.9	1019.8	1020.7
155°	1039.7	1040.0	1040.3	1041.0	1041.6	1042.3	1042.9	1044.0	1045.1	1046.2	1047.3
157.5°	1065.6	1065.8	1066.0	1066.5	1066.9	1067.4	1067.8	1069.3	1070.9	1072.4	1073.9
160°	1089.4	1089.6	1089.7	1089.9	1090.2	1090.4	1090.6	1091.9	1093.2	1094.5	1095.8
162.5°	1109.4	1109.4	1109.5	1109.7	1110.0	1110.2	1110.4	1112.0	1113.5	1115.1	1116.6
165°	1127.4	1127.3	1127.3	1127.3	1127.3	1127.3	1127.3	1128.8	1130.4	1131.9	1133.4
167.5°	1142.5	1142.2	1142.2	1142.2	1142.2	1142.2	1142.2	1143.7	1145.3	1146.8	1148.3
170°	1155.4	1155.1	1155.0	1154.8	1154.5	1154.3	1154.1	1155.6	1157.2	1158.7	1160.2
172.5°	1164.3	1164.0	1163.9	1163.7	1163.4	1163.2	1163.0	1164.6	1166.1	1167.7	1169.2
175°	1171.3	1171.0	1170.8	1170.3	1169.9	1169.4	1169.0	1170.5	1172.1	1173.6	1175.1
177.5°	1175.2	1174.9	1174.7	1174.2	1173.8	1173.3	1172.9	1174.2	1175.6	1176.9	1178.2
180°	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9

TEST NUMBER: P1000242

CATALOG NUMBER: SA2XXRDIP-B865D925UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1
2.5°	1824.0	1821.3	1813.4	1816.0	1812.1	1812.1	1809.4	1809.4	1809.4	1816.0	1812.1
5°	1724.6	1715.4	1706.1	1702.1	1698.1	1694.2	1694.2	1692.9	1704.8	1702.1	1712.7
7.5°	1601.5	1598.8	1580.3	1580.3	1573.6	1571.0	1577.6	1578.9	1580.3	1582.9	1589.5
10°	1491.5	1484.9	1458.4	1461.0	1457.1	1451.8	1455.7	1453.1	1462.4	1465.0	1462.4
12.5°	1361.7	1349.8	1320.6	1306.1	1290.2	1278.2	1292.8	1282.2	1319.3	1329.9	1359.0
15°	1189.5	1167.0	1147.1	1147.1	1132.5	1121.9	1128.6	1140.5	1148.4	1160.4	1165.7
17.5°	1074.3	1065.0	1049.1	1039.8	1035.8	1031.9	1031.9	1037.2	1054.4	1053.1	1063.7
20°	976.2	970.9	963.0	951.1	947.1	944.4	944.4	944.4	956.4	967.0	973.6
22.5°	908.7	904.7	899.4	883.5	875.6	872.9	879.5	883.5	892.8	900.7	907.4
25°	841.1	831.9	822.6	817.3	813.3	813.3	816.0	817.3	821.3	825.2	833.2
27.5°	785.5	778.9	765.6	751.1	751.1	747.1	749.7	752.4	761.7	774.9	781.5
30°	723.2	721.9	716.6	711.3	706.0	703.4	708.7	712.6	714.0	720.6	720.6
32.5°	678.2	668.9	659.7	654.4	651.7	650.4	651.7	657.0	657.0	665.0	674.2
35°	633.2	627.9	618.6	609.3	606.7	600.0	605.3	610.6	619.9	623.9	627.9
37.5°	584.2	577.5	573.6	570.9	565.6	566.9	563.0	570.9	578.9	577.5	580.2
40°	547.1	535.1	523.2	521.9	520.6	519.2	519.2	520.6	525.9	531.2	539.1
42.5°	499.4	495.4	484.8	474.2	471.6	468.9	466.3	471.6	482.2	491.4	495.4
45°	450.4	445.1	442.4	434.5	429.2	427.8	425.2	431.8	441.1	445.1	447.7
47.5°	405.3	404.0	396.1	397.4	393.4	394.7	393.4	397.4	397.4	401.4	404.0
50°	374.9	370.9	366.9	364.3	360.3	360.3	359.0	360.3	365.6	370.9	369.6
52.5°	344.4	337.8	336.5	335.1	332.5	335.1	331.2	332.5	337.8	340.4	339.1
55°	308.6	307.3	304.7	302.0	300.7	299.4	299.4	299.4	304.7	308.6	310.0
57.5°	280.8	274.2	268.9	268.9	263.6	262.3	264.9	266.2	270.2	272.9	275.5
60°	242.4	239.8	231.8	227.8	219.9	218.6	218.6	223.9	230.5	239.8	242.4
62.5°	201.3	197.4	196.0	196.0	196.0	196.0	196.0	196.0	196.0	197.4	197.4
65°	178.8	180.1	178.8	177.5	178.8	178.8	177.5	177.5	177.5	178.8	180.1
67.5°	160.3	159.0	160.3	159.0	157.6	157.6	156.3	157.6	159.0	160.3	160.3
70°	139.1	139.1	137.8	139.1	137.8	136.4	135.1	135.1	137.8	139.1	139.1
72.5°	119.2	119.2	117.9	117.9	115.2	115.2	116.6	115.2	115.2	119.2	119.2
75°	99.3	98.0	96.7	96.7	95.4	95.4	95.4	94.0	96.7	96.7	98.0
77.5°	78.2	78.2	78.2	76.8	76.8	75.5	75.5	76.8	76.8	76.8	78.2
80°	59.6	59.6	59.6	58.3	57.0	57.0	57.0	57.0	57.0	58.3	57.0
82.5°	41.1	41.1	41.1	41.1	41.1	39.7	39.7	39.7	41.1	41.1	39.7
85°	25.2	23.8	25.2	25.2	23.8	25.2	23.8	23.8	22.5	22.5	23.8
87.5°	10.6	9.3	7.9	7.9	9.3	7.9	7.9	7.9	9.3	7.9	7.9
90°	32.7	32.8	33.0	33.3	33.5	33.7	33.5	33.3	33.0	32.8	32.7
92.5°	31.8	31.8	31.8	31.8	31.8	31.8	31.8	31.8	31.8	31.8	31.8
95°	63.5	63.3	62.8	62.4	61.9	61.5	61.9	62.4	62.8	63.3	63.5
97.5°	99.2	99.2	99.2	99.2	99.2	99.2	99.2	99.2	99.2	99.2	99.2
100°	136.9	136.8	136.6	136.4	136.2	136.0	136.2	136.4	136.6	136.8	136.9
102.5°	178.6	178.5	178.3	178.0	177.8	177.6	177.8	178.0	178.3	178.5	178.6
105°	220.3	220.3	220.3	220.3	220.3	220.3	220.3	220.3	220.3	220.3	220.3
107.5°	264.0	263.4	262.3	261.2	260.1	259.0	260.1	261.2	262.3	263.4	264.0
110°	308.6	308.3	307.6	306.9	306.3	305.6	306.3	306.9	307.6	308.3	308.6

TEST NUMBER: P1000242

CATALOG NUMBER: SA2XXRDIP-B865D925UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	352.3	352.1	351.6	351.2	350.7	350.3	350.7	351.2	351.6	352.1	352.3
115°	399.9	399.6	398.9	398.2	397.6	396.9	397.6	398.2	398.9	399.6	399.9
117.5°	443.6	443.3	442.6	441.9	441.3	440.6	441.3	441.9	442.6	443.3	443.6
120°	490.2	489.9	489.2	488.5	487.9	487.2	487.9	488.5	489.2	489.9	490.2
122.5°	534.9	534.7	534.2	533.8	533.3	532.9	533.3	533.8	534.2	534.7	534.9
125°	580.5	580.4	580.2	579.9	579.7	579.5	579.7	579.9	580.2	580.4	580.5
127.5°	624.2	623.9	623.2	622.5	621.9	621.2	621.9	622.5	623.2	623.9	624.2
130°	670.8	670.4	669.5	668.6	667.8	666.9	667.8	668.6	669.5	670.4	670.8
132.5°	713.5	713.2	712.5	711.8	711.2	710.5	711.2	711.8	712.5	713.2	713.5
135°	759.1	758.8	758.1	757.5	756.8	756.2	756.8	757.5	758.1	758.8	759.1
137.5°	800.8	800.4	799.5	798.6	797.7	796.8	797.7	798.6	799.5	800.4	800.8
140°	843.5	843.1	842.2	841.3	840.4	839.5	840.4	841.3	842.2	843.1	843.5
142.5°	882.2	881.8	880.9	880.0	879.1	878.2	879.1	880.0	880.9	881.8	882.2
145°	920.9	920.5	919.6	918.7	917.8	916.9	917.8	918.7	919.6	920.5	920.9
147.5°	955.6	955.2	954.3	953.4	952.6	951.7	952.6	953.4	954.3	955.2	955.6
150°	988.4	988.1	987.4	986.7	986.1	985.4	986.1	986.7	987.4	988.1	988.4
152.5°	1021.1	1020.7	1019.8	1018.9	1018.0	1017.1	1018.0	1018.9	1019.8	1020.7	1021.1
155°	1047.9	1047.6	1046.9	1046.2	1045.6	1044.9	1045.6	1046.2	1046.9	1047.6	1047.9
157.5°	1074.7	1074.1	1073.0	1071.9	1070.8	1069.7	1070.8	1071.9	1073.0	1074.1	1074.7
160°	1096.5	1096.1	1095.2	1094.3	1093.5	1092.6	1093.5	1094.3	1095.2	1096.1	1096.5
162.5°	1117.4	1116.8	1115.7	1114.6	1113.5	1112.4	1113.5	1114.6	1115.7	1116.8	1117.4
165°	1134.2	1133.7	1132.6	1131.5	1130.4	1129.3	1130.4	1131.5	1132.6	1133.7	1134.2
167.5°	1149.1	1148.6	1147.5	1146.4	1145.3	1144.2	1145.3	1146.4	1147.5	1148.6	1149.1
170°	1161.0	1160.3	1159.0	1157.7	1156.4	1155.1	1156.4	1157.7	1159.0	1160.3	1161.0
172.5°	1170.0	1169.3	1168.0	1166.7	1165.3	1164.0	1165.3	1166.7	1168.0	1169.3	1170.0
175°	1175.9	1175.2	1173.9	1172.6	1171.3	1170.0	1171.3	1172.6	1173.9	1175.2	1175.9
177.5°	1178.9	1178.2	1176.9	1175.6	1174.2	1172.9	1174.2	1175.6	1176.9	1178.2	1178.9
180°	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9

TEST NUMBER: P1000242

CATALOG NUMBER: SA2XXRDIP-B865D925UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1
2.5°	1816.0	1822.7	1820.0	1805.4	1820.0	1824.0	1831.9	1839.9	1845.2	1853.1	1859.8
5°	1702.1	1715.4	1723.3	1715.4	1741.9	1745.8	1764.4	1775.0	1790.9	1804.1	1814.7
7.5°	1594.8	1605.4	1621.3	1624.0	1639.9	1658.4	1684.9	1711.4	1736.6	1749.8	1761.7
10°	1479.6	1498.1	1522.0	1516.7	1540.5	1569.7	1597.5	1639.9	1661.1	1684.9	1706.1
12.5°	1364.3	1376.3	1408.1	1418.7	1453.1	1475.6	1514.0	1540.5	1593.5	1621.3	1639.9
15°	1163.0	1212.0	1251.8	1299.4	1344.5	1386.9	1421.3	1469.0	1515.4	1536.5	1567.0
17.5°	1071.6	1094.1	1118.0	1141.8	1200.1	1275.6	1336.5	1388.2	1427.9	1455.7	1491.5
20°	976.2	998.8	1025.2	1047.8	1083.5	1137.8	1213.3	1302.1	1349.8	1378.9	1413.4
22.5°	908.7	929.9	947.1	967.0	994.8	1034.5	1091.5	1201.4	1265.0	1300.8	1331.2
25°	835.8	862.3	880.9	895.4	918.0	961.7	1008.0	1070.3	1184.2	1212.0	1254.4
27.5°	785.5	793.4	814.6	837.2	859.7	883.5	931.2	984.2	1061.0	1121.9	1173.6
30°	725.9	745.8	765.6	774.9	794.8	829.2	858.3	915.3	974.9	1022.6	1084.9
32.5°	680.8	692.8	706.0	728.5	747.1	770.9	800.1	847.8	898.1	928.6	976.2
35°	630.5	638.5	666.3	675.6	694.1	717.9	747.1	784.2	838.5	862.3	896.8
37.5°	582.8	601.4	609.3	630.5	647.7	671.6	692.8	735.2	770.9	798.7	830.5
40°	545.7	553.7	568.3	586.8	601.4	619.9	646.4	676.9	715.3	737.8	765.6
42.5°	500.7	507.3	525.9	536.5	560.3	577.5	593.4	630.5	665.0	682.2	710.0
45°	451.7	467.6	479.5	500.7	513.9	535.1	555.0	581.5	613.3	633.2	649.1
47.5°	409.3	425.2	437.1	457.0	478.2	487.5	508.7	536.5	565.6	581.5	604.0
50°	374.9	380.2	402.7	412.0	434.5	453.0	467.6	491.4	523.2	532.5	551.0
52.5°	341.7	345.7	360.3	372.2	392.1	408.0	426.5	449.0	475.5	490.1	504.7
55°	312.6	315.3	321.9	335.1	348.4	368.2	385.5	406.7	429.2	445.1	458.3
57.5°	279.5	284.8	290.1	298.0	311.3	329.8	348.4	368.2	386.8	397.4	414.6
60°	241.1	249.0	258.3	267.6	276.8	290.1	311.3	329.8	347.0	356.3	369.6
62.5°	200.0	215.9	223.9	234.5	242.4	254.3	270.2	291.4	303.3	315.3	325.9
65°	180.1	181.5	182.8	193.4	208.0	219.9	234.5	250.4	268.9	276.8	284.8
67.5°	160.3	161.6	164.3	165.6	170.9	184.1	200.0	217.2	231.8	237.1	245.1
70°	140.4	140.4	145.7	147.0	148.4	149.7	162.9	180.1	193.4	200.0	209.3
72.5°	119.2	120.5	123.2	124.5	127.2	129.8	133.8	143.1	159.0	165.6	176.2
75°	98.0	99.3	100.7	102.0	106.0	107.3	111.3	116.6	123.2	131.1	137.8
77.5°	78.2	78.2	79.5	82.1	84.8	86.1	90.1	92.7	95.4	99.3	104.6
80°	58.3	59.6	59.6	62.3	62.3	63.6	64.9	68.9	71.5	74.2	76.8
82.5°	39.7	42.4	42.4	42.4	43.7	45.0	46.4	46.4	49.0	50.3	54.3
85°	23.8	25.2	25.2	25.2	23.8	26.5	26.5	27.8	27.8	27.8	29.1
87.5°	9.3	7.9	9.3	9.3	9.3	10.6	9.3	9.3	10.6	11.9	11.9
90°	32.9	33.4	33.8	34.3	34.7	29.9	25.0	20.2	15.3	12.9	11.6
92.5°	31.7	31.5	31.2	31.0	30.8	30.6	30.4	30.1	29.9	29.8	28.9
95°	63.5	63.5	63.5	63.5	63.5	63.1	62.6	62.2	61.7	61.5	60.4
97.5°	99.2	99.2	99.2	99.2	99.2	98.3	97.5	96.6	95.7	95.3	94.3
100°	136.9	136.9	136.9	136.9	136.9	136.3	135.6	135.0	134.3	134.0	133.1
102.5°	178.5	178.3	178.0	177.8	177.6	176.7	175.9	175.0	174.1	173.7	173.0
105°	220.1	219.6	219.2	218.7	218.3	217.9	217.4	217.0	216.5	216.3	216.0
107.5°	263.9	263.7	263.4	263.2	263.0	263.0	263.0	263.0	263.0	263.0	262.6
110°	308.6	308.6	308.6	308.6	308.6	308.6	308.6	308.6	308.6	308.6	307.9

TEST NUMBER: P1000242

CATALOG NUMBER: SA2XXRDIP-B865D925UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	352.6	353.3	354.0	354.6	355.3	355.5	355.7	355.9	356.1	356.2	355.5
115°	400.0	400.2	400.5	400.7	400.9	401.3	401.8	402.2	402.7	402.9	402.2
117.5°	443.9	444.6	445.3	445.9	446.6	447.7	448.8	449.9	451.0	451.5	450.6
120°	490.2	490.2	490.2	490.2	490.2	492.0	493.8	495.5	497.3	498.2	497.3
122.5°	535.2	535.9	536.5	537.2	537.8	538.9	540.0	541.1	542.2	542.8	541.7
125°	580.8	581.5	582.2	582.8	583.5	584.2	584.8	585.5	586.2	586.5	585.5
127.5°	624.6	625.5	626.4	627.3	628.2	629.1	629.9	630.8	631.7	632.1	630.9
130°	671.0	671.5	671.9	672.4	672.8	673.2	673.7	674.1	674.6	674.8	673.4
132.5°	714.1	715.2	716.3	717.4	718.5	718.3	718.1	717.8	717.6	717.5	716.4
135°	759.2	759.4	759.7	759.9	760.1	759.7	759.2	758.8	758.3	758.1	756.9
137.5°	800.9	801.1	801.4	801.6	801.8	801.4	800.9	800.5	800.0	799.8	798.8
140°	843.5	843.5	843.5	843.5	843.5	842.4	841.3	840.2	839.1	838.5	837.5
142.5°	882.1	881.9	881.6	881.4	881.2	880.5	879.9	879.2	878.5	878.2	877.2
145°	920.8	920.6	920.3	920.1	919.9	918.6	917.2	915.9	914.6	913.9	913.1
147.5°	955.4	954.9	954.5	954.0	953.6	952.7	951.9	951.0	950.1	949.7	948.7
150°	988.1	987.4	986.7	986.1	985.4	984.5	983.6	982.7	981.8	981.4	980.7
152.5°	1020.7	1019.8	1018.9	1018.0	1017.1	1016.0	1014.9	1013.8	1012.7	1012.2	1011.5
155°	1047.3	1046.2	1045.1	1044.0	1042.9	1042.3	1041.6	1041.0	1040.3	1040.0	1039.7
157.5°	1073.9	1072.4	1070.9	1069.3	1067.8	1067.4	1066.9	1066.5	1066.0	1065.8	1065.6
160°	1095.8	1094.5	1093.2	1091.9	1090.6	1090.4	1090.2	1089.9	1089.7	1089.6	1089.4
162.5°	1116.6	1115.1	1113.5	1112.0	1110.4	1110.2	1110.0	1109.7	1109.5	1109.4	1109.4
165°	1133.4	1131.9	1130.4	1128.8	1127.3	1127.3	1127.3	1127.3	1127.3	1127.3	1127.4
167.5°	1148.3	1146.8	1145.3	1143.7	1142.2	1142.2	1142.2	1142.2	1142.2	1142.2	1142.5
170°	1160.2	1158.7	1157.2	1155.6	1154.1	1154.3	1154.5	1154.8	1155.0	1155.1	1155.4
172.5°	1169.2	1167.7	1166.1	1164.6	1163.0	1163.2	1163.4	1163.7	1163.9	1164.0	1164.3
175°	1175.1	1173.6	1172.1	1170.5	1169.0	1169.4	1169.9	1170.3	1170.8	1171.0	1171.3
177.5°	1178.2	1176.9	1175.6	1174.2	1172.9	1173.3	1173.8	1174.2	1174.7	1174.9	1175.2
180°	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9	1175.9

TEST NUMBER: P1000242

CATALOG NUMBER: SA2XXRDIP-B865D925UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1906.1	1906.1	1906.1	1906.1
2.5°	1871.7	1867.7	1891.5	1918.0
5°	1833.3	1839.9	1870.3	1907.4
7.5°	1793.5	1808.1	1843.9	1892.9
10°	1737.9	1764.4	1818.7	1869.0
12.5°	1683.6	1719.3	1771.0	1830.6
15°	1622.6	1662.4	1726.0	1797.5
17.5°	1555.1	1600.1	1674.3	1752.5
20°	1483.6	1543.2	1621.3	1706.1
22.5°	1404.1	1475.6	1556.4	1650.5
25°	1327.3	1405.4	1486.2	1594.8
27.5°	1251.8	1328.6	1418.7	1528.6
30°	1176.3	1246.5	1343.2	1461.0
32.5°	1095.5	1168.3	1270.3	1390.8
35°	1021.3	1094.1	1189.5	1308.7
37.5°	941.8	1019.9	1111.3	1234.5
40°	849.1	940.5	1029.2	1147.1
42.5°	772.2	868.9	955.0	1066.3
45°	711.3	802.7	874.2	982.9
47.5°	654.4	728.5	801.4	902.1
50°	600.0	657.0	732.5	822.6
52.5°	544.4	593.4	658.3	743.1
55°	494.1	540.4	598.7	663.6
57.5°	447.7	480.8	539.1	597.4
60°	396.1	430.5	475.5	524.5
62.5°	352.3	378.8	421.2	462.3
65°	306.0	331.2	362.9	401.4
67.5°	263.6	286.1	311.3	341.7
70°	225.2	242.4	260.9	287.4
72.5°	184.1	202.7	219.9	241.1
75°	151.0	159.0	173.5	188.1
77.5°	116.6	127.2	135.1	147.0
80°	83.5	92.7	95.4	104.6
82.5°	55.6	60.9	66.2	68.9
85°	31.8	34.4	39.7	41.1
87.5°	11.9	13.2	15.9	18.5
90°	8.9	6.3	3.6	1.0
92.5°	27.1	25.4	23.6	21.8
95°	58.2	56.0	53.8	51.6
97.5°	92.3	90.3	88.3	86.3
100°	131.3	129.6	127.8	126.0
102.5°	171.7	170.4	169.0	167.7
105°	215.3	214.7	214.0	213.4
107.5°	261.7	260.8	259.9	259.0
110°	306.6	305.3	304.0	302.7

TEST NUMBER: P1000242

CATALOG NUMBER: SA2XXRDIP-B865D925UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	354.2	352.9	351.6	350.3
115°	400.9	399.6	398.2	396.9
117.5°	448.9	447.1	445.4	443.6
120°	495.5	493.8	492.0	490.2
122.5°	539.5	537.3	535.1	532.9
125°	583.5	581.5	579.5	577.5
127.5°	628.5	626.0	623.6	621.2
130°	670.5	667.6	664.8	661.9
132.5°	714.2	711.9	709.7	707.5
135°	754.5	752.0	749.6	747.2
137.5°	796.8	794.9	792.9	790.9
140°	835.5	833.6	831.6	829.6
142.5°	875.2	873.3	871.3	869.3
145°	911.6	910.1	908.5	907.0
147.5°	946.7	944.7	942.7	940.7
150°	979.4	978.1	976.8	975.5
152.5°	1010.2	1008.9	1007.5	1006.2
155°	1039.0	1038.3	1037.7	1037.0
157.5°	1065.1	1064.7	1064.2	1063.8
160°	1088.9	1088.5	1088.0	1087.6
162.5°	1109.4	1109.4	1109.4	1109.4
165°	1127.6	1127.9	1128.1	1128.3
167.5°	1143.2	1143.9	1144.5	1145.2
170°	1156.1	1156.8	1157.4	1158.1
172.5°	1165.0	1165.7	1166.3	1167.0
175°	1172.0	1172.6	1173.3	1173.9
177.5°	1175.9	1176.6	1177.2	1177.9
180°	1175.9	1175.9	1175.9	1175.9

(END OF REPORT)