

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001832

Luminaire Tested: SA4XXDIP-B795D365UB2750-4F0-XX-W2A-D_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001832
REPORT IS A COMBINATION OF REPORTS P996455 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B795D365UB2750-4F0-XX-W2A-D_3500K
Description: Define 4 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4748.0 lumens
Efficiency: N/A
Efficacy: 105.0 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 45.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001832

CATALOG NUMBER: SA4XXDIP-B795D365UB2750-4F0-XX-W2A-D_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1001832

CATALOG NUMBER: SA4XXDIP-B795D365UB2750-4F0-XX-W2A-D_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	104	104	104	104	91	91	91	79	79	79	69	69	69
1	100	95	90	86	93	89	85	81	78	75	72	68	66	64	59	57	56
2	90	82	75	69	84	77	71	66	68	63	59	59	55	52	51	48	46
3	82	72	64	57	76	67	60	54	59	53	49	52	47	43	45	41	38
4	75	63	55	48	70	59	52	46	52	46	41	46	41	37	40	36	33
5	69	56	47	41	64	53	45	39	47	40	35	41	36	32	36	31	28
6	63	50	42	35	59	47	40	34	42	36	31	37	32	28	32	28	25
7	58	45	37	31	54	43	35	30	38	32	27	34	28	24	29	25	22
8	54	41	33	27	51	39	31	26	35	28	24	31	25	22	27	23	19
9	50	38	30	24	47	36	28	23	32	26	21	28	23	19	25	21	18
10	47	34	27	22	44	33	26	21	29	23	19	26	21	18	23	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7821	7821	7821
5°	7843	7617	7631
10°	7791	7467	7446
15°	7718	7299	7237
20°	7611	7116	7034
25°	7489	6915	6816
30°	7357	6715	6593
35°	7208	6512	6395
40°	7089	6317	6190
45°	6911	6133	6008
50°	6761	5924	5816
55°	6605	5723	5595
60°	6364	5473	5387
65°	6097	5203	5138
70°	5774	4896	4849
75°	5323	4553	4573
80°	4816	4204	4286
85°	4141	3854	4052

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6911 cd/sqm

TEST NUMBER: P1001832

CATALOG NUMBER: SA4XXDIP-B795D365UB2750-4F0-XX-W2A-D_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.9	1.9
10°-20°	260.4	5.5
20°-30°	393.7	8.3
30°-40°	476.3	10.0
40°-50°	503.5	10.6
50°-60°	473.9	10.0
60°-70°	393.2	8.3
70°-80°	276.0	5.8
80°-90°	156.6	3.3
90°-100°	108.5	2.3
100°-110°	172.9	3.6
110°-120°	245.3	5.2
120°-130°	278.9	5.9
130°-140°	281.8	5.9
140°-150°	255.3	5.4
150°-160°	204.1	4.3
160°-170°	131.6	2.8
170°-180°	45.4	1.0
0°-30°	744.9	15.7
0°-40°	1221.2	25.7
0°-60°	2198.6	46.3
0°-90°	3024.4	63.7
90°-120°	526.7	11.1
90°-150°	1342.6	28.3
90°-180°	1724.0	36.3
0°-180°	4748.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	959	959	959	959	959	
5°	960	957	949	958	957	91
15°	920	922	918	928	927	259
25°	842	848	852	864	865	388
35°	737	750	760	776	779	461
45°	614	635	655	673	679	475
55°	481	504	536	557	564	429
65°	333	367	404	431	439	330
75°	185	224	270	300	309	196
85°	57	102	150	183	193	59
90°	18	65	114	148	157	13
95°	34	57	101	132	142	35
105°	117	141	182	212	208	123
115°	207	218	252	276	284	204
125°	286	287	313	334	341	256
135°	352	352	361	379	386	272
145°	404	404	404	411	416	253
155°	442	443	442	443	442	204
165°	467	465	465	468	464	132
175°	477	475	476	479	474	45
180°	477	477	477	477	477	

TEST NUMBER: P1001832

CATALOG NUMBER: SA4XXDIP-B795D365UB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	959.1	959.1	959.1	959.1	959.1
2.5°	963.4	960.2	951.6	959.1	958.0
5°	960.2	957.0	949.4	958.0	957.0
7.5°	953.7	951.6	945.1	954.8	953.7
10°	945.1	944.1	938.7	948.4	947.3
12.5°	933.3	933.3	930.1	938.7	938.7
15°	920.4	921.5	918.3	928.0	926.9
17.5°	903.3	906.5	905.4	915.1	914.0
20°	885.0	888.2	889.3	900.0	900.0
22.5°	864.6	868.9	871.0	881.8	883.9
25°	842.0	848.5	851.7	863.5	864.6
27.5°	817.3	827.0	831.3	842.0	843.1
30°	792.6	801.2	808.7	820.6	822.7
32.5°	765.8	776.5	785.1	799.1	801.2
35°	736.8	749.7	760.4	775.5	778.7
37.5°	707.8	722.8	735.7	750.7	754.0
40°	679.9	693.8	708.9	725.0	729.3
42.5°	647.6	663.8	682.0	700.3	703.5
45°	614.3	634.8	655.2	673.4	678.8
47.5°	583.2	603.6	627.2	645.5	651.9
50°	548.8	572.5	596.1	617.6	624.0
52.5°	514.5	538.1	566.0	587.5	593.9
55°	481.2	503.7	535.9	557.4	563.9
57.5°	443.6	471.5	502.6	528.4	533.8
60°	407.1	435.0	470.4	495.1	503.7
62.5°	371.6	402.8	438.2	462.9	471.5
65°	332.9	367.3	403.8	430.7	439.3
67.5°	296.4	332.9	371.6	398.5	407.1
70°	258.8	295.4	336.2	365.2	372.7
72.5°	222.3	259.9	304.0	331.9	340.5
75°	184.7	224.5	269.6	299.7	309.3
77.5°	149.3	191.2	238.4	268.5	279.2
80°	117.1	160.0	207.3	239.5	248.1
82.5°	84.8	130.0	177.2	210.5	220.2
85°	56.9	102.0	150.4	182.6	193.3
87.5°	35.4	79.5	126.7	157.9	167.5
90°	18.3	65.1	114.2	147.5	156.8
92.5°	21.5	58.3	107.4	139.6	148.2
95°	33.6	56.9	101.3	132.4	142.5
97.5°	50.4	89.3	96.0	125.6	135.7
100°	70.4	104.7	97.3	120.2	128.1
102.5°	93.9	121.8	167.0	114.6	123.2
105°	117.2	140.7	182.3	212.3	208.0
107.5°	140.4	159.6	199.7	228.4	237.3
110°	162.8	178.9	218.6	244.1	253.7



TEST NUMBER: P1001832

CATALOG NUMBER: SA4XXDIP-B795D365UB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	184.6	199.6	235.7	259.1	269.1
115°	207.0	217.8	251.9	276.2	283.7
117.5°	228.1	236.0	269.3	291.5	300.1
120°	248.5	253.2	283.9	306.1	314.0
122.5°	268.5	269.2	298.9	320.7	327.6
125°	286.3	286.7	312.9	334.3	341.1
127.5°	304.5	303.8	327.1	346.0	353.3
130°	320.9	320.2	338.5	358.2	364.6
132.5°	337.0	336.6	350.9	369.6	375.6
135°	352.0	351.6	360.6	378.6	385.7
137.5°	366.3	365.3	371.3	388.2	393.2
140°	380.2	379.9	381.6	396.7	402.4
142.5°	391.7	393.1	392.4	404.9	409.2
145°	404.5	404.5	404.5	411.3	416.3
147.5°	414.5	415.6	415.2	416.7	421.3
150°	425.6	425.9	425.6	425.6	425.9
152.5°	433.8	434.8	434.1	434.8	434.5
155°	442.3	442.7	441.6	443.1	442.0
157.5°	449.8	449.8	448.4	450.2	448.4
160°	456.3	455.2	454.8	457.0	454.8
162.5°	462.0	460.5	460.2	462.3	459.8
165°	466.6	464.8	464.8	467.7	464.5
167.5°	470.5	468.8	468.4	471.6	468.0
170°	473.8	471.6	472.0	474.8	471.3
172.5°	475.9	473.8	474.1	477.0	473.0
175°	477.3	475.2	475.5	478.8	474.5
177.5°	478.4	475.9	476.6	479.5	475.2
180°	477.3	477.3	477.3	477.3	477.3

(END OF REPORT)