

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000251

Luminaire Tested: SA2XXRDIP-B865D925UB40-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000251
REPORT IS A COMBINATION OF REPORTS P988811 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B865D925UB40-4F0-XX-W2A-F1
Description: Define 2 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6239.0 lumens
Efficiency: N/A
Efficacy: 82.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 75.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000251

CATALOG NUMBER: SA2XXRDIP-B865D925UB40-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1000251

CATALOG NUMBER: SA2XXRDIP-B865D925UB40-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54	48	48	48
1	98	94	90	87	90	86	83	80	73	70	68	60	59	57	49	48	47	41	41	41
2	89	82	76	71	82	76	71	67	64	61	57	53	51	48	43	42	40	35	35	35
3	82	73	66	60	75	67	61	56	57	52	49	48	44	41	39	36	35	30	30	30
4	75	65	57	51	69	60	53	48	51	46	42	43	39	36	35	32	30	26	26	26
5	69	58	50	44	63	54	47	42	46	41	36	39	35	31	32	29	27	23	23	23
6	64	52	44	39	59	48	41	36	41	36	32	35	31	28	29	26	24	21	21	21
7	59	47	39	34	54	44	37	32	38	32	28	32	28	25	27	23	21	19	19	19
8	55	43	35	30	51	40	33	29	34	29	25	29	25	22	24	21	19	17	17	17
9	51	39	32	27	47	37	30	26	32	26	23	27	23	20	23	20	17	15	15	15
10	48	36	29	24	44	34	27	23	29	24	21	25	21	18	21	18	16	14	14	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	22945	22945	22945
5°	22982	21828	21666
10°	22755	20703	20020
15°	22442	19374	18143
20°	22028	17863	16179
25°	21605	16312	14383
30°	21034	14804	12420
35°	20477	13280	10736
40°	19911	11786	9001
45°	19252	10242	7487
50°	18569	8753	6096
55°	17861	7265	4840
60°	17035	5811	3662
65°	16086	4429	2976
70°	14941	3214	2367
75°	13504	2450	1807
80°	11417	1660	1213
85°	7967	759	586

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 19252 cd/sqm

TEST NUMBER: P1000251

CATALOG NUMBER: SA2XXRDIP-B865D925UB40-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	135.8	2.2
10°-20°	372.9	6.0
20°-30°	523.6	8.4
30°-40°	570.7	9.1
40°-50°	524.5	8.4
50°-60°	412.0	6.6
60°-70°	268.1	4.3
70°-80°	138.0	2.2
80°-90°	38.6	0.6
90°-100°	72.0	1.2
100°-110°	228.9	3.7
110°-120°	391.7	6.3
120°-130°	515.2	8.3
130°-140°	578.3	9.3
140°-150°	567.1	9.1
150°-160°	475.7	7.6
160°-170°	315.5	5.1
170°-180°	110.3	1.8
0°-30°	1032.3	16.5
0°-40°	1603.1	25.7
0°-60°	2539.6	40.7
0°-90°	2984.3	47.8
90°-120°	692.7	11.1
90°-150°	2353.2	37.7
90°-180°	3255.0	52.2
0°-180°	6239.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1450	1450	1450	1450	1450	
5°	1450	1443	1426	1438	1434	137
15°	1379	1364	1320	1295	1282	388
25°	1251	1209	1123	1069	1049	576
35°	1078	1011	896	813	784	675
45°	882	794	656	563	531	681
55°	670	568	426	348	323	599
65°	452	346	228	184	180	449
75°	241	150	105	96	94	255
85°	56	29	25	25	25	65
90°	1	13	34	32	33	6
95°	51	61	63	63	61	57
105°	211	214	216	218	218	223
115°	393	399	397	396	393	389
125°	572	581	578	575	574	511
135°	740	750	752	752	749	572
145°	898	905	911	912	908	561
155°	1027	1030	1032	1037	1034	473
165°	1117	1116	1116	1123	1118	315
175°	1162	1159	1157	1164	1158	110
180°	1164	1164	1164	1164	1164	

TEST NUMBER: P1000251

CATALOG NUMBER: SA2XXRDIP-B865D925UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1449.5	1449.5	1449.5	1449.5	1449.5
2.5°	1456.0	1449.5	1435.0	1448.1	1445.5
5°	1449.5	1442.9	1425.8	1437.7	1433.7
7.5°	1437.7	1429.8	1411.4	1416.7	1410.1
10°	1421.9	1412.7	1386.5	1382.6	1374.7
12.5°	1402.2	1390.4	1355.0	1347.1	1332.7
15°	1378.6	1364.2	1319.6	1294.7	1281.6
17.5°	1351.1	1330.1	1275.0	1246.1	1225.2
20°	1319.6	1293.4	1227.8	1195.0	1166.1
22.5°	1285.5	1255.3	1179.2	1134.6	1115.0
25°	1251.4	1209.4	1122.8	1069.1	1049.4
27.5°	1210.7	1166.1	1070.4	1008.7	978.5
30°	1167.4	1117.6	1012.7	945.8	910.3
32.5°	1125.5	1065.1	957.6	878.9	846.1
35°	1078.2	1011.3	895.9	813.3	784.4
37.5°	1032.3	960.2	838.2	747.7	714.9
40°	983.8	905.1	777.9	684.7	650.6
42.5°	934.0	850.0	717.5	620.4	587.7
45°	881.5	793.6	655.9	562.7	531.2
47.5°	831.6	738.5	596.8	503.7	474.8
50°	776.5	683.4	539.1	448.6	421.1
52.5°	722.8	624.4	484.0	397.5	372.5
55°	670.3	568.0	426.3	347.6	322.7
57.5°	616.5	511.6	375.2	301.7	280.7
60°	561.4	456.5	321.4	254.5	233.5
62.5°	507.6	402.7	275.5	212.5	202.0
65°	452.5	346.3	228.2	183.6	179.7
67.5°	400.1	293.8	183.6	161.3	157.4
70°	345.0	242.7	152.2	139.0	133.8
72.5°	292.5	195.4	127.2	116.7	114.1
75°	241.4	149.5	104.9	95.8	94.4
77.5°	190.2	106.2	82.6	77.4	74.8
80°	143.0	76.1	63.0	57.7	57.7
82.5°	99.7	51.2	43.3	40.7	40.7
85°	56.4	28.9	24.9	24.9	24.9
87.5°	21.0	10.5	10.5	9.2	9.2
90°	1.0	12.8	34.4	32.4	33.4
92.5°	21.6	29.5	30.5	31.4	31.4
95°	51.1	60.9	62.9	62.9	60.9
97.5°	85.5	94.3	98.2	98.2	98.2
100°	124.8	132.6	135.6	135.6	134.6
102.5°	166.0	171.9	175.8	176.8	175.8
105°	211.2	214.2	216.1	218.1	218.1
107.5°	256.4	260.3	260.3	261.3	256.4
110°	299.6	305.5	305.5	305.5	302.6

TEST NUMBER: P1000251

CATALOG NUMBER: SA2XXRDIP-B865D925UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	346.8	352.7	351.7	348.7	346.8
115°	393.0	398.8	396.9	395.9	393.0
117.5°	439.1	447.0	442.1	439.1	436.2
120°	485.3	493.2	485.3	485.3	482.4
122.5°	527.5	537.4	532.5	529.5	527.5
125°	571.7	580.6	577.6	574.7	573.7
127.5°	615.0	625.8	621.9	617.9	615.0
130°	655.3	668.0	666.1	664.1	660.2
132.5°	700.4	710.3	711.2	706.3	703.4
135°	739.7	750.5	752.5	751.5	748.6
137.5°	783.0	791.8	793.8	792.8	788.9
140°	821.3	830.1	835.0	835.0	831.1
142.5°	860.6	869.4	872.4	873.3	869.4
145°	897.9	904.8	910.7	911.7	907.7
147.5°	931.3	940.1	944.1	946.0	942.1
150°	965.7	971.6	975.5	978.5	975.5
152.5°	996.1	1002.0	1006.9	1010.9	1006.9
155°	1026.6	1029.5	1032.5	1037.4	1034.5
157.5°	1053.1	1055.1	1057.0	1063.9	1059.0
160°	1076.7	1078.7	1079.6	1085.5	1081.6
162.5°	1098.3	1098.3	1099.3	1106.2	1101.3
165°	1117.0	1116.0	1116.0	1122.9	1118.0
167.5°	1133.7	1130.7	1130.7	1137.6	1132.7
170°	1146.4	1143.5	1142.5	1149.4	1143.5
172.5°	1155.3	1152.3	1151.4	1158.2	1152.3
175°	1162.2	1159.2	1157.3	1164.1	1158.2
177.5°	1166.1	1163.1	1161.2	1167.1	1161.2
180°	1164.1	1164.1	1164.1	1164.1	1164.1

(END OF REPORT)