

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P997539

Luminaire Tested: SA2XXDP-B1005DB2750-4F0-XX-W2A-A_3500K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P997539
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-19)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDP-B1005DB2750-4F0-XX-W2A-A_3500K
Description: Define 2 Direct Recessed with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4428.0 lumens
Efficiency: N/A
Efficacy: 72.2 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 61.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P997539

CATALOG NUMBER: SA2XXDP-B1005DB2750-4F0-XX-W2A-A_3500K

Luminous Intensity Polar Plot





TEST NUMBER: P997539

CATALOG NUMBER: SA2XXDP-B1005DB2750-4F0-XX-W2A-A_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10		0			
RCR																										
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102		100			
1	110	106	102	98		107	103	100	97		99	96	94		95	93	91		92	90	88		86			
2	101	94	87	82		98	92	86	81		88	83	79		85	81	78		82	79	76		74			
3	93	83	76	70		90	82	75	69		79	73	68		76	71	67		74	69	66		64			
4	86	75	66	60		83	73	66	60		71	64	59		69	63	58		66	62	58		55			
5	79	67	59	53		77	66	58	52		64	57	52		62	56	51		60	55	51		49			
6	74	61	53	47		72	60	52	46		58	51	46		57	51	46		55	50	45		43			
7	69	56	48	42		67	55	47	42		54	46	41		52	46	41		51	45	41		39			
8	64	51	43	38		63	51	43	38		49	42	37		48	42	37		47	41	37		35			
9	60	47	39	34		59	47	39	34		46	39	34		45	38	34		44	38	34		32			
10	56	44	36	31		55	43	36	31		42	36	31		41	35	31		41	35	31		29			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	31769	31769	31769	31769
5°	31915	35617	32037	28336
10°	31615	40814	31813	24523
15°	30917	45151	31348	21665
20°	30508	44463	30508	19749
25°	29611	40091	29746	18536
30°	28084	33131	28620	17651
35°	26739	24145	27187	17021
40°	25183	19285	25470	16671
45°	23241	16852	23622	16196
50°	21577	15842	21617	15879
55°	19669	14602	19796	15455
60°	17631	13382	17874	14797
65°	15832	12192	16121	14154
70°	14065	11066	14421	13209
75°	12079	9810	12550	11700
80°	9845	8441	10547	9426
85°	7283	7574	7846	5612

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 155°

Vertical Angle: 45°

Luminance: 41475 cd/sqm

TEST NUMBER: P997539

CATALOG NUMBER: SA2XXDP-B1005DB2750-4F0-XX-W2A-A_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	191.2	4.3
10°-20°	556.4	12.6
20°-30°	807.5	18.2
30°-40°	851.2	19.2
40°-50°	753.3	17.0
50°-60°	601.5	13.6
60°-70°	408.5	9.2
70°-80°	209.0	4.7
80°-90°	49.4	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1555.0	35.1
0°-40°	2406.3	54.3
0°-60°	3761.0	84.9
0°-90°	4428.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4428.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2007	2007	2007	2007	2007	
5°	2008	2242	2016	1783	2008	190
15°	1887	2755	1913	1322	1887	533
25°	1695	2295	1703	1061	1695	775
35°	1384	1250	1407	881	1384	866
45°	1038	753	1055	724	1038	805
55°	713	529	717	560	713	636
65°	423	326	430	378	423	420
75°	198	160	205	191	198	212
85°	40	42	43	31	40	49
90°	0	0	0	0	0	

TEST NUMBER: P997539

CATALOG NUMBER: SA2XXDP-B1005DB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0
2.5°	2017.8	2022.4	2030.1	2031.7	2047.1	2059.4	2073.3	2073.3	2077.9	2076.4	2064.1
5°	2008.5	2022.4	2042.5	2059.4	2087.2	2099.5	2118.0	2131.9	2144.3	2153.5	2152.0
7.5°	1993.1	2017.8	2047.1	2079.5	2116.5	2138.1	2164.3	2189.0	2206.0	2221.4	2232.2
10°	1966.9	2008.5	2048.6	2091.8	2139.6	2169.0	2199.8	2232.2	2258.4	2287.7	2315.5
12.5°	1931.4	1991.5	2040.9	2098.0	2156.6	2189.0	2238.4	2263.1	2314.0	2388.0	2408.1
15°	1886.6	1968.4	2014.7	2087.2	2164.3	2190.6	2258.4	2298.5	2403.4	2449.7	2505.2
17.5°	1845.0	1936.0	1997.7	2081.0	2156.6	2207.5	2273.9	2355.6	2443.5	2509.9	2571.6
20°	1811.1	1899.0	1973.0	2065.6	2161.2	2226.0	2295.4	2394.2	2489.8	2557.7	2605.5
22.5°	1733.9	1846.5	1932.9	2036.3	2152.0	2241.5	2307.8	2415.8	2519.1	2560.8	2602.4
25°	1695.4	1792.5	1892.8	2010.1	2145.8	2252.3	2309.3	2429.7	2520.7	2536.1	2545.4
27.5°	1624.4	1733.9	1851.2	1985.4	2144.3	2233.7	2306.2	2415.8	2488.3	2477.5	2449.7
30°	1536.5	1670.7	1800.3	1945.3	2122.7	2219.9	2287.7	2388.0	2425.0	2369.5	2320.1
32.5°	1471.7	1598.2	1741.6	1909.8	2098.0	2190.6	2256.9	2335.6	2343.3	2243.0	2159.7
35°	1383.7	1524.1	1686.1	1863.5	2056.3	2139.6	2201.3	2249.2	2212.1	2071.8	1973.0
37.5°	1305.1	1443.9	1616.7	1797.2	1999.3	2081.0	2130.4	2138.1	2047.1	1923.7	1778.7
40°	1218.7	1362.2	1542.6	1732.4	1936.0	2007.0	2037.8	2014.7	1883.6	1740.1	1572.0
42.5°	1132.3	1274.2	1468.6	1663.0	1855.8	1916.0	1928.3	1865.1	1704.6	1536.5	1342.1
45°	1038.2	1186.3	1380.7	1576.6	1763.2	1797.2	1798.7	1707.7	1518.0	1342.1	1161.6
47.5°	961.1	1098.4	1291.2	1487.1	1644.5	1667.6	1658.3	1553.4	1346.7	1149.3	991.9
50°	876.2	1007.3	1198.6	1391.5	1525.7	1531.8	1508.7	1359.1	1157.0	976.5	851.5
52.5°	785.2	917.9	1093.7	1278.8	1399.2	1389.9	1345.2	1184.7	995.0	845.4	749.7
55°	712.7	829.9	995.0	1175.5	1260.3	1234.1	1184.7	1021.2	871.6	745.1	661.8
57.5°	632.5	735.8	897.8	1055.2	1104.5	1079.8	1030.5	877.8	738.9	643.3	587.7
60°	556.9	651.0	792.9	924.0	962.6	936.4	879.3	742.0	641.7	561.5	519.9
62.5°	487.5	569.2	688.0	808.3	823.8	797.5	748.2	637.1	550.7	487.5	456.6
65°	422.7	499.8	595.5	686.5	700.4	672.6	621.7	541.5	469.0	428.9	399.5
67.5°	359.4	421.1	506.0	572.3	580.0	553.8	512.2	447.4	402.6	359.4	337.8
70°	303.9	350.2	416.5	470.5	473.6	448.9	427.3	368.7	334.8	303.9	286.9
72.5°	249.9	282.3	333.2	373.3	374.9	359.4	339.4	302.4	273.0	251.5	234.5
75°	197.5	225.2	256.1	291.6	290.0	277.7	262.2	239.1	214.4	200.5	192.8
77.5°	151.2	168.1	192.8	216.0	216.0	209.8	200.5	183.6	168.1	154.3	146.6
80°	108.0	118.8	138.8	146.6	149.6	148.1	140.4	128.0	121.9	111.1	108.0
82.5°	69.4	77.1	86.4	94.1	98.7	95.6	94.1	87.9	78.7	75.6	72.5
85°	40.1	43.2	47.8	52.4	54.0	52.4	55.5	50.9	46.3	46.3	44.7
87.5°	17.0	18.5	21.6	21.6	23.1	23.1	21.6	23.1	23.1	21.6	20.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P997539

CATALOG NUMBER: SA2XXDP-B1005DB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0
2.5°	2085.7	2087.2	2090.3	2105.7	2113.4	2115.0	2108.8	2122.7	2127.3	2122.7	2119.6
5°	2184.4	2193.6	2212.1	2232.2	2230.7	2232.2	2241.5	2250.7	2253.8	2241.5	2246.1
7.5°	2270.8	2289.3	2309.3	2340.2	2340.2	2355.6	2361.8	2369.5	2388.0	2378.8	2375.7
10°	2369.5	2394.2	2431.2	2480.6	2482.1	2497.5	2513.0	2537.6	2545.4	2539.2	2542.3
12.5°	2492.9	2540.7	2543.8	2597.8	2622.5	2625.6	2650.3	2645.6	2661.1	2661.1	2687.3
15°	2546.9	2620.9	2662.6	2715.0	2730.5	2712.0	2732.0	2753.6	2755.2	2755.2	2753.6
17.5°	2644.1	2673.4	2715.0	2742.8	2749.0	2749.0	2750.5	2759.8	2753.6	2741.3	2750.5
20°	2664.1	2676.5	2691.9	2688.8	2691.9	2676.5	2661.1	2645.6	2647.2	2639.5	2662.6
22.5°	2627.1	2624.0	2588.6	2565.4	2565.4	2534.6	2505.2	2491.4	2477.5	2482.1	2489.8
25°	2534.6	2486.7	2443.5	2409.6	2401.9	2352.5	2312.4	2300.1	2276.9	2295.4	2298.5
27.5°	2386.5	2332.5	2263.1	2233.7	2193.6	2173.6	2145.8	2108.8	2061.0	2088.7	2084.1
30°	2227.6	2147.4	2090.3	2019.3	1956.1	1951.4	1899.0	1837.3	1812.6	1812.6	1826.5
32.5°	2050.2	1943.7	1860.4	1760.2	1698.4	1672.2	1609.0	1547.3	1561.2	1514.9	1531.8
35°	1843.5	1703.1	1598.2	1501.0	1454.7	1423.9	1342.1	1308.2	1271.1	1249.5	1289.6
37.5°	1646.0	1484.0	1349.8	1243.4	1226.4	1170.9	1115.3	1093.7	1072.1	1081.4	1079.8
40°	1405.3	1261.9	1141.6	1058.3	1028.9	1002.7	965.7	939.5	925.6	933.3	934.8
42.5°	1187.8	1067.5	978.0	919.4	894.7	876.2	857.7	836.1	831.5	831.5	837.7
45°	1019.7	921.0	860.8	813.0	799.1	785.2	771.3	762.1	759.0	752.8	757.4
47.5°	885.5	806.8	769.8	734.3	718.9	715.8	703.4	698.8	692.6	691.1	692.6
50°	772.9	723.5	689.6	669.5	658.7	654.1	647.9	638.7	635.6	643.3	640.2
52.5°	694.2	647.9	629.4	609.3	603.2	597.0	587.7	589.3	587.7	584.7	584.7
55°	615.5	586.2	567.7	552.3	550.7	544.6	536.8	533.8	532.2	529.1	533.8
57.5°	552.3	529.1	512.2	498.3	492.1	492.1	484.4	478.2	478.2	476.7	478.2
60°	489.0	465.9	455.1	441.2	436.6	435.0	430.4	427.3	422.7	422.7	422.7
62.5°	430.4	411.9	399.5	387.2	388.7	381.0	374.9	371.8	371.8	373.3	373.3
65°	374.9	362.5	347.1	336.3	333.2	331.7	328.6	327.0	322.4	325.5	325.5
67.5°	324.0	307.0	297.7	293.1	288.5	286.9	283.8	280.8	279.2	277.7	280.8
70°	273.0	259.2	251.5	248.4	243.7	242.2	240.7	236.0	237.6	239.1	240.7
72.5°	226.8	214.4	212.9	203.6	203.6	203.6	197.5	200.5	199.0	195.9	199.0
75°	178.9	172.8	169.7	165.1	166.6	165.1	163.5	158.9	158.9	160.4	162.0
77.5°	141.9	135.8	134.2	129.6	126.5	129.6	126.5	125.0	125.0	126.5	126.5
80°	104.9	101.8	97.2	97.2	97.2	95.6	95.6	95.6	94.1	92.6	94.1
82.5°	69.4	69.4	67.9	66.3	67.9	64.8	66.3	66.3	66.3	66.3	66.3
85°	44.7	43.2	43.2	41.7	41.7	41.7	43.2	40.1	40.1	41.7	41.7
87.5°	20.1	20.1	20.1	21.6	20.1	20.1	20.1	21.6	20.1	20.1	20.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P997539

CATALOG NUMBER: SA2XXDP-B1005DB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0
2.5°	2127.3	2116.5	2107.2	2108.8	2116.5	2110.3	2094.9	2074.9	2067.1	2057.9	2067.1
5°	2255.3	2246.1	2227.6	2229.1	2224.5	2218.3	2193.6	2162.8	2162.8	2138.1	2135.0
7.5°	2381.8	2368.0	2355.6	2352.5	2335.6	2323.2	2301.6	2258.4	2241.5	2212.1	2195.2
10°	2523.8	2513.0	2499.1	2482.1	2472.9	2451.3	2415.8	2352.5	2321.7	2281.6	2252.3
12.5°	2667.2	2665.7	2634.8	2600.9	2599.3	2565.4	2540.7	2455.9	2414.2	2360.2	2290.8
15°	2758.2	2750.5	2733.6	2716.6	2721.2	2684.2	2628.7	2528.4	2500.6	2435.8	2361.8
17.5°	2756.7	2756.7	2752.1	2749.0	2744.4	2733.6	2702.7	2636.4	2591.6	2509.9	2440.5
20°	2668.8	2688.8	2693.5	2691.9	2707.3	2715.0	2713.5	2671.9	2636.4	2563.9	2492.9
22.5°	2492.9	2539.2	2559.2	2571.6	2604.0	2620.9	2661.1	2645.6	2636.4	2582.4	2522.2
25°	2329.4	2344.8	2405.0	2408.1	2452.8	2494.5	2534.6	2560.8	2594.7	2574.7	2523.8
27.5°	2118.0	2153.5	2196.7	2229.1	2238.4	2323.2	2389.6	2438.9	2516.0	2522.2	2505.2
30°	1878.9	1895.9	1966.9	2010.1	2059.4	2121.1	2216.8	2301.6	2371.0	2434.3	2455.9
32.5°	1587.4	1656.8	1698.4	1750.9	1794.1	1903.6	2020.9	2130.4	2210.6	2317.0	2363.3
35°	1320.5	1374.5	1445.5	1467.1	1545.7	1638.3	1791.0	1931.4	2053.3	2161.2	2255.3
37.5°	1099.9	1143.1	1218.7	1252.6	1298.9	1417.7	1545.7	1720.0	1866.6	1999.3	2116.5
40°	948.7	981.1	1038.2	1049.0	1087.6	1195.5	1298.9	1462.4	1656.8	1835.7	1963.8
42.5°	845.4	860.8	899.4	913.2	937.9	1010.4	1103.0	1257.3	1437.7	1622.9	1803.3
45°	771.3	782.1	805.3	817.6	848.5	880.8	956.4	1079.8	1221.8	1408.4	1602.8
47.5°	705.0	718.9	728.1	735.8	752.8	788.3	837.7	928.7	1064.4	1235.7	1423.9
50°	649.5	654.1	671.0	672.6	683.4	706.5	752.8	808.3	916.3	1055.2	1237.2
52.5°	593.9	598.5	609.3	620.1	624.8	643.3	674.1	720.4	800.6	910.2	1072.1
55°	538.4	544.6	555.4	563.1	567.7	583.1	601.6	646.4	709.6	786.7	919.4
57.5°	482.8	496.7	499.8	504.4	512.2	529.1	546.1	572.3	621.7	692.6	789.8
60°	430.4	435.0	445.8	450.5	458.2	467.4	489.0	509.1	544.6	600.1	688.0
62.5°	376.4	387.2	391.8	396.5	402.6	413.4	427.3	448.9	479.8	524.5	593.9
65°	330.1	331.7	340.9	347.1	353.3	361.0	374.9	394.9	413.4	455.1	506.0
67.5°	285.4	288.5	291.6	297.7	305.4	313.2	325.5	336.3	359.4	387.2	427.3
70°	242.2	242.2	249.9	254.5	253.0	262.2	271.5	283.8	300.8	327.0	359.4
72.5°	203.6	202.1	208.3	209.8	212.9	219.1	225.2	237.6	246.8	266.9	291.6
75°	162.0	165.1	168.1	168.1	172.8	177.4	183.6	189.7	200.5	212.9	231.4
77.5°	128.0	128.0	131.1	132.7	137.3	135.8	141.9	148.1	155.8	166.6	180.5
80°	94.1	97.2	97.2	97.2	98.7	100.3	106.4	111.1	115.7	123.4	129.6
82.5°	66.3	66.3	69.4	69.4	69.4	72.5	72.5	74.0	77.1	81.8	86.4
85°	41.7	41.7	41.7	43.2	41.7	43.2	46.3	44.7	46.3	49.4	49.4
87.5°	20.1	20.1	20.1	20.1	20.1	21.6	20.1	21.6	23.1	23.1	23.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P997539

CATALOG NUMBER: SA2XXDP-B1005DB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0
2.5°	2059.4	2051.7	2047.1	2050.2	2040.9	2017.8	2017.8	2025.5	2016.2	2007.0	1993.1
5°	2116.5	2101.1	2091.8	2090.3	2068.7	2031.7	2023.9	2016.2	1996.2	1974.6	1951.4
7.5°	2172.0	2144.3	2128.8	2118.0	2087.2	2039.4	2019.3	2002.3	1970.0	1937.6	1908.2
10°	2218.3	2178.2	2159.7	2142.7	2102.6	2042.5	2010.1	1979.2	1937.6	1895.9	1858.9
12.5°	2255.3	2209.1	2185.9	2161.2	2111.9	2033.2	1993.1	1943.7	1902.1	1846.5	1809.5
15°	2317.0	2221.4	2199.8	2176.7	2125.8	2017.8	1968.4	1912.9	1855.8	1781.8	1741.6
17.5°	2366.4	2238.4	2236.8	2187.5	2121.1	2011.6	1936.0	1863.5	1801.8	1727.8	1664.5
20°	2395.7	2264.6	2239.9	2189.0	2105.7	1970.0	1891.3	1811.1	1744.7	1655.3	1592.0
22.5°	2420.4	2301.6	2236.8	2175.1	2073.3	1956.1	1840.4	1764.8	1673.8	1576.6	1516.4
25°	2429.7	2309.3	2241.5	2170.5	2050.2	1916.0	1784.8	1703.1	1601.3	1513.3	1431.6
27.5°	2431.2	2307.8	2224.5	2150.4	2017.8	1863.5	1729.3	1642.9	1530.3	1428.5	1346.7
30°	2415.8	2290.8	2215.2	2135.0	1986.9	1815.7	1661.4	1565.8	1445.5	1343.6	1258.8
32.5°	2369.5	2256.9	2195.2	2107.2	1946.8	1749.4	1596.6	1490.2	1363.7	1263.4	1181.7
35°	2292.4	2215.2	2147.4	2065.6	1894.4	1687.6	1531.8	1406.9	1278.8	1183.2	1106.1
37.5°	2196.7	2155.1	2091.8	2011.6	1834.2	1632.1	1459.3	1320.5	1192.5	1099.9	1024.3
40°	2067.1	2077.9	2016.2	1943.7	1763.2	1556.5	1365.2	1232.6	1112.2	1025.9	951.8
42.5°	1926.8	1971.5	1936.0	1866.6	1684.6	1473.2	1295.8	1149.3	1032.0	942.6	880.8
45°	1775.6	1852.7	1831.1	1780.2	1602.8	1385.3	1197.1	1055.2	951.8	865.4	811.4
47.5°	1610.5	1720.0	1720.0	1683.0	1511.8	1297.4	1112.2	967.2	865.4	803.7	751.3
50°	1442.4	1565.8	1585.8	1561.2	1410.0	1197.1	1008.9	877.8	789.8	729.7	691.1
52.5°	1266.5	1410.0	1447.0	1434.7	1302.0	1101.4	924.0	796.0	715.8	663.3	629.4
55°	1098.4	1265.0	1305.1	1309.7	1186.3	996.5	829.9	717.3	640.2	604.7	575.4
57.5°	939.5	1099.9	1144.6	1152.4	1069.1	900.9	742.0	643.3	573.9	544.6	521.4
60°	803.7	937.9	996.5	1013.5	941.0	789.8	660.3	564.6	512.2	484.4	462.8
62.5°	692.6	800.6	862.3	867.0	834.6	692.6	575.4	495.2	450.5	425.8	415.0
65°	584.7	681.8	718.9	737.4	711.2	600.1	496.7	430.4	394.9	373.3	362.5
67.5°	498.3	560.0	590.8	615.5	589.3	506.0	422.7	368.7	342.5	320.9	314.7
70°	408.8	459.7	482.8	507.5	484.4	421.1	361.0	311.6	288.5	271.5	263.8
72.5°	327.0	367.1	388.7	404.2	390.3	337.8	288.5	254.5	237.6	225.2	220.6
75°	259.2	286.9	299.3	310.1	303.9	263.8	232.9	205.2	189.7	178.9	175.9
77.5°	197.5	217.5	231.4	234.5	226.8	200.5	174.3	157.3	145.0	138.8	135.8
80°	140.4	152.7	160.4	165.1	157.3	146.6	128.0	115.7	104.9	97.2	95.6
82.5°	94.1	100.3	106.4	104.9	101.8	92.6	81.8	75.6	71.0	64.8	64.8
85°	54.0	55.5	58.6	60.2	58.6	52.4	46.3	43.2	40.1	35.5	35.5
87.5°	23.1	24.7	24.7	26.2	23.1	23.1	20.1	17.0	17.0	15.4	13.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P997539

CATALOG NUMBER: SA2XXDP-B1005DB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0
2.5°	1985.4	1993.1	1991.5	1976.1	1959.2	1945.3	1919.0	1922.1	1912.9	1914.4	1923.7
5°	1936.0	1936.0	1929.8	1908.2	1880.5	1865.1	1835.7	1828.0	1809.5	1808.0	1806.4
7.5°	1883.6	1875.9	1868.1	1837.3	1803.3	1778.7	1738.6	1729.3	1710.8	1698.4	1692.3
10°	1821.9	1811.1	1795.6	1760.2	1718.5	1687.6	1646.0	1633.7	1598.2	1582.7	1573.5
12.5°	1754.0	1747.8	1723.1	1693.8	1625.9	1592.0	1531.8	1544.2	1508.7	1477.9	1473.2
15°	1686.1	1663.0	1649.1	1601.3	1519.5	1504.1	1456.3	1431.6	1399.2	1374.5	1374.5
17.5°	1619.8	1584.3	1553.4	1502.5	1442.4	1399.2	1363.7	1351.4	1311.2	1286.6	1281.9
20°	1531.8	1491.7	1484.0	1411.5	1369.9	1322.0	1288.1	1257.3	1227.9	1217.1	1209.4
22.5°	1448.5	1402.3	1389.9	1328.2	1286.6	1238.7	1204.8	1183.2	1161.6	1153.9	1140.0
25°	1359.1	1331.3	1312.8	1246.5	1200.2	1155.4	1132.3	1116.9	1096.8	1095.3	1086.0
27.5°	1272.7	1246.5	1227.9	1164.7	1130.8	1089.1	1070.6	1053.6	1042.8	1038.2	1033.6
30°	1198.6	1169.3	1147.7	1101.4	1059.8	1025.9	1010.4	999.6	993.5	985.7	984.2
32.5°	1116.9	1099.9	1070.6	1035.1	1002.7	970.3	961.1	953.4	944.1	941.0	939.5
35°	1047.5	1024.3	1005.8	965.7	951.8	924.0	913.2	907.1	894.7	891.6	888.6
37.5°	979.6	958.0	937.9	913.2	887.0	871.6	865.4	856.2	850.0	851.5	848.5
40°	911.7	894.7	879.3	853.1	837.7	829.9	817.6	808.3	805.3	806.8	805.3
42.5°	845.4	829.9	820.7	800.6	785.2	777.5	769.8	760.5	765.1	765.1	769.8
45°	785.2	771.3	765.1	749.7	740.5	728.1	720.4	718.9	725.0	723.5	723.5
47.5°	723.5	718.9	711.2	697.3	684.9	677.2	675.7	675.7	681.8	684.9	683.4
50°	675.7	666.4	657.2	646.4	637.1	634.0	629.4	632.5	638.7	638.7	641.7
52.5°	615.5	609.3	606.3	597.0	590.8	590.8	590.8	592.4	597.0	601.6	600.1
55°	563.1	558.4	555.4	550.7	543.0	544.6	543.0	546.1	550.7	555.4	558.4
57.5°	507.5	506.0	502.9	495.2	495.2	493.6	498.3	499.8	507.5	510.6	515.2
60°	458.2	453.5	453.5	447.4	447.4	447.4	452.0	456.6	462.8	464.3	467.4
62.5°	405.7	405.7	404.2	399.5	399.5	404.2	405.7	411.9	415.0	415.0	419.6
65°	356.4	354.8	353.3	354.8	356.4	356.4	361.0	364.1	367.1	368.7	370.2
67.5°	307.0	305.4	308.5	307.0	310.1	316.2	314.7	319.3	324.0	324.0	325.5
70°	260.7	263.8	262.2	265.3	263.8	266.9	271.5	273.0	273.0	274.6	279.2
72.5°	217.5	217.5	217.5	216.0	217.5	220.6	223.7	225.2	228.3	229.9	234.5
75°	175.9	175.9	172.8	175.9	175.9	178.9	182.0	182.0	182.0	185.1	189.7
77.5°	132.7	134.2	132.7	135.8	135.8	137.3	140.4	138.8	141.9	143.5	145.0
80°	97.2	95.6	95.6	95.6	97.2	97.2	100.3	101.8	101.8	106.4	103.4
82.5°	61.7	63.2	61.7	63.2	63.2	64.8	63.2	64.8	66.3	69.4	67.9
85°	35.5	33.9	33.9	35.5	33.9	33.9	35.5	33.9	35.5	33.9	35.5
87.5°	13.9	12.3	12.3	12.3	12.3	10.8	10.8	9.3	9.3	9.3	7.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P997539

CATALOG NUMBER: SA2XXDP-B1005DB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0
2.5°	1912.9	1917.5	1906.7	1903.6	1906.7	1895.9	1899.0	1902.1	1902.1	1906.7	1909.8
5°	1801.8	1795.6	1784.8	1781.8	1778.7	1783.3	1780.2	1784.8	1786.4	1797.2	1798.7
7.5°	1692.3	1683.0	1673.8	1664.5	1661.4	1653.7	1661.4	1661.4	1672.2	1669.1	1676.9
10°	1562.7	1561.2	1548.8	1544.2	1538.0	1525.7	1542.6	1538.0	1545.7	1559.6	1562.7
12.5°	1467.1	1450.1	1457.8	1436.2	1443.9	1431.6	1433.1	1433.1	1445.5	1447.0	1443.9
15°	1376.0	1362.2	1342.1	1332.8	1328.2	1322.0	1342.1	1343.6	1334.4	1356.0	1348.3
17.5°	1283.5	1283.5	1265.0	1260.3	1248.0	1254.2	1251.1	1252.6	1249.5	1265.0	1272.7
20°	1203.3	1195.5	1189.4	1190.9	1175.5	1172.4	1169.3	1172.4	1183.2	1194.0	1197.1
22.5°	1138.5	1133.8	1118.4	1121.5	1109.2	1113.8	1110.7	1118.4	1120.0	1120.0	1130.8
25°	1076.8	1070.6	1072.1	1066.0	1061.3	1061.3	1056.7	1061.3	1067.5	1070.6	1072.1
27.5°	1030.5	1025.9	1018.1	1013.5	1016.6	1008.9	1015.1	1019.7	1019.7	1016.6	1019.7
30°	974.9	978.0	978.0	962.6	968.8	965.7	970.3	973.4	973.4	974.9	971.9
32.5°	937.9	928.7	927.1	925.6	925.6	919.4	919.4	924.0	925.6	927.1	931.8
35°	888.6	888.6	880.8	885.5	879.3	880.8	879.3	880.8	883.9	879.3	883.9
37.5°	843.8	845.4	842.3	845.4	846.9	843.8	840.7	846.9	843.8	843.8	840.7
40°	805.3	803.7	805.3	805.3	805.3	806.8	803.7	803.7	803.7	800.6	797.5
42.5°	772.9	763.6	766.7	768.2	763.6	763.6	765.1	763.6	768.2	759.0	759.0
45°	726.6	723.5	725.0	725.0	728.1	723.5	726.6	728.1	723.5	722.0	718.9
47.5°	684.9	688.0	684.9	688.0	688.0	691.1	684.9	686.5	688.0	681.8	677.2
50°	643.3	643.3	647.9	646.4	647.9	644.8	644.8	643.3	644.8	641.7	637.1
52.5°	604.7	600.1	607.8	606.3	604.7	603.2	601.6	603.2	600.1	597.0	597.0
55°	556.9	556.9	561.5	563.1	563.1	560.0	556.9	558.4	556.9	555.4	553.8
57.5°	518.3	512.2	515.2	516.8	516.8	512.2	515.2	512.2	512.2	513.7	509.1
60°	469.0	469.0	465.9	470.5	470.5	467.4	467.4	469.0	465.9	464.3	462.8
62.5°	416.5	418.1	422.7	424.2	425.8	422.7	419.6	421.1	421.1	416.5	418.1
65°	371.8	374.9	381.0	379.5	376.4	377.9	374.9	376.4	371.8	373.3	368.7
67.5°	328.6	327.0	328.6	328.6	331.7	330.1	327.0	327.0	325.5	330.1	325.5
70°	282.3	282.3	282.3	282.3	283.8	285.4	282.3	279.2	280.8	277.7	276.1
72.5°	234.5	236.0	234.5	237.6	232.9	236.0	236.0	234.5	232.9	232.9	232.9
75°	189.7	192.8	188.2	189.7	188.2	191.3	189.7	189.7	186.7	185.1	186.7
77.5°	145.0	146.6	143.5	145.0	143.5	145.0	145.0	143.5	143.5	143.5	143.5
80°	103.4	104.9	103.4	101.8	100.3	103.4	100.3	101.8	103.4	101.8	104.9
82.5°	66.3	66.3	64.8	66.3	63.2	63.2	64.8	64.8	63.2	66.3	63.2
85°	32.4	32.4	35.5	32.4	30.9	30.9	30.9	32.4	30.9	33.9	32.4
87.5°	7.7	6.2	7.7	7.7	6.2	6.2	7.7	6.2	7.7	9.3	6.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P997539

CATALOG NUMBER: SA2XXDP-B1005DB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0
2.5°	1905.2	1917.5	1912.9	1895.9	1916.0	1916.0	1929.8	1929.8	1946.8	1953.0	1962.2
5°	1797.2	1806.4	1814.1	1806.4	1820.3	1841.9	1854.3	1865.1	1888.2	1897.4	1911.3
7.5°	1681.5	1698.4	1706.2	1706.2	1729.3	1754.0	1778.7	1794.1	1826.5	1838.8	1852.7
10°	1568.9	1588.9	1604.3	1602.8	1641.4	1656.8	1687.6	1723.1	1755.5	1774.0	1794.1
12.5°	1450.1	1460.9	1482.5	1513.3	1522.6	1550.4	1585.8	1630.6	1689.2	1706.2	1735.5
15°	1351.4	1380.7	1397.6	1411.5	1433.1	1459.3	1497.9	1541.1	1599.7	1636.7	1667.6
17.5°	1268.1	1306.6	1317.4	1314.3	1342.1	1382.2	1426.9	1459.3	1511.8	1556.5	1585.8
20°	1200.2	1215.6	1234.1	1241.8	1263.4	1306.6	1349.8	1386.8	1430.0	1465.5	1499.4
22.5°	1132.3	1144.6	1160.1	1173.9	1190.9	1215.6	1257.3	1303.5	1345.2	1379.1	1417.7
25°	1076.8	1084.5	1098.4	1109.2	1127.7	1144.6	1173.9	1224.9	1274.2	1294.3	1328.2
27.5°	1022.8	1028.9	1038.2	1050.5	1059.8	1076.8	1103.0	1144.6	1195.5	1215.6	1261.9
30°	974.9	979.6	988.8	995.0	999.6	1019.7	1039.7	1072.1	1110.7	1138.5	1172.4
32.5°	930.2	934.8	944.1	945.6	951.8	962.6	981.1	1010.4	1044.4	1067.5	1096.8
35°	880.8	883.9	893.2	896.3	900.9	910.2	924.0	945.6	976.5	993.5	1019.7
37.5°	842.3	840.7	846.9	851.5	857.7	862.3	867.0	888.6	911.7	927.1	947.2
40°	800.6	797.5	799.1	805.3	808.3	814.5	814.5	836.1	851.5	863.9	879.3
42.5°	759.0	757.4	754.4	757.4	760.5	762.1	763.6	779.0	794.5	805.3	822.2
45°	717.3	715.8	712.7	714.2	714.2	717.3	722.0	728.1	738.9	748.2	757.4
47.5°	678.8	675.7	671.0	669.5	672.6	672.6	672.6	678.8	689.6	692.6	701.9
50°	638.7	634.0	627.9	624.8	624.8	623.2	626.3	627.9	637.1	640.2	647.9
52.5°	595.5	592.4	586.2	580.0	581.6	578.5	580.0	581.6	584.7	589.3	593.9
55°	552.3	546.1	541.5	539.9	535.3	535.3	530.7	536.8	535.3	536.8	543.0
57.5°	510.6	504.4	496.7	493.6	489.0	487.5	484.4	482.8	484.4	489.0	493.6
60°	461.2	458.2	453.5	448.9	445.8	441.2	438.1	438.1	436.6	436.6	438.1
62.5°	413.4	411.9	405.7	404.2	401.1	398.0	393.4	390.3	390.3	393.4	394.9
65°	367.1	365.6	361.0	359.4	351.7	348.6	347.1	345.6	342.5	342.5	342.5
67.5°	324.0	319.3	319.3	311.6	305.4	302.4	299.3	297.7	297.7	297.7	299.3
70°	276.1	276.1	271.5	266.9	260.7	262.2	257.6	253.0	253.0	249.9	251.5
72.5°	229.9	228.3	223.7	222.1	217.5	212.9	209.8	212.9	208.3	206.7	208.3
75°	185.1	183.6	180.5	177.4	178.9	174.3	169.7	168.1	168.1	165.1	165.1
77.5°	141.9	145.0	138.8	137.3	134.2	131.1	129.6	128.0	128.0	128.0	131.1
80°	98.7	100.3	100.3	97.2	98.7	94.1	94.1	94.1	89.5	91.0	92.6
82.5°	63.2	63.2	61.7	63.2	61.7	61.7	60.2	60.2	58.6	58.6	60.2
85°	35.5	33.9	32.4	35.5	33.9	33.9	32.4	32.4	32.4	32.4	32.4
87.5°	7.7	9.3	9.3	9.3	9.3	10.8	10.8	10.8	12.3	12.3	12.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P997539

CATALOG NUMBER: SA2XXDP-B1005DB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	2007.0	2007.0	2007.0	2007.0
2.5°	1970.0	1970.0	1993.1	2017.8
5°	1926.8	1937.6	1974.6	2008.5
7.5°	1885.1	1903.6	1949.9	1993.1
10°	1834.2	1858.9	1916.0	1966.9
12.5°	1784.8	1808.0	1874.3	1931.4
15°	1715.4	1744.7	1815.7	1886.6
17.5°	1646.0	1675.3	1761.7	1845.0
20°	1564.2	1602.8	1700.0	1811.1
22.5°	1488.6	1536.5	1644.5	1733.9
25°	1405.3	1479.4	1579.7	1695.4
27.5°	1331.3	1405.3	1507.2	1624.4
30°	1248.0	1323.6	1428.5	1536.5
32.5°	1167.8	1237.2	1339.0	1471.7
35°	1084.5	1150.8	1249.5	1383.7
37.5°	1008.9	1073.7	1181.7	1305.1
40°	934.8	1002.7	1095.3	1218.7
42.5°	865.4	925.6	1008.9	1132.3
45°	802.2	845.4	922.5	1038.2
47.5°	735.8	774.4	845.4	961.1
50°	674.1	706.5	768.2	876.2
52.5°	614.0	641.7	698.8	785.2
55°	560.0	586.2	627.9	712.7
57.5°	504.4	524.5	564.6	632.5
60°	450.5	469.0	501.4	556.9
62.5°	396.5	411.9	442.7	487.5
65°	348.6	361.0	384.1	422.7
67.5°	302.4	310.1	328.6	359.4
70°	257.6	263.8	279.2	303.9
72.5°	209.8	216.0	232.9	249.9
75°	169.7	171.2	183.6	197.5
77.5°	132.7	131.1	140.4	151.2
80°	91.0	95.6	103.4	108.0
82.5°	61.7	63.2	66.3	69.4
85°	33.9	35.5	35.5	40.1
87.5°	13.9	15.4	15.4	17.0
90°	0.0	0.0	0.0	0.0

TEST NUMBER: P997539

CATALOG NUMBER: SA2XXDP-B1005DB2750-4F0-XX-W2A-A_3500K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	23.99	25.50	24.35	25.82	26.13	20.25	21.77	20.62	22.08	22.40
	3H	25.10	26.46	25.48	26.79	27.15	21.67	23.03	22.05	23.36	23.72
	4H	25.43	26.70	25.83	27.05	27.43	22.17	23.45	22.57	23.80	24.18
	6H	25.62	26.80	26.03	27.16	27.55	22.53	23.71	22.94	24.08	24.47
	8H	25.66	26.78	26.08	27.17	27.57	22.64	23.77	23.07	24.16	24.56
	12H	25.67	26.74	26.10	27.13	27.56	22.72	23.79	23.15	24.18	24.60
4H	2H	24.11	25.38	24.51	25.73	26.11	21.05	22.33	21.45	22.68	23.06
	3H	25.44	26.50	25.85	26.90	27.30	22.63	23.69	23.04	24.09	24.49
	4H	25.91	26.87	26.34	27.28	27.72	23.23	24.18	23.66	24.60	25.04
	6H	26.24	27.07	26.70	27.51	27.97	23.68	24.51	24.14	24.95	25.41
	8H	26.32	27.09	26.78	27.54	28.00	23.82	24.60	24.29	25.04	25.51
	12H	26.36	27.05	26.84	27.53	28.00	23.93	24.62	24.41	25.10	25.57
8H	4H	26.00	26.77	26.46	27.21	27.68	23.64	24.41	24.10	24.86	25.32
	6H	26.40	27.04	26.90	27.53	28.01	24.18	24.82	24.68	25.31	25.79
	8H	26.53	27.10	27.05	27.61	28.10	24.38	24.95	24.89	25.46	25.95
	12H	26.62	27.13	27.13	27.62	28.18	24.54	25.05	25.05	25.54	26.10
12H	4H	25.99	26.68	26.47	27.16	27.63	23.69	24.38	24.17	24.86	25.33
	6H	26.40	26.97	26.91	27.48	27.97	24.25	24.83	24.77	25.34	25.83
	8H	26.56	27.07	27.07	27.56	28.13	24.50	25.01	25.01	25.50	26.07

END OF REPORT