

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P997541

Luminaire Tested: SA2XXDP-B1005DB2750-4F0-XX-W2A-A_5000K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P997541
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-19)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDP-B1005DB2750-4F0-XX-W2A-A_5000K
Description: Define 2 Direct Recessed with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4239.0 lumens
Efficiency: N/A
Efficacy: 69.2 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 61.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P997541

CATALOG NUMBER: SA2XXDP-B1005DB2750-4F0-XX-W2A-A_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P997541

CATALOG NUMBER: SA2XXDP-B1005DB2750-4F0-XX-W2A-A_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	110	106	102	98	107	103	100	97	99	96	94	95	93	91	92	90	88	86		
2	101	94	87	82	98	92	86	81	88	83	79	85	81	78	82	79	76	74		
3	93	83	76	70	90	82	75	69	79	73	68	76	71	67	74	69	66	64		
4	86	75	66	60	83	73	66	60	71	64	59	69	63	58	66	62	58	55		
5	79	67	59	53	77	66	58	52	64	57	52	62	56	51	60	55	51	49		
6	74	61	53	47	72	60	52	46	58	51	46	57	51	46	55	50	45	43		
7	69	56	48	42	67	55	47	42	54	46	41	52	46	41	51	45	41	39		
8	64	51	43	38	63	51	43	38	49	42	37	48	42	37	47	41	37	35		
9	60	47	39	34	59	47	39	34	46	39	34	45	38	34	44	38	34	32		
10	56	44	36	31	55	43	36	31	42	36	31	41	35	31	41	35	31	29		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	30413	30413	30413	30413
5°	30553	34096	30670	27127
10°	30265	39071	30454	23477
15°	29598	43224	30009	20740
20°	29206	42564	29206	18907
25°	28347	38381	28476	17745
30°	26885	31716	27397	16898
35°	25598	23115	26026	16296
40°	24108	18463	24383	15961
45°	22249	16134	22612	15505
50°	20656	15165	20693	15202
55°	18830	13978	18951	14795
60°	16877	12809	17111	14167
65°	15154	11671	15432	13551
70°	13463	10594	13806	12644
75°	11559	9394	12012	11198
80°	9426	8077	10100	9015
85°	6974	7247	7519	5358

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 155°

Vertical Angle: 45°

Luminance: 39704 cd/sqm

TEST NUMBER: P997541

CATALOG NUMBER: SA2XXDP-B1005DB2750-4F0-XX-W2A-A_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.0	4.3
10°-20°	532.6	12.6
20°-30°	773.0	18.2
30°-40°	814.9	19.2
40°-50°	721.1	17.0
50°-60°	575.8	13.6
60°-70°	391.1	9.2
70°-80°	200.1	4.7
80°-90°	47.3	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1488.7	35.1
0°-40°	2303.6	54.3
0°-60°	3600.5	84.9
0°-90°	4239.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4239.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1921	1921	1921	1921	1921	
5°	1923	2146	1930	1707	1923	182
15°	1806	2638	1831	1266	1806	510
25°	1623	2198	1630	1016	1623	742
35°	1325	1196	1347	843	1325	829
45°	994	721	1010	693	994	771
55°	682	506	687	536	682	609
65°	405	312	412	362	405	402
75°	189	154	196	183	189	203
85°	38	40	41	30	38	47
90°	0	0	0	0	0	

TEST NUMBER: P997541

CATALOG NUMBER: SA2XXDP-B1005DB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3
2.5°	1931.6	1936.1	1943.5	1944.9	1959.7	1971.5	1984.8	1984.8	1989.2	1987.8	1976.0
5°	1922.8	1936.1	1955.3	1971.5	1998.1	2009.9	2027.6	2040.9	2052.7	2061.6	2060.1
7.5°	1908.0	1931.6	1959.7	1990.7	2026.2	2046.8	2071.9	2095.6	2111.8	2126.6	2136.9
10°	1882.9	1922.8	1961.2	2002.5	2048.3	2076.4	2105.9	2136.9	2162.0	2190.1	2216.7
12.5°	1848.9	1906.5	1953.8	2008.4	2064.6	2095.6	2142.8	2166.5	2215.2	2286.1	2305.3
15°	1806.1	1884.4	1928.7	1998.1	2071.9	2097.1	2162.0	2200.4	2300.8	2345.2	2398.3
17.5°	1766.2	1853.4	1912.5	1992.2	2064.6	2113.3	2176.8	2255.1	2339.2	2402.7	2461.8
20°	1733.8	1817.9	1888.8	1977.4	2069.0	2131.0	2197.5	2292.0	2383.5	2448.5	2494.3
22.5°	1659.9	1767.7	1850.4	1949.4	2060.1	2145.8	2209.3	2312.7	2411.6	2451.5	2491.4
25°	1623.0	1716.0	1812.0	1924.3	2054.2	2156.1	2210.8	2326.0	2413.1	2427.9	2436.7
27.5°	1555.1	1659.9	1772.2	1900.6	2052.7	2138.4	2207.8	2312.7	2382.1	2371.7	2345.2
30°	1470.9	1599.4	1723.4	1862.2	2032.1	2125.1	2190.1	2286.1	2321.5	2268.4	2221.1
32.5°	1408.9	1530.0	1667.3	1828.3	2008.4	2097.1	2160.6	2235.9	2243.3	2147.3	2067.5
35°	1324.7	1459.1	1614.1	1784.0	1968.6	2048.3	2107.4	2153.2	2117.7	1983.3	1888.8
37.5°	1249.4	1382.3	1547.7	1720.5	1913.9	1992.2	2039.5	2046.8	1959.7	1841.6	1702.7
40°	1166.7	1304.0	1476.8	1658.4	1853.4	1921.3	1950.8	1928.7	1803.2	1665.8	1504.9
42.5°	1084.0	1219.8	1405.9	1592.0	1776.6	1834.2	1846.0	1785.4	1631.9	1470.9	1284.8
45°	993.9	1135.7	1321.7	1509.3	1688.0	1720.5	1721.9	1634.8	1453.2	1284.8	1112.0
47.5°	920.0	1051.5	1236.1	1423.6	1574.3	1596.4	1587.6	1487.1	1289.2	1100.2	949.6
50°	838.8	964.3	1147.5	1332.1	1460.6	1466.5	1444.3	1301.1	1107.6	934.8	815.2
52.5°	751.7	878.7	1047.0	1224.3	1339.5	1330.6	1287.8	1134.2	952.5	809.3	717.7
55°	682.3	794.5	952.5	1125.3	1206.5	1181.4	1134.2	977.6	834.4	713.3	633.5
57.5°	605.5	704.4	859.5	1010.1	1057.4	1033.8	986.5	840.3	707.4	615.8	562.7
60°	533.1	623.2	759.1	884.6	921.5	896.4	841.8	710.3	614.3	537.6	497.7
62.5°	466.7	544.9	658.7	773.8	788.6	763.5	716.2	609.9	527.2	466.7	437.1
65°	404.6	478.5	570.0	657.2	670.5	643.9	595.1	518.4	448.9	410.5	382.5
67.5°	344.1	403.2	484.4	547.9	555.3	530.2	490.3	428.3	385.4	344.1	323.4
70°	290.9	335.2	398.7	450.4	453.4	429.7	409.1	353.0	320.5	290.9	274.7
72.5°	239.2	270.3	319.0	357.4	358.9	344.1	324.9	289.5	261.4	240.7	224.5
75°	189.0	215.6	245.1	279.1	277.6	265.8	251.1	228.9	205.3	192.0	184.6
77.5°	144.7	161.0	184.6	206.8	206.8	200.8	192.0	175.7	161.0	147.7	140.3
80°	103.4	113.7	132.9	140.3	143.2	141.8	134.4	122.6	116.7	106.3	103.4
82.5°	66.5	73.8	82.7	90.1	94.5	91.6	90.1	84.2	75.3	72.4	69.4
85°	38.4	41.4	45.8	50.2	51.7	50.2	53.2	48.7	44.3	44.3	42.8
87.5°	16.2	17.7	20.7	20.7	22.2	22.2	20.7	22.2	22.2	20.7	19.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P997541

CATALOG NUMBER: SA2XXDP-B1005DB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3
2.5°	1996.6	1998.1	2001.1	2015.8	2023.2	2024.7	2018.8	2032.1	2036.5	2032.1	2029.1
5°	2091.1	2100.0	2117.7	2136.9	2135.4	2136.9	2145.8	2154.6	2157.6	2145.8	2150.2
7.5°	2173.8	2191.6	2210.8	2240.3	2240.3	2255.1	2261.0	2268.4	2286.1	2277.2	2274.3
10°	2268.4	2292.0	2327.4	2374.7	2376.2	2390.9	2405.7	2429.3	2436.7	2430.8	2433.8
12.5°	2386.5	2432.3	2435.2	2486.9	2510.6	2513.5	2537.1	2532.7	2547.5	2547.5	2572.6
15°	2438.2	2509.1	2549.0	2599.2	2613.9	2596.2	2615.4	2636.1	2637.6	2637.6	2636.1
17.5°	2531.2	2559.3	2599.2	2625.7	2631.7	2631.7	2633.1	2642.0	2636.1	2624.3	2633.1
20°	2550.4	2562.2	2577.0	2574.1	2577.0	2562.2	2547.5	2532.7	2534.2	2526.8	2549.0
22.5°	2515.0	2512.0	2478.1	2455.9	2455.9	2426.4	2398.3	2385.0	2371.7	2376.2	2383.5
25°	2426.4	2380.6	2339.2	2306.8	2299.4	2252.1	2213.7	2201.9	2179.8	2197.5	2200.4
27.5°	2284.6	2232.9	2166.5	2138.4	2100.0	2080.8	2054.2	2018.8	1973.0	1999.6	1995.2
30°	2132.5	2055.7	2001.1	1933.1	1872.6	1868.1	1817.9	1758.9	1735.2	1735.2	1748.5
32.5°	1962.7	1860.8	1781.0	1685.0	1626.0	1600.8	1540.3	1481.2	1494.5	1450.2	1466.5
35°	1764.8	1630.4	1530.0	1436.9	1392.6	1363.1	1284.8	1252.3	1216.9	1196.2	1234.6
37.5°	1575.7	1420.7	1292.2	1190.3	1174.1	1120.9	1067.7	1047.0	1026.4	1035.2	1033.8
40°	1345.4	1208.0	1092.8	1013.1	985.0	959.9	924.5	899.4	886.1	893.5	894.9
42.5°	1137.1	1021.9	936.3	880.2	856.5	838.8	821.1	800.4	796.0	796.0	801.9
45°	976.2	881.6	824.1	778.3	765.0	751.7	738.4	729.5	726.6	720.7	725.1
47.5°	847.7	772.4	736.9	703.0	688.2	685.2	673.4	669.0	663.1	661.6	663.1
50°	739.9	692.6	660.1	640.9	630.6	626.2	620.3	611.4	608.4	615.8	612.9
52.5°	664.6	620.3	602.5	583.3	577.4	571.5	562.7	564.1	562.7	559.7	559.7
55°	589.2	561.2	543.5	528.7	527.2	521.3	513.9	511.0	509.5	506.5	511.0
57.5°	528.7	506.5	490.3	477.0	471.1	471.1	463.7	457.8	457.8	456.3	457.8
60°	468.1	446.0	435.7	422.4	417.9	416.5	412.0	409.1	404.6	404.6	404.6
62.5°	412.0	394.3	382.5	370.7	372.2	364.8	358.9	355.9	355.9	357.4	357.4
65°	358.9	347.0	332.3	321.9	319.0	317.5	314.6	313.1	308.7	311.6	311.6
67.5°	310.1	293.9	285.0	280.6	276.2	274.7	271.7	268.8	267.3	265.8	268.8
70°	261.4	248.1	240.7	237.8	233.3	231.9	230.4	225.9	227.4	228.9	230.4
72.5°	217.1	205.3	203.8	194.9	194.9	194.9	189.0	192.0	190.5	187.6	190.5
75°	171.3	165.4	162.4	158.0	159.5	158.0	156.5	152.1	152.1	153.6	155.1
77.5°	135.9	130.0	128.5	124.1	121.1	124.1	121.1	119.6	119.6	121.1	121.1
80°	100.4	97.5	93.0	93.0	93.0	91.6	91.6	91.6	90.1	88.6	90.1
82.5°	66.5	66.5	65.0	63.5	65.0	62.0	63.5	63.5	63.5	63.5	63.5
85°	42.8	41.4	41.4	39.9	39.9	39.9	41.4	38.4	38.4	39.9	39.9
87.5°	19.2	19.2	19.2	20.7	19.2	19.2	19.2	20.7	19.2	19.2	19.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P997541

CATALOG NUMBER: SA2XXDP-B1005DB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3
2.5°	2036.5	2026.2	2017.3	2018.8	2026.2	2020.3	2005.5	1986.3	1978.9	1970.0	1978.9
5°	2159.1	2150.2	2132.5	2134.0	2129.5	2123.6	2100.0	2070.5	2070.5	2046.8	2043.9
7.5°	2280.2	2266.9	2255.1	2252.1	2235.9	2224.1	2203.4	2162.0	2145.8	2117.7	2101.5
10°	2416.0	2405.7	2392.4	2376.2	2367.3	2346.6	2312.7	2252.1	2222.6	2184.2	2156.1
12.5°	2553.4	2551.9	2522.4	2489.9	2488.4	2455.9	2432.3	2351.1	2311.2	2259.5	2193.0
15°	2640.5	2633.1	2616.9	2600.6	2605.1	2569.6	2516.5	2420.5	2393.9	2331.9	2261.0
17.5°	2639.0	2639.0	2634.6	2631.7	2627.2	2616.9	2587.3	2523.8	2481.0	2402.7	2336.3
20°	2554.9	2574.1	2578.5	2577.0	2591.8	2599.2	2597.7	2557.8	2523.8	2454.4	2386.5
22.5°	2386.5	2430.8	2450.0	2461.8	2492.8	2509.1	2547.5	2532.7	2523.8	2472.2	2414.6
25°	2230.0	2244.7	2302.3	2305.3	2348.1	2388.0	2426.4	2451.5	2484.0	2464.8	2416.0
27.5°	2027.6	2061.6	2103.0	2134.0	2142.8	2224.1	2287.6	2334.8	2408.7	2414.6	2398.3
30°	1798.7	1815.0	1882.9	1924.3	1971.5	2030.6	2122.2	2203.4	2269.8	2330.4	2351.1
32.5°	1519.6	1586.1	1626.0	1676.2	1717.5	1822.4	1934.6	2039.5	2116.2	2218.1	2262.5
35°	1264.1	1315.8	1383.8	1404.4	1479.8	1568.4	1714.6	1848.9	1965.6	2069.0	2159.1
37.5°	1053.0	1094.3	1166.7	1199.2	1243.5	1357.2	1479.8	1646.6	1786.9	1913.9	2026.2
40°	908.2	939.2	993.9	1004.2	1041.1	1144.5	1243.5	1400.0	1586.1	1757.4	1880.0
42.5°	809.3	824.1	861.0	874.3	897.9	967.3	1055.9	1203.6	1376.4	1553.6	1726.4
45°	738.4	748.7	770.9	782.7	812.2	843.3	915.6	1033.8	1169.6	1348.3	1534.4
47.5°	674.9	688.2	697.0	704.4	720.7	754.6	801.9	889.0	1019.0	1182.9	1363.1
50°	621.7	626.2	642.4	643.9	654.2	676.4	720.7	773.8	877.2	1010.1	1184.4
52.5°	568.6	573.0	583.3	593.7	598.1	615.8	645.4	689.7	766.5	871.3	1026.4
55°	515.4	521.3	531.6	539.0	543.5	558.2	576.0	618.8	679.3	753.2	880.2
57.5°	462.2	475.5	478.5	482.9	490.3	506.5	522.8	547.9	595.1	663.1	756.1
60°	412.0	416.5	426.8	431.2	438.6	447.5	468.1	487.3	521.3	574.5	658.7
62.5°	360.3	370.7	375.1	379.5	385.4	395.8	409.1	429.7	459.3	502.1	568.6
65°	316.0	317.5	326.4	332.3	338.2	345.6	358.9	378.1	395.8	435.7	484.4
67.5°	273.2	276.2	279.1	285.0	292.4	299.8	311.6	321.9	344.1	370.7	409.1
70°	231.9	231.9	239.2	243.7	242.2	251.1	259.9	271.7	288.0	313.1	344.1
72.5°	194.9	193.5	199.4	200.8	203.8	209.7	215.6	227.4	236.3	255.5	279.1
75°	155.1	158.0	161.0	161.0	165.4	169.8	175.7	181.6	192.0	203.8	221.5
77.5°	122.6	122.6	125.5	127.0	131.4	130.0	135.9	141.8	149.2	159.5	172.8
80°	90.1	93.0	93.0	93.0	94.5	96.0	101.9	106.3	110.8	118.1	124.1
82.5°	63.5	63.5	66.5	66.5	66.5	69.4	69.4	70.9	73.8	78.3	82.7
85°	39.9	39.9	39.9	41.4	39.9	41.4	44.3	42.8	44.3	47.3	47.3
87.5°	19.2	19.2	19.2	19.2	19.2	20.7	19.2	20.7	22.2	22.2	22.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P997541

CATALOG NUMBER: SA2XXDP-B1005DB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3
2.5°	1971.5	1964.1	1959.7	1962.7	1953.8	1931.6	1931.6	1939.0	1930.2	1921.3	1908.0
5°	2026.2	2011.4	2002.5	2001.1	1980.4	1944.9	1937.6	1930.2	1911.0	1890.3	1868.1
7.5°	2079.3	2052.7	2038.0	2027.6	1998.1	1952.3	1933.1	1916.9	1885.9	1854.9	1826.8
10°	2123.6	2085.2	2067.5	2051.3	2012.9	1955.3	1924.3	1894.7	1854.9	1815.0	1779.5
12.5°	2159.1	2114.8	2092.6	2069.0	2021.7	1946.4	1908.0	1860.8	1820.9	1767.7	1732.3
15°	2218.1	2126.6	2105.9	2083.8	2035.0	1931.6	1884.4	1831.2	1776.6	1705.7	1667.3
17.5°	2265.4	2142.8	2141.4	2094.1	2030.6	1925.7	1853.4	1784.0	1724.9	1654.0	1593.5
20°	2293.5	2167.9	2144.3	2095.6	2015.8	1885.9	1810.6	1733.8	1670.3	1584.6	1524.1
22.5°	2317.1	2203.4	2141.4	2082.3	1984.8	1872.6	1761.8	1689.5	1602.3	1509.3	1451.7
25°	2326.0	2210.8	2145.8	2077.9	1962.7	1834.2	1708.7	1630.4	1532.9	1448.7	1370.5
27.5°	2327.4	2209.3	2129.5	2058.7	1931.6	1784.0	1655.5	1572.8	1465.0	1367.5	1289.2
30°	2312.7	2193.0	2120.7	2043.9	1902.1	1738.2	1590.5	1498.9	1383.8	1286.3	1205.1
32.5°	2268.4	2160.6	2101.5	2017.3	1863.7	1674.7	1528.5	1426.6	1305.5	1209.5	1131.2
35°	2194.5	2120.7	2055.7	1977.4	1813.5	1615.6	1466.5	1346.8	1224.3	1132.7	1058.9
37.5°	2103.0	2063.1	2002.5	1925.7	1755.9	1562.5	1397.0	1264.1	1141.6	1053.0	980.6
40°	1978.9	1989.2	1930.2	1860.8	1688.0	1490.1	1307.0	1180.0	1064.8	982.1	911.2
42.5°	1844.5	1887.3	1853.4	1786.9	1612.7	1410.3	1240.5	1100.2	988.0	902.3	843.3
45°	1699.8	1773.6	1753.0	1704.2	1534.4	1326.2	1146.0	1010.1	911.2	828.5	776.8
47.5°	1541.8	1646.6	1646.6	1611.2	1447.3	1242.0	1064.8	926.0	828.5	769.4	719.2
50°	1380.8	1498.9	1518.1	1494.5	1349.8	1146.0	965.8	840.3	756.1	698.5	661.6
52.5°	1212.4	1349.8	1385.2	1373.4	1246.4	1054.4	884.6	762.0	685.2	635.0	602.5
55°	1051.5	1211.0	1249.4	1253.8	1135.7	954.0	794.5	686.7	612.9	578.9	550.8
57.5°	899.4	1053.0	1095.8	1103.2	1023.4	862.4	710.3	615.8	549.4	521.3	499.2
60°	769.4	897.9	954.0	970.3	900.8	756.1	632.1	540.5	490.3	463.7	443.0
62.5°	663.1	766.5	825.5	830.0	798.9	663.1	550.8	474.1	431.2	407.6	397.3
65°	559.7	652.7	688.2	705.9	680.8	574.5	475.5	412.0	378.1	357.4	347.0
67.5°	477.0	536.1	565.6	589.2	564.1	484.4	404.6	353.0	327.8	307.2	301.3
70°	391.4	440.1	462.2	485.9	463.7	403.2	345.6	298.3	276.2	259.9	252.5
72.5°	313.1	351.5	372.2	386.9	373.6	323.4	276.2	243.7	227.4	215.6	211.2
75°	248.1	274.7	286.5	296.8	290.9	252.5	223.0	196.4	181.6	171.3	168.4
77.5°	189.0	208.2	221.5	224.5	217.1	192.0	166.9	150.6	138.8	132.9	130.0
80°	134.4	146.2	153.6	158.0	150.6	140.3	122.6	110.8	100.4	93.0	91.6
82.5°	90.1	96.0	101.9	100.4	97.5	88.6	78.3	72.4	67.9	62.0	62.0
85°	51.7	53.2	56.1	57.6	56.1	50.2	44.3	41.4	38.4	34.0	34.0
87.5°	22.2	23.6	23.6	25.1	22.2	22.2	19.2	16.2	16.2	14.8	13.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P997541

CATALOG NUMBER: SA2XXDP-B1005DB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3
2.5°	1900.6	1908.0	1906.5	1891.8	1875.5	1862.2	1837.1	1840.1	1831.2	1832.7	1841.6
5°	1853.4	1853.4	1847.5	1826.8	1800.2	1785.4	1757.4	1750.0	1732.3	1730.8	1729.3
7.5°	1803.2	1795.8	1788.4	1758.9	1726.4	1702.7	1664.3	1655.5	1637.8	1626.0	1620.0
10°	1744.1	1733.8	1719.0	1685.0	1645.2	1615.6	1575.7	1563.9	1530.0	1515.2	1506.3
12.5°	1679.1	1673.2	1649.6	1621.5	1556.5	1524.1	1466.5	1478.3	1444.3	1414.8	1410.3
15°	1614.1	1592.0	1578.7	1532.9	1454.6	1439.9	1394.1	1370.5	1339.5	1315.8	1315.8
17.5°	1550.6	1516.7	1487.1	1438.4	1380.8	1339.5	1305.5	1293.7	1255.3	1231.6	1227.2
20°	1466.5	1428.1	1420.7	1351.3	1311.4	1265.6	1233.1	1203.6	1175.5	1165.2	1157.8
22.5°	1386.7	1342.4	1330.6	1271.5	1231.6	1185.9	1153.4	1132.7	1112.0	1104.6	1091.4
25°	1301.1	1274.5	1256.8	1193.3	1148.9	1106.1	1084.0	1069.2	1050.0	1048.5	1039.7
27.5°	1218.4	1193.3	1175.5	1115.0	1082.5	1042.6	1024.9	1008.7	998.3	993.9	989.5
30°	1147.5	1119.4	1098.7	1054.4	1014.6	982.1	967.3	957.0	951.1	943.7	942.2
32.5°	1069.2	1053.0	1024.9	990.9	959.9	928.9	920.0	912.7	903.8	900.8	899.4
35°	1002.7	980.6	962.9	924.5	911.2	884.6	874.3	868.4	856.5	853.6	850.6
37.5°	937.8	917.1	897.9	874.3	849.2	834.4	828.5	819.6	813.7	815.2	812.2
40°	872.8	856.5	841.8	816.7	801.9	794.5	782.7	773.8	770.9	772.4	770.9
42.5°	809.3	794.5	785.7	766.5	751.7	744.3	736.9	728.1	732.5	732.5	736.9
45°	751.7	738.4	732.5	717.7	708.9	697.0	689.7	688.2	694.1	692.6	692.6
47.5°	692.6	688.2	680.8	667.5	655.7	648.3	646.8	646.8	652.7	655.7	654.2
50°	646.8	638.0	629.1	618.8	609.9	607.0	602.5	605.5	611.4	611.4	614.3
52.5°	589.2	583.3	580.4	571.5	565.6	565.6	565.6	567.1	571.5	576.0	574.5
55°	539.0	534.6	531.6	527.2	519.8	521.3	519.8	522.8	527.2	531.6	534.6
57.5°	485.9	484.4	481.4	474.1	474.1	472.6	477.0	478.5	485.9	488.8	493.3
60°	438.6	434.2	434.2	428.3	428.3	428.3	432.7	437.1	443.0	444.5	447.5
62.5°	388.4	388.4	386.9	382.5	382.5	386.9	388.4	394.3	397.3	397.3	401.7
65°	341.1	339.7	338.2	339.7	341.1	341.1	345.6	348.5	351.5	353.0	354.4
67.5°	293.9	292.4	295.4	293.9	296.8	302.7	301.3	305.7	310.1	310.1	311.6
70°	249.6	252.5	251.1	254.0	252.5	255.5	259.9	261.4	261.4	262.9	267.3
72.5°	208.2	208.2	208.2	206.8	208.2	211.2	214.1	215.6	218.6	220.0	224.5
75°	168.4	168.4	165.4	168.4	168.4	171.3	174.3	174.3	174.3	177.2	181.6
77.5°	127.0	128.5	127.0	130.0	130.0	131.4	134.4	132.9	135.9	137.3	138.8
80°	93.0	91.6	91.6	91.6	93.0	93.0	96.0	97.5	97.5	101.9	98.9
82.5°	59.1	60.5	59.1	60.5	60.5	62.0	60.5	62.0	63.5	66.5	65.0
85°	34.0	32.5	32.5	34.0	32.5	32.5	34.0	32.5	34.0	32.5	34.0
87.5°	13.3	11.8	11.8	11.8	11.8	10.3	10.3	8.9	8.9	8.9	7.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P997541

CATALOG NUMBER: SA2XXDP-B1005DB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3
2.5°	1831.2	1835.7	1825.3	1822.4	1825.3	1815.0	1817.9	1820.9	1820.9	1825.3	1828.3
5°	1724.9	1719.0	1708.7	1705.7	1702.7	1707.2	1704.2	1708.7	1710.1	1720.5	1721.9
7.5°	1620.0	1611.2	1602.3	1593.5	1590.5	1583.1	1590.5	1590.5	1600.8	1597.9	1605.3
10°	1496.0	1494.5	1482.7	1478.3	1472.4	1460.6	1476.8	1472.4	1479.8	1493.0	1496.0
12.5°	1404.4	1388.2	1395.6	1374.9	1382.3	1370.5	1371.9	1371.9	1383.8	1385.2	1382.3
15°	1317.3	1304.0	1284.8	1276.0	1271.5	1265.6	1284.8	1286.3	1277.4	1298.1	1290.7
17.5°	1228.7	1228.7	1211.0	1206.5	1194.7	1200.6	1197.7	1199.2	1196.2	1211.0	1218.4
20°	1151.9	1144.5	1138.6	1140.1	1125.3	1122.4	1119.4	1122.4	1132.7	1143.0	1146.0
22.5°	1089.9	1085.4	1070.7	1073.6	1061.8	1066.2	1063.3	1070.7	1072.2	1072.2	1082.5
25°	1030.8	1024.9	1026.4	1020.5	1016.0	1016.0	1011.6	1016.0	1021.9	1024.9	1026.4
27.5°	986.5	982.1	974.7	970.3	973.2	965.8	971.7	976.2	976.2	973.2	976.2
30°	933.3	936.3	936.3	921.5	927.4	924.5	928.9	931.9	931.9	933.3	930.4
32.5°	897.9	889.0	887.6	886.1	886.1	880.2	880.2	884.6	886.1	887.6	892.0
35°	850.6	850.6	843.3	847.7	841.8	843.3	841.8	843.3	846.2	841.8	846.2
37.5°	807.8	809.3	806.3	809.3	810.8	807.8	804.9	810.8	807.8	807.8	804.9
40°	770.9	769.4	770.9	770.9	770.9	772.4	769.4	769.4	769.4	766.5	763.5
42.5°	739.9	731.0	734.0	735.4	731.0	731.0	732.5	731.0	735.4	726.6	726.6
45°	695.6	692.6	694.1	694.1	697.0	692.6	695.6	697.0	692.6	691.1	688.2
47.5°	655.7	658.7	655.7	658.7	658.7	661.6	655.7	657.2	658.7	652.7	648.3
50°	615.8	615.8	620.3	618.8	620.3	617.3	617.3	615.8	617.3	614.3	609.9
52.5°	578.9	574.5	581.9	580.4	578.9	577.4	576.0	577.4	574.5	571.5	571.5
55°	533.1	533.1	537.6	539.0	539.0	536.1	533.1	534.6	533.1	531.6	530.2
57.5°	496.2	490.3	493.3	494.7	494.7	490.3	493.3	490.3	490.3	491.8	487.3
60°	448.9	448.9	446.0	450.4	450.4	447.5	447.5	448.9	446.0	444.5	443.0
62.5°	398.7	400.2	404.6	406.1	407.6	404.6	401.7	403.2	403.2	398.7	400.2
65°	355.9	358.9	364.8	363.3	360.3	361.8	358.9	360.3	355.9	357.4	353.0
67.5°	314.6	313.1	314.6	314.6	317.5	316.0	313.1	313.1	311.6	316.0	311.6
70°	270.3	270.3	270.3	270.3	271.7	273.2	270.3	267.3	268.8	265.8	264.3
72.5°	224.5	225.9	224.5	227.4	223.0	225.9	225.9	224.5	223.0	223.0	223.0
75°	181.6	184.6	180.2	181.6	180.2	183.1	181.6	181.6	178.7	177.2	178.7
77.5°	138.8	140.3	137.3	138.8	137.3	138.8	138.8	137.3	137.3	137.3	137.3
80°	98.9	100.4	98.9	97.5	96.0	98.9	96.0	97.5	98.9	97.5	100.4
82.5°	63.5	63.5	62.0	63.5	60.5	60.5	62.0	62.0	60.5	63.5	60.5
85°	31.0	31.0	34.0	31.0	29.5	29.5	29.5	31.0	29.5	32.5	31.0
87.5°	7.4	5.9	7.4	7.4	5.9	5.9	7.4	5.9	7.4	8.9	5.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P997541

CATALOG NUMBER: SA2XXDP-B1005DB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3
2.5°	1823.8	1835.7	1831.2	1815.0	1834.2	1834.2	1847.5	1847.5	1863.7	1869.6	1878.5
5°	1720.5	1729.3	1736.7	1729.3	1742.6	1763.3	1775.1	1785.4	1807.6	1816.5	1829.8
7.5°	1609.7	1626.0	1633.3	1633.3	1655.5	1679.1	1702.7	1717.5	1748.5	1760.3	1773.6
10°	1501.9	1521.1	1535.9	1534.4	1571.3	1586.1	1615.6	1649.6	1680.6	1698.3	1717.5
12.5°	1388.2	1398.5	1419.2	1448.7	1457.6	1484.2	1518.1	1561.0	1617.1	1633.3	1661.4
15°	1293.7	1321.7	1338.0	1351.3	1371.9	1397.0	1434.0	1475.3	1531.4	1566.9	1596.4
17.5°	1213.9	1250.8	1261.2	1258.2	1284.8	1323.2	1366.0	1397.0	1447.3	1490.1	1518.1
20°	1148.9	1163.7	1181.4	1188.8	1209.5	1250.8	1292.2	1327.6	1369.0	1403.0	1435.4
22.5°	1084.0	1095.8	1110.6	1123.8	1140.1	1163.7	1203.6	1247.9	1287.8	1320.3	1357.2
25°	1030.8	1038.2	1051.5	1061.8	1079.5	1095.8	1123.8	1172.6	1219.8	1239.0	1271.5
27.5°	979.1	985.0	993.9	1005.7	1014.6	1030.8	1055.9	1095.8	1144.5	1163.7	1208.0
30°	933.3	937.8	946.6	952.5	957.0	976.2	995.4	1026.4	1063.3	1089.9	1122.4
32.5°	890.5	894.9	903.8	905.3	911.2	921.5	939.2	967.3	999.8	1021.9	1050.0
35°	843.3	846.2	855.1	858.0	862.4	871.3	884.6	905.3	934.8	951.1	976.2
37.5°	806.3	804.9	810.8	815.2	821.1	825.5	830.0	850.6	872.8	887.6	906.8
40°	766.5	763.5	765.0	770.9	773.8	779.7	779.7	800.4	815.2	827.0	841.8
42.5°	726.6	725.1	722.2	725.1	728.1	729.5	731.0	745.8	760.6	770.9	787.1
45°	686.7	685.2	682.3	683.8	683.8	686.7	691.1	697.0	707.4	716.2	725.1
47.5°	649.8	646.8	642.4	640.9	643.9	643.9	643.9	649.8	660.1	663.1	671.9
50°	611.4	607.0	601.1	598.1	598.1	596.6	599.6	601.1	609.9	612.9	620.3
52.5°	570.0	567.1	561.2	555.3	556.8	553.8	555.3	556.8	559.7	564.1	568.6
55°	528.7	522.8	518.4	516.9	512.4	512.4	508.0	513.9	512.4	513.9	519.8
57.5°	488.8	482.9	475.5	472.6	468.1	466.7	463.7	462.2	463.7	468.1	472.6
60°	441.6	438.6	434.2	429.7	426.8	422.4	419.4	419.4	417.9	417.9	419.4
62.5°	395.8	394.3	388.4	386.9	384.0	381.0	376.6	373.6	373.6	376.6	378.1
65°	351.5	350.0	345.6	344.1	336.7	333.8	332.3	330.8	327.8	327.8	327.8
67.5°	310.1	305.7	305.7	298.3	292.4	289.5	286.5	285.0	285.0	285.0	286.5
70°	264.3	264.3	259.9	255.5	249.6	251.1	246.6	242.2	242.2	239.2	240.7
72.5°	220.0	218.6	214.1	212.7	208.2	203.8	200.8	203.8	199.4	197.9	199.4
75°	177.2	175.7	172.8	169.8	171.3	166.9	162.4	161.0	161.0	158.0	158.0
77.5°	135.9	138.8	132.9	131.4	128.5	125.5	124.1	122.6	122.6	122.6	125.5
80°	94.5	96.0	96.0	93.0	94.5	90.1	90.1	90.1	85.7	87.1	88.6
82.5°	60.5	60.5	59.1	60.5	59.1	59.1	57.6	57.6	56.1	56.1	57.6
85°	34.0	32.5	31.0	34.0	32.5	32.5	31.0	31.0	31.0	31.0	31.0
87.5°	7.4	8.9	8.9	8.9	8.9	10.3	10.3	10.3	11.8	11.8	11.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P997541

CATALOG NUMBER: SA2XXDP-B1005DB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1921.3	1921.3	1921.3	1921.3
2.5°	1885.9	1885.9	1908.0	1931.6
5°	1844.5	1854.9	1890.3	1922.8
7.5°	1804.6	1822.4	1866.7	1908.0
10°	1755.9	1779.5	1834.2	1882.9
12.5°	1708.7	1730.8	1794.3	1848.9
15°	1642.2	1670.3	1738.2	1806.1
17.5°	1575.7	1603.8	1686.5	1766.2
20°	1497.5	1534.4	1627.4	1733.8
22.5°	1425.1	1470.9	1574.3	1659.9
25°	1345.4	1416.2	1512.2	1623.0
27.5°	1274.5	1345.4	1442.8	1555.1
30°	1194.7	1267.1	1367.5	1470.9
32.5°	1117.9	1184.4	1281.9	1408.9
35°	1038.2	1101.7	1196.2	1324.7
37.5°	965.8	1027.9	1131.2	1249.4
40°	894.9	959.9	1048.5	1166.7
42.5°	828.5	886.1	965.8	1084.0
45°	767.9	809.3	883.1	993.9
47.5°	704.4	741.4	809.3	920.0
50°	645.4	676.4	735.4	838.8
52.5°	587.8	614.3	669.0	751.7
55°	536.1	561.2	601.1	682.3
57.5°	482.9	502.1	540.5	605.5
60°	431.2	448.9	480.0	533.1
62.5°	379.5	394.3	423.8	466.7
65°	333.8	345.6	367.7	404.6
67.5°	289.5	296.8	314.6	344.1
70°	246.6	252.5	267.3	290.9
72.5°	200.8	206.8	223.0	239.2
75°	162.4	163.9	175.7	189.0
77.5°	127.0	125.5	134.4	144.7
80°	87.1	91.6	98.9	103.4
82.5°	59.1	60.5	63.5	66.5
85°	32.5	34.0	34.0	38.4
87.5°	13.3	14.8	14.8	16.2
90°	0.0	0.0	0.0	0.0

TEST NUMBER: P997541

CATALOG NUMBER: SA2XXDP-B1005DB2750-4F0-XX-W2A-A_5000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	23.84	25.35	24.20	25.67	25.98	20.10	21.62	20.47	21.93	22.25
	3H	24.95	26.31	25.33	26.64	27.00	21.52	22.88	21.89	23.21	23.57
	4H	25.27	26.55	25.67	26.90	27.28	22.02	23.30	22.42	23.65	24.03
	6H	25.46	26.64	25.88	27.01	27.40	22.38	23.56	22.79	23.93	24.32
	8H	25.50	26.63	25.93	27.02	27.42	22.49	23.62	22.92	24.01	24.41
	12H	25.52	26.59	25.95	26.98	27.40	22.57	23.64	23.00	24.02	24.45
4H	2H	23.95	25.23	24.35	25.58	25.96	20.90	22.18	21.30	22.53	22.90
	3H	25.29	26.35	25.70	26.75	27.15	22.48	23.54	22.89	23.94	24.34
	4H	25.76	26.71	26.19	27.13	27.57	23.08	24.03	23.51	24.45	24.88
	6H	26.09	26.92	26.55	27.36	27.82	23.53	24.36	23.99	24.80	25.26
	8H	26.17	26.94	26.63	27.39	27.85	23.67	24.45	24.14	24.89	25.36
	12H	26.21	26.90	26.69	27.38	27.85	23.78	24.47	24.26	24.95	25.42
8H	4H	25.84	26.62	26.31	27.06	27.53	23.48	24.26	23.95	24.70	25.17
	6H	26.25	26.89	26.75	27.38	27.86	24.03	24.67	24.52	25.16	25.64
	8H	26.38	26.95	26.89	27.46	27.95	24.23	24.80	24.74	25.31	25.80
	12H	26.47	26.98	26.98	27.47	28.03	24.39	24.90	24.90	25.39	25.95
12H	4H	25.84	26.53	26.32	27.01	27.48	23.54	24.23	24.02	24.71	25.18
	6H	26.24	26.82	26.76	27.33	27.82	24.10	24.68	24.62	25.19	25.67
	8H	26.41	26.92	26.92	27.41	27.98	24.35	24.86	24.86	25.35	25.91

END OF REPORT