

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001948

Luminaire Tested: SA4XXDIP-B795D810UB2750-4F0-XX-W2A-D_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001948
REPORT IS A COMBINATION OF REPORTS P996573 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B795D810UB2750-4F0-XX-W2A-D_2700K
Description: Define 4 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6362.0 lumens
Efficiency: N/A
Efficacy: 111.6 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 57
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001948

CATALOG NUMBER: SA4XXDIP-B795D810UB2750-4F0-XX-W2A-D_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1001948

CATALOG NUMBER: SA4XXDIP-B795D810UB2750-4F0-XX-W2A-D_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	53	53	53	47		
1	96	91	87	83	88	84	80	77	70	67	65	57	55	54	46	44	43	38		
2	87	79	73	67	80	73	67	62	61	57	53	50	47	44	40	37	36	31		
3	79	69	62	56	72	64	57	52	53	48	44	44	40	37	35	32	30	26		
4	72	61	53	47	66	56	49	43	47	42	37	39	35	31	31	28	25	22		
5	66	54	46	40	60	50	43	37	42	36	32	35	30	27	28	24	22	19		
6	61	49	40	34	56	45	37	32	38	32	28	31	27	23	25	22	19	16		
7	56	44	36	30	51	40	33	28	34	28	24	28	24	21	23	19	17	14		
8	52	40	32	26	48	37	30	25	31	25	21	26	21	18	21	18	15	13		
9	49	36	28	23	44	33	27	22	28	23	19	24	19	16	19	16	14	11		
10	45	33	26	21	41	31	24	20	26	21	17	22	18	15	18	15	12	10		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7721	7721	7721
5°	7742	7519	7533
10°	7692	7371	7350
15°	7619	7205	7144
20°	7513	7025	6944
25°	7393	6827	6729
30°	7263	6630	6508
35°	7116	6428	6313
40°	6997	6236	6110
45°	6824	6054	5931
50°	6674	5848	5741
55°	6520	5650	5523
60°	6281	5403	5319
65°	6020	5136	5071
70°	5700	4833	4786
75°	5256	4494	4514
80°	4754	4149	4230
85°	4090	3803	3999

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6824 cd/sqm

TEST NUMBER: P1001948

CATALOG NUMBER: SA4XXDIP-B795D810UB2750-4F0-XX-W2A-D_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.7	1.4
10°-20°	257.0	4.0
20°-30°	388.6	6.1
30°-40°	470.2	7.4
40°-50°	497.1	7.8
50°-60°	467.8	7.4
60°-70°	388.2	6.1
70°-80°	272.4	4.3
80°-90°	155.7	2.4
90°-100°	125.0	2.0
100°-110°	289.0	4.5
110°-120°	467.9	7.4
120°-130°	561.9	8.8
130°-140°	584.9	9.2
140°-150°	538.7	8.5
150°-160°	432.7	6.8
160°-170°	279.0	4.4
170°-180°	96.2	1.5
0°-30°	735.4	11.6
0°-40°	1205.6	18.9
0°-60°	2170.4	34.1
0°-90°	2986.7	46.9
90°-120°	881.9	13.9
90°-150°	2567.5	40.4
90°-180°	3375.0	53.0
0°-180°	6362.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	947	947	947	947	947	
5°	948	945	937	946	945	90
15°	909	910	906	916	915	256
25°	831	838	841	852	854	383
35°	727	740	751	766	769	455
45°	606	627	647	665	670	469
55°	475	497	529	550	557	423
65°	329	363	399	425	434	326
75°	182	222	266	296	305	194
85°	56	101	148	180	191	59
90°	19	70	122	157	167	14
95°	55	65	109	142	152	62
105°	237	263	306	340	321	249
115°	432	444	477	502	509	425
125°	602	604	629	652	659	538
135°	744	743	754	772	780	574
145°	856	858	858	865	871	535
155°	938	939	936	940	937	433
165°	989	986	986	992	985	280
175°	1012	1008	1008	1015	1006	96
180°	1012	1012	1012	1012	1012	

TEST NUMBER: P1001948

CATALOG NUMBER: SA4XXDIP-B795D810UB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	946.8	946.8	946.8	946.8	946.8
2.5°	951.0	947.9	939.4	946.8	945.7
5°	947.9	944.7	937.2	945.7	944.7
7.5°	941.5	939.4	933.0	942.6	941.5
10°	933.0	931.9	926.6	936.2	935.1
12.5°	921.3	921.3	918.2	926.6	926.6
15°	908.6	909.7	906.5	916.0	915.0
17.5°	891.7	894.8	893.8	903.3	902.3
20°	873.6	876.8	877.9	888.5	888.5
22.5°	853.5	857.7	859.9	870.5	872.6
25°	831.2	837.6	840.8	852.4	853.5
27.5°	806.8	816.4	820.6	831.2	832.3
30°	782.5	790.9	798.4	810.0	812.1
32.5°	755.9	766.6	775.0	788.8	790.9
35°	727.3	740.0	750.6	765.5	768.7
37.5°	698.7	713.5	726.3	741.1	744.3
40°	671.1	684.9	699.8	715.7	719.9
42.5°	639.3	655.2	673.3	691.3	694.5
45°	606.5	626.6	646.7	664.8	670.1
47.5°	575.7	595.9	619.2	637.2	643.6
50°	541.8	565.1	588.4	609.6	616.0
52.5°	507.9	531.2	558.7	579.9	586.3
55°	475.0	497.3	529.1	550.3	556.6
57.5°	437.9	465.4	496.2	521.6	526.9
60°	401.8	429.4	464.4	488.8	497.3
62.5°	366.8	397.6	432.6	457.0	465.4
65°	328.7	362.6	398.6	425.2	433.6
67.5°	292.6	328.7	366.8	393.3	401.8
70°	255.5	291.6	331.9	360.5	367.9
72.5°	219.5	256.6	300.0	327.6	336.1
75°	182.4	221.6	266.1	295.8	305.3
77.5°	147.4	188.7	235.4	265.1	275.7
80°	115.6	158.0	204.6	236.4	244.9
82.5°	83.8	128.3	174.9	207.8	217.3
85°	56.2	100.7	148.4	180.2	190.8
87.5°	35.0	78.5	125.1	155.9	165.4
90°	19.3	70.0	121.7	156.9	166.9
92.5°	27.3	62.8	114.5	148.7	157.2
95°	55.4	64.7	108.9	142.1	152.4
97.5°	92.2	139.6	103.6	134.9	145.2
100°	135.9	177.0	113.9	129.6	137.8
102.5°	185.8	218.2	267.6	124.8	133.3
105°	237.4	263.1	306.2	339.5	320.8
107.5°	286.6	306.9	349.3	379.6	390.1
110°	335.5	352.6	394.2	420.2	430.9



TEST NUMBER: P1001948

CATALOG NUMBER: SA4XXDIP-B795D810UB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	382.9	400.1	436.6	459.3	470.7
115°	431.8	443.6	476.8	501.7	509.1
117.5°	476.5	485.8	519.9	541.5	550.0
120°	520.8	527.1	557.0	579.7	586.7
122.5°	563.2	564.7	594.9	616.8	622.8
125°	602.2	604.3	629.3	651.6	658.8
127.5°	640.9	640.6	665.6	683.9	690.6
130°	676.9	676.6	695.9	715.7	722.0
132.5°	711.0	711.4	727.2	746.0	751.6
135°	744.0	743.2	753.7	772.2	780.1
137.5°	774.3	773.3	781.2	798.7	803.2
140°	803.8	804.3	806.8	822.9	828.9
142.5°	829.3	832.3	832.0	845.2	849.4
145°	856.5	857.7	857.7	864.9	870.6
147.5°	877.7	881.2	880.4	882.3	887.2
150°	901.2	903.1	902.4	902.4	903.1
152.5°	919.8	922.1	920.5	922.1	921.3
155°	937.9	938.7	936.4	939.5	937.2
157.5°	953.8	953.8	950.8	954.6	950.8
160°	967.5	965.2	964.4	969.0	964.4
162.5°	979.6	976.6	975.8	980.3	975.0
165°	989.4	985.6	985.6	991.7	984.9
167.5°	997.8	994.0	993.2	1000.0	992.5
170°	1004.6	1000.0	1000.8	1006.8	999.3
172.5°	1009.1	1004.6	1005.3	1011.4	1003.1
175°	1012.1	1007.6	1008.4	1015.2	1006.1
177.5°	1014.4	1009.1	1010.6	1016.7	1007.6
180°	1012.1	1012.1	1012.1	1012.1	1012.1

(END OF REPORT)