

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001949

Luminaire Tested: SA4XXDIP-B795D810UB2750-4F0-XX-W2A-D_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001949
REPORT IS A COMBINATION OF REPORTS P996574 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B795D810UB2750-4F0-XX-W2A-D_3000K
Description: Define 4 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6417.0 lumens
Efficiency: N/A
Efficacy: 112.6 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 57
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001949

CATALOG NUMBER: SA4XXDIP-B795D810UB2750-4F0-XX-W2A-D_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1001949

CATALOG NUMBER: SA4XXDIP-B795D810UB2750-4F0-XX-W2A-D_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	106	106	106	106	98	98	98	98		82	82	82		67	67	67		53	53	53
1	96	91	87	83	88	84	80	77		70	67	65		57	55	54		46	44	43
2	87	79	73	67	80	73	67	62		61	57	53		50	47	44		40	37	36
3	79	69	62	56	72	64	57	52		53	48	44		44	40	37		35	32	30
4	72	61	53	47	66	56	49	43		47	42	37		39	35	31		31	28	25
5	66	54	46	40	60	50	43	37		42	36	32		35	30	27		28	24	22
6	61	49	40	34	56	45	37	32		38	32	28		31	27	23		25	22	19
7	56	44	36	30	51	40	33	28		34	28	24		28	24	21		23	19	17
8	52	40	32	26	48	37	30	25		31	25	21		26	21	18		21	18	15
9	49	36	28	23	44	33	27	22		28	23	19		24	19	16		19	16	14
10	45	33	26	21	41	31	24	20		26	21	17		22	18	15		18	15	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7788	7788	7788
5°	7809	7585	7599
10°	7758	7435	7414
15°	7686	7268	7206
20°	7578	7086	7005
25°	7457	6886	6787
30°	7325	6687	6565
35°	7177	6485	6367
40°	7059	6289	6162
45°	6882	6107	5982
50°	6732	5899	5791
55°	6577	5698	5572
60°	6336	5450	5365
65°	6071	5181	5115
70°	5749	4874	4828
75°	5300	4533	4554
80°	4796	4186	4267
85°	4126	3836	4035

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6882 cd/sqm

TEST NUMBER: P1001949

CATALOG NUMBER: SA4XXDIP-B795D810UB2750-4F0-XX-W2A-D_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.5	1.4
10°-20°	259.3	4.0
20°-30°	392.0	6.1
30°-40°	474.3	7.4
40°-50°	501.4	7.8
50°-60°	471.9	7.4
60°-70°	391.5	6.1
70°-80°	274.8	4.3
80°-90°	157.0	2.4
90°-100°	126.1	2.0
100°-110°	291.4	4.5
110°-120°	472.0	7.4
120°-130°	566.8	8.8
130°-140°	589.9	9.2
140°-150°	543.4	8.5
150°-160°	436.4	6.8
160°-170°	281.4	4.4
170°-180°	97.0	1.5
0°-30°	741.8	11.6
0°-40°	1216.0	19.0
0°-60°	2189.2	34.1
0°-90°	3012.6	46.9
90°-120°	889.5	13.9
90°-150°	2589.6	40.4
90°-180°	3404.0	53.0
0°-180°	6417.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	955	955	955	955	955	
5°	956	953	945	954	953	91
15°	916	918	914	924	923	258
25°	838	845	848	860	861	386
35°	734	746	757	772	775	459
45°	612	632	652	670	676	473
55°	479	502	534	555	562	427
65°	332	366	402	429	437	329
75°	184	224	268	298	308	195
85°	57	102	150	182	192	59
90°	19	71	123	158	168	14
95°	56	65	110	143	154	63
105°	239	265	309	342	324	251
115°	436	447	481	506	514	429
125°	608	610	635	657	664	543
135°	750	750	760	779	787	579
145°	864	865	865	872	878	540
155°	946	947	944	948	945	436
165°	998	994	994	1000	993	282
175°	1021	1016	1017	1024	1015	97
180°	1021	1021	1021	1021	1021	

TEST NUMBER: P1001949

CATALOG NUMBER: SA4XXDIP-B795D810UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	955.0	955.0	955.0	955.0	955.0
2.5°	959.3	956.1	947.5	955.0	953.9
5°	956.1	952.9	945.4	953.9	952.9
7.5°	949.7	947.5	941.1	950.7	949.7
10°	941.1	940.0	934.7	944.3	943.2
12.5°	929.3	929.3	926.1	934.7	934.7
15°	916.5	917.6	914.4	924.0	922.9
17.5°	899.4	902.6	901.5	911.2	910.1
20°	881.2	884.4	885.5	896.2	896.2
22.5°	860.9	865.2	867.3	878.0	880.1
25°	838.4	844.9	848.1	859.8	860.9
27.5°	813.8	823.5	827.7	838.4	839.5
30°	789.2	797.8	805.3	817.0	819.2
32.5°	762.5	773.2	781.8	795.7	797.8
35°	733.6	746.5	757.2	772.1	775.3
37.5°	704.8	719.7	732.6	747.5	750.7
40°	677.0	690.9	705.8	721.9	726.1
42.5°	644.9	660.9	679.1	697.3	700.5
45°	611.7	632.0	652.4	670.5	675.9
47.5°	580.7	601.0	624.5	642.7	649.1
50°	546.5	570.0	593.5	614.9	621.3
52.5°	512.3	535.8	563.6	585.0	591.4
55°	479.1	501.6	533.6	555.0	561.5
57.5°	441.7	469.5	500.5	526.2	531.5
60°	405.3	433.1	468.4	493.0	501.6
62.5°	370.0	401.0	436.3	460.9	469.5
65°	331.5	365.7	402.1	428.8	437.4
67.5°	295.2	331.5	370.0	396.8	405.3
70°	257.7	294.1	334.7	363.6	371.1
72.5°	221.4	258.8	302.6	330.5	339.0
75°	183.9	223.5	268.4	298.4	308.0
77.5°	148.7	190.4	237.4	267.4	278.1
80°	116.6	159.3	206.4	238.5	247.0
82.5°	84.5	129.4	176.5	209.6	219.2
85°	56.7	101.6	149.7	181.8	192.5
87.5°	35.3	79.1	126.2	157.2	166.8
90°	19.4	70.6	122.7	158.3	168.3
92.5°	27.5	63.4	115.5	150.0	158.6
95°	55.9	65.2	109.8	143.3	153.6
97.5°	93.0	140.8	104.5	136.1	146.5
100°	137.0	178.6	114.9	130.8	139.0
102.5°	187.4	220.1	269.8	125.8	134.4
105°	239.4	265.4	308.8	342.4	323.5
107.5°	289.1	309.5	352.3	382.9	393.5
110°	338.5	355.6	397.7	423.8	434.6

TEST NUMBER: P1001949

CATALOG NUMBER: SA4XXDIP-B795D810UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	386.2	403.6	440.4	463.2	474.8
115°	435.5	447.4	480.9	506.0	513.5
117.5°	480.6	490.0	524.4	546.1	554.6
120°	525.3	531.6	561.9	584.8	591.8
122.5°	568.0	569.6	600.0	622.1	628.1
125°	607.5	609.5	634.6	657.3	664.5
127.5°	646.4	646.1	671.3	689.8	696.5
130°	682.8	682.4	701.8	721.9	728.3
132.5°	717.1	717.5	733.5	752.5	758.1
135°	750.4	749.6	760.2	778.8	786.8
137.5°	780.9	779.9	787.9	805.6	810.1
140°	810.7	811.2	813.7	829.9	836.1
142.5°	836.4	839.5	839.1	852.5	856.7
145°	863.9	865.1	865.1	872.3	878.1
147.5°	885.3	888.8	888.0	889.9	894.8
150°	909.0	910.9	910.1	910.1	910.9
152.5°	927.7	930.0	928.5	930.0	929.2
155°	946.0	946.8	944.5	947.6	945.3
157.5°	962.1	962.1	959.0	962.8	959.0
160°	975.8	973.5	972.8	977.3	972.8
162.5°	988.0	985.0	984.2	988.8	983.4
165°	998.0	994.1	994.1	1000.2	993.4
167.5°	1006.3	1002.5	1001.8	1008.6	1001.0
170°	1013.2	1008.6	1009.4	1015.5	1007.9
172.5°	1017.8	1013.2	1014.0	1020.1	1011.7
175°	1020.9	1016.3	1017.0	1023.9	1014.7
177.5°	1023.1	1017.8	1019.3	1025.4	1016.3
180°	1020.9	1020.9	1020.9	1020.9	1020.9

(END OF REPORT)