

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001955

Luminaire Tested: SA4XXDIP-B795D810UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001955
REPORT IS A COMBINATION OF REPORTS P996580 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B795D810UB2750-4F0-XX-W2A-F_3500K
Description: Define 4 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6615.0 lumens
Efficiency: N/A
Efficacy: 116.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 57
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001955

CATALOG NUMBER: SA4XXDIP-B795D810UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1001955

CATALOG NUMBER: SA4XXDIP-B795D810UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	84	84	84	71	71	71	58	58	58
1	98	94	90	86	91	87	84	81	74	72	69	62	60	59	51	50	49
2	89	82	76	71	82	76	71	66	65	61	57	55	52	49	45	43	41
3	82	72	65	59	75	67	60	55	57	52	48	48	45	42	40	37	35
4	75	64	56	50	69	59	52	47	51	45	41	43	39	36	36	33	30
5	69	57	49	43	63	53	46	40	45	40	35	39	34	31	32	29	26
6	63	51	43	37	58	48	40	35	41	35	31	35	30	27	29	26	23
7	58	46	38	32	54	43	36	31	37	31	27	32	27	24	27	23	21
8	54	42	34	29	50	39	32	27	34	28	24	29	25	21	24	21	18
9	50	38	31	26	47	36	29	24	31	26	22	27	22	19	23	19	17
10	47	35	28	23	44	33	26	22	29	23	20	25	20	17	21	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10929	10929	10929
5°	10938	10615	10627
10°	10845	10320	10247
15°	10690	9969	9820
20°	10491	9591	9376
25°	10268	9190	8898
30°	9998	8757	8374
35°	9719	8314	7867
40°	9427	7837	7328
45°	9122	7359	6824
50°	8785	6895	6266
55°	8417	6353	5711
60°	8041	5760	5134
65°	7611	5148	4484
70°	7117	4409	3786
75°	6374	3555	3032
80°	5433	2570	2133
85°	4221	1430	1149

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9122 cd/sqm

TEST NUMBER: P1001955

CATALOG NUMBER: SA4XXDIP-B795D810UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.3	1.9
10°-20°	355.9	5.4
20°-30°	523.8	7.9
30°-40°	608.9	9.2
40°-50°	608.8	9.2
50°-60°	532.5	8.0
60°-70°	395.3	6.0
70°-80°	224.3	3.4
80°-90°	66.4	1.0
90°-100°	34.0	0.5
100°-110°	224.1	3.4
110°-120°	428.0	6.5
120°-130°	543.4	8.2
130°-140°	581.3	8.8
140°-150°	543.6	8.2
150°-160°	438.3	6.6
160°-170°	282.7	4.3
170°-180°	97.4	1.5
0°-30°	1006.0	15.2
0°-40°	1614.9	24.4
0°-60°	2756.1	41.7
0°-90°	3442.1	52.0
90°-120°	686.2	10.4
90°-150°	2354.4	35.6
90°-180°	3173.0	48.0
0°-180°	6615.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1340	1340	1340	1340	1340	
5°	1339	1335	1323	1335	1333	127
15°	1275	1270	1254	1261	1258	359
25°	1154	1147	1132	1133	1129	531
35°	993	986	971	963	958	621
45°	811	803	786	774	771	625
55°	613	610	595	582	576	549
65°	416	410	400	389	383	411
75°	221	216	210	206	205	235
85°	58	58	56	56	55	62
90°	2	11	17	22	23	6
95°	42	16	17	22	22	52
105°	231	235	239	246	219	242
115°	431	433	432	434	434	424
125°	606	609	607	610	610	541
135°	752	751	754	755	757	579
145°	867	869	869	870	871	542
155°	950	951	949	952	950	438
165°	1002	998	998	1005	998	283
175°	1025	1021	1022	1028	1019	98
180°	1025	1025	1025	1025	1025	

TEST NUMBER: P1001955

CATALOG NUMBER: SA4XXDIP-B795D810UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1340.2	1340.2	1340.2	1340.2	1340.2
2.5°	1344.5	1341.3	1329.5	1340.2	1339.2
5°	1339.2	1334.9	1323.1	1334.9	1332.7
7.5°	1329.5	1325.2	1312.3	1322.0	1320.9
10°	1315.5	1311.2	1297.3	1305.9	1303.7
12.5°	1297.3	1293.0	1278.0	1287.6	1284.4
15°	1274.7	1270.4	1254.3	1260.8	1257.6
17.5°	1249.0	1243.6	1228.6	1232.9	1230.7
20°	1220.0	1214.6	1198.5	1201.7	1199.6
22.5°	1188.8	1181.3	1165.2	1171.6	1167.3
25°	1154.5	1146.9	1131.9	1133.0	1128.7
27.5°	1115.8	1108.3	1094.3	1092.2	1086.8
30°	1077.1	1068.5	1054.6	1050.3	1044.9
32.5°	1036.3	1028.8	1013.8	1008.4	1003.0
35°	993.4	985.9	970.8	963.3	957.9
37.5°	948.3	941.8	925.7	918.2	910.7
40°	904.2	895.6	879.5	868.8	863.4
42.5°	857.0	852.7	834.4	821.5	818.3
45°	810.8	803.3	786.1	774.3	771.1
47.5°	762.5	757.1	741.0	728.1	719.5
50°	713.1	708.8	693.7	678.7	672.3
52.5°	664.8	659.4	643.3	630.4	621.8
55°	613.2	610.0	594.9	582.1	575.6
57.5°	564.9	561.7	546.6	533.7	527.3
60°	514.4	509.0	495.1	485.4	480.0
62.5°	465.0	460.7	445.7	437.1	431.7
65°	415.6	410.2	399.5	388.8	383.4
67.5°	365.1	360.8	350.1	339.4	338.3
70°	319.0	311.4	302.8	294.3	291.0
72.5°	269.6	262.0	255.6	249.1	245.9
75°	221.2	215.9	210.5	206.2	205.1
77.5°	174.0	171.8	166.5	165.4	162.2
80°	132.1	128.9	126.7	124.6	123.5
82.5°	91.3	90.2	90.2	89.1	88.1
85°	58.0	58.0	55.8	55.8	54.8
87.5°	27.9	26.8	25.8	25.8	25.8
90°	2.3	10.7	16.9	21.5	23.0
92.5°	11.5	10.0	16.1	20.7	20.7
95°	42.2	16.1	16.9	21.5	22.2
97.5°	80.5	97.4	16.9	20.7	21.5
100°	125.8	139.6	33.7	20.7	21.5
102.5°	176.4	185.6	194.8	22.2	22.2
105°	230.8	235.4	239.3	246.2	218.6
107.5°	280.7	283.0	288.4	292.2	295.3
110°	331.3	333.6	338.2	339.7	342.0



TEST NUMBER: P1001955

CATALOG NUMBER: SA4XXDIP-B795D810UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	380.4	385.0	386.5	385.8	388.8
115°	431.0	433.3	432.5	434.1	434.1
117.5°	476.3	479.3	481.6	480.9	480.9
120°	522.3	525.3	524.6	526.1	524.6
122.5°	565.2	566.8	568.3	569.1	567.5
125°	605.9	608.9	607.4	609.7	610.5
127.5°	645.0	645.8	649.6	648.8	648.1
130°	682.6	683.3	685.6	686.4	686.4
132.5°	717.1	718.6	721.7	722.4	721.7
135°	751.6	750.8	753.9	755.4	757.0
137.5°	782.3	782.3	786.1	787.6	786.9
140°	812.2	813.7	815.2	817.5	818.3
142.5°	839.0	842.1	842.9	844.4	844.4
145°	866.6	868.9	868.9	869.7	871.2
147.5°	888.1	892.7	891.9	892.7	893.5
150°	911.9	914.9	914.2	914.2	914.9
152.5°	931.8	934.1	932.6	934.1	933.3
155°	950.2	951.0	948.7	951.8	949.5
157.5°	966.3	966.3	963.3	967.1	963.3
160°	980.1	977.8	977.1	981.7	977.1
162.5°	992.4	989.3	988.6	993.2	987.8
165°	1002.4	998.5	998.5	1004.7	997.8
167.5°	1010.8	1007.0	1006.2	1013.1	1005.4
170°	1017.7	1013.1	1013.9	1020.0	1012.3
172.5°	1022.3	1017.7	1018.5	1024.6	1016.2
175°	1025.4	1020.8	1021.5	1028.4	1019.2
177.5°	1027.7	1022.3	1023.8	1030.0	1020.8
180°	1025.4	1025.4	1025.4	1025.4	1025.4

(END OF REPORT)