

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000547

Luminaire Tested: SA4XXDIP-B1020D1035UB35-4F0-XX-W2A-D4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000547
REPORT IS A COMBINATION OF REPORTS P995157 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B1020D1035UB35-4F0-XX-W2A-D4
Description: Define 4 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7891.4 lumens
Efficiency: N/A
Efficacy: 104.8 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 75.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000547

CATALOG NUMBER: SA4XXDIP-B1020D1035UB35-4F0-XX-W2A-D4

Luminous Intensity Polar Plot



TEST NUMBER: P1000547

CATALOG NUMBER: SA4XXDIP-B1020D1035UB35-4F0-XX-W2A-D4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	55	55	55
1	97	92	88	84	89	85	81	78	71	69	66	59	57	55	47	46	45
2	88	80	73	68	80	73	68	63	62	58	54	51	48	45	41	39	37
3	80	70	62	56	73	64	57	52	54	49	45	45	41	38	36	33	31
4	73	61	53	47	66	57	49	44	48	42	38	40	35	32	32	29	26
5	67	55	46	40	61	50	43	37	43	37	32	35	31	28	29	25	23
6	61	49	40	34	56	45	38	32	38	32	28	32	27	24	26	23	20
7	57	44	36	30	52	41	33	28	35	29	25	29	24	21	24	20	18
8	52	40	32	26	48	37	30	25	32	26	22	26	22	19	22	18	16
9	49	36	29	23	45	34	27	22	29	23	19	24	20	17	20	17	14
10	46	33	26	21	42	31	24	20	27	21	17	22	18	15	19	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10050	10050	10050
5°	10078	9788	9806
10°	10012	9595	9568
15°	9919	9379	9300
20°	9779	9145	9040
25°	9623	8887	8759
30°	9454	8630	8472
35°	9263	8368	8217
40°	9108	8117	7953
45°	8881	7881	7720
50°	8689	7613	7474
55°	8487	7355	7190
60°	8177	7033	6923
65°	7834	6686	6602
70°	7420	6291	6231
75°	6841	5850	5877
80°	6186	5403	5507
85°	5319	4951	5207

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8881 cd/sqm

TEST NUMBER: P1000547

CATALOG NUMBER: SA4XXDIP-B1020D1035UB35-4F0-XX-W2A-D4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.8	1.5
10°-20°	334.6	4.2
20°-30°	505.9	6.4
30°-40°	612.0	7.8
40°-50°	647.0	8.2
50°-60°	608.9	7.7
60°-70°	505.3	6.4
70°-80°	354.6	4.5
80°-90°	201.8	2.6
90°-100°	494.4	6.3
100°-110°	851.5	10.8
110°-120°	739.6	9.4
120°-130°	604.9	7.7
130°-140°	491.3	6.2
140°-150°	367.1	4.7
150°-160°	256.0	3.2
160°-170°	150.6	1.9
170°-180°	49.0	0.6
0°-30°	957.3	12.1
0°-40°	1569.3	19.9
0°-60°	2825.3	35.8
0°-90°	3887.0	49.3
90°-120°	2085.4	26.4
90°-150°	3548.7	45.0
90°-180°	4004.0	50.7
0°-180°	7891.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1232	1232	1232	1232	1232	
5°	1234	1230	1220	1231	1230	117
15°	1183	1184	1180	1192	1191	333
25°	1082	1090	1094	1110	1111	498
35°	947	963	977	996	1001	593
45°	789	816	842	865	872	610
55°	618	647	689	716	725	551
65°	428	472	519	553	564	424
75°	237	288	346	385	398	252
85°	73	131	193	235	248	76
90°	23	85	154	197	208	17
95°	51	167	929	558	412	50
105°	128	208	742	1528	1533	138
115°	213	277	646	1211	1446	212
125°	290	343	616	1014	1143	259
135°	341	406	585	877	1000	264
145°	392	447	570	719	795	246
155°	444	479	554	627	654	205
165°	483	498	531	562	571	137
175°	504	505	509	516	514	48
180°	505	505	505	505	505	

TEST NUMBER: P1000547

CATALOG NUMBER: SA4XXDIP-B1020D1035UB35-4F0-XX-W2A-D4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1232.5	1232.5	1232.5	1232.5	1232.5
2.5°	1238.0	1233.9	1222.8	1232.5	1231.1
5°	1233.9	1229.7	1220.0	1231.1	1229.7
7.5°	1225.6	1222.8	1214.5	1227.0	1225.6
10°	1214.5	1213.1	1206.2	1218.7	1217.3
12.5°	1199.3	1199.3	1195.2	1206.2	1206.2
15°	1182.8	1184.2	1180.0	1192.4	1191.1
17.5°	1160.7	1164.8	1163.5	1175.9	1174.5
20°	1137.2	1141.4	1142.8	1156.6	1156.6
22.5°	1111.0	1116.5	1119.3	1133.1	1135.9
25°	1082.0	1090.3	1094.5	1109.6	1111.0
27.5°	1050.3	1062.7	1068.2	1082.0	1083.4
30°	1018.5	1029.6	1039.3	1054.4	1057.2
32.5°	984.0	997.8	1008.9	1026.8	1029.6
35°	946.8	963.3	977.1	996.5	1000.6
37.5°	909.5	928.8	945.4	964.7	968.9
40°	873.6	891.6	910.9	931.6	937.1
42.5°	832.2	852.9	876.4	899.9	904.0
45°	789.4	815.7	841.9	865.4	872.3
47.5°	749.4	775.6	806.0	829.5	837.7
50°	705.3	735.6	766.0	793.6	801.9
52.5°	661.1	691.5	727.3	754.9	763.2
55°	618.3	647.3	688.7	716.3	724.6
57.5°	570.0	605.9	645.9	679.0	685.9
60°	523.1	559.0	604.5	636.2	647.3
62.5°	477.5	517.6	563.1	594.8	605.9
65°	427.8	472.0	518.9	553.4	564.5
67.5°	380.9	427.8	477.5	512.0	523.1
70°	332.6	379.5	432.0	469.2	478.9
72.5°	285.7	334.0	390.6	426.5	437.5
75°	237.4	288.5	346.4	385.1	397.5
77.5°	191.8	245.7	306.4	345.0	358.8
80°	150.4	205.6	266.4	307.8	318.8
82.5°	109.0	167.0	227.7	270.5	282.9
85°	73.1	131.1	193.2	234.6	248.4
87.5°	45.5	102.1	162.9	202.9	215.3
90°	23.1	85.2	154.5	196.6	208.5
92.5°	34.6	145.4	517.5	295.6	268.3
95°	50.7	166.8	929.1	557.8	412.0
97.5°	71.2	170.8	978.8	967.1	743.2
100°	90.6	180.2	903.0	1273.9	1062.1
102.5°	110.5	192.4	811.7	1462.1	1341.1
105°	128.5	208.3	742.3	1527.8	1533.3
107.5°	151.4	226.0	694.7	1498.5	1620.4
110°	172.8	242.3	670.3	1410.8	1615.5

TEST NUMBER: P1000547

CATALOG NUMBER: SA4XXDIP-B1020D1035UB35-4F0-XX-W2A-D4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	193.3	260.0	654.5	1305.2	1548.6
115°	212.8	277.3	645.6	1211.0	1446.0
117.5°	234.6	294.6	637.7	1134.2	1346.8
120°	255.1	309.8	630.8	1079.9	1263.0
122.5°	274.9	326.0	622.9	1042.6	1195.2
125°	290.4	342.6	616.3	1014.4	1143.2
127.5°	306.3	360.5	607.5	985.8	1108.5
130°	317.8	376.5	599.6	954.5	1076.5
132.5°	330.7	391.4	593.1	918.8	1042.8
135°	341.3	405.8	585.2	877.3	999.7
137.5°	353.2	416.8	579.7	834.6	950.7
140°	366.1	428.2	574.6	793.0	899.2
142.5°	378.6	438.7	571.8	755.2	844.6
145°	391.5	446.7	569.8	719.1	795.0
147.5°	406.4	455.6	566.8	687.8	748.4
150°	420.3	464.0	563.8	664.1	708.8
152.5°	431.8	472.0	558.9	645.2	679.0
155°	443.7	479.0	553.9	627.3	654.2
157.5°	455.6	485.4	548.9	610.5	631.3
160°	466.6	490.8	543.0	593.6	610.5
162.5°	476.5	495.4	537.0	577.2	590.6
165°	483.4	498.3	531.1	562.3	570.8
167.5°	491.4	500.8	525.1	549.4	554.9
170°	496.3	502.8	519.2	536.6	540.0
172.5°	501.3	504.3	513.2	525.1	525.1
175°	504.3	505.3	509.2	516.2	514.2
177.5°	506.3	505.3	506.3	509.7	506.3
180°	505.3	505.3	505.3	505.3	505.3

(END OF REPORT)