

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000606

Luminaire Tested: SA4XXDIP-B1020D1205UB35-4F0-XX-W2A-D1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000606
REPORT IS A COMBINATION OF REPORTS P995216 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B1020D1205UB35-4F0-XX-W2A-D1
Description: Define 4 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8389.0 lumens
Efficiency: N/A
Efficacy: 102.6 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 81.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000606

CATALOG NUMBER: SA4XXDIP-B1020D1205UB35-4F0-XX-W2A-D1

Luminous Intensity Polar Plot



TEST NUMBER: P1000606

CATALOG NUMBER: SA4XXDIP-B1020D1205UB35-4F0-XX-W2A-D1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	98	98	98	98	81	81	81	66	66	66	53	53	53
1	96	91	87	83	88	84	80	77	70	67	65	57	55	53	45	44	43
2	87	79	73	67	79	73	67	62	61	56	53	49	46	44	39	37	35
3	79	69	62	55	72	64	57	52	53	48	44	43	40	37	34	32	30
4	72	61	53	47	66	56	49	43	47	41	37	38	34	31	31	28	25
5	66	54	46	40	60	50	43	37	42	36	32	34	30	27	27	24	22
6	61	48	40	34	56	45	37	32	38	32	28	31	27	23	25	21	19
7	56	44	36	30	51	40	33	28	34	28	24	28	24	20	23	19	17
8	52	40	32	26	48	37	30	25	31	25	21	26	21	18	21	17	15
9	48	36	28	23	44	33	27	22	28	23	19	24	19	16	19	16	13
10	45	33	26	21	41	31	24	20	26	21	17	22	18	15	18	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10050	10050	10050
5°	10078	9788	9806
10°	10012	9595	9568
15°	9919	9379	9300
20°	9779	9145	9040
25°	9623	8887	8759
30°	9454	8630	8472
35°	9263	8368	8217
40°	9108	8117	7953
45°	8881	7881	7720
50°	8689	7613	7474
55°	8487	7355	7190
60°	8177	7033	6923
65°	7834	6686	6602
70°	7420	6291	6231
75°	6841	5850	5877
80°	6186	5403	5507
85°	5319	4951	5207

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8881 cd/sqm

TEST NUMBER: P1000606

CATALOG NUMBER: SA4XXDIP-B1020D1205UB35-4F0-XX-W2A-D1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.8	1.4
10°-20°	334.6	4.0
20°-30°	505.9	6.0
30°-40°	612.0	7.3
40°-50°	647.0	7.7
50°-60°	608.9	7.3
60°-70°	505.3	6.0
70°-80°	354.6	4.2
80°-90°	203.1	2.4
90°-100°	217.3	2.6
100°-110°	382.5	4.6
110°-120°	559.3	6.7
120°-130°	692.9	8.3
130°-140°	755.2	9.0
140°-150°	731.0	8.7
150°-160°	612.4	7.3
160°-170°	407.5	4.9
170°-180°	142.7	1.7
0°-30°	957.3	11.4
0°-40°	1569.3	18.7
0°-60°	2825.3	33.7
0°-90°	3888.3	46.4
90°-120°	1159.1	13.8
90°-150°	3338.2	39.8
90°-180°	4501.0	53.7
0°-180°	8389.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1232	1232	1232	1232	1232	
5°	1234	1230	1220	1231	1230	117
15°	1183	1184	1180	1192	1191	333
25°	1082	1090	1094	1110	1111	498
35°	947	963	977	996	1001	593
45°	789	816	842	865	872	610
55°	618	647	689	716	725	551
65°	428	472	519	553	564	424
75°	237	288	346	385	398	252
85°	73	131	193	235	248	76
90°	26	94	162	209	223	20
95°	88	144	209	249	262	90
105°	284	313	369	407	421	302
115°	517	529	571	600	609	510
125°	746	745	778	802	808	665
135°	958	965	974	994	999	741
145°	1162	1165	1166	1173	1175	727
155°	1329	1329	1328	1333	1328	612
165°	1447	1444	1441	1448	1444	408
175°	1506	1500	1498	1507	1498	143
180°	1508	1508	1508	1508	1508	

TEST NUMBER: P1000606

CATALOG NUMBER: SA4XXDIP-B1020D1205UB35-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1232.5	1232.5	1232.5	1232.5	1232.5
2.5°	1238.0	1233.9	1222.8	1232.5	1231.1
5°	1233.9	1229.7	1220.0	1231.1	1229.7
7.5°	1225.6	1222.8	1214.5	1227.0	1225.6
10°	1214.5	1213.1	1206.2	1218.7	1217.3
12.5°	1199.3	1199.3	1195.2	1206.2	1206.2
15°	1182.8	1184.2	1180.0	1192.4	1191.1
17.5°	1160.7	1164.8	1163.5	1175.9	1174.5
20°	1137.2	1141.4	1142.8	1156.6	1156.6
22.5°	1111.0	1116.5	1119.3	1133.1	1135.9
25°	1082.0	1090.3	1094.5	1109.6	1111.0
27.5°	1050.3	1062.7	1068.2	1082.0	1083.4
30°	1018.5	1029.6	1039.3	1054.4	1057.2
32.5°	984.0	997.8	1008.9	1026.8	1029.6
35°	946.8	963.3	977.1	996.5	1000.6
37.5°	909.5	928.8	945.4	964.7	968.9
40°	873.6	891.6	910.9	931.6	937.1
42.5°	832.2	852.9	876.4	899.9	904.0
45°	789.4	815.7	841.9	865.4	872.3
47.5°	749.4	775.6	806.0	829.5	837.7
50°	705.3	735.6	766.0	793.6	801.9
52.5°	661.1	691.5	727.3	754.9	763.2
55°	618.3	647.3	688.7	716.3	724.6
57.5°	570.0	605.9	645.9	679.0	685.9
60°	523.1	559.0	604.5	636.2	647.3
62.5°	477.5	517.6	563.1	594.8	605.9
65°	427.8	472.0	518.9	553.4	564.5
67.5°	380.9	427.8	477.5	512.0	523.1
70°	332.6	379.5	432.0	469.2	478.9
72.5°	285.7	334.0	390.6	426.5	437.5
75°	237.4	288.5	346.4	385.1	397.5
77.5°	191.8	245.7	306.4	345.0	358.8
80°	150.4	205.6	266.4	307.8	318.8
82.5°	109.0	167.0	227.7	270.5	282.9
85°	73.1	131.1	193.2	234.6	248.4
87.5°	45.5	102.1	162.9	202.9	215.3
90°	25.6	93.6	162.3	209.4	222.7
92.5°	51.0	114.5	179.7	221.8	234.0
95°	87.9	144.0	208.7	249.4	261.9
97.5°	128.6	177.9	243.8	284.4	296.8
100°	178.5	219.0	283.3	323.0	332.6
102.5°	232.1	263.6	325.4	364.8	377.0
105°	284.1	312.9	368.7	406.6	421.1
107.5°	341.3	365.9	415.4	454.6	463.1
110°	398.2	419.9	467.0	496.4	511.0

TEST NUMBER: P1000606

CATALOG NUMBER: SA4XXDIP-B1020D1205UB35-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	457.5	474.0	517.3	547.6	558.7
115°	516.8	529.2	571.0	600.2	608.7
117.5°	573.9	582.2	622.4	647.8	655.4
120°	629.6	638.4	675.0	696.8	710.1
122.5°	689.1	690.3	726.4	750.5	754.3
125°	746.0	744.6	778.0	801.9	807.8
127.5°	798.5	800.6	825.9	848.4	856.9
130°	853.1	855.3	877.3	899.8	903.5
132.5°	910.2	911.3	926.6	947.8	954.9
135°	957.9	964.9	974.5	994.3	999.1
137.5°	1012.7	1014.8	1022.6	1039.8	1047.9
140°	1067.5	1068.5	1069.9	1086.6	1092.3
142.5°	1116.3	1118.6	1116.0	1131.2	1136.7
145°	1161.7	1165.0	1166.2	1173.3	1175.3
147.5°	1208.4	1212.8	1211.7	1211.9	1216.2
150°	1250.4	1253.6	1253.6	1253.6	1252.5
152.5°	1288.6	1291.0	1292.1	1295.6	1292.1
155°	1329.4	1329.4	1328.3	1332.9	1328.3
157.5°	1364.4	1362.1	1362.1	1365.6	1362.1
160°	1394.7	1393.6	1392.4	1395.9	1390.1
162.5°	1422.7	1419.2	1418.1	1425.1	1419.2
165°	1447.2	1443.7	1441.4	1448.4	1443.7
167.5°	1467.1	1462.4	1462.4	1469.4	1462.4
170°	1483.4	1477.5	1478.7	1485.7	1477.5
172.5°	1495.0	1490.4	1490.4	1498.5	1490.4
175°	1505.5	1499.7	1498.5	1506.7	1498.5
177.5°	1510.2	1504.4	1504.4	1512.5	1503.2
180°	1507.9	1507.9	1507.9	1507.9	1507.9

(END OF REPORT)