

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000607

Luminaire Tested: SA4XXDIP-B1020D1205UB35-4F0-XX-W2A-D4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000607
REPORT IS A COMBINATION OF REPORTS P995217 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B1020D1205UB35-4F0-XX-W2A-D4
Description: Define 4 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8536.6 lumens
Efficiency: N/A
Efficacy: 104.4 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 81.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000607

CATALOG NUMBER: SA4XXDIP-B1020D1205UB35-4F0-XX-W2A-D4

Luminous Intensity Polar Plot



TEST NUMBER: P1000607

CATALOG NUMBER: SA4XXDIP-B1020D1205UB35-4F0-XX-W2A-D4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52
1	96	91	87	83	88	84	80	77	69	67	64	56	55	53	45	43	42
2	87	79	73	67	79	73	67	62	60	56	53	49	46	43	39	37	35
3	79	69	62	55	72	63	57	51	53	48	44	43	39	36	34	31	29
4	72	61	53	47	66	56	49	43	47	41	37	38	34	31	30	27	25
5	66	54	46	40	60	50	42	37	42	36	32	34	30	26	27	24	21
6	61	48	40	34	55	45	37	32	37	32	27	31	26	23	24	21	19
7	56	44	35	30	51	40	33	28	34	28	24	28	23	20	22	19	17
8	52	39	32	26	47	36	29	25	31	25	21	25	21	18	20	17	15
9	48	36	28	23	44	33	26	22	28	23	19	23	19	16	19	16	13
10	45	33	26	21	41	30	24	19	26	21	17	21	17	14	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10050	10050	10050
5°	10078	9788	9806
10°	10012	9595	9568
15°	9919	9379	9300
20°	9779	9145	9040
25°	9623	8887	8759
30°	9454	8630	8472
35°	9263	8368	8217
40°	9108	8117	7953
45°	8881	7881	7720
50°	8689	7613	7474
55°	8487	7355	7190
60°	8177	7033	6923
65°	7834	6686	6602
70°	7420	6291	6231
75°	6841	5850	5877
80°	6186	5403	5507
85°	5319	4951	5207

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8881 cd/sqm

TEST NUMBER: P1000607

CATALOG NUMBER: SA4XXDIP-B1020D1205UB35-4F0-XX-W2A-D4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.8	1.4
10°-20°	334.6	3.9
20°-30°	505.9	5.9
30°-40°	612.0	7.2
40°-50°	647.0	7.6
50°-60°	608.9	7.1
60°-70°	505.3	5.9
70°-80°	354.6	4.2
80°-90°	202.2	2.4
90°-100°	560.0	6.6
100°-110°	985.0	11.5
110°-120°	858.6	10.1
120°-130°	704.8	8.3
130°-140°	574.8	6.7
140°-150°	430.8	5.0
150°-160°	300.8	3.5
160°-170°	176.9	2.1
170°-180°	57.5	0.7
0°-30°	957.3	11.2
0°-40°	1569.3	18.4
0°-60°	2825.3	33.1
0°-90°	3887.4	45.5
90°-120°	2403.6	28.2
90°-150°	4114.0	48.2
90°-180°	4649.0	54.5
0°-180°	8536.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1232	1232	1232	1232	1232	
5°	1234	1230	1220	1231	1230	117
15°	1183	1184	1180	1192	1191	333
25°	1082	1090	1094	1110	1111	498
35°	947	963	977	996	1001	593
45°	789	816	842	865	872	610
55°	618	647	689	716	725	551
65°	428	472	519	553	564	424
75°	237	288	346	385	398	252
85°	73	131	193	235	248	76
90°	23	87	158	200	212	18
95°	56	185	1071	628	454	56
105°	149	238	856	1773	1778	159
115°	249	322	747	1406	1681	247
125°	340	402	717	1180	1330	304
135°	400	476	685	1025	1167	310
145°	460	525	670	843	932	289
155°	521	563	651	737	769	240
165°	568	586	624	661	671	160
175°	592	594	598	606	604	56
180°	594	594	594	594	594	

TEST NUMBER: P1000607

CATALOG NUMBER: SA4XXDIP-B1020D1205UB35-4F0-XX-W2A-D4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1232.5	1232.5	1232.5	1232.5	1232.5
2.5°	1238.0	1233.9	1222.8	1232.5	1231.1
5°	1233.9	1229.7	1220.0	1231.1	1229.7
7.5°	1225.6	1222.8	1214.5	1227.0	1225.6
10°	1214.5	1213.1	1206.2	1218.7	1217.3
12.5°	1199.3	1199.3	1195.2	1206.2	1206.2
15°	1182.8	1184.2	1180.0	1192.4	1191.1
17.5°	1160.7	1164.8	1163.5	1175.9	1174.5
20°	1137.2	1141.4	1142.8	1156.6	1156.6
22.5°	1111.0	1116.5	1119.3	1133.1	1135.9
25°	1082.0	1090.3	1094.5	1109.6	1111.0
27.5°	1050.3	1062.7	1068.2	1082.0	1083.4
30°	1018.5	1029.6	1039.3	1054.4	1057.2
32.5°	984.0	997.8	1008.9	1026.8	1029.6
35°	946.8	963.3	977.1	996.5	1000.6
37.5°	909.5	928.8	945.4	964.7	968.9
40°	873.6	891.6	910.9	931.6	937.1
42.5°	832.2	852.9	876.4	899.9	904.0
45°	789.4	815.7	841.9	865.4	872.3
47.5°	749.4	775.6	806.0	829.5	837.7
50°	705.3	735.6	766.0	793.6	801.9
52.5°	661.1	691.5	727.3	754.9	763.2
55°	618.3	647.3	688.7	716.3	724.6
57.5°	570.0	605.9	645.9	679.0	685.9
60°	523.1	559.0	604.5	636.2	647.3
62.5°	477.5	517.6	563.1	594.8	605.9
65°	427.8	472.0	518.9	553.4	564.5
67.5°	380.9	427.8	477.5	512.0	523.1
70°	332.6	379.5	432.0	469.2	478.9
72.5°	285.7	334.0	390.6	426.5	437.5
75°	237.4	288.5	346.4	385.1	397.5
77.5°	191.8	245.7	306.4	345.0	358.8
80°	150.4	205.6	266.4	307.8	318.8
82.5°	109.0	167.0	227.7	270.5	282.9
85°	73.1	131.1	193.2	234.6	248.4
87.5°	45.5	102.1	162.9	202.9	215.3
90°	23.3	86.6	157.6	200.0	212.2
92.5°	37.0	158.8	585.6	318.0	284.1
95°	56.4	184.8	1070.6	627.9	454.4
97.5°	80.7	190.7	1130.2	1110.1	844.9
100°	103.8	202.8	1042.6	1471.8	1221.3
102.5°	127.2	218.1	936.6	1694.4	1550.3
105°	148.9	237.7	856.2	1773.0	1777.6
107.5°	175.7	259.2	801.5	1739.8	1881.3
110°	201.1	279.4	773.8	1638.2	1876.8

TEST NUMBER: P1000607

CATALOG NUMBER: SA4XXDIP-B1020D1205UB35-4F0-XX-W2A-D4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	225.5	300.8	756.4	1515.6	1799.7
115°	248.6	322.2	747.2	1406.1	1680.6
117.5°	274.2	343.2	739.1	1317.4	1565.2
120°	298.5	362.0	732.2	1254.9	1468.3
122.5°	321.8	381.8	724.2	1212.4	1390.0
125°	340.2	401.8	717.4	1180.4	1330.4
127.5°	358.9	422.8	708.2	1148.2	1290.8
130°	372.6	441.9	700.1	1112.8	1254.6
132.5°	387.8	459.4	693.4	1072.0	1216.2
135°	400.5	476.4	685.4	1024.6	1167.1
137.5°	414.5	489.5	679.9	975.8	1111.0
140°	429.7	502.9	674.6	928.1	1051.6
142.5°	444.6	515.2	671.8	884.7	988.7
145°	459.8	524.8	669.5	843.4	931.7
147.5°	477.2	535.4	666.0	807.9	878.1
150°	493.6	545.2	662.5	780.2	832.7
152.5°	507.3	554.6	656.6	758.1	797.7
155°	521.3	562.8	650.8	737.1	768.6
157.5°	535.3	570.3	645.0	717.2	741.8
160°	548.2	576.7	638.0	697.4	717.3
162.5°	559.8	582.0	631.0	678.2	693.9
165°	568.0	585.5	624.0	660.7	670.6
167.5°	577.3	588.4	617.0	645.6	652.0
170°	583.1	590.8	610.0	630.4	634.5
172.5°	589.0	592.4	603.0	617.0	617.0
175°	592.5	593.6	598.3	606.5	604.1
177.5°	594.8	593.6	594.8	598.9	594.8
180°	593.6	593.6	593.6	593.6	593.6

(END OF REPORT)