

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P997610

Luminaire Tested: SA2XXDP-B485DB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P997610
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-10)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDP-B485DB2750-4F0-XX-W2A-F_4000K
Description: Define 2 Direct Recessed with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1957.0 lumens
Efficiency: N/A
Efficacy: 81.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 24
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P997610

CATALOG NUMBER: SA2XXDP-B485DB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P997610

CATALOG NUMBER: SA2XXDP-B485DB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102
1	109	104	100	96	106	102	98	95	98	95	92	94	91	89	90	88	86
2	99	91	85	79	97	89	83	78	86	81	76	83	78	74	80	76	73
3	91	80	72	66	88	79	71	65	76	69	64	73	68	63	71	66	62
4	83	71	63	56	81	70	62	56	68	61	55	65	59	54	63	58	54
5	77	64	55	49	75	63	55	48	61	53	48	59	52	47	57	51	47
6	71	58	49	43	69	57	48	42	55	48	42	53	47	42	52	46	41
7	66	52	44	38	64	52	43	38	50	43	37	49	42	37	47	41	37
8	61	48	40	34	60	47	39	34	46	39	33	45	38	33	44	38	33
9	57	44	36	30	56	43	36	30	42	35	30	41	35	30	40	34	30
10	54	41	33	28	53	40	33	28	39	32	27	38	32	27	37	32	27

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12176	12176	12176
5°	12222	12046	12118
10°	12150	11923	11983
15°	11999	11770	11757
20°	11787	11537	11525
25°	11575	11251	11251
30°	11301	10991	10896
35°	11048	10677	10520
40°	10729	10363	10164
45°	10414	10051	9803
50°	10072	9727	9380
55°	9717	9347	9002
60°	9320	8899	8570
65°	8892	8450	8060
70°	8354	7910	7530
75°	7602	7284	7101
80°	6746	6536	6199
85°	5503	5231	4704

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10414 cd/sqm

TEST NUMBER: P997610

CATALOG NUMBER: SA2XXDP-B485DB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.4	3.7
10°-20°	203.7	10.4
20°-30°	299.3	15.3
30°-40°	347.7	17.8
40°-50°	347.2	17.7
50°-60°	302.8	15.5
60°-70°	223.8	11.4
70°-80°	126.6	6.5
80°-90°	33.4	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	575.4	29.4
0°-40°	923.1	47.2
0°-60°	1573.1	80.4
0°-90°	1957.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1957.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	769	769	769	769	769	
5°	769	766	758	764	763	73
15°	732	728	718	721	717	206
25°	663	657	644	646	644	305
35°	572	564	552	548	544	357
45°	465	460	449	441	438	359
55°	352	348	339	330	326	315
65°	237	233	226	219	215	235
75°	124	123	119	115	116	133
85°	30	30	29	27	26	36
90°	0	0	0	0	0	

TEST NUMBER: P997610

CATALOG NUMBER: SA2XXDP-B485DB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	769.2	769.2	769.2	769.2	769.2
2.5°	773.7	770.0	761.8	769.2	767.7
5°	769.2	766.3	758.1	764.0	762.6
7.5°	764.0	759.6	751.5	757.4	755.9
10°	755.9	750.7	741.8	747.8	745.5
12.5°	744.8	740.4	731.5	735.2	733.7
15°	732.2	727.8	718.2	721.1	717.4
17.5°	716.7	712.3	702.6	706.3	702.6
20°	699.7	695.2	684.9	687.1	684.2
22.5°	682.7	676.0	666.4	666.4	664.9
25°	662.7	656.8	644.2	645.7	644.2
27.5°	640.5	635.3	625.7	623.5	619.8
30°	618.3	612.4	601.3	599.1	596.1
32.5°	594.7	590.2	578.4	574.0	571.0
35°	571.7	564.3	552.5	548.1	544.4
37.5°	545.8	539.2	527.4	522.2	518.5
40°	519.2	513.3	501.5	494.8	491.9
42.5°	493.3	487.4	475.6	468.2	463.7
45°	465.2	460.0	449.0	440.8	437.9
47.5°	437.9	432.7	420.8	412.7	408.3
50°	409.0	405.3	395.0	384.6	380.9
52.5°	380.9	375.7	366.1	358.0	352.8
55°	352.1	347.6	338.7	329.9	326.2
57.5°	323.2	319.5	309.9	301.0	298.1
60°	294.4	291.4	281.1	272.9	270.7
62.5°	266.3	261.1	253.7	246.3	243.3
65°	237.4	233.0	225.6	218.9	215.2
67.5°	207.8	204.1	197.5	192.3	189.3
70°	180.5	177.5	170.9	165.7	162.7
72.5°	152.4	149.4	145.7	140.5	138.3
75°	124.3	122.8	119.1	114.6	116.1
77.5°	99.1	96.2	94.7	92.5	90.2
80°	74.0	73.2	71.7	69.5	68.0
82.5°	50.3	50.3	49.6	46.6	46.6
85°	30.3	29.6	28.8	26.6	25.9
87.5°	13.3	11.8	10.4	8.1	7.4
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P997610

CATALOG NUMBER: SA2XXDP-B485DB2750-4F0-XX-W2A-F_4000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	19.97	21.58	20.33	21.89	22.20	19.52	21.13	19.89	21.45	21.76
	3H	21.72	23.17	22.09	23.50	23.86	21.23	22.68	21.60	23.01	23.37
	4H	22.36	23.73	22.76	24.08	24.46	21.87	23.24	22.27	23.58	23.96
	6H	22.83	24.10	23.24	24.47	24.86	22.33	23.60	22.74	23.96	24.35
	8H	22.97	24.19	23.40	24.57	24.97	22.47	23.68	22.90	24.07	24.47
	12H	23.07	24.23	23.49	24.61	25.04	22.55	23.71	22.98	24.09	24.52
4H	2H	20.53	21.90	20.92	22.24	22.62	20.17	21.54	20.57	21.89	22.27
	3H	22.50	23.65	22.91	24.05	24.45	22.10	23.24	22.50	23.64	24.04
	4H	23.28	24.31	23.71	24.73	25.16	22.85	23.89	23.29	24.30	24.74
	6H	23.88	24.78	24.33	25.22	25.68	23.44	24.35	23.90	24.79	25.24
	8H	24.06	24.91	24.53	25.35	25.82	23.63	24.47	24.09	24.91	25.38
	12H	24.20	24.96	24.68	25.43	25.90	23.74	24.50	24.22	24.98	25.45
8H	4H	23.55	24.40	24.01	24.84	25.31	23.18	24.02	23.64	24.47	24.93
	6H	24.27	24.97	24.76	25.46	25.93	23.88	24.59	24.38	25.08	25.55
	8H	24.53	25.16	25.04	25.66	26.15	24.13	24.76	24.64	25.27	25.76
	12H	24.73	25.28	25.23	25.77	26.34	24.31	24.87	24.82	25.36	25.92
12H	4H	23.58	24.34	24.06	24.81	25.28	23.21	23.97	23.69	24.45	24.92
	6H	24.31	24.94	24.82	25.45	25.94	23.94	24.57	24.45	25.08	25.57
	8H	24.63	25.18	25.13	25.67	26.24	24.25	24.80	24.75	25.30	25.86

END OF REPORT

FIELD PERFORMANCE MAY DIFFER FROM LABORATORY PERFORMANCE

7 of 7