

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P997631

Luminaire Tested: SA2XXDP-B675DB2750-4F0-XX-W2A-A_5000K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P997631
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-19)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDP-B675DB2750-4F0-XX-W2A-A_5000K
Description: Define 2 Direct Recessed with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2832.0 lumens
Efficiency: N/A
Efficacy: 78.9 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 35.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P997631

CATALOG NUMBER: SA2XXDP-B675DB2750-4F0-XX-W2A-A_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P997631

CATALOG NUMBER: SA2XXDP-B675DB2750-4F0-XX-W2A-A_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	110	106	102	98	107	103	100	97	99	96	94	95	93	91	92	90	88	86		
2	101	94	87	82	98	92	86	81	88	83	79	85	81	78	82	79	76	74		
3	93	83	76	70	90	82	75	69	79	73	68	76	71	67	74	69	66	64		
4	86	75	66	60	83	73	66	60	71	64	59	69	63	58	66	62	58	55		
5	79	67	59	53	77	66	58	52	64	57	52	62	56	51	60	55	51	49		
6	74	61	53	47	72	60	52	46	58	51	46	57	51	46	55	50	45	43		
7	69	56	48	42	67	55	47	42	54	46	41	52	46	41	51	45	41	39		
8	64	51	43	38	63	51	43	38	49	42	37	48	42	37	47	41	37	35		
9	60	47	39	34	59	47	39	34	46	39	34	45	38	34	44	38	34	32		
10	56	44	36	31	55	43	36	31	42	36	31	41	35	31	41	35	31	29		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	20318	20318	20318	20318
5°	20412	22780	20490	18122
10°	20219	26103	20346	15685
15°	19773	28877	20049	13856
20°	19512	28436	19512	12631
25°	18938	25641	19024	11856
30°	17962	21190	18304	11289
35°	17102	15444	17388	10887
40°	16105	12334	16289	10662
45°	14864	10779	15106	10358
50°	13800	10131	13825	10156
55°	12579	9339	12662	9883
60°	11277	8557	11432	9463
65°	10124	7798	10311	9053
70°	8997	7076	9224	8446
75°	7724	6275	8024	7480
80°	6299	5397	6746	6025
85°	4668	4831	5013	3578

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 155°

Vertical Angle: 45°

Luminance: 26525 cd/sqm

TEST NUMBER: P997631

CATALOG NUMBER: SA2XXDP-B675DB2750-4F0-XX-W2A-A_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.3	4.3
10°-20°	355.8	12.6
20°-30°	516.4	18.2
30°-40°	544.4	19.2
40°-50°	481.8	17.0
50°-60°	384.7	13.6
60°-70°	261.3	9.2
70°-80°	133.7	4.7
80°-90°	31.6	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	994.6	35.1
0°-40°	1539.0	54.3
0°-60°	2405.4	84.9
0°-90°	2832.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2832.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1284	1284	1284	1284	1284	
5°	1285	1434	1290	1140	1285	122
15°	1207	1762	1223	846	1207	341
25°	1084	1468	1089	679	1084	496
35°	885	799	900	563	885	554
45°	664	482	675	463	664	515
55°	456	338	459	358	456	407
65°	270	208	275	242	270	269
75°	126	103	131	122	126	136
85°	26	27	28	20	26	31
90°	0	0	0	0	0	

TEST NUMBER: P997631

CATALOG NUMBER: SA2XXDP-B675DB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6
2.5°	1290.5	1293.5	1298.4	1299.4	1309.2	1317.1	1326.0	1326.0	1329.0	1328.0	1320.1
5°	1284.6	1293.5	1306.3	1317.1	1334.9	1342.8	1354.6	1363.5	1371.4	1377.3	1376.3
7.5°	1274.7	1290.5	1309.2	1330.0	1353.6	1367.5	1384.2	1400.0	1410.9	1420.7	1427.6
10°	1257.9	1284.6	1310.2	1337.9	1368.4	1387.2	1406.9	1427.6	1444.4	1463.2	1480.9
12.5°	1235.2	1273.7	1305.3	1341.8	1379.3	1400.0	1431.6	1447.4	1479.9	1527.3	1540.1
15°	1206.6	1258.9	1288.5	1334.9	1384.2	1401.0	1444.4	1470.1	1537.2	1566.8	1602.3
17.5°	1180.0	1238.2	1277.7	1331.0	1379.3	1411.9	1454.3	1506.6	1562.8	1605.2	1644.7
20°	1158.3	1214.5	1261.9	1321.1	1382.3	1423.7	1468.1	1531.2	1592.4	1635.8	1666.4
22.5°	1109.0	1181.0	1236.2	1302.3	1376.3	1433.6	1476.0	1545.0	1611.2	1637.8	1664.4
25°	1084.3	1146.5	1210.6	1285.6	1372.4	1440.5	1477.0	1553.9	1612.1	1622.0	1627.9
27.5°	1038.9	1109.0	1183.9	1269.8	1371.4	1428.6	1475.0	1545.0	1591.4	1584.5	1566.8
30°	982.7	1068.5	1151.4	1244.1	1357.6	1419.7	1463.2	1527.3	1551.0	1515.5	1483.9
32.5°	941.2	1022.1	1113.9	1221.4	1341.8	1401.0	1443.4	1493.7	1498.7	1434.5	1381.3
35°	885.0	974.8	1078.4	1191.8	1315.2	1368.4	1407.9	1438.5	1414.8	1325.0	1261.9
37.5°	834.7	923.5	1034.0	1149.4	1278.7	1331.0	1362.5	1367.5	1309.2	1230.3	1137.6
40°	779.4	871.2	986.6	1108.0	1238.2	1283.6	1303.3	1288.5	1204.7	1112.9	1005.4
42.5°	724.2	814.9	939.3	1063.6	1186.9	1225.4	1233.3	1192.8	1090.2	982.7	858.4
45°	664.0	758.7	883.0	1008.3	1127.7	1149.4	1150.4	1092.2	970.8	858.4	742.9
47.5°	614.7	702.5	825.8	951.1	1051.7	1066.5	1060.6	993.5	861.3	735.0	634.4
50°	560.4	644.3	766.6	889.9	975.8	979.7	964.9	869.2	740.0	624.5	544.6
52.5°	502.2	587.0	699.5	817.9	894.9	888.9	860.3	757.7	636.4	540.7	479.5
55°	455.8	530.8	636.4	751.8	806.1	789.3	757.7	653.1	557.4	476.5	423.3
57.5°	404.5	470.6	574.2	674.8	706.4	690.6	659.1	561.4	472.6	411.4	375.9
60°	356.2	416.4	507.1	591.0	615.7	598.9	562.4	474.6	410.4	359.1	332.5
62.5°	311.8	364.1	440.0	517.0	526.9	510.1	478.5	407.5	352.2	311.8	292.0
65°	270.3	319.7	380.8	439.0	447.9	430.2	397.6	346.3	299.9	274.3	255.5
67.5°	229.9	269.3	323.6	366.0	371.0	354.2	327.6	286.1	257.5	229.9	216.1
70°	194.4	224.0	266.4	300.9	302.9	287.1	273.3	235.8	214.1	194.4	183.5
72.5°	159.8	180.6	213.1	238.8	239.7	229.9	217.1	193.4	174.6	160.8	150.0
75°	126.3	144.0	163.8	186.5	185.5	177.6	167.7	152.9	137.1	128.3	123.3
77.5°	96.7	107.5	123.3	138.1	138.1	134.2	128.3	117.4	107.5	98.7	93.7
80°	69.1	76.0	88.8	93.7	95.7	94.7	89.8	81.9	77.9	71.0	69.1
82.5°	44.4	49.3	55.3	60.2	63.1	61.2	60.2	56.2	50.3	48.3	46.4
85°	25.7	27.6	30.6	33.5	34.5	33.5	35.5	32.6	29.6	29.6	28.6
87.5°	10.9	11.8	13.8	13.8	14.8	14.8	13.8	14.8	14.8	13.8	12.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P997631

CATALOG NUMBER: SA2XXDP-B675DB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6
2.5°	1333.9	1334.9	1336.9	1346.7	1351.7	1352.7	1348.7	1357.6	1360.6	1357.6	1355.6
5°	1397.1	1403.0	1414.8	1427.6	1426.7	1427.6	1433.6	1439.5	1441.5	1433.6	1436.5
7.5°	1452.3	1464.1	1477.0	1496.7	1496.7	1506.6	1510.5	1515.5	1527.3	1521.4	1519.4
10°	1515.5	1531.2	1554.9	1586.5	1587.5	1597.3	1607.2	1623.0	1627.9	1624.0	1626.0
12.5°	1594.4	1625.0	1626.9	1661.5	1677.3	1679.2	1695.0	1692.1	1701.9	1701.9	1718.7
15°	1628.9	1676.3	1702.9	1736.5	1746.3	1734.5	1747.3	1761.1	1762.1	1762.1	1761.1
17.5°	1691.1	1709.8	1736.5	1754.2	1758.2	1758.2	1759.1	1765.1	1761.1	1753.2	1759.1
20°	1703.9	1711.8	1721.7	1719.7	1721.7	1711.8	1701.9	1692.1	1693.0	1688.1	1702.9
22.5°	1680.2	1678.2	1655.6	1640.8	1640.8	1621.0	1602.3	1593.4	1584.5	1587.5	1592.4
25°	1621.0	1590.4	1562.8	1541.1	1536.2	1504.6	1478.9	1471.1	1456.3	1468.1	1470.1
27.5°	1526.3	1491.8	1447.4	1428.6	1403.0	1390.1	1372.4	1348.7	1318.1	1335.9	1332.9
30°	1424.7	1373.4	1336.9	1291.5	1251.0	1248.1	1214.5	1175.1	1159.3	1159.3	1168.2
32.5°	1311.2	1243.1	1189.9	1125.7	1086.3	1069.5	1029.0	989.6	998.5	968.9	979.7
35°	1179.0	1089.2	1022.1	960.0	930.4	910.7	858.4	836.7	813.0	799.2	824.8
37.5°	1052.7	949.1	863.3	795.2	784.4	748.8	713.3	699.5	685.7	691.6	690.6
40°	898.8	807.1	730.1	676.8	658.1	641.3	617.6	600.9	592.0	596.9	597.9
42.5°	759.7	682.7	625.5	588.0	572.2	560.4	548.6	534.7	531.8	531.8	535.7
45°	652.2	589.0	550.5	519.9	511.1	502.2	493.3	487.4	485.4	481.5	484.4
47.5°	566.3	516.0	492.3	469.6	459.8	457.8	449.9	446.9	443.0	442.0	443.0
50°	494.3	462.7	441.0	428.2	421.3	418.3	414.4	408.5	406.5	411.4	409.4
52.5°	444.0	414.4	402.5	389.7	385.8	381.8	375.9	376.9	375.9	373.9	373.9
55°	393.7	374.9	363.1	353.2	352.2	348.3	343.3	341.4	340.4	338.4	341.4
57.5°	353.2	338.4	327.6	318.7	314.7	314.7	309.8	305.9	305.9	304.9	305.9
60°	312.8	298.0	291.1	282.2	279.2	278.2	275.3	273.3	270.3	270.3	270.3
62.5°	275.3	263.4	255.5	247.6	248.6	243.7	239.7	237.8	237.8	238.8	238.8
65°	239.7	231.9	222.0	215.1	213.1	212.1	210.2	209.2	206.2	208.2	208.2
67.5°	207.2	196.3	190.4	187.5	184.5	183.5	181.5	179.6	178.6	177.6	179.6
70°	174.6	165.8	160.8	158.8	155.9	154.9	153.9	151.0	151.9	152.9	153.9
72.5°	145.0	137.1	136.2	130.2	130.2	130.2	126.3	128.3	127.3	125.3	127.3
75°	114.4	110.5	108.5	105.6	106.6	105.6	104.6	101.6	101.6	102.6	103.6
77.5°	90.8	86.8	85.8	82.9	80.9	82.9	80.9	79.9	79.9	80.9	80.9
80°	67.1	65.1	62.2	62.2	62.2	61.2	61.2	61.2	60.2	59.2	60.2
82.5°	44.4	44.4	43.4	42.4	43.4	41.4	42.4	42.4	42.4	42.4	42.4
85°	28.6	27.6	27.6	26.6	26.6	26.6	27.6	25.7	25.7	26.6	26.6
87.5°	12.8	12.8	12.8	13.8	12.8	12.8	12.8	13.8	12.8	12.8	12.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P997631

CATALOG NUMBER: SA2XXDP-B675DB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6
2.5°	1360.6	1353.6	1347.7	1348.7	1353.6	1349.7	1339.8	1327.0	1322.1	1316.2	1322.1
5°	1442.4	1436.5	1424.7	1425.7	1422.7	1418.8	1403.0	1383.2	1383.2	1367.5	1365.5
7.5°	1523.3	1514.5	1506.6	1504.6	1493.7	1485.9	1472.0	1444.4	1433.6	1414.8	1404.0
10°	1614.1	1607.2	1598.3	1587.5	1581.6	1567.7	1545.0	1504.6	1484.9	1459.2	1440.5
12.5°	1705.9	1704.9	1685.1	1663.4	1662.5	1640.8	1625.0	1570.7	1544.1	1509.5	1465.1
15°	1764.1	1759.1	1748.3	1737.4	1740.4	1716.7	1681.2	1617.1	1599.3	1557.9	1510.5
17.5°	1763.1	1763.1	1760.1	1758.2	1755.2	1748.3	1728.6	1686.1	1657.5	1605.2	1560.8
20°	1706.9	1719.7	1722.6	1721.7	1731.5	1736.5	1735.5	1708.8	1686.1	1639.8	1594.4
22.5°	1594.4	1624.0	1636.8	1644.7	1665.4	1676.3	1701.9	1692.1	1686.1	1651.6	1613.1
25°	1489.8	1499.7	1538.1	1540.1	1568.7	1595.4	1621.0	1637.8	1659.5	1646.7	1614.1
27.5°	1354.6	1377.3	1404.9	1425.7	1431.6	1485.9	1528.3	1559.8	1609.2	1613.1	1602.3
30°	1201.7	1212.6	1257.9	1285.6	1317.1	1356.6	1417.8	1472.0	1516.4	1556.9	1570.7
32.5°	1015.2	1059.6	1086.3	1119.8	1147.4	1217.5	1292.5	1362.5	1413.8	1481.9	1511.5
35°	844.5	879.1	924.5	938.3	988.6	1047.8	1145.5	1235.2	1313.2	1382.3	1442.4
37.5°	703.5	731.1	779.4	801.1	830.7	906.7	988.6	1100.1	1193.8	1278.7	1353.6
40°	606.8	627.5	664.0	670.9	695.6	764.6	830.7	935.3	1059.6	1174.1	1256.0
42.5°	540.7	550.5	575.2	584.1	599.9	646.2	705.4	804.1	919.5	1037.9	1153.4
45°	493.3	500.2	515.0	522.9	542.6	563.4	611.7	690.6	781.4	900.8	1025.1
47.5°	450.9	459.8	465.7	470.6	481.5	504.2	535.7	593.9	680.8	790.3	910.7
50°	415.4	418.3	429.2	430.2	437.1	451.9	481.5	517.0	586.1	674.8	791.3
52.5°	379.8	382.8	389.7	396.6	399.6	411.4	431.2	460.8	512.1	582.1	685.7
55°	344.3	348.3	355.2	360.1	363.1	372.9	384.8	413.4	453.8	503.2	588.0
57.5°	308.8	317.7	319.7	322.6	327.6	338.4	349.3	366.0	397.6	443.0	505.2
60°	275.3	278.2	285.1	288.1	293.0	298.9	312.8	325.6	348.3	383.8	440.0
62.5°	240.7	247.6	250.6	253.6	257.5	264.4	273.3	287.1	306.8	335.5	379.8
65°	211.1	212.1	218.0	222.0	225.9	230.9	239.7	252.6	264.4	291.1	323.6
67.5°	182.5	184.5	186.5	190.4	195.4	200.3	208.2	215.1	229.9	247.6	273.3
70°	154.9	154.9	159.8	162.8	161.8	167.7	173.6	181.5	192.4	209.2	229.9
72.5°	130.2	129.2	133.2	134.2	136.2	140.1	144.0	151.9	157.9	170.7	186.5
75°	103.6	105.6	107.5	107.5	110.5	113.5	117.4	121.4	128.3	136.2	148.0
77.5°	81.9	81.9	83.9	84.8	87.8	86.8	90.8	94.7	99.6	106.6	115.4
80°	60.2	62.2	62.2	62.2	63.1	64.1	68.1	71.0	74.0	78.9	82.9
82.5°	42.4	42.4	44.4	44.4	44.4	46.4	46.4	47.4	49.3	52.3	55.3
85°	26.6	26.6	26.6	27.6	26.6	27.6	29.6	28.6	29.6	31.6	31.6
87.5°	12.8	12.8	12.8	12.8	12.8	13.8	12.8	13.8	14.8	14.8	14.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P997631

CATALOG NUMBER: SA2XXDP-B675DB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6
2.5°	1317.1	1312.2	1309.2	1311.2	1305.3	1290.5	1290.5	1295.4	1289.5	1283.6	1274.7
5°	1353.6	1343.8	1337.9	1336.9	1323.1	1299.4	1294.4	1289.5	1276.7	1262.9	1248.1
7.5°	1389.2	1371.4	1361.5	1354.6	1334.9	1304.3	1291.5	1280.6	1259.9	1239.2	1220.5
10°	1418.8	1393.1	1381.3	1370.4	1344.8	1306.3	1285.6	1265.8	1239.2	1212.6	1188.9
12.5°	1442.4	1412.8	1398.0	1382.3	1350.7	1300.4	1274.7	1243.1	1216.5	1181.0	1157.3
15°	1481.9	1420.7	1406.9	1392.1	1359.6	1290.5	1258.9	1223.4	1186.9	1139.5	1113.9
17.5°	1513.5	1431.6	1430.6	1399.0	1356.6	1286.6	1238.2	1191.8	1152.4	1105.0	1064.6
20°	1532.2	1448.4	1432.6	1400.0	1346.7	1259.9	1209.6	1158.3	1115.9	1058.6	1018.2
22.5°	1548.0	1472.0	1430.6	1391.1	1326.0	1251.0	1177.0	1128.7	1070.5	1008.3	969.8
25°	1553.9	1477.0	1433.6	1388.2	1311.2	1225.4	1141.5	1089.2	1024.1	967.9	915.6
27.5°	1554.9	1476.0	1422.7	1375.4	1290.5	1191.8	1106.0	1050.8	978.7	913.6	861.3
30°	1545.0	1465.1	1416.8	1365.5	1270.8	1161.3	1062.6	1001.4	924.5	859.3	805.1
32.5°	1515.5	1443.4	1404.0	1347.7	1245.1	1118.8	1021.2	953.1	872.2	808.0	755.8
35°	1466.1	1416.8	1373.4	1321.1	1211.6	1079.4	979.7	899.8	817.9	756.7	707.4
37.5°	1404.9	1378.3	1337.9	1286.6	1173.1	1043.8	933.3	844.5	762.7	703.5	655.1
40°	1322.1	1329.0	1289.5	1243.1	1127.7	995.5	873.2	788.3	711.4	656.1	608.7
42.5°	1232.3	1260.9	1238.2	1193.8	1077.4	942.2	828.8	735.0	660.0	602.8	563.4
45°	1135.6	1184.9	1171.1	1138.6	1025.1	886.0	765.6	674.8	608.7	553.5	519.0
47.5°	1030.0	1100.1	1100.1	1076.4	966.9	829.7	711.4	618.6	553.5	514.0	480.5
50°	922.5	1001.4	1014.2	998.5	901.8	765.6	645.3	561.4	505.2	466.7	442.0
52.5°	810.0	901.8	925.5	917.6	832.7	704.4	591.0	509.1	457.8	424.2	402.5
55°	702.5	809.0	834.7	837.6	758.7	637.4	530.8	458.8	409.4	386.8	368.0
57.5°	600.9	703.5	732.1	737.0	683.7	576.2	474.6	411.4	367.0	348.3	333.5
60°	514.0	599.9	637.4	648.2	601.8	505.2	422.3	361.1	327.6	309.8	296.0
62.5°	443.0	512.1	551.5	554.5	533.8	443.0	368.0	316.7	288.1	272.3	265.4
65°	373.9	436.1	459.8	471.6	454.8	383.8	317.7	275.3	252.6	238.8	231.9
67.5°	318.7	358.1	377.9	393.7	376.9	323.6	270.3	235.8	219.0	205.2	201.3
70°	261.5	294.0	308.8	324.6	309.8	269.3	230.9	199.3	184.5	173.6	168.7
72.5°	209.2	234.8	248.6	258.5	249.6	216.1	184.5	162.8	151.9	144.0	141.1
75°	165.8	183.5	191.4	198.3	194.4	168.7	149.0	131.2	121.4	114.4	112.5
77.5°	126.3	139.1	148.0	150.0	145.0	128.3	111.5	100.6	92.7	88.8	86.8
80°	89.8	97.7	102.6	105.6	100.6	93.7	81.9	74.0	67.1	62.2	61.2
82.5°	60.2	64.1	68.1	67.1	65.1	59.2	52.3	48.3	45.4	41.4	41.4
85°	34.5	35.5	37.5	38.5	37.5	33.5	29.6	27.6	25.7	22.7	22.7
87.5°	14.8	15.8	15.8	16.8	14.8	14.8	12.8	10.9	10.9	9.9	8.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P997631

CATALOG NUMBER: SA2XXDP-B675DB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6
2.5°	1269.8	1274.7	1273.7	1263.9	1253.0	1244.1	1227.4	1229.3	1223.4	1224.4	1230.3
5°	1238.2	1238.2	1234.3	1220.5	1202.7	1192.8	1174.1	1169.1	1157.3	1156.3	1155.3
7.5°	1204.7	1199.7	1194.8	1175.1	1153.4	1137.6	1111.9	1106.0	1094.2	1086.3	1082.3
10°	1165.2	1158.3	1148.4	1125.7	1099.1	1079.4	1052.7	1044.8	1022.1	1012.3	1006.4
12.5°	1121.8	1117.8	1102.1	1083.3	1039.9	1018.2	979.7	987.6	964.9	945.2	942.2
15°	1078.4	1063.6	1054.7	1024.1	971.8	962.0	931.4	915.6	894.9	879.1	879.1
17.5°	1036.0	1013.3	993.5	961.0	922.5	894.9	872.2	864.3	838.6	822.8	819.9
20°	979.7	954.1	949.1	902.8	876.1	845.5	823.8	804.1	785.4	778.4	773.5
22.5°	926.4	896.8	888.9	849.5	822.8	792.3	770.6	756.7	742.9	738.0	729.1
25°	869.2	851.5	839.6	797.2	767.6	739.0	724.2	714.3	701.5	700.5	694.6
27.5°	814.0	797.2	785.4	744.9	723.2	696.6	684.7	673.9	667.0	664.0	661.0
30°	766.6	747.9	734.0	704.4	677.8	656.1	646.2	639.3	635.4	630.5	629.5
32.5°	714.3	703.5	684.7	662.0	641.3	620.6	614.7	609.7	603.8	601.8	600.9
35°	669.9	655.1	643.3	617.6	608.7	591.0	584.1	580.1	572.2	570.3	568.3
37.5°	626.5	612.7	599.9	584.1	567.3	557.4	553.5	547.6	543.6	544.6	542.6
40°	583.1	572.2	562.4	545.6	535.7	530.8	522.9	517.0	515.0	516.0	515.0
42.5°	540.7	530.8	524.9	512.1	502.2	497.3	492.3	486.4	489.4	489.4	492.3
45°	502.2	493.3	489.4	479.5	473.6	465.7	460.8	459.8	463.7	462.7	462.7
47.5°	462.7	459.8	454.8	446.0	438.1	433.1	432.1	432.1	436.1	438.1	437.1
50°	432.1	426.2	420.3	413.4	407.5	405.5	402.5	404.5	408.5	408.5	410.4
52.5°	393.7	389.7	387.7	381.8	377.9	377.9	377.9	378.9	381.8	384.8	383.8
55°	360.1	357.2	355.2	352.2	347.3	348.3	347.3	349.3	352.2	355.2	357.2
57.5°	324.6	323.6	321.6	316.7	316.7	315.7	318.7	319.7	324.6	326.6	329.5
60°	293.0	290.1	290.1	286.1	286.1	286.1	289.1	292.0	296.0	297.0	298.9
62.5°	259.5	259.5	258.5	255.5	255.5	258.5	259.5	263.4	265.4	265.4	268.4
65°	227.9	226.9	225.9	226.9	227.9	227.9	230.9	232.8	234.8	235.8	236.8
67.5°	196.3	195.4	197.3	196.3	198.3	202.3	201.3	204.2	207.2	207.2	208.2
70°	166.7	168.7	167.7	169.7	168.7	170.7	173.6	174.6	174.6	175.6	178.6
72.5°	139.1	139.1	139.1	138.1	139.1	141.1	143.1	144.0	146.0	147.0	150.0
75°	112.5	112.5	110.5	112.5	112.5	114.4	116.4	116.4	116.4	118.4	121.4
77.5°	84.8	85.8	84.8	86.8	86.8	87.8	89.8	88.8	90.8	91.8	92.7
80°	62.2	61.2	61.2	61.2	62.2	62.2	64.1	65.1	65.1	68.1	66.1
82.5°	39.5	40.5	39.5	40.5	40.5	41.4	40.5	41.4	42.4	44.4	43.4
85°	22.7	21.7	21.7	22.7	21.7	21.7	22.7	21.7	22.7	21.7	22.7
87.5°	8.9	7.9	7.9	7.9	7.9	6.9	6.9	5.9	5.9	5.9	4.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P997631

CATALOG NUMBER: SA2XXDP-B675DB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6
2.5°	1223.4	1226.4	1219.5	1217.5	1219.5	1212.6	1214.5	1216.5	1216.5	1219.5	1221.4
5°	1152.4	1148.4	1141.5	1139.5	1137.6	1140.5	1138.6	1141.5	1142.5	1149.4	1150.4
7.5°	1082.3	1076.4	1070.5	1064.6	1062.6	1057.7	1062.6	1062.6	1069.5	1067.5	1072.5
10°	999.4	998.5	990.6	987.6	983.7	975.8	986.6	983.7	988.6	997.5	999.4
12.5°	938.3	927.4	932.4	918.5	923.5	915.6	916.6	916.6	924.5	925.5	923.5
15°	880.1	871.2	858.4	852.4	849.5	845.5	858.4	859.3	853.4	867.2	862.3
17.5°	820.9	820.9	809.0	806.1	798.2	802.1	800.1	801.1	799.2	809.0	814.0
20°	769.6	764.6	760.7	761.7	751.8	749.8	747.9	749.8	756.7	763.6	765.6
22.5°	728.1	725.2	715.3	717.3	709.4	712.3	710.4	715.3	716.3	716.3	723.2
25°	688.7	684.7	685.7	681.8	678.8	678.8	675.8	678.8	682.7	684.7	685.7
27.5°	659.1	656.1	651.2	648.2	650.2	645.3	649.2	652.2	652.2	650.2	652.2
30°	623.5	625.5	625.5	615.7	619.6	617.6	620.6	622.6	622.6	623.5	621.6
32.5°	599.9	593.9	593.0	592.0	592.0	588.0	588.0	591.0	592.0	593.0	595.9
35°	568.3	568.3	563.4	566.3	562.4	563.4	562.4	563.4	565.3	562.4	565.3
37.5°	539.7	540.7	538.7	540.7	541.7	539.7	537.7	541.7	539.7	539.7	537.7
40°	515.0	514.0	515.0	515.0	515.0	516.0	514.0	514.0	514.0	512.1	510.1
42.5°	494.3	488.4	490.4	491.3	488.4	488.4	489.4	488.4	491.3	485.4	485.4
45°	464.7	462.7	463.7	463.7	465.7	462.7	464.7	465.7	462.7	461.7	459.8
47.5°	438.1	440.0	438.1	440.0	440.0	442.0	438.1	439.0	440.0	436.1	433.1
50°	411.4	411.4	414.4	413.4	414.4	412.4	412.4	411.4	412.4	410.4	407.5
52.5°	386.8	383.8	388.7	387.7	386.8	385.8	384.8	385.8	383.8	381.8	381.8
55°	356.2	356.2	359.1	360.1	360.1	358.1	356.2	357.2	356.2	355.2	354.2
57.5°	331.5	327.6	329.5	330.5	330.5	327.6	329.5	327.6	327.6	328.5	325.6
60°	299.9	299.9	298.0	300.9	300.9	298.9	298.9	299.9	298.0	297.0	296.0
62.5°	266.4	267.4	270.3	271.3	272.3	270.3	268.4	269.3	269.3	266.4	267.4
65°	237.8	239.7	243.7	242.7	240.7	241.7	239.7	240.7	237.8	238.8	235.8
67.5°	210.2	209.2	210.2	210.2	212.1	211.1	209.2	209.2	208.2	211.1	208.2
70°	180.6	180.6	180.6	180.6	181.5	182.5	180.6	178.6	179.6	177.6	176.6
72.5°	150.0	151.0	150.0	151.9	149.0	151.0	151.0	150.0	149.0	149.0	149.0
75°	121.4	123.3	120.4	121.4	120.4	122.3	121.4	121.4	119.4	118.4	119.4
77.5°	92.7	93.7	91.8	92.7	91.8	92.7	92.7	91.8	91.8	91.8	91.8
80°	66.1	67.1	66.1	65.1	64.1	66.1	64.1	65.1	66.1	65.1	67.1
82.5°	42.4	42.4	41.4	42.4	40.5	40.5	41.4	41.4	40.5	42.4	40.5
85°	20.7	20.7	22.7	20.7	19.7	19.7	19.7	20.7	19.7	21.7	20.7
87.5°	4.9	3.9	4.9	4.9	3.9	3.9	4.9	3.9	4.9	5.9	3.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P997631

CATALOG NUMBER: SA2XXDP-B675DB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6
2.5°	1218.5	1226.4	1223.4	1212.6	1225.4	1225.4	1234.3	1234.3	1245.1	1249.1	1255.0
5°	1149.4	1155.3	1160.3	1155.3	1164.2	1178.0	1185.9	1192.8	1207.6	1213.5	1222.4
7.5°	1075.4	1086.3	1091.2	1091.2	1106.0	1121.8	1137.6	1147.4	1168.2	1176.1	1184.9
10°	1003.4	1016.2	1026.1	1025.1	1049.8	1059.6	1079.4	1102.1	1122.8	1134.6	1147.4
12.5°	927.4	934.3	948.1	967.9	973.8	991.6	1014.2	1042.9	1080.4	1091.2	1109.9
15°	864.3	883.0	893.9	902.8	916.6	933.3	958.0	985.6	1023.1	1046.8	1066.5
17.5°	811.0	835.7	842.6	840.6	858.4	884.0	912.6	933.3	966.9	995.5	1014.2
20°	767.6	777.5	789.3	794.2	808.0	835.7	863.3	887.0	914.6	937.3	959.0
22.5°	724.2	732.1	741.9	750.8	761.7	777.5	804.1	833.7	860.3	882.0	906.7
25°	688.7	693.6	702.5	709.4	721.2	732.1	750.8	783.4	814.9	827.8	849.5
27.5°	654.1	658.1	664.0	671.9	677.8	688.7	705.4	732.1	764.6	777.5	807.1
30°	623.5	626.5	632.4	636.4	639.3	652.2	665.0	685.7	710.4	728.1	749.8
32.5°	594.9	597.9	603.8	604.8	608.7	615.7	627.5	646.2	667.9	682.7	701.5
35°	563.4	565.3	571.3	573.2	576.2	582.1	591.0	604.8	624.5	635.4	652.2
37.5°	538.7	537.7	541.7	544.6	548.6	551.5	554.5	568.3	583.1	593.0	605.8
40°	512.1	510.1	511.1	515.0	517.0	520.9	520.9	534.7	544.6	552.5	562.4
42.5°	485.4	484.4	482.5	484.4	486.4	487.4	488.4	498.2	508.1	515.0	525.9
45°	458.8	457.8	455.8	456.8	456.8	458.8	461.7	465.7	472.6	478.5	484.4
47.5°	434.1	432.1	429.2	428.2	430.2	430.2	430.2	434.1	441.0	443.0	448.9
50°	408.5	405.5	401.6	399.6	399.6	398.6	400.6	401.6	407.5	409.4	414.4
52.5°	380.8	378.9	374.9	371.0	372.0	370.0	371.0	372.0	373.9	376.9	379.8
55°	353.2	349.3	346.3	345.3	342.4	342.4	339.4	343.3	342.4	343.3	347.3
57.5°	326.6	322.6	317.7	315.7	312.8	311.8	309.8	308.8	309.8	312.8	315.7
60°	295.0	293.0	290.1	287.1	285.1	282.2	280.2	280.2	279.2	279.2	280.2
62.5°	264.4	263.4	259.5	258.5	256.5	254.5	251.6	249.6	249.6	251.6	252.6
65°	234.8	233.8	230.9	229.9	224.9	223.0	222.0	221.0	219.0	219.0	219.0
67.5°	207.2	204.2	204.2	199.3	195.4	193.4	191.4	190.4	190.4	190.4	191.4
70°	176.6	176.6	173.6	170.7	166.7	167.7	164.8	161.8	161.8	159.8	160.8
72.5°	147.0	146.0	143.1	142.1	139.1	136.2	134.2	136.2	133.2	132.2	133.2
75°	118.4	117.4	115.4	113.5	114.4	111.5	108.5	107.5	107.5	105.6	105.6
77.5°	90.8	92.7	88.8	87.8	85.8	83.9	82.9	81.9	81.9	81.9	83.9
80°	63.1	64.1	64.1	62.2	63.1	60.2	60.2	60.2	57.2	58.2	59.2
82.5°	40.5	40.5	39.5	40.5	39.5	39.5	38.5	38.5	37.5	37.5	38.5
85°	22.7	21.7	20.7	22.7	21.7	21.7	20.7	20.7	20.7	20.7	20.7
87.5°	4.9	5.9	5.9	5.9	5.9	6.9	6.9	6.9	7.9	7.9	7.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P997631

CATALOG NUMBER: SA2XXDP-B675DB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1283.6	1283.6	1283.6	1283.6
2.5°	1259.9	1259.9	1274.7	1290.5
5°	1232.3	1239.2	1262.9	1284.6
7.5°	1205.7	1217.5	1247.1	1274.7
10°	1173.1	1188.9	1225.4	1257.9
12.5°	1141.5	1156.3	1198.7	1235.2
15°	1097.1	1115.9	1161.3	1206.6
17.5°	1052.7	1071.5	1126.7	1180.0
20°	1000.4	1025.1	1087.3	1158.3
22.5°	952.1	982.7	1051.7	1109.0
25°	898.8	946.2	1010.3	1084.3
27.5°	851.5	898.8	963.9	1038.9
30°	798.2	846.5	913.6	982.7
32.5°	746.9	791.3	856.4	941.2
35°	693.6	736.0	799.2	885.0
37.5°	645.3	686.7	755.8	834.7
40°	597.9	641.3	700.5	779.4
42.5°	553.5	592.0	645.3	724.2
45°	513.0	540.7	590.0	664.0
47.5°	470.6	495.3	540.7	614.7
50°	431.2	451.9	491.3	560.4
52.5°	392.7	410.4	446.9	502.2
55°	358.1	374.9	401.6	455.8
57.5°	322.6	335.5	361.1	404.5
60°	288.1	299.9	320.7	356.2
62.5°	253.6	263.4	283.2	311.8
65°	223.0	230.9	245.7	270.3
67.5°	193.4	198.3	210.2	229.9
70°	164.8	168.7	178.6	194.4
72.5°	134.2	138.1	149.0	159.8
75°	108.5	109.5	117.4	126.3
77.5°	84.8	83.9	89.8	96.7
80°	58.2	61.2	66.1	69.1
82.5°	39.5	40.5	42.4	44.4
85°	21.7	22.7	22.7	25.7
87.5°	8.9	9.9	9.9	10.9
90°	0.0	0.0	0.0	0.0

TEST NUMBER: P997631

CATALOG NUMBER: SA2XXDP-B675DB2750-4F0-XX-W2A-A_5000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	22.43	23.95	22.80	24.26	24.58	18.70	20.22	19.07	20.53	20.85
	3H	23.55	24.91	23.93	25.24	25.60	20.12	21.48	20.49	21.80	22.17
	4H	23.87	25.15	24.27	25.50	25.88	20.62	21.90	21.02	22.25	22.63
	6H	24.06	25.24	24.48	25.61	26.00	20.98	22.16	21.39	22.53	22.92
	8H	24.10	25.23	24.53	25.62	26.02	21.09	22.21	21.52	22.60	23.01
	12H	24.12	25.19	24.55	25.57	26.00	21.17	22.24	21.60	22.62	23.05
4H	2H	22.55	23.83	22.95	24.18	24.56	19.50	20.78	19.90	21.12	21.50
	3H	23.88	24.94	24.30	25.34	25.75	21.08	22.14	21.49	22.54	22.94
	4H	24.36	25.31	24.79	25.73	26.17	21.67	22.63	22.11	23.04	23.48
	6H	24.69	25.52	25.15	25.96	26.42	22.13	22.96	22.59	23.40	23.86
	8H	24.76	25.54	25.23	25.98	26.45	22.27	23.05	22.74	23.49	23.96
	12H	24.81	25.50	25.29	25.98	26.45	22.38	23.07	22.86	23.55	24.02
8H	4H	24.44	25.22	24.91	25.66	26.13	22.08	22.86	22.55	23.30	23.77
	6H	24.85	25.49	25.35	25.98	26.46	22.63	23.27	23.12	23.76	24.23
	8H	24.98	25.55	25.49	26.06	26.55	22.82	23.40	23.34	23.91	24.40
	12H	25.07	25.57	25.58	26.07	26.63	22.99	23.49	23.50	23.99	24.55
12H	4H	24.43	25.13	24.92	25.60	26.08	22.14	22.83	22.62	23.31	23.78
	6H	24.84	25.42	25.36	25.93	26.42	22.70	23.27	23.21	23.78	24.27
	8H	25.01	25.52	25.52	26.01	26.57	22.95	23.46	23.46	23.95	24.51

END OF REPORT