

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000693

Luminaire Tested: SA4XXDIP-B1020D590UB27-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000693
REPORT IS A COMBINATION OF REPORTS P995306 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B1020D590UB27-4F0-XX-W2A-F1
Description: Define 4 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6398.0 lumens
Efficiency: N/A
Efficacy: 102.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 62.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000693

CATALOG NUMBER: SA4XXDIP-B1020D590UB27-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1000693

CATALOG NUMBER: SA4XXDIP-B1020D590UB27-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	105	105	105	105	93	93	93	83	83	83	73	73	73
1	102	97	93	90	96	92	88	85	82	79	77	73	71	69	64	63	61
2	93	85	79	73	87	80	75	70	72	67	64	64	61	58	57	54	52
3	85	75	67	61	80	71	64	59	63	58	54	57	52	49	50	47	44
4	77	66	58	52	73	63	55	50	56	50	46	50	46	42	45	41	38
5	71	59	51	45	67	56	49	43	51	44	40	45	40	36	40	36	33
6	66	53	45	39	62	51	43	37	46	39	35	41	36	32	37	33	29
7	61	48	40	34	57	46	38	33	41	35	31	37	32	28	34	29	26
8	57	44	36	30	53	42	34	29	38	32	27	34	29	25	31	27	23
9	53	40	32	27	50	38	31	26	35	29	25	32	26	23	29	24	21
10	49	37	29	25	47	35	28	24	32	26	22	29	24	21	26	22	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13864	13864	13864
5°	13876	13466	13482
10°	13758	13091	13000
15°	13561	12648	12456
20°	13310	12167	11894
25°	13026	11658	11288
30°	12684	11109	10623
35°	12329	10547	9980
40°	11960	9942	9296
45°	11573	9336	8657
50°	11144	8747	7948
55°	10678	8061	7246
60°	10201	7308	6513
65°	9655	6530	5688
70°	9027	5595	4803
75°	8086	4509	3847
80°	6893	3261	2707
85°	5356	1814	1457

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11573 cd/sqm

TEST NUMBER: P1000693

CATALOG NUMBER: SA4XXDIP-B1020D590UB27-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.3	2.5
10°-20°	451.5	7.1
20°-30°	664.5	10.4
30°-40°	772.4	12.1
40°-50°	772.3	12.1
50°-60°	675.5	10.6
60°-70°	501.5	7.8
70°-80°	284.5	4.4
80°-90°	83.1	1.3
90°-100°	47.7	0.7
100°-110°	143.0	2.2
110°-120°	242.9	3.8
120°-130°	320.4	5.0
130°-140°	359.9	5.6
140°-150°	353.7	5.5
150°-160°	297.5	4.6
160°-170°	197.9	3.1
170°-180°	69.3	1.1
0°-30°	1276.2	19.9
0°-40°	2048.6	32.0
0°-60°	3496.5	54.6
0°-90°	4365.6	68.2
90°-120°	433.7	6.8
90°-150°	1467.7	22.9
90°-180°	2032.0	31.8
0°-180°	6398.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1700	1700	1700	1700	1700	
5°	1699	1693	1678	1693	1691	161
15°	1617	1612	1591	1599	1595	456
25°	1465	1455	1436	1437	1432	674
35°	1260	1251	1232	1222	1215	788
45°	1029	1019	997	982	978	793
55°	778	774	755	738	730	697
65°	527	520	507	493	486	522
75°	281	274	267	262	260	298
85°	74	74	71	71	70	79
90°	2	8	12	16	17	7
95°	34	39	43	45	45	37
105°	132	133	135	136	138	140
115°	247	247	246	245	245	244
125°	360	360	359	358	357	321
135°	464	467	467	466	464	359
145°	564	566	566	566	564	353
155°	646	646	645	648	645	297
165°	703	701	700	704	701	198
175°	731	728	728	732	728	69
180°	732	732	732	732	732	

TEST NUMBER: P1000693

CATALOG NUMBER: SA4XXDIP-B1020D590UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1700.2	1700.2	1700.2	1700.2	1700.2
2.5°	1705.7	1701.6	1686.6	1700.2	1698.9
5°	1698.9	1693.4	1678.4	1693.4	1690.7
7.5°	1686.6	1681.2	1664.8	1677.1	1675.7
10°	1668.9	1663.5	1645.7	1656.6	1653.9
12.5°	1645.7	1640.3	1621.2	1633.5	1629.4
15°	1617.1	1611.7	1591.3	1599.4	1595.3
17.5°	1584.4	1577.6	1558.6	1564.0	1561.3
20°	1547.7	1540.8	1520.4	1524.5	1521.8
22.5°	1508.1	1498.6	1478.2	1486.3	1480.9
25°	1464.6	1455.0	1435.9	1437.3	1431.9
27.5°	1415.5	1406.0	1388.3	1385.5	1378.7
30°	1366.5	1355.6	1337.8	1332.4	1325.6
32.5°	1314.7	1305.2	1286.1	1279.3	1272.5
35°	1260.2	1250.7	1231.6	1222.0	1215.2
37.5°	1203.0	1194.8	1174.4	1164.8	1155.3
40°	1147.1	1136.2	1115.8	1102.2	1095.3
42.5°	1087.2	1081.7	1058.6	1042.2	1038.1
45°	1028.6	1019.1	997.3	982.3	978.2
47.5°	967.3	960.5	940.0	923.7	912.8
50°	904.6	899.2	880.1	861.0	852.8
52.5°	843.3	836.5	816.1	799.7	788.8
55°	777.9	773.8	754.8	738.4	730.2
57.5°	716.6	712.5	693.4	677.1	668.9
60°	652.6	645.8	628.1	615.8	609.0
62.5°	589.9	584.5	565.4	554.5	547.7
65°	527.2	520.4	506.8	493.2	486.4
67.5°	463.2	457.8	444.1	430.5	429.1
70°	404.6	395.1	384.2	373.3	369.2
72.5°	342.0	332.4	324.2	316.1	312.0
75°	280.6	273.8	267.0	261.6	260.2
77.5°	220.7	218.0	211.2	209.8	205.7
80°	167.6	163.5	160.8	158.0	156.7
82.5°	115.8	114.4	114.4	113.1	111.7
85°	73.6	73.6	70.8	70.8	69.5
87.5°	35.4	34.1	32.7	32.7	32.7
90°	1.7	7.9	12.5	15.9	17.0
92.5°	14.7	22.1	24.9	26.6	27.2
95°	34.0	39.1	43.1	44.8	44.8
97.5°	54.4	58.9	63.4	65.7	65.7
100°	79.3	81.6	86.7	87.8	87.8
102.5°	105.4	105.9	110.5	112.2	112.7
105°	132.0	132.6	134.8	136.5	138.2
107.5°	159.8	160.3	160.9	163.2	162.6
110°	188.1	189.2	188.6	187.5	189.2

TEST NUMBER: P1000693

CATALOG NUMBER: SA4XXDIP-B1020D590UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	217.5	217.5	216.4	216.4	216.4
115°	247.0	247.0	245.9	245.3	244.7
117.5°	274.8	274.8	274.2	272.5	270.8
120°	302.5	304.8	303.1	300.3	301.4
122.5°	331.4	332.0	331.4	329.7	326.9
125°	359.7	359.7	359.2	358.0	356.9
127.5°	385.2	386.9	385.8	384.7	384.1
130°	412.4	414.1	414.1	413.0	410.7
132.5°	440.2	441.3	440.7	439.6	439.1
135°	464.0	467.4	467.4	466.2	464.5
137.5°	490.6	492.3	493.4	491.7	492.3
140°	517.2	518.4	518.4	517.8	517.2
142.5°	541.6	542.7	542.2	542.2	542.2
145°	563.7	565.9	566.5	565.9	564.3
147.5°	586.3	589.2	588.6	588.0	587.5
150°	606.7	609.0	609.0	609.0	608.4
152.5°	626.0	627.1	627.7	629.4	627.7
155°	645.8	645.8	645.3	647.5	645.3
157.5°	662.8	661.7	661.7	663.4	661.7
160°	677.6	677.0	676.4	678.1	675.3
162.5°	691.2	689.5	688.9	692.3	689.5
165°	703.0	701.3	700.2	703.6	701.3
167.5°	712.7	710.4	710.4	713.8	710.4
170°	720.6	717.8	718.3	721.7	717.8
172.5°	726.3	724.0	724.0	728.0	724.0
175°	731.4	728.5	728.0	731.9	728.0
177.5°	733.6	730.8	730.8	734.8	730.2
180°	732.5	732.5	732.5	732.5	732.5

(END OF REPORT)