

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000724

Luminaire Tested: SA4XXDIP-B1020D590UB35-4F0-XX-W2A-D4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000724
REPORT IS A COMBINATION OF REPORTS P995337 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B1020D590UB35-4F0-XX-W2A-D4
Description: Define 4 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6335.3 lumens
Efficiency: N/A
Efficacy: 101.9 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 62.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000724

CATALOG NUMBER: SA4XXDIP-B1020D590UB35-4F0-XX-W2A-D4

Luminous Intensity Polar Plot



TEST NUMBER: P1000724

CATALOG NUMBER: SA4XXDIP-B1020D590UB35-4F0-XX-W2A-D4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67
1	99	94	90	86	92	88	84	81	77	74	71	66	64	62	57	55	54
2	90	82	75	69	84	76	70	65	67	62	58	58	54	51	49	47	44
3	82	71	63	57	76	67	60	54	58	53	48	51	46	43	43	40	37
4	74	63	54	48	69	59	51	45	52	45	41	45	40	36	38	35	32
5	68	56	47	41	63	52	45	39	46	40	35	40	35	31	34	31	27
6	63	50	41	35	58	47	39	34	41	35	30	36	31	27	31	27	24
7	58	45	37	31	54	42	35	29	37	31	27	33	28	24	28	24	21
8	54	41	33	27	50	39	31	26	34	28	24	30	25	21	26	22	19
9	50	37	30	24	47	35	28	23	31	25	21	28	23	19	24	20	17
10	47	34	27	22	44	32	25	21	29	23	19	25	21	17	22	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10050	10050	10050
5°	10078	9788	9806
10°	10012	9595	9568
15°	9919	9379	9300
20°	9779	9145	9040
25°	9623	8887	8759
30°	9454	8630	8472
35°	9263	8368	8217
40°	9108	8117	7953
45°	8881	7881	7720
50°	8689	7613	7474
55°	8487	7355	7190
60°	8177	7033	6923
65°	7834	6686	6602
70°	7420	6291	6231
75°	6841	5850	5877
80°	6186	5403	5507
85°	5319	4951	5207

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8881 cd/sqm

TEST NUMBER: P1000724

CATALOG NUMBER: SA4XXDIP-B1020D590UB35-4F0-XX-W2A-D4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.8	1.8
10°-20°	334.6	5.3
20°-30°	505.9	8.0
30°-40°	612.0	9.7
40°-50°	647.0	10.2
50°-60°	608.9	9.6
60°-70°	505.3	8.0
70°-80°	354.6	5.6
80°-90°	201.0	3.2
90°-100°	336.1	5.3
100°-110°	529.5	8.4
110°-120°	452.6	7.1
120°-130°	363.8	5.7
130°-140°	290.2	4.6
140°-150°	213.5	3.4
150°-160°	148.1	2.3
160°-170°	87.1	1.4
170°-180°	28.3	0.4
0°-30°	957.3	15.1
0°-40°	1569.3	24.8
0°-60°	2825.3	44.6
0°-90°	3886.2	61.3
90°-120°	1318.2	20.8
90°-150°	2185.6	34.5
90°-180°	2449.0	38.7
0°-180°	6335.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1232	1232	1232	1232	1232	
5°	1234	1230	1220	1231	1230	117
15°	1183	1184	1180	1192	1191	333
25°	1082	1090	1094	1110	1111	498
35°	947	963	977	996	1001	593
45°	789	816	842	865	872	610
55°	618	647	689	716	725	551
65°	428	472	519	553	564	424
75°	237	288	346	385	398	252
85°	73	131	193	235	248	76
90°	23	82	147	188	200	16
95°	37	123	588	389	310	35
105°	80	137	468	936	944	86
115°	126	169	401	740	880	126
125°	170	200	373	614	692	152
135°	198	236	344	522	596	154
145°	227	258	330	419	466	143
155°	257	277	320	363	378	118
165°	280	288	307	325	330	79
175°	292	292	294	298	297	28
180°	292	292	292	292	292	

TEST NUMBER: P1000724

CATALOG NUMBER: SA4XXDIP-B1020D590UB35-4F0-XX-W2A-D4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1232.5	1232.5	1232.5	1232.5	1232.5
2.5°	1238.0	1233.9	1222.8	1232.5	1231.1
5°	1233.9	1229.7	1220.0	1231.1	1229.7
7.5°	1225.6	1222.8	1214.5	1227.0	1225.6
10°	1214.5	1213.1	1206.2	1218.7	1217.3
12.5°	1199.3	1199.3	1195.2	1206.2	1206.2
15°	1182.8	1184.2	1180.0	1192.4	1191.1
17.5°	1160.7	1164.8	1163.5	1175.9	1174.5
20°	1137.2	1141.4	1142.8	1156.6	1156.6
22.5°	1111.0	1116.5	1119.3	1133.1	1135.9
25°	1082.0	1090.3	1094.5	1109.6	1111.0
27.5°	1050.3	1062.7	1068.2	1082.0	1083.4
30°	1018.5	1029.6	1039.3	1054.4	1057.2
32.5°	984.0	997.8	1008.9	1026.8	1029.6
35°	946.8	963.3	977.1	996.5	1000.6
37.5°	909.5	928.8	945.4	964.7	968.9
40°	873.6	891.6	910.9	931.6	937.1
42.5°	832.2	852.9	876.4	899.9	904.0
45°	789.4	815.7	841.9	865.4	872.3
47.5°	749.4	775.6	806.0	829.5	837.7
50°	705.3	735.6	766.0	793.6	801.9
52.5°	661.1	691.5	727.3	754.9	763.2
55°	618.3	647.3	688.7	716.3	724.6
57.5°	570.0	605.9	645.9	679.0	685.9
60°	523.1	559.0	604.5	636.2	647.3
62.5°	477.5	517.6	563.1	594.8	605.9
65°	427.8	472.0	518.9	553.4	564.5
67.5°	380.9	427.8	477.5	512.0	523.1
70°	332.6	379.5	432.0	469.2	478.9
72.5°	285.7	334.0	390.6	426.5	437.5
75°	237.4	288.5	346.4	385.1	397.5
77.5°	191.8	245.7	306.4	345.0	358.8
80°	150.4	205.6	266.4	307.8	318.8
82.5°	109.0	167.0	227.7	270.5	282.9
85°	73.1	131.1	193.2	234.6	248.4
87.5°	45.5	102.1	162.9	202.9	215.3
90°	22.7	81.9	146.9	188.2	199.8
92.5°	28.7	113.2	353.4	241.4	230.2
95°	36.8	123.2	587.9	388.9	309.9
97.5°	48.2	122.6	613.7	622.1	497.9
100°	58.8	125.7	566.4	796.6	678.1
102.5°	70.3	130.4	510.7	901.8	836.5
105°	79.6	137.3	467.6	936.4	944.2
107.5°	92.8	145.8	437.2	916.5	991.1
110°	104.6	153.0	420.8	862.3	985.3



TEST NUMBER: P1000724

CATALOG NUMBER: SA4XXDIP-B1020D590UB35-4F0-XX-W2A-D4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	115.9	161.4	408.7	797.8	943.2
115°	126.5	169.0	400.7	740.4	880.3
117.5°	139.2	177.4	393.2	692.4	820.1
120°	150.4	183.8	386.3	657.6	768.1
122.5°	161.9	191.5	378.8	633.2	725.4
125°	170.2	199.8	372.7	613.9	691.9
127.5°	179.4	210.2	364.6	593.8	668.9
130°	185.5	218.9	357.1	572.9	646.9
132.5°	192.9	227.6	351.1	549.3	624.5
135°	198.5	235.8	343.6	521.8	596.1
137.5°	205.4	241.6	338.1	494.2	564.3
140°	212.9	248.2	333.4	467.2	531.6
142.5°	219.5	254.2	330.6	443.1	497.1
145°	227.0	258.3	329.5	419.2	465.5
147.5°	235.6	263.4	327.7	398.3	435.7
150°	243.6	268.4	326.0	384.0	409.8
152.5°	249.7	272.9	323.2	373.1	392.6
155°	256.6	277.0	320.3	362.8	378.3
157.5°	263.5	280.6	317.4	353.0	365.1
160°	269.8	283.8	314.0	343.2	353.0
162.5°	275.5	286.4	310.5	333.8	341.5
165°	279.5	288.2	307.1	325.2	330.0
167.5°	284.1	289.6	303.6	317.7	320.9
170°	287.0	290.8	300.2	310.2	312.2
172.5°	289.9	291.6	296.7	303.6	303.6
175°	291.6	292.2	294.5	298.5	297.3
177.5°	292.7	292.2	292.7	294.8	292.7
180°	292.2	292.2	292.2	292.2	292.2

(END OF REPORT)