

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P997686

Luminaire Tested: SA2XXRDP-B1005DB2750-4F0-XX-W2A-A_2700K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P997686
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-29)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDP-B1005DB2750-4F0-XX-W2A-A_2700K
Description: Define 2 Regressed Direct Recessed with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3787.0 lumens
Efficiency: N/A
Efficacy: 61.8 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 61.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P997686

CATALOG NUMBER: SA2XXRDP-B1005DB2750-4F0-XX-W2A-A_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P997686

CATALOG NUMBER: SA2XXRDP-B1005DB2750-4F0-XX-W2A-A_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	106	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87			
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76			
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66			
4	87	77	69	63	85	76	68	63	73	67	62	71	66	61	69	64	60	59			
5	81	70	62	56	79	69	61	56	67	60	55	65	59	55	63	58	54	52			
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47			
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42			
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	39			
9	62	50	43	38	61	50	42	37	49	42	37	47	41	37	47	41	37	35			
10	59	47	39	35	58	46	39	35	45	39	34	44	38	34	44	38	34	33			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	34688	34688	34688	34688
5°	34845	38741	34965	30948
10°	34539	42982	34783	26828
15°	33865	45096	34439	21138
20°	33040	39094	33759	18290
25°	32023	25640	32715	16330
30°	30702	17258	31537	14780
35°	29075	13979	30016	13332
40°	27251	12429	28415	12336
45°	25296	11249	26353	11012
50°	23289	10237	24377	10200
55°	21057	9623	22191	9499
60°	19093	8051	20103	7956
65°	17282	6787	18308	7701
70°	15296	6271	16490	7262
75°	13223	5865	14434	6703
80°	10966	5415	11796	5971
85°	8572	4976	9408	5249

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 160°

Vertical Angle: 45°

Luminance: 38079 cd/sqm

TEST NUMBER: P997686

CATALOG NUMBER: SA2XXRDP-B1005DB2750-4F0-XX-W2A-A_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	207.9	5.5
10°-20°	580.2	15.3
20°-30°	746.7	19.7
30°-40°	708.4	18.7
40°-50°	607.1	16.0
50°-60°	462.3	12.2
60°-70°	291.6	7.7
70°-80°	145.5	3.8
80°-90°	37.4	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1534.7	40.5
0°-40°	2243.1	59.2
0°-60°	3312.6	87.5
0°-90°	3787.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3787.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2191	2191	2191	2191	2191	
5°	2193	2438	2200	1948	2193	208
15°	2066	2752	2102	1290	2066	581
25°	1834	1468	1873	935	1834	842
35°	1505	723	1553	690	1505	941
45°	1130	502	1177	492	1130	872
55°	763	349	804	344	763	688
65°	461	181	489	206	461	458
75°	216	96	236	110	216	234
85°	47	27	52	29	47	57
90°	0	0	0	0	0	

TEST NUMBER: P997686

CATALOG NUMBER: SA2XXRDP-B1005DB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4
2.5°	2205.1	2214.2	2218.8	2224.9	2238.6	2247.7	2261.4	2264.5	2263.0	2269.1	2252.3
5°	2192.9	2212.7	2231.0	2246.2	2270.6	2285.8	2302.6	2322.4	2326.9	2349.8	2336.1
7.5°	2176.2	2205.1	2231.0	2261.4	2298.0	2317.8	2343.7	2374.1	2387.8	2415.3	2422.9
10°	2148.8	2189.9	2234.0	2266.0	2316.3	2351.3	2375.7	2424.4	2456.4	2497.5	2491.4
12.5°	2104.6	2157.9	2217.3	2270.6	2336.1	2358.9	2404.6	2454.8	2496.0	2534.0	2567.5
15°	2066.5	2127.4	2192.9	2258.4	2333.0	2375.7	2421.3	2486.8	2531.0	2598.0	2626.9
17.5°	2014.7	2092.4	2170.1	2243.2	2331.5	2380.2	2436.6	2500.5	2566.0	2630.0	2652.8
20°	1961.4	2045.2	2129.0	2227.9	2328.5	2375.7	2433.5	2512.7	2576.7	2626.9	2626.9
22.5°	1897.5	1999.5	2095.5	2189.9	2299.5	2368.0	2427.4	2520.3	2566.0	2576.7	2535.6
25°	1833.5	1935.6	2040.6	2157.9	2282.8	2343.7	2410.7	2497.5	2512.7	2470.1	2363.5
27.5°	1757.4	1871.6	1990.4	2116.8	2247.7	2323.9	2384.8	2442.7	2413.7	2299.5	2133.5
30°	1679.7	1803.1	1937.1	2057.4	2215.8	2285.8	2337.6	2354.3	2263.0	2077.2	1862.5
32.5°	1599.0	1719.3	1860.9	2005.6	2165.5	2232.5	2266.0	2221.9	2054.3	1819.8	1557.9
35°	1504.6	1640.1	1787.8	1938.6	2097.0	2147.2	2167.0	2058.9	1844.2	1541.1	1280.7
37.5°	1419.3	1554.8	1713.2	1867.0	2020.8	2048.2	2028.4	1859.4	1586.8	1286.8	1032.5
40°	1318.8	1463.5	1618.8	1790.9	1917.3	1924.9	1876.2	1656.9	1318.8	1037.1	880.2
42.5°	1225.9	1372.1	1527.4	1702.6	1798.5	1772.6	1707.1	1419.3	1101.0	893.9	767.5
45°	1130.0	1268.5	1436.1	1591.4	1659.9	1599.0	1500.0	1193.9	924.4	769.0	671.6
47.5°	1037.1	1166.5	1332.5	1481.7	1493.9	1425.4	1308.1	1000.5	801.0	676.1	597.0
50°	945.7	1075.1	1230.5	1353.8	1341.6	1247.2	1114.7	869.6	695.9	597.0	531.5
52.5°	854.3	971.6	1122.3	1219.8	1168.0	1076.7	945.7	737.1	607.6	520.8	470.6
55°	763.0	872.6	1002.0	1082.8	1000.5	895.4	802.5	632.0	526.9	456.9	418.8
57.5°	686.8	773.6	892.4	941.1	842.1	759.9	679.2	543.7	456.9	406.6	362.4
60°	603.1	682.2	779.7	808.6	706.6	639.6	571.1	459.9	391.4	347.2	318.3
62.5°	531.5	597.0	671.6	671.6	581.7	531.5	479.7	385.3	328.9	293.9	280.2
65°	461.4	508.6	561.9	555.8	479.7	435.5	394.4	318.3	275.6	251.3	237.6
67.5°	392.9	429.4	464.5	443.2	388.3	350.3	312.2	257.4	228.4	211.7	193.4
70°	330.5	359.4	377.7	357.9	303.0	271.1	243.7	207.1	184.3	162.9	152.3
72.5°	277.2	289.3	295.4	271.1	225.4	207.1	187.3	161.4	141.6	131.0	127.9
75°	216.2	226.9	222.3	204.1	166.0	152.3	137.1	118.8	114.2	108.1	105.1
77.5°	169.0	169.0	161.4	144.7	118.8	108.1	102.0	92.9	88.3	86.8	83.8
80°	120.3	118.8	114.2	95.9	80.7	74.6	74.6	68.5	67.0	64.0	64.0
82.5°	79.2	79.2	73.1	57.9	53.3	51.8	50.3	47.2	47.2	45.7	45.7
85°	47.2	44.2	36.5	32.0	30.5	30.5	28.9	27.4	28.9	27.4	27.4
87.5°	21.3	16.8	12.2	12.2	12.2	12.2	12.2	12.2	12.2	12.2	12.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P997686

CATALOG NUMBER: SA2XXRDP-B1005DB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4
2.5°	2269.1	2272.1	2276.7	2298.0	2301.0	2307.1	2304.1	2304.1	2305.6	2302.6	2304.1
5°	2366.5	2371.1	2393.9	2419.8	2425.9	2419.8	2427.4	2438.1	2438.1	2438.1	2435.1
7.5°	2457.9	2474.6	2500.5	2538.6	2546.2	2553.8	2567.5	2558.4	2561.4	2575.2	2570.6
10°	2546.2	2570.6	2599.5	2631.5	2648.3	2658.9	2665.0	2678.7	2710.7	2674.1	2687.8
12.5°	2630.0	2665.0	2695.5	2730.5	2742.7	2756.4	2760.9	2773.1	2773.1	2771.6	2782.3
15°	2684.8	2716.8	2744.2	2767.0	2770.1	2767.0	2764.0	2765.5	2770.1	2751.8	2762.5
17.5°	2697.0	2700.0	2709.2	2700.0	2701.6	2669.6	2651.3	2646.7	2604.1	2605.6	2640.6
20°	2637.6	2585.8	2572.1	2521.9	2491.4	2409.2	2406.1	2383.3	2293.4	2320.8	2314.7
22.5°	2474.6	2386.3	2269.1	2211.2	2182.3	2095.5	2028.4	1981.2	1949.3	1917.3	1903.6
25°	2259.9	2116.8	1950.8	1836.6	1819.8	1739.1	1615.8	1557.9	1489.4	1468.0	1504.6
27.5°	1982.8	1797.0	1609.7	1434.5	1402.6	1329.5	1267.0	1225.9	1146.7	1142.1	1145.2
30°	1606.6	1419.3	1262.4	1148.2	1069.0	1035.5	994.4	964.0	932.0	944.2	947.2
32.5°	1320.3	1142.1	995.9	935.0	898.5	877.2	842.1	822.3	808.6	804.1	802.5
35°	1049.2	930.5	865.0	805.6	784.3	769.0	743.2	734.0	721.8	723.4	723.4
37.5°	898.5	799.5	750.8	720.3	700.5	692.9	676.1	667.0	659.4	656.4	660.9
40°	775.1	706.6	676.1	648.7	632.0	628.9	619.8	609.1	600.0	601.5	606.1
42.5°	685.3	645.7	609.1	587.8	575.6	571.1	563.5	555.8	555.8	551.3	549.8
45°	613.7	581.7	551.3	531.5	523.9	517.8	508.6	507.1	501.0	502.5	504.1
47.5°	549.8	523.9	501.0	481.2	473.6	472.1	462.9	456.9	456.9	455.3	453.8
50°	491.9	466.0	446.2	435.5	424.9	421.8	420.3	418.8	415.7	415.7	417.3
52.5°	444.7	418.8	403.6	394.4	388.3	385.3	385.3	383.8	383.8	383.8	382.2
55°	392.9	371.6	359.4	356.3	353.3	351.8	350.3	347.2	345.7	348.7	345.7
57.5°	344.2	336.6	325.9	322.8	315.2	315.2	310.7	307.6	304.6	307.6	307.6
60°	306.1	295.4	289.3	280.2	274.1	268.0	260.4	258.9	255.8	254.3	252.8
62.5°	266.5	257.4	242.1	228.4	219.3	213.2	210.2	208.6	208.6	207.1	207.1
65°	222.3	201.0	193.4	188.8	187.3	185.8	182.7	181.2	182.7	181.2	182.7
67.5°	173.6	170.6	166.0	162.9	161.4	159.9	159.9	158.4	158.4	158.4	158.4
70°	150.8	143.1	141.6	138.6	138.6	137.1	137.1	137.1	137.1	135.5	138.6
72.5°	124.9	120.3	118.8	117.3	117.3	117.3	115.7	115.7	115.7	114.2	115.7
75°	102.0	100.5	97.5	97.5	95.9	97.5	95.9	95.9	94.4	95.9	95.9
77.5°	82.2	80.7	79.2	79.2	77.7	77.7	77.7	77.7	77.7	77.7	79.2
80°	62.4	60.9	59.4	60.9	59.4	60.9	59.4	59.4	60.9	59.4	59.4
82.5°	45.7	44.2	44.2	42.6	42.6	42.6	42.6	42.6	42.6	42.6	42.6
85°	27.4	25.9	25.9	27.4	25.9	27.4	25.9	25.9	25.9	27.4	27.4
87.5°	12.2	13.7	12.2	12.2	12.2	12.2	12.2	12.2	12.2	12.2	13.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P997686

CATALOG NUMBER: SA2XXRDP-B1005DB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4
2.5°	2310.2	2299.5	2296.5	2299.5	2296.5	2298.0	2287.3	2247.7	2258.4	2241.6	2250.8
5°	2441.1	2432.0	2412.2	2409.2	2406.1	2403.1	2387.8	2352.8	2339.1	2316.3	2314.7
7.5°	2566.0	2566.0	2550.8	2540.1	2526.4	2515.8	2496.0	2444.2	2422.9	2395.5	2380.2
10°	2689.4	2649.8	2666.5	2655.9	2622.4	2616.3	2579.7	2549.3	2508.1	2480.7	2456.4
12.5°	2777.7	2765.5	2750.3	2741.1	2732.0	2712.2	2687.8	2610.2	2588.9	2534.0	2506.6
15°	2774.6	2767.0	2771.6	2771.6	2768.6	2764.0	2744.2	2687.8	2651.3	2598.0	2550.8
17.5°	2625.4	2645.2	2665.0	2678.7	2709.2	2722.9	2741.1	2707.6	2684.8	2639.1	2588.9
20°	2365.0	2413.7	2471.6	2483.8	2511.2	2591.9	2628.5	2657.4	2666.5	2651.3	2610.2
22.5°	2002.6	2043.7	2183.8	2180.7	2220.3	2316.3	2422.9	2509.7	2578.2	2616.3	2601.0
25°	1568.5	1626.4	1701.0	1757.4	1886.8	2030.0	2162.5	2301.0	2419.8	2524.9	2550.8
27.5°	1186.3	1262.4	1321.8	1396.5	1461.9	1631.0	1801.5	2017.8	2156.4	2355.9	2459.4
30°	959.4	994.4	1053.8	1088.8	1120.8	1250.3	1443.7	1656.9	1900.5	2130.5	2308.7
32.5°	819.3	843.7	887.8	903.1	936.6	1023.4	1145.2	1340.1	1591.4	1870.1	2104.6
35°	735.5	761.4	770.6	784.3	811.7	866.5	950.3	1091.9	1318.8	1591.4	1871.6
37.5°	664.0	677.7	703.6	712.7	721.8	763.0	819.3	918.3	1069.0	1292.9	1603.6
40°	613.7	621.3	635.0	642.6	648.7	677.7	727.9	794.9	906.1	1076.7	1363.0
42.5°	560.4	569.5	578.7	587.8	595.4	618.3	648.7	712.7	787.3	916.8	1123.9
45°	508.6	514.7	525.4	531.5	542.1	560.4	587.8	632.0	699.0	781.2	948.7
47.5°	461.4	469.0	473.6	481.2	488.8	508.6	534.5	563.5	618.3	699.0	820.8
50°	418.8	427.9	434.0	435.5	441.6	459.9	481.2	513.2	548.2	610.7	717.3
52.5°	388.3	389.9	394.4	400.5	399.0	409.6	429.4	453.8	490.4	540.6	618.3
55°	353.3	357.9	360.9	362.4	362.4	371.6	382.2	405.1	434.0	475.1	540.6
57.5°	309.1	313.7	322.8	325.9	330.5	335.0	339.6	354.8	379.2	418.8	472.1
60°	263.5	266.5	275.6	281.7	284.8	297.0	303.0	315.2	328.9	357.9	408.1
62.5°	211.7	214.7	219.3	225.4	231.5	249.7	265.0	277.2	287.8	307.6	348.7
65°	184.3	185.8	188.8	190.4	191.9	199.5	213.2	230.0	249.7	265.0	289.3
67.5°	159.9	161.4	162.9	166.0	167.5	169.0	175.1	179.7	199.5	220.8	239.1
70°	137.1	140.1	141.6	141.6	143.1	146.2	149.2	155.3	161.4	172.1	194.9
72.5°	115.7	117.3	120.3	120.3	120.3	123.4	126.4	129.4	132.5	138.6	147.7
75°	95.9	99.0	99.0	99.0	100.5	100.5	103.6	106.6	109.6	114.2	117.3
77.5°	79.2	79.2	79.2	79.2	80.7	80.7	82.2	85.3	86.8	88.3	91.4
80°	59.4	60.9	60.9	60.9	62.4	62.4	62.4	65.5	67.0	67.0	70.1
82.5°	44.2	44.2	44.2	45.7	44.2	45.7	45.7	47.2	45.7	47.2	48.7
85°	27.4	27.4	27.4	28.9	28.9	28.9	28.9	28.9	28.9	28.9	30.5
87.5°	13.7	13.7	13.7	13.7	13.7	13.7	13.7	13.7	15.2	13.7	13.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P997686

CATALOG NUMBER: SA2XXRDP-B1005DB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4
2.5°	2237.1	2229.5	2229.5	2224.9	2224.9	2200.5	2200.5	2208.1	2199.0	2188.3	2173.1
5°	2294.9	2278.2	2273.6	2267.5	2247.7	2217.3	2205.1	2200.5	2182.3	2159.4	2133.5
7.5°	2349.8	2322.4	2308.7	2294.9	2269.1	2226.4	2202.1	2185.3	2157.9	2122.9	2089.4
10°	2403.1	2368.0	2333.0	2316.3	2279.7	2226.4	2191.4	2164.0	2124.4	2077.2	2030.0
12.5°	2451.8	2378.7	2372.6	2339.1	2285.8	2224.9	2171.6	2132.0	2081.7	2026.9	1972.1
15°	2494.4	2419.8	2383.3	2352.8	2282.8	2206.6	2150.3	2101.5	2034.5	1972.1	1905.1
17.5°	2515.8	2435.1	2410.7	2360.4	2288.9	2189.9	2113.7	2054.3	1981.2	1906.6	1830.5
20°	2537.1	2442.7	2403.1	2368.0	2270.6	2157.9	2072.6	2004.1	1923.4	1835.0	1751.3
22.5°	2547.7	2442.7	2395.5	2346.7	2252.3	2122.9	2022.4	1941.6	1847.2	1757.4	1656.9
25°	2529.5	2433.5	2377.2	2326.9	2220.3	2080.2	1964.5	1873.1	1772.6	1670.6	1568.5
27.5°	2483.8	2412.2	2346.7	2294.9	2176.2	2025.4	1903.6	1800.0	1696.5	1582.3	1478.7
30°	2398.5	2366.5	2314.7	2256.9	2127.4	1976.7	1832.0	1725.4	1611.2	1497.0	1388.8
32.5°	2266.0	2293.4	2259.9	2209.7	2069.6	1909.7	1755.9	1647.7	1522.9	1399.5	1300.5
35°	2104.6	2202.1	2183.8	2148.8	2008.7	1838.1	1684.3	1553.3	1428.4	1303.6	1204.6
37.5°	1927.9	2075.7	2090.9	2069.6	1938.6	1765.0	1596.0	1468.0	1340.1	1213.7	1113.2
40°	1685.8	1912.7	1961.4	1970.6	1865.5	1676.7	1500.0	1375.1	1248.7	1125.4	1003.6
42.5°	1463.5	1749.8	1810.7	1848.8	1772.6	1589.9	1411.7	1273.1	1148.2	1037.1	915.2
45°	1254.8	1553.3	1652.3	1701.0	1667.5	1490.9	1306.6	1177.2	1063.0	960.9	843.7
47.5°	1040.1	1340.1	1478.7	1556.4	1556.4	1390.4	1206.1	1078.2	968.5	881.7	778.2
50°	897.0	1146.7	1289.9	1391.9	1419.3	1288.3	1114.7	989.9	886.3	791.9	712.7
52.5°	764.5	988.3	1107.1	1213.7	1292.9	1178.7	1012.7	900.0	798.0	709.7	647.2
55°	660.9	828.4	936.6	1053.8	1142.1	1067.5	913.7	804.1	715.7	642.6	589.3
57.5°	561.9	708.1	796.5	900.0	994.4	938.1	814.7	720.3	642.6	578.7	531.5
60°	478.2	597.0	665.5	746.2	863.5	823.9	721.8	635.0	572.6	514.7	475.1
62.5°	406.6	501.0	558.9	616.8	723.4	705.1	625.9	558.9	505.6	456.9	423.4
65°	333.5	411.2	456.9	507.1	592.4	600.0	536.0	488.8	440.1	397.5	367.0
67.5°	269.5	330.5	371.6	414.2	482.7	504.1	459.9	420.3	379.2	344.2	316.8
70°	217.8	260.4	290.9	324.4	380.7	406.6	383.8	356.3	322.8	293.9	269.5
72.5°	172.1	199.5	217.8	243.7	289.3	315.2	313.7	289.3	265.0	245.2	225.4
75°	126.4	147.7	162.9	179.7	216.2	240.6	246.7	236.0	211.7	196.4	181.2
77.5°	95.9	108.1	115.7	127.9	153.8	175.1	184.3	181.2	164.5	152.3	141.6
80°	73.1	76.1	79.2	83.8	105.1	124.9	131.0	129.4	120.3	115.7	103.6
82.5°	51.8	53.3	54.8	56.3	64.0	80.7	86.8	89.8	82.2	77.7	67.0
85°	30.5	32.0	32.0	35.0	36.5	41.1	51.8	51.8	50.3	44.2	42.6
87.5°	15.2	15.2	13.7	13.7	15.2	16.8	19.8	22.8	19.8	18.3	16.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P997686

CATALOG NUMBER: SA2XXRDP-B1005DB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4
2.5°	2167.0	2168.6	2173.1	2159.4	2138.1	2129.0	2101.5	2097.0	2092.4	2092.4	2097.0
5°	2118.3	2112.2	2113.7	2087.8	2057.4	2039.1	2001.0	2007.1	1987.3	1975.1	1978.2
7.5°	2065.0	2048.2	2046.7	2013.2	1975.1	1941.6	1902.1	1892.9	1874.6	1853.3	1844.2
10°	1998.0	1985.8	1963.0	1924.9	1876.2	1848.8	1795.5	1763.5	1758.9	1726.9	1714.7
12.5°	1929.5	1908.1	1885.3	1832.0	1777.2	1733.0	1693.4	1658.4	1634.0	1606.6	1588.3
15°	1850.3	1824.4	1798.5	1742.2	1678.2	1634.0	1574.6	1522.9	1451.3	1394.9	1363.0
17.5°	1763.5	1734.5	1699.5	1637.1	1574.6	1513.7	1404.1	1343.2	1292.9	1259.4	1239.6
20°	1673.6	1641.6	1606.6	1544.2	1436.1	1329.5	1268.5	1221.3	1190.9	1157.4	1133.0
22.5°	1579.2	1545.7	1507.6	1410.2	1296.0	1221.3	1174.1	1130.0	1085.8	1067.5	1055.3
25°	1490.9	1460.4	1411.7	1279.2	1189.4	1120.8	1067.5	1038.6	1015.7	991.4	968.5
27.5°	1399.5	1343.2	1274.6	1163.5	1107.1	1037.1	999.0	977.7	938.1	921.3	910.7
30°	1289.9	1227.4	1161.9	1082.8	1017.3	968.5	933.5	898.5	875.6	858.9	840.6
32.5°	1178.7	1119.3	1078.2	995.9	947.2	897.0	863.5	842.1	808.6	798.0	790.4
35°	1082.8	1032.5	995.9	928.9	883.3	837.6	813.2	781.2	759.9	740.1	727.9
37.5°	988.3	960.9	922.9	866.5	817.8	781.2	747.7	737.1	708.1	697.5	685.3
40°	922.9	881.7	849.8	801.0	759.9	720.3	699.0	674.6	654.8	638.1	633.5
42.5°	843.7	813.2	794.9	741.6	699.0	676.1	650.3	622.8	607.6	593.9	577.2
45°	784.3	756.9	731.0	688.3	650.3	621.3	598.5	580.2	554.3	548.2	522.3
47.5°	721.8	694.4	674.6	632.0	597.0	569.5	552.8	528.4	507.1	493.4	481.2
50°	659.4	636.6	618.3	581.7	551.3	522.3	499.5	475.1	466.0	443.2	435.5
52.5°	600.0	584.8	565.0	530.0	499.5	475.1	450.8	431.0	417.3	405.1	395.9
55°	549.8	525.4	516.2	478.2	452.3	426.4	405.1	392.9	376.1	368.5	360.9
57.5°	493.4	479.7	464.5	435.5	406.6	382.2	367.0	348.7	339.6	330.5	324.4
60°	444.7	424.9	412.7	388.3	362.4	339.6	325.9	312.2	300.0	292.4	280.2
62.5°	388.3	373.1	365.5	339.6	318.3	297.0	284.8	271.1	261.9	248.2	233.0
65°	339.6	327.4	318.3	297.0	277.2	257.4	245.2	228.4	216.2	208.6	207.1
67.5°	297.0	287.8	274.1	254.3	234.5	219.3	205.6	191.9	190.4	187.3	187.3
70°	249.7	240.6	233.0	211.7	194.9	178.2	175.1	170.6	166.0	164.5	161.4
72.5°	208.6	201.0	191.9	173.6	156.9	152.3	149.2	146.2	141.6	140.1	138.6
75°	169.0	158.4	152.3	135.5	131.0	127.9	124.9	120.3	117.3	115.7	112.7
77.5°	129.4	118.8	118.8	109.6	106.6	102.0	99.0	95.9	94.4	91.4	91.4
80°	91.4	91.4	88.3	83.8	79.2	77.7	73.1	71.6	70.1	71.6	68.5
82.5°	67.0	60.9	60.9	57.9	54.8	53.3	50.3	50.3	48.7	48.7	48.7
85°	38.1	38.1	36.5	33.5	32.0	32.0	30.5	30.5	28.9	28.9	27.4
87.5°	15.2	13.7	15.2	13.7	13.7	12.2	12.2	12.2	10.7	12.2	10.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P997686

CATALOG NUMBER: SA2XXRDP-B1005DB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4
2.5°	2097.0	2093.9	2084.8	2087.8	2083.3	2083.3	2080.2	2080.2	2080.2	2087.8	2083.3
5°	1982.8	1972.1	1961.4	1956.9	1952.3	1947.7	1947.7	1946.2	1959.9	1956.9	1969.1
7.5°	1841.1	1838.1	1816.8	1816.8	1809.2	1806.1	1813.7	1815.2	1816.8	1819.8	1827.4
10°	1714.7	1707.1	1676.7	1679.7	1675.1	1669.1	1673.6	1670.6	1681.2	1684.3	1681.2
12.5°	1565.5	1551.8	1518.3	1501.5	1483.3	1469.6	1486.3	1474.1	1516.8	1529.0	1562.5
15°	1367.5	1341.6	1318.8	1318.8	1302.0	1289.9	1297.5	1311.2	1320.3	1334.0	1340.1
17.5°	1235.0	1224.4	1206.1	1195.4	1190.9	1186.3	1186.3	1192.4	1212.2	1210.7	1222.9
20°	1122.3	1116.3	1107.1	1093.4	1088.8	1085.8	1085.8	1085.8	1099.5	1111.7	1119.3
22.5°	1044.7	1040.1	1034.0	1015.7	1006.6	1003.6	1011.2	1015.7	1026.4	1035.5	1043.2
25°	967.0	956.4	945.7	939.6	935.0	935.0	938.1	939.6	944.2	948.7	957.9
27.5°	903.1	895.4	880.2	863.5	863.5	858.9	861.9	865.0	875.6	890.9	898.5
30°	831.5	830.0	823.9	817.8	811.7	808.6	814.7	819.3	820.8	828.4	828.4
32.5°	779.7	769.0	758.4	752.3	749.2	747.7	749.2	755.3	755.3	764.5	775.1
35°	727.9	721.8	711.2	700.5	697.5	689.9	695.9	702.0	712.7	717.3	721.8
37.5°	671.6	664.0	659.4	656.4	650.3	651.8	647.2	656.4	665.5	664.0	667.0
40°	628.9	615.2	601.5	600.0	598.5	597.0	597.0	598.5	604.6	610.7	619.8
42.5°	574.1	569.5	557.4	545.2	542.1	539.1	536.0	542.1	554.3	565.0	569.5
45°	517.8	511.7	508.6	499.5	493.4	491.9	488.8	496.5	507.1	511.7	514.7
47.5°	466.0	464.5	455.3	456.9	452.3	453.8	452.3	456.9	456.9	461.4	464.5
50°	431.0	426.4	421.8	418.8	414.2	414.2	412.7	414.2	420.3	426.4	424.9
52.5°	395.9	388.3	386.8	385.3	382.2	385.3	380.7	382.2	388.3	391.4	389.9
55°	354.8	353.3	350.3	347.2	345.7	344.2	344.2	344.2	350.3	354.8	356.3
57.5°	322.8	315.2	309.1	309.1	303.0	301.5	304.6	306.1	310.7	313.7	316.8
60°	278.7	275.6	266.5	261.9	252.8	251.3	251.3	257.4	265.0	275.6	278.7
62.5°	231.5	226.9	225.4	225.4	225.4	225.4	225.4	225.4	225.4	226.9	226.9
65°	205.6	207.1	205.6	204.1	205.6	205.6	204.1	204.1	204.1	205.6	207.1
67.5°	184.3	182.7	184.3	182.7	181.2	181.2	179.7	181.2	182.7	184.3	184.3
70°	159.9	159.9	158.4	159.9	158.4	156.9	155.3	155.3	158.4	159.9	159.9
72.5°	137.1	137.1	135.5	135.5	132.5	132.5	134.0	132.5	132.5	137.1	137.1
75°	114.2	112.7	111.2	111.2	109.6	109.6	109.6	108.1	111.2	111.2	112.7
77.5°	89.8	89.8	89.8	88.3	88.3	86.8	86.8	88.3	88.3	88.3	89.8
80°	68.5	68.5	68.5	67.0	65.5	65.5	65.5	65.5	65.5	67.0	65.5
82.5°	47.2	47.2	47.2	47.2	47.2	45.7	45.7	45.7	47.2	47.2	45.7
85°	28.9	27.4	28.9	28.9	27.4	28.9	27.4	27.4	25.9	25.9	27.4
87.5°	12.2	10.7	9.1	9.1	10.7	9.1	9.1	9.1	10.7	9.1	9.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P997686

CATALOG NUMBER: SA2XXRDP-B1005DB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4	2191.4
2.5°	2087.8	2095.5	2092.4	2075.7	2092.4	2097.0	2106.1	2115.3	2121.3	2130.5	2138.1
5°	1956.9	1972.1	1981.2	1972.1	2002.6	2007.1	2028.4	2040.6	2058.9	2074.1	2086.3
7.5°	1833.5	1845.7	1864.0	1867.0	1885.3	1906.6	1937.1	1967.5	1996.5	2011.7	2025.4
10°	1701.0	1722.4	1749.8	1743.7	1771.1	1804.6	1836.6	1885.3	1909.7	1937.1	1961.4
12.5°	1568.5	1582.3	1618.8	1631.0	1670.6	1696.5	1740.6	1771.1	1832.0	1864.0	1885.3
15°	1337.1	1393.4	1439.1	1493.9	1545.7	1594.4	1634.0	1688.9	1742.2	1766.5	1801.5
17.5°	1232.0	1257.9	1285.3	1312.7	1379.7	1466.5	1536.6	1596.0	1641.6	1673.6	1714.7
20°	1122.3	1148.2	1178.7	1204.6	1245.7	1308.1	1394.9	1497.0	1551.8	1585.3	1624.9
22.5°	1044.7	1069.0	1088.8	1111.7	1143.7	1189.4	1254.8	1381.2	1454.3	1495.4	1530.5
25°	960.9	991.4	1012.7	1029.5	1055.3	1105.6	1158.9	1230.5	1361.4	1393.4	1442.1
27.5°	903.1	912.2	936.6	962.4	988.3	1015.7	1070.6	1131.5	1219.8	1289.9	1349.3
30°	834.5	857.4	880.2	890.9	913.7	953.3	986.8	1052.3	1120.8	1175.6	1247.2
32.5°	782.7	796.5	811.7	837.6	858.9	886.3	919.8	974.6	1032.5	1067.5	1122.3
35°	724.9	734.0	766.0	776.7	798.0	825.4	858.9	901.5	964.0	991.4	1031.0
37.5°	670.1	691.4	700.5	724.9	744.7	772.1	796.5	845.2	886.3	918.3	954.8
40°	627.4	636.6	653.3	674.6	691.4	712.7	743.2	778.2	822.3	848.2	880.2
42.5°	575.6	583.3	604.6	616.8	644.2	664.0	682.2	724.9	764.5	784.3	816.3
45°	519.3	537.6	551.3	575.6	590.9	615.2	638.1	668.5	705.1	727.9	746.2
47.5°	470.6	488.8	502.5	525.4	549.8	560.4	584.8	616.8	650.3	668.5	694.4
50°	431.0	437.1	462.9	473.6	499.5	520.8	537.6	565.0	601.5	612.2	633.5
52.5°	392.9	397.5	414.2	427.9	450.8	469.0	490.4	516.2	546.7	563.5	580.2
55°	359.4	362.4	370.1	385.3	400.5	423.4	443.2	467.5	493.4	511.7	526.9
57.5°	321.3	327.4	333.5	342.6	357.9	379.2	400.5	423.4	444.7	456.9	476.7
60°	277.2	286.3	297.0	307.6	318.3	333.5	357.9	379.2	399.0	409.6	424.9
62.5°	230.0	248.2	257.4	269.5	278.7	292.4	310.7	335.0	348.7	362.4	374.6
65°	207.1	208.6	210.2	222.3	239.1	252.8	269.5	287.8	309.1	318.3	327.4
67.5°	184.3	185.8	188.8	190.4	196.4	211.7	230.0	249.7	266.5	272.6	281.7
70°	161.4	161.4	167.5	169.0	170.6	172.1	187.3	207.1	222.3	230.0	240.6
72.5°	137.1	138.6	141.6	143.1	146.2	149.2	153.8	164.5	182.7	190.4	202.5
75°	112.7	114.2	115.7	117.3	121.8	123.4	127.9	134.0	141.6	150.8	158.4
77.5°	89.8	89.8	91.4	94.4	97.5	99.0	103.6	106.6	109.6	114.2	120.3
80°	67.0	68.5	68.5	71.6	71.6	73.1	74.6	79.2	82.2	85.3	88.3
82.5°	45.7	48.7	48.7	48.7	50.3	51.8	53.3	53.3	56.3	57.9	62.4
85°	27.4	28.9	28.9	28.9	27.4	30.5	30.5	32.0	32.0	32.0	33.5
87.5°	10.7	9.1	10.7	10.7	10.7	12.2	10.7	10.7	12.2	13.7	13.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P997686

CATALOG NUMBER: SA2XXRDP-B1005DB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	2191.4	2191.4	2191.4	2191.4
2.5°	2151.8	2147.2	2174.6	2205.1
5°	2107.6	2115.3	2150.3	2192.9
7.5°	2062.0	2078.7	2119.8	2176.2
10°	1998.0	2028.4	2090.9	2148.8
12.5°	1935.6	1976.7	2036.1	2104.6
15°	1865.5	1911.2	1984.3	2066.5
17.5°	1787.8	1839.6	1924.9	2014.7
20°	1705.6	1774.1	1864.0	1961.4
22.5°	1614.2	1696.5	1789.4	1897.5
25°	1525.9	1615.8	1708.6	1833.5
27.5°	1439.1	1527.4	1631.0	1757.4
30°	1352.3	1433.0	1544.2	1679.7
32.5°	1259.4	1343.2	1460.4	1599.0
35°	1174.1	1257.9	1367.5	1504.6
37.5°	1082.8	1172.6	1277.7	1419.3
40°	976.2	1081.2	1183.3	1318.8
42.5°	887.8	999.0	1098.0	1225.9
45°	817.8	922.9	1005.1	1130.0
47.5°	752.3	837.6	921.3	1037.1
50°	689.9	755.3	842.1	945.7
52.5°	625.9	682.2	756.9	854.3
55°	568.0	621.3	688.3	763.0
57.5°	514.7	552.8	619.8	686.8
60°	455.3	494.9	546.7	603.1
62.5°	405.1	435.5	484.3	531.5
65°	351.8	380.7	417.3	461.4
67.5°	303.0	328.9	357.9	392.9
70°	258.9	278.7	300.0	330.5
72.5°	211.7	233.0	252.8	277.2
75°	173.6	182.7	199.5	216.2
77.5°	134.0	146.2	155.3	169.0
80°	95.9	106.6	109.6	120.3
82.5°	64.0	70.1	76.1	79.2
85°	36.5	39.6	45.7	47.2
87.5°	13.7	15.2	18.3	21.3
90°	0.0	0.0	0.0	0.0

TEST NUMBER: P997686

CATALOG NUMBER: SA2XXRDP-B1005DB2750-4F0-XX-W2A-A_2700K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	23.36	24.81	23.72	25.12	25.44	17.77	19.22	18.14	19.54	19.85
	3H	24.69	25.99	25.06	26.31	26.68	18.90	20.20	19.28	20.53	20.89
	4H	25.11	26.33	25.51	26.68	27.06	19.36	20.58	19.76	20.93	21.31
	6H	25.39	26.51	25.80	26.88	27.27	19.74	20.86	20.15	21.23	21.62
	8H	25.46	26.53	25.89	26.92	27.32	19.86	20.93	20.29	21.32	21.72
	12H	25.50	26.52	25.93	26.90	27.33	19.94	20.96	20.38	21.35	21.78
4H	2H	23.33	24.55	23.73	24.90	25.28	18.45	19.67	18.86	20.02	20.40
	3H	24.78	25.78	25.19	26.19	26.59	19.75	20.75	20.16	21.15	21.56
	4H	25.28	26.19	25.72	26.60	27.04	20.30	21.21	20.74	21.62	22.06
	6H	25.66	26.44	26.12	26.89	27.35	20.79	21.57	21.24	22.01	22.48
	8H	25.77	26.50	26.24	26.95	27.42	20.95	21.68	21.41	22.13	22.60
	12H	25.85	26.50	26.33	26.98	27.45	21.07	21.72	21.55	22.20	22.67
8H	4H	25.27	26.00	25.74	26.45	26.92	20.62	21.36	21.09	21.80	22.27
	6H	25.69	26.29	26.19	26.79	27.26	21.21	21.81	21.71	22.30	22.78
	8H	25.83	26.37	26.35	26.89	27.38	21.44	21.98	21.95	22.49	22.98
	12H	25.95	26.43	26.46	26.92	27.49	21.63	22.10	22.14	22.60	23.16
12H	4H	25.25	25.90	25.73	26.38	26.85	20.66	21.31	21.14	21.79	22.26
	6H	25.66	26.21	26.18	26.72	27.21	21.27	21.81	21.78	22.32	22.81
	8H	25.84	26.32	26.35	26.81	27.38	21.55	22.03	22.06	22.52	23.09