

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000735

Luminaire Tested: SA4XXDIP-B1020D590UB40-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000735
REPORT IS A COMBINATION OF REPORTS P995348 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B1020D590UB40-4F0-XX-W2A-F1
Description: Define 4 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6417.0 lumens
Efficiency: N/A
Efficacy: 103.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 62.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000735

CATALOG NUMBER: SA4XXDIP-B1020D590UB40-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1000735

CATALOG NUMBER: SA4XXDIP-B1020D590UB40-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	105	105	105	105	93	93	93	83	83	83	73	73	73
1	102	97	93	90	96	92	88	85	82	79	77	73	71	69	64	63	61
2	93	85	79	73	87	80	75	70	72	67	64	64	61	58	57	54	52
3	85	75	67	61	80	71	64	59	63	58	54	57	52	49	50	47	44
4	77	66	58	52	73	63	55	50	56	50	46	50	46	42	45	41	38
5	71	59	51	45	67	56	49	43	51	44	40	45	40	36	40	36	33
6	66	53	45	39	62	51	43	37	46	39	35	41	36	32	37	33	29
7	61	48	40	34	57	46	38	33	41	35	31	37	32	28	34	29	26
8	57	44	36	30	53	42	34	29	38	32	27	34	29	25	31	27	23
9	53	40	32	27	50	38	31	26	35	29	25	32	26	23	29	24	21
10	49	37	29	25	47	35	28	24	32	26	22	29	24	21	26	22	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13906	13906	13906
5°	13917	13506	13522
10°	13800	13130	13039
15°	13602	12685	12494
20°	13349	12203	11929
25°	13064	11693	11321
30°	12721	11142	10654
35°	12365	10579	10010
40°	11995	9972	9324
45°	11608	9363	8683
50°	11177	8773	7973
55°	10710	8084	7267
60°	10231	7329	6533
65°	9684	6550	5705
70°	9053	5611	4818
75°	8112	4522	3859
80°	6914	3269	2714
85°	5370	1822	1461

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11608 cd/sqm

TEST NUMBER: P1000735

CATALOG NUMBER: SA4XXDIP-B1020D590UB40-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.7	2.5
10°-20°	452.8	7.1
20°-30°	666.4	10.4
30°-40°	774.7	12.1
40°-50°	774.6	12.1
50°-60°	677.5	10.6
60°-70°	503.0	7.8
70°-80°	285.4	4.4
80°-90°	83.3	1.3
90°-100°	47.9	0.7
100°-110°	143.4	2.2
110°-120°	243.7	3.8
120°-130°	321.4	5.0
130°-140°	360.9	5.6
140°-150°	354.8	5.5
150°-160°	298.4	4.6
160°-170°	198.5	3.1
170°-180°	69.5	1.1
0°-30°	1280.0	19.9
0°-40°	2054.7	32.0
0°-60°	3506.8	54.6
0°-90°	4378.6	68.2
90°-120°	435.0	6.8
90°-150°	1472.0	22.9
90°-180°	2038.0	31.8
0°-180°	6417.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1705	1705	1705	1705	1705	
5°	1704	1698	1683	1698	1696	162
15°	1622	1616	1596	1604	1600	457
25°	1469	1459	1440	1442	1436	676
35°	1264	1254	1235	1226	1219	790
45°	1032	1022	1000	985	981	795
55°	780	776	757	741	732	699
65°	529	522	508	495	488	523
75°	282	275	268	262	261	299
85°	74	74	71	71	70	79
90°	2	8	12	16	17	7
95°	34	39	43	45	45	37
105°	132	133	135	137	139	140
115°	248	248	247	246	246	244
125°	361	361	360	359	358	322
135°	465	469	469	468	466	360
145°	565	568	568	568	566	354
155°	648	648	647	649	647	298
165°	705	703	702	706	703	199
175°	734	731	730	734	730	70
180°	735	735	735	735	735	

TEST NUMBER: P1000735

CATALOG NUMBER: SA4XXDIP-B1020D590UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1705.3	1705.3	1705.3	1705.3	1705.3
2.5°	1710.8	1706.7	1691.6	1705.3	1703.9
5°	1703.9	1698.5	1683.4	1698.5	1695.7
7.5°	1691.6	1686.2	1669.8	1682.1	1680.7
10°	1673.9	1668.4	1650.6	1661.6	1658.8
12.5°	1650.6	1645.2	1626.1	1638.4	1634.3
15°	1622.0	1616.5	1596.0	1604.2	1600.1
17.5°	1589.2	1582.3	1563.2	1568.7	1565.9
20°	1552.3	1545.4	1524.9	1529.0	1526.3
22.5°	1512.6	1503.1	1482.6	1490.8	1485.3
25°	1468.9	1459.3	1440.2	1441.6	1436.1
27.5°	1419.7	1410.2	1392.4	1389.7	1382.8
30°	1370.5	1359.6	1341.8	1336.4	1329.5
32.5°	1318.6	1309.0	1289.9	1283.1	1276.2
35°	1263.9	1254.4	1235.3	1225.7	1218.9
37.5°	1206.6	1198.4	1177.9	1168.3	1158.7
40°	1150.5	1139.6	1119.1	1105.4	1098.6
42.5°	1090.4	1084.9	1061.7	1045.3	1041.2
45°	1031.7	1022.1	1000.2	985.2	981.1
47.5°	970.2	963.3	942.8	926.4	915.5
50°	907.3	901.8	882.7	863.6	855.4
52.5°	845.8	839.0	818.5	802.1	791.2
55°	780.2	776.1	757.0	740.6	732.4
57.5°	718.7	714.6	695.5	679.1	670.9
60°	654.5	647.7	629.9	617.6	610.8
62.5°	591.7	586.2	567.1	556.1	549.3
65°	528.8	522.0	508.3	494.6	487.8
67.5°	464.6	459.1	445.5	431.8	430.4
70°	405.8	396.3	385.3	374.4	370.3
72.5°	343.0	333.4	325.2	317.0	312.9
75°	281.5	274.7	267.8	262.4	261.0
77.5°	221.4	218.6	211.8	210.4	206.3
80°	168.1	164.0	161.2	158.5	157.1
82.5°	116.1	114.8	114.8	113.4	112.0
85°	73.8	73.8	71.1	71.1	69.7
87.5°	35.5	34.2	32.8	32.8	32.8
90°	1.7	8.0	12.5	15.9	17.0
92.5°	14.8	22.2	25.0	26.7	27.3
95°	34.1	39.2	43.2	44.9	44.9
97.5°	54.5	59.1	63.6	65.9	65.9
100°	79.5	81.8	86.9	88.1	88.1
102.5°	105.7	106.3	110.8	112.5	113.1
105°	132.4	133.0	135.2	136.9	138.6
107.5°	160.2	160.8	161.4	163.6	163.1
110°	188.6	189.8	189.2	188.1	189.8



TEST NUMBER: P1000735

CATALOG NUMBER: SA4XXDIP-B1020D590UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	218.2	218.2	217.0	217.0	217.0
115°	247.7	247.7	246.6	246.0	245.5
117.5°	275.6	275.6	275.0	273.3	271.6
120°	303.4	305.7	304.0	301.1	302.3
122.5°	332.4	333.0	332.4	330.7	327.8
125°	360.8	360.8	360.2	359.1	358.0
127.5°	386.4	388.1	386.9	385.8	385.2
130°	413.6	415.3	415.3	414.2	411.9
132.5°	441.5	442.6	442.0	440.9	440.3
135°	465.3	468.8	468.8	467.6	465.9
137.5°	492.1	493.8	494.9	493.2	493.8
140°	518.8	519.9	519.9	519.3	518.8
142.5°	543.2	544.3	543.8	543.8	543.8
145°	565.3	567.6	568.2	567.6	565.9
147.5°	588.1	590.9	590.3	589.8	589.2
150°	608.5	610.8	610.8	610.8	610.2
152.5°	627.8	629.0	629.6	631.3	629.6
155°	647.7	647.7	647.2	649.4	647.2
157.5°	664.8	663.6	663.6	665.3	663.6
160°	679.6	679.0	678.4	680.1	677.3
162.5°	693.2	691.5	690.9	694.3	691.5
165°	705.1	703.4	702.3	705.7	703.4
167.5°	714.8	712.5	712.5	715.9	712.5
170°	722.7	719.9	720.5	723.9	719.9
172.5°	728.4	726.1	726.1	730.1	726.1
175°	733.5	730.7	730.1	734.1	730.1
177.5°	735.8	733.0	733.0	736.9	732.4
180°	734.7	734.7	734.7	734.7	734.7

(END OF REPORT)