

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P997687

Luminaire Tested: SA2XXRDP-B1005DB2750-4F0-XX-W2A-A_3000K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P997687
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-29)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDP-B1005DB2750-4F0-XX-W2A-A_3000K
Description: Define 2 Regressed Direct Recessed with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3819.0 lumens
Efficiency: N/A
Efficacy: 62.3 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 61.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P997687

CATALOG NUMBER: SA2XXRDP-B1005DB2750-4F0-XX-W2A-A_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P997687

CATALOG NUMBER: SA2XXRDP-B1005DB2750-4F0-XX-W2A-A_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10		0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102		100
1	111	106	103	100	108	104	101	98	100	97	95		96	94	92		93	91	89		87
2	102	95	89	84	100	93	88	83	90	85	81		87	83	80		84	81	78		76
3	94	85	78	72	92	84	77	72	81	75	71		78	73	69		76	72	68		66
4	87	77	69	63	85	76	68	63	73	67	62		71	66	61		69	64	60		59
5	81	70	62	56	79	69	61	56	67	60	55		65	59	55		63	58	54		52
6	76	64	56	50	74	63	55	50	61	54	49		60	54	49		58	53	49		47
7	71	59	51	45	69	58	50	45	56	50	45		55	49	44		54	48	44		42
8	66	54	46	41	65	53	46	41	52	45	41		51	45	40		50	44	40		39
9	62	50	43	38	61	50	42	37	49	42	37		47	41	37		47	41	37		35
10	59	47	39	35	58	46	39	35	45	39	34		44	38	34		44	38	34		33

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	34981	34981	34981	34981
5°	35139	39068	35261	31211
10°	34830	43345	35077	27055
15°	34152	45477	34730	21317
20°	33320	39424	34044	18445
25°	32294	25856	32991	16468
30°	30961	17404	31804	14906
35°	29320	14097	30269	13444
40°	27481	12535	28656	12440
45°	25509	11345	26574	11103
50°	23486	10326	24582	10286
55°	21234	9706	22379	9579
60°	19252	8120	20274	8022
65°	17428	6847	18465	7764
70°	15426	6327	16634	7322
75°	13339	5920	14556	6764
80°	11057	5460	11896	6016
85°	8645	5013	9481	5303

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 160°

Vertical Angle: 45°

Luminance: 38401 cd/sqm

TEST NUMBER: P997687

CATALOG NUMBER: SA2XXRDP-B1005DB2750-4F0-XX-W2A-A_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	209.6	5.5
10°-20°	585.1	15.3
20°-30°	753.0	19.7
30°-40°	714.4	18.7
40°-50°	612.2	16.0
50°-60°	466.2	12.2
60°-70°	294.0	7.7
70°-80°	146.7	3.8
80°-90°	37.7	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1547.7	40.5
0°-40°	2262.1	59.2
0°-60°	3340.6	87.5
0°-90°	3819.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3819.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2210	2210	2210	2210	2210	
5°	2211	2459	2219	1964	2211	210
15°	2084	2775	2119	1301	2084	586
25°	1849	1480	1889	943	1849	849
35°	1517	730	1566	696	1517	949
45°	1140	507	1187	496	1140	880
55°	769	352	811	347	769	693
65°	465	183	493	207	465	462
75°	218	97	238	111	218	236
85°	48	28	52	29	48	57
90°	0	0	0	0	0	

TEST NUMBER: P997687

CATALOG NUMBER: SA2XXRDP-B1005DB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9
2.5°	2223.7	2232.9	2237.6	2243.7	2257.5	2266.7	2280.6	2283.6	2282.1	2288.2	2271.3
5°	2211.4	2231.4	2249.8	2265.2	2289.8	2305.1	2322.0	2342.0	2346.6	2369.6	2355.8
7.5°	2194.6	2223.7	2249.8	2280.6	2317.4	2337.4	2363.5	2394.2	2408.0	2435.7	2443.3
10°	2166.9	2208.4	2252.9	2285.2	2335.8	2371.2	2395.7	2444.9	2477.1	2518.6	2512.4
12.5°	2122.4	2176.1	2236.0	2289.8	2355.8	2378.8	2424.9	2475.6	2517.1	2555.4	2589.2
15°	2084.0	2145.4	2211.4	2277.5	2352.7	2395.7	2441.8	2507.8	2552.4	2619.9	2649.1
17.5°	2031.8	2110.1	2188.4	2262.1	2351.2	2400.3	2457.2	2521.7	2587.7	2652.2	2675.2
20°	1978.0	2062.5	2146.9	2246.8	2348.1	2395.7	2454.1	2533.9	2598.4	2649.1	2649.1
22.5°	1913.5	2016.4	2113.2	2208.4	2318.9	2388.1	2447.9	2541.6	2587.7	2598.4	2557.0
25°	1849.0	1951.9	2057.9	2176.1	2302.1	2363.5	2431.1	2518.6	2533.9	2490.9	2383.4
27.5°	1772.2	1887.4	2007.2	2134.7	2266.7	2343.5	2404.9	2463.3	2434.1	2318.9	2151.6
30°	1693.9	1818.3	1953.4	2074.8	2234.5	2305.1	2357.3	2374.2	2282.1	2094.7	1878.2
32.5°	1612.5	1733.8	1876.7	2022.6	2183.8	2251.4	2285.2	2240.6	2071.7	1835.2	1571.0
35°	1517.3	1654.0	1802.9	1955.0	2114.7	2165.4	2185.3	2076.3	1859.8	1554.2	1291.5
37.5°	1431.3	1568.0	1727.7	1882.8	2037.9	2065.6	2045.6	1875.1	1600.2	1297.7	1041.2
40°	1329.9	1475.8	1632.5	1806.0	1933.5	1941.2	1892.0	1670.9	1329.9	1045.8	887.7
42.5°	1236.3	1383.7	1540.3	1716.9	1813.7	1787.6	1721.5	1431.3	1110.3	901.5	774.0
45°	1139.5	1279.3	1448.2	1604.8	1673.9	1612.5	1512.7	1204.0	932.2	775.5	677.3
47.5°	1045.8	1176.4	1343.8	1494.3	1506.5	1437.4	1319.2	1009.0	807.8	681.9	602.0
50°	953.7	1084.2	1240.9	1365.3	1353.0	1257.8	1124.2	876.9	701.8	602.0	536.0
52.5°	861.5	979.8	1131.8	1230.1	1177.9	1085.8	953.7	743.3	612.8	525.2	474.5
55°	769.4	880.0	1010.5	1091.9	1009.0	903.0	809.3	637.3	531.4	460.7	422.3
57.5°	692.6	780.1	899.9	949.1	849.3	766.3	684.9	548.3	460.7	410.0	365.5
60°	608.1	688.0	786.3	815.5	712.6	645.0	575.9	463.8	394.7	350.1	321.0
62.5°	536.0	602.0	677.3	677.3	586.6	536.0	483.8	388.5	331.7	296.4	282.6
65°	465.3	512.9	566.7	560.5	483.8	439.2	397.8	321.0	278.0	253.4	239.6
67.5°	396.2	433.1	468.4	446.9	391.6	353.2	314.8	259.5	230.4	213.5	195.0
70°	333.3	362.4	380.9	360.9	305.6	273.4	245.7	208.9	185.8	164.3	153.6
72.5°	279.5	291.8	297.9	273.4	227.3	208.9	188.9	162.8	142.8	132.1	129.0
75°	218.1	228.8	224.2	205.8	167.4	153.6	138.2	119.8	115.2	109.0	106.0
77.5°	170.5	170.5	162.8	145.9	119.8	109.0	102.9	93.7	89.1	87.5	84.5
80°	121.3	119.8	115.2	96.8	81.4	75.3	75.3	69.1	67.6	64.5	64.5
82.5°	79.9	79.9	73.7	58.4	53.8	52.2	50.7	47.6	47.6	46.1	46.1
85°	47.6	44.5	36.9	32.3	30.7	30.7	29.2	27.6	29.2	27.6	27.6
87.5°	21.5	16.9	12.3	12.3	12.3	12.3	12.3	12.3	12.3	12.3	12.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P997687

CATALOG NUMBER: SA2XXRDP-B1005DB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9
2.5°	2288.2	2291.3	2295.9	2317.4	2320.5	2326.6	2323.6	2323.6	2325.1	2322.0	2323.6
5°	2386.5	2391.1	2414.2	2440.3	2446.4	2440.3	2447.9	2458.7	2458.7	2458.7	2455.6
7.5°	2478.7	2495.6	2521.7	2560.1	2567.7	2575.4	2589.2	2580.0	2583.1	2596.9	2592.3
10°	2567.7	2592.3	2621.5	2653.7	2670.6	2681.4	2687.5	2701.3	2733.6	2696.7	2710.6
12.5°	2652.2	2687.5	2718.2	2753.6	2765.8	2779.7	2784.3	2796.6	2796.6	2795.0	2805.8
15°	2707.5	2739.7	2767.4	2790.4	2793.5	2790.4	2787.3	2788.9	2793.5	2775.1	2785.8
17.5°	2719.8	2722.8	2732.1	2722.8	2724.4	2692.1	2673.7	2669.1	2626.1	2627.6	2663.0
20°	2659.9	2607.7	2593.8	2543.2	2512.4	2429.5	2426.4	2403.4	2312.8	2340.4	2334.3
22.5°	2495.6	2406.5	2288.2	2229.9	2200.7	2113.2	2045.6	1998.0	1965.7	1933.5	1919.7
25°	2279.0	2134.7	1967.3	1852.1	1835.2	1753.8	1629.4	1571.0	1501.9	1480.4	1517.3
27.5°	1999.5	1812.2	1623.3	1446.7	1414.4	1340.7	1277.7	1236.3	1156.4	1151.8	1154.9
30°	1620.2	1431.3	1273.1	1157.9	1078.1	1044.3	1002.8	972.1	939.9	952.2	955.2
32.5°	1331.5	1151.8	1004.4	942.9	906.1	884.6	849.3	829.3	815.5	810.9	809.3
35°	1058.1	938.3	872.3	812.4	790.9	775.5	749.4	740.2	727.9	729.5	729.5
37.5°	906.1	806.3	757.1	726.4	706.4	698.8	681.9	672.6	665.0	661.9	666.5
40°	781.7	712.6	681.9	654.2	637.3	634.3	625.0	614.3	605.1	606.6	611.2
42.5°	691.1	651.1	614.3	592.8	580.5	575.9	568.2	560.5	560.5	555.9	554.4
45°	618.9	586.6	555.9	536.0	528.3	522.1	512.9	511.4	505.3	506.8	508.3
47.5°	554.4	528.3	505.3	485.3	477.6	476.1	466.9	460.7	460.7	459.2	457.6
50°	496.0	469.9	450.0	439.2	428.5	425.4	423.9	422.3	419.3	419.3	420.8
52.5°	448.4	422.3	407.0	397.8	391.6	388.5	388.5	387.0	387.0	387.0	385.5
55°	396.2	374.7	362.4	359.4	356.3	354.8	353.2	350.1	348.6	351.7	348.6
57.5°	347.1	339.4	328.6	325.6	317.9	317.9	313.3	310.2	307.1	310.2	310.2
60°	308.7	297.9	291.8	282.6	276.4	270.3	262.6	261.1	258.0	256.5	254.9
62.5°	268.8	259.5	244.2	230.4	221.1	215.0	211.9	210.4	210.4	208.9	208.9
65°	224.2	202.7	195.0	190.4	188.9	187.4	184.3	182.8	184.3	182.8	184.3
67.5°	175.1	172.0	167.4	164.3	162.8	161.3	161.3	159.7	159.7	159.7	159.7
70°	152.0	144.4	142.8	139.8	139.8	138.2	138.2	138.2	138.2	136.7	139.8
72.5°	125.9	121.3	119.8	118.3	118.3	118.3	116.7	116.7	116.7	115.2	116.7
75°	102.9	101.4	98.3	98.3	96.8	98.3	96.8	96.8	95.2	96.8	96.8
77.5°	82.9	81.4	79.9	79.9	78.3	78.3	78.3	78.3	78.3	78.3	79.9
80°	63.0	61.4	59.9	61.4	59.9	61.4	59.9	59.9	61.4	59.9	59.9
82.5°	46.1	44.5	44.5	43.0	43.0	43.0	43.0	43.0	43.0	43.0	43.0
85°	27.6	26.1	26.1	27.6	26.1	27.6	26.1	26.1	26.1	27.6	27.6
87.5°	12.3	13.8	12.3	12.3	12.3	12.3	12.3	12.3	12.3	12.3	13.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P997687

CATALOG NUMBER: SA2XXRDP-B1005DB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9
2.5°	2329.7	2318.9	2315.9	2318.9	2315.9	2317.4	2306.7	2266.7	2277.5	2260.6	2269.8
5°	2461.8	2452.6	2432.6	2429.5	2426.4	2423.4	2408.0	2372.7	2358.9	2335.8	2334.3
7.5°	2587.7	2587.7	2572.3	2561.6	2547.8	2537.0	2517.1	2464.8	2443.3	2415.7	2400.3
10°	2712.1	2672.2	2689.1	2678.3	2644.5	2638.4	2601.5	2570.8	2529.3	2501.7	2477.1
12.5°	2801.2	2788.9	2773.5	2764.3	2755.1	2735.1	2710.6	2632.2	2610.7	2555.4	2527.8
15°	2798.1	2790.4	2795.0	2795.0	2792.0	2787.3	2767.4	2710.6	2673.7	2619.9	2572.3
17.5°	2647.6	2667.6	2687.5	2701.3	2732.1	2745.9	2764.3	2730.5	2707.5	2661.4	2610.7
20°	2385.0	2434.1	2492.5	2504.8	2532.4	2613.8	2650.7	2679.8	2689.1	2673.7	2632.2
22.5°	2019.5	2060.9	2202.2	2199.2	2239.1	2335.8	2443.3	2530.9	2600.0	2638.4	2623.0
25°	1581.8	1640.2	1715.4	1772.2	1902.8	2047.1	2180.7	2320.5	2440.3	2546.2	2572.3
27.5°	1196.3	1273.1	1333.0	1408.3	1474.3	1644.8	1816.8	2034.8	2174.6	2375.8	2480.2
30°	967.5	1002.8	1062.7	1098.0	1130.3	1260.8	1455.9	1670.9	1916.6	2148.5	2328.2
32.5°	826.2	850.8	895.3	910.7	944.5	1032.0	1154.9	1351.4	1604.8	1885.9	2122.4
35°	741.8	767.9	777.1	790.9	818.5	873.8	958.3	1101.1	1329.9	1604.8	1887.4
37.5°	669.6	683.4	709.5	718.7	727.9	769.4	826.2	926.0	1078.1	1303.8	1617.1
40°	618.9	626.6	640.4	648.1	654.2	683.4	734.1	801.6	913.8	1085.8	1374.5
42.5°	565.1	574.4	583.6	592.8	600.5	623.5	654.2	718.7	794.0	924.5	1133.4
45°	512.9	519.1	529.8	536.0	546.7	565.1	592.8	637.3	704.9	787.8	956.8
47.5°	465.3	473.0	477.6	485.3	493.0	512.9	539.0	568.2	623.5	704.9	827.8
50°	422.3	431.5	437.7	439.2	445.4	463.8	485.3	517.5	552.9	615.8	723.3
52.5°	391.6	393.1	397.8	403.9	402.4	413.1	433.1	457.6	494.5	545.2	623.5
55°	356.3	360.9	364.0	365.5	365.5	374.7	385.5	408.5	437.7	479.1	545.2
57.5°	311.8	316.4	325.6	328.6	333.3	337.9	342.5	357.8	382.4	422.3	476.1
60°	265.7	268.8	278.0	284.1	287.2	299.5	305.6	317.9	331.7	360.9	411.6
62.5°	213.5	216.5	221.1	227.3	233.4	251.9	267.2	279.5	290.3	310.2	351.7
65°	185.8	187.4	190.4	192.0	193.5	201.2	215.0	231.9	251.9	267.2	291.8
67.5°	161.3	162.8	164.3	167.4	168.9	170.5	176.6	181.2	201.2	222.7	241.1
70°	138.2	141.3	142.8	142.8	144.4	147.4	150.5	156.6	162.8	173.5	196.6
72.5°	116.7	118.3	121.3	121.3	121.3	124.4	127.5	130.5	133.6	139.8	149.0
75°	96.8	99.8	99.8	99.8	101.4	101.4	104.4	107.5	110.6	115.2	118.3
77.5°	79.9	79.9	79.9	79.9	81.4	81.4	82.9	86.0	87.5	89.1	92.1
80°	59.9	61.4	61.4	61.4	63.0	63.0	63.0	66.0	67.6	67.6	70.6
82.5°	44.5	44.5	44.5	46.1	44.5	46.1	46.1	47.6	46.1	47.6	49.1
85°	27.6	27.6	27.6	29.2	29.2	29.2	29.2	29.2	29.2	29.2	30.7
87.5°	13.8	13.8	13.8	13.8	13.8	13.8	13.8	13.8	15.4	13.8	13.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P997687

CATALOG NUMBER: SA2XXRDP-B1005DB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9
2.5°	2256.0	2248.3	2248.3	2243.7	2243.7	2219.1	2219.1	2226.8	2217.6	2206.8	2191.5
5°	2314.3	2297.4	2292.8	2286.7	2266.7	2236.0	2223.7	2219.1	2200.7	2177.7	2151.6
7.5°	2369.6	2342.0	2328.2	2314.3	2288.2	2245.2	2220.7	2203.8	2176.1	2140.8	2107.0
10°	2423.4	2388.1	2352.7	2335.8	2299.0	2245.2	2209.9	2182.3	2142.3	2094.7	2047.1
12.5°	2472.5	2398.8	2392.7	2358.9	2305.1	2243.7	2189.9	2150.0	2099.3	2044.1	1988.8
15°	2515.5	2440.3	2403.4	2372.7	2302.1	2225.3	2168.4	2119.3	2051.7	1988.8	1921.2
17.5°	2537.0	2455.6	2431.1	2380.4	2308.2	2208.4	2131.6	2071.7	1998.0	1922.7	1845.9
20°	2558.5	2463.3	2423.4	2388.1	2289.8	2176.1	2090.1	2021.0	1939.6	1850.6	1766.1
22.5°	2569.3	2463.3	2415.7	2366.6	2271.3	2140.8	2039.4	1958.1	1862.8	1772.2	1670.9
25°	2550.8	2454.1	2397.3	2346.6	2239.1	2097.8	1981.1	1888.9	1787.6	1684.7	1581.8
27.5°	2504.8	2432.6	2366.6	2314.3	2194.6	2042.5	1919.7	1815.2	1710.8	1595.6	1491.2
30°	2418.8	2386.5	2334.3	2275.9	2145.4	1993.4	1847.5	1740.0	1624.8	1509.6	1400.6
32.5°	2285.2	2312.8	2279.0	2228.3	2087.1	1925.8	1770.7	1661.7	1535.7	1411.3	1311.5
35°	2122.4	2220.7	2202.2	2166.9	2025.6	1853.6	1698.5	1566.4	1440.5	1314.6	1214.8
37.5°	1944.2	2093.2	2108.6	2087.1	1955.0	1779.9	1609.4	1480.4	1351.4	1224.0	1122.6
40°	1700.0	1928.9	1978.0	1987.2	1881.3	1690.8	1512.7	1386.8	1259.3	1134.9	1012.0
42.5°	1475.8	1764.5	1826.0	1864.4	1787.6	1603.3	1423.6	1283.9	1157.9	1045.8	923.0
45°	1265.4	1566.4	1666.3	1715.4	1681.6	1503.5	1317.7	1187.1	1071.9	969.0	850.8
47.5°	1048.9	1351.4	1491.2	1569.5	1569.5	1402.1	1216.3	1087.3	976.7	889.2	784.8
50°	904.5	1156.4	1300.8	1403.7	1431.3	1299.2	1124.2	998.2	893.8	798.6	718.7
52.5°	770.9	996.7	1116.5	1224.0	1303.8	1188.7	1021.3	907.6	804.7	715.6	652.7
55°	666.5	835.4	944.5	1062.7	1151.8	1076.5	921.4	810.9	721.8	648.1	594.3
57.5°	566.7	714.1	803.2	907.6	1002.8	946.0	821.6	726.4	648.1	583.6	536.0
60°	482.2	602.0	671.1	752.5	870.8	830.8	727.9	640.4	577.4	519.1	479.1
62.5°	410.0	505.3	563.6	622.0	729.5	711.0	631.2	563.6	509.9	460.7	426.9
65°	336.3	414.6	460.7	511.4	597.4	605.1	540.6	493.0	443.8	400.8	370.1
67.5°	271.8	333.3	374.7	417.7	486.8	508.3	463.8	423.9	382.4	347.1	319.4
70°	219.6	262.6	293.3	327.1	383.9	410.0	387.0	359.4	325.6	296.4	271.8
72.5°	173.5	201.2	219.6	245.7	291.8	317.9	316.4	291.8	267.2	247.3	227.3
75°	127.5	149.0	164.3	181.2	218.1	242.6	248.8	238.0	213.5	198.1	182.8
77.5°	96.8	109.0	116.7	129.0	155.1	176.6	185.8	182.8	165.9	153.6	142.8
80°	73.7	76.8	79.9	84.5	106.0	125.9	132.1	130.5	121.3	116.7	104.4
82.5°	52.2	53.8	55.3	56.8	64.5	81.4	87.5	90.6	82.9	78.3	67.6
85°	30.7	32.3	32.3	35.3	36.9	41.5	52.2	52.2	50.7	44.5	43.0
87.5°	15.4	15.4	13.8	13.8	15.4	16.9	20.0	23.0	20.0	18.4	16.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P997687

CATALOG NUMBER: SA2XXRDP-B1005DB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9
2.5°	2185.3	2186.9	2191.5	2177.7	2156.2	2146.9	2119.3	2114.7	2110.1	2110.1	2114.7
5°	2136.2	2130.1	2131.6	2105.5	2074.8	2056.3	2017.9	2024.1	2004.1	1991.8	1994.9
7.5°	2082.4	2065.6	2064.0	2030.2	1991.8	1958.1	1918.1	1908.9	1890.5	1869.0	1859.8
10°	2014.9	2002.6	1979.6	1941.2	1892.0	1864.4	1810.6	1778.4	1773.8	1741.5	1729.2
12.5°	1945.8	1924.3	1901.2	1847.5	1792.2	1747.7	1707.7	1672.4	1647.8	1620.2	1601.8
15°	1865.9	1839.8	1813.7	1756.9	1692.4	1647.8	1587.9	1535.7	1463.5	1406.7	1374.5
17.5°	1778.4	1749.2	1713.9	1650.9	1587.9	1526.5	1415.9	1354.5	1303.8	1270.0	1250.1
20°	1687.8	1655.5	1620.2	1557.2	1448.2	1340.7	1279.3	1231.7	1200.9	1167.2	1142.6
22.5°	1592.5	1558.8	1520.4	1422.1	1306.9	1231.7	1184.0	1139.5	1095.0	1076.5	1064.3
25°	1503.5	1472.8	1423.6	1290.0	1199.4	1130.3	1076.5	1047.4	1024.3	999.8	976.7
27.5°	1411.3	1354.5	1285.4	1173.3	1116.5	1045.8	1007.4	985.9	946.0	929.1	918.4
30°	1300.8	1237.8	1171.8	1091.9	1025.9	976.7	941.4	906.1	883.0	866.1	847.7
32.5°	1188.7	1128.8	1087.3	1004.4	955.2	904.5	870.8	849.3	815.5	804.7	797.0
35°	1091.9	1041.2	1004.4	936.8	890.7	844.6	820.1	787.8	766.3	746.4	734.1
37.5°	996.7	969.0	930.7	873.8	824.7	787.8	754.0	743.3	714.1	703.4	691.1
40°	930.7	889.2	856.9	807.8	766.3	726.4	704.9	680.3	660.4	643.5	638.9
42.5°	850.8	820.1	801.6	747.9	704.9	681.9	655.8	628.1	612.8	598.9	582.0
45°	790.9	763.3	737.1	694.1	655.8	626.6	603.5	585.1	559.0	552.9	526.8
47.5°	727.9	700.3	680.3	637.3	602.0	574.4	557.5	532.9	511.4	497.6	485.3
50°	665.0	641.9	623.5	586.6	555.9	526.8	503.7	479.1	469.9	446.9	439.2
52.5°	605.1	589.7	569.8	534.4	503.7	479.1	454.6	434.6	420.8	408.5	399.3
55°	554.4	529.8	520.6	482.2	456.1	430.0	408.5	396.2	379.3	371.6	364.0
57.5°	497.6	483.8	468.4	439.2	410.0	385.5	370.1	351.7	342.5	333.3	327.1
60°	448.4	428.5	416.2	391.6	365.5	342.5	328.6	314.8	302.5	294.9	282.6
62.5°	391.6	376.3	368.6	342.5	321.0	299.5	287.2	273.4	264.1	250.3	235.0
65°	342.5	330.2	321.0	299.5	279.5	259.5	247.3	230.4	218.1	210.4	208.9
67.5°	299.5	290.3	276.4	256.5	236.5	221.1	207.3	193.5	192.0	188.9	188.9
70°	251.9	242.6	235.0	213.5	196.6	179.7	176.6	172.0	167.4	165.9	162.8
72.5°	210.4	202.7	193.5	175.1	158.2	153.6	150.5	147.4	142.8	141.3	139.8
75°	170.5	159.7	153.6	136.7	132.1	129.0	125.9	121.3	118.3	116.7	113.6
77.5°	130.5	119.8	119.8	110.6	107.5	102.9	99.8	96.8	95.2	92.1	92.1
80°	92.1	92.1	89.1	84.5	79.9	78.3	73.7	72.2	70.6	72.2	69.1
82.5°	67.6	61.4	61.4	58.4	55.3	53.8	50.7	50.7	49.1	49.1	49.1
85°	38.4	38.4	36.9	33.8	32.3	32.3	30.7	30.7	29.2	29.2	27.6
87.5°	15.4	13.8	15.4	13.8	13.8	12.3	12.3	12.3	10.8	12.3	10.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P997687

CATALOG NUMBER: SA2XXRDP-B1005DB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9
2.5°	2114.7	2111.6	2102.4	2105.5	2100.9	2100.9	2097.8	2097.8	2097.8	2105.5	2100.9
5°	1999.5	1988.8	1978.0	1973.4	1968.8	1964.2	1964.2	1962.7	1976.5	1973.4	1985.7
7.5°	1856.7	1853.6	1832.1	1832.1	1824.4	1821.4	1829.1	1830.6	1832.1	1835.2	1842.9
10°	1729.2	1721.5	1690.8	1693.9	1689.3	1683.2	1687.8	1684.7	1695.4	1698.5	1695.4
12.5°	1578.7	1564.9	1531.1	1514.2	1495.8	1482.0	1498.9	1486.6	1529.6	1541.9	1575.7
15°	1379.1	1353.0	1329.9	1329.9	1313.0	1300.8	1308.4	1322.3	1331.5	1345.3	1351.4
17.5°	1245.5	1234.7	1216.3	1205.5	1200.9	1196.3	1196.3	1202.5	1222.4	1220.9	1233.2
20°	1131.8	1125.7	1116.5	1102.7	1098.0	1095.0	1095.0	1095.0	1108.8	1121.1	1128.8
22.5°	1053.5	1048.9	1042.8	1024.3	1015.1	1012.0	1019.7	1024.3	1035.1	1044.3	1052.0
25°	975.2	964.4	953.7	947.5	942.9	942.9	946.0	947.5	952.2	956.8	966.0
27.5°	910.7	903.0	887.7	870.8	870.8	866.1	869.2	872.3	883.0	898.4	906.1
30°	838.5	837.0	830.8	824.7	818.5	815.5	821.6	826.2	827.8	835.4	835.4
32.5°	786.3	775.5	764.8	758.6	755.6	754.0	755.6	761.7	761.7	770.9	781.7
35°	734.1	727.9	717.2	706.4	703.4	695.7	701.8	708.0	718.7	723.3	727.9
37.5°	677.3	669.6	665.0	661.9	655.8	657.3	652.7	661.9	671.1	669.6	672.6
40°	634.3	620.4	606.6	605.1	603.5	602.0	602.0	603.5	609.7	615.8	625.0
42.5°	579.0	574.4	562.1	549.8	546.7	543.6	540.6	546.7	559.0	569.8	574.4
45°	522.1	516.0	512.9	503.7	497.6	496.0	493.0	500.6	511.4	516.0	519.1
47.5°	469.9	468.4	459.2	460.7	456.1	457.6	456.1	460.7	460.7	465.3	468.4
50°	434.6	430.0	425.4	422.3	417.7	417.7	416.2	417.7	423.9	430.0	428.5
52.5°	399.3	391.6	390.1	388.5	385.5	388.5	383.9	385.5	391.6	394.7	393.1
55°	357.8	356.3	353.2	350.1	348.6	347.1	347.1	347.1	353.2	357.8	359.4
57.5°	325.6	317.9	311.8	311.8	305.6	304.1	307.1	308.7	313.3	316.4	319.4
60°	281.0	278.0	268.8	264.1	254.9	253.4	253.4	259.5	267.2	278.0	281.0
62.5°	233.4	228.8	227.3	227.3	227.3	227.3	227.3	227.3	227.3	228.8	228.8
65°	207.3	208.9	207.3	205.8	207.3	207.3	205.8	205.8	205.8	207.3	208.9
67.5°	185.8	184.3	185.8	184.3	182.8	182.8	181.2	182.8	184.3	185.8	185.8
70°	161.3	161.3	159.7	161.3	159.7	158.2	156.6	156.6	159.7	161.3	161.3
72.5°	138.2	138.2	136.7	136.7	133.6	133.6	135.1	133.6	133.6	138.2	138.2
75°	115.2	113.6	112.1	112.1	110.6	110.6	110.6	109.0	112.1	112.1	113.6
77.5°	90.6	90.6	90.6	89.1	89.1	87.5	87.5	89.1	89.1	89.1	90.6
80°	69.1	69.1	69.1	67.6	66.0	66.0	66.0	66.0	66.0	67.6	66.0
82.5°	47.6	47.6	47.6	47.6	47.6	46.1	46.1	46.1	47.6	47.6	46.1
85°	29.2	27.6	29.2	29.2	27.6	29.2	27.6	27.6	26.1	26.1	27.6
87.5°	12.3	10.8	9.2	9.2	10.8	9.2	9.2	9.2	10.8	9.2	9.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P997687

CATALOG NUMBER: SA2XXRDP-B1005DB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9
2.5°	2105.5	2113.2	2110.1	2093.2	2110.1	2114.7	2123.9	2133.1	2139.3	2148.5	2156.2
5°	1973.4	1988.8	1998.0	1988.8	2019.5	2024.1	2045.6	2057.9	2076.3	2091.7	2103.9
7.5°	1849.0	1861.3	1879.7	1882.8	1901.2	1922.7	1953.4	1984.2	2013.3	2028.7	2042.5
10°	1715.4	1736.9	1764.5	1758.4	1786.1	1819.8	1852.1	1901.2	1925.8	1953.4	1978.0
12.5°	1581.8	1595.6	1632.5	1644.8	1684.7	1710.8	1755.3	1786.1	1847.5	1879.7	1901.2
15°	1348.4	1405.2	1451.3	1506.5	1558.8	1607.9	1647.8	1703.1	1756.9	1781.4	1816.8
17.5°	1242.4	1268.5	1296.2	1323.8	1391.4	1478.9	1549.5	1609.4	1655.5	1687.8	1729.2
20°	1131.8	1157.9	1188.7	1214.8	1256.2	1319.2	1406.7	1509.6	1564.9	1598.7	1638.6
22.5°	1053.5	1078.1	1098.0	1121.1	1153.3	1199.4	1265.4	1392.9	1466.6	1508.1	1543.4
25°	969.0	999.8	1021.3	1038.2	1064.3	1114.9	1168.7	1240.9	1372.9	1405.2	1454.3
27.5°	910.7	919.9	944.5	970.6	996.7	1024.3	1079.6	1141.0	1230.1	1300.8	1360.7
30°	841.6	864.6	887.7	898.4	921.4	961.4	995.2	1061.2	1130.3	1185.6	1257.8
32.5°	789.4	803.2	818.5	844.6	866.1	893.8	927.6	982.9	1041.2	1076.5	1131.8
35°	731.0	740.2	772.5	783.2	804.7	832.4	866.1	909.2	972.1	999.8	1039.7
37.5°	675.7	697.2	706.4	731.0	751.0	778.6	803.2	852.3	893.8	926.0	962.9
40°	632.7	641.9	658.8	680.3	697.2	718.7	749.4	784.8	829.3	855.4	887.7
42.5°	580.5	588.2	609.7	622.0	649.6	669.6	688.0	731.0	770.9	790.9	823.1
45°	523.7	542.1	555.9	580.5	595.9	620.4	643.5	674.2	711.0	734.1	752.5
47.5°	474.5	493.0	506.8	529.8	554.4	565.1	589.7	622.0	655.8	674.2	700.3
50°	434.6	440.8	466.9	477.6	503.7	525.2	542.1	569.8	606.6	617.4	638.9
52.5°	396.2	400.8	417.7	431.5	454.6	473.0	494.5	520.6	551.3	568.2	585.1
55°	362.4	365.5	373.2	388.5	403.9	426.9	446.9	471.5	497.6	516.0	531.4
57.5°	324.0	330.2	336.3	345.5	360.9	382.4	403.9	426.9	448.4	460.7	480.7
60°	279.5	288.7	299.5	310.2	321.0	336.3	360.9	382.4	402.4	413.1	428.5
62.5°	231.9	250.3	259.5	271.8	281.0	294.9	313.3	337.9	351.7	365.5	377.8
65°	208.9	210.4	211.9	224.2	241.1	254.9	271.8	290.3	311.8	321.0	330.2
67.5°	185.8	187.4	190.4	192.0	198.1	213.5	231.9	251.9	268.8	274.9	284.1
70°	162.8	162.8	168.9	170.5	172.0	173.5	188.9	208.9	224.2	231.9	242.6
72.5°	138.2	139.8	142.8	144.4	147.4	150.5	155.1	165.9	184.3	192.0	204.3
75°	113.6	115.2	116.7	118.3	122.9	124.4	129.0	135.1	142.8	152.0	159.7
77.5°	90.6	90.6	92.1	95.2	98.3	99.8	104.4	107.5	110.6	115.2	121.3
80°	67.6	69.1	69.1	72.2	72.2	73.7	75.3	79.9	82.9	86.0	89.1
82.5°	46.1	49.1	49.1	49.1	50.7	52.2	53.8	53.8	56.8	58.4	63.0
85°	27.6	29.2	29.2	29.2	27.6	30.7	30.7	32.3	32.3	32.3	33.8
87.5°	10.8	9.2	10.8	10.8	10.8	12.3	10.8	10.8	12.3	13.8	13.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P997687

CATALOG NUMBER: SA2XXRDP-B1005DB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	2209.9	2209.9	2209.9	2209.9
2.5°	2170.0	2165.4	2193.0	2223.7
5°	2125.4	2133.1	2168.4	2211.4
7.5°	2079.4	2096.3	2137.7	2194.6
10°	2014.9	2045.6	2108.6	2166.9
12.5°	1951.9	1993.4	2053.3	2122.4
15°	1881.3	1927.3	2001.1	2084.0
17.5°	1802.9	1855.2	1941.2	2031.8
20°	1720.0	1789.1	1879.7	1978.0
22.5°	1627.9	1710.8	1804.5	1913.5
25°	1538.8	1629.4	1723.1	1849.0
27.5°	1451.3	1540.3	1644.8	1772.2
30°	1363.7	1445.1	1557.2	1693.9
32.5°	1270.0	1354.5	1472.8	1612.5
35°	1184.0	1268.5	1379.1	1517.3
37.5°	1091.9	1182.5	1288.5	1431.3
40°	984.4	1090.4	1193.3	1329.9
42.5°	895.3	1007.4	1107.3	1236.3
45°	824.7	930.7	1013.6	1139.5
47.5°	758.6	844.6	929.1	1045.8
50°	695.7	761.7	849.3	953.7
52.5°	631.2	688.0	763.3	861.5
55°	572.8	626.6	694.1	769.4
57.5°	519.1	557.5	625.0	692.6
60°	459.2	499.1	551.3	608.1
62.5°	408.5	439.2	488.4	536.0
65°	354.8	383.9	420.8	465.3
67.5°	305.6	331.7	360.9	396.2
70°	261.1	281.0	302.5	333.3
72.5°	213.5	235.0	254.9	279.5
75°	175.1	184.3	201.2	218.1
77.5°	135.1	147.4	156.6	170.5
80°	96.8	107.5	110.6	121.3
82.5°	64.5	70.6	76.8	79.9
85°	36.9	39.9	46.1	47.6
87.5°	13.8	15.4	18.4	21.5
90°	0.0	0.0	0.0	0.0

TEST NUMBER: P997687

CATALOG NUMBER: SA2XXRDP-B1005DB2750-4F0-XX-W2A-A_3000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	23.39	24.84	23.75	25.15	25.47	17.80	19.25	18.17	19.57	19.88
	3H	24.72	26.01	25.09	26.34	26.71	18.93	20.23	19.31	20.56	20.92
	4H	25.14	26.36	25.54	26.71	27.09	19.39	20.61	19.79	20.96	21.34
	6H	25.42	26.54	25.83	26.91	27.30	19.77	20.89	20.18	21.26	21.65
	8H	25.49	26.56	25.92	26.95	27.35	19.89	20.96	20.32	21.35	21.75
	12H	25.53	26.55	25.96	26.93	27.36	19.97	20.99	20.41	21.38	21.81
4H	2H	23.36	24.58	23.76	24.93	25.31	18.49	19.70	18.89	20.05	20.43
	3H	24.81	25.81	25.22	26.22	26.62	19.78	20.78	20.19	21.18	21.59
	4H	25.31	26.22	25.75	26.63	27.07	20.33	21.24	20.77	21.65	22.09
	6H	25.69	26.47	26.15	26.92	27.38	20.82	21.60	21.27	22.04	22.51
	8H	25.80	26.53	26.27	26.98	27.45	20.98	21.71	21.44	22.16	22.62
	12H	25.88	26.53	26.36	27.01	27.48	21.10	21.75	21.58	22.23	22.70
8H	4H	25.30	26.03	25.77	26.48	26.95	20.65	21.39	21.12	21.83	22.30
	6H	25.72	26.32	26.22	26.81	27.29	21.24	21.84	21.74	22.33	22.81
	8H	25.86	26.40	26.38	26.92	27.41	21.47	22.01	21.98	22.52	23.01
	12H	25.98	26.46	26.49	26.95	27.52	21.66	22.13	22.17	22.63	23.19
12H	4H	25.28	25.93	25.76	26.41	26.88	20.69	21.34	21.17	21.82	22.29
	6H	25.69	26.24	26.21	26.75	27.24	21.30	21.84	21.81	22.35	22.84
	8H	25.87	26.35	26.38	26.84	27.41	21.58	22.06	22.09	22.55	23.12