

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000736

Luminaire Tested: SA4XXDIP-B1020D590UB40-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000736
REPORT IS A COMBINATION OF REPORTS P995349 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B1020D590UB40-4F0-XX-W2A-F4
Description: Define 4 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6489.2 lumens
Efficiency: N/A
Efficacy: 104.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 62.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000736

CATALOG NUMBER: SA4XXDIP-B1020D590UB40-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1000736

CATALOG NUMBER: SA4XXDIP-B1020D590UB40-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72
1	102	97	93	90	96	92	88	85	82	79	76	72	70	68	64	62	61
2	93	85	79	73	87	80	75	70	72	67	63	64	60	57	56	54	51
3	84	75	67	61	79	71	64	58	63	58	53	56	52	48	50	46	44
4	77	66	58	52	73	63	55	50	56	50	46	50	45	42	44	41	38
5	71	59	51	44	67	56	48	43	50	44	39	45	40	36	40	36	33
6	66	53	45	39	62	50	43	37	45	39	34	41	36	32	36	32	29
7	61	48	40	34	57	46	38	33	41	35	30	37	32	28	33	29	26
8	56	44	36	30	53	42	34	29	38	32	27	34	29	25	31	26	23
9	53	40	32	27	50	38	31	26	35	29	24	31	26	23	28	24	21
10	49	37	29	24	46	35	28	24	32	26	22	29	24	21	26	22	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13906	13906	13906
5°	13917	13506	13522
10°	13800	13130	13039
15°	13602	12685	12494
20°	13349	12203	11929
25°	13064	11693	11321
30°	12721	11142	10654
35°	12365	10579	10010
40°	11995	9972	9324
45°	11608	9363	8683
50°	11177	8773	7973
55°	10710	8084	7267
60°	10231	7329	6533
65°	9684	6550	5705
70°	9053	5611	4818
75°	8112	4522	3859
80°	6914	3269	2714
85°	5370	1822	1461

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11608 cd/sqm

TEST NUMBER: P1000736

CATALOG NUMBER: SA4XXDIP-B1020D590UB40-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.7	2.5
10°-20°	452.8	7.0
20°-30°	666.4	10.3
30°-40°	774.7	11.9
40°-50°	774.6	11.9
50°-60°	677.5	10.4
60°-70°	503.0	7.8
70°-80°	285.4	4.4
80°-90°	82.9	1.3
90°-100°	214.9	3.3
100°-110°	437.0	6.7
110°-120°	389.5	6.0
120°-130°	327.2	5.0
130°-140°	273.1	4.2
140°-150°	208.5	3.2
150°-160°	146.6	2.3
160°-170°	86.2	1.3
170°-180°	28.0	0.4
0°-30°	1280.0	19.7
0°-40°	2054.7	31.7
0°-60°	3506.8	54.0
0°-90°	4378.1	67.5
90°-120°	1041.5	16.0
90°-150°	1850.3	28.5
90°-180°	2111.0	32.5
0°-180°	6489.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1705	1705	1705	1705	1705	
5°	1704	1698	1683	1698	1696	162
15°	1622	1616	1596	1604	1600	457
25°	1469	1459	1440	1442	1436	676
35°	1264	1254	1235	1226	1219	790
45°	1032	1022	1000	985	981	795
55°	780	776	757	741	732	699
65°	529	522	508	495	488	523
75°	282	275	268	262	261	299
85°	74	74	71	71	70	79
90°	1	4	10	11	12	6
95°	19	59	463	229	139	21
105°	66	96	373	803	800	71
115°	117	147	332	639	768	116
125°	163	194	331	544	613	145
135°	194	231	328	482	548	150
145°	223	256	326	407	447	140
155°	254	274	317	359	374	117
165°	277	285	304	322	327	78
175°	289	289	292	296	294	27
180°	289	289	289	289	289	

TEST NUMBER: P1000736

CATALOG NUMBER: SA4XXDIP-B1020D590UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1705.3	1705.3	1705.3	1705.3	1705.3
2.5°	1710.8	1706.7	1691.6	1705.3	1703.9
5°	1703.9	1698.5	1683.4	1698.5	1695.7
7.5°	1691.6	1686.2	1669.8	1682.1	1680.7
10°	1673.9	1668.4	1650.6	1661.6	1658.8
12.5°	1650.6	1645.2	1626.1	1638.4	1634.3
15°	1622.0	1616.5	1596.0	1604.2	1600.1
17.5°	1589.2	1582.3	1563.2	1568.7	1565.9
20°	1552.3	1545.4	1524.9	1529.0	1526.3
22.5°	1512.6	1503.1	1482.6	1490.8	1485.3
25°	1468.9	1459.3	1440.2	1441.6	1436.1
27.5°	1419.7	1410.2	1392.4	1389.7	1382.8
30°	1370.5	1359.6	1341.8	1336.4	1329.5
32.5°	1318.6	1309.0	1289.9	1283.1	1276.2
35°	1263.9	1254.4	1235.3	1225.7	1218.9
37.5°	1206.6	1198.4	1177.9	1168.3	1158.7
40°	1150.5	1139.6	1119.1	1105.4	1098.6
42.5°	1090.4	1084.9	1061.7	1045.3	1041.2
45°	1031.7	1022.1	1000.2	985.2	981.1
47.5°	970.2	963.3	942.8	926.4	915.5
50°	907.3	901.8	882.7	863.6	855.4
52.5°	845.8	839.0	818.5	802.1	791.2
55°	780.2	776.1	757.0	740.6	732.4
57.5°	718.7	714.6	695.5	679.1	670.9
60°	654.5	647.7	629.9	617.6	610.8
62.5°	591.7	586.2	567.1	556.1	549.3
65°	528.8	522.0	508.3	494.6	487.8
67.5°	464.6	459.1	445.5	431.8	430.4
70°	405.8	396.3	385.3	374.4	370.3
72.5°	343.0	333.4	325.2	317.0	312.9
75°	281.5	274.7	267.8	262.4	261.0
77.5°	221.4	218.6	211.8	210.4	206.3
80°	168.1	164.0	161.2	158.5	157.1
82.5°	116.1	114.8	114.8	113.4	112.0
85°	73.8	73.8	71.1	71.1	69.7
87.5°	35.5	34.2	32.8	32.8	32.8
90°	0.6	4.5	10.2	11.4	11.9
92.5°	8.0	43.8	222.8	73.6	51.7
95°	18.8	59.1	463.2	229.4	138.7
97.5°	31.3	65.4	495.6	468.3	333.0
100°	43.2	73.9	456.9	647.9	521.1
102.5°	54.6	84.1	408.6	760.4	684.8
105°	66.5	96.4	372.8	802.8	799.6
107.5°	79.6	108.8	349.5	790.0	854.2
110°	92.6	121.4	338.7	744.5	855.3

TEST NUMBER: P1000736

CATALOG NUMBER: SA4XXDIP-B1020D590UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	105.1	133.8	333.6	688.8	821.8
115°	117.1	146.9	332.5	638.8	767.8
117.5°	129.6	159.1	331.9	599.6	714.9
120°	142.1	171.0	331.9	573.2	671.8
122.5°	153.4	182.7	331.3	555.8	637.7
125°	163.1	193.8	330.8	543.6	612.6
127.5°	172.2	204.0	329.6	532.0	596.7
130°	179.6	214.0	329.1	518.0	583.1
132.5°	187.0	222.5	328.5	501.6	567.8
135°	193.8	230.7	327.9	482.5	547.9
137.5°	200.6	237.8	327.9	462.0	524.6
140°	208.0	244.4	327.4	442.2	499.0
142.5°	216.0	250.4	327.4	423.6	471.7
145°	223.3	255.8	326.2	407.0	447.3
147.5°	231.9	260.8	324.5	393.0	424.5
150°	239.8	265.7	322.8	380.2	405.8
152.5°	247.2	270.2	320.0	369.4	388.7
155°	254.0	274.2	317.1	359.2	374.5
157.5°	260.9	277.9	314.3	349.5	361.5
160°	267.1	281.0	310.9	339.8	349.5
162.5°	272.8	283.6	307.5	330.5	338.2
165°	276.8	285.3	304.1	322.0	326.8
167.5°	281.3	286.7	300.6	314.5	317.7
170°	284.2	287.8	297.2	307.2	309.2
172.5°	287.0	288.7	293.8	300.6	300.6
175°	288.7	289.3	291.5	295.5	294.4
177.5°	289.8	289.3	289.8	291.8	289.8
180°	289.3	289.3	289.3	289.3	289.3

(END OF REPORT)