

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000745

Luminaire Tested: SA4XXDIP-B1020D590UB50-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000745
REPORT IS A COMBINATION OF REPORTS P995358 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B1020D590UB50-4F0-XX-W2A-F4
Description: Define 4 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6276.1 lumens
Efficiency: N/A
Efficacy: 100.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 62.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000745

CATALOG NUMBER: SA4XXDIP-B1020D590UB50-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1000745

CATALOG NUMBER: SA4XXDIP-B1020D590UB50-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72
1	102	97	93	90	96	92	88	85	82	79	76	72	70	68	64	62	61
2	93	85	79	73	87	80	75	70	72	67	63	64	60	57	56	54	51
3	84	75	67	61	79	71	64	58	63	58	53	56	52	48	50	46	44
4	77	66	58	52	73	63	55	50	56	50	46	50	45	42	44	41	38
5	71	59	51	44	67	56	48	43	50	44	39	45	40	36	40	36	33
6	66	53	45	39	62	50	43	37	45	39	34	41	36	32	36	32	29
7	61	48	40	34	57	46	38	33	41	35	30	37	32	28	33	29	26
8	56	44	36	30	53	42	34	29	38	32	27	34	29	25	31	26	23
9	53	40	32	27	50	38	31	26	35	29	24	31	26	23	28	24	21
10	49	37	29	24	46	35	28	24	32	26	22	29	24	21	26	22	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13448	13448	13448
5°	13460	13062	13078
10°	13345	12698	12610
15°	13154	12268	12082
20°	12910	11802	11537
25°	12635	11309	10949
30°	12302	10776	10304
35°	11959	10230	9681
40°	11601	9644	9017
45°	11225	9055	8397
50°	10810	8485	7710
55°	10358	7818	7028
60°	9895	7088	6318
65°	9365	6335	5518
70°	8757	5427	4659
75°	7844	4374	3732
80°	6683	3162	2626
85°	5196	1760	1413

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11225 cd/sqm

TEST NUMBER: P1000745

CATALOG NUMBER: SA4XXDIP-B1020D590UB50-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	155.4	2.5
10°-20°	437.9	7.0
20°-30°	644.5	10.3
30°-40°	749.2	11.9
40°-50°	749.1	11.9
50°-60°	655.2	10.4
60°-70°	486.5	7.8
70°-80°	276.0	4.4
80°-90°	80.1	1.3
90°-100°	207.8	3.3
100°-110°	422.7	6.7
110°-120°	376.8	6.0
120°-130°	316.5	5.0
130°-140°	264.1	4.2
140°-150°	201.7	3.2
150°-160°	141.8	2.3
160°-170°	83.4	1.3
170°-180°	27.1	0.4
0°-30°	1237.9	19.7
0°-40°	1987.1	31.7
0°-60°	3391.5	54.0
0°-90°	4234.1	67.5
90°-120°	1007.4	16.1
90°-150°	1789.7	28.5
90°-180°	2042.0	32.5
0°-180°	6276.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1649	1649	1649	1649	1649	
5°	1648	1643	1628	1643	1640	156
15°	1569	1563	1544	1551	1547	442
25°	1421	1411	1393	1394	1389	654
35°	1222	1213	1195	1185	1179	764
45°	998	988	967	953	949	769
55°	755	751	732	716	708	676
65°	511	505	492	478	472	506
75°	272	266	259	254	252	289
85°	71	71	69	69	67	77
90°	0	4	10	11	12	6
95°	18	57	448	222	134	20
105°	64	93	361	776	774	69
115°	113	142	322	618	743	112
125°	158	187	320	526	593	141
135°	188	223	317	467	530	145
145°	216	247	316	394	433	136
155°	246	265	307	347	362	113
165°	268	276	294	311	316	76
175°	279	280	282	286	285	27
180°	280	280	280	280	280	

TEST NUMBER: P1000745

CATALOG NUMBER: SA4XXDIP-B1020D590UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1649.2	1649.2	1649.2	1649.2	1649.2
2.5°	1654.5	1650.5	1636.0	1649.2	1647.9
5°	1647.9	1642.6	1628.1	1642.6	1640.0
7.5°	1636.0	1630.7	1614.8	1626.7	1625.4
10°	1618.8	1613.5	1596.3	1606.9	1604.3
12.5°	1596.3	1591.1	1572.6	1584.5	1580.5
15°	1568.6	1563.3	1543.5	1551.4	1547.4
17.5°	1536.9	1530.3	1511.8	1517.1	1514.4
20°	1501.2	1494.6	1474.8	1478.7	1476.1
22.5°	1462.9	1453.6	1433.8	1441.7	1436.4
25°	1420.6	1411.3	1392.8	1394.2	1388.9
27.5°	1373.0	1363.8	1346.6	1343.9	1337.3
30°	1325.4	1314.9	1297.7	1292.4	1285.8
32.5°	1275.2	1266.0	1247.5	1240.9	1234.3
35°	1222.4	1213.1	1194.6	1185.4	1178.8
37.5°	1166.9	1158.9	1139.1	1129.9	1120.6
40°	1112.7	1102.1	1082.3	1069.1	1062.5
42.5°	1054.5	1049.3	1026.8	1010.9	1007.0
45°	997.7	988.5	967.3	952.8	948.8
47.5°	938.2	931.6	911.8	896.0	885.4
50°	877.5	872.2	853.7	835.2	827.2
52.5°	818.0	811.4	791.6	775.7	765.1
55°	754.6	750.6	732.1	716.2	708.3
57.5°	695.1	691.1	672.6	656.8	648.8
60°	633.0	626.4	609.2	597.3	590.7
62.5°	572.2	566.9	548.4	537.8	531.2
65°	511.4	504.8	491.6	478.4	471.8
67.5°	449.3	444.0	430.8	417.6	416.3
70°	392.5	383.2	372.7	362.1	358.1
72.5°	331.7	322.4	314.5	306.6	302.6
75°	272.2	265.6	259.0	253.7	252.4
77.5°	214.1	211.4	204.8	203.5	199.5
80°	162.5	158.6	155.9	153.3	152.0
82.5°	112.3	111.0	111.0	109.7	108.4
85°	71.4	71.4	68.7	68.7	67.4
87.5°	34.4	33.0	31.7	31.7	31.7
90°	0.5	4.4	9.9	11.0	11.5
92.5°	7.7	42.4	215.5	71.2	50.0
95°	18.1	57.2	448.0	221.8	134.1
97.5°	30.2	63.2	479.4	453.0	322.1
100°	41.8	71.5	442.0	626.6	504.1
102.5°	52.8	81.4	395.2	735.5	662.4
105°	64.3	93.2	360.6	776.4	773.5
107.5°	77.0	105.2	338.1	764.1	826.2
110°	89.6	117.4	327.6	720.2	827.3



TEST NUMBER: P1000745

CATALOG NUMBER: SA4XXDIP-B1020D590UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	101.7	129.4	322.7	666.2	794.9
115°	113.2	142.1	321.6	617.9	742.7
117.5°	125.3	153.9	321.0	580.0	691.5
120°	137.4	165.5	321.0	554.4	649.8
122.5°	148.4	176.8	320.5	537.6	616.8
125°	157.8	187.4	319.9	525.8	592.6
127.5°	166.6	197.4	318.8	514.5	577.2
130°	173.7	207.0	318.3	501.0	564.0
132.5°	180.9	215.2	317.7	485.2	549.2
135°	187.5	223.2	317.2	466.8	529.9
137.5°	194.1	230.0	317.2	447.0	507.4
140°	201.2	236.4	316.6	427.6	482.7
142.5°	208.9	242.2	316.6	409.8	456.3
145°	216.0	247.4	315.5	393.6	432.6
147.5°	224.3	252.3	313.9	380.2	410.6
150°	232.0	257.0	312.2	367.8	392.5
152.5°	239.1	261.4	309.5	357.4	376.0
155°	245.7	265.2	306.7	347.4	362.3
157.5°	252.3	268.8	304.0	338.0	349.6
160°	258.4	271.8	300.7	328.7	338.1
162.5°	263.9	274.3	297.4	319.6	327.1
165°	267.7	276.0	294.1	311.4	316.1
167.5°	272.1	277.4	290.8	304.2	307.3
170°	274.9	278.5	287.5	297.1	299.0
172.5°	277.6	279.2	284.2	290.8	290.8
175°	279.3	279.8	282.0	285.9	284.8
177.5°	280.4	279.8	280.4	282.3	280.4
180°	279.8	279.8	279.8	279.8	279.8

(END OF REPORT)