

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000813

Luminaire Tested: SA4XXDIP-B1195D1035UB27-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000813
REPORT IS A COMBINATION OF REPORTS P995426 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B1195D1035UB27-4F0-XX-W2A-F1
Description: Define 4 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8599.0 lumens
Efficiency: N/A
Efficacy: 95.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 89.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000813

CATALOG NUMBER: SA4XXDIP-B1195D1035UB27-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1000813

CATALOG NUMBER: SA4XXDIP-B1195D1035UB27-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	65	65	65
1	100	95	91	88	93	89	86	83	78	75	73	67	65	63	57	56	54
2	91	83	77	72	85	78	72	68	68	64	60	59	56	53	50	48	46
3	83	73	66	60	77	69	62	57	60	55	51	52	48	45	44	41	39
4	76	65	57	51	71	61	54	48	53	48	43	46	42	38	40	36	34
5	70	58	50	43	65	54	47	41	48	42	37	42	37	33	36	32	29
6	64	52	44	38	60	49	41	36	43	37	33	38	33	29	32	29	26
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	30	26	23
8	55	43	35	29	51	40	33	28	36	30	26	31	27	23	27	23	21
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	19
10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	23	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16146	16146	16146
5°	16159	15681	15700
10°	16022	15246	15139
15°	15792	14729	14506
20°	15499	14169	13850
25°	15168	13577	13145
30°	14770	12938	12371
35°	14357	12282	11622
40°	13928	11578	10826
45°	13476	10871	10081
50°	12977	10186	9257
55°	12435	9386	8438
60°	11879	8510	7585
65°	11244	7605	6624
70°	10512	6515	5593
75°	9418	5252	4480
80°	8024	3797	3151
85°	6236	2114	1696

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13476 cd/sqm

TEST NUMBER: P1000813

CATALOG NUMBER: SA4XXDIP-B1195D1035UB27-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	186.6	2.2
10°-20°	525.8	6.1
20°-30°	773.8	9.0
30°-40°	899.5	10.5
40°-50°	899.4	10.5
50°-60°	786.6	9.1
60°-70°	584.0	6.8
70°-80°	331.4	3.9
80°-90°	97.6	1.1
90°-100°	82.6	1.0
100°-110°	247.3	2.9
110°-120°	420.1	4.9
120°-130°	554.0	6.4
130°-140°	622.3	7.2
140°-150°	611.6	7.1
150°-160°	514.4	6.0
160°-170°	342.3	4.0
170°-180°	119.8	1.4
0°-30°	1486.2	17.3
0°-40°	2385.7	27.7
0°-60°	4071.7	47.4
0°-90°	5084.7	59.1
90°-120°	749.9	8.7
90°-150°	2537.8	29.5
90°-180°	3514.0	40.9
0°-180°	8599.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1980	1980	1980	1980	1980	
5°	1978	1972	1955	1972	1969	188
15°	1883	1877	1853	1863	1858	531
25°	1706	1694	1672	1674	1667	785
35°	1468	1456	1434	1423	1415	918
45°	1198	1187	1161	1144	1139	923
55°	906	901	879	860	850	811
65°	614	606	590	574	566	608
75°	327	319	311	305	303	347
85°	86	86	82	82	81	92
90°	3	14	22	27	29	10
95°	59	68	74	77	77	64
105°	228	229	233	236	239	242
115°	427	427	425	424	423	421
125°	622	622	621	619	617	554
135°	802	808	808	806	803	621
145°	975	979	980	979	976	610
155°	1117	1117	1116	1120	1116	514
165°	1216	1213	1211	1217	1213	343
175°	1265	1260	1259	1266	1259	120
180°	1267	1267	1267	1267	1267	

TEST NUMBER: P1000813

CATALOG NUMBER: SA4XXDIP-B1195D1035UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1980.0	1980.0	1980.0	1980.0	1980.0
2.5°	1986.3	1981.6	1964.1	1980.0	1978.4
5°	1978.4	1972.0	1954.6	1972.0	1968.9
7.5°	1964.1	1957.8	1938.7	1953.0	1951.4
10°	1943.5	1937.1	1916.5	1929.2	1926.0
12.5°	1916.5	1910.2	1888.0	1902.2	1897.5
15°	1883.2	1876.9	1853.1	1862.6	1857.8
17.5°	1845.1	1837.2	1815.0	1821.3	1818.2
20°	1802.3	1794.4	1770.6	1775.3	1772.1
22.5°	1756.3	1745.2	1721.4	1730.9	1724.5
25°	1705.5	1694.4	1672.2	1673.8	1667.4
27.5°	1648.4	1637.3	1616.7	1613.5	1605.6
30°	1591.3	1578.6	1558.0	1551.6	1543.7
32.5°	1531.0	1519.9	1497.7	1489.7	1481.8
35°	1467.5	1456.4	1434.2	1423.1	1415.2
37.5°	1400.9	1391.4	1367.6	1356.5	1345.4
40°	1335.9	1323.2	1299.4	1283.5	1275.6
42.5°	1266.0	1259.7	1232.7	1213.7	1208.9
45°	1197.8	1186.7	1161.3	1143.9	1139.1
47.5°	1126.4	1118.5	1094.7	1075.7	1063.0
50°	1053.4	1047.1	1024.9	1002.7	993.2
52.5°	982.1	974.1	950.3	931.3	918.6
55°	905.9	901.1	878.9	859.9	850.4
57.5°	834.5	829.8	807.5	788.5	779.0
60°	759.9	752.0	731.4	717.1	709.2
62.5°	687.0	680.6	658.4	645.7	637.8
65°	614.0	606.1	590.2	574.3	566.4
67.5°	539.4	533.1	517.2	501.3	499.8
70°	471.2	460.1	447.4	434.7	429.9
72.5°	398.2	387.1	377.6	368.1	363.3
75°	326.8	318.9	311.0	304.6	303.0
77.5°	257.0	253.8	245.9	244.3	239.6
80°	195.1	190.4	187.2	184.0	182.4
82.5°	134.9	133.3	133.3	131.7	130.1
85°	85.7	85.7	82.5	82.5	80.9
87.5°	41.2	39.7	38.1	38.1	38.1
90°	2.9	13.7	21.6	27.4	29.4
92.5°	25.5	38.2	43.1	46.0	47.0
95°	58.8	67.6	74.4	77.4	77.4
97.5°	94.0	101.9	109.7	113.6	113.6
100°	137.1	141.1	149.9	151.8	151.8
102.5°	182.2	183.2	191.0	194.0	194.9
105°	228.2	229.2	233.1	236.1	239.0
107.5°	276.2	277.2	278.2	282.1	281.1
110°	325.2	327.2	326.2	324.2	327.2



TEST NUMBER: P1000813

CATALOG NUMBER: SA4XXDIP-B1195D1035UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	376.2	376.2	374.2	374.2	374.2
115°	427.1	427.1	425.1	424.2	423.2
117.5°	475.1	475.1	474.1	471.2	468.2
120°	523.1	527.0	524.1	519.2	521.1
122.5°	573.0	574.0	573.0	570.1	565.2
125°	622.0	622.0	621.0	619.1	617.1
127.5°	666.1	669.0	667.1	665.1	664.1
130°	713.1	716.1	716.1	714.1	710.2
132.5°	761.1	763.1	762.1	760.1	759.2
135°	802.3	808.1	808.1	806.2	803.2
137.5°	848.3	851.2	853.2	850.3	851.2
140°	894.3	896.3	896.3	895.3	894.3
142.5°	936.5	938.4	937.4	937.4	937.4
145°	974.7	978.6	979.6	978.6	975.6
147.5°	1013.9	1018.7	1017.8	1016.8	1015.8
150°	1049.1	1053.0	1053.0	1053.0	1052.1
152.5°	1082.4	1084.4	1085.4	1088.3	1085.4
155°	1116.7	1116.7	1115.7	1119.6	1115.7
157.5°	1146.1	1144.1	1144.1	1147.1	1144.1
160°	1171.6	1170.6	1169.6	1172.5	1167.6
162.5°	1195.1	1192.1	1191.2	1197.0	1192.1
165°	1215.6	1212.7	1210.7	1216.6	1212.7
167.5°	1232.3	1228.4	1228.4	1234.3	1228.4
170°	1246.0	1241.1	1242.1	1248.0	1241.1
172.5°	1255.8	1251.9	1251.9	1258.7	1251.9
175°	1264.6	1259.7	1258.7	1265.6	1258.7
177.5°	1268.5	1263.6	1263.6	1270.5	1262.7
180°	1266.6	1266.6	1266.6	1266.6	1266.6

(END OF REPORT)