

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000835

Luminaire Tested: SA4XXDIP-B1195D1035UB30-4F0-XX-W2A-D4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000835
REPORT IS A COMBINATION OF REPORTS P995448 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B1195D1035UB30-4F0-XX-W2A-D4
Description: Define 4 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8545.3 lumens
Efficiency: N/A
Efficacy: 95.2 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 89.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000835

CATALOG NUMBER: SA4XXDIP-B1195D1035UB30-4F0-XX-W2A-D4

Luminous Intensity Polar Plot



TEST NUMBER: P1000835

CATALOG NUMBER: SA4XXDIP-B1195D1035UB30-4F0-XX-W2A-D4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59
1	97	93	88	84	90	86	82	79	73	70	68	61	59	57	50	49	47
2	88	80	74	68	81	74	68	64	63	59	55	53	50	47	43	41	39
3	80	70	62	56	74	65	58	53	55	50	46	46	42	39	38	35	33
4	73	62	53	47	67	57	50	44	49	43	39	41	37	33	34	31	28
5	67	55	46	40	62	51	43	38	44	38	33	37	32	29	30	27	24
6	62	49	41	35	57	46	38	33	39	33	29	33	28	25	27	24	21
7	57	44	36	30	52	41	34	29	35	30	25	30	25	22	25	21	19
8	53	40	32	27	49	37	30	25	32	26	22	27	23	19	23	19	17
9	49	37	29	24	45	34	27	22	30	24	20	25	21	17	21	18	15
10	46	34	26	21	42	31	25	20	27	22	18	23	19	16	20	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11653	11653	11653
5°	11685	11349	11370
10°	11609	11126	11094
15°	11501	10875	10783
20°	11339	10603	10481
25°	11158	10303	10156
30°	10962	10006	9823
35°	10739	9702	9528
40°	10561	9411	9221
45°	10298	9137	8950
50°	10073	8827	8665
55°	9841	8527	8336
60°	9481	8155	8027
65°	9085	7753	7654
70°	8605	7294	7225
75°	7931	6784	6815
80°	7173	6263	6384
85°	6171	5740	6037

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10298 cd/sqm

TEST NUMBER: P1000835

CATALOG NUMBER: SA4XXDIP-B1195D1035UB30-4F0-XX-W2A-D4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	135.4	1.6
10°-20°	387.9	4.5
20°-30°	586.6	6.9
30°-40°	709.6	8.3
40°-50°	750.2	8.8
50°-60°	706.0	8.3
60°-70°	585.9	6.9
70°-80°	411.1	4.8
80°-90°	233.7	2.7
90°-100°	511.7	6.0
100°-110°	862.2	10.1
110°-120°	746.0	8.7
120°-130°	607.7	7.1
130°-140°	491.6	5.8
140°-150°	366.0	4.3
150°-160°	254.9	3.0
160°-170°	149.9	1.8
170°-180°	48.8	0.6
0°-30°	1109.9	13.0
0°-40°	1819.6	21.3
0°-60°	3275.8	38.3
0°-90°	4506.5	52.7
90°-120°	2119.9	24.8
90°-150°	3585.2	42.0
90°-180°	4039.0	47.3
0°-180°	8545.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1429	1429	1429	1429	1429	
5°	1431	1426	1415	1427	1426	136
15°	1371	1373	1368	1383	1381	386
25°	1255	1264	1269	1287	1288	578
35°	1098	1117	1133	1155	1160	687
45°	915	946	976	1003	1011	707
55°	717	750	798	830	840	639
65°	496	547	602	642	654	492
75°	275	334	402	446	461	292
85°	85	152	224	272	288	88
90°	27	98	176	225	238	20
95°	53	176	945	581	438	52
105°	130	214	754	1542	1549	139
115°	213	279	653	1221	1457	212
125°	290	342	620	1021	1150	259
135°	340	404	585	879	1002	263
145°	390	445	567	717	794	245
155°	442	477	552	625	651	204
165°	481	496	529	560	568	136
175°	502	503	507	514	512	48
180°	503	503	503	503	503	

TEST NUMBER: P1000835

CATALOG NUMBER: SA4XXDIP-B1195D1035UB30-4F0-XX-W2A-D4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1429.0	1429.0	1429.0	1429.0	1429.0
2.5°	1435.4	1430.6	1417.8	1429.0	1427.4
5°	1430.6	1425.8	1414.6	1427.4	1425.8
7.5°	1421.0	1417.8	1408.2	1422.6	1421.0
10°	1408.2	1406.6	1398.6	1413.0	1411.4
12.5°	1390.6	1390.6	1385.8	1398.6	1398.6
15°	1371.4	1373.0	1368.2	1382.6	1381.0
17.5°	1345.8	1350.6	1349.0	1363.4	1361.8
20°	1318.6	1323.4	1325.0	1341.0	1341.0
22.5°	1288.2	1294.6	1297.8	1313.8	1317.0
25°	1254.6	1264.2	1269.0	1286.6	1288.2
27.5°	1217.8	1232.2	1238.6	1254.6	1256.2
30°	1181.0	1193.8	1205.0	1222.6	1225.8
32.5°	1140.9	1157.0	1169.8	1190.6	1193.8
35°	1097.7	1116.9	1132.9	1155.4	1160.2
37.5°	1054.5	1076.9	1096.1	1118.5	1123.3
40°	1012.9	1033.7	1056.1	1080.1	1086.5
42.5°	964.9	988.9	1016.1	1043.3	1048.1
45°	915.3	945.7	976.1	1003.3	1011.3
47.5°	868.9	899.3	934.5	961.7	971.3
50°	817.7	852.9	888.1	920.1	929.7
52.5°	766.5	801.7	843.3	875.3	884.9
55°	716.9	750.5	798.5	830.5	840.1
57.5°	660.9	702.5	748.9	787.3	795.3
60°	606.5	648.1	700.9	737.7	750.5
62.5°	553.7	600.1	652.9	689.7	702.5
65°	496.1	547.3	601.7	641.7	654.5
67.5°	441.7	496.1	553.7	593.7	606.5
70°	385.7	440.1	500.9	544.1	555.3
72.5°	331.2	387.3	452.9	494.5	507.3
75°	275.2	334.4	401.7	446.5	460.9
77.5°	222.4	284.8	355.2	400.1	416.1
80°	174.4	238.4	308.8	356.8	369.6
82.5°	126.4	193.6	264.0	313.6	328.0
85°	84.8	152.0	224.0	272.0	288.0
87.5°	52.8	118.4	188.8	235.2	249.6
90°	26.6	97.5	176.2	224.6	238.4
92.5°	37.8	156.2	536.2	321.6	296.3
95°	53.4	176.4	944.7	581.2	438.0
97.5°	73.6	179.3	993.0	987.2	766.4
100°	92.7	187.7	916.2	1291.6	1082.3
102.5°	112.5	199.1	824.2	1477.6	1359.0
105°	130.0	214.0	754.0	1541.6	1549.0
107.5°	152.8	230.8	705.4	1511.4	1634.3
110°	173.9	246.2	680.3	1422.8	1628.3

TEST NUMBER: P1000835

CATALOG NUMBER: SA4XXDIP-B1195D1035UB30-4F0-XX-W2A-D4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	194.0	263.2	663.4	1316.3	1560.4
115°	213.2	279.4	653.4	1221.4	1456.9
117.5°	234.9	296.0	644.4	1143.5	1357.0
120°	255.1	310.3	636.4	1088.0	1272.2
122.5°	274.9	325.8	627.4	1049.8	1203.3
125°	290.1	341.8	620.0	1020.6	1150.3
127.5°	305.9	359.7	610.0	990.7	1114.6
130°	317.1	375.3	601.1	958.5	1081.3
132.5°	330.0	390.2	593.7	921.8	1046.6
135°	340.2	404.4	584.7	879.1	1002.4
137.5°	352.1	415.2	578.3	835.6	952.3
140°	364.9	426.6	572.5	793.0	899.8
142.5°	377.2	437.0	569.3	754.4	844.3
145°	390.0	444.8	567.3	717.2	793.8
147.5°	404.9	453.6	564.4	685.1	746.3
150°	418.7	462.0	561.4	661.2	705.7
152.5°	429.9	470.0	556.4	642.4	676.0
155°	441.8	476.9	551.5	624.7	651.3
157.5°	453.7	483.3	546.6	607.8	628.6
160°	464.5	488.8	540.6	591.0	607.8
162.5°	474.4	493.2	534.7	574.8	588.1
165°	481.3	496.2	528.8	559.9	568.3
167.5°	489.2	498.6	522.8	547.0	552.5
170°	494.2	500.6	516.9	534.2	537.7
172.5°	499.1	502.1	511.0	522.8	522.8
175°	502.1	503.1	507.0	513.9	512.0
177.5°	504.1	503.1	504.1	507.5	504.1
180°	503.1	503.1	503.1	503.1	503.1

(END OF REPORT)