

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P997766

Luminaire Tested: SA2XXRDP-B865DB2750-4F0-XX-W2A-A_2700K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P997766
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-29)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDP-B865DB2750-4F0-XX-W2A-A_2700K
Description: Define 2 Regressed Direct Recessed with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3252.0 lumens
Efficiency: N/A
Efficacy: 69.5 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 46.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P997766

CATALOG NUMBER: SA2XXRDP-B865DB2750-4F0-XX-W2A-A_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P997766

CATALOG NUMBER: SA2XXRDP-B865DB2750-4F0-XX-W2A-A_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10		0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102		100
1	111	106	103	100	108	104	101	98	100	97	95		96	94	92		93	91	89		87
2	102	95	89	84	100	93	88	83	90	85	81		87	83	80		84	81	78		76
3	94	85	78	72	92	84	77	72	81	75	71		78	73	69		76	72	68		66
4	87	77	69	63	85	76	68	63	73	67	62		71	66	61		69	64	60		59
5	81	70	62	56	79	69	61	56	67	60	55		65	59	55		63	58	54		52
6	76	64	56	50	74	63	55	50	61	54	49		60	54	49		58	53	49		47
7	71	59	51	45	69	58	50	45	56	50	45		55	49	44		54	48	44		42
8	66	54	46	41	65	53	46	41	52	45	41		51	45	40		50	44	40		39
9	62	50	43	38	61	50	42	37	49	42	37		47	41	37		47	41	37		35
10	59	47	39	35	58	46	39	35	45	39	34		44	38	34		44	38	34		33

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	29788	29788	29788	29788
5°	29922	33268	30027	26577
10°	29659	36911	29869	23038
15°	29082	38726	29575	18151
20°	28372	33572	28991	15706
25°	27500	22017	28094	14023
30°	26364	14820	27081	12692
35°	24967	12004	25776	11448
40°	23402	10673	24402	10592
45°	21721	9660	22630	9456
50°	19999	8791	20932	8759
55°	18082	8265	19056	8155
60°	16396	6914	17263	6832
65°	14840	5828	15724	6611
70°	13135	5387	14162	6234
75°	11357	5040	12397	5761
80°	9417	4649	10137	5123
85°	7356	4268	8082	4504

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 160°

Vertical Angle: 45°

Luminance: 32699 cd/sqm

TEST NUMBER: P997766

CATALOG NUMBER: SA2XXRDP-B865DB2750-4F0-XX-W2A-A_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	178.5	5.5
10°-20°	498.2	15.3
20°-30°	641.2	19.7
30°-40°	608.3	18.7
40°-50°	521.3	16.0
50°-60°	397.0	12.2
60°-70°	250.4	7.7
70°-80°	124.9	3.8
80°-90°	32.1	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1317.9	40.5
0°-40°	1926.2	59.2
0°-60°	2844.6	87.5
0°-90°	3252.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3252.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1882	1882	1882	1882	1882	
5°	1883	2094	1890	1673	1883	179
15°	1775	2363	1805	1108	1775	499
25°	1574	1261	1608	803	1574	723
35°	1292	621	1334	592	1292	808
45°	970	432	1011	422	970	749
55°	655	300	690	296	655	590
65°	396	156	420	176	396	393
75°	186	82	203	94	186	201
85°	40	24	44	25	40	49
90°	0	0	0	0	0	

TEST NUMBER: P997766

CATALOG NUMBER: SA2XXRDP-B865DB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8
2.5°	1893.6	1901.4	1905.3	1910.6	1922.3	1930.2	1942.0	1944.6	1943.3	1948.5	1934.1
5°	1883.1	1900.1	1915.8	1928.9	1949.8	1962.9	1977.3	1994.3	1998.2	2017.8	2006.0
7.5°	1868.7	1893.6	1915.8	1942.0	1973.3	1990.4	2012.6	2038.7	2050.5	2074.0	2080.6
10°	1845.2	1880.5	1918.4	1945.9	1989.0	2019.1	2040.0	2081.9	2109.4	2144.7	2139.4
12.5°	1807.3	1853.0	1904.0	1949.8	2006.0	2025.7	2064.9	2108.0	2143.4	2176.0	2204.8
15°	1774.6	1826.9	1883.1	1939.3	2003.4	2040.0	2079.3	2135.5	2173.4	2231.0	2255.8
17.5°	1730.1	1796.8	1863.5	1926.3	2002.1	2044.0	2092.4	2147.3	2203.5	2258.4	2278.0
20°	1684.3	1756.3	1828.2	1913.2	1999.5	2040.0	2089.7	2157.7	2212.7	2255.8	2255.8
22.5°	1629.4	1717.0	1799.4	1880.5	1974.7	2033.5	2084.5	2164.3	2203.5	2212.7	2177.4
25°	1574.5	1662.1	1752.3	1853.0	1960.3	2012.6	2070.1	2144.7	2157.7	2121.1	2029.6
27.5°	1509.1	1607.2	1709.2	1817.7	1930.2	1995.6	2047.9	2097.6	2072.7	1974.7	1832.1
30°	1442.4	1548.3	1663.4	1766.7	1902.7	1962.9	2007.4	2021.7	1943.3	1783.7	1599.3
32.5°	1373.1	1476.4	1598.0	1722.3	1859.6	1917.1	1945.9	1908.0	1764.1	1562.7	1337.8
35°	1292.0	1408.4	1535.3	1664.7	1800.7	1843.9	1860.9	1768.0	1583.6	1323.4	1099.8
37.5°	1218.8	1335.2	1471.2	1603.3	1735.3	1758.9	1741.9	1596.7	1362.6	1105.0	886.6
40°	1132.5	1256.7	1390.1	1537.9	1646.4	1653.0	1611.1	1422.8	1132.5	890.6	755.9
42.5°	1052.7	1178.3	1311.6	1462.0	1544.4	1522.2	1466.0	1218.8	945.5	767.6	659.1
45°	970.3	1089.3	1233.2	1366.6	1425.4	1373.1	1288.1	1025.3	793.8	660.4	576.7
47.5°	890.6	1001.7	1144.3	1272.4	1282.9	1224.0	1123.3	859.2	687.9	580.6	512.6
50°	812.1	923.3	1056.6	1162.6	1152.1	1071.0	957.3	746.7	597.6	512.6	456.4
52.5°	733.6	834.3	963.8	1047.5	1003.0	924.6	812.1	632.9	521.8	447.2	404.1
55°	655.2	749.3	860.5	929.8	859.2	768.9	689.2	542.7	452.5	392.3	359.6
57.5°	589.8	664.3	766.3	808.2	723.2	652.6	583.2	466.9	392.3	349.2	311.2
60°	517.9	585.9	669.6	694.4	606.8	549.2	490.4	394.9	336.1	298.2	273.3
62.5°	456.4	512.6	576.7	576.7	499.5	456.4	411.9	330.9	282.5	252.4	240.6
65°	396.2	436.8	482.5	477.3	411.9	374.0	338.7	273.3	236.7	215.8	204.0
67.5°	337.4	368.8	398.9	380.5	333.5	300.8	268.1	221.0	196.2	181.8	166.1
70°	283.8	308.6	324.3	307.3	260.2	232.8	209.2	177.8	158.2	139.9	130.8
72.5°	238.0	248.5	253.7	232.8	193.5	177.8	160.8	138.6	121.6	112.5	109.8
75°	185.7	194.9	190.9	175.2	142.5	130.8	117.7	102.0	98.1	92.8	90.2
77.5°	145.2	145.2	138.6	124.2	102.0	92.8	87.6	79.8	75.8	74.5	71.9
80°	103.3	102.0	98.1	82.4	69.3	64.1	64.1	58.8	57.5	54.9	54.9
82.5°	68.0	68.0	62.8	49.7	45.8	44.5	43.2	40.5	40.5	39.2	39.2
85°	40.5	37.9	31.4	27.5	26.2	26.2	24.8	23.5	24.8	23.5	23.5
87.5°	18.3	14.4	10.5	10.5	10.5	10.5	10.5	10.5	10.5	10.5	10.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P997766

CATALOG NUMBER: SA2XXRDP-B865DB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8
2.5°	1948.5	1951.1	1955.0	1973.3	1976.0	1981.2	1978.6	1978.6	1979.9	1977.3	1978.6
5°	2032.2	2036.1	2055.7	2078.0	2083.2	2078.0	2084.5	2093.7	2093.7	2093.7	2091.0
7.5°	2110.7	2125.0	2147.3	2180.0	2186.5	2193.0	2204.8	2197.0	2199.6	2211.4	2207.4
10°	2186.5	2207.4	2232.3	2259.7	2274.1	2283.3	2288.5	2300.3	2327.7	2296.4	2308.1
12.5°	2258.4	2288.5	2314.7	2344.7	2355.2	2367.0	2370.9	2381.4	2381.4	2380.1	2389.2
15°	2305.5	2333.0	2356.5	2376.1	2378.7	2376.1	2373.5	2374.8	2378.7	2363.1	2372.2
17.5°	2316.0	2318.6	2326.4	2318.6	2319.9	2292.4	2276.7	2272.8	2236.2	2237.5	2267.6
20°	2265.0	2220.5	2208.7	2165.6	2139.4	2068.8	2066.2	2046.6	1969.4	1993.0	1987.7
22.5°	2125.0	2049.2	1948.5	1898.8	1874.0	1799.4	1741.9	1701.3	1673.9	1646.4	1634.7
25°	1940.7	1817.7	1675.2	1577.1	1562.7	1493.4	1387.5	1337.8	1279.0	1260.6	1292.0
27.5°	1702.7	1543.1	1382.3	1231.9	1204.4	1141.6	1088.0	1052.7	984.7	980.8	983.4
30°	1379.6	1218.8	1084.1	986.0	918.0	889.2	853.9	827.8	800.3	810.8	813.4
32.5°	1133.8	980.8	855.2	802.9	771.6	753.2	723.2	706.2	694.4	690.5	689.2
35°	901.0	799.0	742.8	691.8	673.5	660.4	638.2	630.3	619.9	621.2	621.2
37.5°	771.6	686.6	644.7	618.6	601.6	595.0	580.6	572.8	566.2	563.6	567.6
40°	665.6	606.8	580.6	557.1	542.7	540.1	532.2	523.1	515.2	516.5	520.5
42.5°	588.5	554.5	523.1	504.8	494.3	490.4	483.9	477.3	477.3	473.4	472.1
45°	527.0	499.5	473.4	456.4	449.9	444.6	436.8	435.5	430.2	431.5	432.9
47.5°	472.1	449.9	430.2	413.2	406.7	405.4	397.5	392.3	392.3	391.0	389.7
50°	422.4	400.2	383.2	374.0	364.9	362.2	360.9	359.6	357.0	357.0	358.3
52.5°	381.9	359.6	346.5	338.7	333.5	330.9	330.9	329.5	329.5	329.5	328.2
55°	337.4	319.1	308.6	306.0	303.4	302.1	300.8	298.2	296.9	299.5	296.9
57.5°	295.5	289.0	279.9	277.2	270.7	270.7	266.8	264.2	261.5	264.2	264.2
60°	262.9	253.7	248.5	240.6	235.4	230.2	223.6	222.3	219.7	218.4	217.1
62.5°	228.9	221.0	207.9	196.2	188.3	183.1	180.5	179.2	179.2	177.8	177.8
65°	190.9	172.6	166.1	162.2	160.8	159.5	156.9	155.6	156.9	155.6	156.9
67.5°	149.1	146.5	142.5	139.9	138.6	137.3	137.3	136.0	136.0	136.0	136.0
70°	129.5	122.9	121.6	119.0	119.0	117.7	117.7	117.7	117.7	116.4	119.0
72.5°	107.2	103.3	102.0	100.7	100.7	100.7	99.4	99.4	99.4	98.1	99.4
75°	87.6	86.3	83.7	83.7	82.4	83.7	82.4	82.4	81.1	82.4	82.4
77.5°	70.6	69.3	68.0	68.0	66.7	66.7	66.7	66.7	66.7	66.7	68.0
80°	53.6	52.3	51.0	52.3	51.0	52.3	51.0	51.0	52.3	51.0	51.0
82.5°	39.2	37.9	37.9	36.6	36.6	36.6	36.6	36.6	36.6	36.6	36.6
85°	23.5	22.2	22.2	23.5	22.2	23.5	22.2	22.2	22.2	23.5	23.5
87.5°	10.5	11.8	10.5	10.5	10.5	10.5	10.5	10.5	10.5	10.5	11.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P997766

CATALOG NUMBER: SA2XXRDP-B865DB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8
2.5°	1983.8	1974.7	1972.0	1974.7	1972.0	1973.3	1964.2	1930.2	1939.3	1925.0	1932.8
5°	2096.3	2088.4	2071.4	2068.8	2066.2	2063.6	2050.5	2020.4	2008.7	1989.0	1987.7
7.5°	2203.5	2203.5	2190.4	2181.3	2169.5	2160.4	2143.4	2098.9	2080.6	2057.0	2044.0
10°	2309.4	2275.4	2289.8	2280.7	2251.9	2246.7	2215.3	2189.1	2153.8	2130.3	2109.4
12.5°	2385.3	2374.8	2361.7	2353.9	2346.0	2329.0	2308.1	2241.4	2223.1	2176.0	2152.5
15°	2382.7	2376.1	2380.1	2380.1	2377.4	2373.5	2356.5	2308.1	2276.7	2231.0	2190.4
17.5°	2254.5	2271.5	2288.5	2300.3	2326.4	2338.2	2353.9	2325.1	2305.5	2266.3	2223.1
20°	2030.9	2072.7	2122.4	2132.9	2156.4	2225.7	2257.1	2282.0	2289.8	2276.7	2241.4
22.5°	1719.7	1755.0	1875.3	1872.7	1906.7	1989.0	2080.6	2155.1	2214.0	2246.7	2233.6
25°	1347.0	1396.6	1460.7	1509.1	1620.3	1743.2	1857.0	1976.0	2078.0	2168.2	2190.4
27.5°	1018.7	1084.1	1135.1	1199.2	1255.4	1400.6	1547.0	1732.7	1851.7	2023.0	2112.0
30°	823.9	853.9	904.9	935.0	962.5	1073.6	1239.7	1422.8	1632.0	1829.5	1982.5
32.5°	703.6	724.5	762.4	775.5	804.2	878.8	983.4	1150.8	1366.6	1605.9	1807.3
35°	631.6	653.9	661.7	673.5	697.0	744.1	816.0	937.6	1132.5	1366.6	1607.2
37.5°	570.2	581.9	604.2	612.0	619.9	655.2	703.6	788.6	918.0	1110.3	1377.0
40°	527.0	533.5	545.3	551.9	557.1	581.9	625.1	682.6	778.1	924.6	1170.4
42.5°	481.2	489.1	496.9	504.8	511.3	530.9	557.1	612.0	676.1	787.2	965.1
45°	436.8	442.0	451.2	456.4	465.5	481.2	504.8	542.7	600.2	670.9	814.7
47.5°	396.2	402.8	406.7	413.2	419.8	436.8	459.0	483.9	530.9	600.2	704.9
50°	359.6	367.5	372.7	374.0	379.2	394.9	413.2	440.7	470.8	524.4	615.9
52.5°	333.5	334.8	338.7	343.9	342.6	351.8	368.8	389.7	421.1	464.2	530.9
55°	303.4	307.3	309.9	311.2	311.2	319.1	328.2	347.9	372.7	408.0	464.2
57.5°	265.5	269.4	277.2	279.9	283.8	287.7	291.6	304.7	325.6	359.6	405.4
60°	226.2	228.9	236.7	241.9	244.5	255.0	260.2	270.7	282.5	307.3	350.5
62.5°	181.8	184.4	188.3	193.5	198.8	214.5	227.5	238.0	247.2	264.2	299.5
65°	158.2	159.5	162.2	163.5	164.8	171.3	183.1	197.5	214.5	227.5	248.5
67.5°	137.3	138.6	139.9	142.5	143.8	145.2	150.4	154.3	171.3	189.6	205.3
70°	117.7	120.3	121.6	121.6	122.9	125.5	128.2	133.4	138.6	147.8	167.4
72.5°	99.4	100.7	103.3	103.3	103.3	105.9	108.5	111.2	113.8	119.0	126.8
75°	82.4	85.0	85.0	85.0	86.3	86.3	88.9	91.5	94.2	98.1	100.7
77.5°	68.0	68.0	68.0	68.0	69.3	69.3	70.6	73.2	74.5	75.8	78.5
80°	51.0	52.3	52.3	52.3	53.6	53.6	53.6	56.2	57.5	57.5	60.2
82.5°	37.9	37.9	37.9	39.2	37.9	39.2	39.2	40.5	39.2	40.5	41.8
85°	23.5	23.5	23.5	24.8	24.8	24.8	24.8	24.8	24.8	24.8	26.2
87.5°	11.8	11.8	11.8	11.8	11.8	11.8	11.8	11.8	13.1	11.8	11.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P997766

CATALOG NUMBER: SA2XXRDP-B865DB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8
2.5°	1921.0	1914.5	1914.5	1910.6	1910.6	1889.7	1889.7	1896.2	1888.3	1879.2	1866.1
5°	1970.7	1956.3	1952.4	1947.2	1930.2	1904.0	1893.6	1889.7	1874.0	1854.3	1832.1
7.5°	2017.8	1994.3	1982.5	1970.7	1948.5	1911.9	1891.0	1876.6	1853.0	1823.0	1794.2
10°	2063.6	2033.5	2003.4	1989.0	1957.7	1911.9	1881.8	1858.3	1824.3	1783.7	1743.2
12.5°	2105.4	2042.7	2037.4	2008.7	1962.9	1910.6	1864.8	1830.8	1787.7	1740.6	1693.5
15°	2142.0	2078.0	2046.6	2020.4	1960.3	1894.9	1846.5	1804.7	1747.1	1693.5	1636.0
17.5°	2160.4	2091.0	2070.1	2027.0	1965.5	1880.5	1815.1	1764.1	1701.3	1637.3	1571.9
20°	2178.7	2097.6	2063.6	2033.5	1949.8	1853.0	1779.8	1721.0	1651.7	1575.8	1503.9
22.5°	2187.8	2097.6	2057.0	2015.2	1934.1	1823.0	1736.7	1667.3	1586.3	1509.1	1422.8
25°	2172.1	2089.7	2041.4	1998.2	1906.7	1786.3	1687.0	1608.5	1522.2	1434.6	1347.0
27.5°	2132.9	2071.4	2015.2	1970.7	1868.7	1739.3	1634.7	1545.7	1456.8	1358.7	1269.8
30°	2059.7	2032.2	1987.7	1938.0	1826.9	1697.4	1573.2	1481.6	1383.6	1285.5	1192.6
32.5°	1945.9	1969.4	1940.7	1897.5	1777.2	1639.9	1507.8	1415.0	1307.7	1201.8	1116.8
35°	1807.3	1891.0	1875.3	1845.2	1724.9	1578.4	1446.3	1333.9	1226.6	1119.4	1034.4
37.5°	1655.6	1782.4	1795.5	1777.2	1664.7	1515.6	1370.5	1260.6	1150.8	1042.3	955.9
40°	1447.6	1642.5	1684.3	1692.2	1602.0	1439.8	1288.1	1180.9	1072.3	966.4	861.8
42.5°	1256.7	1502.6	1554.9	1587.6	1522.2	1365.3	1212.3	1093.3	986.0	890.6	785.9
45°	1077.6	1333.9	1418.9	1460.7	1432.0	1280.3	1122.0	1010.9	912.8	825.2	724.5
47.5°	893.2	1150.8	1269.8	1336.5	1336.5	1193.9	1035.7	925.9	831.7	757.2	668.2
50°	770.2	984.7	1107.6	1195.3	1218.8	1106.3	957.3	850.0	761.1	680.0	612.0
52.5°	656.5	848.7	950.7	1042.3	1110.3	1012.2	869.6	772.9	685.2	609.4	555.8
55°	567.6	711.4	804.2	904.9	980.8	916.7	784.6	690.5	614.6	551.9	506.1
57.5°	482.5	608.1	683.9	772.9	853.9	805.6	699.6	618.6	551.9	496.9	456.4
60°	410.6	512.6	571.5	640.8	741.5	707.5	619.9	545.3	491.7	442.0	408.0
62.5°	349.2	430.2	479.9	529.6	621.2	605.5	537.5	479.9	434.2	392.3	363.5
65°	286.4	353.1	392.3	435.5	508.7	515.2	460.3	419.8	377.9	341.3	315.2
67.5°	231.5	283.8	319.1	355.7	414.5	432.9	394.9	360.9	325.6	295.5	272.0
70°	187.0	223.6	249.8	278.5	326.9	349.2	329.5	306.0	277.2	252.4	231.5
72.5°	147.8	171.3	187.0	209.2	248.5	270.7	269.4	248.5	227.5	210.5	193.5
75°	108.5	126.8	139.9	154.3	185.7	206.6	211.9	202.7	181.8	168.7	155.6
77.5°	82.4	92.8	99.4	109.8	132.1	150.4	158.2	155.6	141.2	130.8	121.6
80°	62.8	65.4	68.0	71.9	90.2	107.2	112.5	111.2	103.3	99.4	88.9
82.5°	44.5	45.8	47.1	48.4	54.9	69.3	74.5	77.2	70.6	66.7	57.5
85°	26.2	27.5	27.5	30.1	31.4	35.3	44.5	44.5	43.2	37.9	36.6
87.5°	13.1	13.1	11.8	11.8	13.1	14.4	17.0	19.6	17.0	15.7	14.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P997766

CATALOG NUMBER: SA2XXRDP-B865DB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8
2.5°	1860.9	1862.2	1866.1	1854.3	1836.0	1828.2	1804.7	1800.7	1796.8	1796.8	1800.7
5°	1819.0	1813.8	1815.1	1792.9	1766.7	1751.0	1718.3	1723.6	1706.6	1696.1	1698.7
7.5°	1773.3	1758.9	1757.6	1728.8	1696.1	1667.3	1633.3	1625.5	1609.8	1591.5	1583.6
10°	1715.7	1705.3	1685.7	1653.0	1611.1	1587.6	1541.8	1514.3	1510.4	1483.0	1472.5
12.5°	1656.9	1638.6	1619.0	1573.2	1526.1	1488.2	1454.2	1424.1	1403.2	1379.6	1364.0
15°	1588.9	1566.6	1544.4	1496.0	1441.1	1403.2	1352.2	1307.7	1246.3	1197.9	1170.4
17.5°	1514.3	1489.5	1459.4	1405.8	1352.2	1299.9	1205.7	1153.4	1110.3	1081.5	1064.5
20°	1437.2	1409.7	1379.6	1326.0	1233.2	1141.6	1089.3	1048.8	1022.6	993.9	972.9
22.5°	1356.1	1327.3	1294.6	1210.9	1112.9	1048.8	1008.3	970.3	932.4	916.7	906.3
25°	1280.3	1254.1	1212.3	1098.5	1021.3	962.5	916.7	891.9	872.2	851.3	831.7
27.5°	1201.8	1153.4	1094.6	999.1	950.7	890.6	857.9	839.6	805.6	791.2	782.0
30°	1107.6	1054.0	997.8	929.8	873.6	831.7	801.6	771.6	751.9	737.6	721.9
32.5°	1012.2	961.2	925.9	855.2	813.4	770.2	741.5	723.2	694.4	685.2	678.7
35°	929.8	886.6	855.2	797.7	758.5	719.2	698.3	670.9	652.6	635.6	625.1
37.5°	848.7	825.2	792.5	744.1	702.2	670.9	642.1	632.9	608.1	598.9	588.5
40°	792.5	757.2	729.7	687.9	652.6	618.6	600.2	579.3	562.3	547.9	544.0
42.5°	724.5	698.3	682.6	636.9	600.2	580.6	558.4	534.9	521.8	510.0	495.6
45°	673.5	649.9	627.7	591.1	558.4	533.5	513.9	498.2	476.0	470.8	448.5
47.5°	619.9	596.3	579.3	542.7	512.6	489.1	474.7	453.8	435.5	423.7	413.2
50°	566.2	546.6	530.9	499.5	473.4	448.5	428.9	408.0	400.2	380.5	374.0
52.5°	515.2	502.2	485.2	455.1	428.9	408.0	387.1	370.1	358.3	347.9	340.0
55°	472.1	451.2	443.3	410.6	388.4	366.2	347.9	337.4	323.0	316.5	309.9
57.5°	423.7	411.9	398.9	374.0	349.2	328.2	315.2	299.5	291.6	283.8	278.5
60°	381.9	364.9	354.4	333.5	311.2	291.6	279.9	268.1	257.6	251.1	240.6
62.5°	333.5	320.4	313.9	291.6	273.3	255.0	244.5	232.8	224.9	213.2	200.1
65°	291.6	281.2	273.3	255.0	238.0	221.0	210.5	196.2	185.7	179.2	177.8
67.5°	255.0	247.2	235.4	218.4	201.4	188.3	176.5	164.8	163.5	160.8	160.8
70°	214.5	206.6	200.1	181.8	167.4	153.0	150.4	146.5	142.5	141.2	138.6
72.5°	179.2	172.6	164.8	149.1	134.7	130.8	128.2	125.5	121.6	120.3	119.0
75°	145.2	136.0	130.8	116.4	112.5	109.8	107.2	103.3	100.7	99.4	96.8
77.5°	111.2	102.0	102.0	94.2	91.5	87.6	85.0	82.4	81.1	78.5	78.5
80°	78.5	78.5	75.8	71.9	68.0	66.7	62.8	61.5	60.2	61.5	58.8
82.5°	57.5	52.3	52.3	49.7	47.1	45.8	43.2	43.2	41.8	41.8	41.8
85°	32.7	32.7	31.4	28.8	27.5	27.5	26.2	26.2	24.8	24.8	23.5
87.5°	13.1	11.8	13.1	11.8	11.8	10.5	10.5	10.5	9.2	10.5	9.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P997766

CATALOG NUMBER: SA2XXRDP-B865DB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8
2.5°	1800.7	1798.1	1790.3	1792.9	1789.0	1789.0	1786.3	1786.3	1786.3	1792.9	1789.0
5°	1702.7	1693.5	1684.3	1680.4	1676.5	1672.6	1672.6	1671.3	1683.0	1680.4	1690.9
7.5°	1581.0	1578.4	1560.1	1560.1	1553.6	1551.0	1557.5	1558.8	1560.1	1562.7	1569.3
10°	1472.5	1466.0	1439.8	1442.4	1438.5	1433.3	1437.2	1434.6	1443.7	1446.3	1443.7
12.5°	1344.3	1332.6	1303.8	1289.4	1273.7	1261.9	1276.3	1265.9	1302.5	1313.0	1341.7
15°	1174.3	1152.1	1132.5	1132.5	1118.1	1107.6	1114.2	1125.9	1133.8	1145.6	1150.8
17.5°	1060.6	1051.4	1035.7	1026.6	1022.6	1018.7	1018.7	1023.9	1040.9	1039.6	1050.1
20°	963.8	958.6	950.7	938.9	935.0	932.4	932.4	932.4	944.2	954.6	961.2
22.5°	897.1	893.2	887.9	872.2	864.4	861.8	868.3	872.2	881.4	889.2	895.8
25°	830.4	821.2	812.1	806.9	802.9	802.9	805.6	806.9	810.8	814.7	822.6
27.5°	775.5	768.9	755.9	741.5	741.5	737.6	740.2	742.8	751.9	765.0	771.6
30°	714.0	712.7	707.5	702.2	697.0	694.4	699.6	703.6	704.9	711.4	711.4
32.5°	669.6	660.4	651.2	646.0	643.4	642.1	643.4	648.6	648.6	656.5	665.6
35°	625.1	619.9	610.7	601.6	598.9	592.4	597.6	602.9	612.0	615.9	619.9
37.5°	576.7	570.2	566.2	563.6	558.4	559.7	555.8	563.6	571.5	570.2	572.8
40°	540.1	528.3	516.5	515.2	513.9	512.6	512.6	513.9	519.2	524.4	532.2
42.5°	493.0	489.1	478.6	468.2	465.5	462.9	460.3	465.5	476.0	485.2	489.1
45°	444.6	439.4	436.8	428.9	423.7	422.4	419.8	426.3	435.5	439.4	442.0
47.5°	400.2	398.9	391.0	392.3	388.4	389.7	388.4	392.3	392.3	396.2	398.9
50°	370.1	366.2	362.2	359.6	355.7	355.7	354.4	355.7	360.9	366.2	364.9
52.5°	340.0	333.5	332.2	330.9	328.2	330.9	326.9	328.2	333.5	336.1	334.8
55°	304.7	303.4	300.8	298.2	296.9	295.5	295.5	295.5	300.8	304.7	306.0
57.5°	277.2	270.7	265.5	265.5	260.2	258.9	261.5	262.9	266.8	269.4	272.0
60°	239.3	236.7	228.9	224.9	217.1	215.8	215.8	221.0	227.5	236.7	239.3
62.5°	198.8	194.9	193.5	193.5	193.5	193.5	193.5	193.5	193.5	194.9	194.9
65°	176.5	177.8	176.5	175.2	176.5	176.5	175.2	175.2	175.2	176.5	177.8
67.5°	158.2	156.9	158.2	156.9	155.6	155.6	154.3	155.6	156.9	158.2	158.2
70°	137.3	137.3	136.0	137.3	136.0	134.7	133.4	133.4	136.0	137.3	137.3
72.5°	117.7	117.7	116.4	116.4	113.8	113.8	115.1	113.8	113.8	117.7	117.7
75°	98.1	96.8	95.5	95.5	94.2	94.2	94.2	92.8	95.5	95.5	96.8
77.5°	77.2	77.2	77.2	75.8	75.8	74.5	74.5	75.8	75.8	75.8	77.2
80°	58.8	58.8	58.8	57.5	56.2	56.2	56.2	56.2	56.2	57.5	56.2
82.5°	40.5	40.5	40.5	40.5	40.5	39.2	39.2	39.2	40.5	40.5	39.2
85°	24.8	23.5	24.8	24.8	23.5	24.8	23.5	23.5	22.2	22.2	23.5
87.5°	10.5	9.2	7.8	7.8	9.2	7.8	7.8	7.8	9.2	7.8	7.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P997766

CATALOG NUMBER: SA2XXRDP-B865DB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8
2.5°	1792.9	1799.4	1796.8	1782.4	1796.8	1800.7	1808.6	1816.4	1821.7	1829.5	1836.0
5°	1680.4	1693.5	1701.3	1693.5	1719.7	1723.6	1741.9	1752.3	1768.0	1781.1	1791.6
7.5°	1574.5	1585.0	1600.6	1603.3	1619.0	1637.3	1663.4	1689.6	1714.4	1727.5	1739.3
10°	1460.7	1479.0	1502.6	1497.3	1520.9	1549.6	1577.1	1619.0	1639.9	1663.4	1684.3
12.5°	1347.0	1358.7	1390.1	1400.6	1434.6	1456.8	1494.7	1520.9	1573.2	1600.6	1619.0
15°	1148.2	1196.6	1235.8	1282.9	1327.3	1369.2	1403.2	1450.3	1496.0	1517.0	1547.0
17.5°	1057.9	1080.2	1103.7	1127.3	1184.8	1259.3	1319.5	1370.5	1409.7	1437.2	1472.5
20°	963.8	986.0	1012.2	1034.4	1069.7	1123.3	1197.9	1285.5	1332.6	1361.3	1395.3
22.5°	897.1	918.0	935.0	954.6	982.1	1021.3	1077.6	1186.1	1248.9	1284.2	1314.3
25°	825.2	851.3	869.6	884.0	906.3	949.4	995.2	1056.6	1169.1	1196.6	1238.4
27.5°	775.5	783.3	804.2	826.5	848.7	872.2	919.3	971.6	1047.5	1107.6	1158.6
30°	716.6	736.2	755.9	765.0	784.6	818.6	847.4	903.6	962.5	1009.6	1071.0
32.5°	672.2	683.9	697.0	719.2	737.6	761.1	789.9	836.9	886.6	916.7	963.8
35°	622.5	630.3	657.8	666.9	685.2	708.8	737.6	774.2	827.8	851.3	885.3
37.5°	575.4	593.7	601.6	622.5	639.5	663.0	683.9	725.8	761.1	788.6	819.9
40°	538.8	546.6	561.0	579.3	593.7	612.0	638.2	668.2	706.2	728.4	755.9
42.5°	494.3	500.9	519.2	529.6	553.2	570.2	585.9	622.5	656.5	673.5	700.9
45°	445.9	461.6	473.4	494.3	507.4	528.3	547.9	574.1	605.5	625.1	640.8
47.5°	404.1	419.8	431.5	451.2	472.1	481.2	502.2	529.6	558.4	574.1	596.3
50°	370.1	375.3	397.5	406.7	428.9	447.2	461.6	485.2	516.5	525.7	544.0
52.5°	337.4	341.3	355.7	367.5	387.1	402.8	421.1	443.3	469.5	483.9	498.2
55°	308.6	311.2	317.8	330.9	343.9	363.5	380.5	401.5	423.7	439.4	452.5
57.5°	275.9	281.2	286.4	294.2	307.3	325.6	343.9	363.5	381.9	392.3	409.3
60°	238.0	245.9	255.0	264.2	273.3	286.4	307.3	325.6	342.6	351.8	364.9
62.5°	197.5	213.2	221.0	231.5	239.3	251.1	266.8	287.7	299.5	311.2	321.7
65°	177.8	179.2	180.5	190.9	205.3	217.1	231.5	247.2	265.5	273.3	281.2
67.5°	158.2	159.5	162.2	163.5	168.7	181.8	197.5	214.5	228.9	234.1	241.9
70°	138.6	138.6	143.8	145.2	146.5	147.8	160.8	177.8	190.9	197.5	206.6
72.5°	117.7	119.0	121.6	122.9	125.5	128.2	132.1	141.2	156.9	163.5	173.9
75°	96.8	98.1	99.4	100.7	104.6	105.9	109.8	115.1	121.6	129.5	136.0
77.5°	77.2	77.2	78.5	81.1	83.7	85.0	88.9	91.5	94.2	98.1	103.3
80°	57.5	58.8	58.8	61.5	61.5	62.8	64.1	68.0	70.6	73.2	75.8
82.5°	39.2	41.8	41.8	41.8	43.2	44.5	45.8	45.8	48.4	49.7	53.6
85°	23.5	24.8	24.8	24.8	23.5	26.2	26.2	27.5	27.5	27.5	28.8
87.5°	9.2	7.8	9.2	9.2	9.2	10.5	9.2	9.2	10.5	11.8	11.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P997766

CATALOG NUMBER: SA2XXRDP-B865DB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1881.8	1881.8	1881.8	1881.8
2.5°	1847.8	1843.9	1867.4	1893.6
5°	1809.9	1816.4	1846.5	1883.1
7.5°	1770.7	1785.0	1820.3	1868.7
10°	1715.7	1741.9	1795.5	1845.2
12.5°	1662.1	1697.4	1748.4	1807.3
15°	1602.0	1641.2	1704.0	1774.6
17.5°	1535.3	1579.7	1653.0	1730.1
20°	1464.6	1523.5	1600.6	1684.3
22.5°	1386.2	1456.8	1536.6	1629.4
25°	1310.3	1387.5	1467.3	1574.5
27.5°	1235.8	1311.6	1400.6	1509.1
30°	1161.3	1230.6	1326.0	1442.4
32.5°	1081.5	1153.4	1254.1	1373.1
35°	1008.3	1080.2	1174.3	1292.0
37.5°	929.8	1006.9	1097.2	1218.8
40°	838.2	928.5	1016.1	1132.5
42.5°	762.4	857.9	942.9	1052.7
45°	702.2	792.5	863.1	970.3
47.5°	646.0	719.2	791.2	890.6
50°	592.4	648.6	723.2	812.1
52.5°	537.5	585.9	649.9	733.6
55°	487.8	533.5	591.1	655.2
57.5°	442.0	474.7	532.2	589.8
60°	391.0	425.0	469.5	517.9
62.5°	347.9	374.0	415.9	456.4
65°	302.1	326.9	358.3	396.2
67.5°	260.2	282.5	307.3	337.4
70°	222.3	239.3	257.6	283.8
72.5°	181.8	200.1	217.1	238.0
75°	149.1	156.9	171.3	185.7
77.5°	115.1	125.5	133.4	145.2
80°	82.4	91.5	94.2	103.3
82.5°	54.9	60.2	65.4	68.0
85°	31.4	34.0	39.2	40.5
87.5°	11.8	13.1	15.7	18.3
90°	0.0	0.0	0.0	0.0

TEST NUMBER: P997766

CATALOG NUMBER: SA2XXRDP-B865DB2750-4F0-XX-W2A-A_2700K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	22.83	24.28	23.19	24.59	24.91	17.24	18.69	17.61	19.01	19.32
	3H	24.16	25.46	24.54	25.78	26.15	18.37	19.67	18.75	20.00	20.36
	4H	24.58	25.80	24.98	26.15	26.53	18.83	20.05	19.23	20.40	20.78
	6H	24.86	25.98	25.27	26.35	26.74	19.21	20.33	19.62	20.70	21.09
	8H	24.93	26.00	25.36	26.39	26.79	19.33	20.40	19.76	20.79	21.19
	12H	24.97	25.99	25.40	26.37	26.80	19.42	20.44	19.85	20.82	21.25
4H	2H	22.81	24.02	23.21	24.37	24.75	17.93	19.14	18.33	19.49	19.87
	3H	24.25	25.26	24.66	25.66	26.06	19.22	20.22	19.63	20.62	21.03
	4H	24.75	25.66	25.19	26.07	26.51	19.78	20.68	20.21	21.10	21.54
	6H	25.13	25.92	25.59	26.36	26.82	20.26	21.04	20.72	21.48	21.95
	8H	25.24	25.97	25.71	26.42	26.89	20.42	21.15	20.89	21.60	22.07
	12H	25.32	25.97	25.80	26.45	26.92	20.54	21.19	21.02	21.67	22.14
8H	4H	24.74	25.47	25.21	25.92	26.39	20.09	20.83	20.56	21.27	21.74
	6H	25.16	25.76	25.66	26.26	26.73	20.68	21.28	21.18	21.77	22.25
	8H	25.31	25.85	25.82	26.36	26.85	20.91	21.45	21.42	21.96	22.45
	12H	25.42	25.90	25.93	26.39	26.96	21.10	21.57	21.61	22.07	22.63
12H	4H	24.72	25.37	25.20	25.85	26.32	20.13	20.78	20.61	21.26	21.73
	6H	25.14	25.68	25.65	26.19	26.68	20.74	21.28	21.25	21.79	22.28
	8H	25.31	25.79	25.82	26.28	26.85	21.02	21.50	21.53	21.99	22.56