

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000846

Luminaire Tested: SA4XXDIP-B1195D1035UB35-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000846
REPORT IS A COMBINATION OF REPORTS P995459 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B1195D1035UB35-4F0-XX-W2A-F1
Description: Define 4 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8711.0 lumens
Efficiency: N/A
Efficacy: 97.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 89.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000846

CATALOG NUMBER: SA4XXDIP-B1195D1035UB35-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1000846

CATALOG NUMBER: SA4XXDIP-B1195D1035UB35-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	65	65	65
1	100	95	91	88	93	89	86	83	78	75	73	67	65	63	57	56	54
2	91	83	77	72	85	78	72	68	68	64	60	59	56	53	50	48	46
3	83	73	66	60	77	69	62	57	60	55	51	52	48	45	44	41	39
4	76	65	57	51	71	61	54	48	53	48	43	46	42	38	40	36	34
5	70	58	50	43	65	54	47	41	48	42	37	42	37	33	36	32	29
6	64	52	44	38	60	49	41	36	43	37	33	38	33	29	32	29	26
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	30	26	23
8	55	43	35	29	51	40	33	28	36	30	26	31	27	23	27	23	21
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	19
10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	23	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16355	16355	16355
5°	16369	15885	15904
10°	16230	15444	15336
15°	15998	14919	14694
20°	15700	14353	14031
25°	15366	13753	13316
30°	14962	13105	12531
35°	14544	12442	11773
40°	14109	11728	10966
45°	13652	11012	10212
50°	13146	10318	9377
55°	12597	9508	8547
60°	12034	8620	7684
65°	11391	7704	6709
70°	10648	6599	5666
75°	9542	5320	4539
80°	8131	3845	3192
85°	6316	2142	1719

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13652 cd/sqm

TEST NUMBER: P1000846

CATALOG NUMBER: SA4XXDIP-B1195D1035UB35-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	189.0	2.2
10°-20°	532.6	6.1
20°-30°	783.8	9.0
30°-40°	911.2	10.5
40°-50°	911.1	10.5
50°-60°	796.9	9.1
60°-70°	591.6	6.8
70°-80°	335.7	3.9
80°-90°	98.9	1.1
90°-100°	83.6	1.0
100°-110°	250.5	2.9
110°-120°	425.6	4.9
120°-130°	561.3	6.4
130°-140°	630.4	7.2
140°-150°	619.6	7.1
150°-160°	521.1	6.0
160°-170°	346.7	4.0
170°-180°	121.4	1.4
0°-30°	1505.5	17.3
0°-40°	2416.7	27.7
0°-60°	4124.6	47.3
0°-90°	5150.8	59.1
90°-120°	759.7	8.7
90°-150°	2571.0	29.5
90°-180°	3560.0	40.9
0°-180°	8711.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2006	2006	2006	2006	2006	
5°	2004	1998	1980	1998	1994	190
15°	1908	1901	1877	1887	1882	538
25°	1728	1716	1694	1696	1689	795
35°	1487	1475	1453	1442	1434	930
45°	1213	1202	1176	1159	1154	935
55°	918	913	890	871	861	822
65°	622	614	598	582	574	616
75°	331	323	315	309	307	351
85°	87	87	84	84	82	93
90°	3	14	22	28	30	10
95°	60	68	75	78	78	64
105°	231	232	236	239	242	245
115°	433	433	431	430	429	427
125°	630	630	629	627	625	562
135°	813	819	819	817	814	629
145°	987	991	992	991	988	618
155°	1131	1131	1130	1134	1130	521
165°	1232	1229	1227	1232	1229	347
175°	1281	1276	1275	1282	1275	122
180°	1283	1283	1283	1283	1283	

TEST NUMBER: P1000846

CATALOG NUMBER: SA4XXDIP-B1195D1035UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2005.7	2005.7	2005.7	2005.7	2005.7
2.5°	2012.1	2007.3	1989.6	2005.7	2004.1
5°	2004.1	1997.7	1980.0	1997.7	1994.4
7.5°	1989.6	1983.2	1963.9	1978.4	1976.8
10°	1968.7	1962.3	1941.4	1954.3	1951.1
12.5°	1941.4	1935.0	1912.5	1926.9	1922.1
15°	1907.7	1901.2	1877.1	1886.8	1881.9
17.5°	1869.1	1861.1	1838.6	1845.0	1841.8
20°	1825.7	1817.7	1793.6	1798.4	1795.2
22.5°	1779.1	1767.8	1743.7	1753.4	1746.9
25°	1727.7	1716.4	1693.9	1695.5	1689.1
27.5°	1669.8	1658.6	1637.7	1634.4	1626.4
30°	1611.9	1599.1	1578.2	1571.8	1563.7
32.5°	1550.9	1539.6	1517.1	1509.1	1501.1
35°	1486.6	1475.3	1452.8	1441.6	1433.6
37.5°	1419.1	1409.4	1385.3	1374.1	1362.8
40°	1353.2	1340.3	1316.2	1300.2	1292.1
42.5°	1282.5	1276.1	1248.7	1229.5	1224.6
45°	1213.4	1202.1	1176.4	1158.7	1153.9
47.5°	1141.1	1133.0	1108.9	1089.6	1076.8
50°	1067.1	1060.7	1038.2	1015.7	1006.1
52.5°	994.8	986.8	962.7	943.4	930.5
55°	917.7	912.8	890.3	871.1	861.4
57.5°	845.3	840.5	818.0	798.7	789.1
60°	769.8	761.8	740.9	726.4	718.4
62.5°	695.9	689.5	667.0	654.1	646.1
65°	622.0	613.9	597.9	581.8	573.7
67.5°	546.4	540.0	523.9	507.9	506.2
70°	477.3	466.1	453.2	440.4	435.5
72.5°	403.4	392.1	382.5	372.9	368.0
75°	331.1	323.0	315.0	308.6	307.0
77.5°	260.4	257.1	249.1	247.5	242.7
80°	197.7	192.9	189.6	186.4	184.8
82.5°	136.6	135.0	135.0	133.4	131.8
85°	86.8	86.8	83.6	83.6	82.0
87.5°	41.8	40.2	38.6	38.6	38.6
90°	3.0	13.9	21.8	27.8	29.8
92.5°	25.8	38.7	43.7	46.6	47.6
95°	59.5	68.5	75.4	78.4	78.4
97.5°	95.3	103.2	111.1	115.1	115.1
100°	138.9	142.9	151.8	153.8	153.8
102.5°	184.6	185.6	193.5	196.5	197.5
105°	231.2	232.2	236.2	239.2	242.1
107.5°	279.9	280.8	281.8	285.8	284.8
110°	329.5	331.5	330.5	328.5	331.5

TEST NUMBER: P1000846

CATALOG NUMBER: SA4XXDIP-B1195D1035UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	381.1	381.1	379.1	379.1	379.1
115°	432.7	432.7	430.7	429.7	428.7
117.5°	481.3	481.3	480.3	477.3	474.4
120°	529.9	533.9	530.9	526.0	527.9
122.5°	580.5	581.5	580.5	577.6	572.6
125°	630.2	630.2	629.2	627.2	625.2
127.5°	674.8	677.8	675.8	673.8	672.8
130°	722.5	725.4	725.4	723.4	719.5
132.5°	771.1	773.1	772.1	770.1	769.1
135°	812.8	818.7	818.7	816.7	813.8
137.5°	859.4	862.4	864.4	861.4	862.4
140°	906.0	908.0	908.0	907.0	906.0
142.5°	948.7	950.7	949.7	949.7	949.7
145°	987.4	991.4	992.4	991.4	988.4
147.5°	1027.1	1032.1	1031.1	1030.1	1029.1
150°	1062.8	1066.8	1066.8	1066.8	1065.8
152.5°	1096.6	1098.6	1099.6	1102.5	1099.6
155°	1131.3	1131.3	1130.3	1134.3	1130.3
157.5°	1161.1	1159.1	1159.1	1162.1	1159.1
160°	1186.9	1185.9	1184.9	1187.9	1182.9
162.5°	1210.7	1207.7	1206.7	1212.7	1207.7
165°	1231.5	1228.6	1226.6	1232.5	1228.6
167.5°	1248.4	1244.4	1244.4	1250.4	1244.4
170°	1262.3	1257.3	1258.3	1264.3	1257.3
172.5°	1272.2	1268.3	1268.3	1275.2	1268.3
175°	1281.2	1276.2	1275.2	1282.2	1275.2
177.5°	1285.1	1280.2	1280.2	1287.1	1279.2
180°	1283.1	1283.1	1283.1	1283.1	1283.1

(END OF REPORT)