

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P997770

Luminaire Tested: SA2XXRDP-B865DB2750-4F0-XX-W2A-A_5000K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P997770
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-29)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDP-B865DB2750-4F0-XX-W2A-A_5000K
Description: Define 2 Regressed Direct Recessed with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3154.0 lumens
Efficiency: N/A
Efficacy: 67.4 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 46.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P997770

CATALOG NUMBER: SA2XXRDP-B865DB2750-4F0-XX-W2A-A_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P997770

CATALOG NUMBER: SA2XXRDP-B865DB2750-4F0-XX-W2A-A_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	106	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87		
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76		
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66		
4	87	77	69	63	85	76	68	63	73	67	62	71	66	61	69	64	60	59		
5	81	70	62	56	79	69	61	56	67	60	55	65	59	55	63	58	54	52		
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47		
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42		
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	39		
9	62	50	43	38	61	50	42	37	49	42	37	47	41	37	47	41	37	35		
10	59	47	39	35	58	46	39	35	45	39	34	44	38	34	44	38	34	33		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	28890	28890	28890	28890
5°	29021	32266	29121	25776
10°	28765	35799	28969	22344
15°	28205	37557	28683	17605
20°	27518	32560	28116	15233
25°	26670	21355	27246	13601
30°	25569	14374	26266	12310
35°	24215	11641	24999	11102
40°	22697	10352	23666	10274
45°	21067	9369	21947	9172
50°	19395	8526	20302	8496
55°	17535	8014	18482	7909
60°	15902	6705	16744	6626
65°	14394	5652	15248	6412
70°	12737	5225	13736	6044
75°	11015	4887	12024	5584
80°	9134	4512	9827	4968
85°	7138	4141	7828	4377

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 160°

Vertical Angle: 45°

Luminance: 31714 cd/sqm

TEST NUMBER: P997770

CATALOG NUMBER: SA2XXRDP-B865DB2750-4F0-XX-W2A-A_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	173.1	5.5
10°-20°	483.2	15.3
20°-30°	621.9	19.7
30°-40°	590.0	18.7
40°-50°	505.6	16.0
50°-60°	385.1	12.2
60°-70°	242.8	7.7
70°-80°	121.1	3.8
80°-90°	31.1	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1278.2	40.5
0°-40°	1868.2	59.2
0°-60°	2758.9	87.5
0°-90°	3154.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3154.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1825	1825	1825	1825	1825	
5°	1826	2031	1833	1622	1826	173
15°	1721	2292	1750	1074	1721	484
25°	1527	1223	1560	779	1527	701
35°	1253	602	1294	574	1253	784
45°	941	418	980	410	941	726
55°	635	290	670	287	635	573
65°	384	151	407	171	384	381
75°	180	80	197	91	180	195
85°	39	23	43	24	39	47
90°	0	0	0	0	0	

TEST NUMBER: P997770

CATALOG NUMBER: SA2XXRDP-B865DB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1
2.5°	1836.5	1844.1	1847.9	1853.0	1864.4	1872.0	1883.4	1886.0	1884.7	1889.8	1875.8
5°	1826.4	1842.9	1858.1	1870.8	1891.1	1903.7	1917.7	1934.2	1938.0	1957.0	1945.6
7.5°	1812.4	1836.5	1858.1	1883.4	1913.9	1930.4	1951.9	1977.3	1988.7	2011.5	2017.9
10°	1789.6	1823.8	1860.6	1887.2	1929.1	1958.3	1978.6	2019.2	2045.8	2080.0	2075.0
12.5°	1752.8	1797.2	1846.7	1891.1	1945.6	1964.6	2002.7	2044.5	2078.8	2110.5	2138.4
15°	1721.1	1771.8	1826.4	1880.9	1943.1	1978.6	2016.6	2071.2	2107.9	2163.7	2187.8
17.5°	1678.0	1742.7	1807.3	1868.2	1941.8	1982.4	2029.3	2082.6	2137.1	2190.4	2209.4
20°	1633.6	1703.3	1773.1	1855.5	1939.2	1978.6	2026.8	2092.7	2146.0	2187.8	2187.8
22.5°	1580.3	1665.3	1745.2	1823.8	1915.2	1972.2	2021.7	2099.1	2137.1	2146.0	2111.7
25°	1527.0	1612.0	1699.5	1797.2	1901.2	1951.9	2007.7	2080.0	2092.7	2057.2	1968.4
27.5°	1463.6	1558.8	1657.7	1763.0	1872.0	1935.4	1986.2	2034.4	2010.3	1915.2	1776.9
30°	1398.9	1501.7	1613.3	1713.5	1845.4	1903.7	1946.9	1960.8	1884.7	1730.0	1551.1
32.5°	1331.7	1431.9	1549.9	1670.4	1803.5	1859.3	1887.2	1850.5	1711.0	1515.6	1297.5
35°	1253.1	1366.0	1489.0	1614.6	1746.5	1788.3	1804.8	1714.8	1535.9	1283.5	1066.7
37.5°	1182.1	1294.9	1426.9	1555.0	1683.0	1705.9	1689.4	1548.6	1321.6	1071.7	859.9
40°	1098.4	1218.8	1348.2	1491.5	1596.8	1603.1	1562.6	1379.9	1098.4	863.7	733.1
42.5°	1021.0	1142.7	1272.1	1418.0	1497.9	1476.3	1421.8	1182.1	917.0	744.5	639.2
45°	941.1	1056.5	1196.0	1325.4	1382.5	1331.7	1249.3	994.4	769.9	640.5	559.3
47.5°	863.7	971.5	1109.8	1234.1	1244.2	1187.1	1089.5	833.3	667.1	563.1	497.2
50°	787.6	895.4	1024.8	1127.5	1117.4	1038.7	928.4	724.2	579.6	497.2	442.6
52.5°	711.5	809.2	934.7	1015.9	972.8	896.7	787.6	613.9	506.1	433.8	391.9
55°	635.4	726.7	834.5	901.8	833.3	745.8	668.4	526.3	438.8	380.5	348.8
57.5°	572.0	644.3	743.2	783.8	701.4	632.9	565.7	452.8	380.5	338.6	301.9
60°	502.3	568.2	649.4	673.5	588.5	532.7	475.6	383.0	326.0	289.2	265.1
62.5°	442.6	497.2	559.3	559.3	484.5	442.6	399.5	320.9	274.0	244.8	233.4
65°	384.3	423.6	468.0	462.9	399.5	362.7	328.5	265.1	229.6	209.3	197.9
67.5°	327.2	357.7	386.8	369.1	323.4	291.7	260.0	214.3	190.2	176.3	161.1
70°	275.2	299.3	314.5	298.1	252.4	225.8	202.9	172.5	153.5	135.7	126.8
72.5°	230.8	241.0	246.1	225.8	187.7	172.5	156.0	134.4	118.0	109.1	106.5
75°	180.1	189.0	185.2	170.0	138.2	126.8	114.1	98.9	95.1	90.1	87.5
77.5°	140.8	140.8	134.4	120.5	98.9	90.1	85.0	77.4	73.6	72.3	69.8
80°	100.2	98.9	95.1	79.9	67.2	62.1	62.1	57.1	55.8	53.3	53.3
82.5°	66.0	66.0	60.9	48.2	44.4	43.1	41.9	39.3	39.3	38.0	38.0
85°	39.3	36.8	30.4	26.6	25.4	25.4	24.1	22.8	24.1	22.8	22.8
87.5°	17.8	14.0	10.1	10.1	10.1	10.1	10.1	10.1	10.1	10.1	10.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P997770

CATALOG NUMBER: SA2XXRDP-B865DB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1
2.5°	1889.8	1892.3	1896.1	1913.9	1916.4	1921.5	1919.0	1919.0	1920.2	1917.7	1919.0
5°	1971.0	1974.8	1993.8	2015.3	2020.4	2015.3	2021.7	2030.6	2030.6	2030.6	2028.0
7.5°	2047.1	2061.0	2082.6	2114.3	2120.6	2127.0	2138.4	2130.8	2133.3	2144.7	2140.9
10°	2120.6	2140.9	2165.0	2191.6	2205.6	2214.5	2219.5	2231.0	2257.6	2227.2	2238.6
12.5°	2190.4	2219.5	2244.9	2274.1	2284.2	2295.6	2299.4	2309.6	2309.6	2308.3	2317.2
15°	2236.0	2262.7	2285.5	2304.5	2307.1	2304.5	2302.0	2303.3	2307.1	2291.8	2300.7
17.5°	2246.2	2248.7	2256.3	2248.7	2250.0	2223.4	2208.1	2204.3	2168.8	2170.1	2199.3
20°	2196.7	2153.6	2142.2	2100.3	2075.0	2006.5	2003.9	1984.9	1910.1	1932.9	1927.8
22.5°	2061.0	1987.4	1889.8	1841.6	1817.5	1745.2	1689.4	1650.1	1623.4	1596.8	1585.4
25°	1882.2	1763.0	1624.7	1529.6	1515.6	1448.4	1345.7	1297.5	1240.4	1222.7	1253.1
27.5°	1651.3	1496.6	1340.6	1194.7	1168.1	1107.2	1055.2	1021.0	955.0	951.2	953.8
30°	1338.1	1182.1	1051.4	956.3	890.4	862.5	828.2	802.8	776.2	786.4	788.9
32.5°	1099.6	951.2	829.5	778.7	748.3	730.5	701.4	684.9	673.5	669.7	668.4
35°	873.9	774.9	720.4	670.9	653.2	640.5	618.9	611.3	601.2	602.4	602.4
37.5°	748.3	665.9	625.3	599.9	583.4	577.1	563.1	555.5	549.2	546.6	550.4
40°	645.6	588.5	563.1	540.3	526.3	523.8	516.2	507.3	499.7	501.0	504.8
42.5°	570.7	537.8	507.3	489.6	479.4	475.6	469.3	462.9	462.9	459.1	457.9
45°	511.1	484.5	459.1	442.6	436.3	431.2	423.6	422.3	417.3	418.5	419.8
47.5°	457.9	436.3	417.3	400.8	394.4	393.2	385.6	380.5	380.5	379.2	378.0
50°	409.7	388.1	371.6	362.7	353.9	351.3	350.1	348.8	346.2	346.2	347.5
52.5°	370.3	348.8	336.1	328.5	323.4	320.9	320.9	319.6	319.6	319.6	318.3
55°	327.2	309.5	299.3	296.8	294.2	293.0	291.7	289.2	287.9	290.4	287.9
57.5°	286.6	280.3	271.4	268.9	262.5	262.5	258.7	256.2	253.7	256.2	256.2
60°	254.9	246.1	241.0	233.4	228.3	223.2	216.9	215.6	213.1	211.8	210.5
62.5°	222.0	214.3	201.7	190.2	182.6	177.6	175.0	173.8	173.8	172.5	172.5
65°	185.2	167.4	161.1	157.3	156.0	154.7	152.2	150.9	152.2	150.9	152.2
67.5°	144.6	142.1	138.2	135.7	134.4	133.2	133.2	131.9	131.9	131.9	131.9
70°	125.6	119.2	118.0	115.4	115.4	114.1	114.1	114.1	114.1	112.9	115.4
72.5°	104.0	100.2	98.9	97.7	97.7	97.7	96.4	96.4	96.4	95.1	96.4
75°	85.0	83.7	81.2	81.2	79.9	81.2	79.9	79.9	78.6	79.9	79.9
77.5°	68.5	67.2	66.0	66.0	64.7	64.7	64.7	64.7	64.7	64.7	66.0
80°	52.0	50.7	49.5	50.7	49.5	50.7	49.5	49.5	50.7	49.5	49.5
82.5°	38.0	36.8	36.8	35.5	35.5	35.5	35.5	35.5	35.5	35.5	35.5
85°	22.8	21.6	21.6	22.8	21.6	22.8	21.6	21.6	21.6	22.8	22.8
87.5°	10.1	11.4	10.1	10.1	10.1	10.1	10.1	10.1	10.1	10.1	11.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P997770

CATALOG NUMBER: SA2XXRDP-B865DB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1
2.5°	1924.0	1915.2	1912.6	1915.2	1912.6	1913.9	1905.0	1872.0	1880.9	1867.0	1874.6
5°	2033.1	2025.5	2009.0	2006.5	2003.9	2001.4	1988.7	1959.5	1948.1	1929.1	1927.8
7.5°	2137.1	2137.1	2124.4	2115.5	2104.1	2095.3	2078.8	2035.6	2017.9	1995.1	1982.4
10°	2239.8	2206.9	2220.8	2211.9	2184.0	2179.0	2148.5	2123.2	2088.9	2066.1	2045.8
12.5°	2313.4	2303.3	2290.6	2283.0	2275.4	2258.9	2238.6	2173.9	2156.1	2110.5	2087.6
15°	2310.9	2304.5	2308.3	2308.3	2305.8	2302.0	2285.5	2238.6	2208.1	2163.7	2124.4
17.5°	2186.6	2203.1	2219.5	2231.0	2256.3	2267.7	2283.0	2255.1	2236.0	2198.0	2156.1
20°	1969.7	2010.3	2058.5	2068.6	2091.4	2158.7	2189.1	2213.2	2220.8	2208.1	2173.9
22.5°	1667.8	1702.1	1818.8	1816.2	1849.2	1929.1	2017.9	2090.2	2147.3	2179.0	2166.3
25°	1306.4	1354.6	1416.7	1463.6	1571.4	1690.7	1801.0	1916.4	2015.3	2102.9	2124.4
27.5°	988.0	1051.4	1100.9	1163.0	1217.6	1358.4	1500.4	1680.5	1795.9	1962.1	2048.3
30°	799.0	828.2	877.7	906.8	933.5	1041.3	1202.4	1379.9	1582.9	1774.4	1922.8
32.5°	682.4	702.6	739.4	752.1	780.0	852.3	953.8	1116.1	1325.4	1557.5	1752.8
35°	612.6	634.2	641.8	653.2	676.0	721.7	791.4	909.4	1098.4	1325.4	1558.8
37.5°	553.0	564.4	586.0	593.6	601.2	635.4	682.4	764.8	890.4	1076.8	1335.5
40°	511.1	517.5	528.9	535.2	540.3	564.4	606.3	662.1	754.6	896.7	1135.1
42.5°	466.7	474.3	482.0	489.6	495.9	514.9	540.3	593.6	655.7	763.5	936.0
45°	423.6	428.7	437.6	442.6	451.5	466.7	489.6	526.3	582.2	650.6	790.2
47.5°	384.3	390.6	394.4	400.8	407.1	423.6	445.2	469.3	514.9	582.2	683.6
50°	348.8	356.4	361.5	362.7	367.8	383.0	400.8	427.4	456.6	508.6	597.4
52.5°	323.4	324.7	328.5	333.6	332.3	341.2	357.7	378.0	408.4	450.3	514.9
55°	294.2	298.1	300.6	301.9	301.9	309.5	318.3	337.4	361.5	395.7	450.3
57.5°	257.5	261.3	268.9	271.4	275.2	279.0	282.8	295.5	315.8	348.8	393.2
60°	219.4	222.0	229.6	234.6	237.2	247.3	252.4	262.5	274.0	298.1	339.9
62.5°	176.3	178.8	182.6	187.7	192.8	208.0	220.7	230.8	239.7	256.2	290.4
65°	153.5	154.7	157.3	158.5	159.8	166.1	177.6	191.5	208.0	220.7	241.0
67.5°	133.2	134.4	135.7	138.2	139.5	140.8	145.9	149.7	166.1	183.9	199.1
70°	114.1	116.7	118.0	118.0	119.2	121.8	124.3	129.4	134.4	143.3	162.3
72.5°	96.4	97.7	100.2	100.2	100.2	102.7	105.3	107.8	110.3	115.4	123.0
75°	79.9	82.4	82.4	82.4	83.7	83.7	86.2	88.8	91.3	95.1	97.7
77.5°	66.0	66.0	66.0	66.0	67.2	67.2	68.5	71.0	72.3	73.6	76.1
80°	49.5	50.7	50.7	50.7	52.0	52.0	52.0	54.5	55.8	55.8	58.3
82.5°	36.8	36.8	36.8	38.0	36.8	38.0	38.0	39.3	38.0	39.3	40.6
85°	22.8	22.8	22.8	24.1	24.1	24.1	24.1	24.1	24.1	24.1	25.4
87.5°	11.4	11.4	11.4	11.4	11.4	11.4	11.4	11.4	12.7	11.4	11.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P997770

CATALOG NUMBER: SA2XXRDP-B865DB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1
2.5°	1863.1	1856.8	1856.8	1853.0	1853.0	1832.7	1832.7	1839.1	1831.4	1822.6	1809.9
5°	1911.3	1897.4	1893.6	1888.5	1872.0	1846.7	1836.5	1832.7	1817.5	1798.5	1776.9
7.5°	1957.0	1934.2	1922.8	1911.3	1889.8	1854.3	1834.0	1820.0	1797.2	1768.0	1740.1
10°	2001.4	1972.2	1943.1	1929.1	1898.7	1854.3	1825.1	1802.3	1769.3	1730.0	1690.7
12.5°	2042.0	1981.1	1976.0	1948.1	1903.7	1853.0	1808.6	1775.6	1733.8	1688.1	1642.5
15°	2077.5	2015.3	1984.9	1959.5	1901.2	1837.8	1790.9	1750.3	1694.5	1642.5	1586.7
17.5°	2095.3	2028.0	2007.7	1965.9	1906.3	1823.8	1760.4	1711.0	1650.1	1587.9	1524.5
20°	2113.0	2034.4	2001.4	1972.2	1891.1	1797.2	1726.2	1669.1	1601.9	1528.3	1458.6
22.5°	2121.9	2034.4	1995.1	1954.5	1875.8	1768.0	1684.3	1617.1	1538.5	1463.6	1379.9
25°	2106.7	2026.8	1979.8	1938.0	1849.2	1732.5	1636.1	1560.0	1476.3	1391.3	1306.4
27.5°	2068.6	2009.0	1954.5	1911.3	1812.4	1686.9	1585.4	1499.1	1412.9	1317.8	1231.5
30°	1997.6	1971.0	1927.8	1879.6	1771.8	1646.3	1525.8	1437.0	1341.9	1246.8	1156.7
32.5°	1887.2	1910.1	1882.2	1840.3	1723.6	1590.5	1462.4	1372.3	1268.3	1165.6	1083.1
35°	1752.8	1834.0	1818.8	1789.6	1672.9	1530.9	1402.8	1293.7	1189.7	1085.7	1003.2
37.5°	1605.7	1728.7	1741.4	1723.6	1614.6	1470.0	1329.2	1222.7	1116.1	1010.8	927.1
40°	1404.0	1593.0	1633.6	1641.2	1553.7	1396.4	1249.3	1145.3	1040.0	937.3	835.8
42.5°	1218.8	1457.3	1508.0	1539.7	1476.3	1324.1	1175.7	1060.3	956.3	863.7	762.3
45°	1045.1	1293.7	1376.1	1416.7	1388.8	1241.7	1088.2	980.4	885.3	800.3	702.6
47.5°	866.3	1116.1	1231.5	1296.2	1296.2	1158.0	1004.5	898.0	806.6	734.4	648.1
50°	747.0	955.0	1074.3	1159.2	1182.1	1073.0	928.4	824.4	738.2	659.5	593.6
52.5°	636.7	823.1	922.1	1010.8	1076.8	981.7	843.4	749.6	664.6	591.0	539.0
55°	550.4	690.0	780.0	877.7	951.2	889.1	761.0	669.7	596.1	535.2	490.8
57.5°	468.0	589.8	663.3	749.6	828.2	781.3	678.5	599.9	535.2	482.0	442.6
60°	398.2	497.2	554.3	621.5	719.1	686.2	601.2	528.9	476.9	428.7	395.7
62.5°	338.6	417.3	465.5	513.7	602.4	587.2	521.3	465.5	421.1	380.5	352.6
65°	277.8	342.4	380.5	422.3	493.4	499.7	446.4	407.1	366.5	331.0	305.7
67.5°	224.5	275.2	309.5	345.0	402.1	419.8	383.0	350.1	315.8	286.6	263.8
70°	181.4	216.9	242.2	270.2	317.1	338.6	319.6	296.8	268.9	244.8	224.5
72.5°	143.3	166.1	181.4	202.9	241.0	262.5	261.3	241.0	220.7	204.2	187.7
75°	105.3	123.0	135.7	149.7	180.1	200.4	205.5	196.6	176.3	163.6	150.9
77.5°	79.9	90.1	96.4	106.5	128.1	145.9	153.5	150.9	137.0	126.8	118.0
80°	60.9	63.4	66.0	69.8	87.5	104.0	109.1	107.8	100.2	96.4	86.2
82.5°	43.1	44.4	45.7	46.9	53.3	67.2	72.3	74.8	68.5	64.7	55.8
85°	25.4	26.6	26.6	29.2	30.4	34.2	43.1	43.1	41.9	36.8	35.5
87.5°	12.7	12.7	11.4	11.4	12.7	14.0	16.5	19.0	16.5	15.2	14.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P997770

CATALOG NUMBER: SA2XXRDP-B865DB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1
2.5°	1804.8	1806.1	1809.9	1798.5	1780.7	1773.1	1750.3	1746.5	1742.7	1742.7	1746.5
5°	1764.2	1759.1	1760.4	1738.9	1713.5	1698.3	1666.6	1671.6	1655.1	1645.0	1647.5
7.5°	1719.8	1705.9	1704.6	1676.7	1645.0	1617.1	1584.1	1576.5	1561.3	1543.5	1535.9
10°	1664.0	1653.9	1634.9	1603.1	1562.6	1539.7	1495.3	1468.7	1464.9	1438.3	1428.1
12.5°	1607.0	1589.2	1570.2	1525.8	1480.1	1443.3	1410.4	1381.2	1360.9	1338.1	1322.8
15°	1541.0	1519.4	1497.9	1450.9	1397.7	1360.9	1311.4	1268.3	1208.7	1161.8	1135.1
17.5°	1468.7	1444.6	1415.4	1363.4	1311.4	1260.7	1169.4	1118.7	1076.8	1048.9	1032.4
20°	1393.9	1367.2	1338.1	1286.1	1196.0	1107.2	1056.5	1017.2	991.8	963.9	943.6
22.5°	1315.2	1287.3	1255.6	1174.5	1079.3	1017.2	977.9	941.1	904.3	889.1	878.9
25°	1241.7	1216.3	1175.7	1065.4	990.6	933.5	889.1	865.0	846.0	825.7	806.6
27.5°	1165.6	1118.7	1061.6	969.0	922.1	863.7	832.0	814.3	781.3	767.3	758.5
30°	1074.3	1022.3	967.7	901.8	847.2	806.6	777.5	748.3	729.3	715.3	700.1
32.5°	981.7	932.2	898.0	829.5	788.9	747.0	719.1	701.4	673.5	664.6	658.3
35°	901.8	859.9	829.5	773.7	735.6	697.6	677.3	650.6	632.9	616.4	606.3
37.5°	823.1	800.3	768.6	721.7	681.1	650.6	622.7	613.9	589.8	580.9	570.7
40°	768.6	734.4	707.7	667.1	632.9	599.9	582.2	561.9	545.4	531.4	527.6
42.5°	702.6	677.3	662.1	617.7	582.2	563.1	541.6	518.7	506.1	494.6	480.7
45°	653.2	630.4	608.8	573.3	541.6	517.5	498.4	483.2	461.7	456.6	435.0
47.5°	601.2	578.4	561.9	526.3	497.2	474.3	460.4	440.1	422.3	410.9	400.8
50°	549.2	530.2	514.9	484.5	459.1	435.0	416.0	395.7	388.1	369.1	362.7
52.5°	499.7	487.0	470.5	441.4	416.0	395.7	375.4	358.9	347.5	337.4	329.8
55°	457.9	437.6	430.0	398.2	376.7	355.1	337.4	327.2	313.3	306.9	300.6
57.5°	410.9	399.5	386.8	362.7	338.6	318.3	305.7	290.4	282.8	275.2	270.2
60°	370.3	353.9	343.7	323.4	301.9	282.8	271.4	260.0	249.9	243.5	233.4
62.5°	323.4	310.7	304.4	282.8	265.1	247.3	237.2	225.8	218.1	206.7	194.1
65°	282.8	272.7	265.1	247.3	230.8	214.3	204.2	190.2	180.1	173.8	172.5
67.5°	247.3	239.7	228.3	211.8	195.3	182.6	171.2	159.8	158.5	156.0	156.0
70°	208.0	200.4	194.1	176.3	162.3	148.4	145.9	142.1	138.2	137.0	134.4
72.5°	173.8	167.4	159.8	144.6	130.6	126.8	124.3	121.8	118.0	116.7	115.4
75°	140.8	131.9	126.8	112.9	109.1	106.5	104.0	100.2	97.7	96.4	93.9
77.5°	107.8	98.9	98.9	91.3	88.8	85.0	82.4	79.9	78.6	76.1	76.1
80°	76.1	76.1	73.6	69.8	66.0	64.7	60.9	59.6	58.3	59.6	57.1
82.5°	55.8	50.7	50.7	48.2	45.7	44.4	41.9	41.9	40.6	40.6	40.6
85°	31.7	31.7	30.4	27.9	26.6	26.6	25.4	25.4	24.1	24.1	22.8
87.5°	12.7	11.4	12.7	11.4	11.4	10.1	10.1	10.1	8.9	10.1	8.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P997770

CATALOG NUMBER: SA2XXRDP-B865DB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1
2.5°	1746.5	1743.9	1736.3	1738.9	1735.1	1735.1	1732.5	1732.5	1732.5	1738.9	1735.1
5°	1651.3	1642.5	1633.6	1629.8	1626.0	1622.2	1622.2	1620.9	1632.3	1629.8	1639.9
7.5°	1533.4	1530.9	1513.1	1513.1	1506.8	1504.2	1510.6	1511.8	1513.1	1515.6	1522.0
10°	1428.1	1421.8	1396.4	1398.9	1395.1	1390.1	1393.9	1391.3	1400.2	1402.8	1400.2
12.5°	1303.8	1292.4	1264.5	1250.6	1235.3	1223.9	1237.9	1227.7	1263.2	1273.4	1301.3
15°	1138.9	1117.4	1098.4	1098.4	1084.4	1074.3	1080.6	1092.0	1099.6	1111.0	1116.1
17.5°	1028.6	1019.7	1004.5	995.6	991.8	988.0	988.0	993.1	1009.6	1008.3	1018.5
20°	934.7	929.7	922.1	910.6	906.8	904.3	904.3	904.3	915.7	925.9	932.2
22.5°	870.1	866.3	861.2	846.0	838.4	835.8	842.2	846.0	854.8	862.5	868.8
25°	805.4	796.5	787.6	782.5	778.7	778.7	781.3	782.5	786.4	790.2	797.8
27.5°	752.1	745.8	733.1	719.1	719.1	715.3	717.9	720.4	729.3	742.0	748.3
30°	692.5	691.2	686.2	681.1	676.0	673.5	678.5	682.4	683.6	690.0	690.0
32.5°	649.4	640.5	631.6	626.5	624.0	622.7	624.0	629.1	629.1	636.7	645.6
35°	606.3	601.2	592.3	583.4	580.9	574.5	579.6	584.7	593.6	597.4	601.2
37.5°	559.3	553.0	549.2	546.6	541.6	542.8	539.0	546.6	554.3	553.0	555.5
40°	523.8	512.4	501.0	499.7	498.4	497.2	497.2	498.4	503.5	508.6	516.2
42.5°	478.2	474.3	464.2	454.1	451.5	449.0	446.4	451.5	461.7	470.5	474.3
45°	431.2	426.2	423.6	416.0	410.9	409.7	407.1	413.5	422.3	426.2	428.7
47.5°	388.1	386.8	379.2	380.5	376.7	378.0	376.7	380.5	380.5	384.3	386.8
50°	358.9	355.1	351.3	348.8	345.0	345.0	343.7	345.0	350.1	355.1	353.9
52.5°	329.8	323.4	322.2	320.9	318.3	320.9	317.1	318.3	323.4	326.0	324.7
55°	295.5	294.2	291.7	289.2	287.9	286.6	286.6	286.6	291.7	295.5	296.8
57.5°	268.9	262.5	257.5	257.5	252.4	251.1	253.7	254.9	258.7	261.3	263.8
60°	232.1	229.6	222.0	218.1	210.5	209.3	209.3	214.3	220.7	229.6	232.1
62.5°	192.8	189.0	187.7	187.7	187.7	187.7	187.7	187.7	187.7	189.0	189.0
65°	171.2	172.5	171.2	170.0	171.2	171.2	170.0	170.0	170.0	171.2	172.5
67.5°	153.5	152.2	153.5	152.2	150.9	150.9	149.7	150.9	152.2	153.5	153.5
70°	133.2	133.2	131.9	133.2	131.9	130.6	129.4	129.4	131.9	133.2	133.2
72.5°	114.1	114.1	112.9	112.9	110.3	110.3	111.6	110.3	110.3	114.1	114.1
75°	95.1	93.9	92.6	92.6	91.3	91.3	91.3	90.1	92.6	92.6	93.9
77.5°	74.8	74.8	74.8	73.6	73.6	72.3	72.3	73.6	73.6	73.6	74.8
80°	57.1	57.1	57.1	55.8	54.5	54.5	54.5	54.5	54.5	55.8	54.5
82.5°	39.3	39.3	39.3	39.3	39.3	38.0	38.0	38.0	39.3	39.3	38.0
85°	24.1	22.8	24.1	24.1	22.8	24.1	22.8	22.8	21.6	21.6	22.8
87.5°	10.1	8.9	7.6	7.6	8.9	7.6	7.6	7.6	8.9	7.6	7.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P997770

CATALOG NUMBER: SA2XXRDP-B865DB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1
2.5°	1738.9	1745.2	1742.7	1728.7	1742.7	1746.5	1754.1	1761.7	1766.8	1774.4	1780.7
5°	1629.8	1642.5	1650.1	1642.5	1667.8	1671.6	1689.4	1699.5	1714.8	1727.4	1737.6
7.5°	1527.0	1537.2	1552.4	1555.0	1570.2	1587.9	1613.3	1638.7	1662.8	1675.4	1686.9
10°	1416.7	1434.5	1457.3	1452.2	1475.0	1502.9	1529.6	1570.2	1590.5	1613.3	1633.6
12.5°	1306.4	1317.8	1348.2	1358.4	1391.3	1412.9	1449.7	1475.0	1525.8	1552.4	1570.2
15°	1113.6	1160.5	1198.6	1244.2	1287.3	1327.9	1360.9	1406.6	1450.9	1471.2	1500.4
17.5°	1026.1	1047.6	1070.5	1093.3	1149.1	1221.4	1279.7	1329.2	1367.2	1393.9	1428.1
20°	934.7	956.3	981.7	1003.2	1037.5	1089.5	1161.8	1246.8	1292.4	1320.3	1353.3
22.5°	870.1	890.4	906.8	925.9	952.5	990.6	1045.1	1150.4	1211.2	1245.5	1274.7
25°	800.3	825.7	843.4	857.4	878.9	920.8	965.2	1024.8	1133.9	1160.5	1201.1
27.5°	752.1	759.7	780.0	801.6	823.1	846.0	891.6	942.4	1015.9	1074.3	1123.7
30°	695.0	714.1	733.1	742.0	761.0	794.0	821.9	876.4	933.5	979.1	1038.7
32.5°	651.9	663.3	676.0	697.6	715.3	738.2	766.1	811.7	859.9	889.1	934.7
35°	603.7	611.3	638.0	646.8	664.6	687.4	715.3	750.8	802.8	825.7	858.6
37.5°	558.1	575.8	583.4	603.7	620.2	643.0	663.3	703.9	738.2	764.8	795.2
40°	522.5	530.2	544.1	561.9	575.8	593.6	618.9	648.1	684.9	706.4	733.1
42.5°	479.4	485.8	503.5	513.7	536.5	553.0	568.2	603.7	636.7	653.2	679.8
45°	432.5	447.7	459.1	479.4	492.1	512.4	531.4	556.8	587.2	606.3	621.5
47.5°	391.9	407.1	418.5	437.6	457.9	466.7	487.0	513.7	541.6	556.8	578.4
50°	358.9	364.0	385.6	394.4	416.0	433.8	447.7	470.5	501.0	509.9	527.6
52.5°	327.2	331.0	345.0	356.4	375.4	390.6	408.4	430.0	455.3	469.3	483.2
55°	299.3	301.9	308.2	320.9	333.6	352.6	369.1	389.4	410.9	426.2	438.8
57.5°	267.6	272.7	277.8	285.4	298.1	315.8	333.6	352.6	370.3	380.5	397.0
60°	230.8	238.4	247.3	256.2	265.1	277.8	298.1	315.8	332.3	341.2	353.9
62.5°	191.5	206.7	214.3	224.5	232.1	243.5	258.7	279.0	290.4	301.9	312.0
65°	172.5	173.8	175.0	185.2	199.1	210.5	224.5	239.7	257.5	265.1	272.7
67.5°	153.5	154.7	157.3	158.5	163.6	176.3	191.5	208.0	222.0	227.0	234.6
70°	134.4	134.4	139.5	140.8	142.1	143.3	156.0	172.5	185.2	191.5	200.4
72.5°	114.1	115.4	118.0	119.2	121.8	124.3	128.1	137.0	152.2	158.5	168.7
75°	93.9	95.1	96.4	97.7	101.5	102.7	106.5	111.6	118.0	125.6	131.9
77.5°	74.8	74.8	76.1	78.6	81.2	82.4	86.2	88.8	91.3	95.1	100.2
80°	55.8	57.1	57.1	59.6	59.6	60.9	62.1	66.0	68.5	71.0	73.6
82.5°	38.0	40.6	40.6	40.6	41.9	43.1	44.4	44.4	46.9	48.2	52.0
85°	22.8	24.1	24.1	24.1	22.8	25.4	25.4	26.6	26.6	26.6	27.9
87.5°	8.9	7.6	8.9	8.9	8.9	10.1	8.9	8.9	10.1	11.4	11.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P997770

CATALOG NUMBER: SA2XXRDP-B865DB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1825.1	1825.1	1825.1	1825.1
2.5°	1792.1	1788.3	1811.1	1836.5
5°	1755.3	1761.7	1790.9	1826.4
7.5°	1717.3	1731.2	1765.5	1812.4
10°	1664.0	1689.4	1741.4	1789.6
12.5°	1612.0	1646.3	1695.7	1752.8
15°	1553.7	1591.7	1652.6	1721.1
17.5°	1489.0	1532.1	1603.1	1678.0
20°	1420.5	1477.6	1552.4	1633.6
22.5°	1344.4	1412.9	1490.3	1580.3
25°	1270.8	1345.7	1423.0	1527.0
27.5°	1198.6	1272.1	1358.4	1463.6
30°	1126.3	1193.5	1286.1	1398.9
32.5°	1048.9	1118.7	1216.3	1331.7
35°	977.9	1047.6	1138.9	1253.1
37.5°	901.8	976.6	1064.1	1182.1
40°	813.0	900.5	985.5	1098.4
42.5°	739.4	832.0	914.5	1021.0
45°	681.1	768.6	837.1	941.1
47.5°	626.5	697.6	767.3	863.7
50°	574.5	629.1	701.4	787.6
52.5°	521.3	568.2	630.4	711.5
55°	473.1	517.5	573.3	635.4
57.5°	428.7	460.4	516.2	572.0
60°	379.2	412.2	455.3	502.3
62.5°	337.4	362.7	403.3	442.6
65°	293.0	317.1	347.5	384.3
67.5°	252.4	274.0	298.1	327.2
70°	215.6	232.1	249.9	275.2
72.5°	176.3	194.1	210.5	230.8
75°	144.6	152.2	166.1	180.1
77.5°	111.6	121.8	129.4	140.8
80°	79.9	88.8	91.3	100.2
82.5°	53.3	58.3	63.4	66.0
85°	30.4	33.0	38.0	39.3
87.5°	11.4	12.7	15.2	17.8
90°	0.0	0.0	0.0	0.0

TEST NUMBER: P997770

CATALOG NUMBER: SA2XXRDP-B865DB2750-4F0-XX-W2A-A_5000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	22.72	24.17	23.09	24.49	24.80	17.14	18.59	17.50	18.90	19.22
	3H	24.05	25.35	24.43	25.68	26.04	18.26	19.56	18.64	19.89	20.25
	4H	24.48	25.69	24.88	26.04	26.42	18.72	19.94	19.13	20.29	20.67
	6H	24.75	25.87	25.16	26.24	26.63	19.10	20.22	19.51	20.59	20.98
	8H	24.82	25.89	25.25	26.28	26.68	19.23	20.29	19.65	20.68	21.08
	12H	24.86	25.88	25.29	26.27	26.69	19.31	20.33	19.74	20.71	21.14
4H	2H	22.70	23.92	23.10	24.26	24.64	17.82	19.04	18.22	19.39	19.77
	3H	24.14	25.15	24.55	25.55	25.95	19.11	20.12	19.52	20.52	20.92
	4H	24.65	25.55	25.08	25.97	26.41	19.67	20.57	20.10	20.99	21.43
	6H	25.02	25.81	25.48	26.25	26.71	20.15	20.93	20.61	21.38	21.84
	8H	25.14	25.87	25.60	26.31	26.78	20.31	21.05	20.78	21.49	21.96
	12H	25.21	25.86	25.69	26.34	26.81	20.44	21.09	20.92	21.57	22.04
8H	4H	24.64	25.37	25.10	25.81	26.28	19.99	20.72	20.45	21.16	21.63
	6H	25.05	25.66	25.55	26.15	26.63	20.57	21.17	21.07	21.67	22.15
	8H	25.20	25.74	25.72	26.25	26.74	20.80	21.34	21.32	21.85	22.34
	12H	25.31	25.79	25.83	26.28	26.85	20.99	21.47	21.50	21.96	22.53
12H	4H	24.61	25.27	25.10	25.75	26.22	20.02	20.68	20.51	21.16	21.63
	6H	25.03	25.57	25.55	26.08	26.57	20.63	21.17	21.15	21.68	22.17
	8H	25.21	25.68	25.72	26.18	26.74	20.92	21.39	21.43	21.89	22.45