

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000868

Luminaire Tested: SA4XXDIP-B1195D1205UB27-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000868
REPORT IS A COMBINATION OF REPORTS P995481 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B1195D1205UB27-4F0-XX-W2A-A4
Description: Define 4 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9554.0 lumens
Efficiency: N/A
Efficacy: 99.2 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.3 / 1.41
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 96.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000868

CATALOG NUMBER: SA4XXDIP-B1195D1205UB27-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1000868

CATALOG NUMBER: SA4XXDIP-B1195D1205UB27-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61
1	99	95	91	88	92	88	85	82	76	74	71	65	63	61	54	53	52
2	91	83	77	72	84	78	72	68	67	63	60	57	54	52	48	46	44
3	83	73	66	60	77	68	62	57	59	54	50	51	47	44	43	40	38
4	76	65	57	51	70	61	54	49	53	47	43	45	41	38	38	35	33
5	70	58	50	44	65	54	47	42	47	42	37	41	36	33	35	31	29
6	64	52	44	38	60	49	42	37	43	37	33	37	33	29	32	28	25
7	60	47	39	34	55	44	37	32	39	33	29	34	29	26	29	25	23
8	55	43	35	30	51	40	33	29	36	30	26	31	26	23	27	23	20
9	52	39	32	27	48	37	30	26	33	27	23	28	24	21	25	21	18
10	48	36	29	24	45	34	27	23	30	25	21	26	22	19	23	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15615	15615	15615	15615
5°	15576	17914	15667	13460
10°	15459	20900	15577	11809
15°	15273	24094	15380	10567
20°	15076	26126	15185	9474
25°	14787	25827	14928	8667
30°	14505	21347	14681	8251
35°	14109	15908	14264	8000
40°	13647	11984	13778	7877
45°	12941	9618	13102	7709
50°	12097	8103	12274	7630
55°	11106	7052	11281	7540
60°	10144	6211	10441	7415
65°	9239	5343	9327	7106
70°	8177	4396	8353	6543
75°	7132	3378	7086	5559
80°	5610	2220	5548	4220
85°	3697	998	3464	2461

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 145°

Vertical Angle: 45°

Luminance: 20191 cd/sqm

TEST NUMBER: P1000868

CATALOG NUMBER: SA4XXDIP-B1195D1205UB27-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	186.4	2.0
10°-20°	575.2	6.0
20°-30°	913.8	9.6
30°-40°	1015.4	10.6
40°-50°	923.4	9.7
50°-60°	754.6	7.9
60°-70°	538.6	5.6
70°-80°	296.4	3.1
80°-90°	82.4	0.9
90°-100°	424.7	4.4
100°-110°	886.6	9.3
110°-120°	788.1	8.2
120°-130°	663.4	6.9
130°-140°	553.5	5.8
140°-150°	422.6	4.4
150°-160°	297.1	3.1
160°-170°	174.7	1.8
170°-180°	56.8	0.6
0°-30°	1675.4	17.5
0°-40°	2690.8	28.2
0°-60°	4368.8	45.7
0°-90°	5286.3	55.3
90°-120°	2099.4	22.0
90°-150°	3739.0	39.1
90°-180°	4268.0	44.7
0°-180°	9554.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1915	1915	1915	1915	1915	
5°	1907	2246	1918	1688	1907	181
15°	1821	3086	1834	1353	1821	514
25°	1663	3276	1678	1099	1663	766
35°	1442	1937	1458	974	1442	901
45°	1150	1087	1164	871	1150	887
55°	809	711	822	760	809	728
65°	504	457	509	608	504	498
75°	248	228	246	376	248	260
85°	51	48	48	117	51	59
90°	1	24	1	24	1	6
95°	38	281	38	281	38	42
105°	135	1620	135	1620	135	143
115°	237	1555	237	1555	237	235
125°	330	1241	330	1241	330	294
135°	393	1110	393	1110	393	303
145°	452	906	452	906	452	284
155°	515	759	515	759	515	237
165°	561	662	561	662	561	158
175°	585	596	585	596	585	56
180°	586	586	586	586	586	

TEST NUMBER: P1000868

CATALOG NUMBER: SA4XXDIP-B1195D1205UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9
2.5°	1914.9	1933.9	1941.9	1948.2	1968.8	1975.2	1976.8	1986.3	1994.2	1995.8	1995.8
5°	1907.0	1937.1	1960.9	1983.1	2016.4	2030.7	2048.2	2067.2	2092.6	2108.4	2116.4
7.5°	1894.3	1938.7	1975.2	2013.3	2059.3	2087.8	2103.7	2154.4	2189.4	2217.9	2252.8
10°	1875.2	1932.3	1984.7	2040.2	2105.3	2140.2	2175.1	2236.9	2286.1	2341.7	2386.1
12.5°	1846.7	1921.2	1984.7	2062.4	2143.3	2184.6	2225.8	2333.7	2390.8	2440.0	2519.3
15°	1821.3	1895.9	1986.3	2065.6	2165.6	2227.4	2287.7	2357.5	2447.9	2554.2	2630.4
17.5°	1792.7	1886.3	1970.4	2081.5	2192.5	2251.2	2300.4	2408.3	2535.2	2639.9	2709.7
20°	1753.1	1848.3	1959.3	2076.7	2208.4	2254.4	2319.4	2463.8	2578.0	2681.2	2795.4
22.5°	1707.1	1818.1	1935.5	2048.2	2184.6	2281.4	2352.8	2479.7	2617.7	2736.7	2865.2
25°	1662.6	1783.2	1886.3	2040.2	2184.6	2249.6	2330.5	2481.3	2632.0	2776.4	2908.0
27.5°	1615.0	1727.7	1867.3	1989.5	2152.9	2224.3	2311.5	2476.5	2636.7	2781.1	2922.3
30°	1562.7	1683.3	1799.1	1943.4	2102.1	2194.1	2275.0	2454.3	2617.7	2768.4	2900.1
32.5°	1504.0	1618.2	1742.0	1878.4	2045.0	2138.6	2240.1	2424.2	2598.7	2728.8	2830.3
35°	1442.1	1557.9	1665.8	1805.4	1976.8	2070.4	2168.7	2371.8	2544.7	2651.0	2709.7
37.5°	1373.9	1483.4	1589.7	1727.7	1899.0	1999.0	2098.9	2295.6	2459.1	2547.9	2532.0
40°	1308.9	1407.2	1505.6	1635.7	1814.9	1921.2	2008.5	2206.8	2349.6	2387.7	2335.3
42.5°	1234.3	1318.4	1413.6	1546.8	1721.3	1821.3	1930.8	2111.6	2217.9	2202.0	2113.2
45°	1150.2	1224.8	1320.0	1445.3	1623.0	1726.1	1818.1	1989.5	2067.2	2027.5	1865.7
47.5°	1069.3	1142.3	1220.0	1345.3	1518.3	1605.5	1699.1	1853.0	1897.4	1813.4	1651.5
50°	982.0	1042.3	1123.2	1242.2	1404.0	1496.1	1573.8	1697.5	1713.4	1610.3	1442.1
52.5°	898.0	948.7	1026.5	1143.9	1294.6	1367.6	1443.7	1553.2	1540.5	1434.2	1272.4
55°	809.1	856.7	928.1	1036.0	1169.2	1239.0	1304.1	1400.9	1373.9	1264.4	1123.2
57.5°	734.5	767.9	837.7	937.6	1047.1	1123.2	1178.8	1254.9	1213.7	1104.2	972.5
60°	648.9	690.1	748.8	829.7	937.6	988.4	1037.6	1088.3	1059.8	955.1	837.7
62.5°	571.1	602.9	653.6	731.4	815.5	861.5	913.8	945.5	917.0	820.2	721.9
65°	504.5	529.9	569.5	633.0	713.9	752.0	782.1	812.3	788.5	698.1	626.7
67.5°	431.5	453.7	487.1	537.8	606.0	633.0	661.6	682.2	655.2	594.9	525.1
70°	366.5	382.3	414.1	452.1	499.7	525.1	548.9	569.5	545.8	495.0	442.6
72.5°	299.8	312.5	341.1	368.1	410.9	428.4	445.8	461.7	453.7	406.1	363.3
75°	247.5	252.3	271.3	293.5	320.5	339.5	352.2	361.7	355.4	317.3	290.3
77.5°	187.2	193.6	207.8	225.3	249.1	260.2	268.1	277.6	269.7	239.6	220.5
80°	136.4	138.0	146.0	161.8	177.7	179.3	187.2	199.9	195.1	174.5	160.2
82.5°	87.3	92.0	95.2	104.7	115.8	119.0	123.7	126.9	125.3	112.6	107.9
85°	50.8	50.8	53.9	60.3	63.5	68.2	69.8	71.4	74.6	66.6	61.9
87.5°	22.2	23.8	23.8	25.4	28.6	28.6	30.1	31.7	33.3	31.7	27.0
90°	1.2	3.5	6.9	8.1	9.2	9.2	9.2	16.1	16.1	18.4	20.7
92.5°	16.1	23.0	35.7	53.0	73.7	88.6	103.6	175.0	286.6	394.9	451.3
95°	38.0	41.4	53.0	67.9	95.5	119.7	143.9	244.1	432.9	708.0	938.2
97.5°	63.3	63.3	73.7	87.5	111.7	132.4	153.1	232.5	394.9	678.1	1003.8
100°	87.5	87.5	95.5	109.4	131.2	149.6	168.1	236.0	366.1	600.9	925.6
102.5°	110.5	112.8	119.7	132.4	153.1	170.4	187.6	247.5	358.0	549.1	827.7
105°	134.7	138.1	143.9	157.7	178.4	195.1	211.8	267.1	362.6	523.8	755.2
107.5°	161.2	163.5	169.2	184.2	203.8	220.4	237.1	287.8	376.4	516.9	708.0
110°	187.6	189.9	195.7	209.5	230.2	245.8	261.3	312.0	392.6	519.2	686.1

TEST NUMBER: P1000868

CATALOG NUMBER: SA4XXDIP-B1195D1205UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	213.0	215.3	222.2	234.8	255.6	271.1	286.6	335.0	409.8	526.1	675.8
115°	237.1	240.6	248.7	260.2	282.0	297.6	313.1	359.2	428.2	535.3	673.5
117.5°	262.5	265.9	272.8	285.5	306.2	322.4	338.5	382.2	446.7	544.5	672.3
120°	287.8	290.1	298.2	310.8	330.4	346.5	362.6	406.4	466.2	554.9	672.3
122.5°	310.8	313.1	321.2	332.7	354.6	370.2	385.7	429.4	484.7	565.2	671.1
125°	330.4	335.0	341.9	354.6	376.4	392.5	408.7	450.1	503.1	575.6	670.0
127.5°	348.8	352.3	360.3	374.1	397.2	413.3	429.4	469.7	519.2	583.7	667.7
130°	363.8	368.4	377.6	394.9	416.7	433.4	450.1	489.3	534.2	592.9	666.5
132.5°	378.7	382.2	394.9	411.0	435.2	450.7	466.2	505.4	549.1	600.9	665.4
135°	392.6	397.2	408.7	428.2	452.4	467.4	482.4	520.3	561.8	609.0	664.2
137.5°	406.4	411.0	423.6	442.1	467.4	481.8	496.2	531.9	571.0	613.6	664.2
140°	421.3	424.8	437.5	457.0	481.2	495.0	508.8	543.4	580.2	619.3	663.1
142.5°	437.5	440.9	452.4	470.8	493.9	507.1	520.3	553.7	587.1	623.9	663.1
145°	452.4	455.9	467.4	483.5	505.4	518.0	530.7	560.6	591.7	625.1	660.8
147.5°	469.7	470.8	481.2	498.5	516.9	528.4	539.9	568.7	596.3	626.3	657.3
150°	485.8	487.0	496.2	510.0	527.2	538.2	549.1	574.4	599.8	626.3	653.9
152.5°	500.8	500.8	510.0	522.6	537.6	547.4	557.2	579.1	602.1	623.9	648.1
155°	514.6	515.7	522.6	534.2	546.8	555.4	564.1	583.7	603.2	621.6	642.4
157.5°	528.4	528.4	535.3	544.5	556.0	562.9	569.8	587.1	603.2	619.3	636.6
160°	541.1	541.1	545.7	553.7	562.9	569.2	575.6	589.4	603.2	615.9	629.7
162.5°	552.6	551.4	554.9	561.8	569.8	574.4	579.1	591.7	603.2	612.4	622.8
165°	560.6	560.6	562.9	568.7	574.4	577.9	581.4	591.7	600.9	607.8	615.9
167.5°	569.8	568.7	569.8	574.4	577.9	580.8	583.7	591.7	598.6	603.2	609.0
170°	575.6	574.4	575.6	579.1	581.4	583.1	584.8	590.6	596.3	598.6	602.1
172.5°	581.4	580.2	580.2	582.5	583.7	584.8	586.0	589.4	594.0	594.0	595.2
175°	584.8	583.7	583.7	584.8	586.0	586.0	586.0	588.3	591.7	590.6	590.6
177.5°	587.1	586.0	584.8	586.0	586.0	586.0	586.0	587.1	589.4	587.1	587.1
180°	586.0	586.0	586.0	586.0	586.0	586.0	586.0	586.0	586.0	586.0	586.0

TEST NUMBER: P1000868

CATALOG NUMBER: SA4XXDIP-B1195D1205UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9
2.5°	2000.6	2029.1	2041.8	2045.0	2062.4	2051.3	2056.1	2054.5	2067.2	2068.8	2068.8
5°	2146.5	2179.8	2190.9	2206.8	2230.6	2236.9	2232.2	2241.7	2259.2	2246.5	2265.5
7.5°	2300.4	2336.9	2362.3	2397.2	2405.1	2425.7	2438.4	2449.5	2452.7	2454.3	2457.5
10°	2443.2	2489.2	2524.1	2582.8	2595.5	2606.6	2662.1	2639.9	2668.5	2659.0	2662.1
12.5°	2559.0	2649.4	2678.0	2776.4	2785.9	2823.9	2820.8	2855.7	2862.0	2874.7	2862.0
15°	2711.3	2816.0	2862.0	2917.5	2949.3	2993.7	3001.6	3049.2	3068.3	3085.7	3068.3
17.5°	2850.9	2906.4	3023.8	3068.3	3088.9	3112.7	3173.0	3190.4	3219.0	3207.9	3239.6
20°	2920.7	3000.0	3123.8	3199.9	3231.7	3253.9	3304.7	3331.6	3342.7	3342.7	3345.9
22.5°	2982.6	3096.8	3188.8	3276.1	3304.7	3320.5	3350.7	3371.3	3376.0	3379.2	3382.4
25°	3038.1	3141.2	3215.8	3265.0	3276.1	3276.1	3293.5	3280.9	3260.2	3276.1	3285.6
27.5°	3038.1	3111.1	3144.4	3161.9	3161.9	3119.0	3093.6	3041.3	2996.9	2984.2	3012.7
30°	2987.4	3020.7	2974.7	2931.8	2898.5	2870.0	2770.0	2690.7	2674.8	2663.7	2706.5
32.5°	2870.0	2827.1	2736.7	2612.9	2563.8	2498.7	2421.0	2360.7	2324.2	2311.5	2302.0
35°	2662.1	2551.1	2433.7	2267.1	2232.2	2149.7	2043.4	1999.0	1938.7	1937.1	1957.7
37.5°	2435.3	2263.9	2137.0	1978.3	1929.2	1841.9	1742.0	1696.0	1654.7	1623.0	1661.1
40°	2170.3	2021.2	1827.6	1697.5	1627.7	1581.7	1497.6	1446.9	1427.8	1412.0	1435.8
42.5°	1922.8	1759.4	1608.7	1475.4	1418.3	1366.0	1310.4	1261.3	1247.0	1245.4	1262.8
45°	1676.9	1516.7	1377.1	1262.8	1226.4	1194.6	1140.7	1126.4	1102.6	1086.7	1094.7
47.5°	1480.2	1315.2	1199.4	1112.1	1080.4	1053.4	1018.5	994.7	974.1	967.8	977.3
50°	1286.6	1175.6	1056.6	983.6	959.8	934.4	907.5	885.3	875.7	869.4	875.7
52.5°	1131.2	1012.2	931.3	872.6	848.8	829.7	810.7	801.2	788.5	791.7	798.0
55°	991.6	886.8	818.6	775.8	761.5	753.6	729.8	718.7	713.9	710.7	713.9
57.5°	859.9	783.7	733.0	696.5	677.4	672.7	653.6	653.6	648.9	644.1	645.7
60°	755.2	690.1	640.9	612.4	609.2	601.3	588.6	587.0	575.9	580.7	582.2
62.5°	648.9	596.5	563.2	545.8	534.6	531.5	523.5	522.0	517.2	518.8	515.6
65°	564.8	522.0	488.6	474.4	469.6	468.0	461.7	456.9	453.7	456.9	453.7
67.5°	480.7	452.1	426.8	412.5	406.1	404.6	399.8	396.6	398.2	393.4	396.6
70°	401.4	372.8	357.0	349.0	345.9	341.1	341.1	341.1	341.1	337.9	336.3
72.5°	337.9	309.4	298.3	293.5	290.3	288.7	284.0	285.6	284.0	282.4	288.7
75°	268.1	250.7	239.6	234.8	238.0	233.2	228.5	231.6	226.9	228.5	234.8
77.5°	203.1	195.1	188.8	185.6	182.4	179.3	179.3	176.1	176.1	176.1	176.1
80°	147.5	146.0	134.9	133.3	133.3	130.1	130.1	130.1	130.1	128.5	130.1
82.5°	98.4	96.8	93.6	92.0	88.8	90.4	90.4	87.3	87.3	85.7	87.3
85°	57.1	57.1	53.9	52.4	50.8	52.4	49.2	47.6	49.2	47.6	49.2
87.5°	27.0	23.8	25.4	23.8	20.6	22.2	19.0	20.6	19.0	17.5	20.6
90°	19.6	20.7	21.9	23.0	23.0	23.0	24.2	25.3	24.2	24.2	24.2
92.5°	375.3	277.4	207.2	163.5	149.1	134.7	117.4	109.4	104.8	104.8	104.8
95°	964.7	853.0	674.6	520.3	464.5	408.7	352.3	316.6	295.9	280.9	295.9
97.5°	1209.9	1228.3	1139.7	1013.1	948.6	884.1	805.8	736.8	702.2	674.6	702.2
100°	1220.3	1388.3	1411.4	1355.0	1312.4	1269.8	1169.6	1099.4	1064.9	1055.6	1064.9
102.5°	1133.9	1380.3	1517.3	1551.8	1540.3	1528.8	1477.0	1430.9	1394.1	1387.2	1394.1
105°	1025.7	1289.3	1488.5	1602.5	1626.1	1649.7	1652.0	1642.8	1626.6	1619.7	1626.6
107.5°	937.1	1177.7	1392.9	1551.8	1600.2	1648.5	1699.2	1719.9	1729.1	1730.3	1729.1
110°	873.8	1078.7	1277.8	1444.8	1508.1	1571.4	1653.1	1701.5	1722.2	1732.6	1722.2

TEST NUMBER: P1000868

CATALOG NUMBER: SA4XXDIP-B1195D1205UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	838.1	1006.1	1176.5	1331.9	1395.2	1458.6	1554.1	1615.1	1646.2	1664.6	1646.2
115°	818.5	962.4	1104.0	1238.7	1294.0	1349.2	1440.1	1509.2	1546.1	1555.3	1546.1
117.5°	808.1	937.1	1056.8	1166.2	1214.6	1262.9	1343.4	1403.3	1442.5	1448.2	1442.5
120°	800.1	921.0	1028.0	1120.1	1161.0	1201.9	1267.5	1318.1	1348.1	1360.7	1348.1
122.5°	790.9	907.1	1009.6	1091.3	1125.8	1160.4	1213.4	1254.8	1279.0	1291.6	1279.0
125°	780.5	891.0	990.0	1069.5	1101.2	1132.8	1178.8	1212.2	1234.1	1241.0	1234.1
127.5°	766.7	872.6	968.2	1047.6	1077.6	1107.5	1153.5	1183.4	1201.9	1208.8	1201.9
130°	754.0	849.6	940.5	1018.8	1049.3	1079.8	1127.0	1155.8	1174.2	1181.1	1174.2
132.5°	742.5	825.4	909.4	985.4	1015.9	1046.4	1092.5	1125.9	1143.1	1150.0	1143.1
135°	731.0	803.5	878.4	948.6	977.4	1006.1	1052.2	1084.4	1102.8	1109.8	1102.8
137.5°	720.7	782.8	848.4	909.4	935.9	962.4	1006.1	1039.5	1054.5	1062.6	1054.5
140°	712.6	765.5	819.7	871.5	895.6	919.8	960.1	985.4	1001.5	1010.8	1001.5
142.5°	705.7	749.4	795.5	838.1	858.2	878.4	912.9	935.9	949.7	955.5	949.7
145°	697.6	734.5	773.6	808.1	824.2	840.4	869.2	888.7	900.2	906.0	900.2
147.5°	690.7	721.8	754.0	782.8	796.0	809.3	831.2	848.4	857.6	859.9	857.6
150°	682.7	710.3	736.8	759.8	770.2	780.5	798.9	813.9	820.8	822.0	820.8
152.5°	673.5	697.6	719.5	740.2	748.2	756.3	771.3	782.8	786.3	787.4	786.3
155°	664.2	685.0	703.4	720.7	727.6	734.5	746.0	755.2	758.6	758.6	758.6
157.5°	655.0	671.1	687.3	702.2	708.0	713.7	723.0	729.9	732.2	732.2	732.2
160°	644.7	658.5	671.1	683.8	688.4	693.0	699.9	706.8	708.0	708.0	708.0
162.5°	635.5	645.8	656.2	665.4	669.4	673.5	678.1	685.0	686.1	685.0	686.1
165°	625.1	634.3	641.2	649.3	652.2	655.0	659.6	664.2	663.1	661.9	663.1
167.5°	615.9	622.8	628.6	635.5	637.2	638.9	641.2	644.7	644.7	643.5	644.7
170°	606.7	612.4	615.9	620.5	622.2	623.9	626.3	627.4	626.3	626.3	626.3
172.5°	598.6	603.2	605.5	607.8	609.0	610.1	611.3	612.4	611.3	609.0	611.3
175°	592.9	595.2	596.3	598.6	598.6	598.6	598.6	600.9	598.6	596.3	598.6
177.5°	588.3	589.4	590.6	590.6	591.2	591.7	590.6	591.7	589.4	587.1	589.4
180°	586.0	586.0	586.0	586.0	586.0	586.0	586.0	586.0	586.0	586.0	586.0

TEST NUMBER: P1000868

CATALOG NUMBER: SA4XXDIP-B1195D1205UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9
2.5°	2065.6	2060.8	2054.5	2054.5	2046.6	2046.6	2033.9	2011.7	1992.6	1986.3	1989.5
5°	2241.7	2243.3	2233.8	2225.8	2211.6	2200.5	2179.8	2140.2	2127.5	2102.1	2084.6
7.5°	2443.2	2436.8	2419.4	2406.7	2403.5	2378.1	2333.7	2286.1	2248.1	2222.7	2186.2
10°	2670.1	2644.7	2619.3	2611.4	2592.3	2549.5	2498.7	2446.4	2394.0	2338.5	2276.6
12.5°	2860.4	2811.3	2809.7	2790.6	2754.1	2730.3	2670.1	2595.5	2505.1	2443.2	2373.4
15°	3065.1	3019.1	2981.0	2946.1	2928.7	2858.8	2808.1	2714.5	2606.6	2540.0	2492.4
17.5°	3211.0	3190.4	3125.4	3109.5	3085.7	3004.8	2923.9	2831.9	2738.3	2644.7	2516.2
20°	3328.4	3315.8	3272.9	3250.7	3212.6	3149.2	3050.8	2944.5	2836.6	2703.4	2582.8
22.5°	3379.2	3363.4	3328.4	3309.4	3285.6	3231.7	3147.6	3027.0	2885.8	2766.8	2638.3
25°	3279.3	3307.8	3298.3	3290.4	3280.9	3249.1	3185.7	3079.4	2941.3	2806.5	2646.3
27.5°	3054.0	3103.2	3150.8	3157.1	3173.0	3185.7	3160.3	3084.1	2968.3	2825.5	2649.4
30°	2751.0	2773.2	2870.0	2898.5	2920.7	3001.6	3049.2	3030.2	2941.3	2812.8	2651.0
32.5°	2362.3	2421.0	2519.3	2587.6	2647.8	2738.3	2862.0	2911.2	2879.5	2774.8	2614.5
35°	1994.2	2064.0	2178.2	2265.5	2325.8	2454.3	2600.3	2706.5	2746.2	2693.9	2551.1
37.5°	1692.8	1776.9	1878.4	1911.7	1981.5	2140.2	2341.7	2489.2	2586.0	2590.7	2479.7
40°	1465.9	1508.7	1589.7	1640.4	1708.6	1841.9	2038.6	2233.8	2379.7	2428.9	2370.2
42.5°	1273.9	1307.3	1367.6	1429.4	1491.3	1592.8	1773.7	1956.1	2152.9	2251.2	2249.6
45°	1121.6	1156.5	1197.8	1248.6	1291.4	1400.9	1543.7	1730.9	1900.6	2052.9	2091.0
47.5°	988.4	1018.5	1069.3	1091.5	1120.1	1223.2	1346.9	1521.4	1697.5	1872.1	1916.5
50°	890.0	915.4	950.3	964.6	996.3	1072.5	1174.0	1315.2	1510.3	1670.6	1753.1
52.5°	801.2	820.2	847.2	858.3	880.5	937.6	1029.6	1140.7	1302.5	1467.5	1583.3
55°	725.0	737.7	756.8	769.4	785.3	836.1	904.3	1004.2	1143.9	1286.6	1399.3
57.5°	653.6	663.2	682.2	688.5	701.2	740.9	788.5	872.6	1001.1	1128.0	1237.5
60°	587.0	593.3	604.5	618.7	628.2	655.2	699.6	769.4	872.6	988.4	1077.2
62.5°	523.5	533.1	536.2	542.6	550.5	575.9	610.8	661.6	752.0	847.2	940.8
65°	458.5	466.4	472.8	474.4	482.3	501.3	533.1	577.5	636.2	718.7	805.9
67.5°	398.2	403.0	406.1	412.5	420.4	429.9	455.3	488.6	542.6	609.2	679.0
70°	342.7	342.7	347.4	349.0	358.5	369.7	380.8	412.5	460.1	514.0	561.6
72.5°	282.4	290.3	288.7	296.7	295.1	303.0	317.3	337.9	372.8	415.7	461.7
75°	230.0	234.8	234.8	234.8	238.0	244.3	252.3	271.3	298.3	333.2	360.1
77.5°	179.3	182.4	182.4	182.4	184.0	190.4	198.3	211.0	230.0	250.7	266.5
80°	128.5	131.7	131.7	134.9	134.9	136.4	144.4	150.7	160.2	176.1	192.0
82.5°	87.3	88.8	92.0	92.0	90.4	93.6	95.2	101.5	111.1	114.2	125.3
85°	47.6	49.2	50.8	50.8	52.4	55.5	53.9	60.3	60.3	66.6	69.8
87.5°	19.0	22.2	22.2	20.6	22.2	22.2	22.2	25.4	27.0	28.6	27.0
90°	25.3	24.2	23.0	23.0	23.0	21.9	20.7	19.6	20.7	18.4	16.1
92.5°	109.4	117.4	134.7	149.1	163.5	207.2	277.4	375.3	451.3	394.9	286.6
95°	316.6	352.3	408.7	464.5	520.3	674.6	853.0	964.7	938.2	708.0	432.9
97.5°	736.8	805.8	884.1	948.6	1013.1	1139.7	1228.3	1209.9	1003.8	678.1	394.9
100°	1099.4	1169.6	1269.8	1312.4	1355.0	1411.4	1388.3	1220.3	925.6	600.9	366.1
102.5°	1430.9	1477.0	1528.8	1540.3	1551.8	1517.3	1380.3	1133.9	827.7	549.1	358.0
105°	1642.8	1652.0	1649.7	1626.1	1602.5	1488.5	1289.3	1025.7	755.2	523.8	362.6
107.5°	1719.9	1699.2	1648.5	1600.2	1551.8	1392.9	1177.7	937.1	708.0	516.9	376.4
110°	1701.5	1653.1	1571.4	1508.1	1444.8	1277.8	1078.7	873.8	686.1	519.2	392.6

TEST NUMBER: P1000868

CATALOG NUMBER: SA4XXDIP-B1195D1205UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1615.1	1554.1	1458.6	1395.2	1331.9	1176.5	1006.1	838.1	675.8	526.1	409.8
115°	1509.2	1440.1	1349.2	1294.0	1238.7	1104.0	962.4	818.5	673.5	535.3	428.2
117.5°	1403.3	1343.4	1262.9	1214.6	1166.2	1056.8	937.1	808.1	672.3	544.5	446.7
120°	1318.1	1267.5	1201.9	1161.0	1120.1	1028.0	921.0	800.1	672.3	554.9	466.2
122.5°	1254.8	1213.4	1160.4	1125.8	1091.3	1009.6	907.1	790.9	671.1	565.2	484.7
125°	1212.2	1178.8	1132.8	1101.2	1069.5	990.0	891.0	780.5	670.0	575.6	503.1
127.5°	1183.4	1153.5	1107.5	1077.6	1047.6	968.2	872.6	766.7	667.7	583.7	519.2
130°	1155.8	1127.0	1079.8	1049.3	1018.8	940.5	849.6	754.0	666.5	592.9	534.2
132.5°	1125.9	1092.5	1046.4	1015.9	985.4	909.4	825.4	742.5	665.4	600.9	549.1
135°	1084.4	1052.2	1006.1	977.4	948.6	878.4	803.5	731.0	664.2	609.0	561.8
137.5°	1039.5	1006.1	962.4	935.9	909.4	848.4	782.8	720.7	664.2	613.6	571.0
140°	985.4	960.1	919.8	895.6	871.5	819.7	765.5	712.6	663.1	619.3	580.2
142.5°	935.9	912.9	878.4	858.2	838.1	795.5	749.4	705.7	663.1	623.9	587.1
145°	888.7	869.2	840.4	824.2	808.1	773.6	734.5	697.6	660.8	625.1	591.7
147.5°	848.4	831.2	809.3	796.0	782.8	754.0	721.8	690.7	657.3	626.3	596.3
150°	813.9	798.9	780.5	770.2	759.8	736.8	710.3	682.7	653.9	626.3	599.8
152.5°	782.8	771.3	756.3	748.2	740.2	719.5	697.6	673.5	648.1	623.9	602.1
155°	755.2	746.0	734.5	727.6	720.7	703.4	685.0	664.2	642.4	621.6	603.2
157.5°	729.9	723.0	713.7	708.0	702.2	687.3	671.1	655.0	636.6	619.3	603.2
160°	706.8	699.9	693.0	688.4	683.8	671.1	658.5	644.7	629.7	615.9	603.2
162.5°	685.0	678.1	673.5	669.4	665.4	656.2	645.8	635.5	622.8	612.4	603.2
165°	664.2	659.6	655.0	652.2	649.3	641.2	634.3	625.1	615.9	607.8	600.9
167.5°	644.7	641.2	638.9	637.2	635.5	628.6	622.8	615.9	609.0	603.2	598.6
170°	627.4	626.3	623.9	622.2	620.5	615.9	612.4	606.7	602.1	598.6	596.3
172.5°	612.4	611.3	610.1	609.0	607.8	605.5	603.2	598.6	595.2	594.0	594.0
175°	600.9	598.6	598.6	598.6	598.6	596.3	595.2	592.9	590.6	590.6	591.7
177.5°	591.7	590.6	591.7	591.2	590.6	590.6	589.4	588.3	587.1	587.1	589.4
180°	586.0	586.0	586.0	586.0	586.0	586.0	586.0	586.0	586.0	586.0	586.0

TEST NUMBER: P1000868

CATALOG NUMBER: SA4XXDIP-B1195D1205UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9
2.5°	1975.2	1968.8	1964.1	1964.1	1949.8	1935.5	1927.6	1924.4	1921.2	1908.5	1891.1
5°	2056.1	2035.5	2021.2	2006.9	1983.1	1957.7	1932.3	1918.1	1897.4	1868.9	1848.3
7.5°	2146.5	2097.3	2081.5	2064.0	2016.4	1973.6	1938.7	1908.5	1875.2	1838.7	1802.2
10°	2222.7	2170.3	2135.4	2105.3	2043.4	1986.3	1933.9	1889.5	1846.7	1799.1	1754.7
12.5°	2295.6	2221.1	2184.6	2140.2	2075.1	1992.6	1924.4	1868.9	1805.4	1756.2	1702.3
15°	2397.2	2271.8	2211.6	2183.0	2095.7	1999.0	1916.5	1834.0	1781.6	1707.1	1659.5
17.5°	2413.0	2311.5	2271.8	2198.9	2094.2	1984.7	1889.5	1807.0	1727.7	1661.1	1599.2
20°	2468.6	2335.3	2271.8	2225.8	2087.8	1976.8	1872.1	1765.8	1689.6	1618.2	1548.4
22.5°	2503.5	2352.8	2286.1	2213.1	2081.5	1948.2	1824.5	1732.4	1638.8	1565.9	1510.3
25°	2494.0	2343.2	2268.7	2200.5	2040.2	1907.0	1795.9	1678.5	1591.2	1511.9	1438.9
27.5°	2489.2	2319.4	2240.1	2164.0	2013.3	1873.6	1734.0	1638.8	1542.1	1450.0	1396.1
30°	2476.5	2289.3	2197.3	2114.8	1957.7	1811.8	1692.8	1581.7	1485.0	1400.9	1329.5
32.5°	2433.7	2238.5	2149.7	2060.8	1897.4	1751.5	1630.9	1527.8	1431.0	1343.8	1275.5
35°	2376.6	2178.2	2081.5	1987.9	1824.5	1676.9	1565.9	1458.0	1367.6	1283.5	1218.4
37.5°	2319.4	2108.4	2018.0	1910.1	1759.4	1605.5	1491.3	1394.5	1310.4	1223.2	1151.8
40°	2236.9	2025.9	1926.0	1834.0	1657.9	1513.5	1408.8	1321.5	1239.0	1156.5	1096.3
42.5°	2124.3	1935.5	1832.4	1730.9	1565.9	1423.1	1321.5	1243.8	1166.1	1097.8	1031.2
45°	2010.1	1826.0	1734.0	1643.6	1464.3	1329.5	1235.9	1164.5	1099.4	1024.9	970.9
47.5°	1872.1	1716.6	1624.6	1535.7	1366.0	1231.1	1145.4	1078.8	1018.5	956.7	905.9
50°	1730.9	1596.0	1511.9	1419.9	1258.1	1135.9	1051.8	996.3	947.1	888.4	847.2
52.5°	1578.6	1461.2	1389.8	1300.9	1158.1	1045.5	959.8	904.3	863.0	820.2	783.7
55°	1416.7	1331.1	1254.9	1183.5	1048.7	947.1	871.0	821.8	793.2	753.6	721.9
57.5°	1270.8	1188.3	1142.3	1061.4	944.0	844.0	783.7	742.5	709.2	685.4	660.0
60°	1118.5	1051.8	1001.1	942.4	839.3	755.2	691.7	667.9	633.0	615.6	604.5
62.5°	972.5	924.9	877.3	832.9	740.9	661.6	614.0	583.8	563.2	545.8	536.2
65°	834.5	790.1	756.8	717.1	640.9	577.5	533.1	509.3	488.6	483.9	472.8
67.5°	699.6	680.6	644.1	612.4	547.3	498.2	464.8	434.7	423.6	418.8	409.3
70°	585.4	563.2	534.6	507.7	458.5	415.7	385.5	374.4	358.5	357.0	345.9
72.5°	482.3	455.3	434.7	414.1	377.6	339.5	323.6	307.8	299.8	293.5	288.7
75°	382.3	363.3	349.0	331.6	299.8	274.5	252.3	245.9	241.1	239.6	236.4
77.5°	285.6	272.9	266.5	249.1	226.9	204.7	195.1	185.6	185.6	182.4	184.0
80°	203.1	195.1	187.2	177.7	158.6	149.1	141.2	134.9	131.7	130.1	131.7
82.5°	128.5	123.7	122.2	115.8	103.1	98.4	92.0	87.3	87.3	87.3	87.3
85°	71.4	71.4	71.4	61.9	57.1	52.4	49.2	47.6	47.6	47.6	49.2
87.5°	30.1	30.1	25.4	25.4	23.8	20.6	19.0	19.0	20.6	20.6	22.2
90°	16.1	9.2	9.2	9.2	8.1	6.9	3.5	1.2	3.5	6.9	8.1
92.5°	175.0	103.6	88.6	73.7	53.0	35.7	23.0	16.1	23.0	35.7	53.0
95°	244.1	143.9	119.7	95.5	67.9	53.0	41.4	38.0	41.4	53.0	67.9
97.5°	232.5	153.1	132.4	111.7	87.5	73.7	63.3	63.3	63.3	73.7	87.5
100°	236.0	168.1	149.6	131.2	109.4	95.5	87.5	87.5	87.5	95.5	109.4
102.5°	247.5	187.6	170.4	153.1	132.4	119.7	112.8	110.5	112.8	119.7	132.4
105°	267.1	211.8	195.1	178.4	157.7	143.9	138.1	134.7	138.1	143.9	157.7
107.5°	287.8	237.1	220.4	203.8	184.2	169.2	163.5	161.2	163.5	169.2	184.2
110°	312.0	261.3	245.8	230.2	209.5	195.7	189.9	187.6	189.9	195.7	209.5

TEST NUMBER: P1000868

CATALOG NUMBER: SA4XXDIP-B1195D1205UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	335.0	286.6	271.1	255.6	234.8	222.2	215.3	213.0	215.3	222.2	234.8
115°	359.2	313.1	297.6	282.0	260.2	248.7	240.6	237.1	240.6	248.7	260.2
117.5°	382.2	338.5	322.4	306.2	285.5	272.8	265.9	262.5	265.9	272.8	285.5
120°	406.4	362.6	346.5	330.4	310.8	298.2	290.1	287.8	290.1	298.2	310.8
122.5°	429.4	385.7	370.2	354.6	332.7	321.2	313.1	310.8	313.1	321.2	332.7
125°	450.1	408.7	392.5	376.4	354.6	341.9	335.0	330.4	335.0	341.9	354.6
127.5°	469.7	429.4	413.3	397.2	374.1	360.3	352.3	348.8	352.3	360.3	374.1
130°	489.3	450.1	433.4	416.7	394.9	377.6	368.4	363.8	368.4	377.6	394.9
132.5°	505.4	466.2	450.7	435.2	411.0	394.9	382.2	378.7	382.2	394.9	411.0
135°	520.3	482.4	467.4	452.4	428.2	408.7	397.2	392.6	397.2	408.7	428.2
137.5°	531.9	496.2	481.8	467.4	442.1	423.6	411.0	406.4	411.0	423.6	442.1
140°	543.4	508.8	495.0	481.2	457.0	437.5	424.8	421.3	424.8	437.5	457.0
142.5°	553.7	520.3	507.1	493.9	470.8	452.4	440.9	437.5	440.9	452.4	470.8
145°	560.6	530.7	518.0	505.4	483.5	467.4	455.9	452.4	455.9	467.4	483.5
147.5°	568.7	539.9	528.4	516.9	498.5	481.2	470.8	469.7	470.8	481.2	498.5
150°	574.4	549.1	538.2	527.2	510.0	496.2	487.0	485.8	487.0	496.2	510.0
152.5°	579.1	557.2	547.4	537.6	522.6	510.0	500.8	500.8	500.8	510.0	522.6
155°	583.7	564.1	555.4	546.8	534.2	522.6	515.7	514.6	515.7	522.6	534.2
157.5°	587.1	569.8	562.9	556.0	544.5	535.3	528.4	528.4	528.4	535.3	544.5
160°	589.4	575.6	569.2	562.9	553.7	545.7	541.1	541.1	541.1	545.7	553.7
162.5°	591.7	579.1	574.4	569.8	561.8	554.9	551.4	552.6	551.4	554.9	561.8
165°	591.7	581.4	577.9	574.4	568.7	562.9	560.6	560.6	560.6	562.9	568.7
167.5°	591.7	583.7	580.8	577.9	574.4	569.8	568.7	569.8	568.7	569.8	574.4
170°	590.6	584.8	583.1	581.4	579.1	575.6	574.4	575.6	574.4	575.6	579.1
172.5°	589.4	586.0	584.8	583.7	582.5	580.2	580.2	581.4	580.2	580.2	582.5
175°	588.3	586.0	586.0	586.0	584.8	583.7	583.7	584.8	583.7	583.7	584.8
177.5°	587.1	586.0	586.0	586.0	586.0	584.8	586.0	587.1	586.0	584.8	586.0
180°	586.0	586.0	586.0	586.0	586.0	586.0	586.0	586.0	586.0	586.0	586.0

TEST NUMBER: P1000868

CATALOG NUMBER: SA4XXDIP-B1195D1205UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9
2.5°	1886.3	1880.0	1883.2	1867.3	1853.0	1832.4	1814.9	1811.8	1808.6	1818.1	1811.8
5°	1832.4	1824.5	1816.5	1797.5	1768.9	1751.5	1726.1	1724.5	1715.0	1700.7	1703.9
7.5°	1773.7	1768.9	1757.8	1727.7	1702.3	1672.2	1651.5	1634.1	1626.1	1613.5	1608.7
10°	1726.1	1708.6	1699.1	1665.8	1635.7	1603.9	1577.0	1564.3	1550.0	1538.9	1531.0
12.5°	1661.1	1656.3	1629.3	1602.4	1577.0	1540.5	1519.9	1483.4	1464.3	1473.8	1470.7
15°	1618.2	1596.0	1589.7	1551.6	1508.7	1485.0	1446.9	1423.1	1415.1	1400.9	1383.4
17.5°	1561.1	1546.8	1524.6	1489.7	1440.5	1407.2	1380.2	1358.0	1348.5	1329.5	1315.2
20°	1507.2	1483.4	1465.9	1434.2	1386.6	1343.8	1310.4	1296.2	1272.4	1256.5	1248.6
22.5°	1458.0	1440.5	1415.1	1367.6	1326.3	1285.1	1245.4	1224.8	1202.6	1193.0	1180.3
25°	1397.7	1369.1	1351.7	1299.3	1254.9	1221.6	1185.1	1158.1	1145.4	1129.6	1126.4
27.5°	1339.0	1312.0	1291.4	1245.4	1191.5	1148.6	1126.4	1107.4	1085.2	1085.2	1077.2
30°	1280.3	1261.3	1229.5	1185.1	1134.3	1093.1	1067.7	1050.3	1042.3	1036.0	1034.4
32.5°	1221.6	1196.2	1177.2	1116.9	1078.8	1040.7	1021.7	1007.4	997.9	996.3	997.9
35°	1161.3	1132.8	1113.7	1059.8	1021.7	986.8	978.9	966.2	961.4	959.8	967.8
37.5°	1097.8	1075.6	1051.8	1007.4	964.6	944.0	928.1	923.3	921.7	931.3	934.4
40°	1039.1	1020.1	997.9	950.3	918.6	896.4	888.4	883.7	890.0	899.5	904.3
42.5°	983.6	956.7	939.2	896.4	867.8	855.1	845.6	845.6	851.9	863.0	871.0
45°	924.9	904.3	886.8	848.8	823.4	809.1	807.5	809.1	817.0	825.0	834.5
47.5°	867.8	847.2	828.1	796.4	774.2	766.3	764.7	766.3	779.0	790.1	801.2
50°	815.5	793.2	775.8	745.6	728.2	718.7	720.3	728.2	737.7	753.6	767.9
52.5°	753.6	737.7	721.9	694.9	679.0	672.7	677.4	683.8	701.2	712.3	729.8
55°	693.3	679.0	666.3	645.7	633.0	628.2	631.4	640.9	655.2	674.3	694.9
57.5°	637.8	621.9	609.2	594.9	580.7	582.2	583.8	596.5	614.0	631.4	655.2
60°	575.9	566.4	555.3	537.8	531.5	531.5	536.2	550.5	566.4	594.9	615.6
62.5°	520.4	507.7	499.7	488.6	479.1	480.7	491.8	504.5	523.5	547.3	574.3
65°	463.3	449.0	442.6	433.1	429.9	431.5	439.5	458.5	479.1	499.7	525.1
67.5°	399.8	395.0	388.7	379.2	382.3	383.9	391.9	407.7	429.9	450.6	479.1
70°	345.9	336.3	334.7	326.8	326.8	331.6	347.4	358.5	379.2	401.4	431.5
72.5°	288.7	280.8	280.8	274.5	279.2	284.0	291.9	307.8	326.8	349.0	374.4
75°	230.0	226.9	230.0	226.9	226.9	234.8	244.3	257.0	277.6	301.4	322.1
77.5°	177.7	177.7	176.1	180.9	180.9	185.6	198.3	211.0	226.9	245.9	268.1
80°	130.1	130.1	130.1	134.9	139.6	139.6	147.5	163.4	177.7	190.4	211.0
82.5°	88.8	88.8	88.8	92.0	98.4	98.4	107.9	117.4	133.3	144.4	153.9
85°	53.9	53.9	52.4	55.5	57.1	61.9	69.8	76.2	84.1	93.6	103.1
87.5°	23.8	23.8	25.4	27.0	28.6	31.7	34.9	38.1	46.0	49.2	53.9
90°	9.2	9.2	9.2	16.1	16.1	18.4	20.7	19.6	20.7	21.9	23.0
92.5°	73.7	88.6	103.6	175.0	286.6	394.9	451.3	375.3	277.4	207.2	163.5
95°	95.5	119.7	143.9	244.1	432.9	708.0	938.2	964.7	853.0	674.6	520.3
97.5°	111.7	132.4	153.1	232.5	394.9	678.1	1003.8	1209.9	1228.3	1139.7	1013.1
100°	131.2	149.6	168.1	236.0	366.1	600.9	925.6	1220.3	1388.3	1411.4	1355.0
102.5°	153.1	170.4	187.6	247.5	358.0	549.1	827.7	1133.9	1380.3	1517.3	1551.8
105°	178.4	195.1	211.8	267.1	362.6	523.8	755.2	1025.7	1289.3	1488.5	1602.5
107.5°	203.8	220.4	237.1	287.8	376.4	516.9	708.0	937.1	1177.7	1392.9	1551.8
110°	230.2	245.8	261.3	312.0	392.6	519.2	686.1	873.8	1078.7	1277.8	1444.8

TEST NUMBER: P1000868

CATALOG NUMBER: SA4XXDIP-B1195D1205UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	255.6	271.1	286.6	335.0	409.8	526.1	675.8	838.1	1006.1	1176.5	1331.9
115°	282.0	297.6	313.1	359.2	428.2	535.3	673.5	818.5	962.4	1104.0	1238.7
117.5°	306.2	322.4	338.5	382.2	446.7	544.5	672.3	808.1	937.1	1056.8	1166.2
120°	330.4	346.5	362.6	406.4	466.2	554.9	672.3	800.1	921.0	1028.0	1120.1
122.5°	354.6	370.2	385.7	429.4	484.7	565.2	671.1	790.9	907.1	1009.6	1091.3
125°	376.4	392.5	408.7	450.1	503.1	575.6	670.0	780.5	891.0	990.0	1069.5
127.5°	397.2	413.3	429.4	469.7	519.2	583.7	667.7	766.7	872.6	968.2	1047.6
130°	416.7	433.4	450.1	489.3	534.2	592.9	666.5	754.0	849.6	940.5	1018.8
132.5°	435.2	450.7	466.2	505.4	549.1	600.9	665.4	742.5	825.4	909.4	985.4
135°	452.4	467.4	482.4	520.3	561.8	609.0	664.2	731.0	803.5	878.4	948.6
137.5°	467.4	481.8	496.2	531.9	571.0	613.6	664.2	720.7	782.8	848.4	909.4
140°	481.2	495.0	508.8	543.4	580.2	619.3	663.1	712.6	765.5	819.7	871.5
142.5°	493.9	507.1	520.3	553.7	587.1	623.9	663.1	705.7	749.4	795.5	838.1
145°	505.4	518.0	530.7	560.6	591.7	625.1	660.8	697.6	734.5	773.6	808.1
147.5°	516.9	528.4	539.9	568.7	596.3	626.3	657.3	690.7	721.8	754.0	782.8
150°	527.2	538.2	549.1	574.4	599.8	626.3	653.9	682.7	710.3	736.8	759.8
152.5°	537.6	547.4	557.2	579.1	602.1	623.9	648.1	673.5	697.6	719.5	740.2
155°	546.8	555.4	564.1	583.7	603.2	621.6	642.4	664.2	685.0	703.4	720.7
157.5°	556.0	562.9	569.8	587.1	603.2	619.3	636.6	655.0	671.1	687.3	702.2
160°	562.9	569.2	575.6	589.4	603.2	615.9	629.7	644.7	658.5	671.1	683.8
162.5°	569.8	574.4	579.1	591.7	603.2	612.4	622.8	635.5	645.8	656.2	665.4
165°	574.4	577.9	581.4	591.7	600.9	607.8	615.9	625.1	634.3	641.2	649.3
167.5°	577.9	580.8	583.7	591.7	598.6	603.2	609.0	615.9	622.8	628.6	635.5
170°	581.4	583.1	584.8	590.6	596.3	598.6	602.1	606.7	612.4	615.9	620.5
172.5°	583.7	584.8	586.0	589.4	594.0	594.0	595.2	598.6	603.2	605.5	607.8
175°	586.0	586.0	586.0	588.3	591.7	590.6	590.6	592.9	595.2	596.3	598.6
177.5°	586.0	586.0	586.0	587.1	589.4	587.1	587.1	588.3	589.4	590.6	590.6
180°	586.0	586.0	586.0	586.0	586.0	586.0	586.0	586.0	586.0	586.0	586.0

TEST NUMBER: P1000868

CATALOG NUMBER: SA4XXDIP-B1195D1205UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9
2.5°	1807.0	1805.4	1797.5	1800.7	1791.1	1794.3	1799.1	1800.7	1807.0	1802.2	1800.7
5°	1696.0	1692.8	1688.0	1683.3	1681.7	1688.0	1676.9	1680.1	1683.3	1688.0	1694.4
7.5°	1605.5	1603.9	1599.2	1591.2	1588.1	1584.9	1586.5	1597.6	1596.0	1594.4	1605.5
10°	1523.0	1524.6	1515.1	1513.5	1504.0	1502.4	1504.0	1507.2	1511.9	1518.3	1519.9
12.5°	1437.4	1458.0	1440.5	1434.2	1419.9	1427.8	1431.0	1416.7	1424.7	1429.4	1453.2
15°	1383.4	1373.9	1362.8	1362.8	1356.4	1353.3	1345.3	1356.4	1362.8	1372.3	1369.1
17.5°	1308.9	1293.0	1286.6	1280.3	1281.9	1288.2	1270.8	1296.2	1296.2	1300.9	1293.0
20°	1243.8	1231.1	1223.2	1220.0	1215.2	1212.1	1210.5	1216.8	1226.4	1229.5	1237.5
22.5°	1175.6	1175.6	1162.9	1158.1	1155.0	1150.2	1158.1	1153.4	1159.7	1166.1	1178.8
25°	1118.5	1118.5	1113.7	1107.4	1102.6	1099.4	1104.2	1102.6	1107.4	1115.3	1118.5
27.5°	1072.5	1067.7	1066.1	1064.5	1062.9	1064.5	1062.9	1067.7	1072.5	1074.1	1070.9
30°	1032.8	1028.0	1029.6	1029.6	1031.2	1029.6	1028.0	1032.8	1034.4	1031.2	1032.8
32.5°	996.3	996.3	999.5	1001.1	1001.1	1002.7	1004.2	1001.1	1002.7	997.9	999.5
35°	966.2	969.3	972.5	974.1	975.7	974.1	977.3	975.7	972.5	969.3	967.8
37.5°	936.0	939.2	945.5	947.1	951.9	953.5	950.3	950.3	948.7	942.4	939.2
40°	904.3	907.5	915.4	920.2	923.3	928.1	924.9	924.9	918.6	912.2	907.5
42.5°	874.2	880.5	888.4	893.2	899.5	899.5	899.5	896.4	888.4	882.1	877.3
45°	844.0	845.6	856.7	864.6	871.0	871.0	871.0	866.2	861.5	848.8	842.4
47.5°	810.7	815.5	828.1	836.1	842.4	844.0	844.0	839.3	829.7	818.6	810.7
50°	774.2	782.1	796.4	807.5	815.5	818.6	813.9	810.7	799.6	786.9	777.4
52.5°	739.3	748.8	766.3	775.8	786.9	788.5	786.9	782.1	769.4	752.0	744.1
55°	704.4	712.3	731.4	747.2	756.8	759.9	756.8	748.8	733.0	715.5	707.6
57.5°	666.3	677.4	698.1	713.9	725.0	726.6	723.4	715.5	702.8	680.6	669.5
60°	626.7	640.9	661.6	677.4	691.7	693.3	690.1	679.0	663.2	640.9	631.4
62.5°	587.0	598.1	621.9	639.4	650.5	658.4	652.0	640.9	625.1	602.9	588.6
65°	541.0	556.9	577.5	593.3	606.0	607.6	604.5	594.9	577.5	553.7	542.6
67.5°	496.6	507.7	528.3	548.9	553.7	558.4	553.7	544.2	529.9	509.3	493.4
70°	442.6	452.1	477.5	491.8	498.2	502.9	499.7	490.2	477.5	458.5	445.8
72.5°	388.7	396.6	420.4	431.5	444.2	442.6	441.0	434.7	417.2	404.6	396.6
75°	331.6	341.1	357.0	371.2	376.0	376.0	376.0	371.2	360.1	339.5	331.6
77.5°	279.2	284.0	296.7	304.6	309.4	311.0	309.4	301.4	295.1	280.8	276.0
80°	214.2	226.9	236.4	238.0	244.3	244.3	244.3	241.1	234.8	220.5	218.9
82.5°	161.8	165.0	174.5	179.3	182.4	180.9	180.9	174.5	172.9	165.0	161.8
85°	109.5	114.2	112.6	119.0	120.6	117.4	117.4	120.6	112.6	114.2	109.5
87.5°	60.3	60.3	63.5	61.9	68.2	68.2	65.0	66.6	63.5	61.9	60.3
90°	23.0	23.0	24.2	25.3	24.2	24.2	24.2	25.3	24.2	23.0	23.0
92.5°	149.1	134.7	117.4	109.4	104.8	104.8	104.8	109.4	117.4	134.7	149.1
95°	464.5	408.7	352.3	316.6	295.9	280.9	295.9	316.6	352.3	408.7	464.5
97.5°	948.6	884.1	805.8	736.8	702.2	674.6	702.2	736.8	805.8	884.1	948.6
100°	1312.4	1269.8	1169.6	1099.4	1064.9	1055.6	1064.9	1099.4	1169.6	1269.8	1312.4
102.5°	1540.3	1528.8	1477.0	1430.9	1394.1	1387.2	1394.1	1430.9	1477.0	1528.8	1540.3
105°	1626.1	1649.7	1652.0	1642.8	1626.6	1619.7	1626.6	1642.8	1652.0	1649.7	1626.1
107.5°	1600.2	1648.5	1699.2	1719.9	1729.1	1730.3	1729.1	1719.9	1699.2	1648.5	1600.2
110°	1508.1	1571.4	1653.1	1701.5	1722.2	1732.6	1722.2	1701.5	1653.1	1571.4	1508.1

TEST NUMBER: P1000868

CATALOG NUMBER: SA4XXDIP-B1195D1205UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1395.2	1458.6	1554.1	1615.1	1646.2	1664.6	1646.2	1615.1	1554.1	1458.6	1395.2
115°	1294.0	1349.2	1440.1	1509.2	1546.1	1555.3	1546.1	1509.2	1440.1	1349.2	1294.0
117.5°	1214.6	1262.9	1343.4	1403.3	1442.5	1448.2	1442.5	1403.3	1343.4	1262.9	1214.6
120°	1161.0	1201.9	1267.5	1318.1	1348.1	1360.7	1348.1	1318.1	1267.5	1201.9	1161.0
122.5°	1125.8	1160.4	1213.4	1254.8	1279.0	1291.6	1279.0	1254.8	1213.4	1160.4	1125.8
125°	1101.2	1132.8	1178.8	1212.2	1234.1	1241.0	1234.1	1212.2	1178.8	1132.8	1101.2
127.5°	1077.6	1107.5	1153.5	1183.4	1201.9	1208.8	1201.9	1183.4	1153.5	1107.5	1077.6
130°	1049.3	1079.8	1127.0	1155.8	1174.2	1181.1	1174.2	1155.8	1127.0	1079.8	1049.3
132.5°	1015.9	1046.4	1092.5	1125.9	1143.1	1150.0	1143.1	1125.9	1092.5	1046.4	1015.9
135°	977.4	1006.1	1052.2	1084.4	1102.8	1109.8	1102.8	1084.4	1052.2	1006.1	977.4
137.5°	935.9	962.4	1006.1	1039.5	1054.5	1062.6	1054.5	1039.5	1006.1	962.4	935.9
140°	895.6	919.8	960.1	985.4	1001.5	1010.8	1001.5	985.4	960.1	919.8	895.6
142.5°	858.2	878.4	912.9	935.9	949.7	955.5	949.7	935.9	912.9	878.4	858.2
145°	824.2	840.4	869.2	888.7	900.2	906.0	900.2	888.7	869.2	840.4	824.2
147.5°	796.0	809.3	831.2	848.4	857.6	859.9	857.6	848.4	831.2	809.3	796.0
150°	770.2	780.5	798.9	813.9	820.8	822.0	820.8	813.9	798.9	780.5	770.2
152.5°	748.2	756.3	771.3	782.8	786.3	787.4	786.3	782.8	771.3	756.3	748.2
155°	727.6	734.5	746.0	755.2	758.6	758.6	758.6	755.2	746.0	734.5	727.6
157.5°	708.0	713.7	723.0	729.9	732.2	732.2	732.2	729.9	723.0	713.7	708.0
160°	688.4	693.0	699.9	706.8	708.0	708.0	708.0	706.8	699.9	693.0	688.4
162.5°	669.4	673.5	678.1	685.0	686.1	685.0	686.1	685.0	678.1	673.5	669.4
165°	652.2	655.0	659.6	664.2	663.1	661.9	663.1	664.2	659.6	655.0	652.2
167.5°	637.2	638.9	641.2	644.7	644.7	643.5	644.7	644.7	641.2	638.9	637.2
170°	622.2	623.9	626.3	627.4	626.3	626.3	626.3	627.4	626.3	623.9	622.2
172.5°	609.0	610.1	611.3	612.4	611.3	609.0	611.3	612.4	611.3	610.1	609.0
175°	598.6	598.6	598.6	600.9	598.6	596.3	598.6	600.9	598.6	598.6	598.6
177.5°	591.2	591.7	590.6	591.7	589.4	587.1	589.4	591.7	590.6	591.7	591.2
180°	586.0	586.0	586.0	586.0	586.0	586.0	586.0	586.0	586.0	586.0	586.0

TEST NUMBER: P1000868

CATALOG NUMBER: SA4XXDIP-B1195D1205UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9
2.5°	1800.7	1810.2	1800.7	1807.0	1810.2	1818.1	1821.3	1835.6	1840.3	1851.4	1851.4
5°	1692.8	1697.5	1699.1	1705.5	1711.8	1727.7	1738.8	1759.4	1783.2	1786.4	1800.7
7.5°	1605.5	1613.5	1626.1	1621.4	1632.5	1656.3	1670.6	1696.0	1719.8	1732.4	1749.9
10°	1527.8	1537.3	1542.1	1546.8	1567.4	1588.1	1610.3	1627.7	1659.5	1678.5	1692.8
12.5°	1464.3	1456.4	1465.9	1483.4	1507.2	1519.9	1550.0	1577.0	1600.8	1621.4	1634.1
15°	1381.8	1388.2	1397.7	1427.8	1434.2	1465.9	1477.0	1507.2	1551.6	1570.6	1586.5
17.5°	1302.5	1323.1	1342.2	1353.3	1372.3	1397.7	1429.4	1462.7	1491.3	1513.5	1532.5
20°	1239.0	1259.7	1270.8	1278.7	1297.7	1332.6	1362.8	1404.0	1440.5	1458.0	1483.4
22.5°	1188.3	1188.3	1204.1	1227.9	1239.0	1272.4	1297.7	1342.2	1381.8	1404.0	1427.8
25°	1124.8	1134.3	1147.0	1167.7	1183.5	1210.5	1247.0	1285.1	1327.9	1346.9	1377.1
27.5°	1072.5	1083.6	1101.0	1105.8	1121.6	1145.4	1183.5	1224.8	1269.2	1289.8	1315.2
30°	1032.8	1039.1	1045.5	1055.0	1069.3	1089.9	1121.6	1158.1	1212.1	1227.9	1259.7
32.5°	997.9	1001.1	1004.2	1012.2	1020.1	1040.7	1066.1	1105.8	1150.2	1174.0	1202.6
35°	966.2	963.0	964.6	969.3	977.3	985.2	1012.2	1045.5	1086.7	1115.3	1137.5
37.5°	936.0	929.7	928.1	928.1	931.3	940.8	961.4	990.0	1034.4	1058.2	1080.4
40°	902.7	896.4	893.2	891.6	890.0	896.4	912.2	940.8	975.7	997.9	1023.3
42.5°	871.0	864.6	856.7	855.1	851.9	855.1	866.2	893.2	923.3	945.5	966.2
45°	839.3	828.1	818.6	812.3	813.9	809.1	817.0	837.7	872.6	886.8	907.5
47.5°	804.3	791.7	779.0	772.6	766.3	769.4	772.6	790.1	820.2	834.5	855.1
50°	771.0	753.6	739.3	731.4	726.6	723.4	726.6	744.1	766.3	779.0	796.4
52.5°	733.0	715.5	701.2	688.5	682.2	677.4	679.0	694.9	715.5	728.2	745.6
55°	698.1	675.8	656.8	640.9	636.2	634.6	633.0	644.1	661.6	674.3	688.5
57.5°	658.4	636.2	615.6	596.5	587.0	585.4	585.4	588.6	610.8	620.3	628.2
60°	618.7	594.9	572.7	555.3	541.0	536.2	534.6	541.0	552.1	561.6	572.7
62.5°	574.3	550.5	523.5	507.7	493.4	480.7	485.5	487.1	502.9	507.7	517.2
65°	531.5	504.5	482.3	456.9	441.0	433.1	429.9	433.1	445.8	447.4	453.7
67.5°	482.3	456.9	429.9	412.5	398.2	383.9	380.8	380.8	387.1	391.9	399.8
70°	434.7	409.3	379.2	360.1	345.9	333.2	328.4	326.8	331.6	334.7	342.7
72.5°	379.2	353.8	331.6	311.0	293.5	284.0	279.2	276.0	280.8	284.0	285.6
75°	320.5	299.8	277.6	257.0	245.9	236.4	230.0	225.3	228.5	228.5	228.5
77.5°	264.9	244.3	226.9	212.6	198.3	187.2	182.4	177.7	179.3	179.3	182.4
80°	206.2	192.0	177.7	165.0	152.3	142.8	139.6	134.9	131.7	130.1	130.1
82.5°	152.3	141.2	128.5	117.4	111.1	101.5	98.4	92.0	92.0	90.4	90.4
85°	101.5	95.2	82.5	74.6	69.8	65.0	61.9	58.7	53.9	53.9	52.4
87.5°	53.9	50.8	47.6	38.1	38.1	33.3	31.7	30.1	25.4	27.0	27.0
90°	23.0	21.9	20.7	19.6	20.7	18.4	16.1	16.1	9.2	9.2	9.2
92.5°	163.5	207.2	277.4	375.3	451.3	394.9	286.6	175.0	103.6	88.6	73.7
95°	520.3	674.6	853.0	964.7	938.2	708.0	432.9	244.1	143.9	119.7	95.5
97.5°	1013.1	1139.7	1228.3	1209.9	1003.8	678.1	394.9	232.5	153.1	132.4	111.7
100°	1355.0	1411.4	1388.3	1220.3	925.6	600.9	366.1	236.0	168.1	149.6	131.2
102.5°	1551.8	1517.3	1380.3	1133.9	827.7	549.1	358.0	247.5	187.6	170.4	153.1
105°	1602.5	1488.5	1289.3	1025.7	755.2	523.8	362.6	267.1	211.8	195.1	178.4
107.5°	1551.8	1392.9	1177.7	937.1	708.0	516.9	376.4	287.8	237.1	220.4	203.8
110°	1444.8	1277.8	1078.7	873.8	686.1	519.2	392.6	312.0	261.3	245.8	230.2

TEST NUMBER: P1000868

CATALOG NUMBER: SA4XXDIP-B1195D1205UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1331.9	1176.5	1006.1	838.1	675.8	526.1	409.8	335.0	286.6	271.1	255.6
115°	1238.7	1104.0	962.4	818.5	673.5	535.3	428.2	359.2	313.1	297.6	282.0
117.5°	1166.2	1056.8	937.1	808.1	672.3	544.5	446.7	382.2	338.5	322.4	306.2
120°	1120.1	1028.0	921.0	800.1	672.3	554.9	466.2	406.4	362.6	346.5	330.4
122.5°	1091.3	1009.6	907.1	790.9	671.1	565.2	484.7	429.4	385.7	370.2	354.6
125°	1069.5	990.0	891.0	780.5	670.0	575.6	503.1	450.1	408.7	392.5	376.4
127.5°	1047.6	968.2	872.6	766.7	667.7	583.7	519.2	469.7	429.4	413.3	397.2
130°	1018.8	940.5	849.6	754.0	666.5	592.9	534.2	489.3	450.1	433.4	416.7
132.5°	985.4	909.4	825.4	742.5	665.4	600.9	549.1	505.4	466.2	450.7	435.2
135°	948.6	878.4	803.5	731.0	664.2	609.0	561.8	520.3	482.4	467.4	452.4
137.5°	909.4	848.4	782.8	720.7	664.2	613.6	571.0	531.9	496.2	481.8	467.4
140°	871.5	819.7	765.5	712.6	663.1	619.3	580.2	543.4	508.8	495.0	481.2
142.5°	838.1	795.5	749.4	705.7	663.1	623.9	587.1	553.7	520.3	507.1	493.9
145°	808.1	773.6	734.5	697.6	660.8	625.1	591.7	560.6	530.7	518.0	505.4
147.5°	782.8	754.0	721.8	690.7	657.3	626.3	596.3	568.7	539.9	528.4	516.9
150°	759.8	736.8	710.3	682.7	653.9	626.3	599.8	574.4	549.1	538.2	527.2
152.5°	740.2	719.5	697.6	673.5	648.1	623.9	602.1	579.1	557.2	547.4	537.6
155°	720.7	703.4	685.0	664.2	642.4	621.6	603.2	583.7	564.1	555.4	546.8
157.5°	702.2	687.3	671.1	655.0	636.6	619.3	603.2	587.1	569.8	562.9	556.0
160°	683.8	671.1	658.5	644.7	629.7	615.9	603.2	589.4	575.6	569.2	562.9
162.5°	665.4	656.2	645.8	635.5	622.8	612.4	603.2	591.7	579.1	574.4	569.8
165°	649.3	641.2	634.3	625.1	615.9	607.8	600.9	591.7	581.4	577.9	574.4
167.5°	635.5	628.6	622.8	615.9	609.0	603.2	598.6	591.7	583.7	580.8	577.9
170°	620.5	615.9	612.4	606.7	602.1	598.6	596.3	590.6	584.8	583.1	581.4
172.5°	607.8	605.5	603.2	598.6	595.2	594.0	594.0	589.4	586.0	584.8	583.7
175°	598.6	596.3	595.2	592.9	590.6	590.6	591.7	588.3	586.0	586.0	586.0
177.5°	590.6	590.6	589.4	588.3	587.1	587.1	589.4	587.1	586.0	586.0	586.0
180°	586.0	586.0	586.0	586.0	586.0	586.0	586.0	586.0	586.0	586.0	586.0

TEST NUMBER: P1000868

CATALOG NUMBER: SA4XXDIP-B1195D1205UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1914.9	1914.9	1914.9	1914.9
2.5°	1862.5	1878.4	1892.7	1914.9
5°	1821.3	1843.5	1873.6	1907.0
7.5°	1773.7	1808.6	1848.3	1894.3
10°	1729.3	1768.9	1819.7	1875.2
12.5°	1683.3	1730.9	1786.4	1846.7
15°	1630.9	1678.5	1740.4	1821.3
17.5°	1583.3	1640.4	1707.1	1792.7
20°	1527.8	1581.7	1654.7	1753.1
22.5°	1478.6	1540.5	1621.4	1707.1
25°	1424.7	1478.6	1559.5	1662.6
27.5°	1370.7	1437.4	1515.1	1615.0
30°	1318.4	1373.9	1458.0	1562.7
32.5°	1261.3	1327.9	1405.6	1504.0
35°	1199.4	1262.8	1335.8	1442.1
37.5°	1143.9	1205.7	1280.3	1373.9
40°	1082.0	1147.0	1215.2	1308.9
42.5°	1021.7	1080.4	1148.6	1234.3
45°	963.0	1013.8	1075.6	1150.2
47.5°	902.7	945.5	1002.7	1069.3
50°	837.7	883.7	926.5	982.0
52.5°	777.4	817.0	851.9	898.0
55°	718.7	745.6	774.2	809.1
57.5°	656.8	677.4	698.1	734.5
60°	594.9	614.0	625.1	648.9
62.5°	534.6	542.6	556.9	571.1
65°	468.0	479.1	487.1	504.5
67.5°	407.7	412.5	420.4	431.5
70°	344.3	355.4	358.5	366.5
72.5°	290.3	295.1	298.3	299.8
75°	230.0	234.8	238.0	247.5
77.5°	180.9	179.3	185.6	187.2
80°	133.3	128.5	130.1	136.4
82.5°	87.3	88.8	87.3	87.3
85°	53.9	52.4	49.2	50.8
87.5°	23.8	23.8	22.2	22.2
90°	8.1	6.9	3.5	1.2
92.5°	53.0	35.7	23.0	16.1
95°	67.9	53.0	41.4	38.0
97.5°	87.5	73.7	63.3	63.3
100°	109.4	95.5	87.5	87.5
102.5°	132.4	119.7	112.8	110.5
105°	157.7	143.9	138.1	134.7
107.5°	184.2	169.2	163.5	161.2
110°	209.5	195.7	189.9	187.6

TEST NUMBER: P1000868

CATALOG NUMBER: SA4XXDIP-B1195D1205UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	234.8	222.2	215.3	213.0
115°	260.2	248.7	240.6	237.1
117.5°	285.5	272.8	265.9	262.5
120°	310.8	298.2	290.1	287.8
122.5°	332.7	321.2	313.1	310.8
125°	354.6	341.9	335.0	330.4
127.5°	374.1	360.3	352.3	348.8
130°	394.9	377.6	368.4	363.8
132.5°	411.0	394.9	382.2	378.7
135°	428.2	408.7	397.2	392.6
137.5°	442.1	423.6	411.0	406.4
140°	457.0	437.5	424.8	421.3
142.5°	470.8	452.4	440.9	437.5
145°	483.5	467.4	455.9	452.4
147.5°	498.5	481.2	470.8	469.7
150°	510.0	496.2	487.0	485.8
152.5°	522.6	510.0	500.8	500.8
155°	534.2	522.6	515.7	514.6
157.5°	544.5	535.3	528.4	528.4
160°	553.7	545.7	541.1	541.1
162.5°	561.8	554.9	551.4	552.6
165°	568.7	562.9	560.6	560.6
167.5°	574.4	569.8	568.7	569.8
170°	579.1	575.6	574.4	575.6
172.5°	582.5	580.2	580.2	581.4
175°	584.8	583.7	583.7	584.8
177.5°	586.0	584.8	586.0	587.1
180°	586.0	586.0	586.0	586.0

(END OF REPORT)