

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000897

Luminaire Tested: SA4XXDIP-B1195D1205UB30-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000897
REPORT IS A COMBINATION OF REPORTS P995510 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B1195D1205UB30-4F0-XX-W2A-F1
Description: Define 4 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9295.0 lumens
Efficiency: N/A
Efficacy: 96.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 96.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000897

CATALOG NUMBER: SA4XXDIP-B1195D1205UB30-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1000897

CATALOG NUMBER: SA4XXDIP-B1195D1205UB30-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61
1	99	95	91	87	92	88	85	81	76	73	71	64	62	61	54	53	51
2	90	83	76	71	83	77	71	67	66	62	59	56	53	51	47	45	43
3	82	73	65	59	76	68	61	56	58	53	49	50	46	43	42	39	37
4	75	64	56	50	70	60	53	47	52	46	42	44	40	37	37	34	32
5	69	57	49	43	64	54	46	41	46	41	36	40	35	32	34	30	28
6	64	51	43	37	59	48	41	35	42	36	32	36	31	28	31	27	24
7	59	46	38	33	55	44	36	31	38	32	28	33	28	25	28	24	22
8	55	42	34	29	51	40	33	28	35	29	25	30	25	22	26	22	19
9	51	39	31	26	47	36	29	25	32	26	22	28	23	20	24	20	18
10	48	35	28	23	44	33	27	22	29	24	20	26	21	18	22	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16285	16285	16285
5°	16299	15817	15836
10°	16161	15378	15270
15°	15929	14856	14632
20°	15633	14291	13971
25°	15300	13695	13259
30°	14899	13050	12478
35°	14482	12389	11722
40°	14048	11678	10919
45°	13593	10965	10169
50°	13090	10275	9337
55°	12542	9467	8511
60°	11982	8583	7650
65°	11341	7671	6681
70°	10604	6572	5643
75°	9501	5298	4518
80°	8094	3829	3178
85°	6287	2132	1710

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13593 cd/sqm

TEST NUMBER: P1000897

CATALOG NUMBER: SA4XXDIP-B1195D1205UB30-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	188.2	2.0
10°-20°	530.3	5.7
20°-30°	780.5	8.4
30°-40°	907.3	9.8
40°-50°	907.2	9.8
50°-60°	793.4	8.5
60°-70°	589.1	6.3
70°-80°	334.2	3.6
80°-90°	98.9	1.1
90°-100°	97.9	1.1
100°-110°	293.1	3.2
110°-120°	498.0	5.4
120°-130°	656.7	7.1
130°-140°	737.6	7.9
140°-150°	725.0	7.8
150°-160°	609.8	6.6
160°-170°	405.7	4.4
170°-180°	142.1	1.5
0°-30°	1499.1	16.1
0°-40°	2406.3	25.9
0°-60°	4107.0	44.2
0°-90°	5129.2	55.2
90°-120°	889.0	9.6
90°-150°	3008.3	32.4
90°-180°	4166.0	44.8
0°-180°	9295.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1997	1997	1997	1997	1997	
5°	1996	1989	1972	1989	1986	189
15°	1900	1893	1869	1879	1874	535
25°	1720	1709	1687	1688	1682	792
35°	1480	1469	1447	1435	1427	926
45°	1208	1197	1171	1154	1149	931
55°	914	909	886	867	858	818
65°	619	611	595	579	571	613
75°	330	322	314	307	306	350
85°	86	86	83	83	82	93
90°	4	16	26	32	35	11
95°	70	80	88	92	92	75
105°	271	272	276	280	283	287
115°	506	506	504	503	502	499
125°	737	737	736	734	732	657
135°	951	958	958	956	952	736
145°	1155	1160	1161	1160	1156	723
155°	1324	1324	1323	1327	1323	609
165°	1441	1438	1435	1442	1438	406
175°	1499	1493	1492	1500	1492	142
180°	1501	1501	1501	1501	1501	

TEST NUMBER: P1000897

CATALOG NUMBER: SA4XXDIP-B1195D1205UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1997.1	1997.1	1997.1	1997.1	1997.1
2.5°	2003.5	1998.7	1981.1	1997.1	1995.5
5°	1995.5	1989.1	1971.5	1989.1	1985.9
7.5°	1981.1	1974.7	1955.5	1969.9	1968.3
10°	1960.3	1953.9	1933.1	1945.9	1942.7
12.5°	1933.1	1926.7	1904.3	1918.7	1913.9
15°	1899.5	1893.1	1869.1	1878.7	1873.9
17.5°	1861.1	1853.1	1830.7	1837.1	1833.9
20°	1817.9	1809.9	1785.9	1790.7	1787.5
22.5°	1771.5	1760.3	1736.3	1745.9	1739.5
25°	1720.3	1709.1	1686.7	1688.3	1681.9
27.5°	1662.7	1651.5	1630.7	1627.5	1619.5
30°	1605.1	1592.3	1571.5	1565.1	1557.1
32.5°	1544.2	1533.0	1510.6	1502.6	1494.6
35°	1480.2	1469.0	1446.6	1435.4	1427.4
37.5°	1413.0	1403.4	1379.4	1368.2	1357.0
40°	1347.4	1334.6	1310.6	1294.6	1286.6
42.5°	1277.0	1270.6	1243.4	1224.2	1219.4
45°	1208.2	1197.0	1171.4	1153.8	1149.0
47.5°	1136.2	1128.2	1104.2	1085.0	1072.2
50°	1062.6	1056.2	1033.8	1011.4	1001.8
52.5°	990.6	982.6	958.6	939.4	926.5
55°	913.7	908.9	886.5	867.3	857.7
57.5°	841.7	836.9	814.5	795.3	785.7
60°	766.5	758.5	737.7	723.3	715.3
62.5°	692.9	686.5	664.1	651.3	643.3
65°	619.3	611.3	595.3	579.3	571.3
67.5°	544.1	537.7	521.7	505.7	504.1
70°	475.3	464.1	451.3	438.5	433.7
72.5°	401.7	390.5	380.9	371.3	366.5
75°	329.7	321.7	313.7	307.2	305.6
77.5°	259.2	256.0	248.0	246.4	241.6
80°	196.8	192.0	188.8	185.6	184.0
82.5°	136.0	134.4	134.4	132.8	131.2
85°	86.4	86.4	83.2	83.2	81.6
87.5°	41.6	40.0	38.4	38.4	38.4
90°	3.5	16.3	25.5	32.5	34.8
92.5°	30.2	45.3	51.1	54.6	55.7
95°	69.7	80.1	88.2	91.7	91.7
97.5°	111.5	120.8	130.1	134.7	134.7
100°	162.6	167.2	177.7	180.0	180.0
102.5°	216.0	217.1	226.4	229.9	231.1
105°	270.6	271.7	276.4	279.8	283.3
107.5°	327.4	328.6	329.8	334.4	333.3
110°	385.5	387.8	386.7	384.3	387.8



TEST NUMBER: P1000897

CATALOG NUMBER: SA4XXDIP-B1195D1205UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	445.9	445.9	443.6	443.6	443.6
115°	506.3	506.3	503.9	502.8	501.6
117.5°	563.2	563.2	562.0	558.5	555.0
120°	620.1	624.7	621.2	615.4	617.7
122.5°	679.3	680.4	679.3	675.8	670.0
125°	737.3	737.3	736.2	733.9	731.5
127.5°	789.6	793.1	790.8	788.4	787.3
130°	845.3	848.8	848.8	846.5	841.8
132.5°	902.2	904.5	903.4	901.1	899.9
135°	951.0	958.0	958.0	955.6	952.2
137.5°	1005.6	1009.1	1011.4	1007.9	1009.1
140°	1060.1	1062.5	1062.5	1061.3	1060.1
142.5°	1110.1	1112.4	1111.2	1111.2	1111.2
145°	1155.4	1160.0	1161.2	1160.0	1156.5
147.5°	1201.8	1207.6	1206.4	1205.3	1204.1
150°	1243.6	1248.3	1248.3	1248.3	1247.1
152.5°	1283.1	1285.4	1286.6	1290.1	1286.6
155°	1323.7	1323.7	1322.6	1327.2	1322.6
157.5°	1358.6	1356.2	1356.2	1359.7	1356.2
160°	1388.8	1387.6	1386.4	1389.9	1384.1
162.5°	1416.6	1413.1	1412.0	1418.9	1413.1
165°	1441.0	1437.5	1435.2	1442.2	1437.5
167.5°	1460.7	1456.1	1456.1	1463.1	1456.1
170°	1477.0	1471.2	1472.4	1479.3	1471.2
172.5°	1488.6	1484.0	1484.0	1492.1	1484.0
175°	1499.1	1493.3	1492.1	1500.2	1492.1
177.5°	1503.7	1497.9	1497.9	1506.0	1496.7
180°	1501.4	1501.4	1501.4	1501.4	1501.4

(END OF REPORT)