

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P997645

Luminaire Tested: SA2XXDP-B675DB35-4F0-XX-W2A-A

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P997645
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-19)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDP-B675DB35-4F0-XX-W2A-A
Description: Define 2 Direct Recessed with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2958.0 lumens
Efficiency: N/A
Efficacy: 82.4 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 35.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P997645

CATALOG NUMBER: SA2XXDP-B675DB35-4F0-XX-W2A-A

Luminous Intensity Polar Plot



TEST NUMBER: P997645

CATALOG NUMBER: SA2XXDP-B675DB35-4F0-XX-W2A-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	110	106	102	98	107	103	100	97	99	96	94	95	93	91	92	90	88	86		
2	101	94	87	82	98	92	86	81	88	83	79	85	81	78	82	79	76	74		
3	93	83	76	70	90	82	75	69	79	73	68	76	71	67	74	69	66	64		
4	86	75	66	60	83	73	66	60	71	64	59	69	63	58	66	62	58	55		
5	79	67	59	53	77	66	58	52	64	57	52	62	56	51	60	55	51	49		
6	74	61	53	47	72	60	52	46	58	51	46	57	51	46	55	50	45	43		
7	69	56	48	42	67	55	47	42	54	46	41	52	46	41	51	45	41	39		
8	64	51	43	38	63	51	43	38	49	42	37	48	42	37	47	41	37	35		
9	60	47	39	34	59	47	39	34	46	39	34	45	38	34	44	38	34	32		
10	56	44	36	31	55	43	36	31	42	36	31	41	35	31	41	35	31	29		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	21222	21222	21222	21222
5°	21319	23792	21402	18929
10°	21119	27264	21252	16382
15°	20653	30162	20940	14474
20°	20379	29701	20379	13193
25°	19780	26782	19871	12383
30°	18761	22133	19119	11791
35°	17863	16130	18161	11370
40°	16822	12884	17014	11138
45°	15525	11258	15780	10819
50°	14414	10582	14441	10609
55°	13139	9756	13225	10324
60°	11777	8940	11942	9884
65°	10577	8143	10768	9457
70°	9395	7391	9636	8821
75°	8067	6556	8385	7816
80°	6572	5634	7046	6290
85°	4867	5049	5249	3741

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 155°

Vertical Angle: 45°

Luminance: 27707 cd/sqm

TEST NUMBER: P997645

CATALOG NUMBER: SA2XXDP-B675DB35-4F0-XX-W2A-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	127.7	4.3
10°-20°	371.7	12.6
20°-30°	539.4	18.2
30°-40°	568.7	19.2
40°-50°	503.2	17.0
50°-60°	401.8	13.6
60°-70°	272.9	9.2
70°-80°	139.6	4.7
80°-90°	33.0	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1038.8	35.1
0°-40°	1607.5	54.3
0°-60°	2512.4	84.9
0°-90°	2958.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2958.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1341	1341	1341	1341	1341	
5°	1342	1497	1347	1191	1342	127
15°	1260	1840	1278	883	1260	356
25°	1132	1533	1138	709	1132	518
35°	924	835	940	588	924	578
45°	694	503	705	483	694	538
55°	476	354	479	374	476	425
65°	282	217	288	252	282	281
75°	132	107	137	128	132	142
85°	27	28	29	21	27	33
90°	0	0	0	0	0	

TEST NUMBER: P997645

CATALOG NUMBER: SA2XXDP-B675DB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1340.7	1340.7	1340.7	1340.7	1340.7	1340.7	1340.7	1340.7	1340.7	1340.7	1340.7
2.5°	1347.9	1351.0	1356.2	1357.2	1367.5	1375.7	1385.0	1385.0	1388.1	1387.1	1378.8
5°	1341.7	1351.0	1364.4	1375.7	1394.3	1402.5	1414.9	1424.2	1432.4	1438.6	1437.6
7.5°	1331.4	1347.9	1367.5	1389.1	1413.9	1428.3	1445.8	1462.3	1473.6	1483.9	1491.2
10°	1313.9	1341.7	1368.5	1397.4	1429.3	1448.9	1469.5	1491.2	1508.7	1528.3	1546.8
12.5°	1290.2	1330.4	1363.4	1401.5	1440.7	1462.3	1495.3	1511.8	1545.8	1595.2	1608.6
15°	1260.3	1314.9	1345.9	1394.3	1445.8	1463.3	1508.7	1535.5	1605.5	1636.5	1673.6
17.5°	1232.5	1293.3	1334.5	1390.2	1440.7	1474.7	1519.0	1573.6	1632.3	1676.7	1717.9
20°	1209.8	1268.6	1318.0	1379.9	1443.8	1487.0	1533.4	1599.4	1663.3	1708.6	1740.5
22.5°	1158.3	1233.5	1291.2	1360.3	1437.6	1497.3	1541.7	1613.8	1682.8	1710.7	1738.5
25°	1132.5	1197.5	1264.4	1342.8	1433.4	1504.6	1542.7	1623.1	1683.9	1694.2	1700.4
27.5°	1085.1	1158.3	1236.6	1326.3	1432.4	1492.2	1540.6	1613.8	1662.2	1655.0	1636.5
30°	1026.4	1116.1	1202.6	1299.5	1418.0	1482.9	1528.3	1595.2	1620.0	1582.9	1549.9
32.5°	983.1	1067.6	1163.5	1275.8	1401.5	1463.3	1507.6	1560.2	1565.4	1498.4	1442.7
35°	924.4	1018.2	1126.4	1244.9	1373.7	1429.3	1470.5	1502.5	1477.8	1384.0	1318.0
37.5°	871.8	964.6	1080.0	1200.6	1335.6	1390.2	1423.1	1428.3	1367.5	1285.1	1188.2
40°	814.1	909.9	1030.5	1157.3	1293.3	1340.7	1361.3	1345.9	1258.3	1162.4	1050.1
42.5°	756.4	851.2	981.1	1110.9	1239.7	1279.9	1288.1	1245.9	1138.7	1026.4	896.6
45°	693.5	792.5	922.3	1053.2	1177.9	1200.6	1201.6	1140.8	1014.0	896.6	776.0
47.5°	642.0	733.7	862.5	993.4	1098.5	1114.0	1107.8	1037.7	899.6	767.7	662.6
50°	585.3	672.9	800.7	929.5	1019.2	1023.3	1007.8	907.9	772.9	652.3	568.8
52.5°	524.5	613.2	730.6	854.3	934.7	928.5	898.6	791.4	664.7	564.7	500.8
55°	476.1	554.4	664.7	785.3	841.9	824.4	791.4	682.2	582.2	497.7	442.1
57.5°	422.5	491.6	599.8	704.9	737.9	721.4	688.4	586.4	493.6	429.7	392.6
60°	372.0	434.9	529.7	617.3	643.0	625.5	587.4	495.7	428.7	375.1	347.3
62.5°	325.6	380.3	459.6	540.0	550.3	532.8	499.8	425.6	367.9	325.6	305.0
65°	282.4	333.9	397.8	458.6	467.9	449.3	415.3	361.7	313.3	286.5	266.9
67.5°	240.1	281.3	338.0	382.3	387.5	370.0	342.1	298.9	269.0	240.1	225.7
70°	203.0	233.9	278.2	314.3	316.4	299.9	285.5	246.3	223.6	203.0	191.7
72.5°	166.9	188.6	222.6	249.4	250.4	240.1	226.7	202.0	182.4	168.0	156.6
75°	131.9	150.5	171.1	194.8	193.7	185.5	175.2	159.7	143.2	134.0	128.8
77.5°	101.0	112.3	128.8	144.3	144.3	140.2	134.0	122.6	112.3	103.1	97.9
80°	72.1	79.3	92.7	97.9	100.0	98.9	93.8	85.5	81.4	74.2	72.1
82.5°	46.4	51.5	57.7	62.9	66.0	63.9	62.9	58.7	52.6	50.5	48.4
85°	26.8	28.9	31.9	35.0	36.1	35.0	37.1	34.0	30.9	30.9	29.9
87.5°	11.3	12.4	14.4	14.4	15.5	15.5	14.4	15.5	15.5	14.4	13.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P997645

CATALOG NUMBER: SA2XXDP-B675DB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1340.7	1340.7	1340.7	1340.7	1340.7	1340.7	1340.7	1340.7	1340.7	1340.7	1340.7
2.5°	1393.3	1394.3	1396.4	1406.7	1411.8	1412.8	1408.7	1418.0	1421.1	1418.0	1415.9
5°	1459.2	1465.4	1477.8	1491.2	1490.1	1491.2	1497.3	1503.5	1505.6	1497.3	1500.4
7.5°	1516.9	1529.3	1542.7	1563.3	1563.3	1573.6	1577.7	1582.9	1595.2	1589.1	1587.0
10°	1582.9	1599.4	1624.1	1657.1	1658.1	1668.4	1678.7	1695.2	1700.4	1696.2	1698.3
12.5°	1665.3	1697.3	1699.3	1735.4	1751.9	1753.9	1770.4	1767.3	1777.6	1777.6	1795.2
15°	1701.4	1750.8	1778.7	1813.7	1824.0	1811.6	1825.0	1839.5	1840.5	1840.5	1839.5
17.5°	1766.3	1785.9	1813.7	1832.3	1836.4	1836.4	1837.4	1843.6	1839.5	1831.2	1837.4
20°	1779.7	1787.9	1798.3	1796.2	1798.3	1787.9	1777.6	1767.3	1768.4	1763.2	1778.7
22.5°	1755.0	1752.9	1729.2	1713.8	1713.8	1693.1	1673.6	1664.3	1655.0	1658.1	1663.3
25°	1693.1	1661.2	1632.3	1609.7	1604.5	1571.5	1544.7	1536.5	1521.0	1533.4	1535.5
27.5°	1594.2	1558.1	1511.8	1492.2	1465.4	1452.0	1433.4	1408.7	1376.8	1395.3	1392.2
30°	1488.1	1434.5	1396.4	1348.9	1306.7	1303.6	1268.6	1227.3	1210.9	1210.9	1220.1
32.5°	1369.6	1298.5	1242.8	1175.8	1134.6	1117.1	1074.8	1033.6	1042.9	1012.0	1023.3
35°	1231.5	1137.7	1067.6	1002.7	971.8	951.2	896.6	873.9	849.1	834.7	861.5
37.5°	1099.6	991.4	901.7	830.6	819.3	782.2	745.1	730.6	716.2	722.4	721.4
40°	938.8	843.0	762.6	706.9	687.4	669.8	645.1	627.6	618.3	623.5	624.5
42.5°	793.5	713.1	653.3	614.2	597.7	585.3	573.0	558.5	555.4	555.4	559.6
45°	681.2	615.2	575.0	543.1	533.8	524.5	515.3	509.1	507.0	502.9	506.0
47.5°	591.5	539.0	514.2	490.5	480.2	478.2	469.9	466.8	462.7	461.7	462.7
50°	516.3	483.3	460.6	447.2	440.0	436.9	432.8	426.6	424.6	429.7	427.7
52.5°	463.7	432.8	420.5	407.1	402.9	398.8	392.6	393.7	392.6	390.6	390.6
55°	411.2	391.6	379.2	368.9	367.9	363.8	358.6	356.6	355.5	353.5	356.6
57.5°	368.9	353.5	342.1	332.9	328.7	328.7	323.6	319.5	319.5	318.4	319.5
60°	326.7	311.2	304.0	294.7	291.6	290.6	287.5	285.5	282.4	282.4	282.4
62.5°	287.5	275.1	266.9	258.7	259.7	254.5	250.4	248.4	248.4	249.4	249.4
65°	250.4	242.2	231.9	224.7	222.6	221.6	219.5	218.5	215.4	217.4	217.4
67.5°	216.4	205.1	198.9	195.8	192.7	191.7	189.6	187.6	186.5	185.5	187.6
70°	182.4	173.1	168.0	165.9	162.8	161.8	160.8	157.7	158.7	159.7	160.8
72.5°	151.5	143.2	142.2	136.0	136.0	136.0	131.9	134.0	132.9	130.9	132.9
75°	119.5	115.4	113.4	110.3	111.3	110.3	109.2	106.1	106.1	107.2	108.2
77.5°	94.8	90.7	89.7	86.6	84.5	86.6	84.5	83.5	83.5	84.5	84.5
80°	70.1	68.0	64.9	64.9	64.9	63.9	63.9	63.9	62.9	61.8	62.9
82.5°	46.4	46.4	45.3	44.3	45.3	43.3	44.3	44.3	44.3	44.3	44.3
85°	29.9	28.9	28.9	27.8	27.8	27.8	28.9	26.8	26.8	27.8	27.8
87.5°	13.4	13.4	13.4	14.4	13.4	13.4	13.4	14.4	13.4	13.4	13.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P997645

CATALOG NUMBER: SA2XXDP-B675DB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1340.7	1340.7	1340.7	1340.7	1340.7	1340.7	1340.7	1340.7	1340.7	1340.7	1340.7
2.5°	1421.1	1413.9	1407.7	1408.7	1413.9	1409.7	1399.4	1386.0	1380.9	1374.7	1380.9
5°	1506.6	1500.4	1488.1	1489.1	1486.0	1481.9	1465.4	1444.8	1444.8	1428.3	1426.2
7.5°	1591.1	1581.8	1573.6	1571.5	1560.2	1552.0	1537.5	1508.7	1497.3	1477.8	1466.4
10°	1685.9	1678.7	1669.4	1658.1	1651.9	1637.5	1613.8	1571.5	1550.9	1524.1	1504.6
12.5°	1781.8	1780.7	1760.1	1737.5	1736.4	1713.8	1697.3	1640.6	1612.8	1576.7	1530.3
15°	1842.6	1837.4	1826.1	1814.7	1817.8	1793.1	1756.0	1689.0	1670.5	1627.2	1577.7
17.5°	1841.5	1841.5	1838.4	1836.4	1833.3	1826.1	1805.5	1761.2	1731.3	1676.7	1630.3
20°	1782.8	1796.2	1799.3	1798.3	1808.6	1813.7	1812.7	1784.9	1761.2	1712.7	1665.3
22.5°	1665.3	1696.2	1709.6	1717.9	1739.5	1750.8	1777.6	1767.3	1761.2	1725.1	1684.9
25°	1556.1	1566.4	1606.6	1608.6	1638.5	1666.3	1693.1	1710.7	1733.3	1719.9	1685.9
27.5°	1414.9	1438.6	1467.5	1489.1	1495.3	1552.0	1596.3	1629.2	1680.8	1684.9	1673.6
30°	1255.2	1266.5	1313.9	1342.8	1375.7	1417.0	1480.9	1537.5	1583.9	1626.2	1640.6
32.5°	1060.4	1106.8	1134.6	1169.6	1198.5	1271.7	1350.0	1423.1	1476.7	1547.8	1578.8
35°	882.1	918.2	965.6	980.0	1032.6	1094.4	1196.4	1290.2	1371.6	1443.8	1506.6
37.5°	734.8	763.6	814.1	836.8	867.7	947.0	1032.6	1149.0	1246.9	1335.6	1413.9
40°	633.8	655.4	693.5	700.8	726.5	798.7	867.7	976.9	1106.8	1226.3	1311.8
42.5°	564.7	575.0	600.8	610.1	626.6	675.0	736.8	839.9	960.4	1084.1	1204.7
45°	515.3	522.5	537.9	546.2	566.8	588.4	638.9	721.4	816.2	940.9	1070.7
47.5°	470.9	480.2	486.4	491.6	502.9	526.6	559.6	620.4	711.1	825.4	951.2
50°	433.8	436.9	448.3	449.3	456.5	472.0	502.9	540.0	612.1	704.9	826.5
52.5°	396.7	399.8	407.1	414.3	417.4	429.7	450.3	481.3	534.8	608.0	716.2
55°	359.7	363.8	371.0	376.1	379.2	389.5	401.9	431.8	474.0	525.6	614.2
57.5°	322.6	331.8	333.9	337.0	342.1	353.5	364.8	382.3	415.3	462.7	527.6
60°	287.5	290.6	297.8	300.9	306.1	312.2	326.7	340.1	363.8	400.9	459.6
62.5°	251.4	258.7	261.8	264.8	269.0	276.2	285.5	299.9	320.5	350.4	396.7
65°	220.5	221.6	227.7	231.9	236.0	241.1	250.4	263.8	276.2	304.0	338.0
67.5°	190.6	192.7	194.8	198.9	204.0	209.2	217.4	224.7	240.1	258.7	285.5
70°	161.8	161.8	166.9	170.0	169.0	175.2	181.4	189.6	201.0	218.5	240.1
72.5°	136.0	135.0	139.1	140.2	142.2	146.3	150.5	158.7	164.9	178.3	194.8
75°	108.2	110.3	112.3	112.3	115.4	118.5	122.6	126.8	134.0	142.2	154.6
77.5°	85.5	85.5	87.6	88.6	91.7	90.7	94.8	98.9	104.1	111.3	120.6
80°	62.9	64.9	64.9	64.9	66.0	67.0	71.1	74.2	77.3	82.4	86.6
82.5°	44.3	44.3	46.4	46.4	46.4	48.4	48.4	49.5	51.5	54.6	57.7
85°	27.8	27.8	27.8	28.9	27.8	28.9	30.9	29.9	30.9	33.0	33.0
87.5°	13.4	13.4	13.4	13.4	13.4	14.4	13.4	14.4	15.5	15.5	15.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P997645

CATALOG NUMBER: SA2XXDP-B675DB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1340.7	1340.7	1340.7	1340.7	1340.7	1340.7	1340.7	1340.7	1340.7	1340.7	1340.7
2.5°	1375.7	1370.6	1367.5	1369.6	1363.4	1347.9	1347.9	1353.1	1346.9	1340.7	1331.4
5°	1413.9	1403.6	1397.4	1396.4	1381.9	1357.2	1352.0	1346.9	1333.5	1319.1	1303.6
7.5°	1451.0	1432.4	1422.1	1414.9	1394.3	1362.3	1348.9	1337.6	1316.0	1294.3	1274.8
10°	1481.9	1455.1	1442.7	1431.4	1404.6	1364.4	1342.8	1322.2	1294.3	1266.5	1241.8
12.5°	1506.6	1475.7	1460.2	1443.8	1410.8	1358.2	1331.4	1298.5	1270.6	1233.5	1208.8
15°	1547.8	1483.9	1469.5	1454.1	1420.1	1347.9	1314.9	1277.8	1239.7	1190.2	1163.5
17.5°	1580.8	1495.3	1494.3	1461.3	1417.0	1343.8	1293.3	1244.9	1203.6	1154.2	1111.9
20°	1600.4	1512.8	1496.3	1462.3	1406.7	1316.0	1263.4	1209.8	1165.5	1105.7	1063.5
22.5°	1616.9	1537.5	1494.3	1453.0	1385.0	1306.7	1229.4	1178.9	1118.1	1053.2	1013.0
25°	1623.1	1542.7	1497.3	1449.9	1369.6	1279.9	1192.3	1137.7	1069.7	1010.9	956.3
27.5°	1624.1	1541.7	1486.0	1436.5	1347.9	1244.9	1155.2	1097.5	1022.3	954.3	899.6
30°	1613.8	1530.3	1479.8	1426.2	1327.3	1212.9	1109.9	1046.0	965.6	897.6	840.9
32.5°	1582.9	1507.6	1466.4	1407.7	1300.5	1168.6	1066.6	995.5	911.0	844.0	789.4
35°	1531.3	1479.8	1434.5	1379.9	1265.5	1127.4	1023.3	939.8	854.3	790.4	738.9
37.5°	1467.5	1439.6	1397.4	1343.8	1225.3	1090.3	974.9	882.1	796.6	734.8	684.3
40°	1380.9	1388.1	1346.9	1298.5	1177.9	1039.8	912.0	823.4	743.0	685.3	635.8
42.5°	1287.1	1317.0	1293.3	1246.9	1125.3	984.1	865.6	767.7	689.4	629.6	588.4
45°	1186.1	1237.7	1223.2	1189.2	1070.7	925.4	799.7	704.9	635.8	578.1	542.1
47.5°	1075.9	1149.0	1149.0	1124.3	1009.9	866.7	743.0	646.1	578.1	536.9	501.9
50°	963.5	1046.0	1059.4	1042.9	941.9	799.7	674.0	586.4	527.6	487.4	461.7
52.5°	846.1	941.9	966.6	958.4	869.8	735.8	617.3	531.7	478.2	443.1	420.5
55°	733.7	845.0	871.8	874.9	792.5	665.7	554.4	479.2	427.7	404.0	384.4
57.5°	627.6	734.8	764.6	769.8	714.1	601.8	495.7	429.7	383.4	363.8	348.3
60°	536.9	626.6	665.7	677.1	628.6	527.6	441.1	377.2	342.1	323.6	309.2
62.5°	462.7	534.8	576.1	579.2	557.5	462.7	384.4	330.8	300.9	284.4	277.2
65°	390.6	455.5	480.2	492.6	475.1	400.9	331.8	287.5	263.8	249.4	242.2
67.5°	332.9	374.1	394.7	411.2	393.7	338.0	282.4	246.3	228.8	214.3	210.2
70°	273.1	307.1	322.6	339.0	323.6	281.3	241.1	208.2	192.7	181.4	176.2
72.5°	218.5	245.3	259.7	270.0	260.7	225.7	192.7	170.0	158.7	150.5	147.4
75°	173.1	191.7	199.9	207.1	203.0	176.2	155.6	137.1	126.8	119.5	117.5
77.5°	131.9	145.3	154.6	156.6	151.5	134.0	116.4	105.1	96.9	92.7	90.7
80°	93.8	102.0	107.2	110.3	105.1	97.9	85.5	77.3	70.1	64.9	63.9
82.5°	62.9	67.0	71.1	70.1	68.0	61.8	54.6	50.5	47.4	43.3	43.3
85°	36.1	37.1	39.2	40.2	39.2	35.0	30.9	28.9	26.8	23.7	23.7
87.5°	15.5	16.5	16.5	17.5	15.5	15.5	13.4	11.3	11.3	10.3	9.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P997645

CATALOG NUMBER: SA2XXDP-B675DB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1340.7	1340.7	1340.7	1340.7	1340.7	1340.7	1340.7	1340.7	1340.7	1340.7	1340.7
2.5°	1326.3	1331.4	1330.4	1320.1	1308.8	1299.5	1282.0	1284.0	1277.8	1278.9	1285.1
5°	1293.3	1293.3	1289.2	1274.8	1256.2	1245.9	1226.3	1221.2	1208.8	1207.8	1206.7
7.5°	1258.3	1253.1	1248.0	1227.3	1204.7	1188.2	1161.4	1155.2	1142.8	1134.6	1130.5
10°	1217.0	1209.8	1199.5	1175.8	1148.0	1127.4	1099.6	1091.3	1067.6	1057.3	1051.1
12.5°	1171.7	1167.6	1151.1	1131.5	1086.2	1063.5	1023.3	1031.5	1007.8	987.2	984.1
15°	1126.4	1110.9	1101.6	1069.7	1015.1	1004.8	972.8	956.3	934.7	918.2	918.2
17.5°	1082.0	1058.3	1037.7	1003.7	963.5	934.7	911.0	902.7	875.9	859.5	856.4
20°	1023.3	996.5	991.4	942.9	915.1	883.2	860.5	839.9	820.3	813.1	807.9
22.5°	967.7	936.7	928.5	887.3	859.5	827.5	804.8	790.4	776.0	770.8	761.6
25°	907.9	889.3	877.0	832.7	801.7	771.9	756.4	746.1	732.7	731.7	725.5
27.5°	850.2	832.7	820.3	778.0	755.4	727.5	715.2	703.8	696.6	693.5	690.4
30°	800.7	781.1	766.7	735.8	708.0	685.3	675.0	667.8	663.7	658.5	657.5
32.5°	746.1	734.8	715.2	691.5	669.8	648.2	642.0	636.9	630.7	628.6	627.6
35°	699.7	684.3	671.9	645.1	635.8	617.3	610.1	605.9	597.7	595.6	593.6
37.5°	654.4	640.0	626.6	610.1	592.5	582.2	578.1	571.9	567.8	568.8	566.8
40°	609.0	597.7	587.4	569.9	559.6	554.4	546.2	540.0	537.9	539.0	537.9
42.5°	564.7	554.4	548.2	534.8	524.5	519.4	514.2	508.0	511.1	511.1	514.2
45°	524.5	515.3	511.1	500.8	494.6	486.4	481.3	480.2	484.3	483.3	483.3
47.5°	483.3	480.2	475.1	465.8	457.5	452.4	451.4	451.4	455.5	457.5	456.5
50°	451.4	445.2	439.0	431.8	425.6	423.5	420.5	422.5	426.6	426.6	428.7
52.5°	411.2	407.1	405.0	398.8	394.7	394.7	394.7	395.7	398.8	401.9	400.9
55°	376.1	373.0	371.0	367.9	362.7	363.8	362.7	364.8	367.9	371.0	373.0
57.5°	339.0	338.0	335.9	330.8	330.8	329.8	332.9	333.9	339.0	341.1	344.2
60°	306.1	303.0	303.0	298.9	298.9	298.9	301.9	305.0	309.2	310.2	312.2
62.5°	271.0	271.0	270.0	266.9	266.9	270.0	271.0	275.1	277.2	277.2	280.3
65°	238.0	237.0	236.0	237.0	238.0	238.0	241.1	243.2	245.3	246.3	247.3
67.5°	205.1	204.0	206.1	205.1	207.1	211.3	210.2	213.3	216.4	216.4	217.4
70°	174.2	176.2	175.2	177.2	176.2	178.3	181.4	182.4	182.4	183.4	186.5
72.5°	145.3	145.3	145.3	144.3	145.3	147.4	149.4	150.5	152.5	153.5	156.6
75°	117.5	117.5	115.4	117.5	117.5	119.5	121.6	121.6	121.6	123.7	126.8
77.5°	88.6	89.7	88.6	90.7	90.7	91.7	93.8	92.7	94.8	95.8	96.9
80°	64.9	63.9	63.9	63.9	64.9	64.9	67.0	68.0	68.0	71.1	69.0
82.5°	41.2	42.3	41.2	42.3	42.3	43.3	42.3	43.3	44.3	46.4	45.3
85°	23.7	22.7	22.7	23.7	22.7	22.7	23.7	22.7	23.7	22.7	23.7
87.5°	9.3	8.2	8.2	8.2	8.2	7.2	7.2	6.2	6.2	6.2	5.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P997645

CATALOG NUMBER: SA2XXDP-B675DB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1340.7	1340.7	1340.7	1340.7	1340.7	1340.7	1340.7	1340.7	1340.7	1340.7	1340.7
2.5°	1277.8	1280.9	1273.7	1271.7	1273.7	1266.5	1268.6	1270.6	1270.6	1273.7	1275.8
5°	1203.6	1199.5	1192.3	1190.2	1188.2	1191.3	1189.2	1192.3	1193.3	1200.6	1201.6
7.5°	1130.5	1124.3	1118.1	1111.9	1109.9	1104.7	1109.9	1109.9	1117.1	1115.0	1120.2
10°	1043.9	1042.9	1034.6	1031.5	1027.4	1019.2	1030.5	1027.4	1032.6	1041.9	1043.9
12.5°	980.0	968.7	973.8	959.4	964.6	956.3	957.4	957.4	965.6	966.6	964.6
15°	919.2	909.9	896.6	890.4	887.3	883.2	896.6	897.6	891.4	905.8	900.7
17.5°	857.4	857.4	845.0	841.9	833.7	837.8	835.7	836.8	834.7	845.0	850.2
20°	803.8	798.7	794.5	795.6	785.3	783.2	781.1	783.2	790.4	797.6	799.7
22.5°	760.5	757.4	747.1	749.2	740.9	744.0	742.0	747.1	748.2	748.2	755.4
25°	719.3	715.2	716.2	712.1	709.0	709.0	705.9	709.0	713.1	715.2	716.2
27.5°	688.4	685.3	680.1	677.1	679.1	674.0	678.1	681.2	681.2	679.1	681.2
30°	651.3	653.3	653.3	643.0	647.2	645.1	648.2	650.3	650.3	651.3	649.2
32.5°	626.6	620.4	619.3	618.3	618.3	614.2	614.2	617.3	618.3	619.3	622.4
35°	593.6	593.6	588.4	591.5	587.4	588.4	587.4	588.4	590.5	587.4	590.5
37.5°	563.7	564.7	562.7	564.7	565.8	563.7	561.6	565.8	563.7	563.7	561.6
40°	537.9	536.9	537.9	537.9	537.9	539.0	536.9	536.9	536.9	534.8	532.8
42.5°	516.3	510.1	512.2	513.2	510.1	510.1	511.1	510.1	513.2	507.0	507.0
45°	485.4	483.3	484.3	484.3	486.4	483.3	485.4	486.4	483.3	482.3	480.2
47.5°	457.5	459.6	457.5	459.6	459.6	461.7	457.5	458.6	459.6	455.5	452.4
50°	429.7	429.7	432.8	431.8	432.8	430.8	430.8	429.7	430.8	428.7	425.6
52.5°	404.0	400.9	406.0	405.0	404.0	402.9	401.9	402.9	400.9	398.8	398.8
55°	372.0	372.0	375.1	376.1	376.1	374.1	372.0	373.0	372.0	371.0	370.0
57.5°	346.3	342.1	344.2	345.2	345.2	342.1	344.2	342.1	342.1	343.2	340.1
60°	313.3	313.3	311.2	314.3	314.3	312.2	312.2	313.3	311.2	310.2	309.2
62.5°	278.2	279.3	282.4	283.4	284.4	282.4	280.3	281.3	281.3	278.2	279.3
65°	248.4	250.4	254.5	253.5	251.4	252.5	250.4	251.4	248.4	249.4	246.3
67.5°	219.5	218.5	219.5	219.5	221.6	220.5	218.5	218.5	217.4	220.5	217.4
70°	188.6	188.6	188.6	188.6	189.6	190.6	188.6	186.5	187.6	185.5	184.5
72.5°	156.6	157.7	156.6	158.7	155.6	157.7	157.7	156.6	155.6	155.6	155.6
75°	126.8	128.8	125.7	126.8	125.7	127.8	126.8	126.8	124.7	123.7	124.7
77.5°	96.9	97.9	95.8	96.9	95.8	96.9	96.9	95.8	95.8	95.8	95.8
80°	69.0	70.1	69.0	68.0	67.0	69.0	67.0	68.0	69.0	68.0	70.1
82.5°	44.3	44.3	43.3	44.3	42.3	42.3	43.3	43.3	42.3	44.3	42.3
85°	21.6	21.6	23.7	21.6	20.6	20.6	20.6	21.6	20.6	22.7	21.6
87.5°	5.2	4.1	5.2	5.2	4.1	4.1	5.2	4.1	5.2	6.2	4.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P997645

CATALOG NUMBER: SA2XXDP-B675DB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1340.7	1340.7	1340.7	1340.7	1340.7	1340.7	1340.7	1340.7	1340.7	1340.7	1340.7
2.5°	1272.7	1280.9	1277.8	1266.5	1279.9	1279.9	1289.2	1289.2	1300.5	1304.6	1310.8
5°	1200.6	1206.7	1211.9	1206.7	1216.0	1230.4	1238.7	1245.9	1261.4	1267.5	1276.8
7.5°	1123.3	1134.6	1139.8	1139.8	1155.2	1171.7	1188.2	1198.5	1220.1	1228.4	1237.7
10°	1048.0	1061.4	1071.7	1070.7	1096.5	1106.8	1127.4	1151.1	1172.7	1185.1	1198.5
12.5°	968.7	975.9	990.3	1010.9	1017.1	1035.7	1059.4	1089.3	1128.4	1139.8	1159.3
15°	902.7	922.3	933.6	942.9	957.4	974.9	1000.6	1029.5	1068.6	1093.4	1114.0
17.5°	847.1	872.8	880.1	878.0	896.6	923.3	953.2	974.9	1009.9	1039.8	1059.4
20°	801.7	812.0	824.4	829.6	844.0	872.8	901.7	926.4	955.3	979.0	1001.7
22.5°	756.4	764.6	774.9	784.2	795.6	812.0	839.9	870.8	898.6	921.3	947.0
25°	719.3	724.5	733.7	740.9	753.3	764.6	784.2	818.2	851.2	864.6	887.3
27.5°	683.2	687.4	693.5	701.8	708.0	719.3	736.8	764.6	798.7	812.0	843.0
30°	651.3	654.4	660.6	664.7	667.8	681.2	694.6	716.2	742.0	760.5	783.2
32.5°	621.4	624.5	630.7	631.7	635.8	643.0	655.4	675.0	697.7	713.1	732.7
35°	588.4	590.5	596.7	598.7	601.8	608.0	617.3	631.7	652.3	663.7	681.2
37.5°	562.7	561.6	565.8	568.8	573.0	576.1	579.2	593.6	609.0	619.3	632.7
40°	534.8	532.8	533.8	537.9	540.0	544.1	544.1	558.5	568.8	577.1	587.4
42.5°	507.0	506.0	503.9	506.0	508.0	509.1	510.1	520.4	530.7	537.9	549.3
45°	479.2	478.2	476.1	477.1	477.1	479.2	482.3	486.4	493.6	499.8	506.0
47.5°	453.4	451.4	448.3	447.2	449.3	449.3	449.3	453.4	460.6	462.7	468.9
50°	426.6	423.5	419.4	417.4	417.4	416.3	418.4	419.4	425.6	427.7	432.8
52.5°	397.8	395.7	391.6	387.5	388.5	386.4	387.5	388.5	390.6	393.7	396.7
55°	368.9	364.8	361.7	360.7	357.6	357.6	354.5	358.6	357.6	358.6	362.7
57.5°	341.1	337.0	331.8	329.8	326.7	325.6	323.6	322.6	323.6	326.7	329.8
60°	308.1	306.1	303.0	299.9	297.8	294.7	292.7	292.7	291.6	291.6	292.7
62.5°	276.2	275.1	271.0	270.0	267.9	265.9	262.8	260.7	260.7	262.8	263.8
65°	245.3	244.2	241.1	240.1	235.0	232.9	231.9	230.8	228.8	228.8	228.8
67.5°	216.4	213.3	213.3	208.2	204.0	202.0	199.9	198.9	198.9	198.9	199.9
70°	184.5	184.5	181.4	178.3	174.2	175.2	172.1	169.0	169.0	166.9	168.0
72.5°	153.5	152.5	149.4	148.4	145.3	142.2	140.2	142.2	139.1	138.1	139.1
75°	123.7	122.6	120.6	118.5	119.5	116.4	113.4	112.3	112.3	110.3	110.3
77.5°	94.8	96.9	92.7	91.7	89.7	87.6	86.6	85.5	85.5	85.5	87.6
80°	66.0	67.0	67.0	64.9	66.0	62.9	62.9	62.9	59.8	60.8	61.8
82.5°	42.3	42.3	41.2	42.3	41.2	41.2	40.2	40.2	39.2	39.2	40.2
85°	23.7	22.7	21.6	23.7	22.7	22.7	21.6	21.6	21.6	21.6	21.6
87.5°	5.2	6.2	6.2	6.2	6.2	7.2	7.2	7.2	8.2	8.2	8.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P997645

CATALOG NUMBER: SA2XXDP-B675DB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1340.7	1340.7	1340.7	1340.7
2.5°	1316.0	1316.0	1331.4	1347.9
5°	1287.1	1294.3	1319.1	1341.7
7.5°	1259.3	1271.7	1302.6	1331.4
10°	1225.3	1241.8	1279.9	1313.9
12.5°	1192.3	1207.8	1252.1	1290.2
15°	1145.9	1165.5	1212.9	1260.3
17.5°	1099.6	1119.1	1176.9	1232.5
20°	1044.9	1070.7	1135.6	1209.8
22.5°	994.4	1026.4	1098.5	1158.3
25°	938.8	988.3	1055.3	1132.5
27.5°	889.3	938.8	1006.8	1085.1
30°	833.7	884.2	954.3	1026.4
32.5°	780.1	826.5	894.5	983.1
35°	724.5	768.8	834.7	924.4
37.5°	674.0	717.2	789.4	871.8
40°	624.5	669.8	731.7	814.1
42.5°	578.1	618.3	674.0	756.4
45°	535.9	564.7	616.2	693.5
47.5°	491.6	517.3	564.7	642.0
50°	450.3	472.0	513.2	585.3
52.5°	410.1	428.7	466.8	524.5
55°	374.1	391.6	419.4	476.1
57.5°	337.0	350.4	377.2	422.5
60°	300.9	313.3	334.9	372.0
62.5°	264.8	275.1	295.8	325.6
65°	232.9	241.1	256.6	282.4
67.5°	202.0	207.1	219.5	240.1
70°	172.1	176.2	186.5	203.0
72.5°	140.2	144.3	155.6	166.9
75°	113.4	114.4	122.6	131.9
77.5°	88.6	87.6	93.8	101.0
80°	60.8	63.9	69.0	72.1
82.5°	41.2	42.3	44.3	46.4
85°	22.7	23.7	23.7	26.8
87.5°	9.3	10.3	10.3	11.3
90°	0.0	0.0	0.0	0.0

TEST NUMBER: P997645

CATALOG NUMBER: SA2XXDP-B675DB35-4F0-XX-W2A-A

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	22.59	24.10	22.95	24.42	24.73	18.85	20.37	19.22	20.68	21.00
	3H	23.70	25.06	24.08	25.39	25.75	20.27	21.63	20.64	21.95	22.32
	4H	24.02	25.30	24.42	25.65	26.03	20.77	22.05	21.17	22.40	22.78
	6H	24.21	25.39	24.63	25.76	26.15	21.13	22.31	21.54	22.68	23.07
	8H	24.25	25.38	24.68	25.77	26.17	21.24	22.37	21.67	22.76	23.16
	12H	24.27	25.34	24.70	25.73	26.15	21.32	22.39	21.75	22.77	23.20
4H	2H	22.70	23.98	23.10	24.33	24.71	19.65	20.93	20.05	21.28	21.65
	3H	24.04	25.10	24.45	25.50	25.90	21.23	22.29	21.64	22.69	23.09
	4H	24.51	25.46	24.94	25.88	26.32	21.83	22.78	22.26	23.20	23.63
	6H	24.84	25.67	25.30	26.11	26.57	22.28	23.11	22.74	23.55	24.01
	8H	24.92	25.69	25.38	26.14	26.60	22.42	23.20	22.89	23.64	24.11
	12H	24.96	25.65	25.44	26.13	26.60	22.53	23.22	23.01	23.70	24.17
8H	4H	24.59	25.37	25.06	25.81	26.28	22.23	23.01	22.70	23.45	23.92
	6H	25.00	25.64	25.50	26.13	26.61	22.78	23.42	23.27	23.91	24.39
	8H	25.13	25.70	25.64	26.21	26.70	22.97	23.55	23.49	24.06	24.55
	12H	25.22	25.73	25.73	26.22	26.78	23.14	23.65	23.65	24.14	24.70
12H	4H	24.59	25.28	25.07	25.76	26.23	22.29	22.98	22.77	23.46	23.93
	6H	24.99	25.57	25.51	26.08	26.57	22.85	23.43	23.37	23.94	24.42
	8H	25.16	25.67	25.67	26.16	26.73	23.10	23.61	23.61	24.10	24.66

END OF REPORT