

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P997778

Luminaire Tested: SA2XXRDP-B865DB35-4F0-XX-W2A-A

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P997778
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-29)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDP-B865DB35-4F0-XX-W2A-A
Description: Define 2 Regressed Direct Recessed with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3294.0 lumens
Efficiency: N/A
Efficacy: 70.4 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 46.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P997778

CATALOG NUMBER: SA2XXRDP-B865DB35-4F0-XX-W2A-A

Luminous Intensity Polar Plot



TEST NUMBER: P997778

CATALOG NUMBER: SA2XXRDP-B865DB35-4F0-XX-W2A-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	106	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87		
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76		
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66		
4	87	77	69	63	85	76	68	63	73	67	62	71	66	61	69	64	60	59		
5	81	70	62	56	79	69	61	56	67	60	55	65	59	55	63	58	54	52		
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47		
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42		
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	39		
9	62	50	43	38	61	50	42	37	49	42	37	47	41	37	47	41	37	35		
10	59	47	39	35	58	46	39	35	45	39	34	44	38	34	44	38	34	33		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	30172	30172	30172	30172
5°	30308	33697	30415	26920
10°	30041	37387	30255	23335
15°	29457	39226	29957	18385
20°	28740	34005	29365	15909
25°	27854	22302	28457	14205
30°	26704	15012	27432	12857
35°	25289	12159	26109	11594
40°	23703	10811	24716	10729
45°	22003	9785	22921	9577
50°	20257	8905	21203	8873
55°	18314	8370	19302	8263
60°	16605	7003	17488	6921
65°	15035	5903	15926	6697
70°	13301	5457	14347	6313
75°	11504	5107	12556	5835
80°	9535	4713	10264	5196
85°	7465	4323	8173	4577

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 160°

Vertical Angle: 45°

Luminance: 33122 cd/sqm

TEST NUMBER: P997778

CATALOG NUMBER: SA2XXRDP-B865DB35-4F0-XX-W2A-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	180.8	5.5
10°-20°	504.7	15.3
20°-30°	649.5	19.7
30°-40°	616.2	18.7
40°-50°	528.1	16.0
50°-60°	402.2	12.2
60°-70°	253.6	7.7
70°-80°	126.5	3.8
80°-90°	32.5	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1334.9	40.5
0°-40°	1951.1	59.2
0°-60°	2881.3	87.5
0°-90°	3294.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3294.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1906	1906	1906	1906	1906	
5°	1907	2121	1914	1694	1907	181
15°	1798	2394	1828	1122	1798	506
25°	1595	1277	1629	813	1595	732
35°	1309	629	1351	600	1309	819
45°	983	437	1024	428	983	759
55°	664	303	699	299	664	598
65°	401	158	425	179	401	398
75°	188	84	205	95	188	204
85°	41	24	45	25	41	49
90°	0	0	0	0	0	

TEST NUMBER: P997778

CATALOG NUMBER: SA2XXRDP-B865DB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1
2.5°	1918.0	1926.0	1930.0	1935.3	1947.2	1955.1	1967.0	1969.7	1968.4	1973.7	1959.1
5°	1907.4	1924.7	1940.6	1953.8	1975.0	1988.2	2002.8	2020.0	2024.0	2043.9	2032.0
7.5°	1892.9	1918.0	1940.6	1967.0	1998.8	2016.1	2038.6	2065.1	2077.0	2100.8	2107.5
10°	1869.0	1904.8	1943.2	1971.0	2014.7	2045.2	2066.4	2108.8	2136.6	2172.4	2167.1
12.5°	1830.6	1877.0	1928.6	1975.0	2032.0	2051.8	2091.6	2135.3	2171.0	2204.2	2233.3
15°	1797.5	1850.5	1907.4	1964.4	2029.3	2066.4	2106.1	2163.1	2201.5	2259.8	2285.0
17.5°	1752.5	1820.0	1887.6	1951.1	2028.0	2070.4	2119.4	2175.0	2232.0	2287.6	2307.5
20°	1706.1	1779.0	1851.8	1937.9	2025.3	2066.4	2116.7	2185.6	2241.2	2285.0	2285.0
22.5°	1650.5	1739.2	1822.7	1904.8	2000.2	2059.8	2111.4	2192.2	2232.0	2241.2	2205.5
25°	1594.8	1683.6	1775.0	1877.0	1985.6	2038.6	2096.9	2172.4	2185.6	2148.5	2055.8
27.5°	1528.6	1627.9	1731.3	1841.2	1955.1	2021.4	2074.3	2124.7	2099.5	2000.2	1855.8
30°	1461.0	1568.3	1684.9	1789.5	1927.3	1988.2	2033.3	2047.8	1968.4	1806.8	1620.0
32.5°	1390.8	1495.5	1618.7	1744.5	1883.6	1941.9	1971.0	1932.6	1786.9	1582.9	1355.1
35°	1308.7	1426.6	1555.1	1686.2	1824.0	1867.7	1884.9	1790.9	1604.1	1340.5	1114.0
37.5°	1234.5	1352.4	1490.2	1624.0	1757.8	1781.6	1764.4	1617.3	1380.2	1119.3	898.1
40°	1147.1	1272.9	1408.1	1557.7	1667.7	1674.3	1631.9	1441.2	1147.1	902.1	765.6
42.5°	1066.3	1193.5	1328.6	1480.9	1564.4	1541.8	1484.9	1234.5	957.7	777.5	667.6
45°	982.9	1103.4	1249.1	1384.2	1443.8	1390.8	1304.7	1038.5	804.0	668.9	584.2
47.5°	902.1	1014.7	1159.0	1288.8	1299.4	1239.8	1137.8	870.3	696.7	588.1	519.2
50°	822.6	935.2	1070.3	1177.6	1167.0	1084.9	969.6	756.4	605.3	519.2	462.3
52.5°	743.1	845.1	976.2	1061.0	1016.0	936.5	822.6	641.1	528.5	453.0	409.3
55°	663.6	759.0	871.6	941.8	870.3	778.9	698.1	549.7	458.3	397.4	364.3
57.5°	597.4	672.9	776.2	818.6	732.5	661.0	590.8	472.9	397.4	353.7	315.3
60°	524.5	593.4	678.2	703.4	614.6	556.3	496.7	400.0	340.4	302.0	276.8
62.5°	462.3	519.2	584.2	584.2	506.0	462.3	417.3	335.1	286.1	255.6	243.7
65°	401.4	442.4	488.8	483.5	417.3	378.8	343.1	276.8	239.8	218.6	206.6
67.5°	341.7	373.5	404.0	385.5	337.8	304.7	271.5	223.9	198.7	184.1	168.2
70°	287.4	312.6	328.5	311.3	263.6	235.8	211.9	180.1	160.3	141.7	132.5
72.5°	241.1	251.7	257.0	235.8	196.0	180.1	162.9	140.4	123.2	113.9	111.3
75°	188.1	197.4	193.4	177.5	144.4	132.5	119.2	103.3	99.3	94.0	91.4
77.5°	147.0	147.0	140.4	125.8	103.3	94.0	88.7	80.8	76.8	75.5	72.9
80°	104.6	103.3	99.3	83.5	70.2	64.9	64.9	59.6	58.3	55.6	55.6
82.5°	68.9	68.9	63.6	50.3	46.4	45.0	43.7	41.1	41.1	39.7	39.7
85°	41.1	38.4	31.8	27.8	26.5	26.5	25.2	23.8	25.2	23.8	23.8
87.5°	18.5	14.6	10.6	10.6	10.6	10.6	10.6	10.6	10.6	10.6	10.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P997778

CATALOG NUMBER: SA2XXRDP-B865DB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1
2.5°	1973.7	1976.3	1980.3	1998.8	2001.5	2006.8	2004.1	2004.1	2005.5	2002.8	2004.1
5°	2058.4	2062.4	2082.3	2104.8	2110.1	2104.8	2111.4	2120.7	2120.7	2120.7	2118.1
7.5°	2137.9	2152.5	2175.0	2208.1	2214.7	2221.4	2233.3	2225.3	2228.0	2239.9	2235.9
10°	2214.7	2235.9	2261.1	2288.9	2303.5	2312.8	2318.1	2330.0	2357.8	2326.0	2337.9
12.5°	2287.6	2318.1	2344.6	2375.0	2385.6	2397.5	2401.5	2412.1	2412.1	2410.8	2420.1
15°	2335.3	2363.1	2386.9	2406.8	2409.5	2406.8	2404.2	2405.5	2409.5	2393.6	2402.8
17.5°	2345.9	2348.5	2356.5	2348.5	2349.9	2322.0	2306.1	2302.2	2265.1	2266.4	2296.9
20°	2294.2	2249.2	2237.3	2193.6	2167.1	2095.5	2092.9	2073.0	1994.9	2018.7	2013.4
22.5°	2152.5	2075.7	1973.7	1923.3	1898.2	1822.7	1764.4	1723.3	1695.5	1667.7	1655.8
25°	1965.7	1841.2	1696.8	1597.5	1582.9	1512.7	1405.4	1355.1	1295.5	1276.9	1308.7
27.5°	1724.6	1563.0	1400.1	1247.8	1220.0	1156.4	1102.1	1066.3	997.4	993.5	996.1
30°	1397.5	1234.5	1098.1	998.8	929.9	900.7	865.0	838.5	810.7	821.3	823.9
32.5°	1148.4	993.5	866.3	813.3	781.5	763.0	732.5	715.3	703.4	699.4	698.1
35°	912.7	809.3	752.4	700.7	682.2	668.9	646.4	638.5	627.9	629.2	629.2
37.5°	781.5	695.4	653.0	626.5	609.3	602.7	588.1	580.2	573.6	570.9	574.9
40°	674.2	614.6	588.1	564.3	549.7	547.1	539.1	529.8	521.9	523.2	527.2
42.5°	596.1	561.6	529.8	511.3	500.7	496.7	490.1	483.5	483.5	479.5	478.2
45°	533.8	506.0	479.5	462.3	455.7	450.4	442.4	441.1	435.8	437.1	438.4
47.5°	478.2	455.7	435.8	418.6	412.0	410.6	402.7	397.4	397.4	396.1	394.7
50°	427.8	405.3	388.1	378.8	369.6	366.9	365.6	364.3	361.6	361.6	362.9
52.5°	386.8	364.3	351.0	343.1	337.8	335.1	335.1	333.8	333.8	333.8	332.5
55°	341.7	323.2	312.6	310.0	307.3	306.0	304.7	302.0	300.7	303.3	300.7
57.5°	299.4	292.7	283.5	280.8	274.2	274.2	270.2	267.6	264.9	267.6	267.6
60°	266.2	257.0	251.7	243.7	238.4	233.1	226.5	225.2	222.5	221.2	219.9
62.5°	231.8	223.9	210.6	198.7	190.7	185.4	182.8	181.5	181.5	180.1	180.1
65°	193.4	174.8	168.2	164.3	162.9	161.6	159.0	157.6	159.0	157.6	159.0
67.5°	151.0	148.4	144.4	141.7	140.4	139.1	139.1	137.8	137.8	137.8	137.8
70°	131.1	124.5	123.2	120.5	120.5	119.2	119.2	119.2	119.2	117.9	120.5
72.5°	108.6	104.6	103.3	102.0	102.0	102.0	100.7	100.7	100.7	99.3	100.7
75°	88.7	87.4	84.8	84.8	83.5	84.8	83.5	83.5	82.1	83.5	83.5
77.5°	71.5	70.2	68.9	68.9	67.6	67.6	67.6	67.6	67.6	67.6	68.9
80°	54.3	53.0	51.7	53.0	51.7	53.0	51.7	51.7	53.0	51.7	51.7
82.5°	39.7	38.4	38.4	37.1	37.1	37.1	37.1	37.1	37.1	37.1	37.1
85°	23.8	22.5	22.5	23.8	22.5	23.8	22.5	22.5	22.5	23.8	23.8
87.5°	10.6	11.9	10.6	10.6	10.6	10.6	10.6	10.6	10.6	10.6	11.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P997778

CATALOG NUMBER: SA2XXRDP-B865DB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1
2.5°	2009.4	2000.2	1997.5	2000.2	1997.5	1998.8	1989.6	1955.1	1964.4	1949.8	1957.8
5°	2123.3	2115.4	2098.2	2095.5	2092.9	2090.2	2077.0	2046.5	2034.6	2014.7	2013.4
7.5°	2232.0	2232.0	2218.7	2209.4	2197.5	2188.3	2171.0	2126.0	2107.5	2083.6	2070.4
10°	2339.3	2304.8	2319.4	2310.1	2281.0	2275.7	2243.9	2217.4	2181.6	2157.8	2136.6
12.5°	2416.1	2405.5	2392.2	2384.3	2376.3	2359.1	2337.9	2270.4	2251.8	2204.2	2180.3
15°	2413.4	2406.8	2410.8	2410.8	2408.1	2404.2	2386.9	2337.9	2306.1	2259.8	2218.7
17.5°	2283.6	2300.8	2318.1	2330.0	2356.5	2368.4	2384.3	2355.2	2335.3	2295.5	2251.8
20°	2057.1	2099.5	2149.8	2160.4	2184.3	2254.5	2286.3	2311.4	2319.4	2306.1	2270.4
22.5°	1741.9	1777.6	1899.5	1896.8	1931.3	2014.7	2107.5	2183.0	2242.6	2275.7	2262.4
25°	1364.3	1414.7	1479.6	1528.6	1641.2	1765.7	1880.9	2001.5	2104.8	2196.2	2218.7
27.5°	1031.9	1098.1	1149.8	1214.7	1271.6	1418.7	1567.0	1755.1	1875.6	2049.2	2139.2
30°	834.5	865.0	916.6	947.1	974.9	1087.5	1255.7	1441.2	1653.1	1853.1	2008.1
32.5°	712.6	733.8	772.2	785.5	814.6	890.1	996.1	1165.7	1384.2	1626.6	1830.6
35°	639.8	662.3	670.3	682.2	706.0	753.7	826.6	949.7	1147.1	1384.2	1627.9
37.5°	577.5	589.5	612.0	619.9	627.9	663.6	712.6	798.7	929.9	1124.6	1394.8
40°	533.8	540.4	552.4	559.0	564.3	589.5	633.2	691.4	788.1	936.5	1185.5
42.5°	487.5	495.4	503.4	511.3	517.9	537.8	564.3	619.9	684.8	797.4	977.6
45°	442.4	447.7	457.0	462.3	471.6	487.5	511.3	549.7	608.0	679.5	825.2
47.5°	401.4	408.0	412.0	418.6	425.2	442.4	464.9	490.1	537.8	608.0	714.0
50°	364.3	372.2	377.5	378.8	384.1	400.0	418.6	446.4	476.9	531.2	623.9
52.5°	337.8	339.1	343.1	348.4	347.0	356.3	373.5	394.7	426.5	470.2	537.8
55°	307.3	311.3	313.9	315.3	315.3	323.2	332.5	352.3	377.5	413.3	470.2
57.5°	268.9	272.9	280.8	283.5	287.4	291.4	295.4	308.6	329.8	364.3	410.6
60°	229.2	231.8	239.8	245.1	247.7	258.3	263.6	274.2	286.1	311.3	355.0
62.5°	184.1	186.8	190.7	196.0	201.3	217.2	230.5	241.1	250.4	267.6	303.3
65°	160.3	161.6	164.3	165.6	166.9	173.5	185.4	200.0	217.2	230.5	251.7
67.5°	139.1	140.4	141.7	144.4	145.7	147.0	152.3	156.3	173.5	192.1	208.0
70°	119.2	121.9	123.2	123.2	124.5	127.2	129.8	135.1	140.4	149.7	169.6
72.5°	100.7	102.0	104.6	104.6	104.6	107.3	109.9	112.6	115.2	120.5	128.5
75°	83.5	86.1	86.1	86.1	87.4	87.4	90.1	92.7	95.4	99.3	102.0
77.5°	68.9	68.9	68.9	68.9	70.2	70.2	71.5	74.2	75.5	76.8	79.5
80°	51.7	53.0	53.0	53.0	54.3	54.3	54.3	57.0	58.3	58.3	60.9
82.5°	38.4	38.4	38.4	39.7	38.4	39.7	39.7	41.1	39.7	41.1	42.4
85°	23.8	23.8	23.8	25.2	25.2	25.2	25.2	25.2	25.2	25.2	26.5
87.5°	11.9	11.9	11.9	11.9	11.9	11.9	11.9	11.9	13.2	11.9	11.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P997778

CATALOG NUMBER: SA2XXRDP-B865DB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1
2.5°	1945.9	1939.2	1939.2	1935.3	1935.3	1914.1	1914.1	1920.7	1912.7	1903.5	1890.2
5°	1996.2	1981.6	1977.6	1972.3	1955.1	1928.6	1918.0	1914.1	1898.2	1878.3	1855.8
7.5°	2043.9	2020.0	2008.1	1996.2	1973.7	1936.6	1915.4	1900.8	1877.0	1846.5	1817.4
10°	2090.2	2059.8	2029.3	2014.7	1982.9	1936.6	1906.1	1882.3	1847.8	1806.8	1765.7
12.5°	2132.6	2069.0	2063.7	2034.6	1988.2	1935.3	1888.9	1854.5	1810.7	1763.1	1715.4
15°	2169.7	2104.8	2073.0	2046.5	1985.6	1919.4	1870.3	1828.0	1769.7	1715.4	1657.1
17.5°	2188.3	2118.1	2096.9	2053.1	1990.9	1904.8	1838.6	1786.9	1723.3	1658.4	1592.2
20°	2206.8	2124.7	2090.2	2059.8	1975.0	1877.0	1802.8	1743.2	1673.0	1596.2	1523.3
22.5°	2216.1	2124.7	2083.6	2041.2	1959.1	1846.5	1759.1	1688.9	1606.8	1528.6	1441.2
25°	2200.2	2116.7	2067.7	2024.0	1931.3	1809.4	1708.7	1629.3	1541.8	1453.1	1364.3
27.5°	2160.4	2098.2	2041.2	1996.2	1892.9	1761.7	1655.8	1565.7	1475.6	1376.3	1286.2
30°	2086.3	2058.4	2013.4	1963.1	1850.5	1719.3	1593.5	1500.8	1401.4	1302.1	1208.0
32.5°	1971.0	1994.9	1965.7	1922.0	1800.1	1661.1	1527.3	1433.2	1324.6	1217.3	1131.2
35°	1830.6	1915.4	1899.5	1869.0	1747.2	1598.8	1465.0	1351.1	1242.5	1133.9	1047.8
37.5°	1677.0	1805.4	1818.7	1800.1	1686.2	1535.2	1388.2	1276.9	1165.7	1055.7	968.3
40°	1466.3	1663.7	1706.1	1714.0	1622.6	1458.4	1304.7	1196.1	1086.2	978.9	872.9
42.5°	1272.9	1522.0	1575.0	1608.1	1541.8	1382.9	1227.9	1107.4	998.8	902.1	796.1
45°	1091.5	1351.1	1437.2	1479.6	1450.4	1296.8	1136.5	1023.9	924.6	835.8	733.8
47.5°	904.7	1165.7	1286.2	1353.8	1353.8	1209.4	1049.1	937.8	842.5	766.9	676.9
50°	780.2	997.4	1121.9	1210.7	1234.5	1120.6	969.6	861.0	770.9	688.8	619.9
52.5°	665.0	859.7	963.0	1055.7	1124.6	1025.2	880.9	782.8	694.1	617.3	563.0
55°	574.9	720.6	814.6	916.6	993.5	928.6	794.8	699.4	622.6	559.0	512.6
57.5°	488.8	615.9	692.8	782.8	865.0	816.0	708.7	626.5	559.0	503.4	462.3
60°	415.9	519.2	578.9	649.1	751.1	716.6	627.9	552.4	498.1	447.7	413.3
62.5°	353.7	435.8	486.1	536.5	629.2	613.3	544.4	486.1	439.8	397.4	368.2
65°	290.1	357.6	397.4	441.1	515.3	521.9	466.3	425.2	382.8	345.7	319.2
67.5°	234.5	287.4	323.2	360.3	419.9	438.4	400.0	365.6	329.8	299.4	275.5
70°	189.4	226.5	253.0	282.1	331.2	353.7	333.8	310.0	280.8	255.6	234.5
72.5°	149.7	173.5	189.4	211.9	251.7	274.2	272.9	251.7	230.5	213.3	196.0
75°	109.9	128.5	141.7	156.3	188.1	209.3	214.6	205.3	184.1	170.9	157.6
77.5°	83.5	94.0	100.7	111.3	133.8	152.3	160.3	157.6	143.1	132.5	123.2
80°	63.6	66.2	68.9	72.9	91.4	108.6	113.9	112.6	104.6	100.7	90.1
82.5°	45.0	46.4	47.7	49.0	55.6	70.2	75.5	78.2	71.5	67.6	58.3
85°	26.5	27.8	27.8	30.5	31.8	35.8	45.0	45.0	43.7	38.4	37.1
87.5°	13.2	13.2	11.9	11.9	13.2	14.6	17.2	19.9	17.2	15.9	14.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P997778

CATALOG NUMBER: SA2XXRDP-B865DB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1
2.5°	1884.9	1886.2	1890.2	1878.3	1859.8	1851.8	1828.0	1824.0	1820.0	1820.0	1824.0
5°	1842.5	1837.2	1838.6	1816.0	1789.5	1773.7	1740.5	1745.8	1728.6	1718.0	1720.7
7.5°	1796.2	1781.6	1780.3	1751.1	1718.0	1688.9	1654.4	1646.5	1630.6	1612.0	1604.1
10°	1737.9	1727.3	1707.4	1674.3	1631.9	1608.1	1561.7	1533.9	1529.9	1502.1	1491.5
12.5°	1678.3	1659.7	1639.9	1593.5	1545.8	1507.4	1473.0	1442.5	1421.3	1397.5	1381.6
15°	1609.4	1586.9	1564.4	1515.4	1459.7	1421.3	1369.6	1324.6	1262.4	1213.3	1185.5
17.5°	1533.9	1508.7	1478.3	1424.0	1369.6	1316.7	1221.3	1168.3	1124.6	1095.5	1078.2
20°	1455.7	1427.9	1397.5	1343.2	1249.1	1156.4	1103.4	1062.3	1035.8	1006.7	985.5
22.5°	1373.6	1344.5	1311.4	1226.6	1127.2	1062.3	1021.3	982.9	944.4	928.6	918.0
25°	1296.8	1270.3	1227.9	1112.7	1034.5	974.9	928.6	903.4	883.5	862.3	842.5
27.5°	1217.3	1168.3	1108.7	1012.0	963.0	902.1	868.9	850.4	816.0	801.4	792.1
30°	1121.9	1067.6	1010.7	941.8	884.8	842.5	812.0	781.5	761.7	747.1	731.2
32.5°	1025.2	973.6	937.8	866.3	823.9	780.2	751.1	732.5	703.4	694.1	687.5
35°	941.8	898.1	866.3	808.0	768.3	728.5	707.3	679.5	661.0	643.8	633.2
37.5°	859.7	835.8	802.7	753.7	711.3	679.5	650.4	641.1	615.9	606.7	596.1
40°	802.7	766.9	739.1	696.7	661.0	626.5	608.0	586.8	569.6	555.0	551.0
42.5°	733.8	707.3	691.4	645.1	608.0	588.1	565.6	541.8	528.5	516.6	502.0
45°	682.2	658.3	635.8	598.7	565.6	540.4	520.6	504.7	482.2	476.9	454.3
47.5°	627.9	604.0	586.8	549.7	519.2	495.4	480.8	459.6	441.1	429.2	418.6
50°	573.6	553.7	537.8	506.0	479.5	454.3	434.5	413.3	405.3	385.5	378.8
52.5°	521.9	508.7	491.4	461.0	434.5	413.3	392.1	374.9	362.9	352.3	344.4
55°	478.2	457.0	449.0	415.9	393.4	370.9	352.3	341.7	327.2	320.6	313.9
57.5°	429.2	417.3	404.0	378.8	353.7	332.5	319.2	303.3	295.4	287.4	282.1
60°	386.8	369.6	359.0	337.8	315.3	295.4	283.5	271.5	260.9	254.3	243.7
62.5°	337.8	324.5	317.9	295.4	276.8	258.3	247.7	235.8	227.8	215.9	202.7
65°	295.4	284.8	276.8	258.3	241.1	223.9	213.3	198.7	188.1	181.5	180.1
67.5°	258.3	250.4	238.4	221.2	204.0	190.7	178.8	166.9	165.6	162.9	162.9
70°	217.2	209.3	202.7	184.1	169.6	155.0	152.3	148.4	144.4	143.1	140.4
72.5°	181.5	174.8	166.9	151.0	136.4	132.5	129.8	127.2	123.2	121.9	120.5
75°	147.0	137.8	132.5	117.9	113.9	111.3	108.6	104.6	102.0	100.7	98.0
77.5°	112.6	103.3	103.3	95.4	92.7	88.7	86.1	83.5	82.1	79.5	79.5
80°	79.5	79.5	76.8	72.9	68.9	67.6	63.6	62.3	60.9	62.3	59.6
82.5°	58.3	53.0	53.0	50.3	47.7	46.4	43.7	43.7	42.4	42.4	42.4
85°	33.1	33.1	31.8	29.1	27.8	27.8	26.5	26.5	25.2	25.2	23.8
87.5°	13.2	11.9	13.2	11.9	11.9	10.6	10.6	10.6	9.3	10.6	9.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P997778

CATALOG NUMBER: SA2XXRDP-B865DB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1
2.5°	1824.0	1821.3	1813.4	1816.0	1812.1	1812.1	1809.4	1809.4	1809.4	1816.0	1812.1
5°	1724.6	1715.4	1706.1	1702.1	1698.1	1694.2	1694.2	1692.9	1704.8	1702.1	1712.7
7.5°	1601.5	1598.8	1580.3	1580.3	1573.6	1571.0	1577.6	1578.9	1580.3	1582.9	1589.5
10°	1491.5	1484.9	1458.4	1461.0	1457.1	1451.8	1455.7	1453.1	1462.4	1465.0	1462.4
12.5°	1361.7	1349.8	1320.6	1306.1	1290.2	1278.2	1292.8	1282.2	1319.3	1329.9	1359.0
15°	1189.5	1167.0	1147.1	1147.1	1132.5	1121.9	1128.6	1140.5	1148.4	1160.4	1165.7
17.5°	1074.3	1065.0	1049.1	1039.8	1035.8	1031.9	1031.9	1037.2	1054.4	1053.1	1063.7
20°	976.2	970.9	963.0	951.1	947.1	944.4	944.4	944.4	956.4	967.0	973.6
22.5°	908.7	904.7	899.4	883.5	875.6	872.9	879.5	883.5	892.8	900.7	907.4
25°	841.1	831.9	822.6	817.3	813.3	813.3	816.0	817.3	821.3	825.2	833.2
27.5°	785.5	778.9	765.6	751.1	751.1	747.1	749.7	752.4	761.7	774.9	781.5
30°	723.2	721.9	716.6	711.3	706.0	703.4	708.7	712.6	714.0	720.6	720.6
32.5°	678.2	668.9	659.7	654.4	651.7	650.4	651.7	657.0	657.0	665.0	674.2
35°	633.2	627.9	618.6	609.3	606.7	600.0	605.3	610.6	619.9	623.9	627.9
37.5°	584.2	577.5	573.6	570.9	565.6	566.9	563.0	570.9	578.9	577.5	580.2
40°	547.1	535.1	523.2	521.9	520.6	519.2	519.2	520.6	525.9	531.2	539.1
42.5°	499.4	495.4	484.8	474.2	471.6	468.9	466.3	471.6	482.2	491.4	495.4
45°	450.4	445.1	442.4	434.5	429.2	427.8	425.2	431.8	441.1	445.1	447.7
47.5°	405.3	404.0	396.1	397.4	393.4	394.7	393.4	397.4	397.4	401.4	404.0
50°	374.9	370.9	366.9	364.3	360.3	360.3	359.0	360.3	365.6	370.9	369.6
52.5°	344.4	337.8	336.5	335.1	332.5	335.1	331.2	332.5	337.8	340.4	339.1
55°	308.6	307.3	304.7	302.0	300.7	299.4	299.4	299.4	304.7	308.6	310.0
57.5°	280.8	274.2	268.9	268.9	263.6	262.3	264.9	266.2	270.2	272.9	275.5
60°	242.4	239.8	231.8	227.8	219.9	218.6	218.6	223.9	230.5	239.8	242.4
62.5°	201.3	197.4	196.0	196.0	196.0	196.0	196.0	196.0	196.0	197.4	197.4
65°	178.8	180.1	178.8	177.5	178.8	178.8	177.5	177.5	177.5	178.8	180.1
67.5°	160.3	159.0	160.3	159.0	157.6	157.6	156.3	157.6	159.0	160.3	160.3
70°	139.1	139.1	137.8	139.1	137.8	136.4	135.1	135.1	137.8	139.1	139.1
72.5°	119.2	119.2	117.9	117.9	115.2	115.2	116.6	115.2	115.2	119.2	119.2
75°	99.3	98.0	96.7	96.7	95.4	95.4	95.4	94.0	96.7	96.7	98.0
77.5°	78.2	78.2	78.2	76.8	76.8	75.5	75.5	76.8	76.8	76.8	78.2
80°	59.6	59.6	59.6	58.3	57.0	57.0	57.0	57.0	57.0	58.3	57.0
82.5°	41.1	41.1	41.1	41.1	41.1	39.7	39.7	39.7	41.1	41.1	39.7
85°	25.2	23.8	25.2	25.2	23.8	25.2	23.8	23.8	22.5	22.5	23.8
87.5°	10.6	9.3	7.9	7.9	9.3	7.9	7.9	7.9	9.3	7.9	7.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P997778

CATALOG NUMBER: SA2XXRDP-B865DB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1
2.5°	1816.0	1822.7	1820.0	1805.4	1820.0	1824.0	1831.9	1839.9	1845.2	1853.1	1859.8
5°	1702.1	1715.4	1723.3	1715.4	1741.9	1745.8	1764.4	1775.0	1790.9	1804.1	1814.7
7.5°	1594.8	1605.4	1621.3	1624.0	1639.9	1658.4	1684.9	1711.4	1736.6	1749.8	1761.7
10°	1479.6	1498.1	1522.0	1516.7	1540.5	1569.7	1597.5	1639.9	1661.1	1684.9	1706.1
12.5°	1364.3	1376.3	1408.1	1418.7	1453.1	1475.6	1514.0	1540.5	1593.5	1621.3	1639.9
15°	1163.0	1212.0	1251.8	1299.4	1344.5	1386.9	1421.3	1469.0	1515.4	1536.5	1567.0
17.5°	1071.6	1094.1	1118.0	1141.8	1200.1	1275.6	1336.5	1388.2	1427.9	1455.7	1491.5
20°	976.2	998.8	1025.2	1047.8	1083.5	1137.8	1213.3	1302.1	1349.8	1378.9	1413.4
22.5°	908.7	929.9	947.1	967.0	994.8	1034.5	1091.5	1201.4	1265.0	1300.8	1331.2
25°	835.8	862.3	880.9	895.4	918.0	961.7	1008.0	1070.3	1184.2	1212.0	1254.4
27.5°	785.5	793.4	814.6	837.2	859.7	883.5	931.2	984.2	1061.0	1121.9	1173.6
30°	725.9	745.8	765.6	774.9	794.8	829.2	858.3	915.3	974.9	1022.6	1084.9
32.5°	680.8	692.8	706.0	728.5	747.1	770.9	800.1	847.8	898.1	928.6	976.2
35°	630.5	638.5	666.3	675.6	694.1	717.9	747.1	784.2	838.5	862.3	896.8
37.5°	582.8	601.4	609.3	630.5	647.7	671.6	692.8	735.2	770.9	798.7	830.5
40°	545.7	553.7	568.3	586.8	601.4	619.9	646.4	676.9	715.3	737.8	765.6
42.5°	500.7	507.3	525.9	536.5	560.3	577.5	593.4	630.5	665.0	682.2	710.0
45°	451.7	467.6	479.5	500.7	513.9	535.1	555.0	581.5	613.3	633.2	649.1
47.5°	409.3	425.2	437.1	457.0	478.2	487.5	508.7	536.5	565.6	581.5	604.0
50°	374.9	380.2	402.7	412.0	434.5	453.0	467.6	491.4	523.2	532.5	551.0
52.5°	341.7	345.7	360.3	372.2	392.1	408.0	426.5	449.0	475.5	490.1	504.7
55°	312.6	315.3	321.9	335.1	348.4	368.2	385.5	406.7	429.2	445.1	458.3
57.5°	279.5	284.8	290.1	298.0	311.3	329.8	348.4	368.2	386.8	397.4	414.6
60°	241.1	249.0	258.3	267.6	276.8	290.1	311.3	329.8	347.0	356.3	369.6
62.5°	200.0	215.9	223.9	234.5	242.4	254.3	270.2	291.4	303.3	315.3	325.9
65°	180.1	181.5	182.8	193.4	208.0	219.9	234.5	250.4	268.9	276.8	284.8
67.5°	160.3	161.6	164.3	165.6	170.9	184.1	200.0	217.2	231.8	237.1	245.1
70°	140.4	140.4	145.7	147.0	148.4	149.7	162.9	180.1	193.4	200.0	209.3
72.5°	119.2	120.5	123.2	124.5	127.2	129.8	133.8	143.1	159.0	165.6	176.2
75°	98.0	99.3	100.7	102.0	106.0	107.3	111.3	116.6	123.2	131.1	137.8
77.5°	78.2	78.2	79.5	82.1	84.8	86.1	90.1	92.7	95.4	99.3	104.6
80°	58.3	59.6	59.6	62.3	62.3	63.6	64.9	68.9	71.5	74.2	76.8
82.5°	39.7	42.4	42.4	42.4	43.7	45.0	46.4	46.4	49.0	50.3	54.3
85°	23.8	25.2	25.2	25.2	23.8	26.5	26.5	27.8	27.8	27.8	29.1
87.5°	9.3	7.9	9.3	9.3	9.3	10.6	9.3	9.3	10.6	11.9	11.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P997778

CATALOG NUMBER: SA2XXRDP-B865DB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1906.1	1906.1	1906.1	1906.1
2.5°	1871.7	1867.7	1891.5	1918.0
5°	1833.3	1839.9	1870.3	1907.4
7.5°	1793.5	1808.1	1843.9	1892.9
10°	1737.9	1764.4	1818.7	1869.0
12.5°	1683.6	1719.3	1771.0	1830.6
15°	1622.6	1662.4	1726.0	1797.5
17.5°	1555.1	1600.1	1674.3	1752.5
20°	1483.6	1543.2	1621.3	1706.1
22.5°	1404.1	1475.6	1556.4	1650.5
25°	1327.3	1405.4	1486.2	1594.8
27.5°	1251.8	1328.6	1418.7	1528.6
30°	1176.3	1246.5	1343.2	1461.0
32.5°	1095.5	1168.3	1270.3	1390.8
35°	1021.3	1094.1	1189.5	1308.7
37.5°	941.8	1019.9	1111.3	1234.5
40°	849.1	940.5	1029.2	1147.1
42.5°	772.2	868.9	955.0	1066.3
45°	711.3	802.7	874.2	982.9
47.5°	654.4	728.5	801.4	902.1
50°	600.0	657.0	732.5	822.6
52.5°	544.4	593.4	658.3	743.1
55°	494.1	540.4	598.7	663.6
57.5°	447.7	480.8	539.1	597.4
60°	396.1	430.5	475.5	524.5
62.5°	352.3	378.8	421.2	462.3
65°	306.0	331.2	362.9	401.4
67.5°	263.6	286.1	311.3	341.7
70°	225.2	242.4	260.9	287.4
72.5°	184.1	202.7	219.9	241.1
75°	151.0	159.0	173.5	188.1
77.5°	116.6	127.2	135.1	147.0
80°	83.5	92.7	95.4	104.6
82.5°	55.6	60.9	66.2	68.9
85°	31.8	34.4	39.7	41.1
87.5°	11.9	13.2	15.9	18.5
90°	0.0	0.0	0.0	0.0

TEST NUMBER: P997778

CATALOG NUMBER: SA2XXRDP-B865DB35-4F0-XX-W2A-A

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	22.87	24.32	23.24	24.64	24.95	17.29	18.74	17.65	19.05	19.37
	3H	24.20	25.50	24.58	25.83	26.19	18.42	19.71	18.79	20.04	20.41
	4H	24.63	25.84	25.03	26.19	26.57	18.88	20.09	19.28	20.44	20.82
	6H	24.90	26.02	25.32	26.39	26.78	19.25	20.37	19.67	20.74	21.13
	8H	24.97	26.04	25.40	26.43	26.83	19.38	20.44	19.80	20.83	21.24
	12H	25.01	26.03	25.44	26.42	26.85	19.46	20.48	19.89	20.86	21.29
4H	2H	22.85	24.07	23.25	24.42	24.80	17.97	19.19	18.37	19.54	19.92
	3H	24.29	25.30	24.71	25.70	26.10	19.26	20.27	19.67	20.67	21.07
	4H	24.80	25.70	25.23	26.12	26.56	19.82	20.72	20.25	21.14	21.58
	6H	25.18	25.96	25.63	26.40	26.87	20.30	21.09	20.76	21.53	21.99
	8H	25.29	26.02	25.75	26.46	26.93	20.47	21.20	20.93	21.64	22.11
	12H	25.36	26.01	25.84	26.49	26.97	20.59	21.24	21.07	21.72	22.19
8H	4H	24.79	25.52	25.25	25.96	26.43	20.14	20.87	20.60	21.32	21.78
	6H	25.21	25.81	25.70	26.30	26.78	20.72	21.33	21.22	21.82	22.30
	8H	25.35	25.89	25.87	26.40	26.89	20.95	21.49	21.47	22.01	22.49
	12H	25.46	25.94	25.98	26.43	27.00	21.14	21.62	21.65	22.11	22.68
12H	4H	24.76	25.42	25.25	25.90	26.37	20.17	20.83	20.66	21.31	21.78
	6H	25.18	25.72	25.70	26.23	26.72	20.78	21.32	21.30	21.84	22.33
	8H	25.36	25.83	25.87	26.33	26.89	21.07	21.54	21.58	22.04	22.60