

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000907

Luminaire Tested: SA4XXDIP-B1195D1205UB35-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000907
REPORT IS A COMBINATION OF REPORTS P995520 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B1195D1205UB35-4F0-XX-W2A-F4
Description: Define 4 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9482.7 lumens
Efficiency: N/A
Efficacy: 98.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 96.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000907

CATALOG NUMBER: SA4XXDIP-B1195D1205UB35-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1000907

CATALOG NUMBER: SA4XXDIP-B1195D1205UB35-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60
1	99	94	90	87	91	88	84	81	75	73	70	64	62	60	53	52	51
2	90	82	76	71	83	77	71	67	66	62	58	56	53	50	47	45	43
3	82	72	65	59	76	67	61	56	58	53	49	49	46	43	41	39	36
4	75	64	56	50	69	60	53	47	52	46	42	44	40	36	37	34	31
5	69	57	49	43	64	53	46	41	46	40	36	40	35	32	33	30	27
6	63	51	43	37	59	48	41	35	42	36	31	36	31	28	30	27	24
7	59	46	38	33	54	43	36	31	38	32	28	33	28	25	28	24	21
8	55	42	34	29	50	39	32	27	34	29	25	30	25	22	25	22	19
9	51	38	31	26	47	36	29	25	32	26	22	27	23	20	23	20	17
10	47	35	28	23	44	33	27	22	29	24	20	25	21	18	22	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16355	16355	16355
5°	16369	15885	15904
10°	16230	15444	15336
15°	15998	14919	14694
20°	15700	14353	14031
25°	15366	13753	13316
30°	14962	13105	12531
35°	14544	12442	11773
40°	14109	11728	10966
45°	13652	11012	10212
50°	13146	10318	9377
55°	12597	9508	8547
60°	12034	8620	7684
65°	11391	7704	6709
70°	10648	6599	5666
75°	9542	5320	4539
80°	8131	3845	3192
85°	6316	2142	1719

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13652 cd/sqm

TEST NUMBER: P1000907

CATALOG NUMBER: SA4XXDIP-B1195D1205UB35-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	189.0	2.0
10°-20°	532.6	5.6
20°-30°	783.8	8.3
30°-40°	911.2	9.6
40°-50°	911.1	9.6
50°-60°	796.9	8.4
60°-70°	591.6	6.2
70°-80°	335.7	3.5
80°-90°	98.4	1.0
90°-100°	441.0	4.7
100°-110°	896.9	9.5
110°-120°	799.4	8.4
120°-130°	671.5	7.1
130°-140°	560.4	5.9
140°-150°	428.0	4.5
150°-160°	300.8	3.2
160°-170°	176.9	1.9
170°-180°	57.5	0.6
0°-30°	1505.5	15.9
0°-40°	2416.7	25.5
0°-60°	4124.6	43.5
0°-90°	5150.3	54.3
90°-120°	2137.3	22.5
90°-150°	3797.1	40.0
90°-180°	4332.0	45.7
0°-180°	9482.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2006	2006	2006	2006	2006	
5°	2004	1998	1980	1998	1994	190
15°	1908	1901	1877	1887	1882	538
25°	1728	1716	1694	1696	1689	795
35°	1487	1475	1453	1442	1434	930
45°	1213	1202	1176	1159	1154	935
55°	918	913	890	871	861	822
65°	622	614	598	582	574	616
75°	331	323	315	309	307	351
85°	87	87	84	84	82	93
90°	1	9	21	23	24	8
95°	38	121	950	471	285	42
105°	136	198	765	1647	1641	145
115°	240	301	682	1311	1576	238
125°	335	398	679	1116	1257	298
135°	398	474	673	990	1124	307
145°	458	525	670	835	918	288
155°	521	563	651	737	769	240
165°	568	586	624	661	671	160
175°	592	594	598	606	604	56
180°	594	594	594	594	594	

TEST NUMBER: P1000907

CATALOG NUMBER: SA4XXDIP-B1195D1205UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2005.7	2005.7	2005.7	2005.7	2005.7
2.5°	2012.1	2007.3	1989.6	2005.7	2004.1
5°	2004.1	1997.7	1980.0	1997.7	1994.4
7.5°	1989.6	1983.2	1963.9	1978.4	1976.8
10°	1968.7	1962.3	1941.4	1954.3	1951.1
12.5°	1941.4	1935.0	1912.5	1926.9	1922.1
15°	1907.7	1901.2	1877.1	1886.8	1881.9
17.5°	1869.1	1861.1	1838.6	1845.0	1841.8
20°	1825.7	1817.7	1793.6	1798.4	1795.2
22.5°	1779.1	1767.8	1743.7	1753.4	1746.9
25°	1727.7	1716.4	1693.9	1695.5	1689.1
27.5°	1669.8	1658.6	1637.7	1634.4	1626.4
30°	1611.9	1599.1	1578.2	1571.8	1563.7
32.5°	1550.9	1539.6	1517.1	1509.1	1501.1
35°	1486.6	1475.3	1452.8	1441.6	1433.6
37.5°	1419.1	1409.4	1385.3	1374.1	1362.8
40°	1353.2	1340.3	1316.2	1300.2	1292.1
42.5°	1282.5	1276.1	1248.7	1229.5	1224.6
45°	1213.4	1202.1	1176.4	1158.7	1153.9
47.5°	1141.1	1133.0	1108.9	1089.6	1076.8
50°	1067.1	1060.7	1038.2	1015.7	1006.1
52.5°	994.8	986.8	962.7	943.4	930.5
55°	917.7	912.8	890.3	871.1	861.4
57.5°	845.3	840.5	818.0	798.7	789.1
60°	769.8	761.8	740.9	726.4	718.4
62.5°	695.9	689.5	667.0	654.1	646.1
65°	622.0	613.9	597.9	581.8	573.7
67.5°	546.4	540.0	523.9	507.9	506.2
70°	477.3	466.1	453.2	440.4	435.5
72.5°	403.4	392.1	382.5	372.9	368.0
75°	331.1	323.0	315.0	308.6	307.0
77.5°	260.4	257.1	249.1	247.5	242.7
80°	197.7	192.9	189.6	186.4	184.8
82.5°	136.6	135.0	135.0	133.4	131.8
85°	86.8	86.8	83.6	83.6	82.0
87.5°	41.8	40.2	38.6	38.6	38.6
90°	1.2	9.3	21.0	23.3	24.5
92.5°	16.3	89.8	457.2	151.0	106.1
95°	38.5	121.3	950.5	470.6	284.6
97.5°	64.1	134.1	1017.0	961.0	683.4
100°	88.6	151.6	937.7	1329.6	1069.5
102.5°	112.0	172.6	838.6	1560.5	1405.4
105°	136.5	197.7	765.1	1647.4	1641.0
107.5°	163.3	223.4	717.3	1621.2	1752.9
110°	190.1	249.0	695.1	1527.8	1755.3

TEST NUMBER: P1000907

CATALOG NUMBER: SA4XXDIP-B1195D1205UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	215.8	274.6	684.6	1413.6	1686.5
115°	240.3	301.4	682.3	1310.9	1575.7
117.5°	265.9	326.5	681.1	1230.4	1467.2
120°	291.6	351.0	681.1	1176.2	1378.6
122.5°	314.9	375.0	680.0	1140.6	1308.6
125°	334.7	397.7	678.8	1115.6	1257.3
127.5°	353.4	418.7	676.5	1091.6	1224.6
130°	368.5	439.1	675.3	1063.1	1196.6
132.5°	383.7	456.6	674.1	1029.2	1165.1
135°	397.7	473.6	673.0	990.2	1124.3
137.5°	411.7	488.1	673.0	948.2	1076.5
140°	426.9	501.5	671.8	907.4	1024.0
142.5°	443.2	513.8	671.8	869.5	968.0
145°	458.4	524.8	669.5	835.0	917.9
147.5°	475.8	535.4	666.0	806.5	871.2
150°	492.2	545.2	662.5	780.2	832.7
152.5°	507.3	554.6	656.6	758.1	797.7
155°	521.3	562.8	650.8	737.1	768.6
157.5°	535.3	570.3	645.0	717.2	741.8
160°	548.2	576.7	638.0	697.4	717.3
162.5°	559.8	582.0	631.0	678.2	693.9
165°	568.0	585.5	624.0	660.7	670.6
167.5°	577.3	588.4	617.0	645.6	652.0
170°	583.1	590.8	610.0	630.4	634.5
172.5°	589.0	592.4	603.0	617.0	617.0
175°	592.5	593.6	598.3	606.5	604.1
177.5°	594.8	593.6	594.8	598.9	594.8
180°	593.6	593.6	593.6	593.6	593.6

(END OF REPORT)