

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000925

Luminaire Tested: SA4XXDIP-B1195D1205UB50-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000925
REPORT IS A COMBINATION OF REPORTS P995538 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B1195D1205UB50-4F0-XX-W2A-F4
Description: Define 4 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9079.3 lumens
Efficiency: N/A
Efficacy: 94.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 96.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000925

CATALOG NUMBER: SA4XXDIP-B1195D1205UB50-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1000925

CATALOG NUMBER: SA4XXDIP-B1195D1205UB50-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60
1	99	94	90	87	91	88	84	81	75	73	70	64	62	60	53	52	51
2	90	82	76	71	83	77	71	67	66	62	58	56	53	50	47	45	43
3	82	72	65	59	76	67	61	56	58	53	49	49	46	43	41	39	36
4	75	64	56	50	69	60	53	47	52	46	42	44	40	36	37	34	31
5	69	57	49	43	64	53	46	41	46	40	36	40	35	32	33	30	27
6	63	51	43	37	59	48	41	35	42	36	31	36	31	28	30	27	24
7	59	46	38	33	54	43	36	31	38	32	28	33	28	25	28	24	21
8	55	42	34	29	50	39	32	27	34	29	25	30	25	22	25	22	19
9	51	38	31	26	47	36	29	25	32	26	22	27	23	20	23	20	17
10	47	35	28	23	44	33	27	22	29	24	20	25	21	18	22	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15660	15660	15660
5°	15672	15209	15228
10°	15540	14787	14684
15°	15317	14285	14069
20°	15032	13742	13434
25°	14712	13168	12749
30°	14326	12548	11998
35°	13926	11912	11272
40°	13508	11229	10500
45°	13071	10544	9778
50°	12586	9879	8978
55°	12060	9104	8184
60°	11522	8254	7356
65°	10906	7376	6424
70°	10196	6318	5425
75°	9135	5093	4345
80°	7786	3683	3057
85°	6047	2050	1645

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13071 cd/sqm

TEST NUMBER: P1000925

CATALOG NUMBER: SA4XXDIP-B1195D1205UB50-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	181.0	2.0
10°-20°	509.9	5.6
20°-30°	750.5	8.3
30°-40°	872.4	9.6
40°-50°	872.3	9.6
50°-60°	763.0	8.4
60°-70°	566.4	6.2
70°-80°	321.4	3.5
80°-90°	94.2	1.0
90°-100°	422.2	4.7
100°-110°	858.7	9.5
110°-120°	765.4	8.4
120°-130°	642.9	7.1
130°-140°	536.5	5.9
140°-150°	409.8	4.5
150°-160°	288.0	3.2
160°-170°	169.4	1.9
170°-180°	55.1	0.6
0°-30°	1441.4	15.9
0°-40°	2313.8	25.5
0°-60°	3949.1	43.5
0°-90°	4931.2	54.3
90°-120°	2046.3	22.5
90°-150°	3635.6	40.0
90°-180°	4148.0	45.7
0°-180°	9079.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1920	1920	1920	1920	1920	
5°	1919	1913	1896	1913	1910	182
15°	1826	1820	1797	1806	1802	515
25°	1654	1643	1622	1623	1617	761
35°	1423	1413	1391	1380	1373	890
45°	1162	1151	1126	1109	1105	896
55°	879	874	852	834	825	787
65°	596	588	572	557	549	589
75°	317	309	302	295	294	336
85°	83	83	80	80	78	89
90°	1	9	20	22	24	8
95°	37	116	910	451	272	40
105°	131	189	732	1577	1571	139
115°	230	289	653	1255	1509	228
125°	320	381	650	1068	1204	286
135°	381	453	644	948	1076	294
145°	439	502	641	800	879	275
155°	499	539	623	706	736	230
165°	544	561	597	633	642	154
175°	567	568	573	581	578	54
180°	568	568	568	568	568	

TEST NUMBER: P1000925

CATALOG NUMBER: SA4XXDIP-B1195D1205UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1920.4	1920.4	1920.4	1920.4	1920.4
2.5°	1926.5	1921.9	1905.0	1920.4	1918.8
5°	1918.8	1912.7	1895.7	1912.7	1909.6
7.5°	1905.0	1898.8	1880.4	1894.2	1892.7
10°	1885.0	1878.8	1858.8	1871.1	1868.1
12.5°	1858.8	1852.7	1831.1	1845.0	1840.4
15°	1826.5	1820.3	1797.3	1806.5	1801.9
17.5°	1789.6	1781.9	1760.3	1766.5	1763.4
20°	1748.0	1740.3	1717.3	1721.9	1718.8
22.5°	1703.4	1692.6	1669.6	1678.8	1672.6
25°	1654.2	1643.4	1621.8	1623.4	1617.2
27.5°	1598.8	1588.0	1568.0	1564.9	1557.2
30°	1543.4	1531.1	1511.1	1504.9	1497.2
32.5°	1484.9	1474.1	1452.6	1444.9	1437.2
35°	1423.4	1412.6	1391.0	1380.3	1372.6
37.5°	1358.7	1349.5	1326.4	1315.6	1304.9
40°	1295.6	1283.3	1260.2	1244.9	1237.2
42.5°	1227.9	1221.8	1195.6	1177.1	1172.5
45°	1161.8	1151.0	1126.4	1109.4	1104.8
47.5°	1092.5	1084.8	1061.7	1043.3	1031.0
50°	1021.7	1015.6	994.0	972.5	963.3
52.5°	952.5	944.8	921.7	903.3	890.9
55°	878.6	874.0	852.5	834.0	824.8
57.5°	809.4	804.8	783.2	764.8	755.5
60°	737.1	729.4	709.4	695.5	687.8
62.5°	666.3	660.1	638.6	626.3	618.6
65°	595.5	587.8	572.4	557.0	549.3
67.5°	523.2	517.0	501.6	486.2	484.7
70°	457.0	446.2	433.9	421.6	417.0
72.5°	386.2	375.5	366.2	357.0	352.4
75°	317.0	309.3	301.6	295.4	293.9
77.5°	249.3	246.2	238.5	237.0	232.4
80°	189.3	184.7	181.6	178.5	177.0
82.5°	130.8	129.3	129.3	127.7	126.2
85°	83.1	83.1	80.0	80.0	78.5
87.5°	40.0	38.5	36.9	36.9	36.9
90°	1.1	8.9	20.1	22.3	23.5
92.5°	15.6	86.0	437.7	144.6	101.6
95°	36.9	116.2	910.1	450.6	272.5
97.5°	61.4	128.4	973.8	920.2	654.4
100°	84.9	145.2	897.8	1273.0	1024.0
102.5°	107.2	165.2	802.9	1494.2	1345.6
105°	130.7	189.3	732.5	1577.3	1571.2
107.5°	156.3	213.8	686.8	1552.2	1678.4
110°	182.0	238.4	665.5	1462.8	1680.6



TEST NUMBER: P1000925

CATALOG NUMBER: SA4XXDIP-B1195D1205UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	206.6	263.0	655.5	1353.4	1614.7
115°	230.0	288.6	653.3	1255.2	1508.6
117.5°	254.6	312.6	652.1	1178.1	1404.8
120°	279.2	336.2	652.1	1126.2	1319.9
122.5°	301.5	359.0	651.0	1092.1	1252.9
125°	320.5	380.8	649.9	1068.1	1203.8
127.5°	338.4	400.9	647.7	1045.2	1172.5
130°	352.9	420.4	646.6	1017.9	1145.7
132.5°	367.4	437.2	645.4	985.5	1115.6
135°	380.8	453.4	644.3	948.1	1076.5
137.5°	394.2	467.4	644.3	907.9	1030.7
140°	408.7	480.2	643.2	868.8	980.5
142.5°	424.3	491.9	643.2	832.4	926.9
145°	438.9	502.5	641.0	799.6	878.8
147.5°	455.6	512.6	637.6	772.2	834.2
150°	471.2	522.0	634.3	747.0	797.3
152.5°	485.8	531.0	628.7	725.8	763.8
155°	499.2	538.8	623.1	705.7	735.9
157.5°	512.6	546.1	617.5	686.8	710.2
160°	524.8	552.2	610.8	667.8	686.8
162.5°	536.0	557.2	604.1	649.3	664.4
165°	543.8	560.6	597.4	632.6	642.1
167.5°	552.8	563.4	590.7	618.1	624.2
170°	558.3	565.6	584.0	603.6	607.5
172.5°	563.9	567.3	577.3	590.7	590.7
175°	567.3	568.4	572.9	580.7	578.4
177.5°	569.5	568.4	569.5	573.4	569.5
180°	568.4	568.4	568.4	568.4	568.4

(END OF REPORT)