

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000964

Luminaire Tested: SA4XXDIP-B1195D365UB35-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000964
REPORT IS A COMBINATION OF REPORTS P995580 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B1195D365UB35-4F0-XX-W2A-F4
Description: Define 4 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6475.7 lumens
Efficiency: N/A
Efficacy: 91.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 70.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000964

CATALOG NUMBER: SA4XXDIP-B1195D365UB35-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1000964

CATALOG NUMBER: SA4XXDIP-B1195D365UB35-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	114	114	114	114	109	109	109	109	100	100	100	91	91	91	83	83	83	80		
1	104	100	96	92	100	96	92	89	88	85	82	80	78	76	74	72	70	67		
2	95	87	81	75	91	84	78	73	77	72	68	71	67	63	65	62	59	56		
3	87	77	69	63	83	74	67	61	68	62	57	62	58	54	57	54	50	47		
4	79	68	60	53	76	65	58	52	60	54	49	56	50	46	51	47	43	41		
5	73	61	52	46	70	59	51	45	54	48	42	50	45	40	46	42	38	35		
6	68	55	46	40	64	53	45	39	49	42	37	45	40	35	42	37	33	31		
7	63	50	41	35	60	48	40	35	45	38	33	41	36	31	38	34	30	28		
8	58	45	37	32	56	44	36	31	41	34	29	38	32	28	35	30	27	25		
9	54	41	34	28	52	40	33	28	37	31	27	35	29	25	33	28	24	22		
10	51	38	31	26	49	37	30	25	35	28	24	32	27	23	30	26	22	20		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16355	16355	16355
5°	16369	15885	15904
10°	16230	15444	15336
15°	15998	14919	14694
20°	15700	14353	14031
25°	15366	13753	13316
30°	14962	13105	12531
35°	14544	12442	11773
40°	14109	11728	10966
45°	13652	11012	10212
50°	13146	10318	9377
55°	12597	9508	8547
60°	12034	8620	7684
65°	11391	7704	6709
70°	10648	6599	5666
75°	9542	5320	4539
80°	8131	3845	3192
85°	6316	2142	1719

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13652 cd/sqm

TEST NUMBER: P1000964

CATALOG NUMBER: SA4XXDIP-B1195D365UB35-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	189.0	2.9
10°-20°	532.6	8.2
20°-30°	783.8	12.1
30°-40°	911.2	14.1
40°-50°	911.1	14.1
50°-60°	796.9	12.3
60°-70°	591.6	9.1
70°-80°	335.7	5.2
80°-90°	96.8	1.5
90°-100°	135.1	2.1
100°-110°	274.7	4.2
110°-120°	244.9	3.8
120°-130°	205.7	3.2
130°-140°	171.6	2.7
140°-150°	131.1	2.0
150°-160°	92.1	1.4
160°-170°	54.2	0.8
170°-180°	17.6	0.3
0°-30°	1505.5	23.2
0°-40°	2416.7	37.3
0°-60°	4124.6	63.7
0°-90°	5148.7	79.5
90°-120°	654.6	10.1
90°-150°	1163.0	18.0
90°-180°	1327.0	20.5
0°-180°	6475.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2006	2006	2006	2006	2006	
5°	2004	1998	1980	1998	1994	190
15°	1908	1901	1877	1887	1882	538
25°	1728	1716	1694	1696	1689	795
35°	1487	1475	1453	1442	1434	930
45°	1213	1202	1176	1159	1154	935
55°	918	913	890	871	861	822
65°	622	614	598	582	574	616
75°	331	323	315	309	307	351
85°	87	87	84	84	82	93
90°	0	3	6	7	8	7
95°	12	37	291	144	87	13
105°	42	61	234	505	503	45
115°	74	92	209	402	483	73
125°	102	122	208	342	385	91
135°	122	145	206	303	344	94
145°	140	161	205	256	281	88
155°	160	172	199	226	235	74
165°	174	179	191	202	205	49
175°	182	182	183	186	185	17
180°	182	182	182	182	182	

TEST NUMBER: P1000964

CATALOG NUMBER: SA4XXDIP-B1195D365UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2005.7	2005.7	2005.7	2005.7	2005.7
2.5°	2012.1	2007.3	1989.6	2005.7	2004.1
5°	2004.1	1997.7	1980.0	1997.7	1994.4
7.5°	1989.6	1983.2	1963.9	1978.4	1976.8
10°	1968.7	1962.3	1941.4	1954.3	1951.1
12.5°	1941.4	1935.0	1912.5	1926.9	1922.1
15°	1907.7	1901.2	1877.1	1886.8	1881.9
17.5°	1869.1	1861.1	1838.6	1845.0	1841.8
20°	1825.7	1817.7	1793.6	1798.4	1795.2
22.5°	1779.1	1767.8	1743.7	1753.4	1746.9
25°	1727.7	1716.4	1693.9	1695.5	1689.1
27.5°	1669.8	1658.6	1637.7	1634.4	1626.4
30°	1611.9	1599.1	1578.2	1571.8	1563.7
32.5°	1550.9	1539.6	1517.1	1509.1	1501.1
35°	1486.6	1475.3	1452.8	1441.6	1433.6
37.5°	1419.1	1409.4	1385.3	1374.1	1362.8
40°	1353.2	1340.3	1316.2	1300.2	1292.1
42.5°	1282.5	1276.1	1248.7	1229.5	1224.6
45°	1213.4	1202.1	1176.4	1158.7	1153.9
47.5°	1141.1	1133.0	1108.9	1089.6	1076.8
50°	1067.1	1060.7	1038.2	1015.7	1006.1
52.5°	994.8	986.8	962.7	943.4	930.5
55°	917.7	912.8	890.3	871.1	861.4
57.5°	845.3	840.5	818.0	798.7	789.1
60°	769.8	761.8	740.9	726.4	718.4
62.5°	695.9	689.5	667.0	654.1	646.1
65°	622.0	613.9	597.9	581.8	573.7
67.5°	546.4	540.0	523.9	507.9	506.2
70°	477.3	466.1	453.2	440.4	435.5
72.5°	403.4	392.1	382.5	372.9	368.0
75°	331.1	323.0	315.0	308.6	307.0
77.5°	260.4	257.1	249.1	247.5	242.7
80°	197.7	192.9	189.6	186.4	184.8
82.5°	136.6	135.0	135.0	133.4	131.8
85°	86.8	86.8	83.6	83.6	82.0
87.5°	41.8	40.2	38.6	38.6	38.6
90°	0.4	2.9	6.4	7.1	7.5
92.5°	5.0	27.5	140.0	46.2	32.5
95°	11.8	37.2	291.1	144.2	87.2
97.5°	19.6	41.1	311.5	294.4	209.3
100°	27.1	46.4	287.2	407.2	327.6
102.5°	34.3	52.8	256.8	478.0	430.5
105°	41.8	60.6	234.3	504.6	502.6
107.5°	50.0	68.4	219.7	496.5	536.9
110°	58.2	76.2	212.9	468.0	537.6

TEST NUMBER: P1000964

CATALOG NUMBER: SA4XXDIP-B1195D365UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	66.1	84.1	209.7	433.0	516.5
115°	73.6	92.4	209.0	401.5	482.6
117.5°	81.4	100.0	208.6	376.9	449.4
120°	89.3	107.5	208.6	360.2	422.2
122.5°	96.4	114.8	208.3	349.4	400.8
125°	102.5	121.8	207.9	341.7	385.1
127.5°	108.2	128.2	207.2	334.4	375.1
130°	112.9	134.5	206.8	325.6	366.5
132.5°	117.5	139.8	206.5	315.2	356.9
135°	121.8	145.0	206.1	303.3	344.4
137.5°	126.1	149.5	206.1	290.4	329.7
140°	130.7	153.6	205.8	277.9	313.6
142.5°	135.7	157.4	205.8	266.4	296.5
145°	140.4	160.8	205.0	255.8	281.1
147.5°	145.7	164.0	204.0	247.0	266.8
150°	150.7	167.0	202.9	239.0	255.1
152.5°	155.4	169.9	201.1	232.2	244.3
155°	159.7	172.4	199.3	225.8	235.4
157.5°	164.0	174.6	197.5	219.7	227.2
160°	167.9	176.6	195.4	213.6	219.7
162.5°	171.5	178.2	193.3	207.8	212.5
165°	174.0	179.4	191.1	202.4	205.4
167.5°	176.8	180.2	189.0	197.8	199.7
170°	178.6	181.0	186.8	193.0	194.3
172.5°	180.4	181.4	184.7	189.0	189.0
175°	181.5	181.8	183.3	185.8	185.0
177.5°	182.2	181.8	182.2	183.4	182.2
180°	181.8	181.8	181.8	181.8	181.8

(END OF REPORT)