

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000990

Luminaire Tested: SA4XXDIP-B1195D590UB27-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000990
REPORT IS A COMBINATION OF REPORTS P995606 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B1195D590UB27-4F0-XX-W2A-F1
Description: Define 4 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7116.0 lumens
Efficiency: N/A
Efficacy: 92.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 76.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000990

CATALOG NUMBER: SA4XXDIP-B1195D590UB27-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1000990

CATALOG NUMBER: SA4XXDIP-B1195D590UB27-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	76	76	76
1	103	98	94	90	97	93	89	86	84	81	78	75	73	71	67	65	64
2	93	86	79	74	88	81	76	71	73	69	65	66	62	59	59	56	54
3	85	75	68	62	80	72	65	59	65	59	55	58	54	50	52	49	46
4	78	67	59	52	74	64	56	50	58	51	47	52	47	43	47	43	40
5	72	60	51	45	68	57	49	43	52	45	40	47	41	37	42	38	35
6	66	54	45	39	63	51	43	38	47	40	35	42	37	33	38	34	30
7	61	49	40	35	58	46	39	33	42	36	31	39	33	29	35	30	27
8	57	44	36	31	54	42	35	30	39	32	28	35	30	26	32	28	24
9	53	41	33	27	50	39	32	27	36	29	25	33	27	24	30	25	22
10	50	37	30	25	47	36	29	24	33	27	23	30	25	21	28	23	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16146	16146	16146
5°	16159	15681	15700
10°	16022	15246	15139
15°	15792	14729	14506
20°	15499	14169	13850
25°	15168	13577	13145
30°	14770	12938	12371
35°	14357	12282	11622
40°	13928	11578	10826
45°	13476	10871	10081
50°	12977	10186	9257
55°	12435	9386	8438
60°	11879	8510	7585
65°	11244	7605	6624
70°	10512	6515	5593
75°	9418	5252	4480
80°	8024	3797	3151
85°	6236	2114	1696

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13476 cd/sqm

TEST NUMBER: P1000990

CATALOG NUMBER: SA4XXDIP-B1195D590UB27-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	186.6	2.6
10°-20°	525.8	7.4
20°-30°	773.8	10.9
30°-40°	899.5	12.6
40°-50°	899.4	12.6
50°-60°	786.6	11.1
60°-70°	584.0	8.2
70°-80°	331.4	4.7
80°-90°	96.5	1.4
90°-100°	47.7	0.7
100°-110°	143.0	2.0
110°-120°	242.9	3.4
120°-130°	320.4	4.5
130°-140°	359.9	5.1
140°-150°	353.7	5.0
150°-160°	297.5	4.2
160°-170°	197.9	2.8
170°-180°	69.3	1.0
0°-30°	1486.2	20.9
0°-40°	2385.7	33.5
0°-60°	4071.7	57.2
0°-90°	5083.6	71.4
90°-120°	433.7	6.1
90°-150°	1467.7	20.6
90°-180°	2032.0	28.6
0°-180°	7116.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1980	1980	1980	1980	1980	
5°	1978	1972	1955	1972	1969	188
15°	1883	1877	1853	1863	1858	531
25°	1706	1694	1672	1674	1667	785
35°	1468	1456	1434	1423	1415	918
45°	1198	1187	1161	1144	1139	923
55°	906	901	879	860	850	811
65°	614	606	590	574	566	608
75°	327	319	311	305	303	347
85°	86	86	82	82	81	92
90°	2	8	12	16	17	8
95°	34	39	43	45	45	37
105°	132	133	135	136	138	140
115°	247	247	246	245	245	244
125°	360	360	359	358	357	321
135°	464	467	467	466	464	359
145°	564	566	566	566	564	353
155°	646	646	645	648	645	297
165°	703	701	700	704	701	198
175°	731	728	728	732	728	69
180°	732	732	732	732	732	

TEST NUMBER: P1000990

CATALOG NUMBER: SA4XXDIP-B1195D590UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1980.0	1980.0	1980.0	1980.0	1980.0
2.5°	1986.3	1981.6	1964.1	1980.0	1978.4
5°	1978.4	1972.0	1954.6	1972.0	1968.9
7.5°	1964.1	1957.8	1938.7	1953.0	1951.4
10°	1943.5	1937.1	1916.5	1929.2	1926.0
12.5°	1916.5	1910.2	1888.0	1902.2	1897.5
15°	1883.2	1876.9	1853.1	1862.6	1857.8
17.5°	1845.1	1837.2	1815.0	1821.3	1818.2
20°	1802.3	1794.4	1770.6	1775.3	1772.1
22.5°	1756.3	1745.2	1721.4	1730.9	1724.5
25°	1705.5	1694.4	1672.2	1673.8	1667.4
27.5°	1648.4	1637.3	1616.7	1613.5	1605.6
30°	1591.3	1578.6	1558.0	1551.6	1543.7
32.5°	1531.0	1519.9	1497.7	1489.7	1481.8
35°	1467.5	1456.4	1434.2	1423.1	1415.2
37.5°	1400.9	1391.4	1367.6	1356.5	1345.4
40°	1335.9	1323.2	1299.4	1283.5	1275.6
42.5°	1266.0	1259.7	1232.7	1213.7	1208.9
45°	1197.8	1186.7	1161.3	1143.9	1139.1
47.5°	1126.4	1118.5	1094.7	1075.7	1063.0
50°	1053.4	1047.1	1024.9	1002.7	993.2
52.5°	982.1	974.1	950.3	931.3	918.6
55°	905.9	901.1	878.9	859.9	850.4
57.5°	834.5	829.8	807.5	788.5	779.0
60°	759.9	752.0	731.4	717.1	709.2
62.5°	687.0	680.6	658.4	645.7	637.8
65°	614.0	606.1	590.2	574.3	566.4
67.5°	539.4	533.1	517.2	501.3	499.8
70°	471.2	460.1	447.4	434.7	429.9
72.5°	398.2	387.1	377.6	368.1	363.3
75°	326.8	318.9	311.0	304.6	303.0
77.5°	257.0	253.8	245.9	244.3	239.6
80°	195.1	190.4	187.2	184.0	182.4
82.5°	134.9	133.3	133.3	131.7	130.1
85°	85.7	85.7	82.5	82.5	80.9
87.5°	41.2	39.7	38.1	38.1	38.1
90°	1.7	7.9	12.5	15.9	17.0
92.5°	14.7	22.1	24.9	26.6	27.2
95°	34.0	39.1	43.1	44.8	44.8
97.5°	54.4	58.9	63.4	65.7	65.7
100°	79.3	81.6	86.7	87.8	87.8
102.5°	105.4	105.9	110.5	112.2	112.7
105°	132.0	132.6	134.8	136.5	138.2
107.5°	159.8	160.3	160.9	163.2	162.6
110°	188.1	189.2	188.6	187.5	189.2

TEST NUMBER: P1000990

CATALOG NUMBER: SA4XXDIP-B1195D590UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	217.5	217.5	216.4	216.4	216.4
115°	247.0	247.0	245.9	245.3	244.7
117.5°	274.8	274.8	274.2	272.5	270.8
120°	302.5	304.8	303.1	300.3	301.4
122.5°	331.4	332.0	331.4	329.7	326.9
125°	359.7	359.7	359.2	358.0	356.9
127.5°	385.2	386.9	385.8	384.7	384.1
130°	412.4	414.1	414.1	413.0	410.7
132.5°	440.2	441.3	440.7	439.6	439.1
135°	464.0	467.4	467.4	466.2	464.5
137.5°	490.6	492.3	493.4	491.7	492.3
140°	517.2	518.4	518.4	517.8	517.2
142.5°	541.6	542.7	542.2	542.2	542.2
145°	563.7	565.9	566.5	565.9	564.3
147.5°	586.3	589.2	588.6	588.0	587.5
150°	606.7	609.0	609.0	609.0	608.4
152.5°	626.0	627.1	627.7	629.4	627.7
155°	645.8	645.8	645.3	647.5	645.3
157.5°	662.8	661.7	661.7	663.4	661.7
160°	677.6	677.0	676.4	678.1	675.3
162.5°	691.2	689.5	688.9	692.3	689.5
165°	703.0	701.3	700.2	703.6	701.3
167.5°	712.7	710.4	710.4	713.8	710.4
170°	720.6	717.8	718.3	721.7	717.8
172.5°	726.3	724.0	724.0	728.0	724.0
175°	731.4	728.5	728.0	731.9	728.0
177.5°	733.6	730.8	730.8	734.8	730.2
180°	732.5	732.5	732.5	732.5	732.5

(END OF REPORT)