

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001041

Luminaire Tested: SA4XXDIP-B1195D590UB50-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001041
REPORT IS A COMBINATION OF REPORTS P995657 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B1195D590UB50-4F0-XX-W2A-F1
Description: Define 4 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6902.0 lumens
Efficiency: N/A
Efficacy: 90.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 76.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001041

CATALOG NUMBER: SA4XXDIP-B1195D590UB50-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1001041

CATALOG NUMBER: SA4XXDIP-B1195D590UB50-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	76	76	76
1	103	98	94	90	97	93	89	86	84	81	78	75	73	71	67	65	64
2	93	86	79	74	88	81	76	71	73	69	65	66	62	59	59	56	54
3	85	75	68	62	80	72	65	59	65	59	55	58	54	50	52	49	46
4	78	67	59	52	74	64	56	50	58	51	47	52	47	43	47	43	40
5	72	60	51	45	68	57	49	43	52	45	40	47	41	37	42	38	35
6	66	54	45	39	63	51	43	38	47	40	35	42	37	33	38	34	30
7	61	49	40	35	58	46	39	33	42	36	31	39	33	29	35	30	27
8	57	44	36	31	54	42	35	30	39	32	28	35	30	26	32	28	24
9	53	41	33	27	50	39	32	27	36	29	25	33	27	24	30	25	22
10	50	37	30	25	47	36	29	24	33	27	23	30	25	21	28	23	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15660	15660	15660
5°	15672	15209	15228
10°	15540	14787	14684
15°	15317	14285	14069
20°	15032	13742	13434
25°	14712	13168	12749
30°	14326	12548	11998
35°	13926	11912	11272
40°	13508	11229	10500
45°	13071	10544	9778
50°	12586	9879	8978
55°	12060	9104	8184
60°	11522	8254	7356
65°	10906	7376	6424
70°	10196	6318	5425
75°	9135	5093	4345
80°	7786	3683	3057
85°	6047	2050	1645

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13071 cd/sqm

TEST NUMBER: P1001041

CATALOG NUMBER: SA4XXDIP-B1195D590UB50-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	181.0	2.6
10°-20°	509.9	7.4
20°-30°	750.5	10.9
30°-40°	872.4	12.6
40°-50°	872.3	12.6
50°-60°	763.0	11.1
60°-70°	566.4	8.2
70°-80°	321.4	4.7
80°-90°	93.6	1.4
90°-100°	46.3	0.7
100°-110°	138.7	2.0
110°-120°	235.6	3.4
120°-130°	310.8	4.5
130°-140°	349.1	5.1
140°-150°	343.1	5.0
150°-160°	288.6	4.2
160°-170°	192.0	2.8
170°-180°	67.2	1.0
0°-30°	1441.4	20.9
0°-40°	2313.8	33.5
0°-60°	3949.1	57.2
0°-90°	4930.5	71.4
90°-120°	420.7	6.1
90°-150°	1423.7	20.6
90°-180°	1971.0	28.6
0°-180°	6902.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1920	1920	1920	1920	1920	
5°	1919	1913	1896	1913	1910	182
15°	1826	1820	1797	1806	1802	515
25°	1654	1643	1622	1623	1617	761
35°	1423	1413	1391	1380	1373	890
45°	1162	1151	1126	1109	1105	896
55°	879	874	852	834	825	787
65°	596	588	572	557	549	589
75°	317	309	302	295	294	336
85°	83	83	80	80	78	89
90°	2	8	12	15	16	8
95°	33	38	42	43	43	36
105°	128	129	131	132	134	136
115°	240	240	238	238	237	236
125°	349	349	348	347	346	311
135°	450	453	453	452	451	348
145°	547	549	550	549	547	342
155°	626	626	626	628	626	288
165°	682	680	679	682	680	192
175°	709	707	706	710	706	67
180°	710	710	710	710	710	

TEST NUMBER: P1001041

CATALOG NUMBER: SA4XXDIP-B1195D590UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1920.4	1920.4	1920.4	1920.4	1920.4
2.5°	1926.5	1921.9	1905.0	1920.4	1918.8
5°	1918.8	1912.7	1895.7	1912.7	1909.6
7.5°	1905.0	1898.8	1880.4	1894.2	1892.7
10°	1885.0	1878.8	1858.8	1871.1	1868.1
12.5°	1858.8	1852.7	1831.1	1845.0	1840.4
15°	1826.5	1820.3	1797.3	1806.5	1801.9
17.5°	1789.6	1781.9	1760.3	1766.5	1763.4
20°	1748.0	1740.3	1717.3	1721.9	1718.8
22.5°	1703.4	1692.6	1669.6	1678.8	1672.6
25°	1654.2	1643.4	1621.8	1623.4	1617.2
27.5°	1598.8	1588.0	1568.0	1564.9	1557.2
30°	1543.4	1531.1	1511.1	1504.9	1497.2
32.5°	1484.9	1474.1	1452.6	1444.9	1437.2
35°	1423.4	1412.6	1391.0	1380.3	1372.6
37.5°	1358.7	1349.5	1326.4	1315.6	1304.9
40°	1295.6	1283.3	1260.2	1244.9	1237.2
42.5°	1227.9	1221.8	1195.6	1177.1	1172.5
45°	1161.8	1151.0	1126.4	1109.4	1104.8
47.5°	1092.5	1084.8	1061.7	1043.3	1031.0
50°	1021.7	1015.6	994.0	972.5	963.3
52.5°	952.5	944.8	921.7	903.3	890.9
55°	878.6	874.0	852.5	834.0	824.8
57.5°	809.4	804.8	783.2	764.8	755.5
60°	737.1	729.4	709.4	695.5	687.8
62.5°	666.3	660.1	638.6	626.3	618.6
65°	595.5	587.8	572.4	557.0	549.3
67.5°	523.2	517.0	501.6	486.2	484.7
70°	457.0	446.2	433.9	421.6	417.0
72.5°	386.2	375.5	366.2	357.0	352.4
75°	317.0	309.3	301.6	295.4	293.9
77.5°	249.3	246.2	238.5	237.0	232.4
80°	189.3	184.7	181.6	178.5	177.0
82.5°	130.8	129.3	129.3	127.7	126.2
85°	83.1	83.1	80.0	80.0	78.5
87.5°	40.0	38.5	36.9	36.9	36.9
90°	1.6	7.7	12.1	15.4	16.5
92.5°	14.3	21.4	24.2	25.8	26.4
95°	33.0	37.9	41.8	43.4	43.4
97.5°	52.8	57.2	61.5	63.7	63.7
100°	76.9	79.1	84.1	85.2	85.2
102.5°	102.2	102.8	107.2	108.8	109.4
105°	128.0	128.6	130.8	132.4	134.1
107.5°	155.0	155.5	156.1	158.3	157.7
110°	182.4	183.5	183.0	181.9	183.5



TEST NUMBER: P1001041

CATALOG NUMBER: SA4XXDIP-B1195D590UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	211.0	211.0	209.9	209.9	209.9
115°	239.6	239.6	238.5	237.9	237.4
117.5°	266.5	266.5	266.0	264.3	262.7
120°	293.4	295.6	294.0	291.2	292.3
122.5°	321.5	322.0	321.5	319.8	317.1
125°	348.9	348.9	348.4	347.3	346.2
127.5°	373.7	375.3	374.2	373.1	372.6
130°	400.1	401.7	401.7	400.6	398.4
132.5°	427.0	428.1	427.5	426.4	425.9
135°	450.1	453.4	453.4	452.3	450.6
137.5°	475.9	477.5	478.6	477.0	477.5
140°	501.7	502.8	502.8	502.3	501.7
142.5°	525.3	526.4	525.9	525.9	525.9
145°	546.8	549.0	549.5	549.0	547.3
147.5°	568.8	571.5	571.0	570.4	569.9
150°	588.5	590.7	590.7	590.7	590.2
152.5°	607.2	608.3	608.9	610.5	608.9
155°	626.5	626.5	625.9	628.1	625.9
157.5°	642.9	641.8	641.8	643.5	641.8
160°	657.2	656.7	656.1	657.8	655.0
162.5°	670.4	668.8	668.2	671.5	668.8
165°	682.0	680.3	679.2	682.5	680.3
167.5°	691.3	689.1	689.1	692.4	689.1
170°	699.0	696.3	696.8	700.1	696.3
172.5°	704.5	702.3	702.3	706.1	702.3
175°	709.4	706.7	706.1	710.0	706.1
177.5°	711.6	708.9	708.9	712.7	708.3
180°	710.5	710.5	710.5	710.5	710.5

(END OF REPORT)