

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000820

Luminaire Tested: SA4XXDIP-B1195D1035UB2750-4F0-XX-W2A-D_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000820
REPORT IS A COMBINATION OF REPORTS P995433 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B1195D1035UB2750-4F0-XX-W2A-D_2700K
Description: Define 4 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8887.0 lumens
Efficiency: N/A
Efficacy: 99.0 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 89.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000820

CATALOG NUMBER: SA4XXDIP-B1195D1035UB2750-4F0-XX-W2A-D_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1000820

CATALOG NUMBER: SA4XXDIP-B1195D1035UB2750-4F0-XX-W2A-D_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	56	56	56
1	97	92	88	84	89	85	81	78	72	69	66	59	58	56	48	47	46	46	46	40
2	88	80	73	68	81	74	68	63	62	58	54	52	48	46	42	40	38	38	38	33
3	80	70	62	56	73	64	58	52	54	49	45	45	41	38	37	34	32	32	32	27
4	73	62	53	47	67	57	50	44	48	43	38	40	36	32	33	29	27	27	27	23
5	67	55	46	40	61	51	43	37	43	37	33	36	31	28	29	26	23	23	23	20
6	61	49	41	34	56	45	38	32	39	33	28	32	28	24	26	23	20	20	20	17
7	57	44	36	30	52	41	34	28	35	29	25	29	25	21	24	21	18	18	18	15
8	53	40	32	27	48	37	30	25	32	26	22	27	22	19	22	19	16	16	16	14
9	49	36	29	24	45	34	27	22	29	23	20	25	20	17	20	17	14	14	14	12
10	46	33	26	21	42	31	24	20	27	21	18	23	18	15	19	15	13	13	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11555	11555	11555
5°	11586	11254	11274
10°	11511	11032	11000
15°	11403	10783	10692
20°	11244	10513	10393
25°	11064	10216	10070
30°	10869	9922	9740
35°	10649	9621	9447
40°	10472	9331	9144
45°	10211	9060	8875
50°	9988	8752	8592
55°	9758	8456	8266
60°	9401	8086	7959
65°	9008	7688	7590
70°	8531	7233	7163
75°	7864	6726	6757
80°	7115	6210	6331
85°	6120	5691	5986

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10211 cd/sqm

TEST NUMBER: P1000820

CATALOG NUMBER: SA4XXDIP-B1195D1035UB2750-4F0-XX-W2A-D_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	134.3	1.5
10°-20°	384.7	4.3
20°-30°	581.6	6.5
30°-40°	703.7	7.9
40°-50°	743.9	8.4
50°-60°	700.1	7.9
60°-70°	581.0	6.5
70°-80°	407.7	4.6
80°-90°	232.5	2.6
90°-100°	180.3	2.0
100°-110°	387.7	4.4
110°-120°	614.8	6.9
120°-130°	732.5	8.2
130°-140°	759.2	8.5
140°-150°	697.6	7.9
150°-160°	560.0	6.3
160°-170°	361.1	4.1
170°-180°	124.5	1.4
0°-30°	1100.6	12.4
0°-40°	1804.2	20.3
0°-60°	3248.2	36.6
0°-90°	4469.4	50.3
90°-120°	1182.8	13.3
90°-150°	3372.0	37.9
90°-180°	4418.0	49.7
0°-180°	8887.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1417	1417	1417	1417	1417	
5°	1418	1414	1403	1415	1414	135
15°	1360	1361	1357	1371	1369	383
25°	1244	1254	1258	1276	1277	573
35°	1088	1108	1123	1146	1150	682
45°	908	938	968	995	1003	701
55°	711	744	792	824	833	633
65°	492	543	597	636	649	488
75°	273	332	398	443	457	290
85°	84	151	222	270	286	88
90°	28	103	179	230	245	20
95°	74	94	160	208	224	83
105°	309	347	410	459	436	325
115°	560	577	627	664	675	552
125°	780	783	820	854	864	697
135°	963	962	977	1005	1016	743
145°	1109	1110	1110	1120	1129	693
155°	1214	1215	1212	1216	1213	560
165°	1280	1276	1276	1283	1275	362
175°	1310	1304	1305	1314	1302	125
180°	1310	1310	1310	1310	1310	

TEST NUMBER: P1000820

CATALOG NUMBER: SA4XXDIP-B1195D1035UB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1417.0	1417.0	1417.0	1417.0	1417.0
2.5°	1423.3	1418.5	1405.9	1417.0	1415.4
5°	1418.5	1413.8	1402.7	1415.4	1413.8
7.5°	1409.0	1405.9	1396.3	1410.6	1409.0
10°	1396.3	1394.7	1386.8	1401.1	1399.5
12.5°	1378.9	1378.9	1374.1	1386.8	1386.8
15°	1359.8	1361.4	1356.7	1370.9	1369.4
17.5°	1334.5	1339.2	1337.6	1351.9	1350.3
20°	1307.5	1312.2	1313.8	1329.7	1329.7
22.5°	1277.3	1283.7	1286.8	1302.7	1305.9
25°	1244.0	1253.5	1258.3	1275.7	1277.3
27.5°	1207.5	1221.8	1228.1	1244.0	1245.6
30°	1171.0	1183.7	1194.8	1212.3	1215.4
32.5°	1131.3	1147.2	1159.9	1180.5	1183.7
35°	1088.5	1107.5	1123.4	1145.6	1150.4
37.5°	1045.7	1067.9	1086.9	1109.1	1113.9
40°	1004.4	1025.0	1047.2	1071.1	1077.4
42.5°	956.8	980.6	1007.6	1034.6	1039.3
45°	907.6	937.8	967.9	994.9	1002.8
47.5°	861.6	891.7	926.7	953.6	963.2
50°	810.8	845.7	880.6	912.4	921.9
52.5°	760.0	795.0	836.2	867.9	877.5
55°	710.9	744.2	791.8	823.5	833.0
57.5°	655.3	696.6	742.6	780.7	788.6
60°	601.4	642.6	695.0	731.5	744.2
62.5°	549.0	595.0	647.4	683.9	696.6
65°	491.9	542.7	596.6	636.3	649.0
67.5°	437.9	491.9	549.0	588.7	601.4
70°	382.4	436.4	496.7	539.5	550.6
72.5°	328.5	384.0	449.0	490.3	503.0
75°	272.9	331.6	398.3	442.7	457.0
77.5°	220.6	282.4	352.3	396.7	412.6
80°	173.0	236.4	306.2	353.8	366.5
82.5°	125.4	192.0	261.8	311.0	325.3
85°	84.1	150.7	222.1	269.7	285.6
87.5°	52.4	117.4	187.2	233.3	247.5
90°	28.3	102.6	178.7	230.5	245.2
92.5°	38.5	92.0	168.2	218.5	231.2
95°	74.5	93.6	159.6	208.3	223.6
97.5°	121.9	189.5	151.7	197.9	213.0
100°	178.2	237.0	163.7	189.9	201.9
102.5°	242.8	289.5	361.6	182.3	195.0
105°	309.2	346.8	410.4	458.9	436.3
107.5°	372.9	402.8	465.2	509.8	524.8
110°	435.9	461.1	522.5	560.9	576.6

TEST NUMBER: P1000820

CATALOG NUMBER: SA4XXDIP-B1195D1035UB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	497.0	521.9	576.3	610.2	626.8
115°	560.1	577.3	627.2	664.0	675.1
117.5°	617.9	631.3	681.9	714.3	727.0
120°	675.1	683.8	728.8	762.5	773.2
122.5°	730.0	731.9	776.8	809.5	818.6
125°	780.3	782.7	820.3	853.5	864.0
127.5°	830.3	829.7	866.3	894.0	904.1
130°	876.8	876.1	904.5	934.0	943.5
132.5°	920.8	921.2	944.1	972.1	980.6
135°	963.3	962.4	977.4	1004.7	1016.2
137.5°	1002.5	1000.9	1012.1	1037.9	1044.9
140°	1040.7	1041.1	1044.7	1068.2	1077.1
142.5°	1073.4	1077.3	1076.7	1096.2	1102.5
145°	1108.7	1110.0	1110.0	1120.5	1128.9
147.5°	1136.1	1140.4	1139.4	1142.0	1149.3
150°	1166.5	1168.8	1167.8	1167.8	1168.8
152.5°	1190.4	1193.3	1191.4	1193.3	1192.3
155°	1213.9	1214.9	1211.9	1215.8	1212.9
157.5°	1234.5	1234.5	1230.5	1235.4	1230.5
160°	1252.1	1249.2	1248.2	1254.1	1248.2
162.5°	1267.8	1263.9	1262.9	1268.8	1261.9
165°	1280.5	1275.6	1275.6	1283.4	1274.6
167.5°	1291.3	1286.4	1285.4	1294.2	1284.4
170°	1300.1	1294.2	1295.2	1303.0	1293.2
172.5°	1306.0	1300.1	1301.1	1308.9	1298.1
175°	1309.9	1304.0	1305.0	1313.8	1302.1
177.5°	1312.8	1306.0	1307.9	1315.8	1304.0
180°	1309.9	1309.9	1309.9	1309.9	1309.9

(END OF REPORT)