

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001083

Luminaire Tested: SA4XXDIP-B1195D810UB35-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001083
REPORT IS A COMBINATION OF REPORTS P995699 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B1195D810UB35-4F0-XX-W2A-F1
Description: Define 4 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7901.0 lumens
Efficiency: N/A
Efficacy: 95.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 82.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001083

CATALOG NUMBER: SA4XXDIP-B1195D810UB35-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1001083

CATALOG NUMBER: SA4XXDIP-B1195D810UB35-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	104	104	104	104	92	92	92	80	80	80	70	70	70
1	101	97	93	89	95	91	88	84	81	78	75	71	69	67	62	60	59
2	92	84	78	73	86	80	74	69	71	66	62	62	59	56	54	52	50
3	84	74	67	61	79	70	63	58	62	57	53	55	51	47	48	45	42
4	77	66	58	51	72	62	55	49	55	50	45	49	44	41	43	40	37
5	71	59	50	44	66	56	48	42	50	43	39	44	39	35	39	35	32
6	65	53	44	38	61	50	42	37	45	39	34	40	35	31	35	31	28
7	60	48	40	34	57	45	38	33	41	34	30	36	31	27	32	28	25
8	56	43	35	30	53	41	34	29	37	31	27	33	28	25	30	26	22
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	27	23	20
10	49	37	29	24	46	35	28	23	32	26	22	28	24	20	25	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16355	16355	16355
5°	16369	15885	15904
10°	16230	15444	15336
15°	15998	14919	14694
20°	15700	14353	14031
25°	15366	13753	13316
30°	14962	13105	12531
35°	14544	12442	11773
40°	14109	11728	10966
45°	13652	11012	10212
50°	13146	10318	9377
55°	12597	9508	8547
60°	12034	8620	7684
65°	11391	7704	6709
70°	10648	6599	5666
75°	9542	5320	4539
80°	8131	3845	3192
85°	6316	2142	1719

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13652 cd/sqm

TEST NUMBER: P1001083

CATALOG NUMBER: SA4XXDIP-B1195D810UB35-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	189.0	2.4
10°-20°	532.6	6.7
20°-30°	783.8	9.9
30°-40°	911.2	11.5
40°-50°	911.1	11.5
50°-60°	796.9	10.1
60°-70°	591.6	7.5
70°-80°	335.7	4.2
80°-90°	98.3	1.2
90°-100°	64.6	0.8
100°-110°	193.6	2.4
110°-120°	328.8	4.2
120°-130°	433.7	5.5
130°-140°	487.1	6.2
140°-150°	478.7	6.1
150°-160°	402.7	5.1
160°-170°	267.9	3.4
170°-180°	93.8	1.2
0°-30°	1505.5	19.1
0°-40°	2416.7	30.6
0°-60°	4124.6	52.2
0°-90°	5150.1	65.2
90°-120°	587.0	7.4
90°-150°	1986.5	25.1
90°-180°	2751.0	34.8
0°-180°	7901.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2006	2006	2006	2006	2006	
5°	2004	1998	1980	1998	1994	190
15°	1908	1901	1877	1887	1882	538
25°	1728	1716	1694	1696	1689	795
35°	1487	1475	1453	1442	1434	930
45°	1213	1202	1176	1159	1154	935
55°	918	913	890	871	861	822
65°	622	614	598	582	574	616
75°	331	323	315	309	307	351
85°	87	87	84	84	82	93
90°	2	11	17	22	23	9
95°	46	53	58	61	61	50
105°	179	179	182	185	187	189
115°	334	334	333	332	331	330
125°	487	487	486	485	483	434
135°	628	633	633	631	629	486
145°	763	766	767	766	764	478
155°	874	874	873	876	873	402
165°	952	949	948	952	949	268
175°	990	986	985	991	985	94
180°	991	991	991	991	991	

TEST NUMBER: P1001083

CATALOG NUMBER: SA4XXDIP-B1195D810UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2005.7	2005.7	2005.7	2005.7	2005.7
2.5°	2012.1	2007.3	1989.6	2005.7	2004.1
5°	2004.1	1997.7	1980.0	1997.7	1994.4
7.5°	1989.6	1983.2	1963.9	1978.4	1976.8
10°	1968.7	1962.3	1941.4	1954.3	1951.1
12.5°	1941.4	1935.0	1912.5	1926.9	1922.1
15°	1907.7	1901.2	1877.1	1886.8	1881.9
17.5°	1869.1	1861.1	1838.6	1845.0	1841.8
20°	1825.7	1817.7	1793.6	1798.4	1795.2
22.5°	1779.1	1767.8	1743.7	1753.4	1746.9
25°	1727.7	1716.4	1693.9	1695.5	1689.1
27.5°	1669.8	1658.6	1637.7	1634.4	1626.4
30°	1611.9	1599.1	1578.2	1571.8	1563.7
32.5°	1550.9	1539.6	1517.1	1509.1	1501.1
35°	1486.6	1475.3	1452.8	1441.6	1433.6
37.5°	1419.1	1409.4	1385.3	1374.1	1362.8
40°	1353.2	1340.3	1316.2	1300.2	1292.1
42.5°	1282.5	1276.1	1248.7	1229.5	1224.6
45°	1213.4	1202.1	1176.4	1158.7	1153.9
47.5°	1141.1	1133.0	1108.9	1089.6	1076.8
50°	1067.1	1060.7	1038.2	1015.7	1006.1
52.5°	994.8	986.8	962.7	943.4	930.5
55°	917.7	912.8	890.3	871.1	861.4
57.5°	845.3	840.5	818.0	798.7	789.1
60°	769.8	761.8	740.9	726.4	718.4
62.5°	695.9	689.5	667.0	654.1	646.1
65°	622.0	613.9	597.9	581.8	573.7
67.5°	546.4	540.0	523.9	507.9	506.2
70°	477.3	466.1	453.2	440.4	435.5
72.5°	403.4	392.1	382.5	372.9	368.0
75°	331.1	323.0	315.0	308.6	307.0
77.5°	260.4	257.1	249.1	247.5	242.7
80°	197.7	192.9	189.6	186.4	184.8
82.5°	136.6	135.0	135.0	133.4	131.8
85°	86.8	86.8	83.6	83.6	82.0
87.5°	41.8	40.2	38.6	38.6	38.6
90°	2.3	10.7	16.9	21.5	23.0
92.5°	19.9	29.9	33.7	36.0	36.8
95°	46.0	52.9	58.3	60.6	60.6
97.5°	73.6	79.7	85.9	88.9	88.9
100°	107.3	110.4	117.3	118.9	118.9
102.5°	142.6	143.4	149.5	151.8	152.6
105°	178.7	179.4	182.5	184.8	187.1
107.5°	216.2	217.0	217.8	220.8	220.1
110°	254.6	256.1	255.3	253.8	256.1

TEST NUMBER: P1001083

CATALOG NUMBER: SA4XXDIP-B1195D810UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	294.4	294.4	292.9	292.9	292.9
115°	334.3	334.3	332.8	332.0	331.2
117.5°	371.9	371.9	371.1	368.8	366.5
120°	409.5	412.5	410.2	406.4	407.9
122.5°	448.6	449.3	448.6	446.3	442.4
125°	486.9	486.9	486.1	484.6	483.1
127.5°	521.4	523.7	522.2	520.6	519.9
130°	558.2	560.5	560.5	559.0	555.9
132.5°	595.8	597.3	596.6	595.0	594.3
135°	628.0	632.6	632.6	631.1	628.8
137.5°	664.0	666.3	667.9	665.6	666.3
140°	700.1	701.6	701.6	700.8	700.1
142.5°	733.0	734.6	733.8	733.8	733.8
145°	762.9	766.0	766.8	766.0	763.7
147.5°	793.6	797.4	796.7	795.9	795.1
150°	821.2	824.3	824.3	824.3	823.5
152.5°	847.3	848.8	849.6	851.9	849.6
155°	874.1	874.1	873.4	876.4	873.4
157.5°	897.1	895.6	895.6	897.9	895.6
160°	917.1	916.3	915.5	917.8	914.0
162.5°	935.5	933.2	932.4	937.0	933.2
165°	951.6	949.3	947.7	952.3	949.3
167.5°	964.6	961.5	961.5	966.1	961.5
170°	975.3	971.5	972.3	976.9	971.5
172.5°	983.0	979.9	979.9	985.3	979.9
175°	989.9	986.1	985.3	990.7	985.3
177.5°	993.0	989.1	989.1	994.5	988.4
180°	991.4	991.4	991.4	991.4	991.4

(END OF REPORT)