

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000945

Luminaire Tested: SA4XXDIP-B1195D365UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000945
REPORT IS A COMBINATION OF REPORTS P995560 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B1195D365UB2750-4F0-XX-W2A-F_3500K
Description: Define 4 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6626.0 lumens
Efficiency: N/A
Efficacy: 93.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 70.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000945

CATALOG NUMBER: SA4XXDIP-B1195D365UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1000945

CATALOG NUMBER: SA4XXDIP-B1195D365UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	114	114	114	114	109	109	109	109	99	99	99	90	90	90	82	82	82	82	82	78
1	104	99	95	92	99	95	91	88	87	84	81	79	77	75	72	70	69	69	69	65
2	95	87	80	75	90	83	77	72	76	71	67	69	66	63	63	61	58	58	58	55
3	86	76	69	63	82	73	66	61	67	61	57	61	57	53	56	53	49	49	49	46
4	79	68	59	53	75	65	57	52	60	53	48	55	50	45	50	46	43	43	43	40
5	73	61	52	46	69	58	50	44	54	47	42	49	44	40	45	41	37	37	37	35
6	67	55	46	40	64	52	45	39	48	42	37	45	39	35	41	36	33	33	33	30
7	62	49	41	35	59	48	40	34	44	37	33	41	35	31	38	33	29	29	29	27
8	58	45	37	31	55	43	36	31	40	34	29	37	32	28	35	30	26	26	26	24
9	54	41	33	28	52	40	32	27	37	31	26	34	29	25	32	27	24	24	24	22
10	51	38	30	25	48	37	30	25	34	28	24	32	26	23	30	25	22	22	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16355	16355	16355
5°	16369	15885	15904
10°	16230	15444	15336
15°	15998	14919	14694
20°	15700	14353	14031
25°	15366	13753	13316
30°	14962	13105	12531
35°	14544	12442	11773
40°	14109	11728	10966
45°	13652	11012	10212
50°	13146	10318	9377
55°	12597	9508	8547
60°	12034	8620	7684
65°	11391	7704	6709
70°	10648	6599	5666
75°	9542	5320	4539
80°	8131	3845	3192
85°	6316	2142	1719

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13652 cd/sqm

TEST NUMBER: P1000945

CATALOG NUMBER: SA4XXDIP-B1195D365UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	189.0	2.9
10°-20°	532.6	8.0
20°-30°	783.8	11.8
30°-40°	911.2	13.8
40°-50°	911.1	13.7
50°-60°	796.9	12.0
60°-70°	591.6	8.9
70°-80°	335.7	5.1
80°-90°	97.1	1.5
90°-100°	15.8	0.2
100°-110°	104.3	1.6
110°-120°	199.2	3.0
120°-130°	252.9	3.8
130°-140°	270.6	4.1
140°-150°	253.0	3.8
150°-160°	204.0	3.1
160°-170°	131.6	2.0
170°-180°	45.4	0.7
0°-30°	1505.5	22.7
0°-40°	2416.7	36.5
0°-60°	4124.6	62.2
0°-90°	5149.0	77.7
90°-120°	319.4	4.8
90°-150°	1096.0	16.5
90°-180°	1477.0	22.3
0°-180°	6626.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2006	2006	2006	2006	2006	
5°	2004	1998	1980	1998	1994	190
15°	1908	1901	1877	1887	1882	538
25°	1728	1716	1694	1696	1689	795
35°	1487	1475	1453	1442	1434	930
45°	1213	1202	1176	1159	1154	935
55°	918	913	890	871	861	822
65°	622	614	598	582	574	616
75°	331	323	315	309	307	351
85°	87	87	84	84	82	93
90°	1	5	8	10	11	7
95°	20	8	8	10	10	24
105°	108	110	111	115	102	112
115°	201	202	201	202	202	197
125°	282	284	283	284	284	252
135°	350	350	351	352	352	270
145°	403	404	404	405	406	252
155°	442	443	442	443	442	204
165°	467	465	465	468	464	132
175°	477	475	476	479	474	45
180°	477	477	477	477	477	

TEST NUMBER: P1000945

CATALOG NUMBER: SA4XXDIP-B1195D365UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2005.7	2005.7	2005.7	2005.7	2005.7
2.5°	2012.1	2007.3	1989.6	2005.7	2004.1
5°	2004.1	1997.7	1980.0	1997.7	1994.4
7.5°	1989.6	1983.2	1963.9	1978.4	1976.8
10°	1968.7	1962.3	1941.4	1954.3	1951.1
12.5°	1941.4	1935.0	1912.5	1926.9	1922.1
15°	1907.7	1901.2	1877.1	1886.8	1881.9
17.5°	1869.1	1861.1	1838.6	1845.0	1841.8
20°	1825.7	1817.7	1793.6	1798.4	1795.2
22.5°	1779.1	1767.8	1743.7	1753.4	1746.9
25°	1727.7	1716.4	1693.9	1695.5	1689.1
27.5°	1669.8	1658.6	1637.7	1634.4	1626.4
30°	1611.9	1599.1	1578.2	1571.8	1563.7
32.5°	1550.9	1539.6	1517.1	1509.1	1501.1
35°	1486.6	1475.3	1452.8	1441.6	1433.6
37.5°	1419.1	1409.4	1385.3	1374.1	1362.8
40°	1353.2	1340.3	1316.2	1300.2	1292.1
42.5°	1282.5	1276.1	1248.7	1229.5	1224.6
45°	1213.4	1202.1	1176.4	1158.7	1153.9
47.5°	1141.1	1133.0	1108.9	1089.6	1076.8
50°	1067.1	1060.7	1038.2	1015.7	1006.1
52.5°	994.8	986.8	962.7	943.4	930.5
55°	917.7	912.8	890.3	871.1	861.4
57.5°	845.3	840.5	818.0	798.7	789.1
60°	769.8	761.8	740.9	726.4	718.4
62.5°	695.9	689.5	667.0	654.1	646.1
65°	622.0	613.9	597.9	581.8	573.7
67.5°	546.4	540.0	523.9	507.9	506.2
70°	477.3	466.1	453.2	440.4	435.5
72.5°	403.4	392.1	382.5	372.9	368.0
75°	331.1	323.0	315.0	308.6	307.0
77.5°	260.4	257.1	249.1	247.5	242.7
80°	197.7	192.9	189.6	186.4	184.8
82.5°	136.6	135.0	135.0	133.4	131.8
85°	86.8	86.8	83.6	83.6	82.0
87.5°	41.8	40.2	38.6	38.6	38.6
90°	1.1	5.0	7.9	10.0	10.7
92.5°	5.4	4.6	7.5	9.6	9.6
95°	19.6	7.5	7.9	10.0	10.4
97.5°	37.5	45.3	7.9	9.6	10.0
100°	58.6	65.0	15.7	9.6	10.0
102.5°	82.1	86.4	90.7	10.4	10.4
105°	107.5	109.6	111.4	114.6	101.7
107.5°	130.7	131.7	134.2	136.0	137.4
110°	154.2	155.3	157.4	158.2	159.2



TEST NUMBER: P1000945

CATALOG NUMBER: SA4XXDIP-B1195D365UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	177.1	179.2	179.9	179.6	181.0
115°	200.6	201.7	201.4	202.1	202.1
117.5°	221.7	223.1	224.2	223.8	223.8
120°	243.1	244.6	244.2	244.9	244.2
122.5°	263.1	263.8	264.5	264.9	264.2
125°	282.0	283.5	282.8	283.8	284.2
127.5°	300.2	300.6	302.4	302.0	301.7
130°	317.7	318.1	319.2	319.5	319.5
132.5°	333.8	334.5	335.9	336.3	335.9
135°	349.9	349.5	350.9	351.7	352.4
137.5°	364.2	364.2	365.9	366.7	366.3
140°	378.1	378.8	379.5	380.6	380.9
142.5°	390.6	392.0	392.4	393.1	393.1
145°	403.4	404.5	404.5	404.9	405.6
147.5°	413.4	415.6	415.2	415.6	415.9
150°	424.5	425.9	425.6	425.6	425.9
152.5°	433.8	434.8	434.1	434.8	434.5
155°	442.3	442.7	441.6	443.1	442.0
157.5°	449.8	449.8	448.4	450.2	448.4
160°	456.3	455.2	454.8	457.0	454.8
162.5°	462.0	460.5	460.2	462.3	459.8
165°	466.6	464.8	464.8	467.7	464.5
167.5°	470.5	468.8	468.4	471.6	468.0
170°	473.8	471.6	472.0	474.8	471.3
172.5°	475.9	473.8	474.1	477.0	473.0
175°	477.3	475.2	475.5	478.8	474.5
177.5°	478.4	475.9	476.6	479.5	475.2
180°	477.3	477.3	477.3	477.3	477.3

(END OF REPORT)