

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001102

Luminaire Tested: SA4XXDIP-B1195D810UB50-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001102
REPORT IS A COMBINATION OF REPORTS P995718 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B1195D810UB50-4F0-XX-W2A-F4
Description: Define 4 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7658.4 lumens
Efficiency: N/A
Efficacy: 92.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 82.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001102

CATALOG NUMBER: SA4XXDIP-B1195D810UB50-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1001102

CATALOG NUMBER: SA4XXDIP-B1195D810UB50-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	111	111	111	111		104	104	104	104		91	91	91		80	80	80		69	69	69
1	101	97	93	89		95	91	87	84		80	77	75		70	68	67		61	60	59
2	92	84	78	73		86	79	74	69		70	66	62		62	58	56		54	51	49
3	84	74	67	61		78	70	63	58		62	57	52		55	50	47		48	45	42
4	77	66	58	51		72	62	55	49		55	49	45		49	44	40		43	39	36
5	71	59	50	44		66	55	48	42		49	43	39		44	39	35		38	35	32
6	65	53	44	38		61	50	42	37		45	38	34		40	35	31		35	31	28
7	60	48	39	34		56	45	38	32		40	34	30		36	31	27		32	28	25
8	56	43	35	30		53	41	34	29		37	31	27		33	28	24		29	25	22
9	52	40	32	27		49	38	31	26		34	28	24		30	25	22		27	23	20
10	49	36	29	24		46	35	28	23		31	26	22		28	23	20		25	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15660	15660	15660
5°	15672	15209	15228
10°	15540	14787	14684
15°	15317	14285	14069
20°	15032	13742	13434
25°	14712	13168	12749
30°	14326	12548	11998
35°	13926	11912	11272
40°	13508	11229	10500
45°	13071	10544	9778
50°	12586	9879	8978
55°	12060	9104	8184
60°	11522	8254	7356
65°	10906	7376	6424
70°	10196	6318	5425
75°	9135	5093	4345
80°	7786	3683	3057
85°	6047	2050	1645

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13071 cd/sqm

TEST NUMBER: P1001102

CATALOG NUMBER: SA4XXDIP-B1195D810UB50-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	181.0	2.4
10°-20°	509.9	6.7
20°-30°	750.5	9.8
30°-40°	872.4	11.4
40°-50°	872.3	11.4
50°-60°	763.0	10.0
60°-70°	566.4	7.4
70°-80°	321.4	4.2
80°-90°	93.5	1.2
90°-100°	277.7	3.6
100°-110°	564.7	7.4
110°-120°	503.4	6.6
120°-130°	422.8	5.5
130°-140°	352.9	4.6
140°-150°	269.5	3.5
150°-160°	189.4	2.5
160°-170°	111.4	1.5
170°-180°	36.2	0.5
0°-30°	1441.4	18.8
0°-40°	2313.8	30.2
0°-60°	3949.1	51.6
0°-90°	4930.4	64.4
90°-120°	1345.8	17.6
90°-150°	2390.9	31.2
90°-180°	2728.0	35.6
0°-180°	7658.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1920	1920	1920	1920	1920	
5°	1919	1913	1896	1913	1910	182
15°	1826	1820	1797	1806	1802	515
25°	1654	1643	1622	1623	1617	761
35°	1423	1413	1391	1380	1373	890
45°	1162	1151	1126	1109	1105	896
55°	879	874	852	834	825	787
65°	596	588	572	557	549	589
75°	317	309	302	295	294	336
85°	83	83	80	80	78	89
90°	1	6	13	15	15	7
95°	24	76	598	296	179	27
105°	86	124	482	1037	1033	92
115°	151	190	430	825	992	150
125°	211	250	427	702	792	188
135°	250	298	424	624	708	194
145°	289	330	422	526	578	181
155°	328	354	410	464	484	151
165°	358	369	393	416	422	101
175°	373	374	377	382	380	35
180°	374	374	374	374	374	

TEST NUMBER: P1001102

CATALOG NUMBER: SA4XXDIP-B1195D810UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1920.4	1920.4	1920.4	1920.4	1920.4
2.5°	1926.5	1921.9	1905.0	1920.4	1918.8
5°	1918.8	1912.7	1895.7	1912.7	1909.6
7.5°	1905.0	1898.8	1880.4	1894.2	1892.7
10°	1885.0	1878.8	1858.8	1871.1	1868.1
12.5°	1858.8	1852.7	1831.1	1845.0	1840.4
15°	1826.5	1820.3	1797.3	1806.5	1801.9
17.5°	1789.6	1781.9	1760.3	1766.5	1763.4
20°	1748.0	1740.3	1717.3	1721.9	1718.8
22.5°	1703.4	1692.6	1669.6	1678.8	1672.6
25°	1654.2	1643.4	1621.8	1623.4	1617.2
27.5°	1598.8	1588.0	1568.0	1564.9	1557.2
30°	1543.4	1531.1	1511.1	1504.9	1497.2
32.5°	1484.9	1474.1	1452.6	1444.9	1437.2
35°	1423.4	1412.6	1391.0	1380.3	1372.6
37.5°	1358.7	1349.5	1326.4	1315.6	1304.9
40°	1295.6	1283.3	1260.2	1244.9	1237.2
42.5°	1227.9	1221.8	1195.6	1177.1	1172.5
45°	1161.8	1151.0	1126.4	1109.4	1104.8
47.5°	1092.5	1084.8	1061.7	1043.3	1031.0
50°	1021.7	1015.6	994.0	972.5	963.3
52.5°	952.5	944.8	921.7	903.3	890.9
55°	878.6	874.0	852.5	834.0	824.8
57.5°	809.4	804.8	783.2	764.8	755.5
60°	737.1	729.4	709.4	695.5	687.8
62.5°	666.3	660.1	638.6	626.3	618.6
65°	595.5	587.8	572.4	557.0	549.3
67.5°	523.2	517.0	501.6	486.2	484.7
70°	457.0	446.2	433.9	421.6	417.0
72.5°	386.2	375.5	366.2	357.0	352.4
75°	317.0	309.3	301.6	295.4	293.9
77.5°	249.3	246.2	238.5	237.0	232.4
80°	189.3	184.7	181.6	178.5	177.0
82.5°	130.8	129.3	129.3	127.7	126.2
85°	83.1	83.1	80.0	80.0	78.5
87.5°	40.0	38.5	36.9	36.9	36.9
90°	0.7	5.9	13.2	14.7	15.4
92.5°	10.3	56.6	287.9	95.1	66.8
95°	24.2	76.4	598.5	296.3	179.2
97.5°	40.4	84.4	640.4	605.2	430.4
100°	55.8	95.4	590.5	837.2	673.4
102.5°	70.5	108.7	528.0	982.6	884.9
105°	85.9	124.4	481.8	1037.4	1033.3
107.5°	102.8	140.6	451.7	1020.8	1103.8
110°	119.7	156.8	437.7	962.0	1105.3

TEST NUMBER: P1001102

CATALOG NUMBER: SA4XXDIP-B1195D810UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	135.9	173.0	431.1	890.1	1061.9
115°	151.3	189.9	429.6	825.4	992.2
117.5°	167.4	205.6	428.9	774.8	923.9
120°	183.6	221.0	428.9	740.7	868.1
122.5°	198.3	236.1	428.2	718.2	824.0
125°	210.8	250.4	427.4	702.4	791.7
127.5°	222.5	263.6	425.9	687.4	771.1
130°	232.1	276.5	425.2	669.4	753.5
132.5°	241.6	287.5	424.5	648.1	733.7
135°	250.4	298.2	423.7	623.5	708.0
137.5°	259.2	307.4	423.7	597.1	677.8
140°	268.8	315.8	423.0	571.3	644.8
142.5°	279.1	323.5	423.0	547.4	609.5
145°	288.6	330.5	421.5	525.8	578.0
147.5°	299.6	337.0	419.3	507.8	548.6
150°	309.9	343.4	417.1	491.3	524.4
152.5°	319.5	349.2	413.5	477.4	502.3
155°	328.3	354.4	409.8	464.1	484.0
157.5°	337.1	359.1	406.1	451.6	467.1
160°	345.2	363.2	401.7	439.2	451.7
162.5°	352.5	366.4	397.3	427.0	437.0
165°	357.7	368.7	392.9	416.0	422.3
167.5°	363.5	370.5	388.5	406.5	410.5
170°	367.2	372.0	384.1	396.9	399.5
172.5°	370.9	373.0	379.7	388.5	388.5
175°	373.1	373.8	376.7	381.9	380.4
177.5°	374.5	373.8	374.5	377.1	374.5
180°	373.8	373.8	373.8	373.8	373.8

(END OF REPORT)