

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001058

Luminaire Tested: SA4XXDIP-B1195D810UB2750-4F0-XX-W2A-D_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001058
REPORT IS A COMBINATION OF REPORTS P995674 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B1195D810UB2750-4F0-XX-W2A-D_3000K
Description: Define 4 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8032.9 lumens
Efficiency: N/A
Efficacy: 97.5 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 82.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001058

CATALOG NUMBER: SA4XXDIP-B1195D810UB2750-4F0-XX-W2A-D_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1001058

CATALOG NUMBER: SA4XXDIP-B1195D810UB2750-4F0-XX-W2A-D_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	56		
1	98	93	89	85	91	87	83	79	74	72	69	63	61	59	53	51	50	45		
2	89	81	74	68	82	75	69	64	65	60	56	55	51	48	46	43	41	37		
3	81	71	63	56	75	66	59	53	57	51	47	48	44	40	40	37	34	31		
4	74	62	54	47	68	58	50	45	50	44	39	43	38	34	36	32	29	26		
5	68	55	47	40	62	52	44	38	45	38	34	38	33	30	32	28	25	22		
6	62	49	41	35	57	46	39	33	40	34	29	34	29	26	29	25	22	19		
7	57	45	36	30	53	42	34	29	36	30	26	31	26	23	26	23	20	17		
8	53	40	32	27	49	38	31	26	33	27	23	28	24	20	24	20	17	15		
9	50	37	29	24	46	35	28	23	30	24	20	26	21	18	22	18	16	14		
10	46	34	26	21	43	32	25	20	28	22	18	24	20	16	21	17	14	12		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11653	11653	11653
5°	11685	11349	11370
10°	11609	11126	11094
15°	11501	10875	10783
20°	11339	10603	10481
25°	11158	10303	10156
30°	10962	10006	9823
35°	10739	9702	9528
40°	10561	9411	9221
45°	10298	9137	8950
50°	10073	8827	8665
55°	9841	8527	8336
60°	9481	8155	8027
65°	9085	7753	7654
70°	8605	7294	7225
75°	7931	6784	6815
80°	7173	6263	6384
85°	6171	5740	6037

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10298 cd/sqm

TEST NUMBER: P1001058

CATALOG NUMBER: SA4XXDIP-B1195D810UB2750-4F0-XX-W2A-D_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	135.4	1.7
10°-20°	387.9	4.8
20°-30°	586.6	7.3
30°-40°	709.6	8.8
40°-50°	750.2	9.3
50°-60°	706.0	8.8
60°-70°	585.9	7.3
70°-80°	411.1	5.1
80°-90°	233.9	2.9
90°-100°	171.9	2.1
100°-110°	325.3	4.0
110°-120°	494.7	6.2
120°-130°	579.6	7.2
130°-140°	595.4	7.4
140°-150°	544.5	6.8
150°-160°	436.4	5.4
160°-170°	281.4	3.5
170°-180°	97.0	1.2
0°-30°	1109.9	13.8
0°-40°	1819.6	22.7
0°-60°	3275.8	40.8
0°-90°	4506.7	56.1
90°-120°	991.9	12.3
90°-150°	2711.4	33.8
90°-180°	3526.0	43.9
0°-180°	8032.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1429	1429	1429	1429	1429	
5°	1431	1426	1415	1427	1426	136
15°	1371	1373	1368	1383	1381	386
25°	1255	1264	1269	1287	1288	578
35°	1098	1117	1133	1155	1160	687
45°	915	946	976	1003	1011	707
55°	717	750	798	830	840	639
65°	496	547	602	642	654	492
75°	275	334	402	446	461	292
85°	85	152	224	272	288	88
90°	28	100	175	226	240	20
95°	63	90	156	204	219	68
105°	244	281	344	391	376	257
115°	439	455	506	543	554	433
125°	610	611	650	682	693	545
135°	752	751	765	792	803	580
145°	864	865	865	876	883	540
155°	946	947	944	948	945	436
165°	998	994	994	1000	993	282
175°	1021	1016	1017	1024	1015	97
180°	1021	1021	1021	1021	1021	

TEST NUMBER: P1001058

CATALOG NUMBER: SA4XXDIP-B1195D810UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1429.0	1429.0	1429.0	1429.0	1429.0
2.5°	1435.4	1430.6	1417.8	1429.0	1427.4
5°	1430.6	1425.8	1414.6	1427.4	1425.8
7.5°	1421.0	1417.8	1408.2	1422.6	1421.0
10°	1408.2	1406.6	1398.6	1413.0	1411.4
12.5°	1390.6	1390.6	1385.8	1398.6	1398.6
15°	1371.4	1373.0	1368.2	1382.6	1381.0
17.5°	1345.8	1350.6	1349.0	1363.4	1361.8
20°	1318.6	1323.4	1325.0	1341.0	1341.0
22.5°	1288.2	1294.6	1297.8	1313.8	1317.0
25°	1254.6	1264.2	1269.0	1286.6	1288.2
27.5°	1217.8	1232.2	1238.6	1254.6	1256.2
30°	1181.0	1193.8	1205.0	1222.6	1225.8
32.5°	1140.9	1157.0	1169.8	1190.6	1193.8
35°	1097.7	1116.9	1132.9	1155.4	1160.2
37.5°	1054.5	1076.9	1096.1	1118.5	1123.3
40°	1012.9	1033.7	1056.1	1080.1	1086.5
42.5°	964.9	988.9	1016.1	1043.3	1048.1
45°	915.3	945.7	976.1	1003.3	1011.3
47.5°	868.9	899.3	934.5	961.7	971.3
50°	817.7	852.9	888.1	920.1	929.7
52.5°	766.5	801.7	843.3	875.3	884.9
55°	716.9	750.5	798.5	830.5	840.1
57.5°	660.9	702.5	748.9	787.3	795.3
60°	606.5	648.1	700.9	737.7	750.5
62.5°	553.7	600.1	652.9	689.7	702.5
65°	496.1	547.3	601.7	641.7	654.5
67.5°	441.7	496.1	553.7	593.7	606.5
70°	385.7	440.1	500.9	544.1	555.3
72.5°	331.2	387.3	452.9	494.5	507.3
75°	275.2	334.4	401.7	446.5	460.9
77.5°	222.4	284.8	355.2	400.1	416.1
80°	174.4	238.4	308.8	356.8	369.6
82.5°	126.4	193.6	264.0	313.6	328.0
85°	84.8	152.0	224.0	272.0	288.0
87.5°	52.8	118.4	188.8	235.2	249.6
90°	27.9	100.3	175.2	226.2	240.5
92.5°	35.5	89.9	164.8	214.2	227.0
95°	62.8	89.6	156.0	203.8	218.9
97.5°	99.4	162.6	148.0	193.4	208.6
100°	142.8	198.2	155.2	185.4	197.4
102.5°	193.2	237.6	307.5	177.3	190.1
105°	244.2	280.8	343.8	390.7	376.0
107.5°	293.9	323.3	384.7	428.5	442.8
110°	342.7	367.3	427.9	466.2	481.3



TEST NUMBER: P1001058

CATALOG NUMBER: SA4XXDIP-B1195D810UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	389.9	413.7	468.0	502.5	518.3
115°	438.7	455.4	505.8	542.6	553.8
117.5°	483.8	496.4	546.7	579.5	592.3
120°	528.0	535.8	581.5	615.0	626.3
122.5°	570.7	572.3	617.0	649.7	659.4
125°	609.6	611.1	649.5	682.2	692.6
127.5°	648.5	647.7	683.5	711.6	722.0
130°	684.4	683.5	711.4	741.0	750.6
132.5°	718.7	718.6	740.9	768.9	777.7
135°	751.5	750.7	765.0	792.1	803.2
137.5°	782.0	780.4	790.6	816.2	823.4
140°	811.8	811.7	814.8	837.9	846.7
142.5°	836.9	840.0	839.1	858.3	864.7
145°	864.4	865.1	865.1	875.5	883.4
147.5°	885.8	888.8	888.0	890.4	897.5
150°	909.5	910.9	910.1	910.1	910.9
152.5°	927.7	930.0	928.5	930.0	929.2
155°	946.0	946.8	944.5	947.6	945.3
157.5°	962.1	962.1	959.0	962.8	959.0
160°	975.8	973.5	972.8	977.3	972.8
162.5°	988.0	985.0	984.2	988.8	983.4
165°	998.0	994.1	994.1	1000.2	993.4
167.5°	1006.3	1002.5	1001.8	1008.6	1001.0
170°	1013.2	1008.6	1009.4	1015.5	1007.9
172.5°	1017.8	1013.2	1014.0	1020.1	1011.7
175°	1020.9	1016.3	1017.0	1023.9	1014.7
177.5°	1023.1	1017.8	1019.3	1025.4	1016.3
180°	1020.9	1020.9	1020.9	1020.9	1020.9

(END OF REPORT)