

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001059

Luminaire Tested: SA4XXDIP-B1195D810UB2750-4F0-XX-W2A-D_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001059
REPORT IS A COMBINATION OF REPORTS P995675 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B1195D810UB2750-4F0-XX-W2A-D_3500K
Description: Define 4 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8068.0 lumens
Efficiency: N/A
Efficacy: 97.9 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 82.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001059

CATALOG NUMBER: SA4XXDIP-B1195D810UB2750-4F0-XX-W2A-D_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1001059

CATALOG NUMBER: SA4XXDIP-B1195D810UB2750-4F0-XX-W2A-D_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	56	56	56
1	98	93	89	85	91	87	83	79	74	72	69	63	61	59	53	51	50	45	45	45
2	89	81	74	68	82	75	69	64	65	60	56	55	51	48	46	43	41	37	37	37
3	81	71	63	56	75	66	59	53	56	51	47	48	44	40	40	37	34	31	31	31
4	74	62	54	47	68	58	50	45	50	44	39	43	38	34	36	32	29	26	26	26
5	68	55	47	40	62	52	44	38	45	38	34	38	33	30	32	28	25	22	22	22
6	62	49	41	35	57	46	39	33	40	34	29	34	29	26	29	25	22	19	19	19
7	57	45	36	30	53	42	34	29	36	30	26	31	26	23	26	23	20	17	17	17
8	53	40	32	27	49	38	31	26	33	27	23	28	24	20	24	20	17	15	15	15
9	50	37	29	24	46	35	28	23	30	24	20	26	21	18	22	18	16	14	14	14
10	46	34	26	21	43	32	25	20	28	22	18	24	20	16	21	17	14	12	12	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11702	11702	11702
5°	11735	11398	11418
10°	11659	11173	11142
15°	11550	10922	10829
20°	11388	10649	10526
25°	11206	10347	10199
30°	11008	10049	9865
35°	10786	9744	9569
40°	10607	9452	9261
45°	10343	9176	8989
50°	10116	8864	8702
55°	9883	8564	8372
60°	9521	8190	8061
65°	9124	7787	7687
70°	8641	7325	7256
75°	7965	6812	6843
80°	7206	6291	6412
85°	6200	5766	6064

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10343 cd/sqm

TEST NUMBER: P1001059

CATALOG NUMBER: SA4XXDIP-B1195D810UB2750-4F0-XX-W2A-D_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	136.0	1.7
10°-20°	389.6	4.8
20°-30°	589.1	7.3
30°-40°	712.7	8.8
40°-50°	753.4	9.3
50°-60°	709.1	8.8
60°-70°	588.4	7.3
70°-80°	412.9	5.1
80°-90°	234.9	2.9
90°-100°	172.6	2.1
100°-110°	326.8	4.1
110°-120°	496.9	6.2
120°-130°	582.2	7.2
130°-140°	598.1	7.4
140°-150°	546.9	6.8
150°-160°	438.3	5.4
160°-170°	282.7	3.5
170°-180°	97.4	1.2
0°-30°	1114.7	13.8
0°-40°	1827.4	22.6
0°-60°	3289.9	40.8
0°-90°	4526.2	56.1
90°-120°	996.3	12.3
90°-150°	2723.4	33.8
90°-180°	3542.0	43.9
0°-180°	8068.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1435	1435	1435	1435	1435	
5°	1437	1432	1421	1434	1432	136
15°	1377	1379	1374	1388	1387	388
25°	1260	1270	1274	1292	1294	580
35°	1102	1122	1138	1160	1165	690
45°	919	950	980	1008	1016	710
55°	720	754	802	834	844	642
65°	498	550	604	644	657	494
75°	276	336	403	448	463	294
85°	85	153	225	273	289	89
90°	28	101	176	227	242	20
95°	63	90	157	205	220	69
105°	245	282	345	392	378	258
115°	441	457	508	545	556	434
125°	612	614	652	685	696	547
135°	755	754	768	796	807	582
145°	868	869	869	879	887	543
155°	950	951	949	952	950	438
165°	1002	998	998	1005	998	283
175°	1025	1021	1022	1028	1019	98
180°	1025	1025	1025	1025	1025	

TEST NUMBER: P1001059

CATALOG NUMBER: SA4XXDIP-B1195D810UB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1435.1	1435.1	1435.1	1435.1	1435.1
2.5°	1441.6	1436.8	1423.9	1435.1	1433.5
5°	1436.8	1431.9	1420.7	1433.5	1431.9
7.5°	1427.1	1423.9	1414.3	1428.7	1427.1
10°	1414.3	1412.6	1404.6	1419.1	1417.5
12.5°	1396.6	1396.6	1391.8	1404.6	1404.6
15°	1377.3	1378.9	1374.1	1388.5	1386.9
17.5°	1351.6	1356.4	1354.8	1369.3	1367.6
20°	1324.3	1329.1	1330.7	1346.8	1346.8
22.5°	1293.7	1300.1	1303.4	1319.4	1322.6
25°	1260.0	1269.6	1274.4	1292.1	1293.7
27.5°	1223.0	1237.5	1243.9	1260.0	1261.6
30°	1186.0	1198.9	1210.2	1227.8	1231.0
32.5°	1145.9	1161.9	1174.8	1195.7	1198.9
35°	1102.5	1121.8	1137.8	1160.3	1165.2
37.5°	1059.1	1081.6	1100.9	1123.4	1128.2
40°	1017.3	1038.2	1060.7	1084.8	1091.2
42.5°	969.1	993.2	1020.5	1047.8	1052.7
45°	919.3	949.8	980.3	1007.7	1015.7
47.5°	872.7	903.2	938.5	965.9	975.5
50°	821.2	856.6	891.9	924.1	933.7
52.5°	769.8	805.2	846.9	879.1	888.7
55°	720.0	753.7	801.9	834.1	843.7
57.5°	663.7	705.5	752.1	790.7	798.7
60°	609.1	650.9	703.9	740.9	753.7
62.5°	556.1	602.7	655.7	692.7	705.5
65°	498.2	549.6	604.3	644.4	657.3
67.5°	443.6	498.2	556.1	596.2	609.1
70°	387.3	442.0	503.0	546.4	557.7
72.5°	332.7	388.9	454.8	496.6	509.5
75°	276.4	335.9	403.4	448.4	462.8
77.5°	223.4	286.1	356.8	401.8	417.8
80°	175.2	239.5	310.2	358.4	371.2
82.5°	127.0	194.5	265.2	315.0	329.5
85°	85.2	152.7	225.0	273.2	289.3
87.5°	53.0	118.9	189.6	236.2	250.7
90°	28.0	100.7	176.0	227.2	241.6
92.5°	35.6	90.4	165.6	215.2	228.0
95°	63.1	90.0	156.7	204.7	219.9
97.5°	99.8	163.3	148.7	194.3	209.5
100°	143.5	199.1	155.8	186.2	198.3
102.5°	194.1	238.6	308.9	178.1	190.9
105°	245.3	282.0	345.4	392.4	377.7
107.5°	295.2	324.8	386.4	430.4	444.8
110°	344.2	369.0	429.8	468.3	483.4



TEST NUMBER: P1001059

CATALOG NUMBER: SA4XXDIP-B1195D810UB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	391.6	415.5	470.1	504.7	520.6
115°	440.6	457.4	508.0	545.0	556.2
117.5°	485.9	498.6	549.1	582.1	595.0
120°	530.3	538.2	584.1	617.7	629.1
122.5°	573.2	574.8	619.7	652.7	662.3
125°	612.3	613.7	652.4	685.2	695.7
127.5°	651.4	650.6	686.6	714.7	725.2
130°	687.4	686.5	714.5	744.3	753.9
132.5°	721.9	721.8	744.2	772.2	781.2
135°	754.8	754.0	768.4	795.6	806.8
137.5°	785.5	783.9	794.1	819.7	827.1
140°	815.4	815.3	818.4	841.6	850.4
142.5°	840.6	843.7	842.9	862.1	868.5
145°	868.2	868.9	868.9	879.3	887.3
147.5°	889.7	892.7	891.9	894.3	901.5
150°	913.5	914.9	914.2	914.2	914.9
152.5°	931.8	934.1	932.6	934.1	933.3
155°	950.2	951.0	948.7	951.8	949.5
157.5°	966.3	966.3	963.3	967.1	963.3
160°	980.1	977.8	977.1	981.7	977.1
162.5°	992.4	989.3	988.6	993.2	987.8
165°	1002.4	998.5	998.5	1004.7	997.8
167.5°	1010.8	1007.0	1006.2	1013.1	1005.4
170°	1017.7	1013.1	1013.9	1020.0	1012.3
172.5°	1022.3	1017.7	1018.5	1024.6	1016.2
175°	1025.4	1020.8	1021.5	1028.4	1019.2
177.5°	1027.7	1022.3	1023.8	1030.0	1020.8
180°	1025.4	1025.4	1025.4	1025.4	1025.4

(END OF REPORT)