

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001061

Luminaire Tested: SA4XXDIP-B1195D810UB2750-4F0-XX-W2A-D_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001061
REPORT IS A COMBINATION OF REPORTS P995677 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B1195D810UB2750-4F0-XX-W2A-D_5000K
Description: Define 4 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7725.0 lumens
Efficiency: N/A
Efficacy: 93.7 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 82.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001061

CATALOG NUMBER: SA4XXDIP-B1195D810UB2750-4F0-XX-W2A-D_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1001061

CATALOG NUMBER: SA4XXDIP-B1195D810UB2750-4F0-XX-W2A-D_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62
1	98	93	89	85	91	87	83	79	74	72	69	63	61	59	53	51	50
2	89	81	74	68	82	75	69	64	65	60	56	55	51	48	46	43	41
3	81	71	63	56	75	66	59	53	56	51	47	48	44	40	40	37	34
4	74	62	54	47	68	58	50	45	50	44	39	43	38	34	36	32	29
5	68	55	47	40	62	52	44	38	45	38	34	38	33	30	32	28	25
6	62	49	41	35	57	46	39	33	40	34	29	34	29	26	29	25	22
7	57	45	36	30	53	42	34	29	36	30	26	31	26	23	26	23	20
8	53	40	32	27	49	38	31	26	33	27	23	28	24	20	24	20	17
9	50	37	29	24	46	35	28	23	30	24	20	26	21	18	22	18	16
10	46	34	26	21	43	32	25	20	28	22	18	24	20	16	21	17	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11205	11205	11205
5°	11236	10913	10933
10°	11163	10699	10668
15°	11059	10457	10369
20°	10904	10196	10078
25°	10729	9908	9765
30°	10541	9622	9446
35°	10327	9330	9162
40°	10156	9050	8867
45°	9903	8787	8607
50°	9686	8488	8332
55°	9463	8201	8017
60°	9117	7842	7719
65°	8735	7456	7361
70°	8272	7013	6947
75°	7628	6522	6553
80°	6897	6023	6141
85°	5938	5520	5806

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9903 cd/sqm

TEST NUMBER: P1001061

CATALOG NUMBER: SA4XXDIP-B1195D810UB2750-4F0-XX-W2A-D_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	130.2	1.7
10°-20°	373.1	4.8
20°-30°	564.1	7.3
30°-40°	682.4	8.8
40°-50°	721.4	9.3
50°-60°	678.9	8.8
60°-70°	563.4	7.3
70°-80°	395.4	5.1
80°-90°	224.9	2.9
90°-100°	165.3	2.1
100°-110°	312.9	4.1
110°-120°	475.8	6.2
120°-130°	557.4	7.2
130°-140°	572.6	7.4
140°-150°	523.6	6.8
150°-160°	419.7	5.4
160°-170°	270.7	3.5
170°-180°	93.3	1.2
0°-30°	1067.3	13.8
0°-40°	1749.7	22.6
0°-60°	3150.1	40.8
0°-90°	4333.7	56.1
90°-120°	953.9	12.3
90°-150°	2607.6	33.8
90°-180°	3391.0	43.9
0°-180°	7725.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1374	1374	1374	1374	1374	
5°	1376	1371	1360	1373	1371	131
15°	1319	1320	1316	1330	1328	372
25°	1206	1216	1220	1237	1239	556
35°	1056	1074	1090	1111	1116	661
45°	880	909	939	965	972	680
55°	689	722	768	799	808	614
65°	477	526	579	617	629	473
75°	265	322	386	429	443	281
85°	82	146	215	262	277	85
90°	27	96	168	218	231	19
95°	60	86	150	196	211	66
105°	235	270	331	376	362	247
115°	422	438	486	522	532	416
125°	586	588	625	656	666	524
135°	723	722	736	762	772	557
145°	831	832	832	842	850	520
155°	910	911	908	911	909	420
165°	960	956	956	962	955	271
175°	982	977	978	985	976	93
180°	982	982	982	982	982	

TEST NUMBER: P1001061

CATALOG NUMBER: SA4XXDIP-B1195D810UB2750-4F0-XX-W2A-D_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1374.1	1374.1	1374.1	1374.1	1374.1
2.5°	1380.3	1375.7	1363.4	1374.1	1372.6
5°	1375.7	1371.1	1360.3	1372.6	1371.1
7.5°	1366.4	1363.4	1354.1	1368.0	1366.4
10°	1354.1	1352.6	1344.9	1358.8	1357.2
12.5°	1337.2	1337.2	1332.6	1344.9	1344.9
15°	1318.7	1320.3	1315.7	1329.5	1328.0
17.5°	1294.1	1298.7	1297.2	1311.0	1309.5
20°	1268.0	1272.6	1274.1	1289.5	1289.5
22.5°	1238.7	1244.9	1248.0	1263.3	1266.4
25°	1206.4	1215.6	1220.3	1237.2	1238.7
27.5°	1171.0	1184.9	1191.0	1206.4	1207.9
30°	1135.6	1147.9	1158.7	1175.6	1178.7
32.5°	1097.2	1112.5	1124.9	1144.9	1147.9
35°	1055.6	1074.1	1089.5	1111.0	1115.6
37.5°	1014.1	1035.6	1054.1	1075.6	1080.2
40°	974.1	994.1	1015.6	1038.7	1044.8
42.5°	927.9	951.0	977.1	1003.3	1007.9
45°	880.2	909.4	938.7	964.8	972.5
47.5°	835.6	864.8	898.7	924.8	934.0
50°	786.3	820.2	854.0	884.8	894.0
52.5°	737.1	770.9	810.9	841.7	850.9
55°	689.4	721.7	767.9	798.6	807.9
57.5°	635.5	675.5	720.2	757.1	764.8
60°	583.2	623.2	674.0	709.4	721.7
62.5°	532.4	577.0	627.8	663.2	675.5
65°	477.0	526.3	578.6	617.1	629.4
67.5°	424.7	477.0	532.4	570.9	583.2
70°	370.8	423.2	481.6	523.2	534.0
72.5°	318.5	372.4	435.5	475.5	487.8
75°	264.7	321.6	386.2	429.3	443.2
77.5°	213.9	273.9	341.6	384.7	400.1
80°	167.7	229.3	297.0	343.1	355.5
82.5°	121.6	186.2	253.9	301.6	315.5
85°	81.6	146.2	215.4	261.6	277.0
87.5°	50.8	113.9	181.6	226.2	240.1
90°	26.8	96.5	168.5	217.6	231.3
92.5°	34.1	86.4	158.5	206.0	218.3
95°	60.4	86.2	150.1	196.0	210.6
97.5°	95.6	156.4	142.4	186.0	200.6
100°	137.3	190.5	149.2	178.3	189.9
102.5°	185.8	228.5	295.8	170.6	182.9
105°	234.8	270.0	330.7	375.7	361.6
107.5°	282.6	311.0	370.0	412.1	425.8
110°	329.5	353.3	411.5	448.4	462.9



TEST NUMBER: P1001061

CATALOG NUMBER: SA4XXDIP-B1195D810UB2750-4F0-XX-W2A-D_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	375.0	397.8	450.1	483.3	498.5
115°	421.9	438.0	486.5	521.8	532.5
117.5°	465.2	477.4	525.8	557.3	569.7
120°	507.8	515.3	559.2	591.4	602.3
122.5°	548.9	550.4	593.3	624.9	634.2
125°	586.3	587.6	624.7	656.1	666.1
127.5°	623.8	622.9	657.4	684.3	694.4
130°	658.1	657.4	684.2	712.6	721.8
132.5°	691.2	691.2	712.5	739.4	747.9
135°	722.7	722.0	735.6	761.8	772.5
137.5°	752.1	750.5	760.4	784.9	791.9
140°	780.7	780.6	783.7	805.9	814.3
142.5°	804.8	807.8	807.0	825.4	831.6
145°	831.3	832.0	832.0	841.9	849.6
147.5°	851.8	854.7	854.0	856.2	863.2
150°	874.6	876.0	875.3	875.3	876.0
152.5°	892.2	894.4	892.9	894.4	893.7
155°	909.8	910.6	908.3	911.3	909.1
157.5°	925.2	925.2	922.3	926.0	922.3
160°	938.5	936.3	935.5	939.9	935.5
162.5°	950.2	947.3	946.5	950.9	945.8
165°	959.8	956.1	956.1	962.0	955.3
167.5°	967.8	964.2	963.4	970.0	962.7
170°	974.4	970.0	970.8	976.6	969.3
172.5°	978.8	974.4	975.2	981.0	973.0
175°	981.8	977.4	978.1	984.7	975.9
177.5°	984.0	978.8	980.3	986.2	977.4
180°	981.8	981.8	981.8	981.8	981.8

(END OF REPORT)