

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001111

Luminaire Tested: SA4XXDIP-B350D1035UB27-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001111
REPORT IS A COMBINATION OF REPORTS P995727 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B350D1035UB27-4F0-XX-W2A-F4
Description: Define 4 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5104.3 lumens
Efficiency: N/A
Efficacy: 123.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 41.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001111

CATALOG NUMBER: SA4XXDIP-B350D1035UB27-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1001111

CATALOG NUMBER: SA4XXDIP-B350D1035UB27-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	37	37	37
1	93	89	85	82	83	80	76	74	62	60	58	47	45	44	32	31	31
2	85	77	72	67	76	70	65	60	55	51	48	41	39	37	28	27	26
3	77	68	61	55	69	61	55	50	48	44	41	36	33	31	25	23	22
4	70	60	52	47	63	54	48	43	43	38	34	32	29	27	22	21	19
5	65	53	46	40	58	48	41	36	38	33	30	29	26	23	20	18	16
6	59	48	40	34	53	43	36	31	34	29	26	26	23	20	18	16	14
7	55	43	35	30	49	39	32	27	31	26	22	24	20	18	17	14	13
8	51	39	31	26	45	35	29	24	28	23	20	21	18	16	15	13	11
9	47	35	28	23	42	32	26	21	26	21	18	20	16	14	14	12	10
10	44	32	25	21	39	29	23	19	24	19	16	18	15	13	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4648	4648	4648
5°	4652	4514	4520
10°	4612	4389	4359
15°	4546	4240	4176
20°	4461	4079	3988
25°	4367	3909	3784
30°	4252	3724	3561
35°	4134	3536	3346
40°	4010	3333	3116
45°	3879	3129	2902
50°	3736	2932	2665
55°	3580	2702	2429
60°	3420	2450	2184
65°	3238	2189	1907
70°	3025	1876	1611
75°	2712	1511	1289
80°	2311	1093	907
85°	1797	607	488

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3879 cd/sqm

TEST NUMBER: P1001111

CATALOG NUMBER: SA4XXDIP-B350D1035UB27-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.7	1.1
10°-20°	151.4	3.0
20°-30°	222.8	4.4
30°-40°	258.9	5.1
40°-50°	258.9	5.1
50°-60°	226.5	4.4
60°-70°	168.1	3.3
70°-80°	95.4	1.9
80°-90°	29.2	0.6
90°-100°	370.4	7.3
100°-110°	753.4	14.8
110°-120°	671.5	13.2
120°-130°	564.1	11.1
130°-140°	470.7	9.2
140°-150°	359.5	7.0
150°-160°	252.7	5.0
160°-170°	148.6	2.9
170°-180°	48.3	0.9
0°-30°	427.8	8.4
0°-40°	686.8	13.5
0°-60°	1172.2	23.0
0°-90°	1464.9	28.7
90°-120°	1795.4	35.2
90°-150°	3189.7	62.5
90°-180°	3639.0	71.3
0°-180°	5104.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	570	570	570	570	570	
5°	570	568	563	568	567	54
15°	542	540	534	536	535	153
25°	491	488	481	482	480	226
35°	422	419	413	410	407	264
45°	345	342	334	329	328	266
55°	261	259	253	248	245	234
65°	177	174	170	165	163	175
75°	94	92	90	88	87	100
85°	25	25	24	24	23	27
90°	1	8	18	20	21	4
95°	32	102	798	395	239	35
105°	115	166	643	1384	1378	122
115°	202	253	573	1101	1324	200
125°	281	334	570	937	1056	251
135°	334	398	565	832	944	258
145°	385	441	562	702	771	242
155°	438	473	547	619	646	202
165°	477	492	524	555	563	135
175°	498	499	503	510	508	47
180°	499	499	499	499	499	

TEST NUMBER: P1001111

CATALOG NUMBER: SA4XXDIP-B350D1035UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	570.0	570.0	570.0	570.0	570.0
2.5°	571.8	570.5	565.4	570.0	569.5
5°	569.5	567.7	562.7	567.7	566.8
7.5°	565.4	563.6	558.1	562.2	561.8
10°	559.5	557.7	551.7	555.4	554.5
12.5°	551.7	549.9	543.5	547.6	546.2
15°	542.1	540.3	533.5	536.2	534.8
17.5°	531.2	528.9	522.5	524.3	523.4
20°	518.8	516.6	509.7	511.1	510.2
22.5°	505.6	502.4	495.5	498.3	496.5
25°	491.0	487.8	481.4	481.8	480.0
27.5°	474.5	471.3	465.4	464.5	462.2
30°	458.1	454.4	448.5	446.7	444.4
32.5°	440.7	437.5	431.1	428.9	426.6
35°	422.5	419.3	412.9	409.7	407.4
37.5°	403.3	400.5	393.7	390.5	387.3
40°	384.6	380.9	374.1	369.5	367.2
42.5°	364.5	362.6	354.9	349.4	348.0
45°	344.8	341.6	334.3	329.3	327.9
47.5°	324.3	322.0	315.1	309.7	306.0
50°	303.3	301.4	295.0	288.7	285.9
52.5°	282.7	280.4	273.6	268.1	264.4
55°	260.8	259.4	253.0	247.5	244.8
57.5°	240.2	238.9	232.5	227.0	224.3
60°	218.8	216.5	210.6	206.4	204.2
62.5°	197.8	195.9	189.5	185.9	183.6
65°	176.8	174.5	169.9	165.3	163.1
67.5°	155.3	153.5	148.9	144.3	143.9
70°	135.6	132.5	128.8	125.1	123.8
72.5°	114.6	111.4	108.7	106.0	104.6
75°	94.1	91.8	89.5	87.7	87.2
77.5°	74.0	73.1	70.8	70.3	69.0
80°	56.2	54.8	53.9	53.0	52.5
82.5°	38.8	38.4	38.4	37.9	37.5
85°	24.7	24.7	23.7	23.7	23.3
87.5°	11.9	11.4	11.0	11.0	11.0
90°	1.0	7.8	17.6	19.6	20.6
92.5°	13.7	75.4	384.1	126.8	89.2
95°	32.3	101.9	798.5	395.3	239.1
97.5°	53.9	112.6	854.3	807.3	574.1
100°	74.5	127.4	787.7	1116.8	898.4
102.5°	94.1	145.0	704.4	1310.9	1180.6
105°	114.6	166.1	642.7	1383.9	1378.5
107.5°	137.2	187.6	602.5	1361.8	1472.5
110°	159.7	209.2	583.9	1283.4	1474.5

TEST NUMBER: P1001111

CATALOG NUMBER: SA4XXDIP-B350D1035UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	181.3	230.8	575.1	1187.4	1416.7
115°	201.8	253.2	573.1	1101.2	1323.6
117.5°	223.4	274.3	572.2	1033.6	1232.5
120°	244.9	294.9	572.2	988.0	1158.0
122.5°	264.5	315.0	571.2	958.2	1099.3
125°	281.2	334.1	570.2	937.2	1056.2
127.5°	296.9	351.7	568.2	917.0	1028.7
130°	309.6	368.9	567.3	893.0	1005.2
132.5°	322.3	383.6	566.3	864.6	978.8
135°	334.1	397.8	565.3	831.8	944.5
137.5°	345.8	410.0	565.3	796.6	904.3
140°	358.6	421.2	564.3	762.2	860.2
142.5°	372.3	431.6	564.3	730.4	813.2
145°	385.0	440.9	562.4	701.5	771.0
147.5°	399.7	449.7	559.4	677.5	731.9
150°	413.4	458.0	556.5	655.4	699.5
152.5°	426.2	465.8	551.6	636.8	670.1
155°	437.9	472.8	546.7	619.2	645.6
157.5°	449.7	479.1	541.8	602.5	623.1
160°	460.5	484.5	535.9	585.9	602.5
162.5°	470.3	488.9	530.0	569.7	582.9
165°	477.1	491.8	524.2	555.0	563.3
167.5°	485.0	494.2	518.3	542.3	547.7
170°	489.9	496.2	512.4	529.6	533.0
172.5°	494.8	497.7	506.5	518.3	518.3
175°	497.7	498.7	502.6	509.5	507.5
177.5°	499.7	498.7	499.7	503.1	499.7
180°	498.7	498.7	498.7	498.7	498.7

(END OF REPORT)